



LED Lamps – ideal for general lighting applications

LEDLamps

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

Benefits

- Color temperature suitable for both functional lighting and to enhance atmosphere
- Up to 80% energy savings compared with incandescent bulbs
- Suitable for retrofit
- Lower maintenance costs

Features

- Long lifetime
- UV- and IR-free light for less heat and protection of heat-sensitive objects
- Instant start

Application

- Homes, hotels, restaurants, cafes
- Bedroom, dining room, living room, study room

Versions



LED Sensor 8 60W B22 WH FR



LEDGlobe 10 75W G120 B22 WW
230V AU



LED Sensor A60 E27 WW POS1



LEDbulb CorePro 9.5-68W E27
Stick Frost 830 24D ND



LEDGlobe 7 60W G95 B22 WW
230V AU



LEDGlobe 10 75W G120 E27 WW
230V AU






LEDStick B22 AU



LEDGlobe 7 60W G95 E27 WW
230V AU




Dimensional drawing



Product	D	C
LEDGlobe 10-75W G120 B22 WW 230V_AU	120 mm	168 mm

Product	D	C
LEDBulb 10W E27 930 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 10W E27 930 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 10W E27 965 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 10W E27 965 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 12W E27 930 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 12W E27 930 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 12W E27 965 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 12W E27 965 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 6W E27 930 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 6W E27 930 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 6W E27 965 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 6W E27 965 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 8W E27 930 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 8W E27 930 230V 2PF/3 AU	60 mm	110 mm
LEDBulb 8W E27 965 230V 1PF/6 AU	60 mm	110 mm
LEDBulb 8W E27 965 230V 2PF/3 AU	60 mm	110 mm

Dimensional drawing







Product	D	C
LEDGlobe 7-60W G95 E27 WW 230V_AU	95 mm	137 mm

Product
LEDBulb 10W B22 930 230V 1PF/6 AU
LEDBulb 10W B22 930 230V 2PF/3 AU
LEDBulb 10W B22 965 230V 1PF/6 AU
LEDBulb 10W B22 965 230V 2PF/3 AU
LEDBulb 12W B22 930 230V 1PF/6 AU
LEDBulb 12W B22 930 230V 2PF/3 AU
LEDBulb 12W B22 965 230V 1PF/6 AU
LEDBulb 12W B22 965 230V 2PF/3 AU
LEDBulb 6W B22 930 230V 1PF/6 AU
LEDBulb 6W B22 930 230V 2PF/3 AU
LEDBulb 6W B22 965 230V 1PF/6 AU
LEDBulb 6W B22 965 230V 2PF/3 AU
LEDBulb 8W B22 930 230V 1PF/6 AU
LEDBulb 8W B22 930 230V 2PF/3 AU
LEDBulb 8W B22 965 230V 1PF/6 AU
LEDBulb 8W B22 965 230V 2PF/3 AU

Product	D	C
LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	62.5 mm	122 mm

Dimensional drawing




Product	D	C
LEDGlobe 7-60W G95 B22 WW 230V_AU	95 mm	135 mm

Product	D	C
LEDStick 9.5W B22 3000K 1PF/6 AU	37.2 mm	113 mm
LEDStick 9.5W B22 6500K 1PF/6 AU	37.2 mm	113 mm

Product	D	C
LED Sensor 8-60W B22 CDL FR 1PF/6 APR	62.5 mm	120 mm

Product	D	C
LEDStick 9.5W E27 6500K 1PF/6 AU	37.2 mm	114.3 mm

Dimensional drawing



Product	D	C
LEDGlobe 10-75W G120 E27 WW 230V_AU	120 mm	170 mm

General Information	
Rated Lifetime (Hours)	15,000 h
Switching Cycle	50,000
Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted

General Information

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929003006319	LEDBulb 6W E27 930 230V 2PF/3 AU	E27	25,000 h
929003006399	LEDBulb 6W E27 930 230V 1PF/6 AU	E27	25,000 h
929003006719	LEDBulb 6W E27 965 230V 2PF/3 AU	E27	25,000 h
929003006799	LEDBulb 6W E27 965 230V 1PF/6 AU	E27	25,000 h
929003006919	LEDBulb 8W E27 930 230V 2PF/3 AU	E27	25,000 h
929003006999	LEDBulb 8W E27 930 230V 1PF/6 AU	E27	25,000 h
929003007319	LEDBulb 8W E27 965 230V 2PF/3 AU	E27	25,000 h
929003007399	LEDBulb 8W E27 965 230V 1PF/6 AU	E27	25,000 h
929002400219	LED Sensor 8-60W B22 CDL FR 1PF/6 APR	B22	15,000 h
929002442369	LEDGlobe 10-75W G120 B22 WW 230V_AU	B22	15,000 h
929003007519	LEDBulb 10W E27 930 230V 2PF/3 AU	E27	25,000 h
929003007599	LEDBulb 10W E27 930 230V 1PF/6 AU	E27	25,000 h
929003007919	LEDBulb 10W E27 965 230V 2PF/3 AU	E27	25,000 h
929003007999	LEDBulb 10W E27 965 230V 1PF/6 AU	E27	25,000 h

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929003008119	LEDBulb 12W E27 930 230V 2PF/3 AU	E27	25,000 h
929003008199	LEDBulb 12W E27 930 230V 1PF/6 AU	E27	25,000 h
929003008519	LEDBulb 12W E27 965 230V 2PF/3 AU	E27	25,000 h
929003008599	LEDBulb 12W E27 965 230V 1PF/6 AU	E27	25,000 h
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	E27	15,000 h
929001901669	LEDStick 9.5W E27 6500K 1PF/6 AU	E27	15,000 h
929003006419	LEDBulb 6W B22 930 230V 2PF/3 AU	B22	25,000 h
929003006499	LEDBulb 6W B22 930 230V 1PF/6 AU	B22	25,000 h
929003006819	LEDBulb 6W B22 965 230V 2PF/3 AU	B22	25,000 h
929003006899	LEDBulb 6W B22 965 230V 1PF/6 AU	B22	25,000 h
929003007019	LEDBulb 8W B22 930 230V 2PF/3 AU	B22	25,000 h
929003007099	LEDBulb 8W B22 930 230V 1PF/6 AU	B22	25,000 h
929003007419	LEDBulb 8W B22 965 230V 2PF/3 AU	B22	25,000 h
929003007499	LEDBulb 8W B22 965 230V 1PF/6 AU	B22	25,000 h
929002442069	LEDGlobe 7-60W G95 B22 WW 230V_AU	B22	15,000 h

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929002442169	LEDGlobe 10-75W G120 E27 WW 230V_AU	E27	15,000 h
929001927069	LEDStick 9.5W B22 3000K 1PF/6 AU	B22	15,000 h
929001927269	LEDStick 9.5W B22 6500K 1PF/6 AU	B22	15,000 h
929002441669	LEDGlobe 7-60W G95 E27 WW 230V_AU	E27	15,000 h
929003007619	LEDBulb 10W B22 930 230V 2PF/3 AU	B22	25,000 h
929003007699	LEDBulb 10W B22 930 230V 1PF/6 AU	B22	25,000 h

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929003008019	LEDBulb 10W B22 965 230V 2PF/3 AU	B22	25,000 h
929003008099	LEDBulb 10W B22 965 230V 1PF/6 AU	B22	25,000 h
929003008219	LEDBulb 12W B22 930 230V 2PF/3 AU	B22	25,000 h
929003008299	LEDBulb 12W B22 930 230V 1PF/6 AU	B22	25,000 h
929003008619	LEDBulb 12W B22 965 230V 2PF/3 AU	B22	25,000 h
929003008699	LEDBulb 12W B22 965 230V 1PF/6 AU	B22	25,000 h

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux
929003006319	LEDBulb 6W E27 930 230V 2PF/3 AU	200 degree(s)	3000 K	90	930	700 lm
929003006399	LEDBulb 6W E27 930 230V 1PF/6 AU	200 degree(s)	3000 K	90	930	700 lm
929003006719	LEDBulb 6W E27 965 230V 2PF/3 AU	200 degree(s)	6500 K	90	965	700 lm
929003006799	LEDBulb 6W E27 965 230V 1PF/6 AU	200 degree(s)	6500 K	90	965	700 lm
929003006919	LEDBulb 8W E27 930 230V 2PF/3 AU	200 degree(s)	3000 K	90	930	910 lm
929003006999	LEDBulb 8W E27 930 230V 1PF/6 AU	200 degree(s)	3000 K	90	930	910 lm
929003007319	LEDBulb 8W E27 965 230V 2PF/3 AU	200 degree(s)	6500 K	90	965	910 lm
929003007399	LEDBulb 8W E27 965 230V 1PF/6 AU	200 degree(s)	6500 K	90	965	910 lm
929002400219	LED Sensor 8-60W B22 CDL FR 1PF/6 APR	280 degree(s)	6500 K	80	865	850 lm
929002442369	LEDGlobe 10-75W G120 B22 WW 230V_AU	150 degree(s)	2700 K	80	827	1,055 lm
929003007519	LEDBulb 10W E27 930 230V 2PF/3 AU	150 degree(s)	3000 K	90	930	1,150 lm
929003007599	LEDBulb 10W E27 930 230V 1PF/6 AU	150 degree(s)	3000 K	90	930	1,150 lm
929003007919	LEDBulb 10W E27 965 230V 2PF/3 AU	150 degree(s)	6500 K	90	965	1,150 lm
929003007999	LEDBulb 10W E27 965 230V 1PF/6 AU	150 degree(s)	6500 K	90	965	1,150 lm
929003008119	LEDBulb 12W E27 930 230V 2PF/3 AU	150 degree(s)	3000 K	90	930	1,360 lm
929003008199	LEDBulb 12W E27 930 230V 1PF/6 AU	150 degree(s)	3000 K	90	930	1,360 lm
929003008519	LEDBulb 12W E27 965 230V 2PF/3 AU	150 degree(s)	6500 K	90	965	1,360 lm
929003008599	LEDBulb 12W E27 965 230V 1PF/6 AU	150 degree(s)	6500 K	90	965	1,360 lm
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	280 degree(s)	6500 K	80	865	850 lm
929001901669	LEDStick 9.5W E27 6500K 1PF/6 AU	200 degree(s)	6500 K	80	865	1,050 lm
929003006419	LEDBulb 6W B22 930 230V 2PF/3 AU	200 degree(s)	3000 K	90	930	700 lm
929003006499	LEDBulb 6W B22 930 230V 1PF/6 AU	200 degree(s)	3000 K	90	930	700 lm
929003006819	LEDBulb 6W B22 965 230V 2PF/3 AU	200 degree(s)	6500 K	90	965	700 lm
929003006899	LEDBulb 6W B22 965 230V 1PF/6 AU	200 degree(s)	6500 K	90	965	700 lm
929003007019	LEDBulb 8W B22 930 230V 2PF/3 AU	200 degree(s)	3000 K	90	930	910 lm
929003007099	LEDBulb 8W B22 930 230V 1PF/6 AU	200 degree(s)	3000 K	90	930	910 lm
929003007419	LEDBulb 8W B22 965 230V 2PF/3 AU	200 degree(s)	6500 K	90	965	910 lm
929003007499	LEDBulb 8W B22 965 230V 1PF/6 AU	200 degree(s)	6500 K	90	965	910 lm
929002442069	LEDGlobe 7-60W G95 B22 WW 230V_AU	150 degree(s)	2700 K	80	827	806 lm
929002442169	LEDGlobe 10-75W G120 E27 WW 230V_AU	150 degree(s)	2700 K	80	827	1,055 lm
929001927069	LEDStick 9.5W B22 3000K 1PF/6 AU	200 degree(s)	3000 K	80	830	950 lm
929001927269	LEDStick 9.5W B22 6500K 1PF/6 AU	200 degree(s)	6500 K	80	865	1,050 lm
929002441669	LEDGlobe 7-60W G95 E27 WW 230V_AU	150 degree(s)	2700 K	80	827	806 lm
929003007619	LEDBulb 10W B22 930 230V 2PF/3 AU	150 degree(s)	3000 K	90	930	1,150 lm
929003007699	LEDBulb 10W B22 930 230V 1PF/6 AU	150 degree(s)	3000 K	90	930	1,150 lm
929003008019	LEDBulb 10W B22 965 230V 2PF/3 AU	150 degree(s)	6500 K	90	965	1,150 lm
929003008099	LEDBulb 10W B22 965 230V 1PF/6 AU	150 degree(s)	6500 K	90	965	1,150 lm
929003008219	LEDBulb 12W B22 930 230V 2PF/3 AU	150 degree(s)	3000 K	90	930	1,360 lm
929003008299	LEDBulb 12W B22 930 230V 1PF/6 AU	150 degree(s)	3000 K	90	930	1,360 lm
929003008619	LEDBulb 12W B22 965 230V 2PF/3 AU	150 degree(s)	6500 K	90	965	1,360 lm

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux
929003008699	LED Bulb 12W B22 965 230V 1PF/6 AU	150 degree(s)	6500 K	90	965	1,360 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Wattage Equivalent	Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929003006319	LED Bulb 6W E27 930 230V 2PF/3 AU	6 W	65 W	929003006499	LED Bulb 6W B22 930 230V 1PF/6 AU	6 W	65 W
929003006399	LED Bulb 6W E27 930 230V 1PF/6 AU	6 W	65 W	929003006819	LED Bulb 6W B22 965 230V 2PF/3 AU	6 W	65 W
929003006719	LED Bulb 6W E27 965 230V 2PF/3 AU	6 W	65 W	929003006899	LED Bulb 6W B22 965 230V 1PF/6 AU	6 W	65 W
929003006799	LED Bulb 6W E27 965 230V 1PF/6 AU	6 W	65 W	929003007019	LED Bulb 8W B22 930 230V 2PF/3 AU	8 W	76 W
929003006919	LED Bulb 8W E27 930 230V 2PF/3 AU	8 W	76 W	929003007099	LED Bulb 8W B22 930 230V 1PF/6 AU	8 W	76 W
929003006999	LED Bulb 8W E27 930 230V 1PF/6 AU	8 W	76 W	929003007419	LED Bulb 8W B22 965 230V 2PF/3 AU	8 W	76 W
929003007319	LED Bulb 8W E27 965 230V 2PF/3 AU	8 W	76 W	929003007499	LED Bulb 8W B22 965 230V 1PF/6 AU	8 W	76 W
929003007399	LED Bulb 8W E27 965 230V 1PF/6 AU	8 W	76 W	929002442069	LED Globe 7-60W G95 B22 WW 230V_AU	7 W	60 W
929002400219	LED Sensor 8-60W B22 CDL FR 1PF/6 APR	8 W	60 W	929002442169	LED Globe 10-75W G120 E27 WW 230V_AU	10 W	75 W
929002442369	LED Globe 10-75W G120 B22 WW 230V_AU	10 W	75 W	929001927069	LED Stick 9.5W B22 3000K 1PF/6 AU	9.5 W	68 W
929003007519	LED Bulb 10W E27 930 230V 2PF/3 AU	10 W	89 W	929001927269	LED Stick 9.5W B22 6500K 1PF/6 AU	9.5 W	75 W
929003007599	LED Bulb 10W E27 930 230V 1PF/6 AU	10 W	89 W	929002441669	LED Globe 7-60W G95 E27 WW 230V_AU	7 W	60 W
929003007919	LED Bulb 10W E27 965 230V 2PF/3 AU	10 W	89 W	929003007619	LED Bulb 10W B22 930 230V 2PF/3 AU	10 W	89 W
929003007999	LED Bulb 10W E27 965 230V 1PF/6 AU	10 W	89 W	929003007699	LED Bulb 10W B22 930 230V 1PF/6 AU	10 W	89 W
929003008119	LED Bulb 12W E27 930 230V 2PF/3 AU	12 W	98 W	929003008019	LED Bulb 10W B22 965 230V 2PF/3 AU	10 W	89 W
929003008199	LED Bulb 12W E27 930 230V 1PF/6 AU	12 W	98 W	929003008099	LED Bulb 10W B22 965 230V 1PF/6 AU	10 W	89 W
929003008519	LED Bulb 12W E27 965 230V 2PF/3 AU	12 W	98 W	929003008219	LED Bulb 12W B22 930 230V 2PF/3 AU	12 W	98 W
929003008599	LED Bulb 12W E27 965 230V 1PF/6 AU	12 W	98 W	929003008299	LED Bulb 12W B22 930 230V 1PF/6 AU	12 W	98 W
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	8 W	60 W	929003008619	LED Bulb 12W B22 965 230V 2PF/3 AU	12 W	98 W
929001901669	LED Stick 9.5W E27 6500K 1PF/6 AU	9.5 W	75 W	929003008699	LED Bulb 12W B22 965 230V 1PF/6 AU	12 W	98 W
929003006419	LED Bulb 6W B22 930 230V 2PF/3 AU	6 W	65 W				

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929003006319	LEDBulb 6W E27 930 230V 2PF/3 AU	85 °C
929003006399	LEDBulb 6W E27 930 230V 1PF/6 AU	85 °C
929003006719	LEDBulb 6W E27 965 230V 2PF/3 AU	85 °C
929003006799	LEDBulb 6W E27 965 230V 1PF/6 AU	85 °C
929003006919	LEDBulb 8W E27 930 230V 2PF/3 AU	95 °C
929003006999	LEDBulb 8W E27 930 230V 1PF/6 AU	95 °C
929003007319	LEDBulb 8W E27 965 230V 2PF/3 AU	95 °C
929003007399	LEDBulb 8W E27 965 230V 1PF/6 AU	95 °C
929002400219	LED Sensor 8-60W B22 CDL FR 1PF/6 APR	75 °C
929002442369	LEDGlobe 10-75W G120 B22 WW 230V_AU	50 °C
929003007519	LEDBulb 10W E27 930 230V 2PF/3 AU	90 °C
929003007599	LEDBulb 10W E27 930 230V 1PF/6 AU	90 °C
929003007919	LEDBulb 10W E27 965 230V 2PF/3 AU	90 °C
929003007999	LEDBulb 10W E27 965 230V 1PF/6 AU	90 °C
929003008119	LEDBulb 12W E27 930 230V 2PF/3 AU	95 °C
929003008199	LEDBulb 12W E27 930 230V 1PF/6 AU	95 °C
929003008519	LEDBulb 12W E27 965 230V 2PF/3 AU	95 °C
929003008599	LEDBulb 12W E27 965 230V 1PF/6 AU	95 °C
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	75 °C
929001901669	LEDStick 9.5W E27 6500K 1PF/6 AU	85 °C
929003006419	LEDBulb 6W B22 930 230V 2PF/3 AU	85 °C

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929003006319	LEDBulb 6W E27 930 230V 2PF/3 AU	A60S
929003006399	LEDBulb 6W E27 930 230V 1PF/6 AU	A60S
929003006719	LEDBulb 6W E27 965 230V 2PF/3 AU	A60S
929003006799	LEDBulb 6W E27 965 230V 1PF/6 AU	A60S
929003006919	LEDBulb 8W E27 930 230V 2PF/3 AU	A60S
929003006999	LEDBulb 8W E27 930 230V 1PF/6 AU	A60S
929003007319	LEDBulb 8W E27 965 230V 2PF/3 AU	A60S
929003007399	LEDBulb 8W E27 965 230V 1PF/6 AU	A60S
929002400219	LED Sensor 8-60W B22 CDL FR 1PF/6 APR	A60
929002442369	LEDGlobe 10-75W G120 B22 WW 230V_AU	G120
929003007519	LEDBulb 10W E27 930 230V 2PF/3 AU	A60M
929003007599	LEDBulb 10W E27 930 230V 1PF/6 AU	A60M
929003007919	LEDBulb 10W E27 965 230V 2PF/3 AU	A60M
929003007999	LEDBulb 10W E27 965 230V 1PF/6 AU	A60M
929003008119	LEDBulb 12W E27 930 230V 2PF/3 AU	A60M
929003008199	LEDBulb 12W E27 930 230V 1PF/6 AU	A60M
929003008519	LEDBulb 12W E27 965 230V 2PF/3 AU	A60M
929003008599	LEDBulb 12W E27 965 230V 1PF/6 AU	A60M
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	A60
929001901669	LEDStick 9.5W E27 6500K 1PF/6 AU	Stick
929003006419	LEDBulb 6W B22 930 230V 2PF/3 AU	A60S

Approval and Application

Order Code	Full Product Name	T-Case Maximum (Nom)
929003006499	LEDBulb 6W B22 930 230V 1PF/6 AU	85 °C
929003006819	LEDBulb 6W B22 965 230V 2PF/3 AU	85 °C
929003006899	LEDBulb 6W B22 965 230V 1PF/6 AU	85 °C
929003007019	LEDBulb 8W B22 930 230V 2PF/3 AU	95 °C
929003007099	LEDBulb 8W B22 930 230V 1PF/6 AU	95 °C
929003007419	LEDBulb 8W B22 965 230V 2PF/3 AU	95 °C
929003007499	LEDBulb 8W B22 965 230V 1PF/6 AU	95 °C
929002442069	LEDGlobe 7-60W G95 B22 WW 230V_AU	45 °C
929002442169	LEDGlobe 10-75W G120 E27 WW 230V_AU	50 °C
929001927069	LEDStick 9.5W B22 3000K 1PF/6 AU	85 °C
929001927269	LEDStick 9.5W B22 6500K 1PF/6 AU	85 °C
929002441669	LEDGlobe 7-60W G95 E27 WW 230V_AU	45 °C
929003007619	LEDBulb 10W B22 930 230V 2PF/3 AU	90 °C
929003007699	LEDBulb 10W B22 930 230V 1PF/6 AU	90 °C
929003008019	LEDBulb 10W B22 965 230V 2PF/3 AU	90 °C
929003008099	LEDBulb 10W B22 965 230V 1PF/6 AU	90 °C
929003008219	LEDBulb 12W B22 930 230V 2PF/3 AU	95 °C
929003008299	LEDBulb 12W B22 930 230V 1PF/6 AU	95 °C
929003008619	LEDBulb 12W B22 965 230V 2PF/3 AU	95 °C
929003008699	LEDBulb 12W B22 965 230V 1PF/6 AU	95 °C

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929003006319	LEDBulb 6W E27 930 230V 2PF/3 AU	-20 to +45 °C	-
929003006399	LEDBulb 6W E27 930 230V 1PF/6 AU	-20 to +45 °C	-
929003006719	LEDBulb 6W E27 965 230V 2PF/3 AU	-20 to +45 °C	-
929003006799	LEDBulb 6W E27 965 230V 1PF/6 AU	-20 to +45 °C	-
929003006919	LEDBulb 8W E27 930 230V 2PF/3 AU	-20 to +45 °C	-
929003006999	LEDBulb 8W E27 930 230V 1PF/6 AU	-20 to +45 °C	-
929003007319	LEDBulb 8W E27 965 230V 2PF/3 AU	-20 to +45 °C	-
929003007399	LEDBulb 8W E27 965 230V 1PF/6 AU	-20 to +45 °C	-
929002400219	LED Sensor 8-60W B22 CDL FR 1PF/6 APR	-20 to +30 °C	8 kWh
929002442369	LEDGlobe 10-75W G120 B22 WW 230V_AU	-20 to +45 °C	10 kWh
929003007519	LEDBulb 10W E27 930 230V 2PF/3 AU	-20 to +45 °C	-
929003007599	LEDBulb 10W E27 930 230V 1PF/6 AU	-20 to +45 °C	-
929003007919	LEDBulb 10W E27 965 230V 2PF/3 AU	-20 to +45 °C	-
929003007999	LEDBulb 10W E27 965 230V 1PF/6 AU	-20 to +45 °C	-
929003008119	LEDBulb 12W E27 930 230V 2PF/3 AU	-20 to +45 °C	-
929003008199	LEDBulb 12W E27 930 230V 1PF/6 AU	-20 to +45 °C	-
929003008519	LEDBulb 12W E27 965 230V 2PF/3 AU	-20 to +45 °C	-
929003008599	LEDBulb 12W E27 965 230V 1PF/6 AU	-20 to +45 °C	-
929002058619	LED Sensor 8-60W A60 E27 CDL FR ND 1PF/6	-20 to +30 °C	8 kWh
929001901669	LEDStick 9.5W E27 6500K 1PF/6 AU	-20 to +45 °C	10 kWh
929003006419	LEDBulb 6W B22 930 230V 2PF/3 AU	-20 to +45 °C	-
929003006499	LEDBulb 6W B22 930 230V 1PF/6 AU	-20 to +45 °C	-
929003006819	LEDBulb 6W B22 965 230V 2PF/3 AU	-20 to +45 °C	-
929003006899	LEDBulb 6W B22 965 230V 1PF/6 AU	-20 to +45 °C	-
929003007019	LEDBulb 8W B22 930 230V 2PF/3 AU	-20 to +45 °C	-

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929003007099	LEDBulb 8W B22 930 230V 1PF/6 AU	-20 to +45 °C	-
929003007419	LEDBulb 8W B22 965 230V 2PF/3 AU	-20 to +45 °C	-
929003007499	LEDBulb 8W B22 965 230V 1PF/6 AU	-20 to +45 °C	-
929002442069	LEDGlobe 7-60W G95 B22 WW 230V_AU	-20 to +45 °C	7 kWh
929002442169	LEDGlobe 10-75W G120 E27 WW 230V_AU	-20 to +45 °C	10 kWh
929001927069	LEDStick 9.5W B22 3000K 1PF/6 AU	-20 to +45 °C	10 kWh
929001927269	LEDStick 9.5W B22 6500K 1PF/6 AU	-20 to +45 °C	10 kWh
929002441669	LEDGlobe 7-60W G95 E27 WW 230V_AU	-20 to +45 °C	7 kWh
929003007619	LEDBulb 10W B22 930 230V 2PF/3 AU	-20 to +45 °C	-
929003007699	LEDBulb 10W B22 930 230V 1PF/6 AU	-20 to +45 °C	-
929003008019	LEDBulb 10W B22 965 230V 2PF/3 AU	-20 to +45 °C	-
929003008099	LEDBulb 10W B22 965 230V 1PF/6 AU	-20 to +45 °C	-
929003008219	LEDBulb 12W B22 930 230V 2PF/3 AU	-20 to +45 °C	-
929003008299	LEDBulb 12W B22 930 230V 1PF/6 AU	-20 to +45 °C	-
929003008619	LEDBulb 12W B22 965 230V 2PF/3 AU	-20 to +45 °C	-
929003008699	LEDBulb 12W B22 965 230V 1PF/6 AU	-20 to +45 °C	-

