



Classic LEDbulbs lamps for decorative lighting

Classic filament LEDbulbs

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

Features

- Heritage design with classic shape
- Designed to be seen, they look good on and off
- Perfect fit and high quality finishing
- High color rendering (CRI> 80) for vivid colors
- Environmentally friendly: contains no mercury or other hazardous substances

Application

- Perfect for decorative installations
- Domestic applications
- Hospitality: restaurants and hotels

Classic filament LEDbulbs

Versions



LEDbulb CLA A15 E27 CL



LEDclassic 60W A60 E27 CL
WGD90 SRT4 1




LED CLA 60W A60 B22 2700K FR
UE SRT4



LED CLA 60W A60 B22 4000K CL
EELA SRT AU



LEDclassic 15W G120 E27 gradient
POS3



LEDbulb 5,5A19 VIN 950 E26 CL G
SP DIM 1PF T20



CLA LEDbulb 60W E27 827 CL G93



LEDbulb MAS EU A60 E27 CL 4

Classic filament LEDbulbs

Versions



LEDbulb MAS EU A60 E27 CL 1



LEDclassic A60 E27 smoky POS2




LED classic E27 G120




LEDclassic T32 E27 smoky POS2



Bulb G95 230V 5W-25W 250lm
2000K E27 D



LEDbulb 5,5ST19 VIN 930 E26 CL
G SP D 1PF T20




LEDbulb classic-giant 40W E27
G200 GOLD DIM



LEDbulb CLA G16,5 E27 CL

Classic filament LEDbulbs

Versions



LEDclassic giant 28W E27 G200
GOLD ND




LEDclassic A95 E27 FR-POS2A



LEDbulb CLA A19 E27 CL



LED CLA 40W A60 B22 3000K CL
EELA SRT AU



LEDclassic G93 E27 POS2



LEDclassic 60W ST64 B22 CL
WGD90 SRT4 1



25W E27 G200




LED CLA 40W A60 B22 4000K CL
EELA SRT AU

Classic filament LEDbulbs


Versions



LEDclassic 15W ST64 E27 pink
POS3



LEDbulb 60W E26 A19 927 CL



LEDbulb MAS G120 E27 CL



LEDclassic 60W G93 B22 CL
WGD90 1PF 4 1



LEDbulb classic-giant 40W E27
T65 GOLD DIM



LEDbulb MAS EU A60 E27 CL 3



LED CLA 60W A60 B22 3000K CL
EELA SRT AU



LEDclassic CM A60 E27 CL POS2

Classic filament LEDbulbs

Versions




LEDclassic ST64 E27 smoky POS2



LEDbulb classic-giant 40W E27
A160 GOLD DIM




LEDclassic 60W G93 E27 CL
WGD90 1PF 4 1



LEDclassic A67 E27 CL 1-POS2A




LED classic 60W E27 WW G120 FR
ND SRT4-SPP



LEDclassic 60W A60 B22 CL
WGD90 SRT4 1



LEDbulb CLA A19 E26 FR



LEDbulb 4,4ST19 VIN 820 E26
Amber G D4 4PFT20

Classic filament LEDbulbs

Versions



LED classic A60 E27



LEDclassic giant 28W E27 A160
GOLD ND



LEDbulb CLA G125 E27 Mirror
Crown




LEDbulb G93 E27 smoky



25W E27 T65



LEDclassic 15W ST64 E27 gradient
POS3



25W E27 A160




LEDclassic 60W ST64 E27 CL
WGD90 SRT4 1

Classic filament LEDbulbs

Versions



LEDclassic 60W B22 2700K G120
D CL AU





LEDclassic 15W G93 E27 pink
POS3



LEDbulb MAS EU A60 E27 CL 2

Dimensional drawing







Product	D	C
LEDclassic 60W G93 2700K B22 D CL AU	95 mm	136 mm

Product	D	C
LEDclassic 11W A60 E27 smoky ND RFSRT4	60 mm	106 mm

Classic filament LEDbulbs

Dimensional drawing



Product	D	C
5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20	60 mm	105 mm
8A19/PER/UD/FR/G/E26/WGD 4/2PFT20	60 mm	105 mm
LED CLA 40W A60 E27 3000K CL EELA SRT AU	60 mm	105 mm
LED CLA 40W A60 E27 4000K CL EELA SRT AU	60 mm	105 mm
LED CLA 4W A60 E27 2700K FR UE SRT6	60 mm	104 mm
LED CLA 4W A60 E27 4000K FR UE SRT6	60 mm	104 mm
LED CLA 60W A60 E27 3000K CL EELA SRT AU	60 mm	105 mm
LED CLA 60W A60 E27 4000K CL EELA SRT AU	60 mm	105 mm
LED CLA 7.3W A60 E27 2700K FR UE SRT6	60 mm	104 mm
LED CLA 7.3W A60 E27 4000K FR UE SRT6	60 mm	104 mm
LED classic CM 50W A60 E27 WW CL D SRT4	60 mm	106 mm
LEDclassic 8W A19 E27 827 CL ND 1PF/10	60 mm	106 mm
LEDclassic 8W A19 E27 850 CL ND 1PF/10	60 mm	106 mm
LEDclassic 60W A60 2700K E27 D CL AU	60 mm	104 mm





Product	D	C
LED classic 60W G93 E27 WW CL ND RF 1PF4	95 mm	140 mm

Product	D	C
LEDclassic 60W ST64 2700K B22 D CL AU	64 mm	139 mm

Product	D	C
LED CLA 40W A60 B22 3000K CL EELA SRT AU	60 mm	105 mm
LED CLA 40W A60 B22 4000K CL EELA SRT AU	60 mm	105 mm
LED CLA 4W A60 B22 2700K FR UE SRT6	60 mm	102 mm
LED CLA 4W A60 B22 4000K FR UE SRT6	60 mm	102 mm
LED CLA 60W A60 B22 3000K CL EELA SRT AU	60 mm	105 mm
LED CLA 60W A60 B22 4000K CL EELA SRT AU	60 mm	105 mm
LED CLA 7.3W A60 B22 2700K FR UE SRT6	60 mm	102 mm
LED CLA 7.3W A60 B22 4000K FR UE SRT6	60 mm	102 mm
LEDclassic 60W A60 2700K B22 D CL AU	60 mm	103 mm

Classic filament LEDbulbs

Dimensional drawing



Product	D	C
LED classic-giant 28W E27 A160 GOLD ND	162 mm	293 mm
LED classic-giant 40W E27 A160 GOLD DIM	162 mm	293 mm
LED giant 20W E27 A160 1800K smoky D	162 mm	293 mm





Product	D	C
LED classic-giant 28W E27 G200 GOLD ND	202 mm	286 mm
LED classic-giant 40W E27 G200 GOLD DIM	202 mm	286 mm
LED giant 20W E27 G200 1800K smoky D	202 mm	286 mm

Product	D	C
LED classic 120W A67 E27 CDL FR ND 1SRT4	70 mm	121 mm
LED classic 120W A67 E27 CW CL ND 1SRT4	70 mm	121 mm
LED classic 120W A67 E27 CW FR NDRF1SRT4	70 mm	121 mm
LED classic 120W A67 E27 WW CL ND SRT4	70 mm	121 mm
LED classic 120W A67 E27 WW FR NDRFSRT4	70 mm	121 mm
LED classic 150W A67 E27 CDL FR ND 1SRT4	70 mm	121 mm
LED classic 150W A67 E27 CW CL ND 1SRT4	70 mm	121 mm
LED classic 150W A67 E27 CW FR ND 1SRT4	70 mm	121 mm
LED classic 150W A67 E27 WW FR NDRFSRT4	70 mm	121 mm

Product	D	C
LEDclassic 60W B22 2700K G120 D CL AU	124 mm	178 mm

Classic filament LEDbulbs

Dimensional drawing



Product	D	C
4.4ST19/VIN/820/AM/G/E26/D/T/SP4/2PF	64 mm	137 mm
5.5ST19/VIN/927/E26/CL/G/SP D 1PF T20	64 mm	137 mm
LED classic 25W ST64 E27 gradient D SRT	64 mm	140 mm
LED classic 25W ST64 E27 pink D SRT4	64 mm	140 mm
LEDclassic 60W ST64 2700K E27 D CL AU	64 mm	140 mm





Product	D	C
LEDClassic 35W ST64 E27 825 100-240VNDBR	64 mm	142 mm
LEDClassic 35W ST64 E27 825 WV ND 2CT	64 mm	142 mm

Product	D	C
LEDClassic 4.5W G16.5 E27 827 CLND1PF/10	52 mm	87 mm

Product	D	C
LED classic-giant 40W E27 T65 GOLD DIM	66 mm	273 mm
LED giant 20W E27 T65 1800K smoky D	66 mm	273 mm

Classic filament LEDbulbs

Dimensional drawing



Product	D	C
LED classic 150W A67 E27 WW CL ND 1SRT4	70 mm	128 mm





Product	D	C
LED classic 25W G93 E27 GOLD SP D SRT4	96 mm	143 mm
LED classic 25W G93 E27 pink D 1PF/4	95 mm	140 mm
LED classic 60W G93 E27 CW FR ND 1PF/4	95 mm	140 mm
LED classic 60W G93 E27 WW FR ND RFSRT4	95 mm	140 mm
LEDclassic 40W G93 E27 825 WV ND 2CT	95 mm	140 mm
LEDclassic 60W G93 2700K E27 D CL AU	95 mm	137 mm

Product	D	C
LED classic 100W A60 CW FR ND 1CT/10	60 mm	104 mm
LED classic 100W A60 CW FR ND RFRFSRT4	60 mm	104 mm
LED classic 100W A60 E27 CW FR ND 2SRT6	60 mm	104 mm
LED classic 100W A60 WW FR ND 1CT/10	60 mm	104 mm
LED classic 75W E27 CW A60 FR ND 1CT/10	60 mm	104 mm
LED classic 75W E27 WW A60 FR ND 1CT10	60 mm	104 mm
LEDclassic 100W A60 E27 WW FR NDRF2SRT6	60 mm	104 mm

Product	D	C
LED classic 200W A95 E27 CDL FR ND 1PF/4	95 mm	165 mm
LED classic 200W A95 E27 CW FR ND 1PF/4	95 mm	165 mm
LED classic 200W A95 E27 WW FR ND 1PF	95 mm	165 mm

Classic filament LEDbulbs

Dimensional drawing



Product	D	C
LED classic 11W G93 E27 smoky ND RF 1PF	95 mm	142 mm





Product	D	C
LEDClassic 4.5W A15 E27 827 CL ND 1PF/10	48 mm	89 mm

Product	D	C
LED classic 100W E27 CW G120 FR ND 1PF/6	125 mm	177 mm
LED classic 100W E27 WW G120 FR ND SRT4	125 mm	177 mm
LED classic 60W E27 WW G120 FR ND SRT4	125 mm	177 mm

Product	D	C
LED cla 120W G120 E27 WW FR ND RFSRT4	124 mm	177 mm
LED classic 120W G120 E27 CDL FRND 1PF/4	124 mm	177 mm
LED classic 120W G120 E27 CW FR ND 1PF/4	124 mm	177 mm
LED classic 25W G120 E27 gradient D 1PF	125 mm	178 mm
LED classic 50W G120 E27 WW CM D RF	125 mm	180 mm
LED classic 75W G120 E27 WW FR ND SRT4	125 mm	177 mm
LEDclassic 60W E27 2700K G120 D CL AU	124 mm	178 mm

Classic filament LEDbulbs

Dimensional drawing



Product	D	C
LEDclassic 11W ST64 E27 smoky ND RFSRT4	64 mm	143 mm


Product	D	C
LED classic 11W T32 E27 smoky ND RFSRT4	32 mm	140 mm

Product	D	C
8A19/PER/927-922/CL/G/E26/WGX 1FB T20	60 mm	108 mm

Product	D	C
LEDClassic 35W A60 E27 825 100-240V NDBR	60 mm	106 mm
LEDClassic 40W A60 E27 825 WV ND 2CT	60 mm	106 mm

Classic filament LEDbulbs

Dimensional drawing



Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Starting Time (Nom)	0.5 s

Product	D	C
LED classic 25W ST64 E27GOLD SP D RFSRT4	65 mm	143 mm
LED classic 5.5W ST64 E27GOLD SP D 1PF/6	64 mm	140 mm

General Information

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Switching Cycle	Nominal lifetime
929002355642	LEDClassic 4.5W A15 E27 827 CL ND 1PF/10	E27	-	20,000	15,000 hour(s)
929002223944	LED classic 5.5W ST64 E27GOLD SP D 1PF/6	E27	-	20,000	15,000 hour(s)
929002982901	LED classic 25W ST64 E27GOLD SP D RFSRT4	E27	15,000	20,000	15,000 hour(s)
929002371801	LED classic 120W A67 E27 WW FR NDRFSRT4	E27	15,000	20,000	15,000 hour(s)
929002371901	LED classic 120W A67 E27 CW FR NDRF1SRT4	E27	15,000	20,000	15,000 hour(s)
929002372001	LED classic 120W A67 E27 CDL FR ND 1SRT4	E27	15,000	20,000	15,000 hour(s)
929002372601	LED classic 150W A67 E27 WW FR NDRFSRT4	E27	15,000	20,000	15,000 hour(s)
929002372701	LED classic 150W A67 E27 CW FR ND 1SRT4	E27	15,000	20,000	15,000 hour(s)
929002372801	LED classic 150W A67 E27 CDL FR ND 1SRT4	E27	15,000	20,000	15,000 hour(s)
929003010379	LEDclassic 60W A60 2700K E27 D CL AU	E27	15,000	20,000	15,000 hour(s)
929003623819	LED CLA 4W A60 B22 2700K FR UE SRT6	B22	-	50,000	50,000 hour(s)
929003624219	LED CLA 4W A60 B22 4000K FR UE SRT6	B22	-	50,000	50,000 hour(s)
929003625419	LED CLA 7.3W A60 B22 2700K FR UE SRT6	B22	-	50,000	50,000 hour(s)

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Switching Cycle	Nominal lifetime
929003625819	LED CLA 7.3W A60 B22 4000K FR UE SRT6	B22	-	50,000	50,000 hour(s)
929003540019	LED CLA 60W A60 B22 4000K CL EELA SRT AU	B22	50,000	50,000	50,000 hour(s)
929002454101	LED classic 25W G120 E27 gradient D 1PF	E27	15,000	20,000	15,000 hour(s)
929001941548	LEDClassic 40W A60 E27 825 WV ND 2CT	E27	-	20,000	15,000 hour(s)
929001941586	LEDClassic 35W A60 E27 825 100-240V NDBR	E27	-	20,000	15,000 hour(s)
929002370801	LED classic 60W G93 E27 WW FR ND RFSRT4	E27	15,000	20,000	15,000 hour(s)
929002370901	LED classic 60W G93 E27 CW FR ND 1PF/4	E27	15,000	20,000	15,000 hour(s)
929002988503	5.5A19/VIN/927/E26/CL/ G/SP DIM 1PF T20	E26	-	20,000	15,000 hour(s)
929001387901	LED classic 60W G93 E27 WW CL ND RF 1PF4	E27	15,000	20,000	15,000 hour(s)
929003066819	LED CLA 60W A60 E27 4000K CL EELA SRT AU	E27	50,000	50,000	50,000 hour(s)
929003066419	LED CLA 40W A60 E27 3000K CL EELA SRT AU	E27	50,000	50,000	50,000 hour(s)
929002026431	LED classic 100W A60 WW FR ND 1CT/10	E27	15,000	20,000	15,000 hour(s)
929002026457	LEDclassic 100W A60 E27 WW FR NDRF2SRT6	E27	15,000	20,000	15,000 hour(s)

Classic filament LEDbulbs

Order Code	Full Product Name	Cap-Base	Rated		
			Lifetime (Hours)	Switching Cycle	Nominal lifetime
929002026531	LED classic 100W A60 CW FR ND 1CT/10	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002026557	LED classic 100W A60 E27 CW FR ND 2SRT6	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002026596	LED classic 100W A60 CW FR ND RFRFSRT4	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002380501	LEDclassic 11W A60 E27 smoky ND RFSRT4	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002067801	LED classic 100W E27 WW G120 FR ND SRT4	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002067901	LED classic 100W E27 CW G120 FR ND 1PF/6	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002380701	LED classic 11W T32 E27 smoky ND RFSRT4	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002983001	LED classic 25W G93 E27 GOLD SP D SRT4	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002989003	5.5ST19/VIN/927/E26/CL /G/SP D 1PF T20	E26	-	20,000	15,000 hour(s)
929002983601	LED classic-giant 40W E27 G200 GOLD DIM	E27	15,000 hour(s)	20,000	15,000 hour(s)
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	E27	-	50,000	50,000 hour(s)
929003624119	LED CLA 4W A60 E27 4000K FR UE SRT6	E27	-	50,000	50,000 hour(s)
929003625319	LED CLA 7.3W A60 E27 2700K FR UE SRT6	E27	-	50,000	50,000 hour(s)
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	E27	-	50,000	50,000 hour(s)
929002355542	LEDClassic 4.5W G16.5 E27 827 CLND1PF/10	E27	-	20,000	15,000 hour(s)
929002983901	LED classic-giant 28W E27 G200 GOLD ND	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002372901	LED classic 200W A95 E27 WW FR ND 1PF	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002373001	LED classic 200W A95 E27 CW FR ND 1PF/4	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002373101	LED classic 200W A95 E27 CDL FR ND 1PF/4	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002355042	LEDClassic 8W A19 E27 827 CL ND 1PF/10	E27	-	20,000	15,000 hour(s)
929003068142	LEDClassic 8W A19 E27 850 CL ND 1PF/10	E27	-	20,000	15,000 hour(s)
929003539719	LED CLA 40W A60 B22 3000K CL EELA SRT AU	B22	50,000 hour(s)	50,000	50,000 hour(s)
929001948248	LEDClassic 40W G93 E27 825 WV ND 2CT	E27	-	20,000	15,000 hour(s)
929003010879	LEDclassic 60W ST64 2700K B22 D CL AU	B22	15,000 hour(s)	20,000	15,000 hour(s)
929002371101	LED classic 75W G120 E27 WW FR ND SRT4	E27	15,000 hour(s)	20,000	15,000 hour(s)

Order Code	Full Product Name	Cap-Base	Rated		
			Lifetime (Hours)	Switching Cycle	Nominal lifetime
929002372101	LED cla 120W G120 E27 WW FR ND RFSRT4	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002372201	LED classic 120W G120 E27 CW FR ND 1PF/4	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002372301	LED classic 120W G120 E27 CDL FRND 1PF/4	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002982601	LED giant 20W E27 G200 1800K smoky D	E27	15,000 hour(s)	20,000	15,000 hour(s)
929003539819	LED CLA 40W A60 B22 4000K CL EELA SRT AU	B22	50,000 hour(s)	50,000	50,000 hour(s)
929002453701	LED classic 25W ST64 E27 pink D SRT4	E27	15,000 hour(s)	20,000	15,000 hour(s)
929001969604	8A19/PER/ 927-922/CL/G/E26/WGX 1FB T20	E26	15,000 hour(s)	20,000	15,000 hour(s)
929003059379	LEDclassic 60W E27 2700K G120 D CL AU	E27	15,000 hour(s)	20,000	15,000 hour(s)
929003011079	LEDclassic 60W G93 2700K B22 D CL AU	B22	15,000 hour(s)	20,000	15,000 hour(s)
929002983701	LED classic-giant 40W E27 T65 GOLD DIM	E27	15,000 hour(s)	20,000	15,000 hour(s)
929003066719	LED CLA 60W A60 E27 3000K CL EELA SRT AU	E27	50,000 hour(s)	50,000	50,000 hour(s)
929003539919	LED CLA 60W A60 B22 3000K CL EELA SRT AU	B22	50,000 hour(s)	50,000	50,000 hour(s)
929002412801	LED classic CM 50W A60 E27 WW CL D SRT4	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002380601	LEDclassic 11W ST64 E27 smoky ND RFSRT4	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002371501	LED classic 120W A67 E27 WW CL ND SRT4	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002371601	LED classic 120W A67 E27 CW CL ND 1SRT4	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002983501	LED classic-giant 40W E27 A160 GOLD DIM	E27	15,000 hour(s)	20,000	15,000 hour(s)
929003010979	LEDclassic 60W G93 2700K E27 D CL AU	E27	15,000 hour(s)	20,000	15,000 hour(s)
929001941648	LEDClassic 35W ST64 E27 825 WV ND 2CT	E27	-	20,000	15,000 hour(s)
929001941686	LEDClassic 35W ST64 E27 825 100-240VNDDBR	E27	-	20,000	15,000 hour(s)
929002055055	LED classic 150W A67 E27 WW CL ND 1SRT4	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002372401	LED classic 150W A67 E27 CW CL ND 1SRT4	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002025201	LED classic 60W E27 WW G120 FR ND SRT4	E27	15,000 hour(s)	20,000	15,000 hour(s)
929003010579	LEDclassic 60W A60 2700K B22 D CL AU	B22	15,000 hour(s)	20,000	15,000 hour(s)

Classic filament LEDbulbs

Order Code	Full Product Name	Cap-Base	Rated		
			Lifetime (Hours)	Switching Cycle	Nominal lifetime
929003083203	8A19/PER/UD/FR/G/E26 /WGD 4/2PFT20	E26	15,000 hour(s)	20,000	15,000 hour(s)
929002990303	4.4ST19/VIN/820/AM/G/E26/D/T/SP4/2PF	E26	-	20,000	15,000 hour(s)
929002025731	LED classic 75W E27 WW A60 FR ND 1CT10	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002025831	LED classic 75W E27 CW A60 FR ND 1CT/10	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002983801	LED classic-giant 28W E27 A160 GOLD ND	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002412901	LED classic 50W G120 E27 WW CM D RF	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002380801	LED classic 11W G93 E27 smoky ND RF 1PF	E27	15,000 hour(s)	20,000	15,000 hour(s)

Order Code	Full Product Name	Cap-Base	Rated		
			Lifetime (Hours)	Switching Cycle	Nominal lifetime
929002982701	LED giant 20W E27 T65 1800K smoky D	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002454001	LED classic 25W ST64 E27 gradient D SRT	E27	15,000 hour(s)	20,000	15,000 hour(s)
929002982501	LED giant 20W E27 A160 1800K smoky D	E27	15,000 hour(s)	20,000	15,000 hour(s)
929003010779	LEDclassic 60W ST64 2700K E27 D CL AU	E27	15,000 hour(s)	20,000	15,000 hour(s)
929003100779	LEDclassic 60W B22 2700K G120 D CL AU	B22	15,000 hour(s)	20,000	15,000 hour(s)
929002453801	LED classic 25W G93 E27 pink D 1PF/4	E27	15,000 hour(s)	20,000	15,000 hour(s)
929003066519	LED CLA 40W A60 E27 4000K CL EELA SRT AU	E27	50,000 hour(s)	50,000	50,000 hour(s)

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index (CRI)		Color Code	Luminous Flux
929002355642	LEDClassic 4.5W A15 E27 827 CL ND 1PF/10	-	2700 K	80		827	500 lm
929002223944	LED classic 5.5W ST64 E27GOLD SP D 1PF/6	330 degree(s)	2000 K	80		820	250 lm
929002982901	LED classic 25W ST64 E27GOLD SP D RFSRT4	330 degree(s)	1800 K	80		818	250 lm
929002371801	LED classic 120W A67 E27 WW FR NDRFSRT4	-	2700 K	80		827	2,000 lm
929002371901	LED classic 120W A67 E27 CW FR NDRFISRT4	-	4000 K	80		840	2,000 lm
929002372001	LED classic 120W A67 E27 CDL FR ND 1SRT4	-	6500 K	80		865	2,000 lm
929002372601	LED classic 150W A67 E27 WW FR NDRFSRT4	-	2700 K	80		827	2,452 lm
929002372701	LED classic 150W A67 E27 CW FR ND 1SRT4	-	4000 K	80		840	2,452 lm
929002372801	LED classic 150W A67 E27 CDL FR ND 1SRT4	-	6500 K	80		865	2,452 lm
929003010379	LEDclassic 60W A60 2700K E27 D CL AU	-	2700 K	90		927	806 lm
929003623819	LED CLA 4W A60 B22 2700K FR UE SRT6	300 degree(s)	2700 K	80		827	840 lm
929003624219	LED CLA 4W A60 B22 4000K FR UE SRT6	300 degree(s)	4000 K	80		840	840 lm
929003625419	LED CLA 7.3W A60 B22 2700K FR UE SRT6	300 degree(s)	2700 K	80		827	1,535 lm
929003625819	LED CLA 7.3W A60 B22 4000K FR UE SRT6	300 degree(s)	4000 K	80		840	1,535 lm
929003540019	LED CLA 60W A60 B22 4000K CL EELA SRT AU	-	4000 K	80		840	840 lm
929002454101	LED classic 25W G120 E27 gradient D 1PF	-	1800 K	80		818	250 lm
929001941548	LEDClassic 40W A60 E27 825 WV ND 2CT	280 degree(s)	2500 K	80		825	400 lm
929001941586	LEDClassic 35W A60 E27 825 100-240V NDBR	-	2500 K	80		825	400 lm
929002370801	LED classic 60W G93 E27 WW FR ND RFSRT4	-	2700 K	80		827	806 lm
929002370901	LED classic 60W G93 E27 CW FR ND 1PF/4	-	4000 K	80		840	806 lm
929002988503	5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20	330 degree(s)	2700 K	90		927	500 lm
929001387901	LED classic 60W G93 E27 WW CL ND RF 1PF4	-	2700 K	80		827	806 lm
929003066819	LED CLA 60W A60 E27 4000K CL EELA SRT AU	-	4000 K	80		840	840 lm
929003066419	LED CLA 40W A60 E27 3000K CL EELA SRT AU	-	3000 K	80		830	485 lm
929002026431	LED classic 100W A60 WW FR ND 1CT/10	-	2700 K	80		827	1,521 lm
929002026457	LEDclassic 100W A60 E27 WW FR NDRF2SRT6	-	2700 K	80		827	1,521 lm
929002026531	LED classic 100W A60 CW FR ND 1CT/10	-	4000 K	80		840	1,521 lm
929002026557	LED classic 100W A60 E27 CW FR ND 2SRT6	-	4000 K	80		840	1,521 lm
929002026596	LED classic 100W A60 CW FR ND RFRFSRT4	-	4000 K	80		840	1,521 lm
929002380501	LEDclassic 11W A60 E27 smoky ND RFSRT4	-	1800 K	80		818	100 lm
929002067801	LED classic 100W E27 WW G120 FR ND SRT4	-	2700 K	80		827	1,521 lm

Classic filament LEDbulbs

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index		Color Code	Luminous Flux
				(CRI)			
929002067901	LED classic 100W E27 CW G120 FR ND 1PF/6	-	4000 K	80		840	1,521 lm
929002380701	LED classic 11W T32 E27 smoky ND RFSRT4	-	1800 K	80		818	100 lm
929002983001	LED classic 25W G93 E27 GOLD SP D SRT4	330 degree(s)	1800 K	80		818	250 lm
929002989003	5.5ST19/VIN/927/E26/CL/G/SP D 1PF T20	330 degree(s)	2700 K	90		927	500 lm
929002983601	LED classic-giant 40W E27 G200 GOLD DIM	330 degree(s)	1800 K	80		818	470 lm
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	300 degree(s)	2700 K	80		827	840 lm
929003624119	LED CLA 4W A60 E27 4000K FR UE SRT6	300 degree(s)	4000 K	80		840	840 lm
929003625319	LED CLA 7.3W A60 E27 2700K FR UE SRT6	300 degree(s)	2700 K	80		827	1,535 lm
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	300 degree(s)	4000 K	80		840	1,535 lm
929002355542	LEDClassic 4.5W G16.5 E27 827 CLND1PF/10	-	2700 K	80		827	500 lm
929002983901	LED classic-giant 28W E27 G200 GOLD ND	330 degree(s)	1800 K	80		818	300 lm
929002372901	LED classic 200W A95 E27 WW FR ND 1PF	-	2700 K	80		827	3,452 lm
929002373001	LED classic 200W A95 E27 CW FR ND 1PF/4	-	4000 K	80		840	3,452 lm
929002373101	LED classic 200W A95 E27 CDL FR ND 1PF/4	-	6500 K	80		865	3,452 lm
929002355042	LEDClassic 8W A19 E27 827 CL ND 1PF/10	-	2700 K	80		827	800 lm
929003068142	LEDClassic 8W A19 E27 850 CL ND 1PF/10	-	5000 K	80		850	800 lm
929003539719	LED CLA 40W A60 B22 3000K CL EELA SRT AU	-	3000 K	80		830	485 lm
929001948248	LEDClassic 40W G93 E27 825 WV ND 2CT	280 degree(s)	2500 K	80		825	400 lm
929003010879	LEDclassic 60W ST64 2700K B22 D CL AU	-	2700 K	90		927	806 lm
929002371101	LED classic 75W G120 E27 WW FR ND SRT4	-	2700 K	80		827	1,055 lm
929002372101	LED cla 120W G120 E27 WW FR ND RFSRT4	-	2700 K	80		827	2,000 lm
929002372201	LED classic 120W G120 E27 CW FR ND 1PF/4	-	4000 K	80		840	2,000 lm
929002372301	LED classic 120W G120 E27 CDL FRND 1PF/4	-	6500 K	80		865	2,000 lm
929002982601	LED giant 20W E27 G200 1800K smoky D	300 degree(s)	1800 K	80		818	200 lm
929003539819	LED CLA 40W A60 B22 4000K CL EELA SRT AU	-	4000 K	80		840	485 lm
929002453701	LED classic 25W ST64 E27 pink D SRT4	-	1800 K	80		818	250 lm
929001969604	8A19/PER/927-922/CL/G/E26/WGX 1FB T20	300 degree(s)	2700 K	90		927-922	800 lm
929003059379	LEDclassic 60W E27 2700K G120 D CL AU	-	2700 K	90		927	806 lm
929003011079	LEDclassic 60W G93 2700K B22 D CL AU	-	2700 K	90		927	806 lm
929002983701	LED classic-giant 40W E27 T65 GOLD DIM	330 degree(s)	1800 K	80		818	470 lm
929003066719	LED CLA 60W A60 E27 3000K CL EELA SRT AU	-	3000 K	80		830	840 lm
929003539919	LED CLA 60W A60 B22 3000K CL EELA SRT AU	-	3000 K	80		830	840 lm
929002412801	LED classic CM 50W A60 E27 WW CL D SRT4	270 degree(s)	2700 K	80		827	650 lm
929002380601	LEDclassic 11W ST64 E27 smoky ND RFSRT4	-	1800 K	80		818	100 lm
929002371501	LED classic 120W A67 E27 WW CL ND SRT4	-	2700 K	80		827	2,000 lm
929002371601	LED classic 120W A67 E27 CW CL ND 1SRT4	-	4000 K	80		840	2,000 lm
929002983501	LED classic-giant 40W E27 A160 GOLD DIM	330 degree(s)	1800 K	80		818	470 lm
929003010979	LEDclassic 60W G93 2700K E27 D CL AU	-	2700 K	90		927	806 lm
929001941648	LEDClassic 35W ST64 E27 825 WV ND 2CT	280 degree(s)	2500 K	80		825	400 lm
929001941686	LEDClassic 35W ST64 E27 825 100-240VNDDBR	-	2500 K	80		825	400 lm
929002055055	LED classic 150W A67 E27 WW CL ND 1SRT4	-	2700 K	80		827	2,452 lm
929002372401	LED classic 150W A67 E27 CW CL ND 1SRT4	-	4000 K	80		840	2,452 lm
929002025201	LED classic 60W E27 WW G120 FR ND SRT4	-	2700 K	80		827	806 lm
929003010579	LEDclassic 60W A60 2700K B22 D CL AU	-	2700 K	90		927	806 lm
929003083203	8A19/PER/UD/FR/G/E26/WGD 4/2PFT20	300 degree(s)	2200 K	95		922-927	800 lm
929002990303	4.4ST19/VIN/820/AM/G/E26/D/T/SP4/2PF	300 degree(s)	2000 K	80		820	300 lm
929002025731	LED classic 75W E27 WW A60 FR ND 1CT10	-	2700 K	80		827	1,055 lm
929002025831	LED classic 75W E27 CW A60 FR ND 1CT/10	-	4000 K	80		840	1,055 lm
929002983801	LED classic-giant 28W E27 A160 GOLD ND	330 degree(s)	1800 K	80		818	300 lm
929002412901	LED classic 50W G120 E27 WW CM D RF	270 degree(s)	2700 K	80		827	650 lm
929002380801	LED classic 11W G93 E27 smoky ND RF 1PF	-	1800 K	80		818	100 lm

Classic filament LEDbulbs

Order Code	Full Product Name	Beam Angle (Nom)	Color rendering index			Luminous Flux
			Correlated Color Temperature (Nom)	(CRI)	Color Code	
929002982701	LED giant 20W E27 T65 1800K smoky D	300 degree(s)	1800 K	80	818	200 lm
929002454001	LED classic 25W ST64 E27 gradient D SRT	-	1800 K	80	818	250 lm
929002982501	LED giant 20W E27 A160 1800K smoky D	-	1800 K	80	818	200 lm
929003010779	LEDclassic 60W ST64 2700K E27 D CL AU	-	2700 K	90	927	806 lm
929003100779	LEDclassic 60W B22 2700K G120 D CL AU	-	2700 K	90	927	806 lm
929002453801	LED classic 25W G93 E27 pink D 1PF/4	-	1800 K	80	818	250 lm
929003066519	LED CLA 40W A60 E27 4000K CL EELA SRT AU	-	4000 K	80	840	485 lm

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929002355642	LEDClassic 4.5W A15 E27 827 CL ND 1PF/10	60 Hz	60 Hz	4.5 W	40 W
929002223944	LED classic 5.5W ST64 E27GOLD SP D 1PF/6	50 to 60 Hz	50 to 60 Hz	5.5 W	25 W
929002982901	LED classic 25W ST64 E27GOLD SP D RFSRT4	50 to 60 Hz	50 to 60 Hz	4 W	25 W
929002371801	LED classic 120W A67 E27 WW FR NDRFSRT4	50 to 60 Hz	50 to 60 Hz	13 W	120 W
929002371901	LED classic 120W A67 E27 CW FR NDRF1SRT4	50 to 60 Hz	50 to 60 Hz	13 W	120 W
929002372001	LED classic 120W A67 E27 CDL FR ND 1SRT4	50 to 60 Hz	50 to 60 Hz	13 W	120 W
929002372601	LED classic 150W A67 E27 WW FR NDRFSRT4	50 to 60 Hz	50 to 60 Hz	17.5 W	150 W
929002372701	LED classic 150W A67 E27 CW FR ND 1SRT4	50 to 60 Hz	50 to 60 Hz	17.5 W	150 W
929002372801	LED classic 150W A67 E27 CDL FR ND 1SRT4	50 to 60 Hz	50 to 60 Hz	17.5 W	150 W
929003010379	LEDclassic 60W A60 2700K E27 D CL AU	50 to 60 Hz	-	6 W	60 W
929003623819	LED CLA 4W A60 B22 2700K FR UE SRT6	50 to 60 Hz	-	4 W	60 W
929003624219	LED CLA 4W A60 B22 4000K FR UE SRT6	50 to 60 Hz	-	4 W	60 W
929003625419	LED CLA 7.3W A60 B22 2700K FR UE SRT6	50 to 60 Hz	-	7.3 W	100 W
929003625819	LED CLA 7.3W A60 B22 4000K FR UE SRT6	50 to 60 Hz	-	7.3 W	100 W
929003540019	LED CLA 60W A60 B22 4000K CL EELA SRT AU	50 to 60 Hz	-	4 W	60 W
929002454101	LED classic 25W G120 E27 gradient D 1PF	50 to 60 Hz	50 to 60 Hz	4.5 W	25 W
929001941548	LEDClassic 40W A60 E27 825 WV ND 2CT	50 to 60 Hz	50 to 60 Hz	4 W	35 W
929001941586	LEDClassic 35W A60 E27 825 100-240V NDBR	50 to 60 Hz	50 to 60 Hz	4 W	35 W
929002370801	LED classic 60W G93 E27 WW FR ND RFSRT4	50 to 60 Hz	50 to 60 Hz	7 W	60 W
929002370901	LED classic 60W G93 E27 CW FR ND 1PF/4	50 to 60 Hz	50 to 60 Hz	7 W	60 W
929002988503	5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20	60 Hz	-	5.5 W	40 W
929001387901	LED classic 60W G93 E27 WW CL ND RF 1PF4	50 to 60 Hz	50 to 60 Hz	7 W	60 W
929003066819	LED CLA 60W A60 E27 4000K CL EELA SRT AU	50 to 60 Hz	-	4 W	60 W
929003066419	LED CLA 40W A60 E27 3000K CL EELA SRT AU	50 to 60 Hz	-	2.3 W	40 W
929002026431	LED classic 100W A60 WW FR ND 1CT/10	50 to 60 Hz	50 to 60 Hz	10.5 W	100 W
929002026457	LEDclassic 100W A60 E27 WW FR NDRF2SRT6	50 to 60 Hz	50 to 60 Hz	10.5 W	100 W

Classic filament LEDbulbs

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929002026531	LED classic 100W A60 CW FR ND 1CT/10	50 to 60 Hz	50 to 60 Hz	10.5 W	100 W
929002026557	LED classic 100W A60 E27 CW FR ND 2SRT6	50 to 60 Hz	50 to 60 Hz	10.5 W	100 W
929002026596	LED classic 100W A60 CW FR ND RFRFSRT4	50 to 60 Hz	50 to 60 Hz	10.5 W	100 W
929002380501	LEDclassic 11W A60 E27 smoky ND RFSRT4	50 to 60 Hz	50 to 60 Hz	2.3 W	11 W
929002067801	LED classic 100W E27 WW G120 FR ND SRT4	50 to 60 Hz	50 to 60 Hz	10.5 W	100 W
929002067901	LED classic 100W E27 CW G120 FR ND 1PF/6	50 to 60 Hz	50 to 60 Hz	10.5 W	100 W
929002380701	LED classic 11W T32 E27 smoky ND RFSRT4	50 to 60 Hz	50 to 60 Hz	2.3 W	11 W
929002983001	LED classic 25W G93 E27 GOLD SP D SRT4	50 to 60 Hz	50 to 60 Hz	4 W	25 W
929002989003	5.5ST19/VIN/927 /E26/CL/G/SP D 1PF T20	60 Hz	-	5.5 W	60 W
929002983601	LED classic-giant 40W E27 G200 GOLD DIM	50 to 60 Hz	50 to 60 Hz	7 W	40 W
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	50 to 60 Hz	-	4 W	60 W
929003624119	LED CLA 4W A60 E27 4000K FR UE SRT6	50 to 60 Hz	-	4 W	60 W
929003625319	LED CLA 7.3W A60 E27 2700K FR UE SRT6	50 to 60 Hz	-	7.3 W	100 W
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	50 to 60 Hz	-	7.3 W	100 W
929002355542	LEDClassic 4.5W G16.5 E27 827 CLND1PF/10	60 Hz	60 Hz	4.5 W	40 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929002983901	LED classic-giant 28W E27 G200 GOLD ND	50 to 60 Hz	50 to 60 Hz	4.5 W	28 W
929002372901	LED classic 200W A95 E27 WW FR ND 1PF	50 to 60 Hz	50 to 60 Hz	23 W	200 W
929002373001	LED classic 200W A95 E27 CW FR ND 1PF/4	50 to 60 Hz	50 to 60 Hz	23 W	200 W
929002373101	LED classic 200W A95 E27 CDL FR ND 1PF/4	50 to 60 Hz	50 to 60 Hz	23 W	200 W
929002355042	LEDClassic 8W A19 E27 827 CL ND 1PF/10	60 Hz	60 Hz	8 W	60 W
929003068142	LEDClassic 8W A19 E27 850 CL ND 1PF/10	60 Hz	60 Hz	8 W	60 W
929003539719	LED CLA 40W A60 B22 3000K CL EELA SRT AU	50 to 60 Hz	-	2.3 W	40 W
929001948248	LEDClassic 40W G93 E27 825 WV ND 2CT	50 to 60 Hz	50 to 60 Hz	4 W	35 W
929003010879	LEDclassic 60W ST64 2700K B22 D CL AU	50 to 60 Hz	-	6 W	60 W
929002371101	LED classic 75W G120 E27 WW FR ND SRT4	50 to 60 Hz	50 to 60 Hz	8.5 W	75 W
929002372101	LED cla 120W G120 E27 WW FR ND RFSRT4	50 to 60 Hz	50 to 60 Hz	13 W	120 W
929002372201	LED classic 120W G120 E27 CW FR ND 1PF/4	50 to 60 Hz	50 to 60 Hz	13 W	120 W
929002372301	LED classic 120W G120 E27 CDL FRND 1PF/4	50 to 60 Hz	50 to 60 Hz	13 W	120 W
929002982601	LED giant 20W E27 G200 1800K smoky D	50 to 60 Hz	50 to 60 Hz	6.5 W	20 W
929003539819	LED CLA 40W A60 B22 4000K CL EELA SRT AU	50 to 60 Hz	-	2.3 W	40 W
929002453701	LED classic 25W ST64 E27 pink D SRT4	50 to 60 Hz	50 to 60 Hz	4.5 W	25 W

Classic filament LEDbulbs

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929001969604	8A19/PER/927-922/CL/G/E 26/WGX 1FB T20	50 to 60 Hz	50 to 60 Hz	8 W	60 W
929003059379	LEDclassic 60W E27 2700K G120 D CL AU	50 to 60 Hz	-	6 W	60 W
929003011079	LEDclassic 60W G93 2700K B22 D CL AU	50 to 60 Hz	-	6 W	60 W
929002983701	LED classic-giant 40W E27 T65 GOLD DIM	50 to 60 Hz	50 to 60 Hz	7 W	40 W
929003066719	LED CLA 60W A60 E27 3000K CL EELA SRT AU	50 to 60 Hz	-	4 W	60 W
929003539919	LED CLA 60W A60 B22 3000K CL EELA SRT AU	50 to 60 Hz	-	4 W	60 W
929002412801	LED classic CM 50W A60 E27 WW CL D SRT4	50 to 60 Hz	50 to 60 Hz	7.2 W	50 W
929002380601	LEDclassic 11W ST64 E27 smoky ND RFSRT4	50 to 60 Hz	50 to 60 Hz	2.3 W	11 W
929002371501	LED classic 120W A67 E27 WW CL ND SRT4	50 to 60 Hz	50 to 60 Hz	13 W	120 W
929002371601	LED classic 120W A67 E27 CW CL ND 1SRT4	50 to 60 Hz	50 to 60 Hz	13 W	120 W
929002983501	LED classic-giant 40W E27 A160 GOLD DIM	50 to 60 Hz	50 to 60 Hz	7 W	40 W
929003010979	LEDclassic 60W G93 2700K E27 D CL AU	50 to 60 Hz	-	6 W	60 W
929001941648	LEDClassic 35W ST64 E27 825 WV ND 2CT	50 to 60 Hz	50 to 60 Hz	4 W	35 W
929001941686	LEDClassic 35W ST64 E27 825 100-240VNDBR	50 to 60 Hz	50 to 60 Hz	4 W	35 W
929002055055	LED classic 150W A67 E27 WW CL ND 1SRT4	50 to 60 Hz	50 to 60 Hz	17 W	150 W
929002372401	LED classic 150W A67 E27 CW CL ND 1SRT4	50 to 60 Hz	50 to 60 Hz	17 W	150 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929002025201	LED classic 60W E27 WW G120 FR ND SRT4	50 to 60 Hz	50 to 60 Hz	7 W	60 W
929003010579	LEDclassic 60W A60 2700K B22 D CL AU	50 to 60 Hz	-	6 W	60 W
929003083203	8A19/PER/UD/F R/G/E26/WGD 4/2PFT20	60 Hz	-	8 W	60 W
929002990303	4.4ST19/VIN/820 /AM/G/E26/D/T /SP4/2PF	60 Hz	60 Hz	4.4 W	40 W
929002025731	LED classic 75W E27 WW A60 FR ND 1CT10	50 to 60 Hz	50 to 60 Hz	8.5 W	75 W
929002025831	LED classic 75W E27 CW A60 FR ND 1CT/10	50 to 60 Hz	50 to 60 Hz	8.5 W	75 W
929002983801	LED classic-giant 28W E27 A160 GOLD ND	50 to 60 Hz	50 to 60 Hz	4.5 W	28 W
929002412901	LED classic 50W G120 E27 WW CM D RF	50 to 60 Hz	50 to 60 Hz	7.2 W	50 W
929002380801	LED classic 11W G93 E27 smoky ND RF 1PF	50 to 60 Hz	50 to 60 Hz	2 W	11 W
929002982701	LED giant 20W E27 T65 1800K smoky D	50 to 60 Hz	50 to 60 Hz	6.5 W	20 W
929002454001	LED classic 25W ST64 E27 gradient D SRT	50 to 60 Hz	50 to 60 Hz	4.5 W	25 W
929002982501	LED giant 20W E27 A160 1800K smoky D	50 to 60 Hz	50 to 60 Hz	6.5 W	20 W
929003010779	LEDclassic 60W ST64 2700K E27 D CL AU	50 to 60 Hz	-	6 W	60 W
929003100779	LEDclassic 60W B22 2700K G120 D CL AU	50 to 60 Hz	-	6 W	60 W
929002453801	LED classic 25W G93 E27 pink D 1PF/4	50 to 60 Hz	50 to 60 Hz	4.5 W	25 W
929003066519	LED CLA 40W A60 E27 4000K CL EELA SRT AU	50 to 60 Hz	-	2.3 W	40 W

Temperature

Classic filament LEDbulbs

Order Code	Full Product Name	T-Case Maximum (Nom)
929002355642	LEDClassic 4.5W A15 E27 827 CL ND 1PF/10	50 °C
929002223944	LED classic 5.5W ST64 E27GOLD SP D 1PF/6	35 °C
929002982901	LED classic 25W ST64 E27GOLD SP D RFSRT4	35 °C
929002371801	LED classic 120W A67 E27 WW FR NDRFSRT4	60 °C
929002371901	LED classic 120W A67 E27 CW FR NDRFISRT4	60 °C
929002372001	LED classic 120W A67 E27 CDL FR ND 1SRT4	60 °C
929002372601	LED classic 150W A67 E27 WW FR NDRFSRT4	60 °C
929002372701	LED classic 150W A67 E27 CW FR ND 1SRT4	60 °C
929002372801	LED classic 150W A67 E27 CDL FR ND 1SRT4	60 °C
929003010379	LEDclassic 60W A60 2700K E27 D CL AU	70 °C
929003623819	LED CLA 4W A60 B22 2700K FR UE SRT6	70 °C
929003624219	LED CLA 4W A60 B22 4000K FR UE SRT6	70 °C
929003625419	LED CLA 7.3W A60 B22 2700K FR UE SRT6	70 °C
929003625819	LED CLA 7.3W A60 B22 4000K FR UE SRT6	70 °C
929003540019	LED CLA 60W A60 B22 4000K CL EELA SRT AU	35 °C
929002454101	LED classic 25W G120 E27 gradient D 1PF	40 °C
929001941548	LEDClassic 40W A60 E27 825 WV ND 2CT	52 °C
929001941586	LEDClassic 35W A60 E27 825 100-240V NDBR	52 °C
929002370801	LED classic 60W G93 E27 WW FR ND RFSRT4	45 °C
929002370901	LED classic 60W G93 E27 CW FR ND 1PF/4	45 °C
929002988503	5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20	-
929001387901	LED classic 60W G93 E27 WW CL ND RF 1PF4	45 °C
929003066819	LED CLA 60W A60 E27 4000K CL EELA SRT AU	35 °C
929003066419	LED CLA 40W A60 E27 3000K CL EELA SRT AU	35 °C
929002026431	LED classic 100W A60 WW FR ND 1CT/10	55 °C
929002026457	LEDclassic 100W A60 E27 WW FR NDRF2SRT6	55 °C
929002026531	LED classic 100W A60 CW FR ND 1CT/10	55 °C
929002026557	LED classic 100W A60 E27 CW FR ND 2SRT6	55 °C
929002026596	LED classic 100W A60 CW FR ND RFRFSRT4	55 °C
929002380501	LEDclassic 11W A60 E27 smoky ND RFSRT4	40 °C
929002067801	LED classic 100W E27 WW G120 FR ND SRT4	50 °C
929002067901	LED classic 100W E27 CW G120 FR ND 1PF/6	50 °C
929002380701	LED classic 11W T32 E27 smoky ND RFSRT4	40 °C
929002983001	LED classic 25W G93 E27 GOLD SP D SRT4	35 °C
929002989003	5.5ST19/VIN/927/E26/CL/G/SP D 1PF T20	-
929002983601	LED classic-giant 40W E27 G200 GOLD DIM	45 °C
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	70 °C
929003624119	LED CLA 4W A60 E27 4000K FR UE SRT6	70 °C
929003625319	LED CLA 7.3W A60 E27 2700K FR UE SRT6	70 °C
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	70 °C
929002355542	LEDClassic 4.5W G16.5 E27 827 CLND1PF/10	50 °C
929002983901	LED classic-giant 28W E27 G200 GOLD ND	45 °C
929002372901	LED classic 200W A95 E27 WW FR ND 1PF	55 °C
929002373001	LED classic 200W A95 E27 CW FR ND 1PF/4	55 °C
929002373101	LED classic 200W A95 E27 CDL FR ND 1PF/4	55 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929002355642	LEDClassic 4.5W A15 E27 827 CL ND 1PF/10	No

Order Code	Full Product Name	T-Case Maximum (Nom)
929002355042	LEDClassic 8W A19 E27 827 CL ND 1PF/10	55 °C
929003068142	LEDClassic 8W A19 E27 850 CL ND 1PF/10	55 °C
929003539719	LED CLA 40W A60 B22 3000K CL EELA SRT AU	35 °C
929001948248	LEDClassic 40W G93 E27 825 WV ND 2CT	45 °C
929003010879	LEDclassic 60W ST64 2700K B22 D CL AU	70 °C
929002371101	LED classic 75W G120 E27 WW FR ND SRT4	50 °C
929002372101	LED cla 120W G120 E27 WW FR ND RFSRT4	55 °C
929002372201	LED classic 120W G120 E27 CW FR ND 1PF/4	55 °C
929002372301	LED classic 120W G120 E27 CDL FRND 1PF/4	55 °C
929002982601	LED giant 20W E27 G200 1800K smoky D	45 °C
929003539819	LED CLA 40W A60 B22 4000K CL EELA SRT AU	35 °C
929002453701	LED classic 25W ST64 E27 pink D SRT4	40 °C
929001969604	8A19/PER/927-922/CL/G/E26/WGX 1FB T20	60 °C
929003059379	LEDclassic 60W E27 2700K G120 D CL AU	80 °C
929003011079	LEDclassic 60W G93 2700K B22 D CL AU	70 °C
929002983701	LED classic-giant 40W E27 T65 GOLD DIM	45 °C
929003066719	LED CLA 60W A60 E27 3000K CL EELA SRT AU	35 °C
929003539919	LED CLA 60W A60 B22 3000K CL EELA SRT AU	35 °C
929002412801	LED classic CM 50W A60 E27 WW CL D SRT4	55 °C
929002380601	LEDclassic 11W ST64 E27 smoky ND RFSRT4	40 °C
929002371501	LED classic 120W A67 E27 WW CL ND SRT4	60 °C
929002371601	LED classic 120W A67 E27 CW CL ND 1SRT4	60 °C
929002983501	LED classic-giant 40W E27 A160 GOLD DIM	45 °C
929003010979	LEDclassic 60W G93 2700K E27 D CL AU	70 °C
929001941648	LEDClassic 35W ST64 E27 825 WV ND 2CT	50 °C
929001941686	LEDClassic 35W ST64 E27 825 100-240VNDBR	50 °C
929002055055	LED classic 150W A67 E27 WW CL ND 1SRT4	60 °C
929002372401	LED classic 150W A67 E27 CW CL ND 1SRT4	60 °C
929002025201	LED classic 60W E27 WW G120 FR ND SRT4	45 °C
929003010579	LEDclassic 60W A60 2700K B22 D CL AU	70 °C
929003083203	8A19/PER/UD/FR/G/E26/WGD 4/2PFT20	-
929002990303	4.4ST19/VIN/820/AM/G/E26/D/T/SP4/2PF	-
929002025731	LED classic 75W E27 WW A60 FR ND 1CT10	50 °C
929002025831	LED classic 75W E27 CW A60 FR ND 1CT/10	50 °C
929002983801	LED classic-giant 28W E27 A160 GOLD ND	45 °C
929002412901	LED classic 50W G120 E27 WW CM D RF	55 °C
929002380801	LED classic 11W G93 E27 smoky ND RF 1PF	40 °C
929002982701	LED giant 20W E27 T65 1800K smoky D	45 °C
929002454001	LED classic 25W ST64 E27 gradient D SRT	40 °C
929002982501	LED giant 20W E27 A160 1800K smoky D	45 °C
929003010779	LEDclassic 60W ST64 2700K E27 D CL AU	70 °C
929003100779	LEDclassic 60W B22 2700K G120 D CL AU	80 °C
929002453801	LED classic 25W G93 E27 pink D 1PF/4	40 °C
929003066519	LED CLA 40W A60 E27 4000K CL EELA SRT AU	35 °C

Order Code	Full Product Name	Dimmable
929002223944	LED classic 5.5W ST64 E27GOLD SP D 1PF/6	Only with specific dimmers

Classic filament LEDbulbs

Order Code	Full Product Name	Dimmable
929002982901	LED classic 25W ST64 E27GOLD SP D RFSRT4	Only with specific dimmers
929002371801	LED classic 120W A67 E27 WW FR NDRFSRT4	No
929002371901	LED classic 120W A67 E27 CW FR NDRF1SRT4	No
929002372001	LED classic 120W A67 E27 CDL FR ND 1SRT4	No
929002372601	LED classic 150W A67 E27 WW FR NDRFSRT4	No
929002372701	LED classic 150W A67 E27 CW FR ND 1SRT4	No
929002372801	LED classic 150W A67 E27 CDL FR ND 1SRT4	No
929003010379	LEDclassic 60W A60 2700K E27 D CL AU	Only with specific dimmers
929003623819	LED CLA 4W A60 B22 2700K FR UE SRT6	No
929003624219	LED CLA 4W A60 B22 4000K FR UE SRT6	No
929003625419	LED CLA 7.3W A60 B22 2700K FR UE SRT6	No
929003625819	LED CLA 7.3W A60 B22 4000K FR UE SRT6	No
929003540019	LED CLA 60W A60 B22 4000K CL EELA SRT AU	No
929002454101	LED classic 25W G120 E27 gradient D 1PF	Yes
929001941548	LEDClassic 40W A60 E27 825 WV ND 2CT	No
929001941586	LEDClassic 35W A60 E27 825 100-240V NDBR	No
929002370801	LED classic 60W G93 E27 WW FR ND RFSRT4	No
929002370901	LED classic 60W G93 E27 CW FR ND 1PF/4	No
929002988503	5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20	Only with specific dimmers
929001387901	LED classic 60W G93 E27 WW CL ND RF 1PF4	No
929003066819	LED CLA 60W A60 E27 4000K CL EELA SRT AU	No
929003066419	LED CLA 40W A60 E27 3000K CL EELA SRT AU	No
929002026431	LED classic 100W A60 WW FR ND 1CT/10	No
929002026457	LEDclassic 100W A60 E27 WW FR NDRF2SRT6	No
929002026531	LED classic 100W A60 CW FR ND 1CT/10	No
929002026557	LED classic 100W A60 E27 CW FR ND 2SRT6	No
929002026596	LED classic 100W A60 CW FR ND RFRFSRT4	No
929002380501	LEDclassic 11W A60 E27 smoky ND RFSRT4	No
929002067801	LED classic 100W E27 WW G120 FR ND SRT4	No
929002067901	LED classic 100W E27 CW G120 FR ND 1PF/6	No
929002380701	LED classic 11W T32 E27 smoky ND RFSRT4	No
929002983001	LED classic 25W G93 E27 GOLD SP D SRT4	Only with specific dimmers
929002989003	5.5ST19/VIN/927/E26/CL/G/SP D 1PF T20	Only with specific dimmers
929002983601	LED classic-giant 40W E27 G200 GOLD DIM	Only with specific dimmers
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	No
929003624119	LED CLA 4W A60 E27 4000K FR UE SRT6	No
929003625319	LED CLA 7.3W A60 E27 2700K FR UE SRT6	No
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	No
929002355542	LEDClassic 4.5W G16.5 E27 827 CLND1PF/10	No
929002983901	LED classic-giant 28W E27 G200 GOLD ND	No
929002372901	LED classic 200W A95 E27 WW FR ND 1PF	No
929002373001	LED classic 200W A95 E27 CW FR ND 1PF/4	No
929002373101	LED classic 200W A95 E27 CDL FR ND 1PF/4	No
929002355042	LEDClassic 8W A19 E27 827 CL ND 1PF/10	No
929003068142	LEDClassic 8W A19 E27 850 CL ND 1PF/10	No
929003539719	LED CLA 40W A60 B22 3000K CL EELA SRT AU	No

Order Code	Full Product Name	Dimmable
929001948248	LEDClassic 40W G93 E27 825 WV ND 2CT	No
929003010879	LEDclassic 60W ST64 2700K B22 D CL AU	Only with specific dimmers
929002371101	LED classic 75W G120 E27 WW FR ND SRT4	No
929002372101	LED cla 120W G120 E27 WW FR ND RFSRT4	No
929002372201	LED classic 120W G120 E27 CW FR ND 1PF/4	No
929002372301	LED classic 120W G120 E27 CDL FRND 1PF/4	No
929002982601	LED giant 20W E27 G200 1800K smoky D	Only with specific dimmers
929003539819	LED CLA 40W A60 B22 4000K CL EELA SRT AU	No
929002453701	LED classic 25W ST64 E27 pink D SRT4	Yes
929001969604	8A19/PER/927-922/CL/G/E26/WGX 1FB T20	Yes
929003059379	LEDclassic 60W E27 2700K G120 D CL AU	Only with specific dimmers
929003011079	LEDclassic 60W G93 2700K B22 D CL AU	Only with specific dimmers
929002983701	LED classic-giant 40W E27 T65 GOLD DIM	Only with specific dimmers
929003066719	LED CLA 60W A60 E27 3000K CL EELA SRT AU	No
929003539919	LED CLA 60W A60 B22 3000K CL EELA SRT AU	No
929002412801	LED classic CM 50W A60 E27 WW CL D SRT4	Only with specific dimmers
929002380601	LEDclassic 11W ST64 E27 smoky ND RFSRT4	No
929002371501	LED classic 120W A67 E27 WW CL ND SRT4	No
929002371601	LED classic 120W A67 E27 CW CL ND 1SRT4	No
929002983501	LED classic-giant 40W E27 A160 GOLD DIM	Only with specific dimmers
929003010979	LEDclassic 60W G93 2700K E27 D CL AU	Only with specific dimmers
929001941648	LEDClassic 35W ST64 E27 825 WV ND 2CT	No
929001941686	LEDClassic 35W ST64 E27 825 100-240VNDBR	No
929002055055	LED classic 150W A67 E27 WW CL ND 1SRT4	No
929002372401	LED classic 150W A67 E27 CW CL ND 1SRT4	No
929002025201	LED classic 60W E27 WW G120 FR ND SRT4	No
929003010579	LEDclassic 60W A60 2700K B22 D CL AU	Only with specific dimmers
929003083203	8A19/PER/UD/FR/G/E26/WGD 4/2PFT20	Only with specific dimmers
929002990303	4.4ST19/VIN/820/AM/G/E26/D/T/SP4/2PF	Only with specific dimmers
929002025731	LED classic 75W E27 WW A60 FR ND 1CT10	No
929002025831	LED classic 75W E27 CW A60 FR ND 1CT/10	No
929002983801	LED classic-giant 28W E27 A160 GOLD ND	No
929002412901	LED classic 50W G120 E27 WW CM D RF	Only with specific dimmers
929002380801	LED classic 11W G93 E27 smoky ND RF 1PF	No
929002982701	LED giant 20W E27 T65 1800K smoky D	Only with specific dimmers
929002454001	LED classic 25W ST64 E27 gradient D SRT	Yes
929002982501	LED giant 20W E27 A160 1800K smoky D	Only with specific dimmers

Classic filament LEDbulbs

Order Code	Full Product Name	Dimmable
929003010779	LEDclassic 60W ST64 2700K E27 D CL AU	Only with specific dimmers
929003100779	LEDclassic 60W B22 2700K G120 D CL AU	Only with specific dimmers

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002355642	LEDClassic 4.5W A15 E27 827 CL ND 1PF/10	Clear	A15
929002223944	LED classic 5.5W ST64 E27GOLD SP D 1PF/6	Transparent amber	ST64
929002982901	LED classic 25W ST64 E27GOLD SP D RFSRT4	Amber	ST64
929002371801	LED classic 120W A67 E27 WW FR NDRFSRT4	Frosted	A67
929002371901	LED classic 120W A67 E27 CW FR NDRFISRT4	Frosted	A67
929002372001	LED classic 120W A67 E27 CDL FR ND 1SRT4	Frosted	A67
929002372601	LED classic 150W A67 E27 WW FR NDRFSRT4	Frosted	A67
929002372701	LED classic 150W A67 E27 CW FR ND 1SRT4	Frosted	A67
929002372801	LED classic 150W A67 E27 CDL FR ND 1SRT4	Frosted	A67
929003010379	LEDclassic 60W A60 2700K E27 D CL AU	Clear	A60
929003623819	LED CLA 4W A60 B22 2700K FR UE SRT6	Frosted	A60
929003624219	LED CLA 4W A60 B22 4000K FR UE SRT6	Frosted	A60
929003625419	LED CLA 7.3W A60 B22 2700K FR UE SRT6	Frosted	A60
929003625819	LED CLA 7.3W A60 B22 4000K FR UE SRT6	Frosted	A60
929003540019	LED CLA 60W A60 B22 4000K CL EELA SRT AU	Clear	A60
929002454101	LED classic 25W G120 E27 gradient D 1PF	Amber Gradient	G120
929001941548	LEDClassic 40W A60 E27 825 WV ND 2CT	Transparent amber	A60
929001941586	LEDClassic 35W A60 E27 825 100-240V NDBR	Transparent amber	A60
929002370801	LED classic 60W G93 E27 WW FR ND RFSRT4	Frosted	G93
929002370901	LED classic 60W G93 E27 CW FR ND 1PF/4	Frosted	G93
929002988503	5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20	Clear	A19
929001387901	LED classic 60W G93 E27 WW CL ND RF 1PF4	Clear	G93
929003066819	LED CLA 60W A60 E27 4000K CL EELA SRT AU	Clear	A60

Order Code	Full Product Name	Dimmable
929002453801	LED classic 25W G93 E27 pink D 1PF/4	Yes
929003066519	LED CLA 40W A60 E27 4000K CL EELA SRT AU	No

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929003066419	LED CLA 40W A60 E27 3000K CL EELA SRT AU	Clear	A60
929002026431	LED classic 100W A60 WW FR ND 1CT/10	Frosted	A60
929002026457	LEDclassic 100W A60 E27 WW FR NDRF2SRT6	Frosted	A60
929002026531	LED classic 100W A60 CW FR ND 1CT/10	Frosted	A60
929002026557	LED classic 100W A60 E27 CW FR ND 2SRT6	Frosted	A60
929002026596	LED classic 100W A60 CW FR ND RFRFSRT4	Frosted	A60
929002380501	LEDclassic 11W A60 E27 smoky ND RFSRT4	smoky	A60
929002067801	LED classic 100W E27 WW G120 FR ND SRT4	Frosted	G120
929002067901	LED classic 100W E27 CW G120 FR ND 1PF/6	Frosted	G120
929002380701	LED classic 11W T32 E27 smoky ND RFSRT4	smoky	T32
929002983001	LED classic 25W G93 E27 GOLD SP D SRT4	Amber	G93
929002989003	5.5ST19/VIN/927/E26/CL/G/SP D 1PF T20	Clear	ST19
929002983601	LED classic-giant 40W E27 G200 GOLD DIM	Amber	G200
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	Frosted	A60
929003624119	LED CLA 4W A60 E27 4000K FR UE SRT6	Frosted	A60
929003625319	LED CLA 7.3W A60 E27 2700K FR UE SRT6	Frosted	A60
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	Frosted	A60
929002355542	LEDClassic 4.5W G16.5 E27 827 CLND1PF/10	Clear	G16.5
929002983901	LED classic-giant 28W E27 G200 GOLD ND	Amber	G200
929002372901	LED classic 200W A95 E27 WW FR ND 1PF	Frosted	A95
929002373001	LED classic 200W A95 E27 CW FR ND 1PF/4	Frosted	A95
929002373101	LED classic 200W A95 E27 CDL FR ND 1PF/4	Frosted	A95
929002355042	LEDClassic 8W A19 E27 827 CL ND 1PF/10	Clear	A19
929003068142	LEDClassic 8W A19 E27 850 CL ND 1PF/10	Clear	A19
929003539719	LED CLA 40W A60 B22 3000K CL EELA SRT AU	Clear	A60
929001948248	LEDClassic 40W G93 E27 825 WV ND 2CT	Transparent amber	G93
929003010879	LEDclassic 60W ST64 2700K B22 D CL AU	Clear	ST64

Classic filament LEDbulbs

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002371101	LED classic 75W G120 E27 WW FR ND SRT4	Frosted	G120
929002372101	LED cla 120W G120 E27 WW FR ND RFSRT4	Frosted	G120
929002372201	LED classic 120W G120 E27 CW FR ND 1PF/4	Frosted	G120
929002372301	LED classic 120W G120 E27 CDL FRND 1PF/4	Frosted	G120
929002982601	LED giant 20W E27 G200 1800K smoky D	smoky	G200
929003539819	LED CLA 40W A60 B22 4000K CL EELA SRT AU	Clear	A60
929002453701	LED classic 25W ST64 E27 pink D SRT4	Pink	ST19
929001969604	8A19/PER/927-922/CL/G/E26/WGX 1FB T20	Clear	A19
929003059379	LEDclassic 60W E27 2700K G120 D CL AU	Clear	G120
929003011079	LEDclassic 60W G93 2700K B22 D CL AU	Clear	G93
929002983701	LED classic-giant 40W E27 T65 GOLD DIM	Amber	T65
929003066719	LED CLA 60W A60 E27 3000K CL EELA SRT AU	Clear	A60
929003539919	LED CLA 60W A60 B22 3000K CL EELA SRT AU	Clear	A60
929002412801	LED classic CM 50W A60 E27 WW CL D SRT4	Mirror Crown	A60
929002380601	LEDclassic 11W ST64 E27 smoky ND RFSRT4	smoky	ST64
929002371501	LED classic 120W A67 E27 WW CL ND SRT4	Clear	A67
929002371601	LED classic 120W A67 E27 CW CL ND 1SRT4	Clear	A67
929002983501	LED classic-giant 40W E27 A160 GOLD DIM	Amber	A160

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929003010979	LEDclassic 60W G93 2700K E27 D CL AU	Clear	G93
929001941648	LEDClassic 35W ST64 E27 825 WV ND 2CT	Transparent amber	ST64
929001941686	LEDClassic 35W ST64 E27 825 100-240VNDBR	Transparent amber	ST64
929002055055	LED classic 150W A67 E27 WW CL ND 1SRT4	Clear	A67
929002372401	LED classic 150W A67 E27 CW CL ND 1SRT4	Clear	A67
929002025201	LED classic 60W E27 WW G120 FR ND SRT4	Frosted	G120
929003010579	LEDclassic 60W A60 2700K B22 D CL AU	Clear	A60
929003083203	8A19/PER/UD/FR/G/E26/WGD 4/2PFT20	Frosted	A19
929002990303	4.4ST19/VIN/820/AM/G/E26/D/T/ SP4/2PF	Amber	ST19
929002025731	LED classic 75W E27 WW A60 FR ND 1CT10	Frosted	A60
929002025831	LED classic 75W E27 CW A60 FR ND 1CT/10	Frosted	A60
929002983801	LED classic-giant 28W E27 A160 GOLD ND	Amber	A160
929002412901	LED classic 50W G120 E27 WW CM D RF	Mirror Crown	G125
929002380801	LED classic 11W G93 E27 smoky ND RF 1PF	smoky	G93
929002982701	LED giant 20W E27 T65 1800K smoky D	smoky	T65
929002454001	LED classic 25W ST64 E27 gradient D SRT	Amber Gradient	ST19
929002982501	LED giant 20W E27 A160 1800K smoky D	smoky	A160
929003010779	LEDclassic 60W ST64 2700K E27 D CL AU	Clear	ST64
929003100779	LEDclassic 60W B22 2700K G120 D CL AU	Clear	G120
929002453801	LED classic 25W G93 E27 pink D 1PF/4	Pink	G93
929003066519	LED CLA 40W A60 E27 4000K CL EELA SRT AU	Clear	A60

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929002355642	LEDClassic 4.5W A15 E27 827 CL ND 1PF/10	-	-
929002223944	LED classic 5.5W ST64 E27GOLD SP D 1PF/6	-	-
929002982901	LED classic 25W ST64 E27GOLD SP D RFSRT4	-20 to +45 °C	4 kWh
929002371801	LED classic 120W A67 E27 WW FR NDRFSRT4	-	13 kWh
929002371901	LED classic 120W A67 E27 CW FR NDRF1SRT4	-	13 kWh
929002372001	LED classic 120W A67 E27 CDL FR ND 1SRT4	-	13 kWh
929002372601	LED classic 150W A67 E27 WW FR NDRFSRT4	-	18 kWh

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929002372701	LED classic 150W A67 E27 CW FR ND 1SRT4	-	18 kWh
929002372801	LED classic 150W A67 E27 CDL FR ND 1SRT4	-	18 kWh
929003010379	LEDclassic 60W A60 2700K E27 D CL AU	-20 to +45 °C	6 kWh
929003623819	LED CLA 4W A60 B22 2700K FR UE SRT6	-20 to +45 °C	-
929003624219	LED CLA 4W A60 B22 4000K FR UE SRT6	-20 to +45 °C	-
929003625419	LED CLA 7.3W A60 B22 2700K FR UE SRT6	-20 to +45 °C	-
929003625819	LED CLA 7.3W A60 B22 4000K FR UE SRT6	-20 to +45 °C	-

Classic filament LEDbulbs


Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929003540019	LED CLA 60W A60 B22 4000K CL EELA SRT AU	-20 to +45 °C	-
929002454101	LED classic 25W G120 E27 gradient D 1PF	-	5 kWh
929001941548	LEDClassic 40W A60 E27 825 WV ND 2CT	-	-
929001941586	LEDClassic 35W A60 E27 825 100-240V NDBR	-	-
929002370801	LED classic 60W G93 E27 WW FR ND RFSRT4	-	7 kWh
929002370901	LED classic 60W G93 E27 CW FR ND 1PF/4	-	7 kWh
929002988503	5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20	-20 to +45 °C	-
929001387901	LED classic 60W G93 E27 WW CL ND RF 1PF4	-	7 kWh
929003066819	LED CLA 60W A60 E27 4000K CL EELA SRT AU	-20 to +45 °C	-
929003066419	LED CLA 40W A60 E27 3000K CL EELA SRT AU	-20 to +45 °C	-
929002026431	LED classic 100W A60 WW FR ND 1CT/10	-	11 kWh
929002026457	LEDclassic 100W A60 E27 WW FR NDRF2SRT6	-	11 kWh
929002026531	LED classic 100W A60 CW FR ND 1CT/10	-	11 kWh
929002026557	LED classic 100W A60 E27 CW FR ND 2SRT6	-	11 kWh
929002026596	LED classic 100W A60 CW FR ND RFRFSRT4	-	11 kWh
929002380501	LEDclassic 11W A60 E27 smoky ND RFSRT4	-20 to +40 °C	3 kWh
929002067801	LED classic 100W E27 WW G120 FR ND SRT4	-	11 kWh
929002067901	LED classic 100W E27 CW G120 FR ND 1PF/6	-	11 kWh
929002380701	LED classic 11W T32 E27 smoky ND RFSRT4	-20 to +40 °C	3 kWh
929002983001	LED classic 25W G93 E27 GOLD SP D SRT4	-20 to +45 °C	4 kWh
929002989003	5.5ST19/VIN/927/E26/CL/G/SP D 1PF T20	-20 to +45 °C	-
929002983601	LED classic-giant 40W E27 G200 GOLD DIM	-20 to +45 °C	7 kWh
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	-20 to +45 °C	-
929003624119	LED CLA 4W A60 E27 4000K FR UE SRT6	-20 to +45 °C	-
929003625319	LED CLA 7.3W A60 E27 2700K FR UE SRT6	-20 to +45 °C	-

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	-20 to +45 °C	-
929002355542	LEDClassic 4.5W G16.5 E27 827 CLND1PF/10	-	-
929002983901	LED classic-giant 28W E27 G200 GOLD ND	-20 to +45 °C	5 kWh
929002372901	LED classic 200W A95 E27 WW FR ND 1PF	-	23 kWh
929002373001	LED classic 200W A95 E27 CW FR ND 1PF/4	-	23 kWh
929002373101	LED classic 200W A95 E27 CDL FR ND 1PF/4	-	23 kWh
929002355042	LEDClassic 8W A19 E27 827 CL ND 1PF/10	-	-
929003068142	LEDClassic 8W A19 E27 850 CL ND 1PF/10	-	-
929003539719	LED CLA 40W A60 B22 3000K CL EELA SRT AU	-20 to +45 °C	-
929001948248	LEDClassic 40W G93 E27 825 WV ND 2CT	-	-
929003010879	LEDclassic 60W ST64 2700K B22 D CL AU	-20 to +45 °C	6 kWh
929002371101	LED classic 75W G120 E27 WW FR ND SRT4	-	9 kWh
929002372101	LED cla 120W G120 E27 WW FR ND RFSRT4	-	13 kWh
929002372201	LED classic 120W G120 E27 CW FR ND 1PF/4	-	13 kWh
929002372301	LED classic 120W G120 E27 CDL FRND 1PF/4	-	13 kWh
929002982601	LED giant 20W E27 G200 1800K smoky D	-20 to +45 °C	7 kWh
929003539819	LED CLA 40W A60 B22 4000K CL EELA SRT AU	-20 to +45 °C	-
929002453701	LED classic 25W ST64 E27 pink D SRT4	-	5 kWh
929001969604	8A19/PER/ 927-922/CL/G/E26/WGX 1FB T20	-	-
929003059379	LEDclassic 60W E27 2700K G120 D CL AU	-20 to +45 °C	6 kWh
929003011079	LEDclassic 60W G93 2700K B22 D CL AU	-20 to +45 °C	6 kWh
929002983701	LED classic-giant 40W E27 T65 GOLD DIM	-20 to +45 °C	7 kWh
929003066719	LED CLA 60W A60 E27 3000K CL EELA SRT AU	-20 to +45 °C	-
929003539919	LED CLA 60W A60 B22 3000K CL EELA SRT AU	-20 to +45 °C	-

Classic filament LEDbulbs


Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929002412801	LED classic CM 50W A60 E27 WW CL D SRT4	-	8 kWh
929002380601	LEDclassic 11W ST64 E27 smoky ND RFSRT4	-20 to +40 °C	3 kWh
929002371501	LED classic 120W A67 E27 WW CL ND SRT4	-	13 kWh
929002371601	LED classic 120W A67 E27 CW CL ND 1SRT4	-	13 kWh
929002983501	LED classic-giant 40W E27 A160 GOLD DIM	-20 to +45 °C	7 kWh
929003010979	LEDclassic 60W G93 2700K E27 D CL AU	-20 to +45 °C	6 kWh
929001941648	LEDClassic 35W ST64 E27 825 WV ND 2CT	-	-
929001941686	LEDClassic 35W ST64 E27 825 100-240VNDDBR	-	-
929002055055	LED classic 150W A67 E27 WW CL ND 1SRT4	-	17 kWh
929002372401	LED classic 150W A67 E27 CW CL ND 1SRT4	-	17 kWh
929002025201	LED classic 60W E27 WW G120 FR ND SRT4	-	7 kWh
929003010579	LEDclassic 60W A60 2700K B22 D CL AU	-20 to +45 °C	6 kWh
929003083203	8A19/PER/UD/FR/G/E26/WGD 4/2PFT20	-20 to +40 °C	-
929002990303	4.4ST19/VIN/820/AM/G/E26/D/ T/SP4/2PF	-20 °C to 45 °C	-
929002025731	LED classic 75W E27 WW A60 FR ND 1CT10	-	9 kWh
929002025831	LED classic 75W E27 CW A60 FR ND 1CT/10	-	9 kWh
929002983801	LED classic-giant 28W E27 A160 GOLD ND	-20 to +45 °C	5 kWh
929002412901	LED classic 50W G120 E27 WW CM D RF	-	8 kWh
929002380801	LED classic 11W G93 E27 smoky ND RF 1PF	-20 to +40 °C	2 kWh
929002982701	LED giant 20W E27 T65 1800K smoky D	-20 to +45 °C	7 kWh
929002454001	LED classic 25W ST64 E27 gradient D SRT	-	5 kWh
929002982501	LED giant 20W E27 A160 1800K smoky D	-20 to +45 °C	7 kWh
929003010779	LEDclassic 60W ST64 2700K E27 D CL AU	-20 to +45 °C	6 kWh
929003100779	LEDclassic 60W B22 2700K G120 D CL AU	-20 to +45 °C	6 kWh
929002453801	LED classic 25W G93 E27 pink D 1PF/4	-	5 kWh

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929003066519	LED CLA 40W A60 E27 4000K CL EELA SRT AU	-20 to +45 °C	-




Classic filament LEDbulbs


Classic filament LEDbulbs




Classic filament LEDbulbs





Classic filament LEDbulbs



Classic filament LEDbulbs





Classic filament LEDbulbs




Classic filament LEDbulbs


Classic filament LEDbulbs













Classic filament LEDbulbs



Classic filament LEDbulbs



Classic filament LEDbulbs



Classic filament LEDbulbs

