

# Classic look & feel and LED filament for decorative lighting

## Classic filament LEDbulbs

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

### Benefits

- Around 90% energy saving
- Long lifetime reduces need for replacement
- Environmentally friendly: contains no mercury or other hazardous substances

### Features

- Heritage design with classic shape
- Long LED Filament

### Application

- Home: living room, bedroom
- Hospitality: restaurants and hotels

Classic filament LEDbulbs

Versions





LEDclassic A60 E27 smoky POS2



LEDclassic ST64 E27 smoky POS2

Dimensional drawing



Product	D	C
LEDclassic 11W A60 E27 smoky ND RFSRT4	60 mm	106 mm


Product	D	C
LEDclassic 11W ST64 E27 smoky ND RFSRT4	64 mm	143 mm

Classic filament LEDbulbs

General Information	
Cap-Base	E27
Rated Lifetime (Hours)	15,000 hour(s)
Switching Cycle	20,000
Nominal lifetime	15,000 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	1800 K
Color rendering index (CRI)	80
Color Code	818
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux	100 lm
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Power Consumption	2.3 W
Starting Time (Nom)	0.5 s
Wattage Equivalent	11 W
Temperature	
T-Case Maximum (Nom)	40 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	smoky
Approval and Application	
Ambient temperature range	-20 to +40 °C
Energy Consumption kWh/1000 h	3 kWh

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
75963600	LEDclassic 11W A60 E27 smoky ND RFSRT4	A60
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	ST64



## Classic filament LEDbulbs

