

Classic LEDbulbs lamps for decorative lighting

Classic filament LEDbulbs

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

Features


- Heritage design with classic shape
- Designed to be seen, they look good on and off
- Perfect fit and high quality finishing
- High color rendering (CRI > 80) for vivid colors
- Environmentally friendly: contains no mercury or other hazardous substances

Application

- Perfect for decorative installations
- Domestic applications
- Hospitality: restaurants and hotels

Classic filament LEDbulbs

Versions



LEDbulb E27 ST6 5.5W



LEDclassic G93 G95 E27 POS2



CLA LEDbulb 60W E27 827 CL G93




LEDclassic A60 E27 smoky POS2



LEDclassic T32 E27 smoky POS2



Bulb G95 230V 5W-25W 250lm
2000K E27 D



LEDbulb classic-giant 40W E27
G200 GOLD DIM



LEDclassic giant 28W E27 G200
GOLD ND

Classic filament LEDbulbs

Versions



LEDclassic A95 E27 FR-POS2A



25W E27 G200




LEDbulb classic-giant 40W E27
T65 GOLD DIM



LEDclassic ST64 E27 smoky POS2



LEDbulb classic-giant 40W E27
A160 GOLD DIM



LEDclassic A67 E27 CL 1-POS2A



LED classic 60W E27 WW G120 FR
ND SRT4-SPP



LED classic A60 E27

Classic filament LEDbulbs

Versions




LEDclassic giant 28W E27 A160
GOLD ND



LEDbulb G93 E27 smoky





25W E27 T65



25W E27 A160

Dimensional drawing







Product	D	C
LEDclassic 11W A60 E27 smoky ND RFSRT4	60 mm	106 mm

Product	D	C
LED classic 60W G93 E27 WW CL ND RF 1PF4	95 mm	140 mm

Classic filament LEDbulbs

Dimensional drawing



Product	D	C
LED classic-giant 28W E27 A160 GOLD ND	162 mm	293 mm
LED classic-giant 40W E27 A160 GOLD DIM	162 mm	293 mm
LED giant 20W E27 A160 1800K smoky D	162 mm	293 mm





Product	D	C
LED classic-giant 28W E27 G200 GOLD ND	202 mm	286 mm
LED classic-giant 40W E27 G200 GOLD DIM	202 mm	286 mm
LED giant 20W E27 G200 1800K smoky D	202 mm	286 mm

Product	D	C
LED classic 120W A67 E27 CDL FR ND 1SRT4	70 mm	121 mm
LED classic 120W A67 E27 CW CL ND 1SRT4	70 mm	121 mm
LED classic 120W A67 E27 CW FR NDRF1SRT4	70 mm	121 mm
LED classic 120W A67 E27 WW CL ND SRT4	70 mm	121 mm
LED classic 120W A67 E27 WW FR NDRFSRT4	70 mm	121 mm
LED classic 150W A67 E27 CDL FR ND 1SRT4	70 mm	121 mm
LED classic 150W A67 E27 CW CL ND 1SRT4	70 mm	121 mm
LED classic 150W A67 E27 CW FR ND 1SRT4	70 mm	121 mm
LED classic 150W A67 E27 WW FR NDRFSRT4	70 mm	121 mm

Product	D	C
LED classic-giant 40W E27 T65 GOLD DIM	66 mm	273 mm
LED giant 20W E27 T65 1800K smoky D	66 mm	273 mm

Classic filament LEDbulbs

Dimensional drawing



Product	D	C
LED classic 150W A67 E27 WW CL ND 1SRT4	70 mm	128 mm





Product	D	C
LED classic 25W G93 E27 GOLD SP D SRT4	96 mm	143 mm
LED classic 60W G93 E27 WW FR ND RFSRT4	95 mm	140 mm

Product	D	C
LED classic 100W A60 CW FR ND 1CT/10	60 mm	104 mm
LED classic 100W A60 E27 CW FR ND 2SRT6	60 mm	104 mm
LED classic 100W A60 WW FR ND 1CT/10	60 mm	104 mm
LED classic 75W E27 CW A60 FR ND 1CT/10	60 mm	104 mm
LED classic 75W E27 WW A60 FR ND 1CT10	60 mm	104 mm
LEDclassic 100W A60 E27 WW FR NDRF2SRT6	60 mm	104 mm

Product	D	C
LED classic 200W A95 E27 CDL FR ND 1PF/4	95 mm	165 mm
LED classic 200W A95 E27 CW FR ND 1PF/4	95 mm	165 mm
LED classic 200W A95 E27 WW FR ND 1PF	95 mm	165 mm

Classic filament LEDbulbs

Dimensional drawing



Product	D	C
LED classic 11W G93 E27 smoky ND RF 1PF	95 mm	142 mm



Product	D	C
LED classic 100W E27 CW G120 FR ND 1PF/6	125 mm	177 mm
LED classic 100W E27 WW G120 FR ND SRT4	125 mm	177 mm
LED classic 60W E27 WW G120 FR ND SRT4	125 mm	177 mm

Product	D	C
LED cla 120W G120 E27 WW FR ND RFSRT4	124 mm	177 mm
LED classic 75W G120 E27 WW FR ND SRT4	125 mm	177 mm

Product	D	C
LEDclassic 11W ST64 E27 smoky ND RFSRT4	64 mm	143 mm

Classic filament LEDbulbs

Dimensional drawing



Product	D	C
LED classic 11W T32 E27 smoky ND RFSRT4	32 mm	140 mm

Product	D	C
LED classic 25W ST64 E27GOLD SP D RFSRT4	65 mm	143 mm

General Information	
Cap-Base	E27
Rated Lifetime (Hours)	15,000 hour(s)
Switching Cycle	20,000
Nominal lifetime	15,000 hour(s)
Light Technical	
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s

Light Technical

		Correlated Color			
		Beam Angle	Temperature	Color	
Order Code	Full Product Name	(Nom)	(Nom)	Code	Luminous Flux
31545700	LED classic 25W ST64 E27GOLD SP D RFSRT4	330 degree(s)	1800 K	818	250 lm
76451700	LED classic 120W A67 E27 WW FR NDRFSRT4	-	2700 K	827	2,000 lm
76453100	LED classic 120W A67 E27 CW FR NDRFISRT4	-	4000 K	840	2,000 lm
76455500	LED classic 120W A67 E27 CDL FR ND 1SRT4	-	6500 K	865	2,000 lm
76457900	LED classic 150W A67 E27 WW FR NDRFSRT4	-	2700 K	827	2,452 lm
76459300	LED classic 150W A67 E27 CW FR ND 1SRT4	-	4000 K	840	2,452 lm
76461600	LED classic 150W A67 E27 CDL FR ND 1SRT4	-	6500 K	865	2,452 lm
76469200	LED classic 60W G93 E27 WW FR ND RFSRT4	-	2700 K	827	806 lm
74245700	LED classic 60W G93 E27 WW CL ND 1PF	-	2700 K	827	806 lm
70416200	LED classic 100W A60 WW FR ND 1CT/10	-	2700 K	827	1,521 lm
76369500	LEDclassic 100W A60 E27 WW FR NDRF2SRT6	-	2700 K	827	1,521 lm

Classic filament LEDbulbs

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		Luminous Flux
			Temperature (Nom)	Color Code	
70414800	LED classic 100W A60 CW FR ND 1CT/10	-	4000 K	840	1,521 lm
76371800	LED classic 100W A60 E27 CW FR ND 2SRT6	-	4000 K	840	1,521 lm
75963600	LEDclassic 11W A60 E27 smoky ND RFSRT4	-	1800 K	818	100 lm
66514200	LED classic 100W E27 WW G120 FRNDRFSRT4	-	2700 K	827	1,521 lm
66516600	LED classic 100W E27 CW G120 FR ND 1PF/6	-	4000 K	840	1,521 lm
75967400	LED classic 11W T32 E27 smoky ND RFSRT4	-	1800 K	818	100 lm
31547100	LED classic 25W G93 E27 GOLD SP D SRT4	330 degree(s)	1800 K	818	250 lm
31378100	LED classic-giant 40W E27 G200 GOLD DIM	330 degree(s)	1800 K	818	470 lm
31384200	LED classic-giant 28W E27 G200 GOLD ND	330 degree(s)	1800 K	818	300 lm
76463000	LED classic 200W A95 E27 WW FR ND 1PF	-	2700 K	827	3,452 lm
76465400	LED classic 200W A95 E27 CW FR ND 1PF/4	-	4000 K	840	3,452 lm
76467800	LED classic 200W A95 E27 CDL FR ND 1PF/4	-	6500 K	865	3,452 lm
76475300	LED classic 75W G120 E27 WW FR ND SRT4	-	2700 K	827	1,055 lm
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	-	2700 K	827	2,000 lm
31539600	LED giant 20W E27 G200 1800K smoky D	300 degree(s)	1800 K	818	200 lm
31380400	LED classic-giant 40W E27 T65 GOLD DIM	330 degree(s)	1800 K	818	470 lm
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	-	1800 K	818	100 lm
76435700	LED classic 120W A67 E27 WW CL ND SRT4	-	2700 K	827	2,000 lm
76437100	LED classic 120W A67 E27 CW CL ND 1SRT4	-	4000 K	840	2,000 lm
31376700	LED classic-giant 40W E27 A160 GOLD DIM	330 degree(s)	1800 K	818	470 lm
76237700	LED classic 150W A67 E27 WW CL ND 1SRT4	-	2700 K	827	2,452 lm
76439500	LED classic 150W A67 E27 CW CL ND 1SRT4	-	4000 K	840	2,452 lm
64817600	LED classic 60W E27 WW G120 FR ND SRT4	-	2700 K	827	806 lm
70555100	LED classic 75W E27 WW A60 FR ND 1CT10	-	2700 K	827	1,055 lm
70561200	LED classic 75W E27 CW A60 FR ND 1CT/10	-	4000 K	840	1,055 lm

Classic filament LEDbulbs

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		
			Temperature (Nom)	Color Code	Luminous Flux
31382800	LED classic-giant 28W E27 A160 GOLD ND	330 degree(s)	1800 K	818	300 lm
75969800	LED classic 11W G93 E27 smoky ND RF 1PF	-	1800 K	818	100 lm
31541900	LED giant 20W E27 T65 1800K smoky D	300 degree(s)	1800 K	818	200 lm
31537200	LED giant 20W E27 A160 1800K smoky D	-	1800 K	818	200 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Wattage Equivalent	Order Code	Full Product Name	Power Consumption	Wattage Equivalent
31545700	LED classic 25W ST64 E27GOLD SP D RFSRT4	4 W	25 W	31378100	LED classic-giant 40W E27 G200 GOLD DIM	7 W	40 W
76451700	LED classic 120W A67 E27 WW FR NDRFSRT4	13 W	120 W	31384200	LED classic-giant 28W E27 G200 GOLD ND	4.5 W	28 W
76453100	LED classic 120W A67 E27 CW FR NDRF1SRT4	13 W	120 W	76463000	LED classic 200W A95 E27 WW FR ND 1PF	23 W	200 W
76455500	LED classic 120W A67 E27 CDL FR ND 1SRT4	13 W	120 W	76465400	LED classic 200W A95 E27 CW FR ND 1PF/4	23 W	200 W
76457900	LED classic 150W A67 E27 WW FR NDRFSRT4	17.5 W	150 W	76467800	LED classic 200W A95 E27 CDL FR ND 1PF/4	23 W	200 W
76459300	LED classic 150W A67 E27 CW FR ND 1SRT4	17.5 W	150 W	76475300	LED classic 75W G120 E27 WW FR ND SRT4	8.5 W	75 W
76461600	LED classic 150W A67 E27 CDL FR ND 1SRT4	17.5 W	150 W	76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	13 W	120 W
76469200	LED classic 60W G93 E27 WW FR ND RFSRT4	7 W	60 W	31539600	LED giant 20W E27 G200 1800K smoky D	6.5 W	20 W
74245700	LED classic 60W G93 E27 WW CL ND 1PF	7 W	60 W	31380400	LED classic-giant 40W E27 T65 GOLD DIM	7 W	40 W
70416200	LED classic 100W A60 WW FR ND 1CT/10	10.5 W	100 W	75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	2.3 W	11 W
76369500	LEDclassic 100W A60 E27 WW FR NDRF2SRT6	10.5 W	100 W	76435700	LED classic 120W A67 E27 WW CL ND SRT4	13 W	120 W
70414800	LED classic 100W A60 CW FR ND 1CT/10	10.5 W	100 W	76437100	LED classic 120W A67 E27 CW CL ND 1SRT4	13 W	120 W
76371800	LED classic 100W A60 E27 CW FR ND 2SRT6	10.5 W	100 W	31376700	LED classic-giant 40W E27 A160 GOLD DIM	7 W	40 W
75963600	LEDclassic 11W A60 E27 smoky ND RFSRT4	2.3 W	11 W	76237700	LED classic 150W A67 E27 WW CL ND 1SRT4	17 W	150 W
66514200	LED classic 100W E27 WW G120 FRNDRFSRT4	10.5 W	100 W	76439500	LED classic 150W A67 E27 CW CL ND 1SRT4	17 W	150 W
66516600	LED classic 100W E27 CW G120 FR ND 1PF/6	10.5 W	100 W	64817600	LED classic 60W E27 WW G120 FR ND SRT4	7 W	60 W
75967400	LED classic 11W T32 E27 smoky ND RFSRT4	2.3 W	11 W	70555100	LED classic 75W E27 WW A60 FR ND 1CT10	8.5 W	75 W
31547100	LED classic 25W G93 E27 GOLD SP D SRT4	4 W	25 W	70561200	LED classic 75W E27 CW A60 FR ND 1CT/10	8.5 W	75 W

Classic filament LEDbulbs

Order Code	Full Product Name	Power	Wattage
		Consumption	Equivalent
31382800	LED classic-giant 28W E27 A160 GOLD ND	4.5 W	28 W
75969800	LED classic 11W G93 E27 smoky ND RF 1PF	2 W	11 W

Order Code	Full Product Name	Power	Wattage
		Consumption	Equivalent
31541900	LED giant 20W E27 T65 1800K smoky D	6.5 W	20 W
31537200	LED giant 20W E27 A160 1800K smoky D	6.5 W	20 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
31545700	LED classic 25W ST64 E27GOLD SP D RFSRT4	35 °C
76451700	LED classic 120W A67 E27 WW FR NDRFSRT4	60 °C
76453100	LED classic 120W A67 E27 CW FR NDRFISRT4	60 °C
76455500	LED classic 120W A67 E27 CDL FR ND 1SRT4	60 °C
76457900	LED classic 150W A67 E27 WW FR NDRFSRT4	60 °C
76459300	LED classic 150W A67 E27 CW FR ND 1SRT4	60 °C
76461600	LED classic 150W A67 E27 CDL FR ND 1SRT4	60 °C
76469200	LED classic 60W G93 E27 WW FR ND RFSRT4	45 °C
74245700	LED classic 60W G93 E27 WW CL ND 1PF	45 °C
70416200	LED classic 100W A60 WW FR ND 1CT/10	55 °C
76369500	LEDclassic 100W A60 E27 WW FR NDRF2SRT6	55 °C
70414800	LED classic 100W A60 CW FR ND 1CT/10	55 °C
76371800	LED classic 100W A60 E27 CW FR ND 2SRT6	55 °C
75963600	LEDclassic 11W A60 E27 smoky ND RFSRT4	40 °C
66514200	LED classic 100W E27 WW G120 FRNDRFSRT4	50 °C
66516600	LED classic 100W E27 CW G120 FR ND 1PF/6	50 °C
75967400	LED classic 11W T32 E27 smoky ND RFSRT4	40 °C
31547100	LED classic 25W G93 E27 GOLD SP D SRT4	35 °C
31378100	LED classic-giant 40W E27 G200 GOLD DIM	45 °C
31384200	LED classic-giant 28W E27 G200 GOLD ND	45 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
76463000	LED classic 200W A95 E27 WW FR ND 1PF	55 °C
76465400	LED classic 200W A95 E27 CW FR ND 1PF/4	55 °C
76467800	LED classic 200W A95 E27 CDL FR ND 1PF/4	55 °C
76475300	LED classic 75W G120 E27 WW FR ND SRT4	50 °C
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	55 °C
31539600	LED giant 20W E27 G200 1800K smoky D	45 °C
31380400	LED classic-giant 40W E27 T65 GOLD DIM	45 °C
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	40 °C
76435700	LED classic 120W A67 E27 WW CL ND SRT4	60 °C
76437100	LED classic 120W A67 E27 CW CL ND 1SRT4	60 °C
31376700	LED classic-giant 40W E27 A160 GOLD DIM	45 °C
76237700	LED classic 150W A67 E27 WW CL ND 1SRT4	60 °C
76439500	LED classic 150W A67 E27 CW CL ND 1SRT4	60 °C
64817600	LED classic 60W E27 WW G120 FR ND SRT4	45 °C
70555100	LED classic 75W E27 WW A60 FR ND 1CT10	50 °C
70561200	LED classic 75W E27 CW A60 FR ND 1CT/10	50 °C
31382800	LED classic-giant 28W E27 A160 GOLD ND	45 °C
75969800	LED classic 11W G93 E27 smoky ND RF 1PF	40 °C
31541900	LED giant 20W E27 T65 1800K smoky D	45 °C
31537200	LED giant 20W E27 A160 1800K smoky D	45 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
31545700	LED classic 25W ST64 E27GOLD SP D RFSRT4	Only with specific dimmers
76451700	LED classic 120W A67 E27 WW FR NDRFSRT4	No
76453100	LED classic 120W A67 E27 CW FR NDRFISRT4	No
76455500	LED classic 120W A67 E27 CDL FR ND 1SRT4	No
76457900	LED classic 150W A67 E27 WW FR NDRFSRT4	No
76459300	LED classic 150W A67 E27 CW FR ND 1SRT4	No
76461600	LED classic 150W A67 E27 CDL FR ND 1SRT4	No
76469200	LED classic 60W G93 E27 WW FR ND RFSRT4	No
74245700	LED classic 60W G93 E27 WW CL ND 1PF	No
70416200	LED classic 100W A60 WW FR ND 1CT/10	No
76369500	LEDclassic 100W A60 E27 WW FR NDRF2SRT6	No
70414800	LED classic 100W A60 CW FR ND 1CT/10	No
76371800	LED classic 100W A60 E27 CW FR ND 2SRT6	No
75963600	LEDclassic 11W A60 E27 smoky ND RFSRT4	No
66514200	LED classic 100W E27 WW G120 FRNDRFSRT4	No
66516600	LED classic 100W E27 CW G120 FR ND 1PF/6	No
75967400	LED classic 11W T32 E27 smoky ND RFSRT4	No
31547100	LED classic 25W G93 E27 GOLD SP D SRT4	Only with specific dimmers

Order Code	Full Product Name	Dimmable
31378100	LED classic-giant 40W E27 G200 GOLD DIM	Only with specific dimmers
31384200	LED classic-giant 28W E27 G200 GOLD ND	No
76463000	LED classic 200W A95 E27 WW FR ND 1PF	No
76465400	LED classic 200W A95 E27 CW FR ND 1PF/4	No
76467800	LED classic 200W A95 E27 CDL FR ND 1PF/4	No
76475300	LED classic 75W G120 E27 WW FR ND SRT4	No
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	No
31539600	LED giant 20W E27 G200 1800K smoky D	Only with specific dimmers
31380400	LED classic-giant 40W E27 T65 GOLD DIM	Only with specific dimmers
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	No
76435700	LED classic 120W A67 E27 WW CL ND SRT4	No
76437100	LED classic 120W A67 E27 CW CL ND 1SRT4	No
31376700	LED classic-giant 40W E27 A160 GOLD DIM	Only with specific dimmers
76237700	LED classic 150W A67 E27 WW CL ND 1SRT4	No
76439500	LED classic 150W A67 E27 CW CL ND 1SRT4	No
64817600	LED classic 60W E27 WW G120 FR ND SRT4	No
70555100	LED classic 75W E27 WW A60 FR ND 1CT10	No
70561200	LED classic 75W E27 CW A60 FR ND 1CT/10	No

Classic filament LEDbulbs

Order Code	Full Product Name	Dimmable
31382800	LED classic-giant 28W E27 A160 GOLD ND	No
75969800	LED classic 11W G93 E27 smoky ND RF 1PF	No

Order Code	Full Product Name	Dimmable
31541900	LED giant 20W E27 T65 1800K smoky D	Only with specific dimmers
31537200	LED giant 20W E27 A160 1800K smoky D	Only with specific dimmers

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
31545700	LED classic 25W ST64 E27GOLD SP D RFSRT4	Amber	ST64
76451700	LED classic 120W A67 E27 WW FR NDRFSRT4	Frosted	A67
76453100	LED classic 120W A67 E27 CW FR NDRF1SRT4	Frosted	A67
76455500	LED classic 120W A67 E27 CDL FR ND 1SRT4	Frosted	A67
76457900	LED classic 150W A67 E27 WW FR NDRFSRT4	Frosted	A67
76459300	LED classic 150W A67 E27 CW FR ND 1SRT4	Frosted	A67
76461600	LED classic 150W A67 E27 CDL FR ND 1SRT4	Frosted	A67
76469200	LED classic 60W G93 E27 WW FR ND RFSRT4	Frosted	G93
74245700	LED classic 60W G93 E27 WW CL ND 1PF	Clear	G93
70416200	LED classic 100W A60 WW FR ND 1CT/10	Frosted	A60
76369500	LEDclassic 100W A60 E27 WW FR NDRF2SRT6	Frosted	A60
70414800	LED classic 100W A60 CW FR ND 1CT/10	Frosted	A60
76371800	LED classic 100W A60 E27 CW FR ND 2SRT6	Frosted	A60
75963600	LEDclassic 11W A60 E27 smoky ND RFSRT4	smoky	A60
66514200	LED classic 100W E27 WW G120 FRNDRFSRT4	Frosted	G120
66516600	LED classic 100W E27 CW G120 FR ND 1PF/6	Frosted	G120
75967400	LED classic 11W T32 E27 smoky ND RFSRT4	smoky	T32
31547100	LED classic 25W G93 E27 GOLD SP D SRT4	Amber	G93
31378100	LED classic-giant 40W E27 G200 GOLD DIM	Amber	G200
31384200	LED classic-giant 28W E27 G200 GOLD ND	Amber	G200

Order Code	Full Product Name	Bulb Finish	Bulb Shape
76463000	LED classic 200W A95 E27 WW FR ND 1PF	Frosted	A95
76465400	LED classic 200W A95 E27 CW FR ND 1PF/4	Frosted	A95
76467800	LED classic 200W A95 E27 CDL FR ND 1PF/4	Frosted	A95
76475300	LED classic 75W G120 E27 WW FR ND SRT4	Frosted	G120
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	Frosted	G120
31539600	LED giant 20W E27 G200 1800K smoky D	smoky	G200
31380400	LED classic-giant 40W E27 T65 GOLD DIM	Amber	T65
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	smoky	ST64
76435700	LED classic 120W A67 E27 WW CL ND SRT4	Clear	A67
76437100	LED classic 120W A67 E27 CW CL ND 1SRT4	Clear	A67
31376700	LED classic-giant 40W E27 A160 GOLD DIM	Amber	A160
76237700	LED classic 150W A67 E27 WW CL ND 1SRT4	Clear	A67
76439500	LED classic 150W A67 E27 CW CL ND 1SRT4	Clear	A67
64817600	LED classic 60W E27 WW G120 FR ND SRT4	Frosted	G120
70555100	LED classic 75W E27 WW A60 FR ND 1CT10	Frosted	A60
70561200	LED classic 75W E27 CW A60 FR ND 1CT/10	Frosted	A60
31382800	LED classic-giant 28W E27 A160 GOLD ND	Amber	A160
75969800	LED classic 11W G93 E27 smoky ND RF 1PF	smoky	G93
31541900	LED giant 20W E27 T65 1800K smoky D	smoky	T65
31537200	LED giant 20W E27 A160 1800K smoky D	smoky	A160


Approval and Application

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
31545700	LED classic 25W ST64 E27GOLD SP D RFSRT4	-20 to +45 °C	4 kWh
76451700	LED classic 120W A67 E27 WW FR NDRFSRT4	-	13 kWh
76453100	LED classic 120W A67 E27 CW FR NDRF1SRT4	-	13 kWh
76455500	LED classic 120W A67 E27 CDL FR ND 1SRT4	-	13 kWh
76457900	LED classic 150W A67 E27 WW FR NDRFSRT4	-	18 kWh
76459300	LED classic 150W A67 E27 CW FR ND 1SRT4	-	18 kWh
76461600	LED classic 150W A67 E27 CDL FR ND 1SRT4	-	18 kWh
76469200	LED classic 60W G93 E27 WW FR ND RFSRT4	-	7 kWh
74245700	LED classic 60W G93 E27 WW CL ND 1PF	-	7 kWh

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
70416200	LED classic 100W A60 WW FR ND 1CT/10	-	11 kWh
76369500	LEDclassic 100W A60 E27 WW FR NDRF2SRT6	-	11 kWh
70414800	LED classic 100W A60 CW FR ND 1CT/10	-	11 kWh
76371800	LED classic 100W A60 E27 CW FR ND 2SRT6	-	11 kWh
75963600	LEDclassic 11W A60 E27 smoky ND RFSRT4	-20 to +40 °C	3 kWh
66514200	LED classic 100W E27 WW G120 FRNDRFSRT4	-	11 kWh
66516600	LED classic 100W E27 CW G120 FR ND 1PF/6	-	11 kWh
75967400	LED classic 11W T32 E27 smoky ND RFSRT4	-20 to +40 °C	3 kWh
31547100	LED classic 25W G93 E27 GOLD SP D SRT4	-20 to +45 °C	4 kWh


Classic filament LEDbulbs

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
31378100	LED classic-giant 40W E27 G200 GOLD DIM	-20 to +45 °C	7 kWh
31384200	LED classic-giant 28W E27 G200 GOLD ND	-20 to +45 °C	5 kWh
76463000	LED classic 200W A95 E27 WW FR ND 1PF	-	23 kWh
76465400	LED classic 200W A95 E27 CW FR ND 1PF/4	-	23 kWh
76467800	LED classic 200W A95 E27 CDL FR ND 1PF/4	-	23 kWh
76475300	LED classic 75W G120 E27 WW FR ND SRT4	-	9 kWh
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	-	13 kWh
31539600	LED giant 20W E27 G200 1800K smoky D	-20 to +45 °C	7 kWh
31380400	LED classic-giant 40W E27 T65 GOLD DIM	-20 to +45 °C	7 kWh
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	-20 to +40 °C	3 kWh
76435700	LED classic 120W A67 E27 WW CL ND SRT4	-	13 kWh
76437100	LED classic 120W A67 E27 CW CL ND 1SRT4	-	13 kWh
31376700	LED classic-giant 40W E27 A160 GOLD DIM	-20 to +45 °C	7 kWh
76237700	LED classic 150W A67 E27 WW CL ND 1SRT4	-	17 kWh
76439500	LED classic 150W A67 E27 CW CL ND 1SRT4	-	17 kWh
64817600	LED classic 60W E27 WW G120 FR ND SRT4	-	7 kWh
70555100	LED classic 75W E27 WW A60 FR ND 1CT10	-	9 kWh
70561200	LED classic 75W E27 CW A60 FR ND 1CT/10	-	9 kWh
31382800	LED classic-giant 28W E27 A160 GOLD ND	-20 to +45 °C	5 kWh
75969800	LED classic 11W G93 E27 smoky ND RF 1PF	-20 to +40 °C	2 kWh
31541900	LED giant 20W E27 T65 1800K smoky D	-20 to +45 °C	7 kWh
31537200	LED giant 20W E27 A160 1800K smoky D	-20 to +45 °C	7 kWh



Classic filament LEDbulbs


Classic filament LEDbulbs




Classic filament LEDbulbs

Classic filament LEDbulbs


Classic filament LEDbulbs



Classic filament LEDbulbs



Classic filament LEDbulbs



Classic filament LEDbulbs

