

Classic LEDbulbs lamps for decorative lighting

Classic filament LEDbulbs

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

Features

- Heritage design with classic shape
- Designed to be seen, they look good on and off
- Perfect fit and high quality finishing
- High color rendering (CRI> 80) for vivid colors
- Environmentally friendly: contains no mercury or other hazardous substances

Application

- Perfect for decorative installations
- Domestic applications
- Hospitality: restaurants and hotels

Classic filament LEDbulbs

Versions





LED classic E27 G120



LEDclassic G120 E27 FR POS2

Dimensional drawing



Product	D	C
LED classic 100W E27 WW G120 FR ND SRT4	125 mm	177 mm

Product	D	C
LED cla 120W G120 E27 WW FR ND RFSRT4	124 mm	177 mm
LED classic 120W G120 E27 CDL FRND 1PF/4	124 mm	177 mm
LED classic 120W G120 E27 CW FR ND 1PF/4	124 mm	177 mm

Classic filament LEDbulbs

General Information	
Cap-Base	E27
Rated Lifetime (Hours)	15,000 hour(s)
Switching Cycle	20,000
Nominal lifetime	15,000 hour(s)
Light Technical	
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	G120

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color Code	Luminous Flux
929002067801	LED classic 100W E27 WW G120 FR ND SRT4	2700 K	827	1,521 lm
929002372101	LED cla 120W G120 E27 WW FR ND RFSRT4	2700 K	827	2,000 lm
929002372201	LED classic 120W G120 E27 CW FR ND 1PF/4	4000 K	840	2,000 lm
929002372301	LED classic 120W G120 E27 CDL FRND 1PF/4	6500 K	865	2,000 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929002067801	LED classic 100W E27 WW G120 FR ND SRT4	10.5 W	100 W
929002372101	LED cla 120W G120 E27 WW FR ND RFSRT4	13 W	120 W

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929002372201	LED classic 120W G120 E27 CW FR ND 1PF/4	13 W	120 W
929002372301	LED classic 120W G120 E27 CDL FRND 1PF/4	13 W	120 W


Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929002067801	LED classic 100W E27 WW G120 FR ND SRT4	50 °C
929002372101	LED cla 120W G120 E27 WW FR ND RFSRT4	55 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929002372201	LED classic 120W G120 E27 CW FR ND 1PF/4	55 °C
929002372301	LED classic 120W G120 E27 CDL FRND 1PF/4	55 °C

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929002067801	LED classic 100W E27 WW G120 FR ND SRT4	11 kWh
929002372101	LED cla 120W G120 E27 WW FR ND RFSRT4	13 kWh
929002372201	LED classic 120W G120 E27 CW FR ND 1PF/4	13 kWh
929002372301	LED classic 120W G120 E27 CDL FRND 1PF/4	13 kWh



Classic filament LEDbulbs

