

Classic look & feel and LED filament for decorative lighting

Classic filament LEDbulbs

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Benefits

- Around 90% energy saving
- Long lifetime reduces need for replacement
- Environmentally friendly: contains no mercury or other hazardous substances

Features

- Heritage design with classic shape
- Long LED Filament

Application

- Home: living room, bedroom
- Hospitality: restaurants and hotels

Classic filament LEDbulbs

Versions



LEDclassic 60W A60 E27 CL
WGD90 SRT4 1




LED CLA 60W A60 B22 4000K CL
EELA SRT AU



LEDbulb MAS EU A60 E27 CL 4




LED CLA 60W A60 E27 3000K FR
UE SRT4




LED CLA 40W A60 B22 3000K CL
EELA SRT AU



LEDclassic 60W ST64 B22 CL
WGD90 SRT4 1



LED CLA 40W A60 B22 4000K CL
EELA SRT AU



LEDbulb MAS G120 E27 CL

Classic filament LEDbulbs

Versions



LEDclassic 60W G93 B22 CL
WGD90 1PF 4 1



LEDbulb MAS EU A60 E27 CL 3



LED CLA 60W A60 B22 3000K CL
EELA SRT AU



LEDclassic 60W G93 E27 CL
WGD90 1PF 4 1



LEDclassic 60W A60 B22 CL
WGD90 SRT4 1



LEDclassic 60W ST64 E27 CL
WGD90 SRT4 1







LEDclassic 60W B22 2700K G120
D CL AU



LEDbulb MAS EU A60 E27 CL 2

Classic filament LEDbulbs

Dimensional drawing



Product	D	C
LEDclassic 60W G93 2700K B22 D CL AU	95 mm	136 mm


Product	D	C
LED CLA 40W A60 E27 4000K CL EELA SRT AU	60 mm	105 mm
LED CLA 4W A60 E27 2700K FR UE SRT6	60 mm	104 mm
LED CLA 60W A60 E27 3000K CL EELA SRT AU	60 mm	105 mm
LED CLA 60W A60 E27 4000K CL EELA SRT AU	60 mm	105 mm
LED CLA 7.3W A60 E27 4000K FR UE SRT6	60 mm	104 mm
LEDclassic 60W A60 2700K E27 D CL AU	60 mm	104 mm

Product	D	C
LEDclassic 60W ST64 2700K B22 D CL AU	64 mm	139 mm


Product	D	C
LED CLA 40W A60 B22 3000K CL EELA SRT AU	60 mm	105 mm
LED CLA 40W A60 B22 4000K CL EELA SRT AU	60 mm	105 mm
LED CLA 60W A60 B22 3000K CL EELA SRT AU	60 mm	105 mm
LED CLA 60W A60 B22 4000K CL EELA SRT AU	60 mm	105 mm
LEDclassic 60W A60 2700K B22 D CL AU	60 mm	103 mm

Classic filament LEDbulbs


Dimensional drawing




Product	D	C
LEDclassic 60W B22 2700K G120 D CL AU	124 mm	178 mm



Product	D	C
LEDclassic 60W ST64 2700K E27 D CL AU	64 mm	140 mm



Product	D	C
LEDclassic 60W G93 2700K E27 D CL AU	95 mm	137 mm



Product	D	C
LEDclassic 60W E27 2700K G120 D CL AU	124 mm	178 mm

Classic filament LEDbulbs

Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Approval and Application	
Ambient temperature range	-20 to +45 °C

General Information

Order Code	Full Product Name	Cap-Base	Rated	Switching Cycle	Nominal lifetime
			Lifetime (Hours)		
929003010379	LEDclassic 60W A60 2700K E27 D CL AU	E27	15,000 hour(s)	20,000	15,000 hour(s)
929003540019	LED CLA 60W A60 B22 4000K CL EELA SRT AU	B22	50,000 hour(s)	50,000	50,000 hour(s)
929003066819	LED CLA 60W A60 E27 4000K CL EELA SRT AU	E27	50,000 hour(s)	50,000	50,000 hour(s)
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	E27	-	50,000	50,000 hour(s)
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	E27	-	50,000	50,000 hour(s)
929003539719	LED CLA 40W A60 B22 3000K CL EELA SRT AU	B22	50,000 hour(s)	50,000	50,000 hour(s)
929003010879	LEDclassic 60W ST64 2700K B22 D CL AU	B22	15,000 hour(s)	20,000	15,000 hour(s)
929003539819	LED CLA 40W A60 B22 4000K CL EELA SRT AU	B22	50,000 hour(s)	50,000	50,000 hour(s)
929003059379	LEDclassic 60W E27 2700K G120 D CL AU	E27	15,000 hour(s)	20,000	15,000 hour(s)

Order Code	Full Product Name	Cap-Base	Rated	Switching Cycle	Nominal lifetime
			Lifetime (Hours)		
929003011079	LEDclassic 60W G93 2700K B22 D CL AU	B22	15,000 hour(s)	20,000	15,000 hour(s)
929003066719	LED CLA 60W A60 E27 3000K CL EELA SRT AU	E27	50,000 hour(s)	50,000	50,000 hour(s)
929003539919	LED CLA 60W A60 B22 3000K CL EELA SRT AU	B22	50,000 hour(s)	50,000	50,000 hour(s)
929003010979	LEDclassic 60W G93 2700K E27 D CL AU	E27	15,000 hour(s)	20,000	15,000 hour(s)
929003010579	LEDclassic 60W A60 2700K B22 D CL AU	B22	15,000 hour(s)	20,000	15,000 hour(s)
929003010779	LEDclassic 60W ST64 2700K E27 D CL AU	E27	15,000 hour(s)	20,000	15,000 hour(s)
929003100779	LEDclassic 60W B22 2700K G120 D CL AU	B22	15,000 hour(s)	20,000	15,000 hour(s)
929003066519	LED CLA 40W A60 E27 4000K CL EELA SRT AU	E27	50,000 hour(s)	50,000	50,000 hour(s)

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index		Color Code	Luminous Flux
				(CRI)			
929003010379	LEDclassic 60W A60 2700K E27 D CL AU	-	2700 K	90		927	806 lm
929003540019	LED CLA 60W A60 B22 4000K CL EELA SRT AU	-	4000 K	80		840	840 lm
929003066819	LED CLA 60W A60 E27 4000K CL EELA SRT AU	-	4000 K	80		840	840 lm
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	300 degree(s)	2700 K	80		827	840 lm
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	300 degree(s)	4000 K	80		840	1,535 lm
929003539719	LED CLA 40W A60 B22 3000K CL EELA SRT AU	-	3000 K	80		830	485 lm
929003010879	LEDclassic 60W ST64 2700K B22 D CL AU	-	2700 K	90		927	806 lm
929003539819	LED CLA 40W A60 B22 4000K CL EELA SRT AU	-	4000 K	80		840	485 lm
929003059379	LEDclassic 60W E27 2700K G120 D CL AU	-	2700 K	90		927	806 lm

Classic filament LEDbulbs

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index		Color Code	Luminous Flux
				(CRI)			
929003011079	LEDclassic 60W G93 2700K B22 D CL AU	-	2700 K	90		927	806 lm
929003066719	LED CLA 60W A60 E27 3000K CL EELA SRT AU	-	3000 K	80		830	840 lm
929003539919	LED CLA 60W A60 B22 3000K CL EELA SRT AU	-	3000 K	80		830	840 lm
929003010979	LEDclassic 60W G93 2700K E27 D CL AU	-	2700 K	90		927	806 lm
929003010579	LEDclassic 60W A60 2700K B22 D CL AU	-	2700 K	90		927	806 lm
929003010779	LEDclassic 60W ST64 2700K E27 D CL AU	-	2700 K	90		927	806 lm
929003100779	LEDclassic 60W B22 2700K G120 D CL AU	-	2700 K	90		927	806 lm
929003066519	LED CLA 40W A60 E27 4000K CL EELA SRT AU	-	4000 K	80		840	485 lm

Operating and Electrical

Order Code	Full Product Name	Power	Wattage
		Consumption	Equivalent
929003010379	LEDclassic 60W A60 2700K E27 D CL AU	6 W	60 W
929003540019	LED CLA 60W A60 B22 4000K CL EELA SRT AU	4 W	60 W
929003066819	LED CLA 60W A60 E27 4000K CL EELA SRT AU	4 W	60 W
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	4 W	60 W
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	7.3 W	100 W
929003539719	LED CLA 40W A60 B22 3000K CL EELA SRT AU	2.3 W	40 W
929003010879	LEDclassic 60W ST64 2700K B22 D CL AU	6 W	60 W
929003539819	LED CLA 40W A60 B22 4000K CL EELA SRT AU	2.3 W	40 W
929003059379	LEDclassic 60W E27 2700K G120 D CL AU	6 W	60 W

Order Code	Full Product Name	Power	Wattage
		Consumption	Equivalent
929003011079	LEDclassic 60W G93 2700K B22 D CL AU	6 W	60 W
929003066719	LED CLA 60W A60 E27 3000K CL EELA SRT AU	4 W	60 W
929003539919	LED CLA 60W A60 B22 3000K CL EELA SRT AU	4 W	60 W
929003010979	LEDclassic 60W G93 2700K E27 D CL AU	6 W	60 W
929003010579	LEDclassic 60W A60 2700K B22 D CL AU	6 W	60 W
929003010779	LEDclassic 60W ST64 2700K E27 D CL AU	6 W	60 W
929003100779	LEDclassic 60W B22 2700K G120 D CL AU	6 W	60 W
929003066519	LED CLA 40W A60 E27 4000K CL EELA SRT AU	2.3 W	40 W

Temperature

Order Code	Full Product Name	T-Case Maximum
		(Nom)
929003010379	LEDclassic 60W A60 2700K E27 D CL AU	70 °C
929003540019	LED CLA 60W A60 B22 4000K CL EELA SRT AU	35 °C
929003066819	LED CLA 60W A60 E27 4000K CL EELA SRT AU	35 °C
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	70 °C
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	70 °C
929003539719	LED CLA 40W A60 B22 3000K CL EELA SRT AU	35 °C
929003010879	LEDclassic 60W ST64 2700K B22 D CL AU	70 °C
929003539819	LED CLA 40W A60 B22 4000K CL EELA SRT AU	35 °C
929003059379	LEDclassic 60W E27 2700K G120 D CL AU	80 °C

Order Code	Full Product Name	T-Case Maximum
		(Nom)
929003011079	LEDclassic 60W G93 2700K B22 D CL AU	70 °C
929003066719	LED CLA 60W A60 E27 3000K CL EELA SRT AU	35 °C
929003539919	LED CLA 60W A60 B22 3000K CL EELA SRT AU	35 °C
929003010979	LEDclassic 60W G93 2700K E27 D CL AU	70 °C
929003010579	LEDclassic 60W A60 2700K B22 D CL AU	70 °C
929003010779	LEDclassic 60W ST64 2700K E27 D CL AU	70 °C
929003100779	LEDclassic 60W B22 2700K G120 D CL AU	80 °C
929003066519	LED CLA 40W A60 E27 4000K CL EELA SRT AU	35 °C

Controls and Dimming

Classic filament LEDbulbs

Order Code	Full Product Name	Dimmable
929003010379	LEDclassic 60W A60 2700K E27 D CL AU	Only with specific dimmers
929003540019	LED CLA 60W A60 B22 4000K CL EELA SRT AU	No
929003066819	LED CLA 60W A60 E27 4000K CL EELA SRT AU	No
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	No
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	No
929003539719	LED CLA 40W A60 B22 3000K CL EELA SRT AU	No
929003010879	LEDclassic 60W ST64 2700K B22 D CL AU	Only with specific dimmers
929003539819	LED CLA 40W A60 B22 4000K CL EELA SRT AU	No
929003059379	LEDclassic 60W E27 2700K G120 D CL AU	Only with specific dimmers
929003011079	LEDclassic 60W G93 2700K B22 D CL AU	Only with specific dimmers

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929003010379	LEDclassic 60W A60 2700K E27 D CL AU	Clear	A60
929003540019	LED CLA 60W A60 B22 4000K CL EELA SRT AU	Clear	A60
929003066819	LED CLA 60W A60 E27 4000K CL EELA SRT AU	Clear	A60
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	Frosted	A60
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	Frosted	A60
929003539719	LED CLA 40W A60 B22 3000K CL EELA SRT AU	Clear	A60
929003010879	LEDclassic 60W ST64 2700K B22 D CL AU	Clear	ST64
929003539819	LED CLA 40W A60 B22 4000K CL EELA SRT AU	Clear	A60


Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929003010379	LEDclassic 60W A60 2700K E27 D CL AU	6 kWh
929003540019	LED CLA 60W A60 B22 4000K CL EELA SRT AU	-
929003066819	LED CLA 60W A60 E27 4000K CL EELA SRT AU	-
929003623719	LED CLA 4W A60 E27 2700K FR UE SRT6	-
929003625719	LED CLA 7.3W A60 E27 4000K FR UE SRT6	-
929003539719	LED CLA 40W A60 B22 3000K CL EELA SRT AU	-
929003010879	LEDclassic 60W ST64 2700K B22 D CL AU	6 kWh
929003539819	LED CLA 40W A60 B22 4000K CL EELA SRT AU	-
929003059379	LEDclassic 60W E27 2700K G120 D CL AU	6 kWh
929003011079	LEDclassic 60W G93 2700K B22 D CL AU	6 kWh
929003066719	LED CLA 60W A60 E27 3000K CL EELA SRT AU	-
929003539919	LED CLA 60W A60 B22 3000K CL EELA SRT AU	-
929003010979	LEDclassic 60W G93 2700K E27 D CL AU	6 kWh
929003010579	LEDclassic 60W A60 2700K B22 D CL AU	6 kWh
929003010779	LEDclassic 60W ST64 2700K E27 D CL AU	6 kWh







Order Code	Full Product Name	Dimmable
929003066719	LED CLA 60W A60 E27 3000K CL EELA SRT AU	No
929003539919	LED CLA 60W A60 B22 3000K CL EELA SRT AU	No
929003010979	LEDclassic 60W G93 2700K E27 D CL AU	Only with specific dimmers
929003010579	LEDclassic 60W A60 2700K B22 D CL AU	Only with specific dimmers
929003010779	LEDclassic 60W ST64 2700K E27 D CL AU	Only with specific dimmers
929003100779	LEDclassic 60W B22 2700K G120 D CL AU	Only with specific dimmers
929003066519	LED CLA 40W A60 E27 4000K CL EELA SRT AU	No

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929003059379	LEDclassic 60W E27 2700K G120 D CL AU	Clear	G120
929003011079	LEDclassic 60W G93 2700K B22 D CL AU	Clear	G93
929003066719	LED CLA 60W A60 E27 3000K CL EELA SRT AU	Clear	A60
929003539919	LED CLA 60W A60 B22 3000K CL EELA SRT AU	Clear	A60
929003010979	LEDclassic 60W G93 2700K E27 D CL AU	Clear	G93
929003010579	LEDclassic 60W A60 2700K B22 D CL AU	Clear	A60
929003010779	LEDclassic 60W ST64 2700K E27 D CL AU	Clear	ST64
929003100779	LEDclassic 60W B22 2700K G120 D CL AU	Clear	G120
929003066519	LED CLA 40W A60 E27 4000K CL EELA SRT AU	Clear	A60


Order Code	Full Product Name	Energy Consumption kWh/1000 h
929003100779	LEDclassic 60W B22 2700K G120 D CL AU	6 kWh
929003066519	LED CLA 40W A60 E27 4000K CL EELA SRT AU	-



Classic filament LEDbulbs



Classic filament LEDbulbs



Classic filament LEDbulbs

