

Classic LEDbulbs lamps for decorative lighting

Classic filament LEDbulbs

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

Features

- Heritage design with classic shape
- Designed to be seen, they look good on and off
- Perfect fit and high quality finishing
- High color rendering (CRI> 80) for vivid colors
- Environmentally friendly: contains no mercury or other hazardous substances

Application

- Perfect for decorative installations
- Domestic applications
- Hospitality: restaurants and hotels

Classic filament LEDbulbs

Versions





LEDclassic A60 E27 smoky POS2



LEDclassic ST64 E27 smoky POS2

Dimensional drawing



Product	D	C
LEDclassic 11W A60 E27 smoky ND RFSRT4	60 mm	106 mm


Product	D	C
LEDclassic 11W ST64 E27 smoky ND RFSRT4	64 mm	143 mm

Classic filament LEDbulbs

General Information	
Cap-Base	E27
Rated Lifetime (Hours)	15,000 hour(s)
Switching Cycle	20,000
Nominal lifetime	15,000 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	1800 K
Color rendering index (CRI)	80
Color Code	818
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux	100 lm
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Power Consumption	2.3 W
Starting Time (Nom)	0.5 s
Wattage Equivalent	11 W
Temperature	
T-Case Maximum (Nom)	40 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	smoky
Approval and Application	
Ambient temperature range	-20 to +40 °C
Energy Consumption kWh/1000 h	3 kWh

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929002380501	LEDclassic 11W A60 E27 smoky ND RFSRT4	A60
929002380601	LEDclassic 11W ST64 E27 smoky ND RFSRT4	ST64



Classic filament LEDbulbs

