

Lampade Classic LEDbulbs per illuminazioni decorative

Classic filament LEDbulbs

Con un design ispirato allo stile classico, le lampade Classic LEDbulbs con filamento combinano le forme familiari delle classiche lampadine a incandescenza ai vantaggi in termini di durata della tecnologia LED. Producono una piacevole luce bianca calda decorativa consentendo un risparmio di circa il 90% sui costi energetici rispetto alle lampadine tradizionali.

Vantaggi

- Circa il 90% di risparmio energetico
- Durata molto lunga che riduce l'esigenza di sostituzione
- Sostituzione semplice delle lampade tradizionali classiche

Caratteristiche

- Design tradizionale con forma classica
- Progettate per la visibilità, sia accese che spente
- Idoneità perfetta e finiture di alta qualità
- Elevata resa cromatica (CRI > 80) per colori naturali
- Rispetto dell'ambiente: non contiene mercurio o altre sostanze nocive

Applicazione

- Perfette per le installazioni decorative
- Applicazioni domestiche
- Hotel, ristoranti e bar

Classic filament LEDbulbs

Versions



LEDclassic G93 G95 E27 POS2






LEDbulb CLA G125 E27 Mirror Crown



LEDclassic 15W ST64 E27 gradient POS3

Disegno tecnico




Product	D	C
LED classic 25W ST64 E27 gradient D SRT	64 mm	140 mm

Product	D	C
LED classic 60W G93 E27 CW FR ND 1PF/4	95 mm	140 mm
LED classic 60W G93 E27 WW FR ND RFSRT4	95 mm	140 mm

Product	D	C
Classic LED 100 W E27 WW G120 FR ND SRT4	125 mm	177 mm
LED classic 100W E27 CW G120 FR ND 1PF/6	125 mm	177 mm

Classic filament LEDbulbs

Disegno tecnico



Product	D	C
LED cla 120W G120 E27 WW FR ND RFSRT4	124 mm	177 mm
LED classic 120W G120 E27 CDL FRND 1PF/4	124 mm	177 mm
LED classic 120W G120 E27 CW FR ND 1PF/4	124 mm	177 mm
LED classic 50W G120 E27 WW CM D RF	125 mm	180 mm
LED classic 75W G120 E27 WW FR ND SRT4	125 mm	177 mm

Informazioni generali	
Attacco	E27
Durata specificata (ore)	15.000 ore
Ciclo di commutazione on/off	20.000
Durata nominale	15.000 ore
Dati tecnici di illuminazione	
Indice di resa cromatica (CRI)	80
LLMF a fine durata vita nominale (Nom)	70 %
Funzionamento e parte elettrica	
Frequenza di ingresso	Da 50 a 60 Hz
Frequenza di linea	50 to 60 Hz
Tempo di avvio (Nom)	0,5 s

Dati tecnici di illuminazione

Order Code	Full Product Name	Angolo del fascio	Temperatura di colore correlata	Codice colore	Flusso luminoso
		(Nom)	(Nom)		
76469200	LED classic 60W G93 E27 WW FR ND RFSRT4	-	2700 K	827	806 lm
76471500	LED classic 60W G93 E27 CW FR ND 1PF/4	-	4000 K	840	806 lm
66514200	LED classic 100W E27 WW G120 FRNDRFSRT4	-	2700 K	827	1.521 lm
66516600	LED classic 100W E27 CW G120 FR ND 1PF/6	-	4000 K	840	1.521 lm
76475300	LED classic 75W G120 E27 WW FR ND SRT4	-	2700 K	827	1.055 lm
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	-	2700 K	827	2.000 lm
76483800	LED classic 120W G120 E27 CW FR ND 1PF/4	-	4000 K	840	2.000 lm
76497500	LED classic 120W G120 E27 CDL FRND 1PF/4	-	6500 K	865	2.000 lm
78249800	LED classic 50W G120 E27 WW CM D RF	270 °	2700 K	827	650 lm
26959000	LED classic 25W ST64 E27 gradient D SRT	-	1800 K	818	250 lm

Funzionamento e parte elettrica

Order Code	Full Product Name	Consumo energetico	Potenza equivalente
76469200	LED classic 60W G93 E27 WW FR ND RFSRT4	7 W	60 W
76471500	LED classic 60W G93 E27 CW FR ND 1PF/4	7 W	60 W
66514200	LED classic 100W E27 WW G120 FRNDRFSRT4	10,5 W	100 W
66516600	LED classic 100W E27 CW G120 FR ND 1PF/6	10,5 W	100 W
76475300	LED classic 75W G120 E27 WW FR ND SRT4	8,5 W	75 W

Order Code	Full Product Name	Consumo energetico	Potenza equivalente
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	13 W	120 W
76483800	LED classic 120W G120 E27 CW FR ND 1PF/4	13 W	120 W
76497500	LED classic 120W G120 E27 CDL FRND 1PF/4	13 W	120 W
78249800	LED classic 50W G120 E27 WW CM D RF	7,2 W	50 W

Classic filament LEDbulbs

Order Code	Full Product Name	Consumo energetico	Potenza equivalente
26959000	LED classic 25W ST64 E27 gradient D SRT	4,5 W	25 W

Temperatura

Order Code	Full Product Name	Temp. massima involucro (Nom)
76469200	LED classic 60W G93 E27 WW FR ND RFSRT4	45 °C
76471500	LED classic 60W G93 E27 CW FR ND 1PF/4	45 °C
66514200	LED classic 100W E27 WW G120 FRNDRFSRT4	50 °C
66516600	LED classic 100W E27 CW G120 FR ND 1PF/6	50 °C
76475300	LED classic 75W G120 E27 WW FR ND SRT4	50 °C

Order Code	Full Product Name	Temp. massima involucro (Nom)
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	55 °C
76483800	LED classic 120W G120 E27 CW FR ND 1PF/4	55 °C
76497500	LED classic 120W G120 E27 CDL FRND 1PF/4	55 °C
78249800	LED classic 50W G120 E27 WW CM D RF	55 °C
26959000	LED classic 25W ST64 E27 gradient D SRT	40 °C

Controlli e dimmerazione

Order Code	Full Product Name	Dimmerabile
76469200	LED classic 60W G93 E27 WW FR ND RFSRT4	No
76471500	LED classic 60W G93 E27 CW FR ND 1PF/4	No
66514200	LED classic 100W E27 WW G120 FRNDRFSRT4	No
66516600	LED classic 100W E27 CW G120 FR ND 1PF/6	No
76475300	LED classic 75W G120 E27 WW FR ND SRT4	No

Order Code	Full Product Name	Dimmerabile
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	No
76483800	LED classic 120W G120 E27 CW FR ND 1PF/4	No
76497500	LED classic 120W G120 E27 CDL FRND 1PF/4	No
78249800	LED classic 50W G120 E27 WW CM D RF	Solo con dimmer specifici
26959000	LED classic 25W ST64 E27 gradient D SRT	Sì

Meccanica e corpo

Order Code	Full Product Name	Finitura lampadina	Forma lampadina
76469200	LED classic 60W G93 E27 WW FR ND RFSRT4	Smerigliata	G93
76471500	LED classic 60W G93 E27 CW FR ND 1PF/4	Smerigliata	G93
66514200	LED classic 100W E27 WW G120 FRNDRFSRT4	Smerigliata	G120
66516600	LED classic 100W E27 CW G120 FR ND 1PF/6	Smerigliata	G120
76475300	LED classic 75W G120 E27 WW FR ND SRT4	Smerigliata	G120

Order Code	Full Product Name	Finitura lampadina	Forma lampadina
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	Smerigliata	G120
76483800	LED classic 120W G120 E27 CW FR ND 1PF/4	Smerigliata	G120
76497500	LED classic 120W G120 E27 CDL FRND 1PF/4	Smerigliata	G120
78249800	LED classic 50W G120 E27 WW CM D RF	Crown Mirror	G125
26959000	LED classic 25W ST64 E27 gradient D SRT	Gradient ambra	ST19

Approvazione e applicazione

Order Code	Full Product Name	Consumo energetico kWh/1000 h
76469200	LED classic 60W G93 E27 WW FR ND RFSRT4	7 kWh
76471500	LED classic 60W G93 E27 CW FR ND 1PF/4	7 kWh
66514200	LED classic 100W E27 WW G120 FRNDRFSRT4	11 kWh
66516600	LED classic 100W E27 CW G120 FR ND 1PF/6	11 kWh
76475300	LED classic 75W G120 E27 WW FR ND SRT4	9 kWh
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	13 kWh
76483800	LED classic 120W G120 E27 CW FR ND 1PF/4	13 kWh
76497500	LED classic 120W G120 E27 CDL FRND 1PF/4	13 kWh
78249800	LED classic 50W G120 E27 WW CM D RF	8 kWh

Order Code	Full Product Name	Consumo energetico kWh/1000 h
26959000	LED classic 25W ST64 E27 gradient D SRT	5 kWh

Classic filament LEDbulbs

