



The affordable LEDbulbs solution

CorePro Plastic LEDbulbs

The CorePro LED bulb is the perfect bulb for your basic lighting needs. It provides beautiful light and dependable performance you expect from LED at an affordable price. CorePro LEDbulbs are compatible with existing fixtures with an E27 or B22 holder and are designed for retrofit replacement of incandescent bulbs. They deliver huge energy savings of 80% and provides excellent quality of light. By offering a lifetime of 15,000 hours it reduces maintenance costs.

Benefits

- This bulb is the perfect replacement for your matted incandescent bulbs
- Up to 80% energy saving
- Lower maintenance costs

Features

- Easy retrofit with existing lamp holders
- Long lifetime
- Instant full light on upon switching on
- UV- and IR-free light
- Free of mercury and hazardous materials – RoHS Compliant

Application

- Hospitality
- Residential
- Walkways

CorePro Plastic LEDbulbs

Versions



LEDbulb ND 10 75W A60 E27 827 6CT



LED Lamps, LEDbulb A60 B22



LEDbulb ND 8 60W A60 E27 827 6CT



LEDbulb A65 E27 FR P1



LEDbulb CorePro B22 A60 5W



SPPR LEDbulb 0031







LEDBulb 9W E27 DS FR DIM 1PF 6 AU RTP



LEDbulb Core EU5 combine 1

CorePro Plastic LEDbulbs

Dimensional drawing



Product	D	C
CorePro LEDbulb ND 10.5-75W A60 B22 930	60 mm	107 mm
CorePro LEDbulb ND 10.5-75W A60B22 930UK	60 mm	107 mm
CorePro LEDbulb ND 11-75W A60 B22 927 UK	60 mm	107 mm
CorePro LEDbulb ND 4.9-40W A60 B22 930	60 mm	105 mm
CorePro LEDbulb ND 4.9-40W A60 B22 930UK	60 mm	105 mm
CorePro LEDbulb ND 7.5-60W A60 B22 930	60 mm	105 mm
CorePro LEDbulb ND 8-60W A60 B22 927 UK	60 mm	105 mm
CoreProLEDbulb ND 4.9-40W A60 B22 927 UK	60 mm	105 mm
CoreProLEDbulb ND 7.5-60W A60 B22 930 UK	60 mm	105 mm





Product	D	C
CorePro LEDbulb ND 10-75W A60 E27 827	60 mm	108 mm
CorePro LEDbulb ND 10-75W A60 E27 830	60 mm	108 mm
CorePro LEDbulb ND 10-75W A60 E27 840	60 mm	108 mm
CorePro LEDbulb ND 10-75W A60 E27 865	60 mm	108 mm
CorePro LEDbulb ND 10-75W A60 E27 940	60 mm	109 mm
CorePro LEDbulb ND 10-75W A60 E27 940UK	60 mm	109 mm
CorePro LEDbulb ND 10.5-75W A60 E27 930	60 mm	109 mm
CorePro LEDbulb ND 10.5-75W A60E27 930UK	60 mm	109 mm
CorePro LEDbulb ND 11-75W A60 E27 927	60 mm	109 mm
CorePro LEDbulb ND 11-75W A60 E27 927 UK	60 mm	109 mm
LEDbulb ND 10-75W A60 E27 827 1CT	60 mm	108 mm
LEDbulb ND 10-75W A60 E27 827 2CT	60 mm	108 mm
LEDbulb ND 10-75W A60 E27 827 6CT	60 mm	108 mm
LEDbulb ND 10-75W A60 E27 840 1CT	60 mm	108 mm
LEDbulb ND 10-75W A60 E27 840 2CT	60 mm	108 mm

Product	D	C
CorePro LEDbulb ND 13-100W A60 B22 930	60 mm	110 mm
CoreProLEDbulb ND 13-100W A60 B22 927 UK	60 mm	118 mm
CoreProLEDbulb ND 13-100W A60 B22 930 UK	60 mm	110 mm

Product	D	C
CorePro LEDbulb DIM 8-60W A60 E27 5CCT	60 mm	115 mm

CorePro Plastic LEDbulbs

Dimensional drawing



Product	D	C
CorePro LEDbulb ND 13-100W A60 E27 827	60 mm	120 mm
CorePro LEDbulb ND 13-100W A60 E27 830	60 mm	120 mm
CorePro LEDbulb ND 13-100W A60 E27 840	60 mm	120 mm
CorePro LEDbulb ND 13-100W A60 E27 865	60 mm	120 mm
LEDbulb ND 13-100W A60 E27 827 1CT	60 mm	120 mm
LEDbulb ND 13-100W A60 E27 840 1CT	60 mm	120 mm
LEDbulb ND 13-100W A67 E27 827 2CT	60 mm	120 mm
LEDbulb ND 13-100W A67 E27 840 2CT	60 mm	120 mm




Product	D	C
CorePro LEDbulb ND 8-60W A60 B22 827	60 mm	110 mm

Product	D	C
CorePro LEDbulbND 8-60W A60E27 827 3CT/8	60 mm	110 mm

Product	D	C
CorePro LEDbulb ND 11-75W A60 B22 827	60 mm	110 mm
CorePro LEDbulb ND 13-100W A60 B22 827	60 mm	110 mm

CorePro Plastic LEDbulbs

Dimensional drawing



Product	D	C
CorePro LEDbulb ND 12.5-100W A60 E27 940	60 mm	110 mm
CorePro LEDbulb ND 13-100W A60 E27 930	60 mm	110 mm
CoreProLEDbulb ND 13-100W A60 E27 927	60 mm	120 mm
CoreProLEDbulb ND 13-100W A60 E27 927 UK	60 mm	120 mm
CoreProLEDbulb ND 13-100W A60 E27 930 UK	60 mm	110 mm


Product	D	C
CorePro LEDbulb ND 4.9-40W A60 B22 827	60 mm	110 mm

Product	D	C
CorePro LEDbulb ND 4.9-40W A60 E27 827	60 mm	107 mm
CorePro LEDbulb ND 4.9-40W A60 E27 827	60 mm	110 mm
CorePro LEDbulb ND 4.9-40W A60 E27 830	60 mm	107 mm
CorePro LEDbulb ND 4.9-40W A60 E27 830	60 mm	110 mm
CorePro LEDbulb ND 4.9-40W A60 E27 840	60 mm	108 mm
CorePro LEDbulb ND 4.9-40W A60 E27 840	60 mm	110 mm
CorePro LEDbulb ND 4.9-40W A60 E27 865	60 mm	110 mm
CorePro LEDbulb ND 4.9-40W A60 E27 865	60 mm	107 mm
CorePro LEDbulb ND 4.9-40W A60 E27 930	60 mm	107 mm
CorePro LEDbulb ND 4.9-40W A60 E27 930UK	60 mm	107 mm
CorePro LEDbulb ND 4.9-40W A60 E27 940	60 mm	107 mm
CorePro LEDbulb ND 4.9-40W A60 E27 940UK	60 mm	107 mm
CorePro LEDbulb ND 7.5-60W A60 E27 930	60 mm	107 mm
CorePro LEDbulb ND 7.5-60W A60 E27 930UK	60 mm	107 mm
CorePro LEDbulb ND 7.5-60W A60 E27 940	60 mm	107 mm
CorePro LEDbulb ND 7.5-60W A60 E27 940UK	60 mm	107 mm
CorePro LEDbulb ND 8-60W A60 E27 827	60 mm	108 mm
CorePro LEDbulb ND 8-60W A60 E27 827 SKT	60 mm	108 mm
CorePro LEDbulb ND 8-60W A60 E27 830	60 mm	108 mm
CorePro LEDbulb ND 8-60W A60 E27 840	60 mm	108 mm
CorePro LEDbulb ND 8-60W A60 E27 865	60 mm	108 mm
CorePro LEDbulb ND 8-60W A60 E27 927	60 mm	107 mm
CorePro LEDbulb ND 8-60W A60 E27 927 UK	60 mm	107 mm
CoreProLEDbulb ND 4.9-40W A60 E27 927	60 mm	107 mm
CoreProLEDbulb ND 4.9-40W A60 E27 927 UK	60 mm	107 mm
LEDbulb ND 4.9-40W A60 E27 827 ICT	60 mm	108 mm

CorePro Plastic LEDbulbs

Dimensional drawing

Product	D	C
LEDbulb ND 4.9-40W A60 E27 827 2CT	60 mm	107 mm
LEDbulb ND 4.9-40W A60 E27 840 1CT	60 mm	108 mm
LEDbulb ND 4.9-40W A60 E27 840 2CT	60 mm	108 mm
LEDbulb ND 8-60W A60 E27 827 12CT	60 mm	107 mm
LEDbulb ND 8-60W A60 E27 827 1CT	60 mm	108 mm
LEDbulb ND 8-60W A60 E27 827 2CT	60 mm	108 mm
LEDbulb ND 8-60W A60 E27 827 6CT	60 mm	108 mm
LEDbulb ND 8-60W A60 E27 830 12CT	60 mm	107 mm
LEDbulb ND 8-60W A60 E27 840 12CT	60 mm	107 mm
LEDbulb ND 8-60W A60 E27 840 1CT	60 mm	108 mm
LEDbulb ND 8-60W A60 E27 840 2CT	60 mm	108 mm



Product	D	C
CorePro LED Stick 7.5-57W E27 3CT 830	37.2 mm	114.3 mm
CorePro LED Stick 7.5-60W E27 3CT 840	37.2 mm	114.3 mm

General Information	
Switching Cycle	50,000
Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Starting Time (Nom)	0.5 s
Mechanical and Housing	
Bulb Finish	Frosted

General Information

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929002306502	LEDbulb ND 10-75W A60 E27 827 6CT	E27	15,000 hour(s)
929003003702	CoreProLEDbulb ND 13-100W A60 E27 927	E27	15,000 hour(s)
929003003799	CoreProLEDbulb ND 13-100W A60 E27 927 UK	E27	15,000 hour(s)
929003003902	CorePro LEDbulb ND 13-100W A60 E27 930	E27	15,000 hour(s)

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929003003999	CoreProLEDbulb ND 13-100W A60 E27 930 UK	E27	15,000 hour(s)
929003004102	CorePro LEDbulb ND 12.5-100W A60 E27 940	E27	15,000 hour(s)
929001233902	CorePro LEDbulb ND 8-60W A60 B22 827	B22	15,000 hour(s)
929003003899	CoreProLEDbulb ND 13-100W A60 B22 927 UK	B22	15,000 hour(s)

CorePro Plastic LEDbulbs

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929003004002	CorePro LEDbulb ND 13-100W A60 B22 930	B22	15,000 hour(s)
929003004099	CoreProLEDbulb ND 13-100W A60 B22 930 UK	B22	15,000 hour(s)
929003544599	CorePro LEDbulb ND 11-75W A60 B22 927 UK	B22	15,000 hour(s)
929003544602	CorePro LEDbulb ND 10.5-75W A60 B22 930	B22	15,000 hour(s)
929003544699	CorePro LEDbulb ND 10.5-75W A60B22 930UK	B22	15,000 hour(s)
929002306202	LEDbulb ND 8-60W A60 E27 827 6CT	E27	15,000 hour(s)
929002306808	CorePro LEDbulb ND 13-100W A60 E27 827	E27	15,000 hour(s)
929002306857	LEDbulb ND 13-100W A60 E27 827 1CT	E27	15,000 hour(s)
929002306862	LEDbulb ND 13-100W A67 E27 827 2CT	E27	15,000 hour(s)
929002306908	CorePro LEDbulb ND 13-100W A60 E27 840	E27	15,000 hour(s)
929002306947	LEDbulb ND 13-100W A60 E27 840 1CT	E27	15,000 hour(s)
929002306962	LEDbulb ND 13-100W A67 E27 840 2CT	E27	15,000 hour(s)
929002307008	CorePro LEDbulb ND 13-100W A60 E27 865	E27	15,000 hour(s)
929003607608	CorePro LEDbulb ND 13-100W A60 E27 830	E27	15,000 hour(s)
929002306508	CorePro LEDbulb ND 10-75W A60 E27 827	E27	15,000 hour(s)
929002306547	LEDbulb ND 10-75W A60 E27 827 1CT	E27	15,000 hour(s)
929002306562	LEDbulb ND 10-75W A60 E27 827 2CT	E27	15,000 hour(s)
929002306608	CorePro LEDbulb ND 10-75W A60 E27 840	E27	15,000 hour(s)
929002306647	LEDbulb ND 10-75W A60 E27 840 1CT	E27	15,000 hour(s)
929002306662	LEDbulb ND 10-75W A60 E27 840 2CT	E27	15,000 hour(s)
929002306708	CorePro LEDbulb ND 10-75W A60 E27 865	E27	15,000 hour(s)
929003544102	CorePro LEDbulb ND 11-75W A60 E27 927	E27	15,000 hour(s)
929003544199	CorePro LEDbulb ND 11-75W A60 E27 927 UK	E27	15,000 hour(s)
929003544202	CorePro LEDbulb ND 10.5-75W A60 E27 930	E27	15,000 hour(s)
929003544299	CorePro LEDbulb ND 10.5-75W A60E27 930UK	E27	15,000 hour(s)
929003544302	CorePro LEDbulb ND 10-75W A60 E27 940	E27	15,000 hour(s)
929003544399	CorePro LEDbulb ND 10-75W A60 E27 940UK	E27	15,000 hour(s)
929003607508	CorePro LEDbulb ND 10-75W A60 E27 830	E27	15,000 hour(s)
929003542999	CoreProLEDbulb ND 4.9-40W A60 B22 927 UK	B22	15,000 hour(s)
929003543002	CorePro LEDbulb ND 4.9-40W A60 B22 930	B22	15,000 hour(s)
929003543099	CorePro LEDbulb ND 4.9-40W A60 B22 930UK	B22	15,000 hour(s)
929003543799	CorePro LEDbulb ND 8-60W A60 B22 927 UK	B22	15,000 hour(s)

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929003543802	CorePro LEDbulb ND 7.5-60W A60 B22 930	B22	15,000 hour(s)
929003543899	CoreProLEDbulb ND 7.5-60W A60 B22 930 UK	B22	15,000 hour(s)
929003603102	CorePro LEDbulb ND 4.9-40W A60 B22 827	B22	15,000 hour(s)
929002306208	CorePro LEDbulb ND 8-60W A60 E27 827	E27	15,000 hour(s)
929002306262	LEDbulb ND 8-60W A60 E27 827 2CT	E27	15,000 hour(s)
929002306308	CorePro LEDbulb ND 8-60W A60 E27 840	E27	15,000 hour(s)
929002306309	LEDbulb ND 8-60W A60 E27 840 12CT	E27	15,000 hour(s)
929002306347	LEDbulb ND 8-60W A60 E27 840 1CT	E27	15,000 hour(s)
929002306362	LEDbulb ND 8-60W A60 E27 840 2CT	E27	15,000 hour(s)
929002306408	CorePro LEDbulb ND 8-60W A60 E27 865	E27	15,000 hour(s)
929003540202	LEDbulb ND 4.9-40W A60 E27 827 2CT	E27	15,000 hour(s)
929003540208	CorePro LEDbulb ND 4.9-40W A60 E27 827	E27	15,000 hour(s)
929003540247	LEDbulb ND 4.9-40W A60 E27 827 1CT	E27	15,000 hour(s)
929003542502	CoreProLEDbulb ND 4.9-40W A60 E27 927	E27	15,000 hour(s)
929003542599	CoreProLEDbulb ND 4.9-40W A60 E27 927 UK	E27	15,000 hour(s)
929003542602	CorePro LEDbulb ND 4.9-40W A60 E27 930	E27	15,000 hour(s)
929003542699	CorePro LEDbulb ND 4.9-40W A60 E27 930UK	E27	15,000 hour(s)
929003542702	CorePro LEDbulb ND 4.9-40W A60 E27 940	E27	15,000 hour(s)
929003542799	CorePro LEDbulb ND 4.9-40W A60 E27 940UK	E27	15,000 hour(s)
929003543302	CorePro LEDbulb ND 8-60W A60 E27 927	E27	15,000 hour(s)
929003543385	CorePro LEDbulb ND 8-60W A60 E27 927 UK	E27	15,000 hour(s)
929003543402	CorePro LEDbulb ND 7.5-60W A60 E27 930	E27	15,000 hour(s)
929003543499	CorePro LEDbulb ND 7.5-60W A60 E27 930UK	E27	15,000 hour(s)
929003543502	CorePro LEDbulb ND 7.5-60W A60 E27 940	E27	15,000 hour(s)
929003543599	CorePro LEDbulb ND 7.5-60W A60 E27 940UK	E27	15,000 hour(s)
929003560908	CorePro LEDbulb ND 4.9-40W A60 E27 830	E27	10,000 hour(s)
929003564102	LEDbulb ND 4.9-40W A60 E27 840 2CT	E27	15,000 hour(s)
929003564108	CorePro LEDbulb ND 4.9-40W A60 E27 840	E27	15,000 hour(s)
929003564147	LEDbulb ND 4.9-40W A60 E27 840 1CT	E27	15,000 hour(s)
929003604208	CorePro LEDbulb ND 4.9-40W A60 E27 865	E27	15,000 hour(s)
929003607408	CorePro LEDbulb ND 8-60W A60 E27 830	E27	15,000 hour(s)
929003607409	LEDbulb ND 8-60W A60 E27 830 12CT	E27	15,000 hour(s)
929003774009	LEDbulb ND 8-60W A60 E27 827 12CT	E27	15,000 hour(s)

CorePro Plastic LEDbulbs

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929003774047	LEDbulb ND 8-60W A60 E27 827 1CT	E27	15,000 hour(s)
929001234002	CorePro LEDbulb ND 11-75W A60 B22 827	B22	15,000 hour(s)
929001234102	CorePro LEDbulb ND 13-100W A60 B22 827	B22	15,000 hour(s)
929001901102	CorePro LED Stick 7.5-57W E27 3CT 830	E27	15,000 hour(s)
929001901202	CorePro LED Stick 7.5-60W E27 3CT 840	E27	15,000 hour(s)
929003785202	CorePro LEDbulb DIM 8-60W A60 E27 5CCT	E27	15,000 hour(s)
929001234332	CorePro LEDbulbND 8-60W A60E27 827 3CT/8	E27	15,000 hour(s)

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929003603202	CorePro LEDbulb ND 4.9-40W A60 E27 827	E27	15,000 hour(s)
929003603302	CorePro LEDbulb ND 4.9-40W A60 E27 840	E27	15,000 hour(s)
929003603432	CorePro LEDbulb ND 4.9-40W A60 E27 830	E27	15,000 hour(s)
929003603532	CorePro LEDbulb ND 4.9-40W A60 E27 865	E27	15,000 hour(s)
929002306274	CorePro LEDbulb ND 8-60W A60 E27 827 SKT	E27	15,000 hour(s)

Light Technical

Order Code	Full Product Name	Correlated Color Temperature		Color rendering		
		Beam Angle (Nom)	(Nom)	index (CRI)	Color Code	Luminous Flux
929002306502	LEDbulb ND 10-75W A60 E27 827 6CT	180 degree(s)	2700 K	80	827	1,055 lm
929003003702	CoreProLEDbulb ND 13-100W A60 E27 927	180 degree(s)	2700 K	90	927	1,521 lm
929003003799	CoreProLEDbulb ND 13-100W A60 E27 927 UK	180 degree(s)	2700 K	90	927	1,521 lm
929003003902	CorePro LEDbulb ND 13-100W A60 E27 930	200 degree(s)	3000 K	90	930	1,521 lm
929003003999	CoreProLEDbulb ND 13-100W A60 E27 930 UK	200 degree(s)	3000 K	90	930	1,521 lm
929003004102	CorePro LEDbulb ND 12.5-100W A60 E27 940	200 degree(s)	4000 K	90	940	1,521 lm
929001233902	CorePro LEDbulb ND 8-60W A60 B22 827	200 degree(s)	2700 K	80	827	806 lm
929003003899	CoreProLEDbulb ND 13-100W A60 B22 927 UK	180 degree(s)	2700 K	90	927	1,521 lm
929003004002	CorePro LEDbulb ND 13-100W A60 B22 930	200 degree(s)	3000 K	90	930	1,521 lm
929003004099	CoreProLEDbulb ND 13-100W A60 B22 930 UK	200 degree(s)	3000 K	90	930	1,521 lm
929003544599	CorePro LEDbulb ND 11-75W A60 B22 927 UK	180 degree(s)	2700 K	90	927	1,055 lm
929003544602	CorePro LEDbulb ND 10.5-75W A60 B22 930	180 degree(s)	3000 K	90	930	1,055 lm
929003544699	CorePro LEDbulb ND 10.5-75W A60B22 930UK	180 degree(s)	3000 K	90	930	1,055 lm
929002306202	LEDbulb ND 8-60W A60 E27 827 6CT	180 degree(s)	2700 K	80	827	806 lm
929002306808	CorePro LEDbulb ND 13-100W A60 E27 827	180 degree(s)	2700 K	80	827	1,521 lm
929002306857	LEDbulb ND 13-100W A60 E27 827 1CT	180 degree(s)	2700 K	80	827	1,521 lm
929002306862	LEDbulb ND 13-100W A67 E27 827 2CT	180 degree(s)	2700 K	80	827	1,521 lm
929002306908	CorePro LEDbulb ND 13-100W A60 E27 840	180 degree(s)	4000 K	80	840	1,521 lm
929002306947	LEDbulb ND 13-100W A60 E27 840 1CT	180 degree(s)	4000 K	80	840	1,521 lm
929002306962	LEDbulb ND 13-100W A67 E27 840 2CT	180 degree(s)	4000 K	80	840	1,521 lm
929002307008	CorePro LEDbulb ND 13-100W A60 E27 865	180 degree(s)	6500 K	80	865	1,521 lm
929003607608	CorePro LEDbulb ND 13-100W A60 E27 830	180 degree(s)	3000 K	80	830	1,521 lm
929002306508	CorePro LEDbulb ND 10-75W A60 E27 827	180 degree(s)	2700 K	80	827	1,055 lm
929002306547	LEDbulb ND 10-75W A60 E27 827 1CT	180 degree(s)	2700 K	80	827	1,055 lm
929002306562	LEDbulb ND 10-75W A60 E27 827 2CT	180 degree(s)	2700 K	80	827	1,055 lm
929002306608	CorePro LEDbulb ND 10-75W A60 E27 840	180 degree(s)	4000 K	80	840	1,055 lm
929002306647	LEDbulb ND 10-75W A60 E27 840 1CT	180 degree(s)	4000 K	80	840	1,055 lm
929002306662	LEDbulb ND 10-75W A60 E27 840 2CT	180 degree(s)	4000 K	80	840	1,055 lm
929002306708	CorePro LEDbulb ND 10-75W A60 E27 865	180 degree(s)	6500 K	80	865	1,055 lm
929003544102	CorePro LEDbulb ND 11-75W A60 E27 927	180 degree(s)	2700 K	90	927	1,055 lm
929003544199	CorePro LEDbulb ND 11-75W A60 E27 927 UK	180 degree(s)	2700 K	90	927	1,055 lm
929003544202	CorePro LEDbulb ND 10.5-75W A60 E27 930	180 degree(s)	3000 K	90	930	1,055 lm
929003544299	CorePro LEDbulb ND 10.5-75W A60E27 930UK	180 degree(s)	3000 K	90	930	1,055 lm
929003544302	CorePro LEDbulb ND 10-75W A60 E27 940	180 degree(s)	4000 K	90	940	1,055 lm
929003544399	CorePro LEDbulb ND 10-75W A60 E27 940UK	180 degree(s)	4000 K	90	940	1,055 lm
929003607508	CorePro LEDbulb ND 10-75W A60 E27 830	180 degree(s)	3000 K	80	830	1,055 lm

CorePro Plastic LEDbulbs

Order Code	Full Product Name	Correlated Color Temperature		Color rendering index (CRI)	Color Code	Luminous Flux
		Beam Angle (Nom)	(Nom)			
929003542999	CoreProLEDbulb ND 4.9-40W A60 B22 927 UK	180 degree(s)	2700 K	90	927	470 lm
929003543002	CorePro LEDbulb ND 4.9-40W A60 B22 930	180 degree(s)	3000 K	90	930	470 lm
929003543099	CorePro LEDbulb ND 4.9-40W A60 B22 930UK	180 degree(s)	3000 K	90	930	470 lm
929003543799	CorePro LEDbulb ND 8-60W A60 B22 927 UK	180 degree(s)	2700 K	90	927	806 lm
929003543802	CorePro LEDbulb ND 7.5-60W A60 B22 930	180 degree(s)	3000 K	90	930	806 lm
929003543899	CoreProLEDbulb ND 7.5-60W A60 B22 930 UK	180 degree(s)	3000 K	90	930	806 lm
929003603102	CorePro LEDbulb ND 4.9-40W A60 B22 827	200 degree(s)	2700 K	80	827	470 lm
929002306208	CorePro LEDbulb ND 8-60W A60 E27 827	180 degree(s)	2700 K	80	827	806 lm
929002306262	LEDbulb ND 8-60W A60 E27 827 2CT	180 degree(s)	2700 K	80	827	806 lm
929002306308	CorePro LEDbulb ND 8-60W A60 E27 840	180 degree(s)	4000 K	80	840	806 lm
929002306309	LEDbulb ND 8-60W A60 E27 840 12CT	150 degree(s)	4000 K	80	840	806 lm
929002306347	LEDbulb ND 8-60W A60 E27 840 1CT	180 degree(s)	4000 K	80	840	806 lm
929002306362	LEDbulb ND 8-60W A60 E27 840 2CT	180 degree(s)	4000 K	80	840	806 lm
929002306408	CorePro LEDbulb ND 8-60W A60 E27 865	180 degree(s)	6500 K	80	865	806 lm
929003540202	LEDbulb ND 4.9-40W A60 E27 827 2CT	180 degree(s)	2700 K	80	827	470 lm
929003540208	CorePro LEDbulb ND 4.9-40W A60 E27 827	180 degree(s)	2700 K	80	827	470 lm
929003540247	LEDbulb ND 4.9-40W A60 E27 827 1CT	180 degree(s)	2700 K	80	827	470 lm
929003542502	CoreProLEDbulb ND 4.9-40W A60 E27 927	180 degree(s)	2700 K	90	927	470 lm
929003542599	CoreProLEDbulb ND 4.9-40W A60 E27 927 UK	180 degree(s)	2700 K	90	927	470 lm
929003542602	CorePro LEDbulb ND 4.9-40W A60 E27 930	180 degree(s)	3000 K	90	930	470 lm
929003542699	CorePro LEDbulb ND 4.9-40W A60 E27 930UK	180 degree(s)	3000 K	90	930	470 lm
929003542702	CorePro LEDbulb ND 4.9-40W A60 E27 940	180 degree(s)	4000 K	90	940	470 lm
929003542799	CorePro LEDbulb ND 4.9-40W A60 E27 940UK	180 degree(s)	4000 K	90	940	470 lm
929003543302	CorePro LEDbulb ND 8-60W A60 E27 927	180 degree(s)	2700 K	90	927	806 lm
929003543385	CorePro LEDbulb ND 8-60W A60 E27 927 UK	180 degree(s)	2700 K	90	927	806 lm
929003543402	CorePro LEDbulb ND 7.5-60W A60 E27 930	180 degree(s)	3000 K	90	930	806 lm
929003543499	CorePro LEDbulb ND 7.5-60W A60 E27 930UK	180 degree(s)	3000 K	90	930	806 lm
929003543502	CorePro LEDbulb ND 7.5-60W A60 E27 940	180 degree(s)	4000 K	90	940	806 lm
929003543599	CorePro LEDbulb ND 7.5-60W A60 E27 940UK	180 degree(s)	4000 K	90	940	806 lm
929003560908	CorePro LEDbulb ND 4.9-40W A60 E27 830	180 degree(s)	3000 K	80	830	470 lm
929003564102	LEDbulb ND 4.9-40W A60 E27 840 2CT	180 degree(s)	4000 K	80	840	470 lm
929003564108	CorePro LEDbulb ND 4.9-40W A60 E27 840	180 degree(s)	4000 K	80	840	470 lm
929003564147	LEDbulb ND 4.9-40W A60 E27 840 1CT	180 degree(s)	4000 K	80	840	470 lm
929003604208	CorePro LEDbulb ND 4.9-40W A60 E27 865	180 degree(s)	6500 K	80	865	470 lm
929003607408	CorePro LEDbulb ND 8-60W A60 E27 830	180 degree(s)	3000 K	80	830	806 lm
929003607409	LEDbulb ND 8-60W A60 E27 830 12CT	150 degree(s)	3000 K	80	830	806 lm
929003774009	LEDbulb ND 8-60W A60 E27 827 12CT	150 degree(s)	2700 K	80	827	806 lm
929003774047	LEDbulb ND 8-60W A60 E27 827 1CT	180 degree(s)	2700 K	80	827	806 lm
929001234002	CorePro LEDbulb ND 11-75W A60 B22 827	200 degree(s)	2700 K	80	827	1,055 lm
929001234102	CorePro LEDbulb ND 13-100W A60 B22 827	200 degree(s)	2700 K	80	827	1,521 lm
929001901102	CorePro LED Stick 7.5-57W E27 3CT 830	200 degree(s)	3000 K	80	830	750 lm
929001901202	CorePro LED Stick 7.5-60W E27 3CT 840	200 degree(s)	4000 K	80	840	806 lm
929003785202	CorePro LEDbulb DIM 8-60W A60 E27 5CCT	200 degree(s)	2700 K	80	2700K/3000K/ 4000K/5000K/ 6500K	806 lm
929001234332	CorePro LEDbulbND 8-60W A60E27 827 3CT/8	200 degree(s)	2700 K	80	827	806 lm
929003603202	CorePro LEDbulb ND 4.9-40W A60 E27 827	200 degree(s)	2700 K	80	827	470 lm
929003603302	CorePro LEDbulb ND 4.9-40W A60 E27 840	200 degree(s)	4000 K	80	840	470 lm
929003603432	CorePro LEDbulb ND 4.9-40W A60 E27 830	200 degree(s)	3000 K	80	830	470 lm
929003603532	CorePro LEDbulb ND 4.9-40W A60 E27 865	200 degree(s)	6500 K	80	865	470 lm
929002306274	CorePro LEDbulb ND 8-60W A60 E27 827 SKT	180 degree(s)	2700 K	80	827	806 lm

CorePro Plastic LEDbulbs

Operating and Electrical

	Full Product	Input	Line	Power	Wattage
Order Code	Name	Frequency	Frequency	Consumption	Equivalent
929002306502	LEDbulb ND 10-75W A60 E27 827 6CT	50 to 60 Hz	50 to 60 Hz	10 W	75 W
929003003702	CoreProLEDbulb ND 13-100W A60 E27 927	50 Hz	50 Hz	13 W	100 W
929003003799	CoreProLEDbulb ND 13-100W A60 E27 927 UK	50 Hz	50 Hz	13 W	100 W
929003003902	CorePro LEDbulb ND 13-100W A60 E27 930	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929003003999	CoreProLEDbulb ND 13-100W A60 E27 930 UK	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929003004102	CorePro LEDbulb ND 12.5-100W A60 E27 940	50 to 60 Hz	50 to 60 Hz	12.5 W	100 W
929001233902	CorePro LEDbulb ND 8-60W A60 B22 827	50 to 60 Hz	50 to 60 Hz	8 W	60 W
929003003899	CoreProLEDbulb ND 13-100W A60 B22 927 UK	50 Hz	50 Hz	13 W	100 W
929003004002	CorePro LEDbulb ND 13-100W A60 B22 930	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929003004099	CoreProLEDbulb ND 13-100W A60 B22 930 UK	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929003544599	CorePro LEDbulb ND 11-75W A60 B22 927 UK	50 Hz	50 Hz	11 W	75 W
929003544602	CorePro LEDbulb ND 10.5-75W A60 B22 930	50 Hz	50 Hz	10.5 W	75 W
929003544699	CorePro LEDbulb ND 10.5-75W A60B22 930UK	50 Hz	50 Hz	10.5 W	75 W
929002306202	LEDbulb ND 8-60W A60 E27 827 6CT	50 to 60 Hz	50 to 60 Hz	8 W	60 W
929002306808	CorePro LEDbulb ND 13-100W A60 E27 827	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929002306857	LEDbulb ND 13-100W A60 E27 827 1CT	50 to 60 Hz	-	13 W	100 W

	Full Product	Input	Line	Power	Wattage
Order Code	Name	Frequency	Frequency	Consumption	Equivalent
929002306862	LEDbulb ND 13-100W A67 E27 827 2CT	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929002306908	CorePro LEDbulb ND 13-100W A60 E27 840	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929002306947	LEDbulb ND 13-100W A60 E27 840 1CT	50 to 60 Hz	-	13 W	100 W
929002306962	LEDbulb ND 13-100W A67 E27 840 2CT	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929002307008	CorePro LEDbulb ND 13-100W A60 E27 865	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929003607608	CorePro LEDbulb ND 13-100W A60 E27 830	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929002306508	CorePro LEDbulb ND 10-75W A60 E27 827	50 to 60 Hz	50 to 60 Hz	10 W	75 W
929002306547	LEDbulb ND 10-75W A60 E27 827 1CT	50 to 60 Hz	-	10 W	75 W
929002306562	LEDbulb ND 10-75W A60 E27 827 2CT	50 to 60 Hz	50 to 60 Hz	10 W	75 W
929002306608	CorePro LEDbulb ND 10-75W A60 E27 840	50 to 60 Hz	50 to 60 Hz	10 W	75 W
929002306647	LEDbulb ND 10-75W A60 E27 840 1CT	50 to 60 Hz	-	10 W	75 W
929002306662	LEDbulb ND 10-75W A60 E27 840 2CT	50 to 60 Hz	50 to 60 Hz	10 W	75 W
929002306708	CorePro LEDbulb ND 10-75W A60 E27 865	50 to 60 Hz	50 to 60 Hz	10 W	75 W
929003544102	CorePro LEDbulb ND 11-75W A60 E27 927	50 Hz	50 Hz	11 W	75 W
929003544199	CorePro LEDbulb ND 11-75W A60 E27 927 UK	50 Hz	50 Hz	11 W	75 W
929003544202	CorePro LEDbulb ND 10.5-75W A60 E27 930	50 Hz	50 Hz	10.5 W	75 W

CorePro Plastic LEDbulbs

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929003544299	CorePro LEDbulb ND 10.5-75W A60E27 930UK	50 Hz	50 Hz	10.5 W	75 W
929003544302	CorePro LEDbulb ND 10-75W A60 E27 940	50 Hz	50 Hz	10 W	75 W
929003544399	CorePro LEDbulb ND 10-75W A60 E27 940UK	50 Hz	50 Hz	10 W	75 W
929003607508	CorePro LEDbulb ND 10-75W A60 E27 830	50 to 60 Hz	50 to 60 Hz	10 W	75 W
929003542999	CoreProLEDbulb ND 4.9-40W A60 B22 927 UK	50 Hz	50 Hz	4.9 W	40 W
929003543002	CorePro LEDbulb ND 4.9-40W A60 B22 930	50 Hz	50 Hz	4.9 W	40 W
929003543099	CorePro LEDbulb ND 4.9-40W A60 B22 930UK	50 Hz	50 Hz	4.9 W	40 W
929003543799	CorePro LEDbulb ND 8-60W A60 B22 927 UK	50 Hz	50 Hz	8 W	60 W
929003543802	CorePro LEDbulb ND 7.5-60W A60 B22 930	50 Hz	50 Hz	7.5 W	60 W
929003543899	CoreProLEDbulb ND 7.5-60W A60 B22 930 UK	50 Hz	50 Hz	7.5 W	60 W
929003603102	CorePro LEDbulb ND 4.9-40W A60 B22 827	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
929002306208	CorePro LEDbulb ND 8-60W A60 E27 827	50 to 60 Hz	50 to 60 Hz	8 W	60 W
929002306262	LEDbulb ND 8-60W A60 E27 827 2CT	50 to 60 Hz	50 to 60 Hz	8 W	60 W
929002306308	CorePro LEDbulb ND 8-60W A60 E27 840	50 to 60 Hz	50 to 60 Hz	8 W	60 W
929002306309	LEDbulb ND 8-60W A60 E27 840 12CT	50 to 60 Hz	-	8 W	60 W
929002306347	LEDbulb ND 8-60W A60 E27 840 1CT	50 to 60 Hz	-	8 W	60 W
929002306362	LEDbulb ND 8-60W A60 E27 840 2CT	50 to 60 Hz	50 to 60 Hz	8 W	60 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929002306408	CorePro LEDbulb ND 8-60W A60 E27 865	50 to 60 Hz	50 to 60 Hz	8 W	60 W
929003540202	LEDbulb ND 4.9-40W A60 E27 827 2CT	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
929003540208	CorePro LEDbulb ND 4.9-40W A60 E27 827	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
929003540247	LEDbulb ND 4.9-40W A60 E27 827 1CT	50 to 60 Hz	-	4.9 W	40 W
929003542502	CoreProLEDbulb ND 4.9-40W A60 E27 927	50 Hz	50 Hz	4.9 W	40 W
929003542599	CoreProLEDbulb ND 4.9-40W A60 E27 927 UK	50 Hz	50 Hz	4.9 W	40 W
929003542602	CorePro LEDbulb ND 4.9-40W A60 E27 930	50 Hz	50 Hz	4.9 W	40 W
929003542699	CorePro LEDbulb ND 4.9-40W A60 E27 930UK	50 Hz	50 Hz	4.9 W	40 W
929003542702	CorePro LEDbulb ND 4.9-40W A60 E27 940	50 Hz	50 Hz	4.9 W	40 W
929003542799	CorePro LEDbulb ND 4.9-40W A60 E27 940UK	50 Hz	50 Hz	4.9 W	40 W
929003543302	CorePro LEDbulb ND 8-60W A60 E27 927	50 Hz	50 Hz	8 W	60 W
929003543385	CorePro LEDbulb ND 8-60W A60 E27 927 UK	50 Hz	50 Hz	8 W	60 W
929003543402	CorePro LEDbulb ND 7.5-60W A60 E27 930	50 Hz	50 Hz	7.5 W	60 W
929003543499	CorePro LEDbulb ND 7.5-60W A60 E27 930UK	50 Hz	50 Hz	7.5 W	60 W
929003543502	CorePro LEDbulb ND 7.5-60W A60 E27 940	50 Hz	50 Hz	7.5 W	60 W
929003543599	CorePro LEDbulb ND 7.5-60W A60 E27 940UK	50 Hz	50 Hz	7.5 W	60 W
929003560908	CorePro LEDbulb ND 4.9-40W A60 E27 830	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W

CorePro Plastic LEDbulbs

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929003564102	LEDbulb ND	50 to 60	50 to 60	4.9 W	40 W
	4.9-40W A60	Hz	Hz		
	E27 840 2CT				
929003564108	CorePro LEDbulb	50 to 60	50 to 60	4.9 W	40 W
	ND 4.9-40W A60	Hz	Hz		
	E27 840				
929003564147	LEDbulb ND	50 to 60	-	4.9 W	40 W
	4.9-40W A60	Hz			
	E27 840 1CT				
929003604208	CorePro LEDbulb	50 to 60	50 to 60	4.9 W	40 W
	ND 4.9-40W A60	Hz	Hz		
	E27 865				
929003607408	CorePro LEDbulb	50 to 60	50 to 60	8 W	60 W
	ND 8-60W A60	Hz	Hz		
	E27 830				
929003607409	LEDbulb ND	50 to 60	-	8 W	60 W
	8-60W A60 E27	Hz			
	830 12CT				
929003774009	LEDbulb ND	50 to 60	-	8 W	60 W
	8-60W A60 E27	Hz			
	827 12CT				
929003774047	LEDbulb ND	50 to 60	-	8 W	60 W
	8-60W A60 E27	Hz			
	827 1CT				
929001234002	CorePro LEDbulb	50 to 60	50 to 60	11 W	75 W
	ND 11-75W A60	Hz	Hz		
	B22 827				
929001234102	CorePro LEDbulb	50 to 60	50 to 60	13 W	100 W
	ND 13-100W A60	Hz	Hz		
	B22 827				

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929001901102	CorePro LED	50 to 60	50 to 60	7.5 W	57 W
	Stick 7.5-57W	Hz	Hz		
	E27 3CT 830				
929001901202	CorePro LED	50 to 60	50 to 60	7.5 W	60 W
	Stick 7.5-60W	Hz	Hz		
	E27 3CT 840				
929003785202	CorePro LEDbulb	50 to 60	-	8 W	60 W
	DIM 8-60W A60	Hz			
	E27 5CCT				
929001234332	CorePro	50 to 60	50 to 60	8 W	60 W
	LEDbulbND	Hz	Hz		
	8-60W A60E27				
929003603202	CorePro LEDbulb	50 to 60	50 to 60	4.9 W	40 W
	ND 4.9-40W A60	Hz	Hz		
	E27 827				
929003603302	CorePro LEDbulb	50 to 60	50 to 60	4.9 W	40 W
	ND 4.9-40W A60	Hz	Hz		
	E27 840				
929003603432	CorePro LEDbulb	50 to 60	50 to 60	4.9 W	40 W
	ND 4.9-40W A60	Hz	Hz		
	E27 830				
929003603532	CorePro LEDbulb	50 to 60	50 to 60	4.9 W	40 W
	ND 4.9-40W A60	Hz	Hz		
	E27 865				
929002306274	CorePro LEDbulb	50 to 60	50 to 60	8 W	60 W
	ND 8-60W A60	Hz	Hz		
	E27 827 SKT				

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929002306502	LEDbulb ND 10-75W A60 E27 827 6CT	95 °C
929003003702	CoreProLEDbulb ND 13-100W A60 E27 927	105 °C
929003003799	CoreProLEDbulb ND 13-100W A60 E27 927 UK	105 °C
929003003902	CorePro LEDbulb ND 13-100W A60 E27 930	95 °C
929003003999	CoreProLEDbulb ND 13-100W A60 E27 930 UK	95 °C
929003004102	CorePro LEDbulb ND 12.5-100W A60 E27 940	95 °C
929001233902	CorePro LEDbulb ND 8-60W A60 B22 827	85 °C
929003003899	CoreProLEDbulb ND 13-100W A60 B22 927 UK	105 °C
929003004002	CorePro LEDbulb ND 13-100W A60 B22 930	95 °C
929003004099	CoreProLEDbulb ND 13-100W A60 B22 930 UK	95 °C
929003544599	CorePro LEDbulb ND 11-75W A60 B22 927 UK	105 °C
929003544602	CorePro LEDbulb ND 10.5-75W A60 B22 930	105 °C
929003544699	CorePro LEDbulb ND 10.5-75W A60B22 930UK	105 °C
929002306202	LEDbulb ND 8-60W A60 E27 827 6CT	95 °C
929002306808	CorePro LEDbulb ND 13-100W A60 E27 827	95 °C
929002306857	LEDbulb ND 13-100W A60 E27 827 1CT	95 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929002306862	LEDbulb ND 13-100W A67 E27 827 2CT	95 °C
929002306908	CorePro LEDbulb ND 13-100W A60 E27 840	95 °C
929002306947	LEDbulb ND 13-100W A60 E27 840 1CT	95 °C
929002306962	LEDbulb ND 13-100W A67 E27 840 2CT	95 °C
929002307008	CorePro LEDbulb ND 13-100W A60 E27 865	95 °C
929003607608	CorePro LEDbulb ND 13-100W A60 E27 830	95 °C
929002306508	CorePro LEDbulb ND 10-75W A60 E27 827	85 °C
929002306547	LEDbulb ND 10-75W A60 E27 827 1CT	95 °C
929002306562	LEDbulb ND 10-75W A60 E27 827 2CT	95 °C
929002306608	CorePro LEDbulb ND 10-75W A60 E27 840	85 °C
929002306647	LEDbulb ND 10-75W A60 E27 840 1CT	95 °C
929002306662	LEDbulb ND 10-75W A60 E27 840 2CT	95 °C
929002306708	CorePro LEDbulb ND 10-75W A60 E27 865	85 °C
929003544102	CorePro LEDbulb ND 11-75W A60 E27 927	105 °C
929003544199	CorePro LEDbulb ND 11-75W A60 E27 927 UK	105 °C
929003544202	CorePro LEDbulb ND 10.5-75W A60 E27 930	105 °C

CorePro Plastic LEDbulbs

Order Code	Full Product Name	T-Case Maximum (Nom)
929003544299	CorePro LEDbulb ND 10.5-75W A60E27 930UK	105 °C
929003544302	CorePro LEDbulb ND 10-75W A60 E27 940	105 °C
929003544399	CorePro LEDbulb ND 10-75W A60 E27 940UK	105 °C
929003607508	CorePro LEDbulb ND 10-75W A60 E27 830	85 °C
929003542999	CoreProLEDbulb ND 4.9-40W A60 B22 927 UK	80 °C
929003543002	CorePro LEDbulb ND 4.9-40W A60 B22 930	80 °C
929003543099	CorePro LEDbulb ND 4.9-40W A60 B22 930UK	80 °C
929003543799	CorePro LEDbulb ND 8-60W A60 B22 927 UK	95 °C
929003543802	CorePro LEDbulb ND 7.5-60W A60 B22 930	95 °C
929003543899	CoreProLEDbulb ND 7.5-60W A60 B22 930 UK	95 °C
929003603102	CorePro LEDbulb ND 4.9-40W A60 B22 827	80 °C
929002306208	CorePro LEDbulb ND 8-60W A60 E27 827	75 °C
929002306262	LEDbulb ND 8-60W A60 E27 827 2CT	95 °C
929002306308	CorePro LEDbulb ND 8-60W A60 E27 840	75 °C
929002306309	LEDbulb ND 8-60W A60 E27 840 12CT	90 °C
929002306347	LEDbulb ND 8-60W A60 E27 840 1CT	95 °C
929002306362	LEDbulb ND 8-60W A60 E27 840 2CT	95 °C
929002306408	CorePro LEDbulb ND 8-60W A60 E27 865	75 °C
929003540202	LEDbulb ND 4.9-40W A60 E27 827 2CT	75 °C
929003540208	CorePro LEDbulb ND 4.9-40W A60 E27 827	75 °C
929003540247	LEDbulb ND 4.9-40W A60 E27 827 1CT	75 °C
929003542502	CoreProLEDbulb ND 4.9-40W A60 E27 927	80 °C
929003542599	CoreProLEDbulb ND 4.9-40W A60 E27 927 UK	80 °C
929003542602	CorePro LEDbulb ND 4.9-40W A60 E27 930	80 °C
929003542699	CorePro LEDbulb ND 4.9-40W A60 E27 930UK	80 °C
929003542702	CorePro LEDbulb ND 4.9-40W A60 E27 940	80 °C
929003542799	CorePro LEDbulb ND 4.9-40W A60 E27 940UK	80 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929002306502	LEDbulb ND 10-75W A60 E27 827 6CT	No
929003003702	CoreProLEDbulb ND 13-100W A60 E27 927	No
929003003799	CoreProLEDbulb ND 13-100W A60 E27 927 UK	No
929003003902	CorePro LEDbulb ND 13-100W A60 E27 930	No
929003003999	CoreProLEDbulb ND 13-100W A60 E27 930 UK	No
929003004102	CorePro LEDbulb ND 12.5-100W A60 E27 940	No
929001233902	CorePro LEDbulb ND 8-60W A60 B22 827	No
929003003899	CoreProLEDbulb ND 13-100W A60 B22 927 UK	No
929003004002	CorePro LEDbulb ND 13-100W A60 B22 930	No
929003004099	CoreProLEDbulb ND 13-100W A60 B22 930 UK	No
929003544599	CorePro LEDbulb ND 11-75W A60 B22 927 UK	No
929003544602	CorePro LEDbulb ND 10.5-75W A60 B22 930	No
929003544699	CorePro LEDbulb ND 10.5-75W A60B22 930UK	No
929002306202	LEDbulb ND 8-60W A60 E27 827 6CT	No
929002306808	CorePro LEDbulb ND 13-100W A60 E27 827	No
929002306857	LEDbulb ND 13-100W A60 E27 827 1CT	No
929002306862	LEDbulb ND 13-100W A67 E27 827 2CT	No
929002306908	CorePro LEDbulb ND 13-100W A60 E27 840	No
929002306947	LEDbulb ND 13-100W A60 E27 840 1CT	No
929002306962	LEDbulb ND 13-100W A67 E27 840 2CT	No

Order Code	Full Product Name	T-Case Maximum (Nom)
929003543302	CorePro LEDbulb ND 8-60W A60 E27 927	95 °C
929003543385	CorePro LEDbulb ND 8-60W A60 E27 927 UK	95 °C
929003543402	CorePro LEDbulb ND 7.5-60W A60 E27 930	95 °C
929003543499	CorePro LEDbulb ND 7.5-60W A60 E27 930UK	95 °C
929003543502	CorePro LEDbulb ND 7.5-60W A60 E27 940	95 °C
929003543599	CorePro LEDbulb ND 7.5-60W A60 E27 940UK	95 °C
929003560908	CorePro LEDbulb ND 4.9-40W A60 E27 830	75 °C
929003564102	LEDbulb ND 4.9-40W A60 E27 840 2CT	-
929003564108	CorePro LEDbulb ND 4.9-40W A60 E27 840	75 °C
929003564147	LEDbulb ND 4.9-40W A60 E27 840 1CT	75 °C
929003604208	CorePro LEDbulb ND 4.9-40W A60 E27 865	75 °C
929003607408	CorePro LEDbulb ND 8-60W A60 E27 830	75 °C
929003607409	LEDbulb ND 8-60W A60 E27 830 12CT	90 °C
929003774009	LEDbulb ND 8-60W A60 E27 827 12CT	90 °C
929003774047	LEDbulb ND 8-60W A60 E27 827 1CT	95 °C
929001234002	CorePro LEDbulb ND 11-75W A60 B22 827	80 °C
929001234102	CorePro LEDbulb ND 13-100W A60 B22 827	85 °C
929001901102	CorePro LED Stick 7.5-57W E27 3CT 830	85 °C
929001901202	CorePro LED Stick 7.5-60W E27 3CT 840	85 °C
929003785202	CorePro LEDbulb DIM 8-60W A60 E27 5CCT	80 °C
929001234332	CorePro LEDbulbND 8-60W A60E27 827 3CT/8	85 °C
929003603202	CorePro LEDbulb ND 4.9-40W A60 E27 827	80 °C
929003603302	CorePro LEDbulb ND 4.9-40W A60 E27 840	80 °C
929003603432	CorePro LEDbulb ND 4.9-40W A60 E27 830	80 °C
929003603532	CorePro LEDbulb ND 4.9-40W A60 E27 865	80 °C
929002306274	CorePro LEDbulb ND 8-60W A60 E27 827 SKT	75 °C

Order Code	Full Product Name	Dimmable
929002307008	CorePro LEDbulb ND 13-100W A60 E27 865	No
929003607608	CorePro LEDbulb ND 13-100W A60 E27 830	No
929002306508	CorePro LEDbulb ND 10-75W A60 E27 827	No
929002306547	LEDbulb ND 10-75W A60 E27 827 1CT	No
929002306562	LEDbulb ND 10-75W A60 E27 827 2CT	No
929002306608	CorePro LEDbulb ND 10-75W A60 E27 840	No
929002306647	LEDbulb ND 10-75W A60 E27 840 1CT	No
929002306662	LEDbulb ND 10-75W A60 E27 840 2CT	No
929002306708	CorePro LEDbulb ND 10-75W A60 E27 865	No
929003544102	CorePro LEDbulb ND 11-75W A60 E27 927	No
929003544199	CorePro LEDbulb ND 11-75W A60 E27 927 UK	No
929003544202	CorePro LEDbulb ND 10.5-75W A60 E27 930	No
929003544299	CorePro LEDbulb ND 10.5-75W A60E27 930UK	No
929003544302	CorePro LEDbulb ND 10-75W A60 E27 940	No
929003544399	CorePro LEDbulb ND 10-75W A60 E27 940UK	No
929003607508	CorePro LEDbulb ND 10-75W A60 E27 830	No
929003542999	CoreProLEDbulb ND 4.9-40W A60 B22 927 UK	No
929003543002	CorePro LEDbulb ND 4.9-40W A60 B22 930	No
929003543099	CorePro LEDbulb ND 4.9-40W A60 B22 930UK	No
929003543799	CorePro LEDbulb ND 8-60W A60 B22 927 UK	No

CorePro Plastic LEDbulbs

Order Code	Full Product Name	Dimmable
929003543802	CorePro LEDbulb ND 7.5–60W A60 B22 930	No
929003543899	CoreProLEDbulb ND 7.5–60W A60 B22 930 UK	No
929003603102	CorePro LEDbulb ND 4.9–40W A60 B22 827	No
929002306208	CorePro LEDbulb ND 8–60W A60 E27 827	No
929002306262	LEDbulb ND 8–60W A60 E27 827 2CT	No
929002306308	CorePro LEDbulb ND 8–60W A60 E27 840	No
929002306309	LEDbulb ND 8–60W A60 E27 840 12CT	No
929002306347	LEDbulb ND 8–60W A60 E27 840 1CT	No
929002306362	LEDbulb ND 8–60W A60 E27 840 2CT	No
929002306408	CorePro LEDbulb ND 8–60W A60 E27 865	No
929003540202	LEDbulb ND 4.9–40W A60 E27 827 2CT	No
929003540208	CorePro LEDbulb ND 4.9–40W A60 E27 827	No
929003540247	LEDbulb ND 4.9–40W A60 E27 827 1CT	No
929003542502	CoreProLEDbulb ND 4.9–40W A60 E27 927	No
929003542599	CoreProLEDbulb ND 4.9–40W A60 E27 927 UK	No
929003542602	CorePro LEDbulb ND 4.9–40W A60 E27 930	No
929003542699	CorePro LEDbulb ND 4.9–40W A60 E27 930UK	No
929003542702	CorePro LEDbulb ND 4.9–40W A60 E27 940	No
929003542799	CorePro LEDbulb ND 4.9–40W A60 E27 940UK	No
929003543302	CorePro LEDbulb ND 8–60W A60 E27 927	No
929003543385	CorePro LEDbulb ND 8–60W A60 E27 927 UK	No
929003543402	CorePro LEDbulb ND 7.5–60W A60 E27 930	No
929003543499	CorePro LEDbulb ND 7.5–60W A60 E27 930UK	No

Order Code	Full Product Name	Dimmable
929003543502	CorePro LEDbulb ND 7.5–60W A60 E27 940	No
929003543599	CorePro LEDbulb ND 7.5–60W A60 E27 940UK	No
929003560908	CorePro LEDbulb ND 4.9–40W A60 E27 830	No
929003564102	LEDbulb ND 4.9–40W A60 E27 840 2CT	No
929003564108	CorePro LEDbulb ND 4.9–40W A60 E27 840	No
929003564147	LEDbulb ND 4.9–40W A60 E27 840 1CT	No
929003604208	CorePro LEDbulb ND 4.9–40W A60 E27 865	No
929003607408	CorePro LEDbulb ND 8–60W A60 E27 830	No
929003607409	LEDbulb ND 8–60W A60 E27 830 12CT	No
929003774009	LEDbulb ND 8–60W A60 E27 827 12CT	No
929003774047	LEDbulb ND 8–60W A60 E27 827 1CT	No
929001234002	CorePro LEDbulb ND 11–75W A60 B22 827	No
929001234102	CorePro LEDbulb ND 13–100W A60 B22 827	No
929001901102	CorePro LED Stick 7.5–57W E27 3CT 830	No
929001901202	CorePro LED Stick 7.5–60W E27 3CT 840	No
929003785202	CorePro LEDbulb DIM 8–60W A60 E27 5CCT	Only with specific dimmers
929001234332	CorePro LEDbulbND 8–60W A60E27 827 3CT/8	No
929003603202	CorePro LEDbulb ND 4.9–40W A60 E27 827	No
929003603302	CorePro LEDbulb ND 4.9–40W A60 E27 840	No
929003603432	CorePro LEDbulb ND 4.9–40W A60 E27 830	No
929003603532	CorePro LEDbulb ND 4.9–40W A60 E27 865	No
929002306274	CorePro LEDbulb ND 8–60W A60 E27 827 SKT	No

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929002306502	LEDbulb ND 10–75W A60 E27 827 6CT	A60
929003003702	CoreProLEDbulb ND 13–100W A60 E27 927	A60
929003003799	CoreProLEDbulb ND 13–100W A60 E27 927 UK	A60
929003003902	CorePro LEDbulb ND 13–100W A60 E27 930	A60
929003003999	CoreProLEDbulb ND 13–100W A60 E27 930 UK	A60
929003004102	CorePro LEDbulb ND 12.5–100W A60 E27 940	A60
929001233902	CorePro LEDbulb ND 8–60W A60 B22 827	A60
929003003899	CoreProLEDbulb ND 13–100W A60 B22 927 UK	A60
929003004002	CorePro LEDbulb ND 13–100W A60 B22 930	A60
929003004099	CoreProLEDbulb ND 13–100W A60 B22 930 UK	A60
929003544599	CorePro LEDbulb ND 11–75W A60 B22 927 UK	A60
929003544602	CorePro LEDbulb ND 10.5–75W A60 B22 930	A60
929003544699	CorePro LEDbulb ND 10.5–75W A60B22 930UK	A60
929002306202	LEDbulb ND 8–60W A60 E27 827 6CT	A60
929002306808	CorePro LEDbulb ND 13–100W A60 E27 827	A60
929002306857	LEDbulb ND 13–100W A60 E27 827 1CT	A60
929002306862	LEDbulb ND 13–100W A67 E27 827 2CT	A67
929002306908	CorePro LEDbulb ND 13–100W A60 E27 840	A60
929002306947	LEDbulb ND 13–100W A60 E27 840 1CT	A60
929002306962	LEDbulb ND 13–100W A67 E27 840 2CT	A67
929002307008	CorePro LEDbulb ND 13–100W A60 E27 865	A60
929003607608	CorePro LEDbulb ND 13–100W A60 E27 830	A60
929002306508	CorePro LEDbulb ND 10–75W A60 E27 827	A60
929002306547	LEDbulb ND 10–75W A60 E27 827 1CT	A60
929002306562	LEDbulb ND 10–75W A60 E27 827 2CT	A60

Order Code	Full Product Name	Bulb Shape
929002306608	CorePro LEDbulb ND 10–75W A60 E27 840	A60
929002306647	LEDbulb ND 10–75W A60 E27 840 1CT	A60
929002306662	LEDbulb ND 10–75W A60 E27 840 2CT	A60
929002306708	CorePro LEDbulb ND 10–75W A60 E27 865	A60
929003544102	CorePro LEDbulb ND 11–75W A60 E27 927	A60
929003544199	CorePro LEDbulb ND 11–75W A60 E27 927 UK	A60
929003544202	CorePro LEDbulb ND 10.5–75W A60 E27 930	A60
929003544299	CorePro LEDbulb ND 10.5–75W A60E27 930UK	A60
929003544302	CorePro LEDbulb ND 10–75W A60 E27 940	A60
929003544399	CorePro LEDbulb ND 10–75W A60 E27 940UK	A60
929003607508	CorePro LEDbulb ND 10–75W A60 E27 830	A60
929003542999	CoreProLEDbulb ND 4.9–40W A60 B22 927 UK	A60
929003543002	CorePro LEDbulb ND 4.9–40W A60 B22 930	A60
929003543099	CorePro LEDbulb ND 4.9–40W A60 B22 930UK	A60
929003543799	CorePro LEDbulb ND 8–60W A60 B22 927 UK	A60
929003543802	CorePro LEDbulb ND 7.5–60W A60 B22 930	A60
929003543899	CoreProLEDbulb ND 7.5–60W A60 B22 930 UK	A60
929003603102	CorePro LEDbulb ND 4.9–40W A60 B22 827	A60
929002306208	CorePro LEDbulb ND 8–60W A60 E27 827	A60
929002306262	LEDbulb ND 8–60W A60 E27 827 2CT	A60
929002306308	CorePro LEDbulb ND 8–60W A60 E27 840	A60
929002306309	LEDbulb ND 8–60W A60 E27 840 12CT	A60
929002306347	LEDbulb ND 8–60W A60 E27 840 1CT	A60
929002306362	LEDbulb ND 8–60W A60 E27 840 2CT	A60
929002306408	CorePro LEDbulb ND 8–60W A60 E27 865	A60

CorePro Plastic LEDbulbs

Order Code	Full Product Name	Bulb Shape
929003540202	LEDbulb ND 4.9-40W A60 E27 827 2CT	A60
929003540208	CorePro LEDbulb ND 4.9-40W A60 E27 827	A60
929003540247	LEDbulb ND 4.9-40W A60 E27 827 1CT	A60
929003542502	CoreProLEDbulb ND 4.9-40W A60 E27 927	A60
929003542599	CoreProLEDbulb ND 4.9-40W A60 E27 927 UK	A60
929003542602	CorePro LEDbulb ND 4.9-40W A60 E27 930	A60
929003542699	CorePro LEDbulb ND 4.9-40W A60 E27 930UK	A60
929003542702	CorePro LEDbulb ND 4.9-40W A60 E27 940	A60
929003542799	CorePro LEDbulb ND 4.9-40W A60 E27 940UK	A60
929003543302	CorePro LEDbulb ND 8-60W A60 E27 927	A60
929003543385	CorePro LEDbulb ND 8-60W A60 E27 927 UK	A60
929003543402	CorePro LEDbulb ND 7.5-60W A60 E27 930	A60
929003543499	CorePro LEDbulb ND 7.5-60W A60 E27 930UK	A60
929003543502	CorePro LEDbulb ND 7.5-60W A60 E27 940	A60
929003543599	CorePro LEDbulb ND 7.5-60W A60 E27 940UK	A60
929003560908	CorePro LEDbulb ND 4.9-40W A60 E27 830	A60
929003564102	LEDbulb ND 4.9-40W A60 E27 840 2CT	A60
929003564108	CorePro LEDbulb ND 4.9-40W A60 E27 840	A60

Order Code	Full Product Name	Bulb Shape
929003564147	LEDbulb ND 4.9-40W A60 E27 840 1CT	A60
929003604208	CorePro LEDbulb ND 4.9-40W A60 E27 865	A60
929003607408	CorePro LEDbulb ND 8-60W A60 E27 830	A60
929003607409	LEDbulb ND 8-60W A60 E27 830 12CT	A60
929003774009	LEDbulb ND 8-60W A60 E27 827 12CT	A60
929003774047	LEDbulb ND 8-60W A60 E27 827 1CT	A60
929001234002	CorePro LEDbulb ND 11-75W A60 B22 827	A60
929001234102	CorePro LEDbulb ND 13-100W A60 B22 827	A60
929001901102	CorePro LED Stick 7.5-57W E27 3CT 830	Stick
929001901202	CorePro LED Stick 7.5-60W E27 3CT 840	Stick
929003785202	CorePro LEDbulb DIM 8-60W A60 E27 5CCT	A60
929001234332	CorePro LEDbulbND 8-60W A60E27 827 3CT/8	A60
929003603202	CorePro LEDbulb ND 4.9-40W A60 E27 827	A60
929003603302	CorePro LEDbulb ND 4.9-40W A60 E27 840	A60
929003603432	CorePro LEDbulb ND 4.9-40W A60 E27 830	A60
929003603532	CorePro LEDbulb ND 4.9-40W A60 E27 865	A60
929002306274	CorePro LEDbulb ND 8-60W A60 E27 827 SKT	A60

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929002306502	LEDbulb ND 10-75W A60 E27 827 6CT	-	10 kWh
929003003702	CoreProLEDbulb ND 13-100W A60 E27 927	-20 °C to 45 °C	13 kWh
929003003799	CoreProLEDbulb ND 13-100W A60 E27 927 UK	-20 °C to 45 °C	13 kWh
929003003902	CorePro LEDbulb ND 13-100W A60 E27 930	-	13 kWh
929003003999	CoreProLEDbulb ND 13-100W A60 E27 930 UK	-	13 kWh
929003004102	CorePro LEDbulb ND 12.5-100W A60 E27 940	-	13 kWh
929001233902	CorePro LEDbulb ND 8-60W A60 B22 827	-	8 kWh
929003003899	CoreProLEDbulb ND 13-100W A60 B22 927 UK	-20 °C to 45 °C	13 kWh
929003004002	CorePro LEDbulb ND 13-100W A60 B22 930	-	13 kWh
929003004099	CoreProLEDbulb ND 13-100W A60 B22 930 UK	-	13 kWh
929003544599	CorePro LEDbulb ND 11-75W A60 B22 927 UK	-20 °C to 45 °C	11 kWh
929003544602	CorePro LEDbulb ND 10.5-75W A60 B22 930	-20 °C to 45 °C	11 kWh
929003544699	CorePro LEDbulb ND 10.5-75W A60B22 930UK	-20 °C to 45 °C	11 kWh
929002306202	LEDbulb ND 8-60W A60 E27 827 6CT	-	8 kWh

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929002306808	CorePro LEDbulb ND 13-100W A60 E27 827	-20 °C to 45 °C	13 kWh
929002306857	LEDbulb ND 13-100W A60 E27 827 1CT	-20 to +45 °C	13 kWh
929002306862	LEDbulb ND 13-100W A67 E27 827 2CT	-20 °C to 45 °C	13 kWh
929002306908	CorePro LEDbulb ND 13-100W A60 E27 840	-20 °C to 45 °C	13 kWh
929002306947	LEDbulb ND 13-100W A60 E27 840 1CT	-20 to +45 °C	13 kWh
929002306962	LEDbulb ND 13-100W A67 E27 840 2CT	-20 °C to 45 °C	13 kWh
929002307008	CorePro LEDbulb ND 13-100W A60 E27 865	-20 °C to 45 °C	13 kWh
929003607608	CorePro LEDbulb ND 13-100W A60 E27 830	-20 °C to 45 °C	13 kWh
929002306508	CorePro LEDbulb ND 10-75W A60 E27 827	-20 °C to 45 °C	10 kWh
929002306547	LEDbulb ND 10-75W A60 E27 827 1CT	-20 to +45 °C	10 kWh
929002306562	LEDbulb ND 10-75W A60 E27 827 2CT	-20 °C to 45 °C	10 kWh
929002306608	CorePro LEDbulb ND 10-75W A60 E27 840	-20 °C to 45 °C	10 kWh
929002306647	LEDbulb ND 10-75W A60 E27 840 1CT	-20 to +45 °C	10 kWh
929002306662	LEDbulb ND 10-75W A60 E27 840 2CT	-20 °C to 45 °C	10 kWh









CorePro Plastic LEDbulbs

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929002306708	CorePro LEDbulb ND 10-75W A60 E27 865	-20 °C to 45 °C	10 kWh
929003544102	CorePro LEDbulb ND 11-75W A60 E27 927	-20 °C to 45 °C	11 kWh
929003544199	CorePro LEDbulb ND 11-75W A60 E27 927 UK	-20 °C to 45 °C	11 kWh
929003544202	CorePro LEDbulb ND 10.5-75W A60 E27 930	-20 °C to 45 °C	11 kWh
929003544299	CorePro LEDbulb ND 10.5-75W A60E27 930UK	-20 °C to 45 °C	11 kWh
929003544302	CorePro LEDbulb ND 10-75W A60 E27 940	-20 °C to 45 °C	10 kWh
929003544399	CorePro LEDbulb ND 10-75W A60 E27 940UK	-20 °C to 45 °C	10 kWh
929003607508	CorePro LEDbulb ND 10-75W A60 E27 830	-20 °C to 45 °C	10 kWh
929003542999	CoreProLEDbulb ND 4.9-40W A60 B22 927 UK	-20 °C to 45 °C	5 kWh
929003543002	CorePro LEDbulb ND 4.9-40W A60 B22 930	-20 °C to 45 °C	5 kWh
929003543099	CorePro LEDbulb ND 4.9-40W A60 B22 930UK	-20 °C to 45 °C	5 kWh
929003543799	CorePro LEDbulb ND 8-60W A60 B22 927 UK	-20 °C to 45 °C	8 kWh
929003543802	CorePro LEDbulb ND 7.5-60W A60 B22 930	-20 °C to 45 °C	8 kWh
929003543899	CoreProLEDbulb ND 7.5-60W A60 B22 930 UK	-20 °C to 45 °C	8 kWh
929003603102	CorePro LEDbulb ND 4.9-40W A60 B22 827	-20 °C to 45 °C	5 kWh
929002306208	CorePro LEDbulb ND 8-60W A60 E27 827	-20 °C to 45 °C	8 kWh
929002306262	LEDbulb ND 8-60W A60 E27 827 2CT	-20 °C to 45 °C	8 kWh
929002306308	CorePro LEDbulb ND 8-60W A60 E27 840	-20 °C to 45 °C	8 kWh
929002306309	LEDbulb ND 8-60W A60 E27 840 12CT	-20 to +45 °C	8 kWh
929002306347	LEDbulb ND 8-60W A60 E27 840 1CT	-20 to +45 °C	8 kWh
929002306362	LEDbulb ND 8-60W A60 E27 840 2CT	-20 °C to 45 °C	8 kWh
929002306408	CorePro LEDbulb ND 8-60W A60 E27 865	-20 °C to 45 °C	8 kWh
929003540202	LEDbulb ND 4.9-40W A60 E27 827 2CT	-20 °C to 45 °C	5 kWh
929003540208	CorePro LEDbulb ND 4.9-40W A60 E27 827	-20 °C to 45 °C	5 kWh
929003540247	LEDbulb ND 4.9-40W A60 E27 827 1CT	-20 to +45 °C	5 kWh











Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929003542502	CoreProLEDbulb ND 4.9-40W A60 E27 927	-20 °C to 45 °C	5 kWh
929003542599	CoreProLEDbulb ND 4.9-40W A60 E27 927 UK	-20 °C to 45 °C	5 kWh
929003542602	CorePro LEDbulb ND 4.9-40W A60 E27 930	-20 °C to 45 °C	5 kWh
929003542699	CorePro LEDbulb ND 4.9-40W A60 E27 930UK	-20 °C to 45 °C	5 kWh
929003542702	CorePro LEDbulb ND 4.9-40W A60 E27 940	-20 °C to 45 °C	5 kWh
929003542799	CorePro LEDbulb ND 4.9-40W A60 E27 940UK	-20 °C to 45 °C	5 kWh
929003543302	CorePro LEDbulb ND 8-60W A60 E27 927	-20 °C to 45 °C	8 kWh
929003543385	CorePro LEDbulb ND 8-60W A60 E27 927 UK	-20 °C to 45 °C	8 kWh
929003543402	CorePro LEDbulb ND 7.5-60W A60 E27 930	-20 °C to 45 °C	8 kWh
929003543499	CorePro LEDbulb ND 7.5-60W A60 E27 930UK	-20 °C to 45 °C	8 kWh
929003543502	CorePro LEDbulb ND 7.5-60W A60 E27 940	-20 °C to 45 °C	8 kWh
929003543599	CorePro LEDbulb ND 7.5-60W A60 E27 940UK	-20 °C to 45 °C	8 kWh
929003560908	CorePro LEDbulb ND 4.9-40W A60 E27 830	-20 °C to 45 °C	5 kWh
929003564102	LEDbulb ND 4.9-40W A60 E27 840 2CT	-20 °C to 45 °C	5 kWh
929003564108	CorePro LEDbulb ND 4.9-40W A60 E27 840	-20 °C to 45 °C	5 kWh
929003564147	LEDbulb ND 4.9-40W A60 E27 840 1CT	-20 to +45 °C	5 kWh
929003604208	CorePro LEDbulb ND 4.9-40W A60 E27 865	-20 °C to 45 °C	5 kWh
929003607408	CorePro LEDbulb ND 8-60W A60 E27 830	-20 °C to 45 °C	8 kWh
929003607409	LEDbulb ND 8-60W A60 E27 830 12CT	-20 to +45 °C	8 kWh
929003774009	LEDbulb ND 8-60W A60 E27 827 12CT	-20 to +45 °C	8 kWh
929003774047	LEDbulb ND 8-60W A60 E27 827 1CT	-20 to +45 °C	8 kWh
929001234002	CorePro LEDbulb ND 11-75W A60 B22 827	-	11 kWh
929001234102	CorePro LEDbulb ND 13-100W A60 B22 827	-	13 kWh
929001901102	CorePro LED Stick 7.5-57W E27 3CT 830	-20 °C to 45 °C	8 kWh
929001901202	CorePro LED Stick 7.5-60W E27 3CT 840	-20 °C to 45 °C	8 kWh

CorePro Plastic LEDbulbs











Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
929003785202	CorePro LEDbulb DIM 8-60W A60 E27 5CCT	-20 to +45 °C	8 kWh
929001234332	CorePro LEDbulbND 8-60W A60E27 827 3CT/8	-	8 kWh
929003603202	CorePro LEDbulb ND 4.9-40W A60 E27 827	-20 °C to 45 °C	5 kWh
929003603302	CorePro LEDbulb ND 4.9-40W A60 E27 840	-20 °C to 45 °C	5 kWh
929003603432	CorePro LEDbulb ND 4.9-40W A60 E27 830	-20 °C to 45 °C	5 kWh
929003603532	CorePro LEDbulb ND 4.9-40W A60 E27 865	-20 °C to 45 °C	5 kWh
929002306274	CorePro LEDbulb ND 8-60W A60 E27 827 SKT	-20 °C to 45 °C	8 kWh












CorePro Plastic LEDbulbs



CorePro Plastic LEDbulbs



CorePro Plastic LEDbulbs



CorePro Plastic LEDbulbs

