



The affordable LEDbulb solution

CorePro Plastic LEDbulbs

CorePro LEDbulbs are compatible with existing fixtures with an E27 or B22 holder and are designed for retrofit replacement of incandescent bulbs. They deliver huge energy savings and minimize maintenance cost.

Benefits

- Warm white light
- Up to 80% energy saving
- Lower maintenance costs

Features

- non dimmable
- warm white light
- lifetime of 15000 to 25000 hours
- UV- and IR-free light for less heat and protection for heat-sensitive objects

Application

- Hotels, restaurants, bars, cafés, museums, shops
- Hotel rooms, lobbies, corridors, stairwells, washrooms, reception areas , exhibitions, display cabinets

CorePro Plastic LEDbulbs

Versions



LED Lamps, LEDbulb A60 B22



CorePro LEDbulb 75W B22 827 FR A60



LED Bulb 9W B22 AU







LEDbulb CorePro B22 A60 5W



LED Bulb 9W E27 DS FR DIM 1PF 6 AU RTP

CorePro Plastic LEDbulbs

Dimensional drawing



Product	D	C
CorePro LEDbulb ND 10.5-75W A60 B22 930	60 mm	107 mm
CorePro LEDbulb ND 4.9-40W A60 B22 930	60 mm	105 mm
CorePro LEDbulb ND 7.5-60W A60 B22 930	60 mm	105 mm





Product	D	C
CorePro LEDbulb ND 10-75W A60 E27 827	60 mm	108 mm
CorePro LEDbulb ND 10-75W A60 E27 830	60 mm	108 mm
CorePro LEDbulb ND 10-75W A60 E27 840	60 mm	108 mm
CorePro LEDbulb ND 10-75W A60 E27 865	60 mm	108 mm
CorePro LEDbulb ND 10-75W A60 E27 940	60 mm	109 mm
CorePro LEDbulb ND 10.5-75W A60 E27 930	60 mm	109 mm
CorePro LEDbulb ND 11-75W A60 E27 927	60 mm	109 mm
LEDbulb ND 10-75W A60 E27 827 1CT	60 mm	108 mm
LEDbulb ND 10-75W A60 E27 827 2CT	60 mm	108 mm
LEDbulb ND 10-75W A60 E27 840 1CT	60 mm	108 mm
LEDbulb ND 10-75W A60 E27 840 2CT	60 mm	108 mm

Product	D	C
CorePro LEDbulb ND 13-100W A60 B22 930	60 mm	110 mm

Product	D	C
CorePro LEDbulb DIM 8-60W A60 E27 5CCT	60 mm	115 mm

CorePro Plastic LEDbulbs

Dimensional drawing



Product	D	C
CorePro LEDbulb ND 13-100W A60 E27 827	60 mm	120 mm
CorePro LEDbulb ND 13-100W A60 E27 830	60 mm	120 mm
CorePro LEDbulb ND 13-100W A60 E27 840	60 mm	120 mm
CorePro LEDbulb ND 13-100W A60 E27 865	60 mm	120 mm
LEDbulb ND 13-100W A60 E27 827 1CT	60 mm	120 mm
LEDbulb ND 13-100W A60 E27 840 1CT	60 mm	120 mm
LEDbulb ND 13-100W A67 E27 827 2CT	60 mm	120 mm
LEDbulb ND 13-100W A67 E27 840 2CT	60 mm	120 mm




Product	D	C
CorePro LEDbulb ND 8-60W A60 B22 827	60 mm	110 mm

Product	D	C
CorePro LEDbulbND 8-60W A60E27 827 3CT/8	60 mm	110 mm

Product	D	C
CorePro LEDbulb ND 11-75W A60 B22 827	60 mm	110 mm
CorePro LEDbulb ND 13-100W A60 B22 827	60 mm	110 mm

CorePro Plastic LEDbulbs

Dimensional drawing



Product	D	C
CorePro LEDbulb ND 12.5-100W A60 E27 940	60 mm	110 mm
CorePro LEDbulb ND 13-100W A60 E27 930	60 mm	110 mm
CoreProLEDbulb ND 13-100W A60 E27 927	60 mm	120 mm

Product	D	C
CorePro LEDbulb ND 4.9-40W A60 B22 827	60 mm	110 mm

Product	D	C
CorePro LEDbulb ND 4.9-40W A60 E27 827	60 mm	110 mm
CorePro LEDbulb ND 4.9-40W A60 E27 827	60 mm	107 mm
CorePro LEDbulb ND 4.9-40W A60 E27 830	60 mm	110 mm
CorePro LEDbulb ND 4.9-40W A60 E27 830	60 mm	107 mm
CorePro LEDbulb ND 4.9-40W A60 E27 840	60 mm	108 mm
CorePro LEDbulb ND 4.9-40W A60 E27 840	60 mm	110 mm
CorePro LEDbulb ND 4.9-40W A60 E27 865	60 mm	107 mm
CorePro LEDbulb ND 4.9-40W A60 E27 865	60 mm	110 mm
CorePro LEDbulb ND 4.9-40W A60 E27 930	60 mm	107 mm
CorePro LEDbulb ND 4.9-40W A60 E27 940	60 mm	107 mm
CorePro LEDbulb ND 7.5-60W A60 E27 930	60 mm	107 mm
CorePro LEDbulb ND 7.5-60W A60 E27 940	60 mm	107 mm
CorePro LEDbulb ND 8-60W A60 E27 827	60 mm	108 mm
CorePro LEDbulb ND 8-60W A60 E27 830	60 mm	108 mm
CorePro LEDbulb ND 8-60W A60 E27 840	60 mm	108 mm
CorePro LEDbulb ND 8-60W A60 E27 865	60 mm	108 mm
CorePro LEDbulb ND 8-60W A60 E27 927	60 mm	107 mm
CoreProLEDbulb ND 4.9-40W A60 E27 927	60 mm	107 mm
LEDbulb ND 4.9-40W A60 E27 827 1CT	60 mm	108 mm
LEDbulb ND 4.9-40W A60 E27 827 2CT	60 mm	107 mm
LEDbulb ND 4.9-40W A60 E27 840 1CT	60 mm	108 mm
LEDbulb ND 4.9-40W A60 E27 840 2CT	60 mm	108 mm
LEDbulb ND 8-60W A60 E27 827 12CT	60 mm	107 mm
LEDbulb ND 8-60W A60 E27 827 1CT	60 mm	108 mm
LEDbulb ND 8-60W A60 E27 827 2CT	60 mm	108 mm
LEDbulb ND 8-60W A60 E27 830 12CT	60 mm	107 mm

CorePro Plastic LEDbulbs

Dimensional drawing

Product	D	C
LEDbulb ND 8-60W A60 E27 840 12CT	60 mm	107 mm
LEDbulb ND 8-60W A60 E27 840 1CT	60 mm	108 mm
LEDbulb ND 8-60W A60 E27 840 2CT	60 mm	108 mm

General Information	
Switching Cycle	50,000
Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Starting Time (Nom)	0.5 s
Mechanical and Housing	
Bulb Finish	Frosted

General Information

Order Code	Full Product Name	Cap-Base	Nominal lifetime
47520500	CoreProLEDbulb ND 13-100W A60 E27 927	E27	15,000 hour(s)
32968300	CorePro LEDbulb ND 13-100W A60 E27 930	E27	15,000 hour(s)
32970600	CorePro LEDbulb ND 12.5-100W A60 E27 940	E27	15,000 hour(s)
57763900	CorePro LEDbulb ND 8-60W A60 B22 827	B22	15,000 hour(s)
32978200	CorePro LEDbulb ND 13-100W A60 B22 930	B22	15,000 hour(s)
32976800	CorePro LEDbulb ND 10.5-75W A60 B22 930	B22	15,000 hour(s)
16901200	CorePro LEDbulb ND 13-100W A60 E27 827	E27	15,000 hour(s)
05770900	LEDbulb ND 13-100W A60 E27 827 1CT	E27	15,000 hour(s)
47105400	LEDbulb ND 13-100W A67 E27 827 2CT	E27	15,000 hour(s)
16909800	CorePro LEDbulb ND 13-100W A60 E27 840	E27	15,000 hour(s)
05772300	LEDbulb ND 13-100W A60 E27 840 1CT	E27	15,000 hour(s)
47103000	LEDbulb ND 13-100W A67 E27 840 2CT	E27	15,000 hour(s)
16925800	CorePro LEDbulb ND 13-100W A60 E27 865	E27	15,000 hour(s)
16917300	CorePro LEDbulb ND 13-100W A60 E27 830	E27	15,000 hour(s)
16899200	CorePro LEDbulb ND 10-75W A60 E27 827	E27	15,000 hour(s)
05766200	LEDbulb ND 10-75W A60 E27 827 1CT	E27	15,000 hour(s)
47111500	LEDbulb ND 10-75W A60 E27 827 2CT	E27	15,000 hour(s)
16907400	CorePro LEDbulb ND 10-75W A60 E27 840	E27	15,000 hour(s)
05768600	LEDbulb ND 10-75W A60 E27 840 1CT	E27	15,000 hour(s)
47101600	LEDbulb ND 10-75W A60 E27 840 2CT	E27	15,000 hour(s)
16923400	CorePro LEDbulb ND 10-75W A60 E27 865	E27	15,000 hour(s)
47514400	CorePro LEDbulb ND 11-75W A60 E27 927	E27	15,000 hour(s)
32964500	CorePro LEDbulb ND 10.5-75W A60 E27 930	E27	15,000 hour(s)
32966900	CorePro LEDbulb ND 10-75W A60 E27 940	E27	15,000 hour(s)
16915900	CorePro LEDbulb ND 10-75W A60 E27 830	E27	15,000 hour(s)
32972000	CorePro LEDbulb ND 4.9-40W A60 B22 930	B22	15,000 hour(s)
32974400	CorePro LEDbulb ND 7.5-60W A60 B22 930	B22	15,000 hour(s)

Order Code	Full Product Name	Cap-Base	Nominal lifetime
57765300	CorePro LEDbulb ND 4.9-40W A60 B22 827	B22	15,000 hour(s)
16897800	CorePro LEDbulb ND 8-60W A60 E27 827	E27	15,000 hour(s)
47109200	LEDbulb ND 8-60W A60 E27 827 2CT	E27	15,000 hour(s)
16905000	CorePro LEDbulb ND 8-60W A60 E27 840	E27	15,000 hour(s)
32471800	LEDbulb ND 8-60W A60 E27 840 12CT	E27	15,000 hour(s)
05764800	LEDbulb ND 8-60W A60 E27 840 1CT	E27	15,000 hour(s)
47097200	LEDbulb ND 8-60W A60 E27 840 2CT	E27	15,000 hour(s)
16921000	CorePro LEDbulb ND 8-60W A60 E27 865	E27	15,000 hour(s)
47107800	LEDbulb ND 4.9-40W A60 E27 827 2CT	E27	15,000 hour(s)
16895400	CorePro LEDbulb ND 4.9-40W A60 E27 827	E27	15,000 hour(s)
05774700	LEDbulb ND 4.9-40W A60 E27 827 1CT	E27	15,000 hour(s)
47518200	CoreProLEDbulb ND 4.9-40W A60 E27 927	E27	15,000 hour(s)
32956000	CorePro LEDbulb ND 4.9-40W A60 E27 930	E27	15,000 hour(s)
32958400	CorePro LEDbulb ND 4.9-40W A60 E27 940	E27	15,000 hour(s)
47516800	CorePro LEDbulb ND 8-60W A60 E27 927	E27	15,000 hour(s)
32960700	CorePro LEDbulb ND 7.5-60W A60 E27 930	E27	15,000 hour(s)
32962100	CorePro LEDbulb ND 7.5-60W A60 E27 940	E27	15,000 hour(s)
16911100	CorePro LEDbulb ND 4.9-40W A60 E27 830	E27	10,000 hour(s)
47099600	LEDbulb ND 4.9-40W A60 E27 840 2CT	E27	15,000 hour(s)
16903600	CorePro LEDbulb ND 4.9-40W A60 E27 840	E27	15,000 hour(s)
05776100	LEDbulb ND 4.9-40W A60 E27 840 1CT	E27	15,000 hour(s)
16919700	CorePro LEDbulb ND 4.9-40W A60 E27 865	E27	15,000 hour(s)
16913500	CorePro LEDbulb ND 8-60W A60 E27 830	E27	15,000 hour(s)
32469500	LEDbulb ND 8-60W A60 E27 830 12CT	E27	15,000 hour(s)
32511100	LEDbulb ND 8-60W A60 E27 827 12CT	E27	15,000 hour(s)
05762400	LEDbulb ND 8-60W A60 E27 827 1CT	E27	15,000 hour(s)
57761500	CorePro LEDbulb ND 11-75W A60 B22 827	B22	15,000 hour(s)

CorePro Plastic LEDbulbs

Order Code	Full Product Name	Cap-Base	Nominal lifetime
51002500	CorePro LEDbulb ND 13-100W A60 B22 827	B22	15,000 hour(s)
35333600	CorePro LEDbulb DIM 8-60W A60 E27 5CCT	E27	15,000 hour(s)
70033100	CorePro LEDbulbND 8-60W A60E27 827	E27	15,000 hour(s)
	3CT/8		

Order Code	Full Product Name	Cap-Base	Nominal lifetime
57757800	CorePro LEDbulb ND 4.9-40W A60 E27 827	E27	15,000 hour(s)
57779000	CorePro LEDbulb ND 4.9-40W A60 E27 840	E27	15,000 hour(s)
57993000	CorePro LEDbulb ND 4.9-40W A60 E27 830	E27	15,000 hour(s)
57787500	CorePro LEDbulb ND 4.9-40W A60 E27 865	E27	15,000 hour(s)

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index		
				(CRI)	Color Code	Luminous Flux
47520500	CoreProLEDbulb ND 13-100W A60 E27 927	180 degree(s)	2700 K	90	927	1,521 lm
32968300	CorePro LEDbulb ND 13-100W A60 E27 930	200 degree(s)	3000 K	90	930	1,521 lm
32970600	CorePro LEDbulb ND 12.5-100W A60 E27 940	200 degree(s)	4000 K	90	940	1,521 lm
57763900	CorePro LEDbulb ND 8-60W A60 B22 827	200 degree(s)	2700 K	80	827	806 lm
32978200	CorePro LEDbulb ND 13-100W A60 B22 930	200 degree(s)	3000 K	90	930	1,521 lm
32976800	CorePro LEDbulb ND 10.5-75W A60 B22 930	180 degree(s)	3000 K	90	930	1,055 lm
16901200	CorePro LEDbulb ND 13-100W A60 E27 827	180 degree(s)	2700 K	80	827	1,521 lm
05770900	LEDbulb ND 13-100W A60 E27 827 1CT	180 degree(s)	2700 K	80	827	1,521 lm
47105400	LEDbulb ND 13-100W A67 E27 827 2CT	180 degree(s)	2700 K	80	827	1,521 lm
16909800	CorePro LEDbulb ND 13-100W A60 E27 840	180 degree(s)	4000 K	80	840	1,521 lm
05772300	LEDbulb ND 13-100W A60 E27 840 1CT	180 degree(s)	4000 K	80	840	1,521 lm
47103000	LEDbulb ND 13-100W A67 E27 840 2CT	180 degree(s)	4000 K	80	840	1,521 lm
16925800	CorePro LEDbulb ND 13-100W A60 E27 865	180 degree(s)	6500 K	80	865	1,521 lm
16917300	CorePro LEDbulb ND 13-100W A60 E27 830	180 degree(s)	3000 K	80	830	1,521 lm
16899200	CorePro LEDbulb ND 10-75W A60 E27 827	180 degree(s)	2700 K	80	827	1,055 lm
05766200	LEDbulb ND 10-75W A60 E27 827 1CT	180 degree(s)	2700 K	80	827	1,055 lm
47111500	LEDbulb ND 10-75W A60 E27 827 2CT	180 degree(s)	2700 K	80	827	1,055 lm
16907400	CorePro LEDbulb ND 10-75W A60 E27 840	180 degree(s)	4000 K	80	840	1,055 lm
05768600	LEDbulb ND 10-75W A60 E27 840 1CT	180 degree(s)	4000 K	80	840	1,055 lm
47101600	LEDbulb ND 10-75W A60 E27 840 2CT	180 degree(s)	4000 K	80	840	1,055 lm
16923400	CorePro LEDbulb ND 10-75W A60 E27 865	180 degree(s)	6500 K	80	865	1,055 lm
47514400	CorePro LEDbulb ND 11-75W A60 E27 927	180 degree(s)	2700 K	90	927	1,055 lm
32964500	CorePro LEDbulb ND 10.5-75W A60 E27 930	180 degree(s)	3000 K	90	930	1,055 lm
32966900	CorePro LEDbulb ND 10-75W A60 E27 940	180 degree(s)	4000 K	90	940	1,055 lm
16915900	CorePro LEDbulb ND 10-75W A60 E27 830	180 degree(s)	3000 K	80	830	1,055 lm
32972000	CorePro LEDbulb ND 4.9-40W A60 B22 930	180 degree(s)	3000 K	90	930	470 lm
32974400	CorePro LEDbulb ND 7.5-60W A60 B22 930	180 degree(s)	3000 K	90	930	806 lm
57765300	CorePro LEDbulb ND 4.9-40W A60 B22 827	200 degree(s)	2700 K	80	827	470 lm
16897800	CorePro LEDbulb ND 8-60W A60 E27 827	180 degree(s)	2700 K	80	827	806 lm
47109200	LEDbulb ND 8-60W A60 E27 827 2CT	180 degree(s)	2700 K	80	827	806 lm
16905000	CorePro LEDbulb ND 8-60W A60 E27 840	180 degree(s)	4000 K	80	840	806 lm
32471800	LEDbulb ND 8-60W A60 E27 840 12CT	150 degree(s)	4000 K	80	840	806 lm
05764800	LEDbulb ND 8-60W A60 E27 840 1CT	180 degree(s)	4000 K	80	840	806 lm
47097200	LEDbulb ND 8-60W A60 E27 840 2CT	180 degree(s)	4000 K	80	840	806 lm
16921000	CorePro LEDbulb ND 8-60W A60 E27 865	180 degree(s)	6500 K	80	865	806 lm
47107800	LEDbulb ND 4.9-40W A60 E27 827 2CT	180 degree(s)	2700 K	80	827	470 lm
16895400	CorePro LEDbulb ND 4.9-40W A60 E27 827	180 degree(s)	2700 K	80	827	470 lm
05774700	LEDbulb ND 4.9-40W A60 E27 827 1CT	180 degree(s)	2700 K	80	827	470 lm
47518200	CoreProLEDbulb ND 4.9-40W A60 E27 927	180 degree(s)	2700 K	90	927	470 lm
32956000	CorePro LEDbulb ND 4.9-40W A60 E27 930	180 degree(s)	3000 K	90	930	470 lm
32958400	CorePro LEDbulb ND 4.9-40W A60 E27 940	180 degree(s)	4000 K	90	940	470 lm
47516800	CorePro LEDbulb ND 8-60W A60 E27 927	180 degree(s)	2700 K	90	927	806 lm

CorePro Plastic LEDbulbs

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index		Luminous Flux
				(CRI)	Color Code	
32960700	CorePro LEDbulb ND 7.5-60W A60 E27 930	180 degree(s)	3000 K	90	930	806 lm
32962100	CorePro LEDbulb ND 7.5-60W A60 E27 940	180 degree(s)	4000 K	90	940	806 lm
16911100	CorePro LEDbulb ND 4.9-40W A60 E27 830	180 degree(s)	3000 K	80	830	470 lm
47099600	LEDbulb ND 4.9-40W A60 E27 840 2CT	180 degree(s)	4000 K	80	840	470 lm
16903600	CorePro LEDbulb ND 4.9-40W A60 E27 840	180 degree(s)	4000 K	80	840	470 lm
05776100	LEDbulb ND 4.9-40W A60 E27 840 1CT	180 degree(s)	4000 K	80	840	470 lm
16919700	CorePro LEDbulb ND 4.9-40W A60 E27 865	180 degree(s)	6500 K	80	865	470 lm
16913500	CorePro LEDbulb ND 8-60W A60 E27 830	180 degree(s)	3000 K	80	830	806 lm
32469500	LEDbulb ND 8-60W A60 E27 830 12CT	150 degree(s)	3000 K	80	830	806 lm
32511100	LEDbulb ND 8-60W A60 E27 827 12CT	150 degree(s)	2700 K	80	827	806 lm
05762400	LEDbulb ND 8-60W A60 E27 827 1CT	180 degree(s)	2700 K	80	827	806 lm
57761500	CorePro LEDbulb ND 11-75W A60 B22 827	200 degree(s)	2700 K	80	827	1,055 lm
51002500	CorePro LEDbulb ND 13-100W A60 B22 827	200 degree(s)	2700 K	80	827	1,521 lm
35333600	CorePro LEDbulb DIM 8-60W A60 E27 5CCT	200 degree(s)	2700 K	80	2700K/3000K/ 4000K/5000K/ 6500K	806 lm
70033100	CorePro LEDbulbND 8-60W A60E27 827 3CT/8	200 degree(s)	2700 K	80	827	806 lm
57757800	CorePro LEDbulb ND 4.9-40W A60 E27 827	200 degree(s)	2700 K	80	827	470 lm
57779000	CorePro LEDbulb ND 4.9-40W A60 E27 840	200 degree(s)	4000 K	80	840	470 lm
57993000	CorePro LEDbulb ND 4.9-40W A60 E27 830	200 degree(s)	3000 K	80	830	470 lm
57787500	CorePro LEDbulb ND 4.9-40W A60 E27 865	200 degree(s)	6500 K	80	865	470 lm

Operating and Electrical

Order	Input	Line	Power	Wattage	
Code	Full Product Name	Frequency	Frequency	Consumption	Equivalent
47520500	CoreProLEDbulb ND 13-100W A60 E27 927	50 Hz	50 Hz	13 W	100 W
32968300	CorePro LEDbulb ND 13-100W A60 E27 930	50 to 60 Hz	50 to 60 Hz	13 W	100 W
32970600	CorePro LEDbulb ND 12.5-100W A60 E27 940	50 to 60 Hz	50 to 60 Hz	12.5 W	100 W
57763900	CorePro LEDbulb ND 8-60W A60 B22 827	50 to 60 Hz	50 to 60 Hz	8 W	60 W
32978200	CorePro LEDbulb ND 13-100W A60 B22 930	50 to 60 Hz	50 to 60 Hz	13 W	100 W
32976800	CorePro LEDbulb ND 10.5-75W A60 B22 930	50 Hz	50 Hz	10.5 W	75 W
16901200	CorePro LEDbulb ND 13-100W A60 E27 827	50 to 60 Hz	50 to 60 Hz	13 W	100 W
05770900	LEDbulb ND 13-100W A60 E27 827 1CT	50 to 60 Hz	-	13 W	100 W
47105400	LEDbulb ND 13-100W A67 E27 827 2CT	50 to 60 Hz	50 to 60 Hz	13 W	100 W
16909800	CorePro LEDbulb ND 13-100W A60 E27 840	50 to 60 Hz	50 to 60 Hz	13 W	100 W
05772300	LEDbulb ND 13-100W A60 E27 840 1CT	50 to 60 Hz	-	13 W	100 W
47103000	LEDbulb ND 13-100W A67 E27 840 2CT	50 to 60 Hz	50 to 60 Hz	13 W	100 W
16925800	CorePro LEDbulb ND 13-100W A60 E27 865	50 to 60 Hz	50 to 60 Hz	13 W	100 W
16917300	CorePro LEDbulb ND 13-100W A60 E27 830	50 to 60 Hz	50 to 60 Hz	13 W	100 W
16899200	CorePro LEDbulb ND 10-75W A60 E27 827	50 to 60 Hz	50 to 60 Hz	10 W	75 W
05766200	LEDbulb ND 10-75W A60 E27 827 1CT	50 to 60 Hz	-	10 W	75 W

CorePro Plastic LEDbulbs

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
47111500	LEDbulb ND 10-75W A60 E27 827 2CT	50 to 60 Hz	50 to 60 Hz	10 W	75 W
16907400	CorePro LEDbulb ND 10-75W A60 E27 840	50 to 60 Hz	50 to 60 Hz	10 W	75 W
05768600	LEDbulb ND 10-75W A60 E27 840 1CT	50 to 60 Hz	-	10 W	75 W
47101600	LEDbulb ND 10-75W A60 E27 840 2CT	50 to 60 Hz	50 to 60 Hz	10 W	75 W
16923400	CorePro LEDbulb ND 10-75W A60 E27 865	50 to 60 Hz	50 to 60 Hz	10 W	75 W
47514400	CorePro LEDbulb ND 11-75W A60 E27 927	50 Hz	50 Hz	11 W	75 W
32964500	CorePro LEDbulb ND 10.5-75W A60 E27 930	50 Hz	50 Hz	10.5 W	75 W
32966900	CorePro LEDbulb ND 10-75W A60 E27 940	50 Hz	50 Hz	10 W	75 W
16915900	CorePro LEDbulb ND 10-75W A60 E27 830	50 to 60 Hz	50 to 60 Hz	10 W	75 W
32972000	CorePro LEDbulb ND 4.9-40W A60 B22 930	50 Hz	50 Hz	4.9 W	40 W
32974400	CorePro LEDbulb ND 7.5-60W A60 B22 930	50 Hz	50 Hz	7.5 W	60 W
57765300	CorePro LEDbulb ND 4.9-40W A60 B22 827	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
16897800	CorePro LEDbulb ND 8-60W A60 E27 827	50 to 60 Hz	50 to 60 Hz	8 W	60 W
47109200	LEDbulb ND 8-60W A60 E27 827 2CT	50 to 60 Hz	50 to 60 Hz	8 W	60 W
16905000	CorePro LEDbulb ND 8-60W A60 E27 840	50 to 60 Hz	50 to 60 Hz	8 W	60 W
32471800	LEDbulb ND 8-60W A60 E27 840 12CT	50 to 60 Hz	-	8 W	60 W
05764800	LEDbulb ND 8-60W A60 E27 840 1CT	50 to 60 Hz	-	8 W	60 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
47097200	LEDbulb ND 8-60W A60 E27 840 2CT	50 to 60 Hz	50 to 60 Hz	8 W	60 W
16921000	CorePro LEDbulb ND 8-60W A60 E27 865	50 to 60 Hz	50 to 60 Hz	8 W	60 W
47107800	LEDbulb ND 4.9-40W A60 E27 827 2CT	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
16895400	CorePro LEDbulb ND 4.9-40W A60 E27 827	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
05774700	LEDbulb ND 4.9-40W A60 E27 827 1CT	50 to 60 Hz	-	4.9 W	40 W
47518200	CorePro LEDbulb ND 4.9-40W A60 E27 927	50 Hz	50 Hz	4.9 W	40 W
32956000	CorePro LEDbulb ND 4.9-40W A60 E27 930	50 Hz	50 Hz	4.9 W	40 W
32958400	CorePro LEDbulb ND 4.9-40W A60 E27 940	50 Hz	50 Hz	4.9 W	40 W
47516800	CorePro LEDbulb ND 8-60W A60 E27 927	50 Hz	50 Hz	8 W	60 W
32960700	CorePro LEDbulb ND 7.5-60W A60 E27 930	50 Hz	50 Hz	7.5 W	60 W
32962100	CorePro LEDbulb ND 7.5-60W A60 E27 940	50 Hz	50 Hz	7.5 W	60 W
16911100	CorePro LEDbulb ND 4.9-40W A60 E27 830	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
47099600	LEDbulb ND 4.9-40W A60 E27 840 2CT	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
16903600	CorePro LEDbulb ND 4.9-40W A60 E27 840	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
05776100	LEDbulb ND 4.9-40W A60 E27 840 1CT	50 to 60 Hz	-	4.9 W	40 W
16919700	CorePro LEDbulb ND 4.9-40W A60 E27 865	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
16913500	CorePro LEDbulb ND 8-60W A60 E27 830	50 to 60 Hz	50 to 60 Hz	8 W	60 W

CorePro Plastic LEDbulbs

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
32469500	LEDbulb ND 8-60W A60 E27 830 12CT	50 to 60 Hz	-	8 W	60 W
32511100	LEDbulb ND 8-60W A60 E27 827 12CT	50 to 60 Hz	-	8 W	60 W
05762400	LEDbulb ND 8-60W A60 E27 827 1CT	50 to 60 Hz	-	8 W	60 W
57761500	CorePro LEDbulb ND 11-75W A60 B22 827	50 to 60 Hz	50 to 60 Hz	11 W	75 W
51002500	CorePro LEDbulb ND 13-100W A60 B22 827	50 to 60 Hz	50 to 60 Hz	13 W	100 W
35333600	CorePro LEDbulb DIM 8-60W A60 E27 5CCT	50 to 60 Hz	-	8 W	60 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
70033100	CorePro LEDbulbND 8-60W A60E27 827 3CT/8	50 to 60 Hz	50 to 60 Hz	8 W	60 W
57757800	CorePro LEDbulb ND 4.9-40W A60 E27 827	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
57779000	CorePro LEDbulb ND 4.9-40W A60 E27 840	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
57993000	CorePro LEDbulb ND 4.9-40W A60 E27 830	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
57787500	CorePro LEDbulb ND 4.9-40W A60 E27 865	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
47520500	CoreProLEDbulb ND 13-100W A60 E27 927	105 °C
32968300	CorePro LEDbulb ND 13-100W A60 E27 930	95 °C
32970600	CorePro LEDbulb ND 12.5-100W A60 E27 940	95 °C
57763900	CorePro LEDbulb ND 8-60W A60 B22 827	85 °C
32978200	CorePro LEDbulb ND 13-100W A60 B22 930	95 °C
32976800	CorePro LEDbulb ND 10.5-75W A60 B22 930	105 °C
16901200	CorePro LEDbulb ND 13-100W A60 E27 827	95 °C
05770900	LEDbulb ND 13-100W A60 E27 827 1CT	95 °C
47105400	LEDbulb ND 13-100W A67 E27 827 2CT	95 °C
16909800	CorePro LEDbulb ND 13-100W A60 E27 840	95 °C
05772300	LEDbulb ND 13-100W A60 E27 840 1CT	95 °C
47103000	LEDbulb ND 13-100W A67 E27 840 2CT	95 °C
16925800	CorePro LEDbulb ND 13-100W A60 E27 865	95 °C
16917300	CorePro LEDbulb ND 13-100W A60 E27 830	95 °C
16899200	CorePro LEDbulb ND 10-75W A60 E27 827	85 °C
05766200	LEDbulb ND 10-75W A60 E27 827 1CT	95 °C
47111500	LEDbulb ND 10-75W A60 E27 827 2CT	95 °C
16907400	CorePro LEDbulb ND 10-75W A60 E27 840	85 °C
05768600	LEDbulb ND 10-75W A60 E27 840 1CT	95 °C
47101600	LEDbulb ND 10-75W A60 E27 840 2CT	95 °C
16923400	CorePro LEDbulb ND 10-75W A60 E27 865	85 °C
47514400	CorePro LEDbulb ND 11-75W A60 E27 927	105 °C
32964500	CorePro LEDbulb ND 10.5-75W A60 E27 930	105 °C
32966900	CorePro LEDbulb ND 10-75W A60 E27 940	105 °C
16915900	CorePro LEDbulb ND 10-75W A60 E27 830	85 °C
32972000	CorePro LEDbulb ND 4.9-40W A60 B22 930	80 °C
32974400	CorePro LEDbulb ND 7.5-60W A60 B22 930	95 °C
57765300	CorePro LEDbulb ND 4.9-40W A60 B22 827	80 °C
16897800	CorePro LEDbulb ND 8-60W A60 E27 827	75 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
47109200	LEDbulb ND 8-60W A60 E27 827 2CT	95 °C
16905000	CorePro LEDbulb ND 8-60W A60 E27 840	75 °C
32471800	LEDbulb ND 8-60W A60 E27 840 12CT	90 °C
05764800	LEDbulb ND 8-60W A60 E27 840 1CT	95 °C
47097200	LEDbulb ND 8-60W A60 E27 840 2CT	95 °C
16921000	CorePro LEDbulb ND 8-60W A60 E27 865	75 °C
47107800	LEDbulb ND 4.9-40W A60 E27 827 2CT	75 °C
16895400	CorePro LEDbulb ND 4.9-40W A60 E27 827	75 °C
05774700	LEDbulb ND 4.9-40W A60 E27 827 1CT	75 °C
47518200	CoreProLEDbulb ND 4.9-40W A60 E27 927	80 °C
32956000	CorePro LEDbulb ND 4.9-40W A60 E27 930	80 °C
32958400	CorePro LEDbulb ND 4.9-40W A60 E27 940	80 °C
47516800	CorePro LEDbulb ND 8-60W A60 E27 927	95 °C
32960700	CorePro LEDbulb ND 7.5-60W A60 E27 930	95 °C
32962100	CorePro LEDbulb ND 7.5-60W A60 E27 940	95 °C
16911100	CorePro LEDbulb ND 4.9-40W A60 E27 830	75 °C
47099600	LEDbulb ND 4.9-40W A60 E27 840 2CT	-
16903600	CorePro LEDbulb ND 4.9-40W A60 E27 840	75 °C
05776100	LEDbulb ND 4.9-40W A60 E27 840 1CT	75 °C
16919700	CorePro LEDbulb ND 4.9-40W A60 E27 865	75 °C
16913500	CorePro LEDbulb ND 8-60W A60 E27 830	75 °C
32469500	LEDbulb ND 8-60W A60 E27 830 12CT	90 °C
32511100	LEDbulb ND 8-60W A60 E27 827 12CT	90 °C
05762400	LEDbulb ND 8-60W A60 E27 827 1CT	95 °C
57761500	CorePro LEDbulb ND 11-75W A60 B22 827	80 °C
51002500	CorePro LEDbulb ND 13-100W A60 B22 827	85 °C
35333600	CorePro LEDbulb DIM 8-60W A60 E27 5CCT	80 °C
70033100	CorePro LEDbulbND 8-60W A60E27 827 3CT/8	85 °C
57757800	CorePro LEDbulb ND 4.9-40W A60 E27 827	80 °C

CorePro Plastic LEDbulbs

Order Code	Full Product Name	T-Case Maximum (Nom)
57779000	CorePro LEDbulb ND 4.9-40W A60 E27 840	80 °C
57993000	CorePro LEDbulb ND 4.9-40W A60 E27 830	80 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
57787500	CorePro LEDbulb ND 4.9-40W A60 E27 865	80 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
47520500	CoreProLEDbulb ND 13-100W A60 E27 927	No
32968300	CorePro LEDbulb ND 13-100W A60 E27 930	No
32970600	CorePro LEDbulb ND 12.5-100W A60 E27 940	No
57763900	CorePro LEDbulb ND 8-60W A60 B22 827	No
32978200	CorePro LEDbulb ND 13-100W A60 B22 930	No
32976800	CorePro LEDbulb ND 10.5-75W A60 B22 930	No
16901200	CorePro LEDbulb ND 13-100W A60 E27 827	No
05770900	LEDbulb ND 13-100W A60 E27 827 1CT	No
47105400	LEDbulb ND 13-100W A67 E27 827 2CT	No
16909800	CorePro LEDbulb ND 13-100W A60 E27 840	No
05772300	LEDbulb ND 13-100W A60 E27 840 1CT	No
47103000	LEDbulb ND 13-100W A67 E27 840 2CT	No
16925800	CorePro LEDbulb ND 13-100W A60 E27 865	No
16917300	CorePro LEDbulb ND 13-100W A60 E27 830	No
16899200	CorePro LEDbulb ND 10-75W A60 E27 827	No
05766200	LEDbulb ND 10-75W A60 E27 827 1CT	No
47111500	LEDbulb ND 10-75W A60 E27 827 2CT	No
16907400	CorePro LEDbulb ND 10-75W A60 E27 840	No
05768600	LEDbulb ND 10-75W A60 E27 840 1CT	No
47101600	LEDbulb ND 10-75W A60 E27 840 2CT	No
16923400	CorePro LEDbulb ND 10-75W A60 E27 865	No
47514400	CorePro LEDbulb ND 11-75W A60 E27 927	No
32964500	CorePro LEDbulb ND 10.5-75W A60 E27 930	No
32966900	CorePro LEDbulb ND 10-75W A60 E27 940	No
16915900	CorePro LEDbulb ND 10-75W A60 E27 830	No
32972000	CorePro LEDbulb ND 4.9-40W A60 B22 930	No
32974400	CorePro LEDbulb ND 7.5-60W A60 B22 930	No
57765300	CorePro LEDbulb ND 4.9-40W A60 B22 827	No
16897800	CorePro LEDbulb ND 8-60W A60 E27 827	No
47109200	LEDbulb ND 8-60W A60 E27 827 2CT	No
16905000	CorePro LEDbulb ND 8-60W A60 E27 840	No

Order Code	Full Product Name	Dimmable
32471800	LEDbulb ND 8-60W A60 E27 840 12CT	No
05764800	LEDbulb ND 8-60W A60 E27 840 1CT	No
47097200	LEDbulb ND 8-60W A60 E27 840 2CT	No
16921000	CorePro LEDbulb ND 8-60W A60 E27 865	No
47107800	LEDbulb ND 4.9-40W A60 E27 827 2CT	No
16895400	CorePro LEDbulb ND 4.9-40W A60 E27 827	No
05774700	LEDbulb ND 4.9-40W A60 E27 827 1CT	No
47518200	CoreProLEDbulb ND 4.9-40W A60 E27 927	No
32956000	CorePro LEDbulb ND 4.9-40W A60 E27 930	No
32958400	CorePro LEDbulb ND 4.9-40W A60 E27 940	No
47516800	CorePro LEDbulb ND 8-60W A60 E27 927	No
32960700	CorePro LEDbulb ND 7.5-60W A60 E27 930	No
32962100	CorePro LEDbulb ND 7.5-60W A60 E27 940	No
16911100	CorePro LEDbulb ND 4.9-40W A60 E27 830	No
47099600	LEDbulb ND 4.9-40W A60 E27 840 2CT	No
16903600	CorePro LEDbulb ND 4.9-40W A60 E27 840	No
05776100	LEDbulb ND 4.9-40W A60 E27 840 1CT	No
16919700	CorePro LEDbulb ND 4.9-40W A60 E27 865	No
16913500	CorePro LEDbulb ND 8-60W A60 E27 830	No
32469500	LEDbulb ND 8-60W A60 E27 830 12CT	No
32511100	LEDbulb ND 8-60W A60 E27 827 12CT	No
05762400	LEDbulb ND 8-60W A60 E27 827 1CT	No
57761500	CorePro LEDbulb ND 11-75W A60 B22 827	No
51002500	CorePro LEDbulb ND 13-100W A60 B22 827	No
35333600	CorePro LEDbulb DIM 8-60W A60 E27 5CCT	Only with specific dimmers
70033100	CorePro LEDbulbND 8-60W A60E27 827 3CT/8	No
57757800	CorePro LEDbulb ND 4.9-40W A60 E27 827	No
57779000	CorePro LEDbulb ND 4.9-40W A60 E27 840	No
57993000	CorePro LEDbulb ND 4.9-40W A60 E27 830	No
57787500	CorePro LEDbulb ND 4.9-40W A60 E27 865	No

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
47520500	CoreProLEDbulb ND 13-100W A60 E27 927	A60
32968300	CorePro LEDbulb ND 13-100W A60 E27 930	A60
32970600	CorePro LEDbulb ND 12.5-100W A60 E27 940	A60
57763900	CorePro LEDbulb ND 8-60W A60 B22 827	A60
32978200	CorePro LEDbulb ND 13-100W A60 B22 930	A60
32976800	CorePro LEDbulb ND 10.5-75W A60 B22 930	A60
16901200	CorePro LEDbulb ND 13-100W A60 E27 827	A60
05770900	LEDbulb ND 13-100W A60 E27 827 1CT	A60
47105400	LEDbulb ND 13-100W A67 E27 827 2CT	A67
16909800	CorePro LEDbulb ND 13-100W A60 E27 840	A60

Order Code	Full Product Name	Bulb Shape
05772300	LEDbulb ND 13-100W A60 E27 840 1CT	A60
47103000	LEDbulb ND 13-100W A67 E27 840 2CT	A67
16925800	CorePro LEDbulb ND 13-100W A60 E27 865	A60
16917300	CorePro LEDbulb ND 13-100W A60 E27 830	A60
16899200	CorePro LEDbulb ND 10-75W A60 E27 827	A60
05766200	LEDbulb ND 10-75W A60 E27 827 1CT	A60
47111500	LEDbulb ND 10-75W A60 E27 827 2CT	A60
16907400	CorePro LEDbulb ND 10-75W A60 E27 840	A60
05768600	LEDbulb ND 10-75W A60 E27 840 1CT	A60
47101600	LEDbulb ND 10-75W A60 E27 840 2CT	A60

CorePro Plastic LEDbulbs

Order Code	Full Product Name	Bulb Shape
16923400	CorePro LEDbulb ND 10-75W A60 E27 865	A60
47514400	CorePro LEDbulb ND 11-75W A60 E27 927	A60
32964500	CorePro LEDbulb ND 10.5-75W A60 E27 930	A60
32966900	CorePro LEDbulb ND 10-75W A60 E27 940	A60
16915900	CorePro LEDbulb ND 10-75W A60 E27 830	A60
32972000	CorePro LEDbulb ND 4.9-40W A60 B22 930	A60
32974400	CorePro LEDbulb ND 7.5-60W A60 B22 930	A60
57765300	CorePro LEDbulb ND 4.9-40W A60 B22 827	A60
16897800	CorePro LEDbulb ND 8-60W A60 E27 827	A60
47109200	LEDbulb ND 8-60W A60 E27 827 2CT	A60
16905000	CorePro LEDbulb ND 8-60W A60 E27 840	A60
32471800	LEDbulb ND 8-60W A60 E27 840 12CT	A60
05764800	LEDbulb ND 8-60W A60 E27 840 1CT	A60
47097200	LEDbulb ND 8-60W A60 E27 840 2CT	A60
16921000	CorePro LEDbulb ND 8-60W A60 E27 865	A60
47107800	LEDbulb ND 4.9-40W A60 E27 827 2CT	A60
16895400	CorePro LEDbulb ND 4.9-40W A60 E27 827	A60
05774700	LEDbulb ND 4.9-40W A60 E27 827 1CT	A60
47518200	CoreProLEDbulb ND 4.9-40W A60 E27 927	A60
32956000	CorePro LEDbulb ND 4.9-40W A60 E27 930	A60
32958400	CorePro LEDbulb ND 4.9-40W A60 E27 940	A60

Order Code	Full Product Name	Bulb Shape
47516800	CorePro LEDbulb ND 8-60W A60 E27 927	A60
32960700	CorePro LEDbulb ND 7.5-60W A60 E27 930	A60
32962100	CorePro LEDbulb ND 7.5-60W A60 E27 940	A60
16911100	CorePro LEDbulb ND 4.9-40W A60 E27 830	A60
47099600	LEDbulb ND 4.9-40W A60 E27 840 2CT	A60
16903600	CorePro LEDbulb ND 4.9-40W A60 E27 840	A60
05776100	LEDbulb ND 4.9-40W A60 E27 840 1CT	A60
16919700	CorePro LEDbulb ND 4.9-40W A60 E27 865	A60
16913500	CorePro LEDbulb ND 8-60W A60 E27 830	A60
32469500	LEDbulb ND 8-60W A60 E27 830 12CT	A60
32511100	LEDbulb ND 8-60W A60 E27 827 12CT	A60
05762400	LEDbulb ND 8-60W A60 E27 827 1CT	A60
57761500	CorePro LEDbulb ND 11-75W A60 B22 827	A60
51002500	CorePro LEDbulb ND 13-100W A60 B22 827	A60
35333600	CorePro LEDbulb DIM 8-60W A60 E27 5CCT	A60
70033100	CorePro LEDbulbND 8-60W A60E27 827 3CT/8	A60
57757800	CorePro LEDbulb ND 4.9-40W A60 E27 827	A60
57779000	CorePro LEDbulb ND 4.9-40W A60 E27 840	A60
57993000	CorePro LEDbulb ND 4.9-40W A60 E27 830	A60
57787500	CorePro LEDbulb ND 4.9-40W A60 E27 865	A60

Approval and Application


Order Code	Full Product Name	Energy	
		Ambient temperature range	Consumption kWh/1000 h
47520500	CoreProLEDbulb ND 13-100W A60 E27 927	-20 °C to 45 °C	13 kWh
32968300	CorePro LEDbulb ND 13-100W A60 E27 930	-	13 kWh
32970600	CorePro LEDbulb ND 12.5-100W A60 E27 940	-	13 kWh
57763900	CorePro LEDbulb ND 8-60W A60 B22 827	-	8 kWh
32978200	CorePro LEDbulb ND 13-100W A60 B22 930	-	13 kWh
32976800	CorePro LEDbulb ND 10.5-75W A60 B22 930	-20 °C to 45 °C	11 kWh
16901200	CorePro LEDbulb ND 13-100W A60 E27 827	-20 °C to 45 °C	13 kWh
05770900	LEDbulb ND 13-100W A60 E27 827 1CT	-20 to +45 °C	13 kWh
47105400	LEDbulb ND 13-100W A67 E27 827 2CT	-20 °C to 45 °C	13 kWh
16909800	CorePro LEDbulb ND 13-100W A60 E27 840	-20 °C to 45 °C	13 kWh
05772300	LEDbulb ND 13-100W A60 E27 840 1CT	-20 to +45 °C	13 kWh
47103000	LEDbulb ND 13-100W A67 E27 840 2CT	-20 °C to 45 °C	13 kWh

Order Code	Full Product Name	Energy	
		Ambient temperature range	Consumption kWh/1000 h
16925800	CorePro LEDbulb ND 13-100W A60 E27 865	-20 °C to 45 °C	13 kWh
16917300	CorePro LEDbulb ND 13-100W A60 E27 830	-20 °C to 45 °C	13 kWh
16899200	CorePro LEDbulb ND 10-75W A60 E27 827	-20 °C to 45 °C	10 kWh
05766200	LEDbulb ND 10-75W A60 E27 827 1CT	-20 to +45 °C	10 kWh
47111500	LEDbulb ND 10-75W A60 E27 827 2CT	-20 °C to 45 °C	10 kWh
16907400	CorePro LEDbulb ND 10-75W A60 E27 840	-20 °C to 45 °C	10 kWh
05768600	LEDbulb ND 10-75W A60 E27 840 1CT	-20 to +45 °C	10 kWh
47101600	LEDbulb ND 10-75W A60 E27 840 2CT	-20 °C to 45 °C	10 kWh
16923400	CorePro LEDbulb ND 10-75W A60 E27 865	-20 °C to 45 °C	10 kWh
47514400	CorePro LEDbulb ND 11-75W A60 E27 927	-20 °C to 45 °C	11 kWh
32964500	CorePro LEDbulb ND 10.5-75W A60 E27 930	-20 °C to 45 °C	11 kWh
32966900	CorePro LEDbulb ND 10-75W A60 E27 940	-20 °C to 45 °C	10 kWh











CorePro Plastic LEDbulbs

Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
16915900	CorePro LEDbulb ND 10-75W A60 E27 830	-20 °C to 45 °C	10 kWh
32972000	CorePro LEDbulb ND 4.9-40W A60 B22 930	-20 °C to 45 °C	5 kWh
32974400	CorePro LEDbulb ND 7.5-60W A60 B22 930	-20 °C to 45 °C	8 kWh
57765300	CorePro LEDbulb ND 4.9-40W A60 B22 827	-20 °C to 45 °C	5 kWh
16897800	CorePro LEDbulb ND 8-60W A60 E27 827	-20 °C to 45 °C	8 kWh
47109200	LEDbulb ND 8-60W A60 E27 827 2CT	-20 °C to 45 °C	8 kWh
16905000	CorePro LEDbulb ND 8-60W A60 E27 840	-20 °C to 45 °C	8 kWh
32471800	LEDbulb ND 8-60W A60 E27 840 12CT	-20 to +45 °C	8 kWh
05764800	LEDbulb ND 8-60W A60 E27 840 1CT	-20 to +45 °C	8 kWh
47097200	LEDbulb ND 8-60W A60 E27 840 2CT	-20 °C to 45 °C	8 kWh
16921000	CorePro LEDbulb ND 8-60W A60 E27 865	-20 °C to 45 °C	8 kWh
47107800	LEDbulb ND 4.9-40W A60 E27 827 2CT	-20 °C to 45 °C	5 kWh
16895400	CorePro LEDbulb ND 4.9-40W A60 E27 827	-20 °C to 45 °C	5 kWh
05774700	LEDbulb ND 4.9-40W A60 E27 827 1CT	-20 to +45 °C	5 kWh
47518200	CorePro LEDbulb ND 4.9-40W A60 E27 927	-20 °C to 45 °C	5 kWh
32956000	CorePro LEDbulb ND 4.9-40W A60 E27 930	-20 °C to 45 °C	5 kWh
32958400	CorePro LEDbulb ND 4.9-40W A60 E27 940	-20 °C to 45 °C	5 kWh
47516800	CorePro LEDbulb ND 8-60W A60 E27 927	-20 °C to 45 °C	8 kWh
32960700	CorePro LEDbulb ND 7.5-60W A60 E27 930	-20 °C to 45 °C	8 kWh
32962100	CorePro LEDbulb ND 7.5-60W A60 E27 940	-20 °C to 45 °C	8 kWh
16911100	CorePro LEDbulb ND 4.9-40W A60 E27 830	-20 °C to 45 °C	5 kWh
47099600	LEDbulb ND 4.9-40W A60 E27 840 2CT	-20 °C to 45 °C	5 kWh
16903600	CorePro LEDbulb ND 4.9-40W A60 E27 840	-20 °C to 45 °C	5 kWh
05776100	LEDbulb ND 4.9-40W A60 E27 840 1CT	-20 to +45 °C	5 kWh
16919700	CorePro LEDbulb ND 4.9-40W A60 E27 865	-20 °C to 45 °C	5 kWh











Order Code	Full Product Name	Ambient temperature range	Energy Consumption kWh/1000 h
16913500	CorePro LEDbulb ND 8-60W A60 E27 830	-20 °C to 45 °C	8 kWh
32469500	LEDbulb ND 8-60W A60 E27 830 12CT	-20 to +45 °C	8 kWh
32511100	LEDbulb ND 8-60W A60 E27 827 12CT	-20 to +45 °C	8 kWh
05762400	LEDbulb ND 8-60W A60 E27 827 1CT	-20 to +45 °C	8 kWh
57761500	CorePro LEDbulb ND 11-75W A60 B22 827	-	11 kWh
51002500	CorePro LEDbulb ND 13-100W A60 B22 827	-	13 kWh
35333600	CorePro LEDbulb DIM 8-60W A60 E27 5CCT	-20 to +45 °C	8 kWh
70033100	CorePro LEDbulb ND 8-60W A60 E27 827 3CT/8	-	8 kWh
57757800	CorePro LEDbulb ND 4.9-40W A60 E27 827	-20 °C to 45 °C	5 kWh
57779000	CorePro LEDbulb ND 4.9-40W A60 E27 840	-20 °C to 45 °C	5 kWh
57993000	CorePro LEDbulb ND 4.9-40W A60 E27 830	-20 °C to 45 °C	5 kWh
57787500	CorePro LEDbulb ND 4.9-40W A60 E27 865	-20 °C to 45 °C	5 kWh













CorePro Plastic LEDbulbs



CorePro Plastic LEDbulbs



CorePro Plastic LEDbulbs



CorePro Plastic LEDbulbs

