



Guaranteed performance, thinking ahead

Maxos fusion

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

Benefits

- Freedom of (re-)positioning enables you to direct the light where needed
- Family of fixtures to create the desired atmosphere; wide variety of beam shapes to suit diversity of applications
- With up to 13-wire track, emergency lighting and third-party hardware can be integrated to declutter ceilings

Features

- Track system inside the trunk with up to 13 wires
- High uniformity and artefact-free light distributions
- Linear fixtures, non-linear fixtures and spots can be easily installed onto the trunk
- Eight optics, including (double) asymmetric distributions and a frosted cover
- IP54 optional, silicone-free
- StoreWise, Indoor Positioning and GreenWarehouse-ready

Maxos fusion

Application


- (Food) retail
- Industrial halls/areas
- Warehouses/distribution centers

Versions




Maxos Fusion Panel-LL512X WB BK

Dimensional drawing



Dimensional drawing



General Information

Driver included	Yes
Number of gear units	1 unit

Light Technical

Beam angle of light source	120 degree(s)
----------------------------	---------------

Operating and Electrical

Protection class IEC	Safety class I
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable

Controls and Dimming

Dimmable	Yes
----------	-----

Approval and Application

Ambient temperature range	-20 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 30 s

Initial Performance (IEC Compliant)

Initial chromaticity	(0.34, 0.35) SDCM <3
Luminous flux tolerance	+/-7%

General Information

Order Code	Full Product Name	Light source replaceable	Service tag
910925870051	LL512X LED61S/840 PSD O-PC 7 VLC WH XA	-	-
910925870052	LL523X LED123S/840 PSD O-PC 7 VLC WH XA	-	-
910925870055	LL523X LED123S/840 SIA O-PC 7 WH HE	-	-
910925870056	LL523X LED100S/840 SIA O-PC 7 WH HE	-	-
910925870057	LL523X LED62S/840 SIA O-PC 7 WH HE	-	-
910925870058	LL512X LED61S/840 SIA O-PC 7 WH HE	-	-
910925870059	LL512X LED31S/840 SIA O-PC 7 WH HE	-	-
910925870061	LL523X LED62S/840 DIA O-PC 7 WH HE	-	-
910925870062	LL523X LED62S/840 DIA O-PC 13 ELP3 WH HE	-	-
910925870063	LL523X LED100S/840 DIA O-PC 7 WH HE	-	-
910925870064	LL523X LED123S/840 DIA O-PC 7 WH HE	-	-
910925870065	LL512X LED31S/840 DIA O-PC 7 WH HE	-	-
910925870066	LL512X LED50S/840 DIA O-PC 7 WH HE	-	-
910925870067	LL512X LED61S/840 DIA O-PC 7 WH HE	-	-
910925868124	LL512X LED31S/840 PSED WB-OC 13 BK XA	No	Yes
910925868128	LL523X LED62S/840 PSED WB-OC 13 BK XA	No	Yes
910925868123	LL512X LED31S/840 PSED WB-OC 13 WH XA	No	Yes
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	No	Yes
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	No	Yes
910925868959		No	Yes
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	No	Yes
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	No	Yes
910925868962	LL512X LED61S/840 PSD NB 7 WH HE	No	Yes
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	No	Yes
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	No	Yes

Order Code	Full Product Name	Light source replaceable	Service tag
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	No	Yes
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	No	Yes
910925868978	LL512X LED50S/840 SIA MB 7 WH HE	No	Yes
910925868979	LL512X LED50S/840 SIA WB 7 WH HE	No	Yes
910925868980	LL512X LED61S/840 SIA NB 7 WH HE	No	Yes
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	No	Yes
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	No	Yes
910925868983	LL512X LED80S/840 SIA NB 7 WH HE	No	Yes
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	No	Yes
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	No	Yes
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	No	Yes
910925870773	LL512X LED31S/830 DIA WB 7 WH HE	-	Yes
910925870775	LL512X LED31S/840 DEIA WB-OC 13 WH HE	-	Yes
910925870777	LL512X LED50S/840 DIA DA35W 7 WH HE	-	Yes
910925870779	LL512X LED80S/840 DIA WB 7 WH HE	-	Yes
910925870801	LL512X LED50S/840 PSD WB 7 BK HE	-	Yes
910925870804	LL512X LED50S/840 PSED WB 7 WH HE	-	Yes
910925870806	LL512X LED31S/840 PSD DA35W 7 WH HE	-	Yes
910925870807	LL512X LED31S/840 PSD WB 7 BK HE	-	Yes
910925870808	LL512X LED61S/840 PSD WB 7 BK HE	-	Yes
910925867810	LL523X LED123S/830 PSD WB 7 WH XA	No	Yes
910925867811	LL523X LED160S/830 PSD MB 7 WH XA	No	Yes
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	No	Yes
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	No	Yes
910925867814	LL523X LED160S/830 PSD WB 7 WH XA	No	Yes
910925867815	LL523X LED160S/830 PSD NB 7 WH XA	No	Yes
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	No	Yes
910925867818	LL523X LED123S/840 PSD MB 7 VLC WH XA	No	Yes
910925867819	LL523X LED123S/840 PSD WB 7 VLC WH XA	No	Yes
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	No	Yes
910925867825	LL523X LED123S/840 PSED NB 13 VLC WH XA	No	Yes
910925867826	LL523X LED123S/840 PSED MB 13 VLC WH XA	No	Yes
910925867827	LL523X LED123S/840 PSED WB 13 VLC WH XA	No	Yes
910925867828	LL523X LED160S/840 PSED NB 13 WH XA	No	Yes
910925867837	LL523X LED123S/840 PSD MB 7 VLC WH XA	No	Yes
910925867838	LL523X LED123S/840 PSD WB 7 VLC WH XA	No	Yes
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	No	Yes
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	No	Yes
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	No	Yes
910925868127	LL523X LED62S/840 PSED WB-OC 13 WH XA	No	Yes
910925868130	LL523X LED62S/840 PSD WB-OC 13 ELP3 WH X	No	Yes
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	No	Yes
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	No	Yes
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	No	Yes
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	No	Yes
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	No	Yes
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	No	Yes
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	No	Yes
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	No	Yes
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	No	Yes
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	No	Yes
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	No	Yes

Order Code	Full Product Name	Light source replaceable	Service tag
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	No	Yes
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	No	Yes
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	No	Yes
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	No	Yes
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	No	Yes
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	No	Yes
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	No	Yes
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	No	Yes
910925870371	LL523X LED62S/840 DIA MB 7 WH HE	-	Yes
910925870372	LL523X LED62S/840 DIA WB 7 WH HE	-	Yes
910925870373	LL523X LED100S/840 DIA MB 7 WH HE	-	Yes
910925870374	LL523X LED123S/840 DIA MB 7 WH HE	-	Yes
910925870375	LL523X LED100S/840 DIA WB 7 WH HE	-	Yes
910925870376	LL523X LED123S/840 DIA NB 7 WH HE	-	Yes
910925870377	LL523X LED123S/840 DIA WB 7 WH HE	-	Yes
910925870378	LL523X LED160S/840 DIA NB 7 WH HE	-	Yes
910925870379	LL523X LED160S/840 DIA MB 7 WH HE	-	Yes
910925870380	LL512X LED31S/840 DIA MB 7 WH HE	-	Yes
910925870381	LL512X LED31S/840 DIA WB 7 WH HE	-	Yes
910925870382	LL512X LED50S/840 DIA MB 7 WH HE	-	Yes
910925870383		-	Yes
910925870384	LL512X LED61S/840 DIA NB 7 WH HE	-	Yes
910925870385	LL512X LED61S/840 DIA MB 7 WH HE	-	Yes
910925870386	LL512X LED61S/840 DIA WB 7 WH HE	-	Yes
910925870387	LL512X LED80S/840 DIA NB 7 WH HE	-	Yes
910925870388	LL512X LED80S/840 DIA MB 7 WH HE	-	Yes
910925870756	LL523X LED62S/840 DEIA WB-OC 13 WH HE	-	Yes
910925870758	LL523X LED62S/840 DIA DA25N 7 WH HE	-	Yes
910925870759	LL523X LED62S/840 DIA DA25W 7 WH HE	-	Yes
910925870760	LL523X LED62S/840 DIA DA35W 7 WH HE	-	Yes
910925870761	LL523X LED100S/840 DIA NB 7 WH HE	-	Yes
910925870763	LL523X LED100S/840 DIA A20 7 WH HE	-	Yes
910925870764	LL523X LED100S/840 DIA DA35W 7 WH HE	-	Yes
910925870766	LL523X LED123S/840 DIA A20 7 WH HE	-	Yes
910925870767	LL523X LED123S/840 DIA DA25W 7 WH HE	-	Yes
910925870768	LL523X LED123S/840 DIA DA35W 7 WH HE	-	Yes
910925870769	LL523X LED160S/840 DIA WB 7 WH HE	-	Yes
910925870796	LL523X LED123S/840 PSD A20 7 WH HE	-	Yes
910925870797	LL523X LED160S/840 PSD XNB 7 WH HE	-	Yes
910925870798	LL523X LED100S/840 PSD WB 7 SI HE	-	Yes
910925870799	LL523X LED123S/840 PSD WB 7 BK HE	-	Yes
910925870802	LL523X LED62S/840 PSD WB 7 SI HE	-	Yes
910925870809	LL523X LED100S/840 PSD DA35W 7 WH HE	-	Yes
910925870810	LL523X LED100S/840 PSD WB 7 BK HE	-	Yes
910925870811	LL523X LED123S/840 PSD DA35W 7 WH HE	-	Yes
910925870812	LL523X LED62S/840 PSD DA35W 7 WH HE	-	Yes
910925870819	LL523X LED123S/840 DIA WB 13 ELP3 WH HE	-	-
910925870780	LL612X LED61S/840 DIA WB 7 WH HE	-	Yes
910925870794	LL612X LED61S/840 DIA MB 7 WH HE	-	Yes
910925870795	LL612X LED61S/840 DIA NB 7 WH HE	-	Yes
910925870803	LL612X LED61S/840 PSD NB 7 WH HE	-	Yes
910925870770	LL623X LED123S/840 DIA MB 7 WH HE	-	Yes

Order Code	Full Product Name	Light source replaceable	Service tag
910925870771	LL623X LED123S/840 DIA WB 7 WH HE	-	Yes
910925870772	LL623X LED123S/840 DIA NB 7 WH HE	-	Yes
910925870805	LL623X LED123S/840 PSD WB 7 WH HE	-	Yes
910925868648	LL515X 61S/840 PSD WB 7 HE WH	No	-
910925868649	LL515X 80S/840 PSD WB 7 HE WH	No	-
910925868650	LL515X 61S/840 PSD MB 7 HE WH	No	-
910925868651	LL515X 80S/840 PSD MB 7 HE WH	No	-
910925868652	LL515X 61S/840 PSD NB 7 HE WH	No	-
910925868653	LL515X 80S/840 PSD NB 7 HE WH	No	-

Light Technical (1/2)

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925870051	LL512X LED61S/840 PSD O-PC 7 VLC WH XA	4000 K	>80	151 lm/W	5,200 lm
910925870052	LL523X LED123S/840 PSD O-PC 7 VLC WH XA	4000 K	>80	158 lm/W	10,400 lm
910925870055	LL523X LED123S/840 SIA O-PC 7 WH HE	4000 K	>80	146 lm/W	10,400 lm
910925870056	LL523X LED100S/840 SIA O-PC 7 WH HE	4000 K	>80	144 lm/W	8,500 lm
910925870057	LL523X LED62S/840 SIA O-PC 7 WH HE	4000 K	>80	154 lm/W	5,300 lm
910925870058	LL512X LED61S/840 SIA O-PC 7 WH HE	4000 K	>80	141 lm/W	5,200 lm
910925870059	LL512X LED31S/840 SIA O-PC 7 WH HE	4000 K	>80	143 lm/W	2,650 lm
910925870061	LL523X LED62S/840 DIA O-PC 7 WH HE	4000 K	>80	147 lm/W	5,300 lm
910925870062	LL523X LED62S/840 DIA O-PC 13 ELP3 WH HE	4000 K	>80	147 lm/W	5,300 lm
910925870063	LL523X LED100S/840	4000 K	>80	144 lm/W	8,500 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	DIA O-PC 7 WH HE				
910925870064	LL523X LED123S/840 DIA O-PC 7 WH HE	4000 K	>80	149 lm/W	10,400 lm
910925870065	LL512X LED31S/840 DIA O-PC 7 WH HE	4000 K	>80	143 lm/W	2,650 lm
910925870066	LL512X LED50S/840 DIA O-PC 7 WH HE	4000 K	>80	142 lm/W	4,250 lm
910925870067	LL512X LED61S/840 DIA O-PC 7 WH HE	4000 K	>80	141 lm/W	5,200 lm
910925868124	LL512X LED31S/840 PSED WB-OC 13 BK XA	4000 K	>80	175 lm/W	3,150 lm
910925868128	LL523X LED62S/840 PSED WB-OC 13 BK XA	4000 K	>80	185 lm/W	6,200 lm
910925868123	LL512X LED31S/840 PSED WB-OC 13 WH XA	4000 K	>80	175 lm/W	3,150 lm
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	4000 K	>80	175 lm/W	3,100 lm
910925868958	LL512X LED31S/840	4000 K	>80	175 lm/W	3,150 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925868959	PSD MB 7 WH HE	4000 K	>80	175 lm/W	3,150 lm
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	4000 K	>80	172 lm/W	5,000 lm
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	4000 K	>80	172 lm/W	5,000 lm
910925868962	LL512X LED61S/840 PSD NB 7 WH HE	4000 K	>80	165 lm/W	6,100 lm
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	4000 K	>80	165 lm/W	6,100 lm
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	4000 K	>80	165 lm/W	6,100 lm
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	4000 K	>80	160 lm/W	8,000 lm
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	4000 K	>80	160 lm/W	8,000 lm
910925868978	LL512X LED50S/840 SIA MB 7 WH HE	4000 K	>80	172 lm/W	5,000 lm
910925868979	LL512X LED50S/840 SIA WB 7 WH HE	4000 K	>80	172 lm/W	5,000 lm
910925868980	LL512X LED61S/840 SIA NB 7 WH HE	4000 K	>80	165 lm/W	6,100 lm
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	4000 K	>80	165 lm/W	6,100 lm
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	4000 K	>80	165 lm/W	6,100 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925868983	LL512X LED80S/840 SIA NB 7 WH HE	4000 K	>80	160 lm/W	8,000 lm
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	4000 K	>80	160 lm/W	8,000 lm
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	4000 K	>80	175 lm/W	3,150 lm
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	4000 K	>80	160 lm/W	8,000 lm
910925870773	LL512X LED31S/830 DIA WB 7 WH HE	3000 K	80	175 lm/W	3,100 lm
910925870775	LL512X LED31S/840 DEIA WB-OC 13 WH HE	4000 K	80	175 lm/W	3,100 lm
910925870777	LL512X LED50S/840 DIA DA35W 7 WH HE	4000 K	80	172 lm/W	5,000 lm
910925870779	LL512X LED80S/840 DIA WB 7 WH HE	4000 K	80	160 lm/W	8,000 lm
910925870801	LL512X LED50S/840 PSD WB 7 BK HE	4000 K	80	172 lm/W	5,000 lm
910925870804	LL512X LED50S/840 PSED WB 7 WH HE	4000 K	80	172 lm/W	5,000 lm
910925870806	LL512X LED31S/840 PSD DA35W 7 WH HE	4000 K	80	175 lm/W	3,100 lm
910925870807	LL512X LED31S/840 PSD WB 7 BK HE	4000 K	80	175 lm/W	3,100 lm
910925870808	LL512X LED61S/840 PSD WB 7 BK HE	4000 K	80	165 lm/W	6,100 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925867810	LL523X LED123S/830 PSD WB 7 WH XA	3000 K	>80	172 lm/W	12,300 lm
910925867811	LL523X LED160S/830 PSD MB 7 WH XA	3000 K	>80	167 lm/W	16,000 lm
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	3000 K	>80	172 lm/W	12,300 lm
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	4000 K	>80	181 lm/W	12,300 lm
910925867814	LL523X LED160S/830 PSD WB 7 WH XA	3000 K	>80	167 lm/W	16,000 lm
910925867815	LL523X LED160S/830 PSD NB 7 WH XA	3000 K	>80	167 lm/W	16,000 lm
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	4000 K	>80	181 lm/W	12,300 lm
910925867818	LL523X LED123S/840 PSD MB 7 VLC WH XA	4000 K	>80	181 lm/W	12,300 lm
910925867819	LL523X LED123S/840 PSD WB 7 VLC WH XA	4000 K	>80	180.9 lm/W	12,300 lm
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	4000 K	>80	176 lm/W	16,000 lm
910925867825	LL523X LED123S/840 PSED NB 13 VLC WH XA	4000 K	>80	180.9 lm/W	12,300 lm
910925867826	LL523X LED123S/840 PSED MB 13 VLC WH XA	4000 K	>80	180.9 lm/W	12,300 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925867827	LL523X LED123S/840 PSED WB 13 VLC WH XA	4000 K	>80	180.9 lm/W	12,300 lm
910925867828	LL523X LED160S/840 PSED NB 13 WH XA	4000 K	>80	175.8 lm/W	16,000 lm
910925867837	LL523X LED123S/840 PSD MB 7 VLC WH XA	4000 K	>80	181 lm/W	12,300 lm
910925867838	LL523X LED123S/840 PSD WB 7 VLC WH XA	4000 K	>80	181 lm/W	12,300 lm
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	4000 K	>80	176 lm/W	16,000 lm
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	4000 K	>80	181 lm/W	12,300 lm
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	4000 K	>80	176 lm/W	16,000 lm
910925868127	LL523X LED62S/840 PSED WB-OC 13 WH XA	4000 K	>80	185 lm/W	6,200 lm
910925868130	LL523X LED62S/840 PSD WB-OC 13 ELP3 WH X	4000 K	>80	185 lm/W	6,200 lm
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	4000 K	>80	185 lm/W	6,200 lm
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	4000 K	>80	180 lm/W	6,200 lm
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	4000 K	>80	180 lm/W	6,200 lm

Maxos fusion

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	4000 K	>80	177 lm/W	10,100 lm
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	4000 K	>80	177 lm/W	10,100 lm
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	4000 K	>80	171 lm/W	12,300 lm
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	4000 K	>80	171 lm/W	12,300 lm
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	4000 K	>80	171 lm/W	12,300 lm
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	4000 K	>80	165 lm/W	16,000 lm
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	4000 K	>80	165 lm/W	16,000 lm
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	4000 K	>80	177 lm/W	10,100 lm
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	4000 K	>80	177 lm/W	10,100 lm
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	4000 K	>80	171 lm/W	12,300 lm
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	4000 K	>80	171 lm/W	12,300 lm
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	4000 K	>80	171 lm/W	12,300 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	4000 K	>80	165 lm/W	16,000 lm
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	4000 K	>80	165 lm/W	16,000 lm
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	4000 K	>80	180 lm/W	6,200 lm
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	4000 K	>80	165 lm/W	16,000 lm
910925870371	LL523X LED62S/840 DIA MB 7 WH HE	4000 K	>80	180 lm/W	6,200 lm
910925870372	LL523X LED62S/840 DIA WB 7 WH HE	4000 K	>80	180 lm/W	6,200 lm
910925870373	LL523X LED100S/840 DIA MB 7 WH HE	4000 K	>80	177 lm/W	10,100 lm
910925870374	LL523X LED123S/840 DIA MB 7 WH HE	4000 K	>80	171 lm/W	12,300 lm
910925870375	LL523X LED100S/840 DIA WB 7 WH HE	4000 K	>80	177 lm/W	10,100 lm
910925870376	LL523X LED123S/840 DIA NB 7 WH HE	4000 K	>80	171 lm/W	12,300 lm
910925870377	LL523X LED123S/840 DIA WB 7 WH HE	4000 K	>80	171 lm/W	12,300 lm
910925870378	LL523X LED160S/840 DIA NB 7 WH HE	4000 K	>80	165 lm/W	16,000 lm
910925870379	LL523X LED160S/840 DIA MB 7 WH HE	4000 K	>80	165 lm/W	16,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925870380	LL512X LED31S/840 DIA MB 7 WH HE	4000 K	>80	175 lm/W	3,150 lm
910925870381	LL512X LED31S/840 DIA WB 7 WH HE	4000 K	>80	175 lm/W	3,150 lm
910925870382	LL512X LED50S/840 DIA MB 7 WH HE	4000 K	>80	172 lm/W	5,000 lm
910925870383		4000 K	>80	172 lm/W	5,000 lm
910925870384	LL512X LED61S/840 DIA NB 7 WH HE	4000 K	>80	165 lm/W	6,100 lm
910925870385	LL512X LED61S/840 DIA MB 7 WH HE	4000 K	>80	165 lm/W	6,100 lm
910925870386	LL512X LED61S/840 DIA WB 7 WH HE	4000 K	>80	165 lm/W	6,100 lm
910925870387	LL512X LED80S/840 DIA NB 7 WH HE	4000 K	>80	160 lm/W	8,000 lm
910925870388	LL512X LED80S/840 DIA MB 7 WH HE	4000 K	>80	160 lm/W	8,000 lm
910925870756	LL523X LED62S/840 DEIA WB-OC 13 WH HE	4000 K	80	180 lm/W	6,200 lm
910925870758	LL523X LED62S/840 DIA DA25N 7 WH HE	4000 K	80	180 lm/W	6,200 lm
910925870759	LL523X LED62S/840 DIA DA25W 7 WH HE	4000 K	80	180 lm/W	6,200 lm
910925870760	LL523X LED62S/840 DIA DA35W 7 WH HE	4000 K	80	180 lm/W	6,200 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925870761	LL523X LED100S/840 DIA NB 7 WH HE	4000 K	80	177 lm/W	10,000 lm
910925870763	LL523X LED100S/840 DIA A20 7 WH HE	4000 K	80	177 lm/W	10,000 lm
910925870764	LL523X LED100S/840 DIA DA35W 7 WH HE	4000 K	80	177 lm/W	10,000 lm
910925870766	LL523X LED123S/840 DIA A20 7 WH HE	4000 K	80	171 lm/W	12,300 lm
910925870767	LL523X LED123S/840 DIA DA25W 7 WH HE	4000 K	80	171 lm/W	12,300 lm
910925870768	LL523X LED123S/840 DIA DA35W 7 WH HE	4000 K	80	171 lm/W	12,300 lm
910925870769	LL523X LED160S/840 DIA WB 7 WH HE	4000 K	80	165 lm/W	16,000 lm
910925870796	LL523X LED123S/840 PSD A20 7 WH HE	4000 K	80	171 lm/W	12,300 lm
910925870797	LL523X LED160S/840 PSD XNB 7 WH HE	4000 K	80	165 lm/W	16,000 lm
910925870798	LL523X LED100S/840 PSD WB 7 SI HE	4000 K	80	177 lm/W	10,000 lm
910925870799	LL523X LED123S/840 PSD WB 7 BK HE	4000 K	80	171 lm/W	12,300 lm
910925870802	LL523X LED62S/840 PSD WB 7 SI HE	4000 K	80	180 lm/W	6,200 lm
910925870809	LL523X LED100S/840 PSD DA35W 7 WH HE	4000 K	80	177 lm/W	10,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925870810	LL523X LED100S/840 PSD WB 7 BK HE	4000 K	80	177 lm/W	10,000 lm
910925870811	LL523X LED123S/840 PSD DA35W 7 WH HE	4000 K	80	171 lm/W	12,300 lm
910925870812	LL523X LED62S/840 PSD DA35W 7 WH HE	4000 K	80	180 lm/W	6,200 lm
910925870819	LL523X LED123S/840 DIA WB 13 ELP3 WH HE	4000 K	>80	162 lm/W	12,300 lm
910925870780	LL612X LED61S/840 DIA WB 7 WH HE	4000 K	80	165 lm/W	6,100 lm
910925870794	LL612X LED61S/840 DIA MB 7 WH HE	4000 K	80	165 lm/W	6,100 lm
910925870795	LL612X LED61S/840 DIA NB 7 WH HE	4000 K	80	165 lm/W	6,100 lm
910925870803	LL612X LED61S/840 PSD NB 7 WH HE	4000 K	80	165 lm/W	6,100 lm
910925870770	LL623X LED123S/840	4000 K	80	171 lm/W	12,300 lm

Light Technical (2/2)

Order Code	Full Product Name	Optic type
910925870051	LL512X LED61S/840 PSD O-PC 7 VLC WH XA	Opal
910925870052	LL523X LED123S/840 PSD O-PC 7 VLC WH XA	Opal
910925870055	LL523X LED123S/840 SIA O-PC 7 WH HE	Opal
910925870056	LL523X LED100S/840 SIA O-PC 7 WH HE	Opal
910925870057	LL523X LED62S/840 SIA O-PC 7 WH HE	Opal
910925870058	LL512X LED61S/840 SIA O-PC 7 WH HE	Opal
910925870059	LL512X LED31S/840 SIA O-PC 7 WH HE	Opal
910925870061	LL523X LED62S/840 DIA O-PC 7 WH HE	Opal
910925870062	LL523X LED62S/840 DIA O-PC 13 ELP3 WH HE	Opal
910925870063	LL523X LED100S/840 DIA O-PC 7 WH HE	Opal
910925870064	LL523X LED123S/840 DIA O-PC 7 WH HE	Opal
910925870065	LL512X LED31S/840 DIA O-PC 7 WH HE	Opal

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	DIA MB 7 WH HE				
910925870771	LL623X LED123S/840 DIA WB 7 WH HE	4000 K	80	171 lm/W	12,300 lm
910925870772	LL623X LED123S/840 DIA NB 7 WH HE	4000 K	80	171 lm/W	12,300 lm
910925870805	LL623X LED123S/840 PSD WB 7 WH HE	4000 K	80	171 lm/W	12,300 lm
910925868648	LL515X 61S/840 PSD WB 7 HE WH	4000 K	>80	165 lm/W	6,100 lm
910925868649	LL515X 80S/840 PSD WB 7 HE WH	4000 K	>80	160 lm/W	8,000 lm
910925868650	LL515X 61S/840 PSD MB 7 HE WH	4000 K	>80	165 lm/W	6,100 lm
910925868651	LL515X 80S/840 PSD MB 7 HE WH	4000 K	>80	160 lm/W	8,000 lm
910925868652	LL515X 61S/840 PSD NB 7 HE WH	4000 K	>80	165 lm/W	6,100 lm
910925868653	LL515X 80S/840 PSD NB 7 HE WH	4000 K	>80	160 lm/W	8,000 lm

Order Code	Full Product Name	Optic type
910925870066	LL512X LED50S/840 DIA O-PC 7 WH HE	Opal
910925870067	LL512X LED61S/840 DIA O-PC 7 WH HE	Opal
910925868124	LL512X LED31S/840 PSED WB-OC 13 BK XA	Wide beam
910925868128	LL523X LED62S/840 PSED WB-OC 13 BK XA	Wide beam
910925868123	LL512X LED31S/840 PSED WB-OC 13 WH XA	Wide beam
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	Wide beam
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	Medium beam
910925868959		Wide beam
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	Medium beam
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	Wide beam
910925868962	LL512X LED61S/840 PSD NB 7 WH HE	Narrow beam
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	Medium beam

Order Code	Full Product Name	Optic type
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	Wide beam
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	Narrow beam
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	Medium beam
910925868978	LL512X LED50S/840 SIA MB 7 WH HE	Medium beam
910925868979	LL512X LED50S/840 SIA WB 7 WH HE	Wide beam
910925868980	LL512X LED61S/840 SIA NB 7 WH HE	Narrow beam
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	Medium beam
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	Wide beam
910925868983	LL512X LED80S/840 SIA NB 7 WH HE	Narrow beam
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	Medium beam
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	Wide beam
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	Wide beam
910925870773	LL512X LED31S/830 DIA WB 7 WH HE	Wide beam
910925870775	LL512X LED31S/840 DEIA WB-OC 13 WH HE	Wide beam
910925870777	LL512X LED50S/840 DIA DA35W 7 WH HE	Double asymmetric optic 35° wide beam
910925870779	LL512X LED80S/840 DIA WB 7 WH HE	Wide beam
910925870801	LL512X LED50S/840 PSD WB 7 BK HE	Wide beam
910925870804	LL512X LED50S/840 PSED WB 7 WH HE	Wide beam
910925870806	LL512X LED31S/840 PSD DA35W 7 WH HE	Double asymmetric optic 35° wide beam
910925870807	LL512X LED31S/840 PSD WB 7 BK HE	Wide beam
910925870808	LL512X LED61S/840 PSD WB 7 BK HE	Wide beam
910925867810	LL523X LED123S/830 PSD WB 7 WH XA	Wide beam
910925867811	LL523X LED160S/830 PSD MB 7 WH XA	Medium beam
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	Double asymmetric optic 45°
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	Double asymmetric optic 45°
910925867814	LL523X LED160S/830 PSD WB 7 WH XA	Wide beam
910925867815	LL523X LED160S/830 PSD NB 7 WH XA	Narrow beam
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	Wide beam
910925867818	LL523X LED123S/840 PSD MB 7 VLC WH XA	Medium beam
910925867819	LL523X LED123S/840 PSD WB 7 VLC WH XA	Wide beam
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	Medium beam
910925867825	LL523X LED123S/840 PSED NB 13 VLC WH XA	Narrow beam
910925867826	LL523X LED123S/840 PSED MB 13 VLC WH XA	Medium beam
910925867827	LL523X LED123S/840 PSED WB 13 VLC WH XA	Wide beam
910925867828	LL523X LED160S/840 PSED NB 13 WH XA	Narrow beam
910925867837	LL523X LED123S/840 PSD MB 7 VLC WH XA	Medium beam
910925867838	LL523X LED123S/840 PSD WB 7 VLC WH XA	Wide beam
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	Medium beam
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	Narrow beam
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	Narrow beam
910925868127	LL523X LED62S/840 PSED WB-OC 13 WH XA	Wide beam
910925868130	LL523X LED62S/840 PSD WB-OC 13 ELP3 WH X	Wide beam
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	Wide beam
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	Medium beam
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	Wide beam
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	Medium beam
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	Wide beam
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	Narrow beam

Order Code	Full Product Name	Optic type
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	Medium beam
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	Wide beam
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	Narrow beam
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	Medium beam
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	Medium beam
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	Wide beam
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	Narrow beam
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	Medium beam
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	Wide beam
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	Narrow beam
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	Medium beam
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	Wide beam
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	Wide beam
910925870371	LL523X LED62S/840 DIA MB 7 WH HE	Medium beam
910925870372	LL523X LED62S/840 DIA WB 7 WH HE	Wide beam
910925870373	LL523X LED100S/840 DIA MB 7 WH HE	Medium beam
910925870374	LL523X LED123S/840 DIA MB 7 WH HE	Medium beam
910925870375	LL523X LED100S/840 DIA WB 7 WH HE	Wide beam
910925870376	LL523X LED123S/840 DIA NB 7 WH HE	Narrow beam
910925870377	LL523X LED123S/840 DIA WB 7 WH HE	Wide beam
910925870378	LL523X LED160S/840 DIA NB 7 WH HE	Narrow beam
910925870379	LL523X LED160S/840 DIA MB 7 WH HE	Medium beam
910925870380	LL512X LED31S/840 DIA MB 7 WH HE	Medium beam
910925870381	LL512X LED31S/840 DIA WB 7 WH HE	Wide beam
910925870382	LL512X LED50S/840 DIA MB 7 WH HE	Medium beam
910925870383		Wide beam
910925870384	LL512X LED61S/840 DIA NB 7 WH HE	Narrow beam
910925870385	LL512X LED61S/840 DIA MB 7 WH HE	Medium beam
910925870386	LL512X LED61S/840 DIA WB 7 WH HE	Wide beam
910925870387	LL512X LED80S/840 DIA NB 7 WH HE	Narrow beam
910925870388	LL512X LED80S/840 DIA MB 7 WH HE	Medium beam
910925870756	LL523X LED62S/840 DEIA WB-OC 13 WH HE	Wide beam
910925870758	LL523X LED62S/840 DIA DA25N 7 WH HE	Double asymmetric optic 25° narrow beam
910925870759	LL523X LED62S/840 DIA DA25W 7 WH HE	Double asymmetric optic 25° narrow beam
910925870760	LL523X LED62S/840 DIA DA35W 7 WH HE	Double asymmetric optic 35° wide beam
910925870761	LL523X LED100S/840 DIA NB 7 WH HE	Narrow beam
910925870763	LL523X LED100S/840 DIA A20 7 WH HE	Asymmetrical mirror
910925870764	LL523X LED100S/840 DIA DA35W 7 WH HE	Double asymmetric optic 35° wide beam
910925870766	LL523X LED123S/840 DIA A20 7 WH HE	Asymmetrical mirror
910925870767	LL523X LED123S/840 DIA DA25W 7 WH HE	Double asymmetric optic 25° narrow beam
910925870768	LL523X LED123S/840 DIA DA35W 7 WH HE	Double asymmetric optic 35° wide beam
910925870769	LL523X LED160S/840 DIA WB 7 WH HE	Wide beam
910925870796	LL523X LED123S/840 PSD A20 7 WH HE	Asymmetrical mirror

Order Code	Full Product Name	Optic type
910925870797	LL523X LED160S/840 PSD XNB 7 WH HE	Extra narrow beam
910925870798	LL523X LED100S/840 PSD WB 7 SI HE	Wide beam
910925870799	LL523X LED123S/840 PSD WB 7 BK HE	Wide beam
910925870802	LL523X LED62S/840 PSD WB 7 SI HE	Wide beam
910925870809	LL523X LED100S/840 PSD DA35W 7 WH HE	Double asymmetric optic 35° wide beam
910925870810	LL523X LED100S/840 PSD WB 7 BK HE	Wide beam
910925870811	LL523X LED123S/840 PSD DA35W 7 WH HE	Double asymmetric optic 35° wide beam
910925870812	LL523X LED62S/840 PSD DA35W 7 WH HE	Double asymmetric optic 35° wide beam
910925870819	LL523X LED123S/840 DIA WB 13 ELP3 WH HE	Wide beam
910925870780	LL612X LED61S/840 DIA WB 7 WH HE	Wide beam

Order Code	Full Product Name	Optic type
910925870794	LL612X LED61S/840 DIA MB 7 WH HE	Medium beam
910925870795	LL612X LED61S/840 DIA NB 7 WH HE	Narrow beam
910925870803	LL612X LED61S/840 PSD NB 7 WH HE	Narrow beam
910925870770	LL623X LED123S/840 DIA MB 7 WH HE	Medium beam
910925870771	LL623X LED123S/840 DIA WB 7 WH HE	Wide beam
910925870772	LL623X LED123S/840 DIA NB 7 WH HE	Narrow beam
910925870805	LL623X LED123S/840 PSD WB 7 WH HE	Wide beam
910925868648	LL515X 61S/840 PSD WB 7 HE WH	Wide beam
910925868649	LL515X 80S/840 PSD WB 7 HE WH	Wide beam
910925868650	LL515X 61S/840 PSD MB 7 HE WH	Medium beam
910925868651	LL515X 80S/840 PSD MB 7 HE WH	Medium beam
910925868652	LL515X 61S/840 PSD NB 7 HE WH	Narrow beam
910925868653	LL515X 80S/840 PSD NB 7 HE WH	Narrow beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910925870051	LL512X LED61S/840 PSD O-PC 7 VLC WH XA	34.5 W
910925870052	LL523X LED123S/840 PSD O-PC 7 VLC WH XA	66 W
910925870055	LL523X LED123S/840 SIA O-PC 7 WH HE	71 W
910925870056	LL523X LED100S/840 SIA O-PC 7 WH HE	59 W
910925870057	LL523X LED62S/840 SIA O-PC 7 WH HE	34.5 W
910925870058	LL512X LED61S/840 SIA O-PC 7 WH HE	37 W
910925870059	LL512X LED31S/840 SIA O-PC 7 WH HE	18.5 W
910925870061	LL523X LED62S/840 DIA O-PC 7 WH HE	36 W
910925870062	LL523X LED62S/840 DIA O-PC 13 ELP3 WH HE	36 W
910925870063	LL523X LED100S/840 DIA O-PC 7 WH HE	59 W
910925870064	LL523X LED123S/840 DIA O-PC 7 WH HE	70 W
910925870065	LL512X LED31S/840 DIA O-PC 7 WH HE	18.5 W
910925870066	LL512X LED50S/840 DIA O-PC 7 WH HE	30 W
910925870067	LL512X LED61S/840 DIA O-PC 7 WH HE	37 W
910925868124	LL512X LED31S/840 PSED WB-OC 13 BK XA	18 W
910925868128	LL523X LED62S/840 PSED WB-OC 13 BK XA	34 W
910925868123	LL512X LED31S/840 PSED WB-OC 13 WH XA	18 W
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	18 W
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	18 W
910925868959		18 W
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	29 W
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	29 W
910925868962	LL512X LED61S/840 PSD NB 7 WH HE	37 W
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	37 W
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	37 W
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	50 W
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	50 W
910925868978	LL512X LED50S/840 SIA MB 7 WH HE	29 W
910925868979	LL512X LED50S/840 SIA WB 7 WH HE	29 W
910925868980	LL512X LED61S/840 SIA NB 7 WH HE	37 W
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	37 W
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	37 W
910925868983	LL512X LED80S/840 SIA NB 7 WH HE	50 W
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	50 W
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	18 W

Order Code	Full Product Name	Power Consumption
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	50 W
910925870773	LL512X LED31S/830 DIA WB 7 WH HE	18 W
910925870775	LL512X LED31S/840 DEIA WB-OC 13 WH HE	18 W
910925870777	LL512X LED50S/840 DIA DA35W 7 WH HE	29 W
910925870779	LL512X LED80S/840 DIA WB 7 WH HE	50 W
910925870801	LL512X LED50S/840 PSD WB 7 BK HE	29 W
910925870804	LL512X LED50S/840 PSED WB 7 WH HE	29 W
910925870806	LL512X LED31S/840 PSD DA35W 7 WH HE	18 W
910925870807	LL512X LED31S/840 PSD WB 7 BK HE	18 W
910925870808	LL512X LED61S/840 PSD WB 7 BK HE	37 W
910925867810	LL523X LED123S/830 PSD WB 7 WH XA	68 W
910925867811	LL523X LED160S/830 PSD MB 7 WH XA	91 W
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	68 W
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	68 W
910925867814	LL523X LED160S/830 PSD WB 7 WH XA	91 W
910925867815	LL523X LED160S/830 PSD NB 7 WH XA	91 W
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	68 W
910925867818	LL523X LED123S/840 PSD MB 7 VLC WH XA	68 W
910925867819	LL523X LED123S/840 PSD WB 7 VLC WH XA	68 W
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	91 W
910925867825	LL523X LED123S/840 PSED NB 13 VLC WH XA	68 W
910925867826	LL523X LED123S/840 PSED MB 13 VLC WH XA	68 W
910925867827	LL523X LED123S/840 PSED WB 13 VLC WH XA	68 W
910925867828	LL523X LED160S/840 PSED NB 13 WH XA	91 W
910925867837	LL523X LED123S/840 PSD MB 7 VLC WH XA	68 W
910925867838	LL523X LED123S/840 PSD WB 7 VLC WH XA	68 W
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	91 W
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	68 W
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	91 W
910925868127	LL523X LED62S/840 PSED WB-OC 13 WH XA	34 W
910925868130	LL523X LED62S/840 PSD WB-OC 13 ELP3 WH X	35 W
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	35 W
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	34.5 W
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	34.5 W
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	57 W

Order Code	Full Product Name	Power Consumption
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	57 W
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	72 W
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	72 W
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	72 W
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	97 W
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	97 W
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	57 W
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	57 W
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	72 W
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	72 W
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	72 W
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	97 W
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	97 W
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	34.5 W
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	97 W
910925870371	LL523X LED62S/840 DIA MB 7 WH HE	34.5 W
910925870372	LL523X LED62S/840 DIA WB 7 WH HE	34.5 W
910925870373	LL523X LED100S/840 DIA MB 7 WH HE	57 W
910925870374	LL523X LED123S/840 DIA MB 7 WH HE	72 W
910925870375	LL523X LED100S/840 DIA WB 7 WH HE	57 W
910925870376	LL523X LED123S/840 DIA NB 7 WH HE	72 W
910925870377	LL523X LED123S/840 DIA WB 7 WH HE	72 W
910925870378	LL523X LED160S/840 DIA NB 7 WH HE	97 W
910925870379	LL523X LED160S/840 DIA MB 7 WH HE	97 W
910925870380	LL512X LED31S/840 DIA MB 7 WH HE	18 W
910925870381	LL512X LED31S/840 DIA WB 7 WH HE	18 W
910925870382	LL512X LED50S/840 DIA MB 7 WH HE	29 W
910925870383		29 W
910925870384	LL512X LED61S/840 DIA NB 7 WH HE	37 W
910925870385	LL512X LED61S/840 DIA MB 7 WH HE	37 W
910925870386	LL512X LED61S/840 DIA WB 7 WH HE	37 W
910925870387	LL512X LED80S/840 DIA NB 7 WH HE	50 W
910925870388	LL512X LED80S/840 DIA MB 7 WH HE	50 W
910925870756	LL523X LED62S/840 DEIA WB-OC 13 WH HE	34.5 W

Order Code	Full Product Name	Power Consumption
910925870758	LL523X LED62S/840 DIA DA25N 7 WH HE	34.5 W
910925870759	LL523X LED62S/840 DIA DA25W 7 WH HE	34.5 W
910925870760	LL523X LED62S/840 DIA DA35W 7 WH HE	34.5 W
910925870761	LL523X LED100S/840 DIA NB 7 WH HE	57 W
910925870763	LL523X LED100S/840 DIA A20 7 WH HE	57 W
910925870764	LL523X LED100S/840 DIA DA35W 7 WH HE	57 W
910925870766	LL523X LED123S/840 DIA A20 7 WH HE	72 W
910925870767	LL523X LED123S/840 DIA DA25W 7 WH HE	72 W
910925870768	LL523X LED123S/840 DIA DA35W 7 WH HE	72 W
910925870769	LL523X LED160S/840 DIA WB 7 WH HE	97 W
910925870796	LL523X LED123S/840 PSD A20 7 WH HE	72 W
910925870797	LL523X LED160S/840 PSD XNB 7 WH HE	97 W
910925870798	LL523X LED100S/840 PSD WB 7 SI HE	57 W
910925870799	LL523X LED123S/840 PSD WB 7 BK HE	72 W
910925870802	LL523X LED62S/840 PSD WB 7 SI HE	34.5 W
910925870809	LL523X LED100S/840 PSD DA35W 7 WH HE	57 W
910925870810	LL523X LED100S/840 PSD WB 7 BK HE	57 W
910925870811	LL523X LED123S/840 PSD DA35W 7 WH HE	72 W
910925870812	LL523X LED62S/840 PSD DA35W 7 WH HE	34.5 W
910925870819	LL523X LED123S/840 DIA WB 13 ELP3 WH HE	76 W
910925870780	LL612X LED61S/840 DIA WB 7 WH HE	37 W
910925870794	LL612X LED61S/840 DIA MB 7 WH HE	37 W
910925870795	LL612X LED61S/840 DIA NB 7 WH HE	37 W
910925870803	LL612X LED61S/840 PSD NB 7 WH HE	37 W
910925870770	LL623X LED123S/840 DIA MB 7 WH HE	72 W
910925870771	LL623X LED123S/840 DIA WB 7 WH HE	72 W
910925870772	LL623X LED123S/840 DIA NB 7 WH HE	72 W
910925870805	LL623X LED123S/840 PSD WB 7 WH HE	72 W
910925868648	LL515X 61S/840 PSD WB 7 HE WH	37 W
910925868649	LL515X 80S/840 PSD WB 7 HE WH	50 W
910925868650	LL515X 61S/840 PSD MB 7 HE WH	37 W
910925868651	LL515X 80S/840 PSD MB 7 HE WH	50 W
910925868652	LL515X 61S/840 PSD NB 7 HE WH	37 W
910925868653	LL515X 80S/840 PSD NB 7 HE WH	50 W

Controls and Dimming

Order Code	Full Product Name	Embedded control	Maximum dim level
910925870051	LL512X LED61S/840 PSD O-PC 7 VLC WH XA	-	-
910925870052	LL523X LED123S/840 PSD O-PC 7 VLC WH XA	-	-
910925870055	LL523X LED123S/840 SIA O-PC 7 WH HE	-	-
910925870056	LL523X LED100S/840 SIA O-PC 7 WH HE	-	-
910925870057	LL523X LED62S/840 SIA O-PC 7 WH HE	-	-
910925870058	LL512X LED61S/840 SIA O-PC 7 WH HE	-	-

Order Code	Full Product Name	Embedded control	Maximum dim level
910925870059	LL512X LED31S/840 SIA O-PC 7 WH HE	-	-
910925870061	LL523X LED62S/840 DIA O-PC 7 WH HE	-	-
910925870062	LL523X LED62S/840 DIA O-PC 13 ELP3 WH HE	-	-
910925870063	LL523X LED100S/840 DIA O-PC 7 WH HE	-	-
910925870064	LL523X LED123S/840 DIA O-PC 7 WH HE	-	-
910925870065	LL512X LED31S/840 DIA O-PC 7 WH HE	-	-

Order Code	Full Product Name	Embedded control	Maximum dim level
910925870066	LL512X LED50S/840 DIA O-PC 7 WH HE	-	-
910925870067	LL512X LED61S/840 DIA O-PC 7 WH HE	-	-
910925868124	LL512X LED31S/840 PSED WB-OC 13 BK XA	-	1%
910925868128	LL523X LED62S/840 PSED WB-OC 13 BK XA	-	1%
910925868123	LL512X LED31S/840 PSED WB-OC 13 WH XA	-	1%
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	-	1%
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	-	1%
910925868959		-	1%
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	-	1%
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	-	1%
910925868962	LL512X LED61S/840 PSD NB 7 WH HE	-	1%
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	-	1%
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	-	1%
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	-	1%
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	-	1%
910925868978	LL512X LED50S/840 SIA MB 7 WH HE	-	1%
910925868979	LL512X LED50S/840 SIA WB 7 WH HE	-	1%
910925868980	LL512X LED61S/840 SIA NB 7 WH HE	-	1%
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	-	1%
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	-	1%
910925868983	LL512X LED80S/840 SIA NB 7 WH HE	-	1%
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	-	1%
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	-	1%
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	-	1%
910925870773	LL512X LED31S/830 DIA WB 7 WH HE	-	1%
910925870775	LL512X LED31S/840 DEIA WB-OC 13 WH HE	-	1%

Order Code	Full Product Name	Embedded control	Maximum dim level
910925870777	LL512X LED50S/840 DIA DA35W 7 WH HE	-	1%
910925870779	LL512X LED80S/840 DIA WB 7 WH HE	-	1%
910925870801	LL512X LED50S/840 PSD WB 7 BK HE	-	1%
910925870804	LL512X LED50S/840 PSED WB 7 WH HE	-	1%
910925870806	LL512X LED31S/840 PSD DA35W 7 WH HE	-	1%
910925870807	LL512X LED31S/840 PSD WB 7 BK HE	-	1%
910925870808	LL512X LED61S/840 PSD WB 7 BK HE	-	1%
910925867810	LL523X LED123S/830 PSD WB 7 WH XA	-	1%
910925867811	LL523X LED160S/830 PSD MB 7 WH XA	-	1%
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	-	1%
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	-	1%
910925867814	LL523X LED160S/830 PSD WB 7 WH XA	-	1%
910925867815	LL523X LED160S/830 PSD NB 7 WH XA	-	1%
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	-	1%
910925867818	LL523X LED123S/840 PSD MB 7 VLC WH XA	Visible light communication	1%
910925867819	LL523X LED123S/840 PSD WB 7 VLC WH XA	Visible light communication	1%
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	-	1%
910925867825	LL523X LED123S/840 PSED NB 13 VLC WH XA	Visible light communication	1%
910925867826	LL523X LED123S/840 PSED MB 13 VLC WH XA	Visible light communication	1%
910925867827	LL523X LED123S/840 PSED WB 13 VLC WH XA	Visible light communication	1%
910925867828	LL523X LED160S/840 PSED NB 13 WH XA	-	1%
910925867837	LL523X LED123S/840 PSD MB 7 VLC WH XA	Visible light communication	1%
910925867838	LL523X LED123S/840 PSD WB 7 VLC WH XA	Visible light communication	1%
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	-	1%
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	Visible light communication	1%

Order Code	Full Product Name	Embedded control	Maximum dim level
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	-	1%
910925868127	LL523X LED62S/840 PSED WB-OC 13 WH XA	-	1%
910925868130	LL523X LED62S/840 PSD WB-OC 13 ELP3 WH X	-	1%
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	-	1%
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	-	1%
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	-	1%
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	-	1%
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	-	1%
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	-	1%
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	-	1%
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	-	1%
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	-	1%
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	-	1%
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	-	1%
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	-	1%
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	-	1%
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	-	1%
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	-	1%
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	-	1%
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	-	1%
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	-	1%
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	-	1%
910925870371	LL523X LED62S/840 DIA MB 7 WH HE	-	1%
910925870372	LL523X LED62S/840 DIA WB 7 WH HE	-	1%
910925870373	LL523X LED100S/840 DIA MB 7 WH HE	-	1%

Order Code	Full Product Name	Embedded control	Maximum dim level
910925870374	LL523X LED123S/840 DIA MB 7 WH HE	-	1%
910925870375	LL523X LED100S/840 DIA WB 7 WH HE	-	1%
910925870376	LL523X LED123S/840 DIA NB 7 WH HE	-	1%
910925870377	LL523X LED123S/840 DIA WB 7 WH HE	-	1%
910925870378	LL523X LED160S/840 DIA NB 7 WH HE	-	1%
910925870379	LL523X LED160S/840 DIA MB 7 WH HE	-	1%
910925870380	LL512X LED31S/840 DIA MB 7 WH HE	-	1%
910925870381	LL512X LED31S/840 DIA WB 7 WH HE	-	1%
910925870382	LL512X LED50S/840 DIA MB 7 WH HE	-	1%
910925870383		-	1%
910925870384	LL512X LED61S/840 DIA NB 7 WH HE	-	1%
910925870385	LL512X LED61S/840 DIA MB 7 WH HE	-	1%
910925870386	LL512X LED61S/840 DIA WB 7 WH HE	-	1%
910925870387	LL512X LED80S/840 DIA NB 7 WH HE	-	1%
910925870388	LL512X LED80S/840 DIA MB 7 WH HE	-	1%
910925870756	LL523X LED62S/840 DEIA WB-OC 13 WH HE	-	1%
910925870758	LL523X LED62S/840 DIA DA25N 7 WH HE	-	1%
910925870759	LL523X LED62S/840 DIA DA25W 7 WH HE	-	1%
910925870760	LL523X LED62S/840 DIA DA35W 7 WH HE	-	1%
910925870761	LL523X LED100S/840 DIA NB 7 WH HE	-	1%
910925870763	LL523X LED100S/840 DIA A20 7 WH HE	-	1%
910925870764	LL523X LED100S/840 DIA DA35W 7 WH HE	-	1%
910925870766	LL523X LED123S/840 DIA A20 7 WH HE	-	1%
910925870767	LL523X LED123S/840 DIA DA25W 7 WH HE	-	1%
910925870768	LL523X LED123S/840 DIA DA35W 7 WH HE	-	1%
910925870769	LL523X LED160S/840 DIA WB 7 WH HE	-	1%

Order Code	Full Product Name	Embedded control	Maximum dim level
910925870796	LL523X LED123S/840 PSD A20 7 WH HE	-	1%
910925870797	LL523X LED160S/840 PSD XNB 7 WH HE	-	1%
910925870798	LL523X LED100S/840 PSD WB 7 SI HE	-	1%
910925870799	LL523X LED123S/840 PSD WB 7 BK HE	-	1%
910925870802	LL523X LED62S/840 PSD WB 7 SI HE	-	1%
910925870809	LL523X LED100S/840 PSD DA35W 7 WH HE	-	1%
910925870810	LL523X LED100S/840 PSD WB 7 BK HE	-	1%
910925870811	LL523X LED123S/840 PSD DA35W 7 WH HE	-	1%
910925870812	LL523X LED62S/840 PSD DA35W 7 WH HE	-	1%
910925870819	LL523X LED123S/840 DIA WB 13 ELP3 WH HE	-	1%
910925870780	LL612X LED61S/840 DIA WB 7 WH HE	-	1%

Order Code	Full Product Name	Embedded control	Maximum dim level
910925870794	LL612X LED61S/840 DIA MB 7 WH HE	-	1%
910925870795	LL612X LED61S/840 DIA NB 7 WH HE	-	1%
910925870803	LL612X LED61S/840 PSD NB 7 WH HE	-	1%
910925870770	LL623X LED123S/840 DIA MB 7 WH HE	-	1%
910925870771	LL623X LED123S/840 DIA WB 7 WH HE	-	1%
910925870772	LL623X LED123S/840 DIA NB 7 WH HE	-	1%
910925870805	LL623X LED123S/840 PSD WB 7 WH HE	-	1%
910925868648	LL515X 61S/840 PSD WB 7 HE WH	-	1%
910925868649	LL515X 80S/840 PSD WB 7 HE WH	-	1%
910925868650	LL515X 61S/840 PSD MB 7 HE WH	-	1%
910925868651	LL515X 80S/840 PSD MB 7 HE WH	-	1%
910925868652	LL515X 61S/840 PSD NB 7 HE WH	-	1%
910925868653	LL515X 80S/840 PSD NB 7 HE WH	-	1%

Mechanical and Housing

Order Code	Full Product Name	Housing Color	Mech. impact protection code	Ingress protection code
910925870051	LL512X LED61S/840 PSD O-PC 7 VLC WH XA	White	IK02	IP20
910925870052	LL523X LED123S/840 PSD O-PC 7 VLC WH XA	White	IK02	IP20
910925870055	LL523X LED123S/840 SIA O-PC 7 WH HE	White	IK02	IP20
910925870056	LL523X LED100S/840 SIA O-PC 7 WH HE	White	IK02	IP20
910925870057	LL523X LED62S/840 SIA O-PC 7 WH HE	White	IK02	IP20
910925870058	LL512X LED61S/840 SIA O-PC 7 WH HE	White	IK02	IP20
910925870059	LL512X LED31S/840 SIA O-PC 7 WH HE	White	IK02	IP20
910925870061	LL523X LED62S/840 DIA O-PC 7 WH HE	White	IK02	IP20
910925870062	LL523X LED62S/840 DIA O-PC 13 ELP3 WH HE	White	IK02	IP20
910925870063	LL523X LED100S/840 DIA O-PC 7 WH HE	White	IK02	IP20
910925870064	LL523X LED123S/840 DIA O-PC 7 WH HE	White	IK02	IP20

Order Code	Full Product Name	Housing Color	Mech. impact protection code	Ingress protection code
910925870065	LL512X LED31S/840 DIA O-PC 7 WH HE	White	IK02	IP20
910925870066	LL512X LED50S/840 DIA O-PC 7 WH HE	White	IK02	IP20
910925870067	LL512X LED61S/840 DIA O-PC 7 WH HE	White	IK02	IP20
910925868124	LL512X LED31S/840 PSED WB-OC 13 BK XA	Black	IK02	IP20
910925868128	LL523X LED62S/840 PSED WB-OC 13 BK XA	Black	IK02	IP20
910925868123	LL512X LED31S/840 PSED WB-OC 13 WH XA	White	IK02	IP20
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	White	IK02	IP20
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	White	IK02	IP20
910925868959		White	IK02	IP20
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	White	IK02	IP20
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	White	IK02	IP20

Order Code	Full Product Name	Housing Color	Mech. impact protection code	Ingress protection code
910925868962	LL512X LED61S/840 PSD NB 7 WH HE	White	IK02	IP20
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	White	IK02	IP20
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	White	IK02	IP20
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	White	IK02	IP20
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	White	IK02	IP20
910925868978	LL512X LED50S/840 SIA MB 7 WH HE	White	IK02	IP20
910925868979	LL512X LED50S/840 SIA WB 7 WH HE	White	IK02	IP20
910925868980	LL512X LED61S/840 SIA NB 7 WH HE	White	IK02	IP20
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	White	IK02	IP20
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	White	IK02	IP20
910925868983	LL512X LED80S/840 SIA NB 7 WH HE	White	IK02	IP20
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	White	IK02	IP20
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	White	IK02	IP20
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	White	IK02	IP20
910925870773	LL512X LED31S/830 DIA WB 7 WH HE	White	IK02	IP20
910925870775	LL512X LED31S/840 DEIA WB-OC 13 WH HE	White	IK02	IP20
910925870777	LL512X LED50S/840 DIA DA35W 7 WH HE	White	IK02	IP20
910925870779	LL512X LED80S/840 DIA WB 7 WH HE	White	IK02	IP20
910925870801	LL512X LED50S/840 PSD WB 7 BK HE	Black	IK02	IP20
910925870804	LL512X LED50S/840 PSED WB 7 WH HE	White	IK02	IP20
910925870806	LL512X LED31S/840 PSD DA35W 7 WH HE	White	IK02	IP20
910925870807	LL512X LED31S/840 PSD WB 7 BK HE	Black	IK02	IP20
910925870808	LL512X LED61S/840 PSD WB 7 BK HE	Black	IK02	IP20
910925867810	LL523X LED123S/830 PSD WB 7 WH XA	White	IK02	IP20

Order Code	Full Product Name	Housing Color	Mech. impact protection code	Ingress protection code
910925867811	LL523X LED160S/830 PSD MB 7 WH XA	White	IK02	IP20
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	White	IK02	IP20
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	White	IK02	IP20
910925867814	LL523X LED160S/830 PSD WB 7 WH XA	White	IK02	IP20
910925867815	LL523X LED160S/830 PSD NB 7 WH XA	White	IK02	IP20
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	White	IK02	IP20
910925867818	LL523X LED123S/840 PSD MB 7 VLC WH XA	White	IK02	IP20
910925867819	LL523X LED123S/840 PSD WB 7 VLC WH XA	White	IK02	IP20
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	White	IK02	IP20
910925867825	LL523X LED123S/840 PSED NB 13 VLC WH XA	White	IK02	IP20
910925867826	LL523X LED123S/840 PSED MB 13 VLC WH XA	White	IK02	IP20
910925867827	LL523X LED123S/840 PSED WB 13 VLC WH XA	White	IK02	IP20
910925867828	LL523X LED160S/840 PSED NB 13 WH XA	White	IK02	IP20
910925867837	LL523X LED123S/840 PSD MB 7 VLC WH XA	White	IK02	IP20
910925867838	LL523X LED123S/840 PSD WB 7 VLC WH XA	White	IK02	IP20
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	White	IK02	IP20
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	White	IK02	IP20
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	White	IK02	IP20
910925868127	LL523X LED62S/840 PSED WB-OC 13 WH XA	White	IK02	IP20
910925868130	LL523X LED62S/840 PSD WB-OC 13 ELP3 WH X	White	IK02	IP20
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	White	IK02	IP20
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	White	IK02	IP20
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	White	IK02	IP20
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	White	IK02	IP20

Order Code	Full Product Name	Housing Color	Mech. impact protection code	Ingress protection code
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	White	IK02	IP20
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	White	IK02	IP20
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	White	IK02	IP20
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	White	IK02	IP20
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	White	IK02	IP20
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	White	IK02	IP20
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	White	IK02	IP20
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	White	IK02	IP20
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	White	IK02	IP20
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	White	IK02	IP20
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	White	IK02	IP20
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	White	IK02	IP20
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	White	IK02	IP20
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	White	IK02	IP20
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	White	IK02	IP20
910925870371	LL523X LED62S/840 DIA MB 7 WH HE	White	IK02	IP20
910925870372	LL523X LED62S/840 DIA WB 7 WH HE	White	IK02	IP20
910925870373	LL523X LED100S/840 DIA MB 7 WH HE	White	IK02	IP20
910925870374	LL523X LED123S/840 DIA MB 7 WH HE	White	IK02	IP20
910925870375	LL523X LED100S/840 DIA WB 7 WH HE	White	IK02	IP20
910925870376	LL523X LED123S/840 DIA NB 7 WH HE	White	IK02	IP20
910925870377	LL523X LED123S/840 DIA WB 7 WH HE	White	IK02	IP20
910925870378	LL523X LED160S/840 DIA NB 7 WH HE	White	IK02	IP20
910925870379	LL523X LED160S/840 DIA MB 7 WH HE	White	IK02	IP20

Order Code	Full Product Name	Housing Color	Mech. impact protection code	Ingress protection code
910925870380	LL512X LED31S/840 DIA MB 7 WH HE	White	IK02	IP20
910925870381	LL512X LED31S/840 DIA WB 7 WH HE	White	IK02	IP20
910925870382	LL512X LED50S/840 DIA MB 7 WH HE	White	IK02	IP20
910925870383		White	IK02	IP20
910925870384	LL512X LED61S/840 DIA NB 7 WH HE	White	IK02	IP20
910925870385	LL512X LED61S/840 DIA MB 7 WH HE	White	IK02	IP20
910925870386	LL512X LED61S/840 DIA WB 7 WH HE	White	IK02	IP20
910925870387	LL512X LED80S/840 DIA NB 7 WH HE	White	IK02	IP20
910925870388	LL512X LED80S/840 DIA MB 7 WH HE	White	IK02	IP20
910925870756	LL523X LED62S/840 DEIA WB-OC 13 WH HE	White	IK02	IP20
910925870758	LL523X LED62S/840 DIA DA25N 7 WH HE	White	IK02	IP20
910925870759	LL523X LED62S/840 DIA DA25W 7 WH HE	White	IK02	IP20
910925870760	LL523X LED62S/840 DIA DA35W 7 WH HE	White	IK02	IP20
910925870761	LL523X LED100S/840 DIA NB 7 WH HE	White	IK02	IP20
910925870763	LL523X LED100S/840 DIA A20 7 WH HE	White	IK02	IP20
910925870764	LL523X LED100S/840 DIA DA35W 7 WH HE	White	IK02	IP20
910925870766	LL523X LED123S/840 DIA A20 7 WH HE	White	IK02	IP20
910925870767	LL523X LED123S/840 DIA DA25W 7 WH HE	White	IK02	IP20
910925870768	LL523X LED123S/840 DIA DA35W 7 WH HE	White	IK02	IP20
910925870769	LL523X LED160S/840 DIA WB 7 WH HE	White	IK02	IP20
910925870796	LL523X LED123S/840 PSD A20 7 WH HE	White	IK02	IP20
910925870797	LL523X LED160S/840 PSD XNB 7 WH HE	White	IK02	IP20
910925870798	LL523X LED100S/840 PSD WB 7 SI HE	Silver	IK02	IP20
910925870799	LL523X LED123S/840 PSD WB 7 BK HE	Black	IK02	IP20
910925870802	LL523X LED62S/840 PSD WB 7 SI HE	Silver	IK02	IP20

Maxos fusion

Order Code	Full Product Name	Housing Color	Mech. impact protection code	Ingress protection code
910925870809	LL523X LED100S/840 PSD DA35W 7 WH HE	White	IK02	IP20
910925870810	LL523X LED100S/840 PSD WB 7 BK HE	Black	IK02	IP20
910925870811	LL523X LED123S/840 PSD DA35W 7 WH HE	White	IK02	IP20
910925870812	LL523X LED62S/840 PSD DA35W 7 WH HE	White	IK02	IP20
910925870819	LL523X LED123S/840 DIA WB 13 ELP3 WH HE	White	IK03	IP20
910925870780	LL612X LED61S/840 DIA WB 7 WH HE	White	IK02	IP54
910925870794	LL612X LED61S/840 DIA MB 7 WH HE	White	IK02	IP54
910925870795	LL612X LED61S/840 DIA NB 7 WH HE	White	IK02	IP54
910925870803	LL612X LED61S/840 PSD NB 7 WH HE	White	IK02	IP54
910925870770	LL623X LED123S/840 DIA MB 7 WH HE	White	IK02	IP54

Order Code	Full Product Name	Housing Color	Mech. impact protection code	Ingress protection code
910925870771	LL623X LED123S/840 DIA WB 7 WH HE	White	IK02	IP54
910925870772	LL623X LED123S/840 DIA NB 7 WH HE	White	IK02	IP54
910925870805	LL623X LED123S/840 PSD WB 7 WH HE	White	IK02	IP54
910925868648	LL515X 61S/840 PSD WB 7 HE WH	White	IK02	IP20
910925868649	LL515X 80S/840 PSD WB 7 HE WH	White	IK02	IP20
910925868650	LL515X 61S/840 PSD MB 7 HE WH	White	IK02	IP20
910925868651	LL515X 80S/840 PSD MB 7 HE WH	White	IK02	IP20
910925868652	LL515X 61S/840 PSD NB 7 HE WH	White	IK02	IP20
910925868653	LL515X 80S/840 PSD NB 7 HE WH	White	IK02	IP20

Emergency Operation (1/2)

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Power consumption during Central DC emergency mode
910925870051	LL512X LED61S/840 PSD O-PC 7 VLC WH XA	-	-	-	-
910925870052	LL523X LED123S/840 PSD O-PC 7 VLC WH XA	-	-	-	-
910925870055	LL523X LED123S/840 SIA O-PC 7 WH HE	-	-	-	-
910925870056	LL523X LED100S/840 SIA O-PC 7 WH HE	-	-	-	-
910925870057	LL523X LED62S/840 SIA O-PC 7 WH HE	-	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Power consumption during Central DC emergency mode
910925870058	LL512X LED61S/840 SIA O-PC 7 WH HE	-	-	-	-
910925870059	LL512X LED31S/840 SIA O-PC 7 WH HE	-	-	-	-
910925870061	LL523X LED62S/840 DIA O-PC 7 WH HE	-	-	-	-
910925870062	LL523X LED62S/840 DIA O-PC 13 ELP3 WH HE	-	-	-	-
910925870063	LL523X LED100S/840 DIA O-PC 7 WH HE	-	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Power consumption during Central DC emergency mode
910925870064	LL523X LED123S/840 DIA O-PC 7 WH HE	-	-	-	-
910925870065	LL512X LED31S/840 DIA O-PC 7 WH HE	-	-	-	-
910925870066	LL512X LED50S/840 DIA O-PC 7 WH HE	-	-	-	-
910925870067	LL512X LED61S/840 DIA O-PC 7 WH HE	-	-	-	-
910925868124	LL512X LED31S/840 PSED WB-OC 13 BK XA	Yes	DC operated central emergency lighting	-	-
910925868128	LL523X LED62S/840 PSED WB-OC 13 BK XA	Yes	DC operated central emergency lighting	-	-
910925868123	LL512X LED31S/840 PSED WB-OC 13 WH XA	Yes	DC operated central emergency lighting	-	-
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	-	-	-	-
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	-	-	-	-
910925868959		-	-	-	-
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	-	-	-	-
910925868961	LL512X LED50S/840	-	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Power consumption during Central DC emergency mode
	PSD WB 7 WH HE				
910925868962	LL512X LED61S/840 PSD NB 7 WH HE	-	-	-	-
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	-	-	-	-
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	-	-	-	-
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	-	-	-	-
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	-	-	-	-
910925868978	LL512X LED50S/840 SIA MB 7 WH HE	-	-	-	-
910925868979	LL512X LED50S/840 SIA WB 7 WH HE	-	-	-	-
910925868980	LL512X LED61S/840 SIA NB 7 WH HE	-	-	-	-
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	-	-	-	-
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	-	-	-	-
910925868983	LL512X LED80S/840 SIA NB 7 WH HE	-	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Power consumption during Central DC emergency mode
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	-	-	-	-
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	-	-	-	-
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	-	-	-	-
910925870773	LL512X LED31S/830 DIA WB 7 WH HE	No	-	-	-
910925870775	LL512X LED31S/840 DEIA WB-OC 13 WH HE	-	DC operated central emergency lighting	-	-
910925870777	LL512X LED50S/840 DIA DA35W 7 WH HE	No	-	-	-
910925870779	LL512X LED80S/840 DIA WB 7 WH HE	No	-	-	-
910925870801	LL512X LED50S/840 PSD WB 7 BK HE	-	-	-	-
910925870804	LL512X LED50S/840 PSD WB 7 WH HE	-	DC operated central emergency lighting	-	-
910925870806	LL512X LED31S/840 PSD DA35W 7 WH HE	-	-	-	-
910925870807	LL512X LED31S/840 PSD WB 7 BK HE	-	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Power consumption during Central DC emergency mode
910925870808	LL512X LED61S/840 PSD WB 7 BK HE	-	-	-	-
91092587810	LL523X LED123S/830 PSD WB 7 WH XA	-	-	-	-
91092587811	LL523X LED160S/830 PSD MB 7 WH XA	-	-	-	-
91092587812	LL523X LED123S/830 PSD DA45W 7 WH XA	-	-	-	-
91092587813	LL523X LED123S/840 PSD DA45W 7 WH XA	-	-	-	-
91092587814	LL523X LED160S/830 PSD WB 7 WH XA	-	-	-	-
91092587815	LL523X LED160S/830 PSD NB 7 WH XA	-	-	-	-
91092587816	LL523X LED123S/840 PSD WB 7 WH XA	-	-	-	-
91092587818	LL523X LED123S/840 PSD MB 7 VLC WH XA	-	-	-	-
91092587819	LL523X LED123S/840 PSD WB 7 VLC WH XA	-	-	-	-
91092587820	LL523X LED160S/840 PSD MB 7 WH XA	-	-	-	-
91092587825	LL523X LED123S/840	Yes	DC operated central	-	-

					Power consumption during Central DC emergency mode
Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	
910925867826	PSED NB 13	Yes	emergency	-	-
	VLC WH XA		lighting		
	LL523X		DC		
	LED123S/840		operated		
	PSED MB 13		central		
910925867827	VLC WH XA	Yes	emergency	-	-
	LL523X		lighting		
	LED123S/840		operated		
	PSED WB 13		central		
	VLC WH XA		emergency		
910925867828	LL523X	Yes	lighting	-	-
	LED160S/840		operated		
	PSED NB 13		central		
	WH XA		emergency		
	LL523X		lighting		
910925867837	LED123S/840	-	operated	-	-
	PSD MB 7 VLC		central		
	WH XA		emergency		
	LL523X		lighting		
	LED123S/840		operated		
910925867838	PSD WB 7 VLC	-	central	-	-
	WH XA		emergency		
	LL523X		lighting		
	LED123S/840		operated		
	PSD MB 7 WH XA		central		
910925867839	LL523X	-	emergency	-	-
	LED160S/840		lighting		
	PSD MB 7 WH XA		operated		
	LL523X		central		
	LED123S/840		emergency		
910925867854	PSD NB 7 VLC	-	lighting	-	-
	WH XA		operated		
	LL523X		central		
	LED123S/840		emergency		
	PSD NB 7 VLC		lighting		
910925867855	WH XA	-	operated	-	-
	LL523X		central		
	LED160S/840		emergency		
	PSD NB 7 WH XA		lighting		
	LED123S/840		operated		
910925868127	PSED WB-OC 13 WH XA	Yes	central	-	-
	LL523X		emergency		
	LED62S/840		lighting		
	PSED WB-OC 13 WH XA		operated		
	LL523X		central		
910925868130	LED62S/840	No	emergency	-	-
	PSD WB-OC 13		lighting 3		
	ELP3 WH X		hours		
			duration		
			Pro version		

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Power consumption during Central DC emergency mode
910925868138	LL523X	-	-	-	-
	LED62S/840		operated		
	PSD WB-OC 7		central		
	WH XA		emergency		
	LL523X		lighting		
910925868949	LED62S/840	-	operated	-	-
	PSD MB 7 WH		central		
	HE		emergency		
	LL523X		lighting		
	LED62S/840		operated		
910925868950	PSD WB 7 WH	-	central	-	-
	HE		emergency		
	LL523X		lighting		
	LED62S/840		operated		
	PSD WB 7 WH		central		
910925868951	HE	-	emergency	-	-
	LL523X		lighting		
	LED100S/840		operated		
	PSD MB 7 WH		central		
	HE		emergency		
910925868952	LL523X	-	lighting	-	-
	LED100S/840		operated		
	PSD WB 7 WH		central		
	HE		emergency		
	LL523X		lighting		
910925868953	LED123S/840	-	operated	-	-
	PSD NB 7 WH		central		
	HE		emergency		
	LL523X		lighting		
	LED123S/840		operated		
910925868954	PSD MB 7 WH	-	central	-	-
	HE		emergency		
	LL523X		lighting		
	LED123S/840		operated		
	PSD MB 7 WH		central		
910925868955	HE	-	emergency	-	-
	LL523X		lighting		
	LED123S/840		operated		
	PSD WB 7 WH		central		
	HE		emergency		
910925868956	LL523X	-	lighting	-	-
	LED160S/840		operated		
	PSD NB 7 WH		central		
	HE		emergency		
	LL523X		lighting		
910925868957	LED160S/840	-	operated	-	-
	PSD MB 7 WH		central		
	HE		emergency		
	LL523X		lighting		
	LED100S/840		operated		
910925868967	SIA MB 7 WH	-	central	-	-
	HE		emergency		
	LL523X		lighting		
	LED100S/840		operated		
	PSD WB 7 WH		central		
910925868968	HE	-	emergency	-	-
	LL523X		lighting		
	LED100S/840		operated		
	PSD WB 7 WH		central		
	HE		emergency		

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Power consumption during Central DC emergency mode
	SIA WB 7 WH HE				
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	-	-	-	-
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	-	-	-	-
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	-	-	-	-
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	-	-	-	-
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	-	-	-	-
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	-	-	-	-
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	-	-	-	-
910925870371	LL523X LED62S/840 DIA MB 7 WH HE	No	-	-	-
910925870372	LL523X LED62S/840 DIA WB 7 WH HE	No	-	-	-
910925870373	LL523X LED100S/840 DIA MB 7 WH HE	No	-	-	-
910925870374	LL523X LED123S/840 DIA MB 7 WH HE	No	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Power consumption during Central DC emergency mode
910925870375	LL523X LED100S/840 DIA WB 7 WH HE	No	-	-	-
910925870376	LL523X LED123S/840 DIA NB 7 WH HE	No	-	-	-
910925870377	LL523X LED123S/840 DIA WB 7 WH HE	No	-	-	-
910925870378	LL523X LED160S/840 DIA NB 7 WH HE	No	-	-	-
910925870379	LL523X LED160S/840 DIA MB 7 WH HE	No	-	-	-
910925870380	LL512X LED31S/840 DIA MB 7 WH HE	No	-	-	-
910925870381	LL512X LED31S/840 DIA WB 7 WH HE	No	-	-	-
910925870382	LL512X LED50S/840 DIA MB 7 WH HE	No	-	-	-
910925870383		No	-	-	-
910925870384	LL512X LED61S/840 DIA NB 7 WH HE	No	-	-	-
910925870385	LL512X LED61S/840 DIA MB 7 WH HE	No	-	-	-
910925870386	LL512X LED61S/840 DIA WB 7 WH HE	No	-	-	-
910925870387	LL512X LED80S/840	No	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Power consumption during Central DC emergency mode
	DIA NB 7 WH HE				
910925870388	LL512X LED80S/840 DIA MB 7 WH HE	No	-	-	-
910925870756	LL523X LED62S/840 DEIA WB-OC 13 WH HE	-	DC operated central emergency lighting	-	-
910925870758	LL523X LED62S/840 DIA DA25N 7 WH HE	No	-	-	-
910925870759	LL523X LED62S/840 DIA DA25W 7 WH HE	No	-	-	-
910925870760	LL523X LED62S/840 DIA DA35W 7 WH HE	No	-	-	-
910925870761	LL523X LED100S/840 DIA NB 7 WH HE	No	-	-	-
910925870763	LL523X LED100S/840 DIA A20 7 WH HE	No	-	-	-
910925870764	LL523X LED100S/840 DIA DA35W 7 WH HE	No	-	-	-
910925870766	LL523X LED123S/840 DIA A20 7 WH HE	No	-	-	-
910925870767	LL523X LED123S/840 DIA DA25W 7 WH HE	No	-	-	-
910925870768	LL523X LED123S/840 DIA DA35W 7 WH HE	No	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Power consumption during Central DC emergency mode
910925870769	LL523X LED160S/840 DIA WB 7 WH HE	No	-	-	-
910925870796	LL523X LED123S/840 PSD A20 7 WH HE	-	-	-	-
910925870797	LL523X LED160S/840 PSD XNB 7 WH HE	-	-	-	-
910925870798	LL523X LED100S/840 PSD WB 7 SI HE	-	-	-	-
910925870799	LL523X LED123S/840 PSD WB 7 BK HE	-	-	-	-
910925870802	LL523X LED62S/840 PSD WB 7 SI HE	-	-	-	-
910925870809	LL523X LED100S/840 PSD DA35W 7 WH HE	-	-	-	-
910925870810	LL523X LED100S/840 PSD WB 7 BK HE	-	-	-	-
910925870811	LL523X LED123S/840 PSD DA35W 7 WH HE	-	-	-	-
910925870812	LL523X LED62S/840 PSD DA35W 7 WH HE	-	-	-	-
910925870819	LL523X LED123S/840 DIA WB 13 ELP3 WH HE	No	Emergency lighting 3 hours duration Pro version	600 lm	3.7 W
910925870780	LL612X LED61S/840	No	-	-	-

					Power consumption during Central DC emergency mode
Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	emergency mode
910925870794	DIA WB 7 WH HE				
	LL612X LED61S/840 DIA MB 7 WH HE	No	-	-	-
910925870795	DIA NB 7 WH HE				
	LL612X LED61S/840 DIA NB 7 WH HE	No	-	-	-
910925870803	PSD NB 7 WH HE				
	LL612X LED61S/840 PSD NB 7 WH HE	-	-	-	-
910925870770	DIA MB 7 WH HE				
	LL623X LED123S/840 DIA MB 7 WH HE	No	-	-	-
910925870771	DIA WB 7 WH HE				
	LL623X LED123S/840 DIA WB 7 WH HE	No	-	-	-
910925870772	LED123S/840				
	LL623X LED123S/840	No	-	-	-

Emergency Operation (2/2)

			Rated duration of the emergency lighting (when fully charged)
Order Code	Full Product Name		
910925870051	LL512X LED61S/840 PSD O-PC 7 VLC WH XA	-	
910925870052	LL523X LED123S/840 PSD O-PC 7 VLC WH XA	-	
910925870055	LL523X LED123S/840 SIA O-PC 7 WH HE	-	
910925870056	LL523X LED100S/840 SIA O-PC 7 WH HE	-	
910925870057	LL523X LED62S/840 SIA O-PC 7 WH HE	-	
910925870058	LL512X LED61S/840 SIA O-PC 7 WH HE	-	
910925870059	LL512X LED31S/840 SIA O-PC 7 WH HE	-	
910925870061	LL523X LED62S/840 DIA O-PC 7 WH HE	-	
910925870062	LL523X LED62S/840 DIA O-PC 13 ELP3 WH HE	-	
910925870063	LL523X LED100S/840 DIA O-PC 7 WH HE	-	
910925870064	LL523X LED123S/840 DIA O-PC 7 WH HE	-	
910925870065	LL512X LED31S/840 DIA O-PC 7 WH HE	-	
910925870066	LL512X LED50S/840 DIA O-PC 7 WH HE	-	
910925870067	LL512X LED61S/840 DIA O-PC 7 WH HE	-	
910925868124	LL512X LED31S/840 PSED WB-OC 13 BK XA	-	
910925868128	LL523X LED62S/840 PSED WB-OC 13 BK XA	-	

					Power consumption during Central DC emergency mode
Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	emergency mode
910925870805	DIA NB 7 WH HE				
	LL623X LED123S/840 PSD WB 7 WH HE	-	-	-	-
910925868648	WB 7 HE WH				
	LL515X 61S/840 PSD WB 7 HE WH	-	-	-	-
910925868649	80S/840 PSD WB 7 HE WH				
	LL515X 80S/840 PSD WB 7 HE WH	-	-	-	-
910925868650	MB 7 HE WH				
	LL515X 61S/840 PSD MB 7 HE WH	-	-	-	-
910925868651	80S/840 PSD MB 7 HE WH				
	LL515X 80S/840 PSD MB 7 HE WH	-	-	-	-
910925868652	NB 7 HE WH				
	LL515X 61S/840 PSD NB 7 HE WH	-	-	-	-
910925868653	NB 7 HE WH				
	LL515X 80S/840 PSD NB 7 HE WH	-	-	-	-

			Rated duration of the emergency lighting (when fully charged)
Order Code	Full Product Name		
910925868123	LL512X LED31S/840 PSED WB-OC 13 WH XA	-	
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	-	
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	-	
910925868959		-	
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	-	
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	-	
910925868962	LL512X LED61S/840 PSD NB 7 WH HE	-	
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	-	
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	-	
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	-	
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	-	
910925868978	LL512X LED50S/840 SIA MB 7 WH HE	-	
910925868979	LL512X LED50S/840 SIA WB 7 WH HE	-	
910925868980	LL512X LED61S/840 SIA NB 7 WH HE	-	
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	-	
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	-	

Order Code	Full Product Name	Rated duration of the emergency lighting (when fully charged)
910925868983	LL512X LED80S/840 SIA NB 7 WH HE	-
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	-
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	-
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	-
910925870773	LL512X LED31S/830 DIA WB 7 WH HE	-
910925870775	LL512X LED31S/840 DEIA WB-OC 13 WH HE	-
910925870777	LL512X LED50S/840 DIA DA35W 7 WH HE	-
910925870779	LL512X LED80S/840 DIA WB 7 WH HE	-
910925870801	LL512X LED50S/840 PSD WB 7 BK HE	-
910925870804	LL512X LED50S/840 PSED WB 7 WH HE	-
910925870806	LL512X LED31S/840 PSD DA35W 7 WH HE	-
910925870807	LL512X LED31S/840 PSD WB 7 BK HE	-
910925870808	LL512X LED61S/840 PSD WB 7 BK HE	-
910925867810	LL523X LED123S/830 PSD WB 7 WH XA	-
910925867811	LL523X LED160S/830 PSD MB 7 WH XA	-
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	-
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	-
910925867814	LL523X LED160S/830 PSD WB 7 WH XA	-
910925867815	LL523X LED160S/830 PSD NB 7 WH XA	-
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	-
910925867818	LL523X LED123S/840 PSD MB 7 VLC WH XA	-
910925867819	LL523X LED123S/840 PSD WB 7 VLC WH XA	-
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	-
910925867825	LL523X LED123S/840 PSED NB 13 VLC WH XA	-
910925867826	LL523X LED123S/840 PSED MB 13 VLC WH XA	-
910925867827	LL523X LED123S/840 PSED WB 13 VLC WH XA	-
910925867828	LL523X LED160S/840 PSED NB 13 WH XA	-
910925867837	LL523X LED123S/840 PSD MB 7 VLC WH XA	-
910925867838	LL523X LED123S/840 PSD WB 7 VLC WH XA	-
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	-
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	-
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	-
910925868127	LL523X LED62S/840 PSED WB-OC 13 WH XA	-
910925868130	LL523X LED62S/840 PSD WB-OC 13 ELP3 WH X	3 hour(s)
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	-
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	-
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	-
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	-
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	-
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	-
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	-
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	-
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	-
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	-
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	-
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	-
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	-
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	-
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	-

Order Code	Full Product Name	Rated duration of the emergency lighting (when fully charged)
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	-
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	-
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	-
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	-
910925870371	LL523X LED62S/840 DIA MB 7 WH HE	-
910925870372	LL523X LED62S/840 DIA WB 7 WH HE	-
910925870373	LL523X LED100S/840 DIA MB 7 WH HE	-
910925870374	LL523X LED123S/840 DIA MB 7 WH HE	-
910925870375	LL523X LED100S/840 DIA WB 7 WH HE	-
910925870376	LL523X LED123S/840 DIA NB 7 WH HE	-
910925870377	LL523X LED123S/840 DIA WB 7 WH HE	-
910925870378	LL523X LED160S/840 DIA NB 7 WH HE	-
910925870379	LL523X LED160S/840 DIA MB 7 WH HE	-
910925870380	LL512X LED31S/840 DIA MB 7 WH HE	-
910925870381	LL512X LED31S/840 DIA WB 7 WH HE	-
910925870382	LL512X LED50S/840 DIA MB 7 WH HE	-
910925870383		-
910925870384	LL512X LED61S/840 DIA NB 7 WH HE	-
910925870385	LL512X LED61S/840 DIA MB 7 WH HE	-
910925870386	LL512X LED61S/840 DIA WB 7 WH HE	-
910925870387	LL512X LED80S/840 DIA NB 7 WH HE	-
910925870388	LL512X LED80S/840 DIA MB 7 WH HE	-
910925870756	LL523X LED62S/840 DEIA WB-OC 13 WH HE	-
910925870758	LL523X LED62S/840 DIA DA25N 7 WH HE	-
910925870759	LL523X LED62S/840 DIA DA25W 7 WH HE	-
910925870760	LL523X LED62S/840 DIA DA35W 7 WH HE	-
910925870761	LL523X LED100S/840 DIA NB 7 WH HE	-
910925870763	LL523X LED100S/840 DIA A20 7 WH HE	-
910925870764	LL523X LED100S/840 DIA DA35W 7 WH HE	-
910925870766	LL523X LED123S/840 DIA A20 7 WH HE	-
910925870767	LL523X LED123S/840 DIA DA25W 7 WH HE	-
910925870768	LL523X LED123S/840 DIA DA35W 7 WH HE	-
910925870769	LL523X LED160S/840 DIA WB 7 WH HE	-
910925870796	LL523X LED123S/840 PSD A20 7 WH HE	-
910925870797	LL523X LED160S/840 PSD XNB 7 WH HE	-
910925870798	LL523X LED100S/840 PSD WB 7 SI HE	-
910925870799	LL523X LED123S/840 PSD WB 7 BK HE	-
910925870802	LL523X LED62S/840 PSD WB 7 SI HE	-
910925870809	LL523X LED100S/840 PSD DA35W 7 WH HE	-
910925870810	LL523X LED100S/840 PSD WB 7 BK HE	-
910925870811	LL523X LED123S/840 PSD DA35W 7 WH HE	-
910925870812	LL523X LED62S/840 PSD DA35W 7 WH HE	-
910925870819	LL523X LED123S/840 DIA WB 13 ELP3 WH HE	-
910925870780	LL612X LED61S/840 DIA WB 7 WH HE	-
910925870794	LL612X LED61S/840 DIA MB 7 WH HE	-
910925870795	LL612X LED61S/840 DIA NB 7 WH HE	-
910925870803	LL612X LED61S/840 PSD NB 7 WH HE	-
910925870770	LL623X LED123S/840 DIA MB 7 WH HE	-
910925870771	LL623X LED123S/840 DIA WB 7 WH HE	-

Order Code	Full Product Name	Rated duration of the emergency lighting (when fully charged)
910925870772	LL623X LED123S/840 DIA NB 7 WH HE	-
910925870805	LL623X LED123S/840 PSD WB 7 WH HE	-
910925868648	LL515X 61S/840 PSD WB 7 HE WH	-
910925868649	LL515X 80S/840 PSD WB 7 HE WH	-

Order Code	Full Product Name	Rated duration of the emergency lighting (when fully charged)
910925868650	LL515X 61S/840 PSD MB 7 HE WH	-
910925868651	LL515X 80S/840 PSD MB 7 HE WH	-
910925868652	LL515X 61S/840 PSD NB 7 HE WH	-
910925868653	LL515X 80S/840 PSD NB 7 HE WH	-

Approval and Application

Order Code	Full Product Name	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910925870051	LL512X LED61S/840 PSD O-PC 7 VLC WH XA	For mounting on normally flammable surfaces	-	-
910925870052	LL523X LED123S/840 PSD O-PC 7 VLC WH XA	For mounting on normally flammable surfaces	-	-
910925870055	LL523X LED123S/840 SIA O-PC 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870056	LL523X LED100S/840 SIA O-PC 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870057	LL523X LED62S/840 SIA O-PC 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870058	LL512X LED61S/840 SIA O-PC 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870059	LL512X LED31S/840 SIA O-PC 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870061	LL523X LED62S/840 DIA O-PC 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870062	LL523X LED62S/840 DIA O-PC 13 ELP3 WH HE	For mounting on normally flammable surfaces	-	-
910925870063	LL523X LED100S/840 DIA O-PC 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870064	LL523X LED123S/840 DIA O-PC 7 WH HE	For mounting on normally flammable surfaces	-	-

Order Code	Full Product Name	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910925870065	LL512X LED31S/840 DIA O-PC 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870066	LL512X LED50S/840 DIA O-PC 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870067	LL512X LED61S/840 DIA O-PC 7 WH HE	For mounting on normally flammable surfaces	-	-
910925868124	LL512X LED31S/840 PSED WB-OC 13 BK XA	For mounting on normally flammable surfaces	1	0.4
910925868128	LL523X LED62S/840 PSED WB-OC 13 BK XA	For mounting on normally flammable surfaces	1	0.4
910925868123	LL512X LED31S/840 PSED WB-OC 13 WH XA	For mounting on normally flammable surfaces	1	0.4
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	For mounting on normally flammable surfaces	1	0.4
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868959	LL512X LED50S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces	1	0.4

Order Code	Full Product Name	Flammability mark	Flickering value (PstLM) - Flickering value as per EN	Stroboscopic effect visibility measure (SVM)
			61000-3-3	
910925868962	LL512X LED61S/840 PSD NB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868978	LL512X LED50S/840 SIA MB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868979	LL512X LED50S/840 SIA WB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868980	LL512X LED61S/840 SIA NB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868983	LL512X LED80S/840 SIA NB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925870773	LL512X LED31S/830 DIA WB 7 WH HE	For mounting on normally flammable surfaces	-	-

Order Code	Full Product Name	Flammability mark	Flickering value (PstLM) - Flickering value as per EN	Stroboscopic effect visibility measure (SVM)
			61000-3-3	
910925870775	LL512X LED31S/840 DEIA WB-OC 13 WH HE	For mounting on normally flammable surfaces	-	-
910925870777	LL512X LED50S/840 DIA DA35W 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870779	LL512X LED80S/840 DIA WB 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870801	LL512X LED50S/840 PSD WB 7 BK HE	For mounting on normally flammable surfaces	-	-
910925870804	LL512X LED50S/840 PSED WB 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870806	LL512X LED31S/840 PSD DA35W 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870807	LL512X LED31S/840 PSD WB 7 BK HE	For mounting on normally flammable surfaces	-	-
910925870808	LL512X LED61S/840 PSD WB 7 BK HE	For mounting on normally flammable surfaces	-	-
910925867810	LL523X LED123S/830 PSD WB 7 WH XA	For mounting on normally flammable surfaces	1	0.4
910925867811	LL523X LED160S/830 PSD MB 7 WH XA	For mounting on normally flammable surfaces	1	0.4
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	For mounting on normally flammable surfaces	1	0.4
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	For mounting on normally flammable surfaces	1	0.4
910925867814	LL523X LED160S/830 PSD WB 7 WH XA	For mounting on normally flammable surfaces	1	0.4
910925867815	LL523X LED160S/830 PSD NB 7 WH XA	For mounting on normally flammable surfaces	1	0.4
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	For mounting on normally flammable surfaces	1	0.4

Order Code	Full Product Name	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910925867818	LL523X LED123S/840 PSD MB 7 VLC WH XA	For mounting on normally flammable surfaces	1	0.4
910925867819	LL523X LED123S/840 PSD WB 7 VLC WH XA	For mounting on normally flammable surfaces	1	0.4
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	For mounting on normally flammable surfaces	1	0.4
910925867825	LL523X LED123S/840 PSED NB 13 VLC WH XA	For mounting on normally flammable surfaces	1	0.4
910925867826	LL523X LED123S/840 PSED MB 13 VLC WH XA	For mounting on normally flammable surfaces	1	0.4
910925867827	LL523X LED123S/840 PSED WB 13 VLC WH XA	For mounting on normally flammable surfaces	1	0.4
910925867828	LL523X LED160S/840 PSED NB 13 WH XA	For mounting on normally flammable surfaces	1	0.4
910925867837	LL523X LED123S/840 PSD MB 7 VLC WH XA	For mounting on normally flammable surfaces	1	0.4
910925867838	LL523X LED123S/840 PSD WB 7 VLC WH XA	For mounting on normally flammable surfaces	1	0.4
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	For mounting on normally flammable surfaces	1	0.4
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	For mounting on normally flammable surfaces	1	0.4
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	For mounting on normally flammable surfaces	1	0.4
910925868127	LL523X LED62S/840 PSED WB-OC 13 WH XA	For mounting on normally flammable surfaces	1	0.4
910925868130	LL523X LED62S/840 PSD WB-OC 13 ELP3 WH X	For mounting on normally flammable surfaces	1	0.4

Order Code	Full Product Name	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	For mounting on normally flammable surfaces	1	0.4
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	For mounting on normally flammable surfaces	1	0.4

Order Code	Full Product Name	Flammability mark	Flickering value (PstLM) - Flickering value as per EN	Stroboscopic effect visibility measure (SVM)
			61000-3-3	
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces	1	0.4
910925870371	LL523X LED62S/840 DIA MB 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870372	LL523X LED62S/840 DIA WB 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870373	LL523X LED100S/840 DIA MB 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870374	LL523X LED123S/840 DIA MB 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870375	LL523X LED100S/840 DIA WB 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870376	LL523X LED123S/840 DIA NB 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870377	LL523X LED123S/840 DIA WB 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870378	LL523X LED160S/840 DIA NB 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870379	LL523X LED160S/840 DIA MB 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870380	LL512X LED31S/840 DIA MB 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870381	LL512X LED31S/840 DIA WB 7 WH HE	For mounting on normally flammable surfaces	-	-

Order Code	Full Product Name	Flammability mark	Flickering value (PstLM) - Flickering value as per EN	Stroboscopic effect visibility measure (SVM)
			61000-3-3	
910925870382	LL512X LED50S/840 DIA MB 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870383		For mounting on normally flammable surfaces	-	-
910925870384	LL512X LED61S/840 DIA NB 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870385	LL512X LED61S/840 DIA MB 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870386	LL512X LED61S/840 DIA WB 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870387	LL512X LED80S/840 DIA NB 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870388	LL512X LED80S/840 DIA MB 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870756	LL523X LED62S/840 DEIA WB-OC 13 WH HE	For mounting on normally flammable surfaces	-	-
910925870758	LL523X LED62S/840 DIA DA25N 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870759	LL523X LED62S/840 DIA DA25W 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870760	LL523X LED62S/840 DIA DA35W 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870761	LL523X LED100S/840 DIA NB 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870763	LL523X LED100S/840 DIA A20 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870764	LL523X LED100S/840 DIA DA35W 7 WH HE	For mounting on normally flammable surfaces	-	-
910925870766	LL523X LED123S/840 DIA A20 7 WH HE	For mounting on normally flammable surfaces	-	-

Order Code	Full Product Name	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3		Stroboscopic effect visibility measure (SVM)
910925870767	LL523X	For mounting on	-	-	
	LED123S/840 DIA	normally flammable			
	DA25W 7 WH HE	surfaces			
910925870768	LL523X	For mounting on	-	-	
	LED123S/840 DIA	normally flammable			
	DA35W 7 WH HE	surfaces			
910925870769	LL523X	For mounting on	-	-	
	LED160S/840 DIA	normally flammable			
	WB 7 WH HE	surfaces			
910925870796	LL523X	For mounting on	-	-	
	LED123S/840 PSD	normally flammable			
	A20 7 WH HE	surfaces			
910925870797	LL523X	For mounting on	-	-	
	LED160S/840 PSD	normally flammable			
	XNB 7 WH HE	surfaces			
910925870798	LL523X	For mounting on	-	-	
	LED100S/840 PSD	normally flammable			
	WB 7 SI HE	surfaces			
910925870799	LL523X	For mounting on	-	-	
	LED123S/840 PSD	normally flammable			
	WB 7 BK HE	surfaces			
910925870802	LL523X	For mounting on	-	-	
	LED62S/840 PSD	normally flammable			
	WB 7 SI HE	surfaces			
910925870809	LL523X	For mounting on	-	-	
	LED100S/840 PSD	normally flammable			
	DA35W 7 WH HE	surfaces			
910925870810	LL523X	For mounting on	-	-	
	LED100S/840 PSD	normally flammable			
	WB 7 BK HE	surfaces			
910925870811	LL523X	For mounting on	-	-	
	LED123S/840 PSD	normally flammable			
	DA35W 7 WH HE	surfaces			
910925870812	LL523X	For mounting on	-	-	
	LED62S/840 PSD	normally flammable			
	DA35W 7 WH HE	surfaces			
910925870819	LL523X	For mounting on	1	0.4	
	LED123S/840 DIA	normally flammable			
	WB 13 ELP3 WH HE	surfaces			
910925870780	LL612X	For mounting on	-	-	
	LED61S/840 DIA	easily flammable			
	WB 7 WH HE	surfaces			

Order Code	Full Product Name	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3		Stroboscopic effect visibility measure (SVM)
910925870794	LL612X	For mounting on	-	-	
	LED61S/840 DIA	easily flammable			
	MB 7 WH HE	surfaces			
910925870795	LL612X	For mounting on	-	-	
	LED61S/840 DIA	easily flammable			
	NB 7 WH HE	surfaces			
910925870803	LL612X	For mounting on	-	-	
	LED61S/840 PSD	easily flammable			
	NB 7 WH HE	surfaces			
910925870770	LL623X	For mounting on	-	-	
	LED123S/840 DIA	easily flammable			
	MB 7 WH HE	surfaces			
910925870771	LL623X	For mounting on	-	-	
	LED123S/840 DIA	easily flammable			
	WB 7 WH HE	surfaces			
910925870772	LL623X	For mounting on	-	-	
	LED123S/840 DIA	easily flammable			
	NB 7 WH HE	surfaces			
910925870805	LL623X	For mounting on	-	-	
	LED123S/840 PSD	easily flammable			
	WB 7 WH HE	surfaces			
910925868648	LL515X 61S/840	For mounting on	1	0.4	
	PSD WB 7 HE WH	normally flammable			
	surfaces				
910925868649	LL515X 80S/840	For mounting on	1	0.4	
	PSD WB 7 HE WH	normally flammable			
	surfaces				
910925868650	LL515X 61S/840	For mounting on	1	0.4	
	PSD MB 7 HE WH	normally flammable			
	surfaces				
910925868651	LL515X 80S/840	For mounting on	1	0.4	
	PSD MB 7 HE WH	normally flammable			
	surfaces				
910925868652	LL515X 61S/840	For mounting on	1	0.4	
	PSD NB 7 HE WH	normally flammable			
	surfaces				
910925868653	LL515X 80S/840	For mounting on	1	0.4	
	PSD NB 7 HE WH	normally flammable			
	surfaces				

Product Data




Order Code	Full Product Name	Product family code
910925870051	LL512X LED61S/840 PSD O-PC 7 VLC WH XA	LL512X
910925870052	LL523X LED123S/840 PSD O-PC 7 VLC WH XA	LL523X
910925870055	LL523X LED123S/840 SIA O-PC 7 WH HE	LL523X
910925870056	LL523X LED100S/840 SIA O-PC 7 WH HE	LL523X
910925870057	LL523X LED62S/840 SIA O-PC 7 WH HE	LL523X
910925870058	LL512X LED61S/840 SIA O-PC 7 WH HE	LL512X
910925870059	LL512X LED31S/840 SIA O-PC 7 WH HE	LL512X
910925870061	LL523X LED62S/840 DIA O-PC 7 WH HE	LL523X
910925870062	LL523X LED62S/840 DIA O-PC 13 ELP3 WH HE	LL523X
910925870063	LL523X LED100S/840 DIA O-PC 7 WH HE	LL523X
910925870064	LL523X LED123S/840 DIA O-PC 7 WH HE	LL523X
910925870065	LL512X LED31S/840 DIA O-PC 7 WH HE	LL512X
910925870066	LL512X LED50S/840 DIA O-PC 7 WH HE	LL512X
910925870067	LL512X LED61S/840 DIA O-PC 7 WH HE	LL512X
910925868124	LL512X LED31S/840 PSED WB-OC 13 BK XA	LL512X
910925868128	LL523X LED62S/840 PSED WB-OC 13 BK XA	LL523X
910925868123	LL512X LED31S/840 PSED WB-OC 13 WH XA	LL512X
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	LL512X
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	LL512X
910925868959		LL512X
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	LL512X
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	LL512X
910925868962	LL512X LED61S/840 PSD NB 7 WH HE	LL512X
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	LL512X
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	LL512X
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	LL512X
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	LL512X
910925868978	LL512X LED50S/840 SIA MB 7 WH HE	LL512X
910925868979	LL512X LED50S/840 SIA WB 7 WH HE	LL512X
910925868980	LL512X LED61S/840 SIA NB 7 WH HE	LL512X
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	LL512X
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	LL512X
910925868983	LL512X LED80S/840 SIA NB 7 WH HE	LL512X
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	LL512X
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	LL512X
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	LL512X
910925870773	LL512X LED31S/830 DIA WB 7 WH HE	LL512X
910925870775	LL512X LED31S/840 DEIA WB-OC 13 WH HE	LL512X
910925870777	LL512X LED50S/840 DIA DA35W 7 WH HE	LL512X
910925870779	LL512X LED80S/840 DIA WB 7 WH HE	LL512X
910925870801	LL512X LED50S/840 PSD WB 7 BK HE	LL512X
910925870804	LL512X LED50S/840 PSED WB 7 WH HE	LL512X
910925870806	LL512X LED31S/840 PSD DA35W 7 WH HE	LL512X
910925870807	LL512X LED31S/840 PSD WB 7 BK HE	LL512X
910925870808	LL512X LED61S/840 PSD WB 7 BK HE	LL512X
910925867810	LL523X LED123S/830 PSD WB 7 WH XA	LL523X
910925867811	LL523X LED160S/830 PSD MB 7 WH XA	LL523X
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	LL523X
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	LL523X
910925867814	LL523X LED160S/830 PSD WB 7 WH XA	LL523X
910925867815	LL523X LED160S/830 PSD NB 7 WH XA	LL523X
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	LL523X

Order Code	Full Product Name	Product family code
910925867818	LL523X LED123S/840 PSD MB 7 VLC WH XA	LL523X
910925867819	LL523X LED123S/840 PSD WB 7 VLC WH XA	LL523X
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	LL523X
910925867825	LL523X LED123S/840 PSED NB 13 VLC WH XA	LL523X
910925867826	LL523X LED123S/840 PSED MB 13 VLC WH XA	LL523X
910925867827	LL523X LED123S/840 PSED WB 13 VLC WH XA	LL523X
910925867828	LL523X LED160S/840 PSED NB 13 WH XA	LL523X
910925867837	LL523X LED123S/840 PSD MB 7 VLC WH XA	LL523X
910925867838	LL523X LED123S/840 PSD WB 7 VLC WH XA	LL523X
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	LL523X
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	LL523X
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	LL523X
910925868127	LL523X LED62S/840 PSED WB-OC 13 WH XA	LL523X
910925868130	LL523X LED62S/840 PSD WB-OC 13 ELP3 WH X	LL523X
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	LL523X
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	LL523X
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	LL523X
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	LL523X
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	LL523X
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	LL523X
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	LL523X
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	LL523X
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	LL523X
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	LL523X
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	LL523X
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	LL523X
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	LL523X
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	LL523X
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	LL523X
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	LL523X
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	LL523X
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	LL523X
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	LL523X
910925870371	LL523X LED62S/840 DIA MB 7 WH HE	LL523X
910925870372	LL523X LED62S/840 DIA WB 7 WH HE	LL523X
910925870373	LL523X LED100S/840 DIA MB 7 WH HE	LL523X
910925870374	LL523X LED123S/840 DIA MB 7 WH HE	LL523X
910925870375	LL523X LED100S/840 DIA WB 7 WH HE	LL523X
910925870376	LL523X LED123S/840 DIA NB 7 WH HE	LL523X
910925870377	LL523X LED123S/840 DIA WB 7 WH HE	LL523X
910925870378	LL523X LED160S/840 DIA NB 7 WH HE	LL523X
910925870379	LL523X LED160S/840 DIA MB 7 WH HE	LL523X
910925870380	LL512X LED31S/840 DIA MB 7 WH HE	LL512X
910925870381	LL512X LED31S/840 DIA WB 7 WH HE	LL512X
910925870382	LL512X LED50S/840 DIA MB 7 WH HE	LL512X
910925870383		LL512X
910925870384	LL512X LED61S/840 DIA NB 7 WH HE	LL512X
910925870385	LL512X LED61S/840 DIA MB 7 WH HE	LL512X
910925870386	LL512X LED61S/840 DIA WB 7 WH HE	LL512X
910925870387	LL512X LED80S/840 DIA NB 7 WH HE	LL512X
910925870388	LL512X LED80S/840 DIA MB 7 WH HE	LL512X
910925870756	LL523X LED62S/840 DEIA WB-OC 13 WH HE	LL523X

Order Code	Full Product Name	Product family code
910925870758	LL523X LED62S/840 DIA DA25N 7 WH HE	LL523X
910925870759	LL523X LED62S/840 DIA DA25W 7 WH HE	LL523X
910925870760	LL523X LED62S/840 DIA DA35W 7 WH HE	LL523X
910925870761	LL523X LED100S/840 DIA NB 7 WH HE	LL523X
910925870763	LL523X LED100S/840 DIA A20 7 WH HE	LL523X
910925870764	LL523X LED100S/840 DIA DA35W 7 WH HE	LL523X
910925870766	LL523X LED123S/840 DIA A20 7 WH HE	LL523X
910925870767	LL523X LED123S/840 DIA DA25W 7 WH HE	LL523X
910925870768	LL523X LED123S/840 DIA DA35W 7 WH HE	LL523X
910925870769	LL523X LED160S/840 DIA WB 7 WH HE	LL523X
910925870796	LL523X LED123S/840 PSD A20 7 WH HE	LL523X
910925870797	LL523X LED160S/840 PSD XNB 7 WH HE	LL523X
910925870798	LL523X LED100S/840 PSD WB 7 SI HE	LL523X
910925870799	LL523X LED123S/840 PSD WB 7 BK HE	LL523X
910925870802	LL523X LED62S/840 PSD WB 7 SI HE	LL523X
910925870809	LL523X LED100S/840 PSD DA35W 7 WH HE	LL523X
910925870810	LL523X LED100S/840 PSD WB 7 BK HE	LL523X

Order Code	Full Product Name	Product family code
910925870811	LL523X LED123S/840 PSD DA35W 7 WH HE	LL523X
910925870812	LL523X LED62S/840 PSD DA35W 7 WH HE	LL523X
910925870819	LL523X LED123S/840 DIA WB 13 ELP3 WH HE	LL523X
910925870780	LL612X LED61S/840 DIA WB 7 WH HE	LL612X
910925870794	LL612X LED61S/840 DIA MB 7 WH HE	LL612X
910925870795	LL612X LED61S/840 DIA NB 7 WH HE	LL612X
910925870803	LL612X LED61S/840 PSD NB 7 WH HE	LL612X
910925870770	LL623X LED123S/840 DIA MB 7 WH HE	LL623X
910925870771	LL623X LED123S/840 DIA WB 7 WH HE	LL623X
910925870772	LL623X LED123S/840 DIA NB 7 WH HE	LL623X
910925870805	LL623X LED123S/840 PSD WB 7 WH HE	LL623X
910925868648	LL515X 61S/840 PSD WB 7 HE WH	LL515X
910925868649	LL515X 80S/840 PSD WB 7 HE WH	LL515X
910925868650	LL515X 61S/840 PSD MB 7 HE WH	LL515X
910925868651	LL515X 80S/840 PSD MB 7 HE WH	LL515X
910925868652	LL515X 61S/840 PSD NB 7 HE WH	LL515X
910925868653	LL515X 80S/840 PSD NB 7 HE WH	LL515X




Polar Wide Diagrams



Polar Normal (separate) - LL500XI - 910925868953

Polar Normal (separate) - LL500XI - 910925868956

Polar Normal (separate) - LL500XI - 910925868950




Polar Normal (separate) - LL500XI - 910925868970


Polar Normal (separate) - LL500XI - 910925868955

Polar Normal (separate) - LL500XI - 910925869742


Polar Wide Diagrams




Polar Normal (separate) - LL500XI - 910925868972




Polar Normal (separate) - LL500XI - 910925868973




Polar Normal (separate) - LL500XI - 910925867816




Polar Normal (separate) - LL500XI - 910925867820




Polar Normal (separate) - LL500XI - 910925867855




Polar Normal (separate) - LL500XI - 910925867838



Polar Normal (separate) - LL500XI - 910925867810




Polar Normal (separate) - LL500XI - 910925868139




Polar Normal (separate) - LL500XI - 910925868138


Polar Wide Diagrams




Polar Normal (separate) - LL500XI - 910925868952




Polar Normal (separate) - LL500XI - 910925868954




Polar Normal (separate) - LL500XI - 910925868959




Polar Normal (separate) - LL500XI - 910925868957




Polar Normal (separate) - LL500XI - 910925868961




Polar Normal (separate) - LL500XI - 910925868969



Polar Normal (separate) - LL500XI - 910925868971




Polar Normal (separate) - LL500XI - 910925869743




Polar Normal (separate) - LL500XI - 910925867814


Polar Wide Diagrams




Polar Normal (separate) - LL500XI - 910925867811




Polar Normal (separate) - LL500XI - 910925867815




Polar Normal (separate) - LL500XI - 910925867819




Polar Normal (separate) - LL500XI - 910925867825




Polar Normal (separate) - LL500XI - 910925867826




Polar Normal (separate) - LL500XI - 910925867827



Polar Normal (separate) - LL500XI - 910925867828




Polar Normal (separate) - LL500XI - 910925868949




Polar Normal (separate) - LL500XI - 910925868951


Polar Wide Diagrams




Polar Normal (separate) - LL500XI - 910925868958




Polar Normal (separate) - LL500XI - 910925868960




Polar Normal (separate) - LL500XI - 910925868962




Polar Normal (separate) - LL500XI - 910925868964




Polar Normal (separate) - LL500XI - 910925868963




Polar Normal (separate) - LL500XI - 910925868966



Polar Normal (separate) - LL500XI - 910925868967




Polar Normal (separate) - LL500XI - 910925868965




Polar Normal (separate) - LL500XI - 910925868968


Polar Wide Diagrams




Polar Normal (separate) - LL500XI - 910925868974




Polar Normal (separate) - LL500XI - 910925868978




Polar Normal (separate) - LL500XI - 910925868979




Polar Normal (separate) - LL500XI - 910925868980




Polar Normal (separate) - LL500XI - 910925868984




Polar Normal (separate) - LL500XI - 910925868981



Polar Normal (separate) - LL500XI - 910925868982




Polar Normal (separate) - LL500XI - 910925868986




Polar Normal (separate) - LL500XI - 910925868983


Polar Wide Diagrams




Polar Normal (separate) - LL500XI - 910925867812




Polar Normal (separate) - LL500XI - 910925867813




Polar Normal (separate) - LL500XI - 910925867818




Polar Normal (separate) - LL500XI - 910925867837




Polar Normal (separate) - LL500XI - 910925867839




Polar Normal (separate) - LL500XI - 910925867854



Polar Normal (separate) - LL500XI - 910925868123




Polar Normal (separate) - LL500XI - 910925868124




Polar Normal (separate) - LL500XI - 910925868127


Polar Wide Diagrams




Polar Normal (separate) - LL500XI - 910925868128




Polar Normal (separate) - LL500XI - 910925868130




Polar Normal (separate) - LL500XI - 910925870375




Polar Normal (separate) - LL500XI - 910925870372




Polar Normal (separate) - LL500XI - 910925870384




Polar Normal (separate) - LL500XI - 910925870373



Polar Normal (separate) - LL500XI - 910925870371




Polar Normal (separate) - LL500XI - 910925870383




Polar Normal (separate) - LL500XI - 910925870388


Polar Wide Diagrams




Polar Normal (separate) - LL500XI - 910925870387




Polar Normal (separate) - LL500XI - 910925870377




Polar Normal (separate) - LL500XI - 910925870374




Polar Normal (separate) - LL500XI - 910925870381




Polar Normal (separate) - LL500XI - 910925870385




Polar Normal (separate) - LL500XI - 910925870378



Polar Normal (separate) - LL500XI - 910925870382




Polar Normal (separate) - LL500XI - 910925870380




Polar Normal (separate) - LL500XI - 910925870379


Polar Wide Diagrams




Polar Normal (separate) - LL500XI - 910925870376




Polar Normal (separate) - LL500XI - 910925870386




Polar Normal (separate) - LL500XI - 910925870768




Polar Normal (separate) - LL500XI - 910925870780




Polar Normal (separate) - LL500XI - 910925870773




Polar Normal (separate) - LL500XI - 910925870767



Polar Normal (separate) - LL500XI - 910925870772




Polar Normal (separate) - LL500XI - 910925870770




Polar Normal (separate) - LL500XI - 910925870769


Polar Wide Diagrams




Polar Normal (separate) - LL500XI - 910925870758




Polar Normal (separate) - LL500XI - 910925870761




Polar Normal (separate) - LL500XI - 910925870775




Polar Normal (separate) - LL500XI - 910925870756




Polar Normal (separate) - LL500XI - 910925870763




Polar Normal (separate) - LL500XI - 910925870777



Polar Normal (separate) - LL500XI - 910925870764




Polar Normal (separate) - LL500XI - 910925870766




Polar Normal (separate) - LL500XI - 910925870759


Polar Wide Diagrams




Polar Normal (separate) - LL500XI - 910925870771




Polar Normal (separate) - LL500XI - 910925870779




Polar Normal (separate) - LL500XI - 910925870760




Polar Normal (separate) - LL500XI - 910925870802




Polar Normal (separate) - LL500XI - 910925870808




Polar Normal (separate) - LL500XI - 910925870798



Polar Normal (separate) - LL500XI - 910925870810




Polar Normal (separate) - LL500XI - 910925870797




Polar Normal (separate) - LL500XI - 910925870811


Polar Wide Diagrams




**Polar Normal (separate) - LL500XI -
910925870796**




**Polar Normal (separate) - LL500XI -
910925870805**




**Polar Normal (separate) - LL500XI -
910925870806**




**Polar Normal (separate) - LL500XI -
910925870804**




**Polar Normal (separate) - LL500XI -
910925870809**




**Polar Normal (separate) - LL500XI -
910925870803**



Polar Normal (separate) - LL500XI - 910925870799




**Polar Normal (separate) - LL500XI -
910925870801**




**Polar Normal (separate) - LL500XI -
910925870807**


Polar Wide Diagrams




Polar Normal (separate) - LL500XI - 910925870812




Polar Normal (separate) - LL500XI - 910925870794




Polar Normal (separate) - LL500XI - 910925870795




Polar Normal (separate) - LL500XI - 910925870819




Polar Normal (separate) - LL500XI - 910925870051




Polar Normal (separate) - LL500XI - 910925870057



Polar Normal (separate) - LL500XI - 910925870052




Polar Normal (separate) - LL500XI - 910925870055




Polar Normal (separate) - LL500XI - 910925870056


Polar Wide Diagrams




Polar Normal (separate) - LL500XI - 910925870064




**Polar Normal (separate) - LL500XI -
910925870059**




**Polar Normal (separate) - LL500XI -
910925870063**




Polar Normal (separate) - LL500XI - 910925870062




**Polar Normal (separate) - LL500XI -
910925870061**




**Polar Normal (separate) - LL500XI -
910925870058**



Polar Normal (separate) - LL500XI - 910925870066



**Polar Normal (separate) - LL500XI -
910925870067**



**Polar Normal (separate) - LL500XI -
910925870065**

