



MASTER LEDcandles – Eye-catching design for chandeliers and other decorative fixtures

MASTER Plastic LEDcandles & lusters

Delivering incandescent-like sparkling light effects, MASTER LEDcandle bulbs are ideal for general and decorative lighting in the hospitality industry, as well as in home environments. The dimmable MASTER LEDcandles drive further efficiencies, while helping to create the desired atmosphere. Mounted in full view in chandeliers, wall scones or modern luminaires, the clear or frosted glass bulbs fit all existing fixtures with an E14 and B15 socket. Drawing upon inputs from chandelier makers and designed to enhance the aesthetic appeal of the chandelier or luminaire, not only when lit but also when not, these lamps come in a classical slender shape with a unique, eye-catching lens design. They produce a beautiful sparkling warm light that delivers huge energy savings and minimizes maintenance cost. The flame-shaped candle lamps comes in a classical slender shape with a unique, eye-catching lens design that perfectly complements modern LED candles.

Benefits

- Sparkling warm white light
- Up to 80% energy saving
- Lower maintenance costs

MASTER Plastic LEDcandles & lusters

Features

- Retrofittable with existing E14 and B22 holders
- Lifetime of 20,000 hours
- Unique DiamondSpark lens
- Free of mercury and hazardous materials

Application

- Hotels, restaurants, bars, cafés
- Chandelier or modern luminaire

Versions





SPPR LEDCL 0021



LEDluster MAS SLR1 P48 E14 CL

Dimensional drawing



Product	D	C
MAS LEDcandle DT 6-40W E14 B38 CL_AP	38 mm	113 mm

Product	D	C
MAS LEDlustre DT 5.5-40W E14 P48 CL	50 mm	95 mm

MASTER Plastic LEDcandles & lusters

General Information	
Cap-Base	E14
Switching Cycle	50,000
Nominal lifetime	25,000 hour(s)
Light Technical	
Color rendering index (CRI)	80
Color Code	822-827
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux	470 lm
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Wattage Equivalent	40 W
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Consumption kWh/1000 h	6 kWh

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)
929001140408	MAS LEDcandle DT 6-40W E14 B38 CL_AP	-
929002491402	MAS LEDlustre DT 5.5-40W E14 P48 CL	2200 K

Operating and Electrical

Order Code	Full Product Name	Power Consumption
929001140408	MAS LEDcandle DT 6-40W E14 B38 CL_AP	6 W

Order Code	Full Product Name	Power Consumption
929002491402	MAS LEDlustre DT 5.5-40W E14 P48 CL	5.5 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929001140408	MAS LEDcandle DT 6-40W E14 B38 CL_AP	95 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929002491402	MAS LEDlustre DT 5.5-40W E14 P48 CL	80 °C


Controls and Dimming


Order Code	Full Product Name	Dimmable
929001140408	MAS LEDcandle DT 6-40W E14 B38 CL_AP	Yes

Order Code	Full Product Name	Dimmable
929002491402	MAS LEDlustre DT 5.5-40W E14 P48 CL	Only with specific dimmers

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929001140408	MAS LEDcandle DT 6-40W E14 B38 CL_AP	B38
929002491402	MAS LEDlustre DT 5.5-40W E14 P48 CL	P48





MASTER Plastic LEDcandles & lusters

