



Create an inviting atmosphere for retail and hospitality with new perfect-fit

MASTER LEDspot LV AR111

With its new perfect-fit design, the Master LEDspot LV AR111 now works with most of G53 luminaires as a true retrofit solution. The lamp creates a brilliant visual effect for retail and hospitality applications such as shops, showrooms and galleries. The high quality light brings out the true colors in merchandise and emphasizes its beauty. It also lasts long, with a strong lumen and color maintenance. The beautifully designed lamp offers a well-defined beam with a multitude of beam angles to suit various applications. Not only does it employ the Philips patented solution to ensure it is compatible with a broad selection of standard 12V halogen electronic transformers, it also delivers high beam intensity which equivalent to halogen AR111 spots of 50W, 75W or 100W.

Benefits

- High intensity of beam for accent lighting with strong lumen maintenance
- Achieve more vivid, vibrant colors over time for merchandise display to emphasize its beauty
- Innovative design with hassle free retrofit solution to enhance retail, hospitality environment

MASTER LEDspot LV AR111

Features

- Superior design with Red Dot award of "innovative product design"
- High intensity of beam equivalent to halogen AR111 50W, 75W, 100W
- Better color realization with high CRI value, while colors remain vibrant and natural
- High lumen and color maintenance with long lifetime of 25,000 hours to 40,000 hours
- Retrofitable with G53 luminaires

Application

- Retail: fashion, cosmetics, jewelry, food, concept stores, museums, exhibitions
- Hospitality: hotel guest room, corridors, lobby, reception area, restaurants, bars, cafes
- Home: dining room, living room, hall way

Versions




LEDclassic 5-50W MR16 830 60D



LEDspot 50W GU10 AR70 827 25D ND


Dimensional drawing



Product	D	C
MAS LED ExpertColor 15-75W 927 AR111 24D	111 mm	62 mm
MAS LED ExpertColor 15-75W 927 AR111 40D	111 mm	62 mm
MAS LED ExpertColor 15-75W 930 AR111 24D	111 mm	62 mm
MAS LED ExpertColor 15-75W 930 AR111 40D	111 mm	62 mm

MASTER LEDspot LV AR111

Dimensional drawing



Product	D	C
AR70 100-240V 5-50W 525lm 25D 2700K ND	70 mm	61 mm

Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Starting Time (Nom)	0.5 s

General Information

Order Code	Full Product Name	Cap-Base	Switching Cycle	Nominal lifetime
929002239008	MAS LED ExpertColor 15-75W 927 AR111 24D	G53	50,000	40,000 hour(s)
929002239108	MAS LED ExpertColor 15-75W 930 AR111 24D	G53	50,000	40,000 hour(s)
929002239308	MAS LED ExpertColor 15-75W 927 AR111 40D	G53	50,000	40,000 hour(s)

Order Code	Full Product Name	Cap-Base	Switching Cycle	Nominal lifetime
929002239408	MAS LED ExpertColor 15-75W 930 AR111 40D	G53	50,000	40,000 hour(s)
929001373041	AR70 100-240V 5-50W 525lm 25D 2700K ND	GU10	15,000	25,000 hour(s)

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux	Luminous Intensity (Nom)
929002239008	MAS LED ExpertColor 15-75W 927 AR111 24D	24 degree(s)	2700 K	97	927	950 lm	3,500 cd
929002239108	MAS LED ExpertColor 15-75W 930 AR111 24D	24 degree(s)	3000 K	97	930	1,000 lm	3,500 cd
929002239308	MAS LED ExpertColor 15-75W 927 AR111 40D	40 degree(s)	2700 K	97	927	950 lm	1,400 cd
929002239408	MAS LED ExpertColor 15-75W 930 AR111 40D	40 degree(s)	3000 K	97	930	1,000 lm	1,400 cd
929001373041	AR70 100-240V 5-50W 525lm 25D 2700K ND	25 degree(s)	2700 K	80	827	525 lm	1,700 cd

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929002239008	MAS LED ExpertColor 15-75W 927 AR111 24D	- Hz	- Hz	15 W	75 W
929002239108	MAS LED ExpertColor 15-75W 927 AR111 40D	- Hz	- Hz	15 W	75 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929002239308	MAS LED ExpertColor 15-75W 927 AR111 40D	- Hz	- Hz	15 W	75 W

MASTER LEDspot LV AR111

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929002239408	MAS LED ExpertColor 15-75W 930 AR111 40D	- Hz	- Hz	15 W	75 W
929001373041	AR70 100-240V	50 to 60 Hz	50 to 60 Hz	5 W	50 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
	5-50W 525lm 25D 2700K ND				

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929002239008	MAS LED ExpertColor 15-75W 927 AR111 24D	74 °C
929002239108	MAS LED ExpertColor 15-75W 930 AR111 24D	74 °C
929002239308	MAS LED ExpertColor 15-75W 927 AR111 40D	74 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929002239408	MAS LED ExpertColor 15-75W 930 AR111 40D	74 °C
929001373041	AR70 100-240V 5-50W 525lm 25D 2700K ND	70 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929002239008	MAS LED ExpertColor 15-75W 927 AR111 24D	Yes
929002239108	MAS LED ExpertColor 15-75W 930 AR111 24D	Yes
929002239308	MAS LED ExpertColor 15-75W 927 AR111 40D	Yes

Order Code	Full Product Name	Dimmable
929002239408	MAS LED ExpertColor 15-75W 930 AR111 40D	Yes
929001373041	AR70 100-240V 5-50W 525lm 25D 2700K ND	No


Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929002239008	MAS LED ExpertColor 15-75W 927 AR111 24D	AR111
929002239108	MAS LED ExpertColor 15-75W 930 AR111 24D	AR111
929002239308	MAS LED ExpertColor 15-75W 927 AR111 40D	AR111



Order Code	Full Product Name	Bulb Shape
929002239408	MAS LED ExpertColor 15-75W 930 AR111 40D	AR111
929001373041	AR70 100-240V 5-50W 525lm 25D 2700K ND	AR70

Approval and Application


Order Code	Full Product Name	Energy Consumption kWh/1000 h
929002239008	MAS LED ExpertColor 15-75W 927 AR111 24D	17 kWh
929002239108	MAS LED ExpertColor 15-75W 930 AR111 24D	17 kWh
929002239308	MAS LED ExpertColor 15-75W 927 AR111 40D	17 kWh
929002239408	MAS LED ExpertColor 15-75W 930 AR111 40D	17 kWh
929001373041	AR70 100-240V 5-50W 525lm 25D 2700K ND	-




MASTER LEDspot LV AR111




Accent Diagrams




Accent Diagram - MAS LED ExpertColor 15-75W 927 AR111 40D



Accent Diagram - MAS LED ExpertColor 15-75W 927 AR111 24D




Accent Diagram - MAS LED ExpertColor 15-75W 930 AR111 24D




Accent Diagram - MAS LED ExpertColor 15-75W 930 AR111 40D

MASTER LEDspot LV AR111


Beam Diagrams




Beam diagram - MAS LED ExpertColor 15-75W 927 AR111 24D



Beam diagram - MAS LED ExpertColor 15-75W 930 AR111 40D



Beam diagram - MAS LED ExpertColor 15-75W 930 AR111 24D



Beam diagram - MAS LED ExpertColor 15-75W 927 AR111 40D

