



MASTER LEDbulb – Elegance meets efficiency

MASTER LEDbulb

MASTER LEDbulb range delivers a dimmable glow effect for a welcoming, warm atmosphere, making it ideal for general lighting applications in the hospitality industry. Its unique design radiates warm light in all directions, making it a true alternative to the incandescent lamp. It is particularly suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 or a B22 holder and designed for retrofit replacement of incandescent bulbs, MASTER LEDbulb delivers huge energy savings and minimises maintenance cost without any compromise on light quality.

Benefits

- 85% energy saving compared with traditional incandescent lamps
- Easy (retrofit) replacement

Features

- Unique optical design allows for sparkling light
- Dimmable
- Compatible with an extensive range of dimmers
- Warm white light
- Lifetime of 25,000 hours
- UV- and IR-free light

Application

- Hotels, restaurants, bars, cafés
- Lobbies, corridors, stairwells, reception areas

MASTER LEDbulb

Warnings and Safety


- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Versions



LEDbulb MAS SLR1 A60 E27 CL 1

Dimensional drawing



Product	D	C
MAS LEDbulb DT 8-60W E27 A60 CL UK	60.5 mm	110 mm



MASTER LEDbulb

