



MASTER Value LEDspot MV -lampulla on optimaalinen hinta-laatusuhde, ja se sopii täydellisesti kohdevalaistukseen

MASTER LEDspot MV

Lämpimän halogeenilampun valon kaltaisen korostevalokeilan tuottava MASTER VALUE soveltuu täydellisesti kohdevalaistukseen. Sen värintöistöindeksi on korkea, joten värit näkyvät luonnollisempina. Se saa aikaan kotoisan ja mukavan tunnelman asunnoissa, hotelleissa ja ravintoloissa sekä korostaa tuotteiden kauneutta vähittäismyymälöissä. Nämä MV GU10 LED -kohdelamput näyttävät ja tuntuvat tutuilta lasisilta kohdelampuilta, mutta niiden klassista kauneutta täydennetään LED-tekniikan tehokkaalla suorituskyvyllä. Himmennystoiminto saa aikaan halutun tunnelman, ja valaisimet toimivat monien erilaisten himmentimien kanssa. Lisäksi MASTER VALUE säästää energiaa enemmän kuin tavalliset LED-kohdelamput.

Hyödyt

- MASTER VALUE -kohdelamppu säästää jopa 80 % enemmän energiaa halogeenilamppuihin verrattuna
- Lampun valo jäljittelee parhaiten halogeenikohdelampun valoa ja luo sopivan tunnelman.
- Korvaa täydellisesti perinteiset GU10-lamput

MASTER LEDspot MV

Ominaisuudet

- Himmennettävä tuotevalikoima
- Yhteensopiva monenlaisten himmentimien kanssa
- Patentoitu älykäs virtalähde
- Käyttöikä 25 000 tuntia
- Ei ultraviolettia-, lämpö- eikä infrapunasäteilyä, joten se sopii myös elintarvikkeiden, orgaanisten materiaalien ja maalausten kaltaisten lämpöherkkien kohteiden valaisemiseen.

Käyttökohteet

- Hotellit ja ravintolat
- Vähittäismyymälät
- Kodit ja asuintalot

Rajoitukset ja turvallisuus


- Käyttölämpötila välillä -20...+45 °C
- Sijoitettava vain kuiviin tai kosteisiin paikkoihin. Sopii useimpiin avoimiin valaisimiin, joissa lampunpidikkeiden ympärillä on tarpeeksi tilaa (10 mm tyhjää tilaa)
- Ei suunniteltu käytettäväksi turvavalaisukseen

Versions



LEDspots 50W GU10 PAR16


Mittapiirros



Product	D	C
MAS LED spot VLE D 3.7-35W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 927 60D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 930 60D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 6.2-80W GU10 965 36D	50 mm	54 mm
MAS LED spot VLE DT 4.9-50W GU10 927 36D	50 mm	54 mm

MASTER LEDspot MV

Mittapiirros



Product	D	C
MAS LED spot VLE D 2.8-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 2.8-35W GU10 927 60D	50 mm	54 mm
MAS LED spot VLE D 2.8-35W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 2.8-35W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 927 60D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 930 60D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 940 60D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 965 36D	50 mm	54 mm
MAS LED spot VLE D 650lm GU10 930 120D	50 mm	55,5 mm
MAS LED spot VLE D 680lm GU10 940 120D	50 mm	55,5 mm
MAS LED spot VLE D 680lm GU10 965 120D	50 mm	55,5 mm
MAS LED spot VLE DT 2.8-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE DT 3.7-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE DT 3.7-50W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE DT 5.5-80W GU10 927 36D	50 mm	54 mm
MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	50 mm	54 mm
MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	50 mm	54 mm

Yleistä tietoa

Kanta	GU10
Nimelliskäyttöikä	25 000 tuntia

Valaistuksen tekniset tiedot

Värintoistoindeksi (CRI)	90
LLMF nimelliskäyttöiän lopussa (nim.)	70 %

Käyttö- ja sähkö tiedot

Syöttötaajuus	50–60 Hz
Syttymisaika (nim.)	0,5 s

Ohjausjärjestelmät ja himmennys

Himmennettävä	Vain tiettyjen himmennimien kanssa
---------------	--

Mekaaniset tiedot ja runko

Hekkulampun muoto	PAR16
-------------------	-------

Yleistä tietoa

Order Code	Full Product Name	Sytytys
929002209902	MAS LED spot VLE D 6.2-80W GU10 965 36D	50 000
929004255702	MAS LED spot VLE DT 5.5-80W GU10 927 36D	50 000
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	50 000
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	50 000
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	50 000
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	50 000
929001348302	MAS LED spot VLE D 3.7-35W GU10 930 36D	50 000
929001348902	MAS LED spot VLE D 4.9-50W GU10 930 36D	50 000
929001349002	MAS LED spot VLE D 4.9-50W GU10 940 36D	50 000
929001349102	MAS LED spot VLE D 4.9-50W GU10 927 60D	50 000
929001349202	MAS LED spot VLE D 4.9-50W GU10 930 60D	50 000
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	50 000
929002979402	MAS LED spot VLE D 3.7-35W GU10 927 36D	50 000
929002979702	MAS LED spot VLE DT 3.7-35W GU10 927 36D	50 000
929004247102	MAS LED spot VLE DT 2.8-35W GU10 927 36D	50 000
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	50 000
929004247302	MAS LED spot VLE D 2.8-35W GU10 927 36D	50 000
929004247402	MAS LED spot VLE D 2.8-35W GU10 930 36D	50 000
929004247502	MAS LED spot VLE D 2.8-35W GU10 940 36D	50 000
929004247602	MAS LED spot VLE D 2.8-35W GU10 927 60D	50 000
929004247902	MAS LED spot VLE D 3.7-50W GU10 927 36D	50 000

Order Code	Full Product Name	Sytytys
929004248002	MAS LED spot VLE D 3.7-50W GU10 930 36D	50 000
929004248102	MAS LED spot VLE D 3.7-50W GU10 940 36D	50 000
929004248202	MAS LED spot VLE D 3.7-50W GU10 927 60D	25 000
929004248302	MAS LED spot VLE D 3.7-50W GU10 930 60D	25 000
929004248402	MAS LED spot VLE D 3.7-50W GU10 940 60D	25 000
929004247952	MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	50 000
929004248052	MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	50 000
929004256202	MAS LED spot VLE D 650lm GU10 930 120D	50 000
929004256302	MAS LED spot VLE D 680lm GU10 940 120D	50 000
929004256402	MAS LED spot VLE D 680lm GU10 965 120D	50 000

Valaistuksen tekniset tiedot (1/2)

Order Code	Full Product Name	Keilakulma (nim.)	Väriämpötila (nim.)	Värikoodi	Valovirta	Order Code	Full Product Name	Keilakulma (nim.)	Väriämpötila (nim.)	Värikoodi	Valovirta
929002209902	MAS LED spot VLE D 6.2-80W GU10 965 36D	36 °	6500 K	6500	575 lm	929002979402	MAS LED spot VLE D 3.7-35W GU10 927 36D	36 °	2700 K	927	270 lm
929004255702	MAS LED spot VLE DT 5.5-80W GU10 927 36D	36 °	2200 K	922-927	575 lm	929002979702	MAS LED spot VLE DT 3.7-35W GU10 927 36D	36 °	2200 K	922-927	270 lm
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	36 °	2700 K	927	575 lm	929004247102	MAS LED spot VLE DT 2.8-35W GU10 927 36D	36 °	2200 K	922-927	280 lm
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	36 °	3000 K	930	575 lm	929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	36 °	2200 K	922-927	355 lm
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	36 °	4000 K	940	575 lm	929004247302	MAS LED spot VLE D 2.8-35W GU10 927 36D	36 °	2700 K	927	270 lm
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	36 °	6500 K	965	575 lm	929004247402	MAS LED spot VLE D 2.8-35W GU10 930 36D	36 °	3000 K	930	270 lm
929001348302	MAS LED spot VLE D 3.7-35W GU10 930 36D	36 °	3000 K	930	270 lm	929004247502	MAS LED spot VLE D 2.8-35W GU10 940 36D	36 °	4000 K	940	285 lm
929001348902	MAS LED spot VLE D 4.9-50W GU10 930 36D	36 °	3000 K	930	365 lm	929004247602	MAS LED spot VLE D 2.8-35W GU10 927 60D	60 °	2700 K	927	270 lm
929001349002	MAS LED spot VLE D 4.9-50W GU10 940 36D	36 °	4000 K	940	380 lm	929004247902	MAS LED spot VLE D 3.7-50W GU10 927 36D	36 °	2700 K	927	355 lm
929001349102	MAS LED spot VLE D 4.9-50W GU10 927 60D	60 °	2700 K	927	355 lm	929004248002	MAS LED spot VLE D 3.7-50W GU10 930 36D	36 °	3000 K	930	365 lm
929001349202	MAS LED spot VLE D 4.9-50W GU10 930 60D	60 °	3000 K	930	365 lm	929004248102	MAS LED spot VLE D 3.7-50W GU10 940 36D	36 °	4000 K	940	380 lm
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	36 °	2200 K	922-927	355 lm	929004248202	MAS LED spot VLE D 3.7-50W GU10 927 60D	60 °	2700 K	927	355 lm

MASTER LEDspot MV

Order Code	Full Product Name	Keilakulma (nim.)	Väriämpötila (nim.)	Värikoodi	Valovirta
929004248302	MAS LED spot VLE D 3.7-50W GU10 930 60D	60 °	3000 K	930	365 lm
929004248402	MAS LED spot VLE D 3.7-50W GU10 940 60D	60 °	4000 K	940	370 lm
929004247952	MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	36 °	2700 K	927	355 lm
929004248052	MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	36 °	3000 K	930	365 lm

Order Code	Full Product Name	Keilakulma (nim.)	Väriämpötila (nim.)	Värikoodi	Valovirta
929004256202	MAS LED spot VLE D 650lm GU10 930 120D	120 °	3000 K	930	650 lm
929004256302	MAS LED spot VLE D 680lm GU10 940 120D	120 °	4000 K	940	680 lm
929004256402	MAS LED spot VLE D 680lm GU10 965 120D	120 °	6500 K	965	680 lm

Valaistuksen tekniset tiedot (2/2)

Order Code	Full Product Name	Valovoima (nim.)
929002209902	MAS LED spot VLE D 6.2-80W GU10 965 36D	850 cd
929004255702	MAS LED spot VLE DT 5.5-80W GU10 927 36D	950 cd
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	950 cd
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	1 000 cd
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	1 000 cd
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	1 000 cd
929001348302	MAS LED spot VLE D 3.7-35W GU10 930 36D	500 cd
929001348902	MAS LED spot VLE D 4.9-50W GU10 930 36D	650 cd
929001349002	MAS LED spot VLE D 4.9-50W GU10 940 36D	700 cd
929001349102	MAS LED spot VLE D 4.9-50W GU10 927 60D	400 cd
929001349202	MAS LED spot VLE D 4.9-50W GU10 930 60D	400 cd
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	650 cd
929002979402	MAS LED spot VLE D 3.7-35W GU10 927 36D	500 cd
929002979702	MAS LED spot VLE DT 3.7-35W GU10 927 36D	500 cd
929004247102	MAS LED spot VLE DT 2.8-35W GU10 927 36D	550 cd
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	700 cd

Order Code	Full Product Name	Valovoima (nim.)
929004247302	MAS LED spot VLE D 2.8-35W GU10 927 36D	600 cd
929004247402	MAS LED spot VLE D 2.8-35W GU10 930 36D	600 cd
929004247502	MAS LED spot VLE D 2.8-35W GU10 940 36D	600 cd
929004247602	MAS LED spot VLE D 2.8-35W GU10 927 60D	300 cd
929004247902	MAS LED spot VLE D 3.7-50W GU10 927 36D	750 cd
929004248002	MAS LED spot VLE D 3.7-50W GU10 930 36D	750 cd
929004248102	MAS LED spot VLE D 3.7-50W GU10 940 36D	800 cd
929004248202	MAS LED spot VLE D 3.7-50W GU10 927 60D	400 cd
929004248302	MAS LED spot VLE D 3.7-50W GU10 930 60D	400 cd
929004248402	MAS LED spot VLE D 3.7-50W GU10 940 60D	420 cd
929004247952	MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	750 cd
929004248052	MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	750 cd
929004256202	MAS LED spot VLE D 650lm GU10 930 120D	220 cd
929004256302	MAS LED spot VLE D 680lm GU10 940 120D	220 cd
929004256402	MAS LED spot VLE D 680lm GU10 965 120D	220 cd

Käyttö- ja sähkö tiedot

Order Code	Full Product Name	Viivatiheys	Virrankulutus	Vastaa teholtaan
929002209902	MAS LED spot VLE D 6.2-80W GU10 965 36D	50 to 60 Hz	6,2 W	80 W
929004255702	MAS LED spot VLE DT 5.5-80W GU10 927 36D	-	5,5 W	80 W
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	-	5,5 W	80 W
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	-	5,5 W	80 W
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	-	5,5 W	80 W
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	-	5,5 W	80 W

Order Code	Full Product Name	Viivatiheys	Virrankulutus	Vastaa teholtaan
929001348302	MAS LED spot VLE D 3.7-35W GU10 930 36D	50 to 60 Hz	3,7 W	35 W
929001348902	MAS LED spot VLE D 4.9-50W GU10 930 36D	50 to 60 Hz	4,9 W	50 W
929001349002	MAS LED spot VLE D 4.9-50W GU10 940 36D	50 to 60 Hz	4,9 W	50 W
929001349102	MAS LED spot VLE D 4.9-50W GU10 927 60D	50 to 60 Hz	4,9 W	50 W
929001349202	MAS LED spot VLE D 4.9-50W GU10 930 60D	50 to 60 Hz	4,9 W	50 W
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	50 to 60 Hz	4,9 W	50 W

MASTER LEDspot MV

Vastaa				
Order Code	Full Product Name	Viivatiheys	Virrankulutus	teholtaan
929002979402	MAS LED spot VLE D 3.7-35W GU10 927 36D	50 to 60 Hz	3,7 W	35 W
929002979702	MAS LED spot VLE DT 3.7-35W GU10 927 36D	50 to 60 Hz	3,7 W	35 W
929004247102	MAS LED spot VLE DT 2.8-35W GU10 927 36D	-	2,8 W	35 W
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	-	3,7 W	50 W
929004247302	MAS LED spot VLE D 2.8-35W GU10 927 36D	-	2,8 W	35 W
929004247402	MAS LED spot VLE D 2.8-35W GU10 930 36D	-	2,8 W	35 W
929004247502	MAS LED spot VLE D 2.8-35W GU10 940 36D	-	2,8 W	35 W
929004247602	MAS LED spot VLE D 2.8-35W GU10 927 60D	-	2,8 W	35 W
929004247902	MAS LED spot VLE D 3.7-50W GU10 927 36D	-	3,7 W	50 W
929004248002	MAS LED spot VLE D 3.7-50W GU10 930 36D	-	3,7 W	50 W

Käyttölämpötila

T-Case, maksimi		
Order Code	Full Product Name	(nim.)
929002209902	MAS LED spot VLE D 6.2-80W GU10 965 36D	80 °C
929004255702	MAS LED spot VLE DT 5.5-80W GU10 927 36D	66 °C
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	66 °C
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	66 °C
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	66 °C
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	66 °C
929001348302	MAS LED spot VLE D 3.7-35W GU10 930 36D	80 °C
929001348902	MAS LED spot VLE D 4.9-50W GU10 930 36D	80 °C
929001349002	MAS LED spot VLE D 4.9-50W GU10 940 36D	80 °C
929001349102	MAS LED spot VLE D 4.9-50W GU10 927 60D	80 °C
929001349202	MAS LED spot VLE D 4.9-50W GU10 930 60D	80 °C
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	80 °C
929002979402	MAS LED spot VLE D 3.7-35W GU10 927 36D	70 °C
929002979702	MAS LED spot VLE DT 3.7-35W GU10 927 36D	70 °C
929004247102	MAS LED spot VLE DT 2.8-35W GU10 927 36D	52 °C
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	60 °C

Mekaaniset tiedot ja runko

Order Code	Full Product Name	Lampun pinta
929002209902	MAS LED spot VLE D 6.2-80W GU10 965 36D	-
929004255702	MAS LED spot VLE DT 5.5-80W GU10 927 36D	Kirkas
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	Kirkas
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	Kirkas
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	Kirkas

Vastaa				
Order Code	Full Product Name	Viivatiheys	Virrankulutus	teholtaan
929004248102	MAS LED spot VLE D 3.7-50W GU10 940 36D	-	3,7 W	50 W
929004248202	MAS LED spot VLE D 3.7-50W GU10 927 60D	-	3,7 W	50 W
929004248302	MAS LED spot VLE D 3.7-50W GU10 930 60D	-	3,7 W	50 W
929004248402	MAS LED spot VLE D 3.7-50W GU10 940 60D	-	3,7 W	50 W
929004247952	MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	-	3,7 W	50 W
929004248052	MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	-	3,7 W	50 W
929004256202	MAS LED spot VLE D 650lm GU10 930 120D	-	5,5 W	-
929004256302	MAS LED spot VLE D 680lm GU10 940 120D	-	5,5 W	-
929004256402	MAS LED spot VLE D 680lm GU10 965 120D	-	5,5 W	-

T-Case, maksimi		
Order Code	Full Product Name	(nim.)
929004247302	MAS LED spot VLE D 2.8-35W GU10 927 36D	50 °C
929004247402	MAS LED spot VLE D 2.8-35W GU10 930 36D	50 °C
929004247502	MAS LED spot VLE D 2.8-35W GU10 940 36D	50 °C
929004247602	MAS LED spot VLE D 2.8-35W GU10 927 60D	50 °C
929004247902	MAS LED spot VLE D 3.7-50W GU10 927 36D	66 °C
929004248002	MAS LED spot VLE D 3.7-50W GU10 930 36D	66 °C
929004248102	MAS LED spot VLE D 3.7-50W GU10 940 36D	66 °C
929004248202	MAS LED spot VLE D 3.7-50W GU10 927 60D	62 °C
929004248302	MAS LED spot VLE D 3.7-50W GU10 930 60D	62 °C
929004248402	MAS LED spot VLE D 3.7-50W GU10 940 60D	62 °C
929004247952	MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	66 °C
929004248052	MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	66 °C
929004256202	MAS LED spot VLE D 650lm GU10 930 120D	66 °C
929004256302	MAS LED spot VLE D 680lm GU10 940 120D	66 °C
929004256402	MAS LED spot VLE D 680lm GU10 965 120D	66 °C

Order Code	Full Product Name	Lampun pinta
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	Kirkas
929001348302	MAS LED spot VLE D 3.7-35W GU10 930 36D	-
929001348902	MAS LED spot VLE D 4.9-50W GU10 930 36D	-
929001349002	MAS LED spot VLE D 4.9-50W GU10 940 36D	-
929001349102	MAS LED spot VLE D 4.9-50W GU10 927 60D	-

MASTER LEDspot MV


Order Code	Full Product Name	Lampun pinta
929001349202	MAS LED spot VLE D 4.9-50W GU10 930 60D	-
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	-
929002979402	MAS LED spot VLE D 3.7-35W GU10 927 36D	-
929002979702	MAS LED spot VLE DT 3.7-35W GU10 927 36D	-
929004247102	MAS LED spot VLE DT 2.8-35W GU10 927 36D	Kirkas
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	Kirkas
929004247302	MAS LED spot VLE D 2.8-35W GU10 927 36D	Kirkas
929004247402	MAS LED spot VLE D 2.8-35W GU10 930 36D	Kirkas
929004247502	MAS LED spot VLE D 2.8-35W GU10 940 36D	Kirkas
929004247602	MAS LED spot VLE D 2.8-35W GU10 927 60D	Kirkas
929004247902	MAS LED spot VLE D 3.7-50W GU10 927 36D	Kirkas

Order Code	Full Product Name	Lampun pinta
929004248002	MAS LED spot VLE D 3.7-50W GU10 930 36D	Kirkas
929004248102	MAS LED spot VLE D 3.7-50W GU10 940 36D	Kirkas
929004248202	MAS LED spot VLE D 3.7-50W GU10 927 60D	Kirkas
929004248302	MAS LED spot VLE D 3.7-50W GU10 930 60D	Kirkas
929004248402	MAS LED spot VLE D 3.7-50W GU10 940 60D	Kirkas
929004247952	MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	Kirkas
929004248052	MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	Kirkas
929004256202	MAS LED spot VLE D 650lm GU10 930 120D	Matta
929004256302	MAS LED spot VLE D 680lm GU10 940 120D	Matta
929004256402	MAS LED spot VLE D 680lm GU10 965 120D	Matta

Merkinnät ja luokitukset

Order Code	Full Product Name	Ympäristön lämpötila	Energiankulutus kWh/1000 h
929002209902	MAS LED spot VLE D 6.2-80W GU10 965 36D	-	7 kWh
929004255702	MAS LED spot VLE DT 5.5-80W GU10 927 36D	-20...+45 °C	6 kWh
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	-20...+45 °C	6 kWh
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	-20...+45 °C	6 kWh
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	-20...+45 °C	6 kWh
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	-20...+45 °C	6 kWh
929001348302	MAS LED spot VLE D 3.7-35W GU10 930 36D	-	4 kWh
929001348902	MAS LED spot VLE D 4.9-50W GU10 930 36D	-	5 kWh
929001349002	MAS LED spot VLE D 4.9-50W GU10 940 36D	-	5 kWh
929001349102	MAS LED spot VLE D 4.9-50W GU10 927 60D	-	5 kWh
929001349202	MAS LED spot VLE D 4.9-50W GU10 930 60D	-	5 kWh
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	-	5 kWh
929002979402	MAS LED spot VLE D 3.7-35W GU10 927 36D	-	4 kWh
929002979702	MAS LED spot VLE DT 3.7-35W GU10 927 36D	-	4 kWh
929004247102	MAS LED spot VLE DT 2.8-35W GU10 927 36D	-20...+45 °C	3 kWh
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	-20...+45 °C	4 kWh
929004247302	MAS LED spot VLE D 2.8-35W GU10 927 36D	-20...+45 °C	3 kWh
929004247402	MAS LED spot VLE D 2.8-35W GU10 930 36D	-20...+45 °C	3 kWh











Order Code	Full Product Name	Ympäristön lämpötila	Energiankulutus kWh/1000 h
929004247502	MAS LED spot VLE D 2.8-35W GU10 940 36D	-20...+45 °C	3 kWh
929004247602	MAS LED spot VLE D 2.8-35W GU10 927 60D	-20...+45 °C	3 kWh
929004247902	MAS LED spot VLE D 3.7-50W GU10 927 36D	-20...+45 °C	4 kWh
929004248002	MAS LED spot VLE D 3.7-50W GU10 930 36D	-20...+45 °C	4 kWh
929004248102	MAS LED spot VLE D 3.7-50W GU10 940 36D	-20...+45 °C	4 kWh
929004248202	MAS LED spot VLE D 3.7-50W GU10 927 60D	-20...+45 °C	4 kWh
929004248302	MAS LED spot VLE D 3.7-50W GU10 930 60D	-20...+45 °C	4 kWh
929004248402	MAS LED spot VLE D 3.7-50W GU10 940 60D	-20...+45 °C	4 kWh
929004247952	MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	-20...+45 °C	4 kWh
929004248052	MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	-20...+45 °C	4 kWh
929004256202	MAS LED spot VLE D 650lm GU10 930 120D	-20...+45 °C	6 kWh
929004256302	MAS LED spot VLE D 680lm GU10 940 120D	-20...+45 °C	6 kWh
929004256402	MAS LED spot VLE D 680lm GU10 965 120D	-20...+45 °C	6 kWh












120°


90°

60°







Accent Diagrams




Accent Diagram - MAS LED spot VLE D 2.8-35W
GU10 930 36D




Accent Diagram - MAS LED spot VLE DT
4.9-50W GU10 927 36D




Accent Diagram - MAS LED spot VLE D 3.7-35W
GU10 930 36D




Accent Diagram - MAS LED spot VLE D
4.9-50W GU10 930 36D




Accent Diagram - MAS LED spot VLE D
4.9-50W GU10 927 60D




Accent Diagram - MAS LED spot VLE DT
3.7-35W GU10 927 36D



Accent Diagram - MAS LED spot VLE D 6.2-80W
GU10 965 36D




Accent Diagram - MAS LED spot VLE D 5.5-80W
GU10 927 36D




Accent Diagram - MAS LED spot VLE DT
5.5-80W GU10 927 36D


Accent Diagrams




Accent Diagram - MAS LED spot VLE D 5.5-80W
GU10 940 36D




Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 927 60D




Accent Diagram - MAS LED spot VLE D 2.8-35W
GU10 940 36D




Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 940 36D




Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 930 36D




Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 927 36D



Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 927 36D




Accent Diagram - MAS LED spot VLE D 2.8-35W
GU10 927 36D




Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 940 60D


Accent Diagrams




Accent Diagram - MAS LED spot VLE D 2.8-35W
GU10 927 60D



Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 930 60D




Accent Diagram - MAS LED spot VLE DT
2.8-35W GU10 927 36D




Accent Diagram - MAS LED spot VLE DT
3.7-50W GU10 927 36D


Beam Diagrams



Beam diagram - MAS LED spot VLE DT 5.5-80W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 3.7-35W
GU10 927 36D




Beam diagram - MAS LED spot VLE DT 4.9-50W
GU10 927 36D


Beam Diagrams




Beam diagram - MAS LED spot VLE D 3.7-35W
GU10 930 36D




Beam diagram - MAS LED spot VLE D 4.9-50W
GU10 930 36D




Beam diagram - MAS LED spot VLE D 4.9-50W
GU10 927 60D




Beam diagram - MAS LED spot VLE D 2.8-35W
GU10 940 36D




Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 940 36D




Beam diagram - MAS LED spot VLE D 2.8-35W
GU10 927 60D



Beam diagram - MAS LED spot VLE DT 2.8-35W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 2.8-35W
GU10 930 36D




Beam diagram - MAS LED spot VLE D 5.5-80W
GU10 940 36D


Beam Diagrams




Beam diagram - MAS LED spot VLE DT 3.7-35W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 927 60D




Beam diagram - MAS LED spot VLE D 5.5-80W
GU10 927 36D




Beam diagram - MAS LED spot VLE DT 3.7-50W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 930 60D



Beam diagram - MAS LED spot VLE D 6.2-80W
GU10 965 36D




Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 940 60D



Beam diagram - MAS LED spot VLE D 2.8-35W
GU10 927 36D

Beam Diagrams



Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 930 36D

