



MASTER Value LEDspot MV, en optimal kombination av värde och prestanda, passar perfekt för spotbelysning

MASTER VALUE LEDspot MV

MASTER VALUE passar perfekt för spotbelysning och ger ett varmt, halogenliknande accentflöde. Tack vare hög CRI ger den mer naturliga färger, vilket skapar mysiga och bekväma miljöer för bostads- och hotellprojekt och kan även framhäva produkter i butik. Dessa LED-spottar MV GU10 ger den välbekanta känslan av spotbelysning, behåller skönheten i glasspottar och lägger till prestanda för LED-teknik. Med dimringsfunktionen kan du skapa den atmosfär du vill ha och den fungerar med många olika dimmers. MASTER VALUE ger också större energibesparingar än vanliga LED-spottar.

Fördelar

- MASTER VALUE-spotlight ger upp till 80 % lägre energiförbrukning jämfört med halogenlampor
- Bästa efterföljaren till en halogenspotlight för en varm stämning
- Perfekt ersättning för traditionella GU10-ljuskällor

MASTER VALUE LEDspot MV

Funktioner

- Dimbar
- Kompatibel med ett stort urval av dimmerenheter
- Patenterat intelligent driftdon
- 25 000 timmars livslängd
- Ljuset är helt fritt från UV- och IR-strålar och är därför lämpligt för belysning av värmekänsliga föremål (livsmedel, organiskt material, målningar osv.)

Användning

- Hotell och restaurang
- Butiker
- Bostadsområden

Varning och Säkerhet


- Omgivningstemperaturen vid drift ligger mellan -20°C och 45°C
- Endast för användning i torra eller fuktiga miljöer och i de flesta öppna armaturer med lamphållare med tillräckligt stort luftutrymme (minst 10 mm)
- Ej avsedd för användning i nödljusarmaturer eller utgångsljus

Versions



LEDspots 50W GU10 PAR16


Måttskiss



Product	D	C
MAS LED spot VLE D 3.7-35W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 927 60D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 930 60D	50 mm	54 mm
MAS LED spot VLE DT 4.9-50W GU10 927 36D	50 mm	54 mm

MASTER VALUE LEDspot MV

Måttskiss



Product	D	C
MAS LED spot VLE D 2.8-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 2.8-35W GU10 927 60D	50 mm	54 mm
MAS LED spot VLE D 2.8-35W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 2.8-35W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 927 60D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 930 60D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 940 60D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 965 36D	50 mm	54 mm
MAS LED spot VLE D 650lm GU10 930 120D	50 mm	55,5 mm
MAS LED spot VLE D 680lm GU10 940 120D	50 mm	55,5 mm
MAS LED spot VLE D 680lm GU10 965 120D	50 mm	55,5 mm
MAS LED spot VLE DT 2.8-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE DT 3.7-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE DT 3.7-50W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE DT 5.5-80W GU10 927 36D	50 mm	54 mm
MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	50 mm	54 mm
MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	50 mm	54 mm

Allmän information

Sockel	GU10
Nominell livslängd	25 000 h

Ljusteknik

Färgåtergivningsindex	90
LLMF vid slutet av nominell livslängd (nom)	70 %

Drift och elektricitet

Ingångsfrekvens	50–60 Hz
Tändningstid (nom)	0,5 s

Styrenheter och dimring

Dimbar	Endast med särskilda dimmers
--------	------------------------------

Mekanik och armaturhus

Lampform	PAR16
----------	-------

Allmän information

Order Code	Full Product Name	Driftcykel
929004255702	MAS LED spot VLE DT 5.5-80W GU10 927 36D	50 000
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	50 000
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	50 000
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	50 000
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	50 000
929001348302	MAS LED spot VLE D 3.7-35W GU10 930 36D	50 000
929001348902	MAS LED spot VLE D 4.9-50W GU10 930 36D	50 000
929001349102	MAS LED spot VLE D 4.9-50W GU10 927 60D	50 000
929001349202	MAS LED spot VLE D 4.9-50W GU10 930 60D	50 000
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	50 000
929002979402	MAS LED spot VLE D 3.7-35W GU10 927 36D	50 000
929002979702	MAS LED spot VLE DT 3.7-35W GU10 927 36D	50 000
929004247102	MAS LED spot VLE DT 2.8-35W GU10 927 36D	50 000
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	50 000
929004247302	MAS LED spot VLE D 2.8-35W GU10 927 36D	50 000
929004247402	MAS LED spot VLE D 2.8-35W GU10 930 36D	50 000
929004247502	MAS LED spot VLE D 2.8-35W GU10 940 36D	50 000
929004247602	MAS LED spot VLE D 2.8-35W GU10 927 60D	50 000
929004247902	MAS LED spot VLE D 3.7-50W GU10 927 36D	50 000
929004248002	MAS LED spot VLE D 3.7-50W GU10 930 36D	50 000
929004248102	MAS LED spot VLE D 3.7-50W GU10 940 36D	50 000

MASTER VALUE LEDspot MV

Order Code	Full Product Name	Driftcykel
929004248202	MAS LED spot VLE D 3.7-50W GU10 927 60D	25 000
929004248302	MAS LED spot VLE D 3.7-50W GU10 930 60D	25 000
929004248402	MAS LED spot VLE D 3.7-50W GU10 940 60D	25 000
929004247952	MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	50 000
929004248052	MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	50 000
929004256202	MAS LED spot VLE D 650lm GU10 930 120D	50 000
929004256302	MAS LED spot VLE D 680lm GU10 940 120D	50 000
929004256402	MAS LED spot VLE D 680lm GU10 965 120D	50 000

Ljusteknik (1/2)

Order Code	Full Product Name	Spridningsvinkel (nom)	Korrelerad färgtemperatur		
			(Nom)	Färgkod	Ljusflöde
929004255702	MAS LED spot VLE DT 5.5-80W GU10 927 36D	36 °	2200 K	922-927	575 lm
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	36 °	2700 K	927	575 lm
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	36 °	3000 K	930	575 lm
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	36 °	4000 K	940	575 lm
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	36 °	6500 K	965	575 lm
929001348302	MAS LED spot VLE D 3.7-35W GU10 930 36D	36 °	3000 K	930	270 lm
929001348902	MAS LED spot VLE D 4.9-50W GU10 930 36D	36 °	3000 K	930	365 lm
929001349102	MAS LED spot VLE D 4.9-50W	60 °	2700 K	927	355 lm

Order Code	Full Product Name	Spridningsvinkel (nom)	Korrelerad färgtemperatur		
			(Nom)	Färgkod	Ljusflöde
	GU10 927 60D				
929001349202	MAS LED spot VLE D 4.9-50W GU10 930 60D	60 °	3000 K	930	365 lm
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	36 °	2200 K	922-927	355 lm
929002979402	MAS LED spot VLE D 3.7-35W GU10 927 36D	36 °	2700 K	927	270 lm
929002979702	MAS LED spot VLE DT 3.7-35W GU10 927 36D	36 °	2200 K	922-927	270 lm
929004247102	MAS LED spot VLE DT 2.8-35W GU10 927 36D	36 °	2200 K	922-927	280 lm
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	36 °	2200 K	922-927	355 lm
929004247302	MAS LED spot VLE D 2.8-35W GU10 927 36D	36 °	2700 K	927	270 lm

MASTER VALUE LEDspot MV

Order Code	Full Product Name	Spridningsvinkel (nom)	Korrelerad färgtemperatur		
			(Nom)	Färgkod	Ljusflöde
929004247402	MAS LED spot VLE D 2.8-35W GU10 930 36D	36 °	3000 K	930	270 lm
929004247502	MAS LED spot VLE D 2.8-35W GU10 940 36D	36 °	4000 K	940	285 lm
929004247602	MAS LED spot VLE D 2.8-35W GU10 927 60D	60 °	2700 K	927	270 lm
929004247902	MAS LED spot VLE D 3.7-50W GU10 927 36D	36 °	2700 K	927	355 lm
929004248002	MAS LED spot VLE D 3.7-50W GU10 930 36D	36 °	3000 K	930	365 lm
929004248102	MAS LED spot VLE D 3.7-50W GU10 940 36D	36 °	4000 K	940	380 lm
929004248202	MAS LED spot VLE D 3.7-50W	60 °	2700 K	927	355 lm

Order Code	Full Product Name	Spridningsvinkel (nom)	Korrelerad färgtemperatur		
			(Nom)	Färgkod	Ljusflöde
929004248302	MAS LED spot VLE D 3.7-50W GU10 930 60D	60 °	3000 K	930	365 lm
929004248402	MAS LED spot VLE D 3.7-50W GU10 940 60D	60 °	4000 K	940	370 lm
929004247952	MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	36 °	2700 K	927	355 lm
929004248052	MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	36 °	3000 K	930	365 lm
929004256202	MAS LED spot VLE D 650lm GU10 930 120D	120 °	3000 K	930	650 lm
929004256302	MAS LED spot VLE D 680lm GU10 940 120D	120 °	4000 K	940	680 lm
929004256402	MAS LED spot VLE D 680lm GU10 965 120D	120 °	6500 K	965	680 lm

Ljusteknik (2/2)

Order Code	Full Product Name	Ljusstyrka (nom)
929004255702	MAS LED spot VLE DT 5.5-80W GU10 927 36D	950 cd
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	950 cd
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	1 000 cd
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	1 000 cd
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	1 000 cd
929001348302	MAS LED spot VLE D 3.7-35W GU10 930 36D	500 cd
929001348902	MAS LED spot VLE D 4.9-50W GU10 930 36D	650 cd
929001349102	MAS LED spot VLE D 4.9-50W GU10 927 60D	400 cd
929001349202	MAS LED spot VLE D 4.9-50W GU10 930 60D	400 cd
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	650 cd
929002979402	MAS LED spot VLE D 3.7-35W GU10 927 36D	500 cd
929002979702	MAS LED spot VLE DT 3.7-35W GU10 927 36D	500 cd

Order Code	Full Product Name	Ljusstyrka (nom)
929004247102	MAS LED spot VLE DT 2.8-35W GU10 927 36D	550 cd
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	700 cd
929004247302	MAS LED spot VLE D 2.8-35W GU10 927 36D	600 cd
929004247402	MAS LED spot VLE D 2.8-35W GU10 930 36D	600 cd
929004247502	MAS LED spot VLE D 2.8-35W GU10 940 36D	600 cd
929004247602	MAS LED spot VLE D 2.8-35W GU10 927 60D	300 cd
929004247902	MAS LED spot VLE D 3.7-50W GU10 927 36D	750 cd
929004248002	MAS LED spot VLE D 3.7-50W GU10 930 36D	750 cd
929004248102	MAS LED spot VLE D 3.7-50W GU10 940 36D	800 cd
929004248202	MAS LED spot VLE D 3.7-50W GU10 927 60D	400 cd
929004248302	MAS LED spot VLE D 3.7-50W GU10 930 60D	400 cd
929004248402	MAS LED spot VLE D 3.7-50W GU10 940 60D	420 cd

MASTER VALUE LEDspot MV

Order Code	Full Product Name	Ljusstyrka (nom)
929004247952	MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	750 cd
929004248052	MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	750 cd
929004256202	MAS LED spot VLE D 650lm GU10 930 120D	220 cd

Order Code	Full Product Name	Ljusstyrka (nom)
929004256302	MAS LED spot VLE D 680lm GU10 940 120D	220 cd
929004256402	MAS LED spot VLE D 680lm GU10 965 120D	220 cd

Drift och elektricitet

Order Code	Full Product Name	Line	Motsvarande	
		Frequency	Effektförbrukning	effekt
929004255702	MAS LED spot VLE DT 5.5-80W GU10 927 36D	-	5,5 W	80 W
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	-	5,5 W	80 W
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	-	5,5 W	80 W
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	-	5,5 W	80 W
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	-	5,5 W	80 W
929001348302	MAS LED spot VLE D 3.7-35W GU10 930 36D	50 to 60 Hz	3,7 W	35 W
929001348902	MAS LED spot VLE D 4.9-50W GU10 930 36D	50 to 60 Hz	4,9 W	50 W
929001349102	MAS LED spot VLE D 4.9-50W GU10 927 60D	50 to 60 Hz	4,9 W	50 W
929001349202	MAS LED spot VLE D 4.9-50W GU10 930 60D	50 to 60 Hz	4,9 W	50 W
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	50 to 60 Hz	4,9 W	50 W
929002979402	MAS LED spot VLE D 3.7-35W GU10 927 36D	50 to 60 Hz	3,7 W	35 W
929002979702	MAS LED spot VLE DT 3.7-35W GU10 927 36D	50 to 60 Hz	3,7 W	35 W
929004247102	MAS LED spot VLE DT 2.8-35W GU10 927 36D	-	2,8 W	35 W
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	-	3,7 W	50 W
929004247302	MAS LED spot VLE D 2.8-35W GU10 927 36D	-	2,8 W	35 W

Order Code	Full Product Name	Line	Motsvarande	
		Frequency	Effektförbrukning	effekt
929004247402	MAS LED spot VLE D 2.8-35W GU10 930 36D	-	2,8 W	35 W
929004247502	MAS LED spot VLE D 2.8-35W GU10 940 36D	-	2,8 W	35 W
929004247602	MAS LED spot VLE D 2.8-35W GU10 927 60D	-	2,8 W	35 W
929004247902	MAS LED spot VLE D 3.7-50W GU10 927 36D	-	3,7 W	50 W
929004248002	MAS LED spot VLE D 3.7-50W GU10 930 36D	-	3,7 W	50 W
929004248102	MAS LED spot VLE D 3.7-50W GU10 940 36D	-	3,7 W	50 W
929004248202	MAS LED spot VLE D 3.7-50W GU10 927 60D	-	3,7 W	50 W
929004248302	MAS LED spot VLE D 3.7-50W GU10 930 60D	-	3,7 W	50 W
929004248402	MAS LED spot VLE D 3.7-50W GU10 940 60D	-	3,7 W	50 W
929004247952	MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	-	3,7 W	50 W
929004248052	MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	-	3,7 W	50 W
929004256202	MAS LED spot VLE D 650lm GU10 930 120D	-	5,5 W	-
929004256302	MAS LED spot VLE D 680lm GU10 940 120D	-	5,5 W	-
929004256402	MAS LED spot VLE D 680lm GU10 965 120D	-	5,5 W	-

MASTER VALUE LEDspot MV

Temperatur

Order Code	Full Product Name	T-Case max. (nom)
929004255702	MAS LED spot VLE DT 5.5-80W GU10 927 36D	66 °C
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	66 °C
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	66 °C
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	66 °C
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	66 °C
929001348302	MAS LED spot VLE D 3.7-35W GU10 930 36D	80 °C
929001348902	MAS LED spot VLE D 4.9-50W GU10 930 36D	80 °C
929001349102	MAS LED spot VLE D 4.9-50W GU10 927 60D	80 °C
929001349202	MAS LED spot VLE D 4.9-50W GU10 930 60D	80 °C
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	80 °C
929002979402	MAS LED spot VLE D 3.7-35W GU10 927 36D	70 °C
929002979702	MAS LED spot VLE DT 3.7-35W GU10 927 36D	70 °C
929004247102	MAS LED spot VLE DT 2.8-35W GU10 927 36D	52 °C
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	60 °C
929004247302	MAS LED spot VLE D 2.8-35W GU10 927 36D	50 °C

Order Code	Full Product Name	T-Case max. (nom)
929004247402	MAS LED spot VLE D 2.8-35W GU10 930 36D	50 °C
929004247502	MAS LED spot VLE D 2.8-35W GU10 940 36D	50 °C
929004247602	MAS LED spot VLE D 2.8-35W GU10 927 60D	50 °C
929004247902	MAS LED spot VLE D 3.7-50W GU10 927 36D	66 °C
929004248002	MAS LED spot VLE D 3.7-50W GU10 930 36D	66 °C
929004248102	MAS LED spot VLE D 3.7-50W GU10 940 36D	66 °C
929004248202	MAS LED spot VLE D 3.7-50W GU10 927 60D	62 °C
929004248302	MAS LED spot VLE D 3.7-50W GU10 930 60D	62 °C
929004248402	MAS LED spot VLE D 3.7-50W GU10 940 60D	62 °C
929004247952	MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	66 °C
929004248052	MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	66 °C
929004256202	MAS LED spot VLE D 650lm GU10 930 120D	66 °C
929004256302	MAS LED spot VLE D 680lm GU10 940 120D	66 °C
929004256402	MAS LED spot VLE D 680lm GU10 965 120D	66 °C

Mekanik och armaturhus

Order Code	Full Product Name	Ljuskällans ytbehandling
929004255702	MAS LED spot VLE DT 5.5-80W GU10 927 36D	Klar
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	Klar
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	Klar
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	Klar
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	Klar
929001348302	MAS LED spot VLE D 3.7-35W GU10 930 36D	-
929001348902	MAS LED spot VLE D 4.9-50W GU10 930 36D	-
929001349102	MAS LED spot VLE D 4.9-50W GU10 927 60D	-
929001349202	MAS LED spot VLE D 4.9-50W GU10 930 60D	-
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	-
929002979402	MAS LED spot VLE D 3.7-35W GU10 927 36D	-
929002979702	MAS LED spot VLE DT 3.7-35W GU10 927 36D	-
929004247102	MAS LED spot VLE DT 2.8-35W GU10 927 36D	Klar
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	Klar
929004247302	MAS LED spot VLE D 2.8-35W GU10 927 36D	Klar

Order Code	Full Product Name	Ljuskällans ytbehandling
929004247402	MAS LED spot VLE D 2.8-35W GU10 930 36D	Klar
929004247502	MAS LED spot VLE D 2.8-35W GU10 940 36D	Klar
929004247602	MAS LED spot VLE D 2.8-35W GU10 927 60D	Klar
929004247902	MAS LED spot VLE D 3.7-50W GU10 927 36D	Klar
929004248002	MAS LED spot VLE D 3.7-50W GU10 930 36D	Klar
929004248102	MAS LED spot VLE D 3.7-50W GU10 940 36D	Klar
929004248202	MAS LED spot VLE D 3.7-50W GU10 927 60D	Klar
929004248302	MAS LED spot VLE D 3.7-50W GU10 930 60D	Klar
929004248402	MAS LED spot VLE D 3.7-50W GU10 940 60D	Klar
929004247952	MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	Klar
929004248052	MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	Klar
929004256202	MAS LED spot VLE D 650lm GU10 930 120D	Frostad
929004256302	MAS LED spot VLE D 680lm GU10 940 120D	Frostad
929004256402	MAS LED spot VLE D 680lm GU10 965 120D	Frostad

Användning och godkännande


Order Code	Full Product Name	Omgivningstemperatur	Energiförbrukning kWh/1 000 tim
929004255702	MAS LED spot VLE DT 5.5-80W GU10 927 36D	-20 till +45 °C	6 kWh
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	-20 till +45 °C	6 kWh
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	-20 till +45 °C	6 kWh
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	-20 till +45 °C	6 kWh



Order Code	Full Product Name	Omgivningstemperatur	Energiförbrukning kWh/1 000 tim
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	-20 till +45 °C	6 kWh
929001348302	MAS LED spot VLE D 3.7-35W GU10 930 36D	-	4 kWh
929001348902	MAS LED spot VLE D 4.9-50W GU10 930 36D	-	5 kWh

MASTER VALUE LEDspot MV











			Energiförbrukning
Order Code	Full Product Name	Omgivningstemperatur	kWh/1 000 tim
929001349102	MAS LED spot VLE D 4.9-50W GU10 927 60D	-	5 kWh
929001349202	MAS LED spot VLE D 4.9-50W GU10 930 60D	-	5 kWh
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	-	5 kWh
929002979402	MAS LED spot VLE D 3.7-35W GU10 927 36D	-	4 kWh
929002979702	MAS LED spot VLE DT 3.7-35W GU10 927 36D	-	4 kWh
929004247102	MAS LED spot VLE DT 2.8-35W GU10 927 36D	-20 till +45 °C	3 kWh
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	-20 till +45 °C	4 kWh
929004247302	MAS LED spot VLE D 2.8-35W GU10 927 36D	-20 till +45 °C	3 kWh
929004247402	MAS LED spot VLE D 2.8-35W GU10 930 36D	-20 till +45 °C	3 kWh
929004247502	MAS LED spot VLE D 2.8-35W GU10 940 36D	-20 till +45 °C	3 kWh
929004247602	MAS LED spot VLE D 2.8-35W GU10 927 60D	-20 till +45 °C	3 kWh
929004247902	MAS LED spot VLE D 3.7-50W GU10 927 36D	-20 till +45 °C	4 kWh
929004248002	MAS LED spot VLE D 3.7-50W GU10 930 36D	-20 till +45 °C	4 kWh
929004248102	MAS LED spot VLE D 3.7-50W GU10 940 36D	-20 till +45 °C	4 kWh
929004248202	MAS LED spot VLE D 3.7-50W GU10 927 60D	-20 till +45 °C	4 kWh
929004248302	MAS LED spot VLE D 3.7-50W GU10 930 60D	-20 till +45 °C	4 kWh
929004248402	MAS LED spot VLE D 3.7-50W GU10 940 60D	-20 till +45 °C	4 kWh
929004247952	MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	-20 till +45 °C	4 kWh
929004248052	MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	-20 till +45 °C	4 kWh
929004256202	MAS LED spot VLE D 650lm GU10 930 120D	-20 till +45 °C	6 kWh

			Energiförbrukning
Order Code	Full Product Name	Omgivningstemperatur	kWh/1 000 tim
929004256302	MAS LED spot VLE D 680lm GU10 940 120D	-20 till +45 °C	6 kWh
929004256402	MAS LED spot VLE D 680lm GU10 965 120D	-20 till +45 °C	6 kWh








MASTER VALUE LEDspot MV




MASTER VALUE LEDspot MV




Accent Diagrams




Accent Diagram - MAS LED spot VLE D 2.8-35W GU10 930 36D




Accent Diagram - MAS LED spot VLE DT 4.9-50W GU10 927 36D




Accent Diagram - MAS LED spot VLE D 3.7-35W GU10 930 36D



Accent Diagram - MAS LED spot VLE D 4.9-50W GU10 930 36D




Accent Diagram - MAS LED spot VLE D 4.9-50W GU10 927 60D




Accent Diagram - MAS LED spot VLE DT 3.7-35W GU10 927 36D


Accent Diagrams




Accent Diagram - MAS LED spot VLE D 5.5-80W
GU10 927 36D




Accent Diagram - MAS LED spot VLE DT
5.5-80W GU10 927 36D




Accent Diagram - MAS LED spot VLE D 5.5-80W
GU10 965 36D




Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 927 60D




Accent Diagram - MAS LED spot VLE D 2.8-35W
GU10 940 36D




Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 940 36D



Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 930 36D




Accent Diagram - MAS LED spot VLE D 3.7-35W
GU10 927 36D




Accent Diagram - MAS LEDspot VLE D 3.7-50W
GU10 92736D5CT


Accent Diagrams




Accent Diagram - MAS LED spot VLE D 2.8-35W
GU10 927 36D




Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 940 60D




Accent Diagram - MAS LED spot VLE D 2.8-35W
GU10 927 60D



Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 930 60D




Accent Diagram - MAS LED spot VLE DT
2.8-35W GU10 927 36D




Accent Diagram - MAS LED spot VLE DT
3.7-50W GU10 927 36D


Beam Diagrams



Beam diagram - MAS LED spot VLE DT 5.5-80W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 3.7-35W
GU10 927 36D




Beam diagram - MAS LED spot VLE DT 4.9-50W
GU10 927 36D


Beam Diagrams




Beam diagram - MAS LED spot VLE D 3.7-35W
GU10 930 36D




Beam diagram - MAS LED spot VLE D 4.9-50W
GU10 930 36D




Beam diagram - MAS LED spot VLE D 4.9-50W
GU10 927 60D




Beam diagram - MAS LED spot VLE D 2.8-35W
GU10 940 36D




Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 940 36D




Beam diagram - MAS LED spot VLE D 2.8-35W
GU10 927 60D



Beam diagram - MAS LED spot VLE DT 2.8-35W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 2.8-35W
GU10 930 36D




Beam diagram - MAS LED spot VLE D 5.5-80W
GU10 965 36D


Beam Diagrams




Beam diagram - MAS LED spot VLE DT 3.7-35W
GU10 927 36D




Beam diagram - MAS LEDspot VLE D 3.7-50W
GU10 92736D5CT




Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 927 60D




Beam diagram - MAS LED spot VLE D 5.5-80W
GU10 927 36D




Beam diagram - MAS LED spot VLE DT 3.7-50W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 930 60D



Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 940 60D



Beam diagram - MAS LED spot VLE D 2.8-35W
GU10 927 36D



Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 930 36D

MASTER VALUE LEDspot MV

