



A small and sustainable pendant in a sleek, subtle design

GreenSpace Evo Mini Pendant

GreenSpace Evo Mini Pendant is a sustainable lighting pendant that comes with a sleek and subtle design. This makes the pendant an ideal choice for hospitality and fashion retail applications. The 3D printed housing is crafted from at least 65% recycled or bio-circular materials, while the heatsink is made from 85% recycled aluminium. Because of its circular design, the luminaire is upgradable, reusable, fully serviceable and recyclable. Combined with the high energy efficiency, this makes the GreenSpace Evo Mini pendant a sustainable choice. The new PerfectAccent deep reflectors ensure a light effect with increased sparkle and improved shopper eye comfort. Further customization of colors and textures is possible via Philips MyCreation

Benefits

- The sleek and subtle design fits perfectly in any installation
- More sparkle and enhanced shopper eye comfort with PerfectAccent deep reflectors
- Extend the useful life of the product with easy serviceability and upgradeability
- The recycled materials and high energy efficiency help further reduce the carbon footprint of the product

GreenSpace Evo Mini Pendant

Features

- Easy access to the optics, LED and front glass
- Serviceable and upgradeable with standard tools
- Reduced carbon footprint due to high efficacy
- Equipped with state-of-the-art PerfectAccent deep reflectors
- Connectivity options: Interact compatible DALI (DIA) and Wireless (WIA)
- Optional front glass (recommended for dusty environments)

Application

- Fashion
- Hospitality
- Residential

Warnings and Safety

- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For food preparation areas and areas with high levels of dust, the use of the optional front glass is strongly advised, as it can be cleaned with a (dry) microfiber cloth
- During maintenance, the product must be switched off and cooled down

Versions



PT332B GreenSpace Evo Mini
Pendant Recessed - Grey



PT332B GreenSpace Evo Mini
Pendant Recessed - White



PT332C GreenSpace Evo Mini
Pendant Surface mount - Black



PT332C GreenSpace Evo Mini
Pendant Surface mount - Grey

GreenSpace Evo Mini Pendant

Versions



PT332T GreenSpace Evo Mini
Pendant Track - Grey



PT332T GreenSpace Evo Mini
Pendant Track - White






PT332B GreenSpace Evo Mini
Pendant Recessed - Black with
White canopy



PT332C GreenSpace Evo Mini
Pendant Surface mount - White

Dimensional drawing



GreenSpace Evo Mini Pendant

General Information	
Driver included	Yes
Number of gear units	1 unit
Light Technical	
Color rendering index (CRI)	>90
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable
Controls and Dimming	
Embedded control	-
Mechanical and Housing	
Explosion hazard class	-
Mech. impact protection code	IK02
Ingress protection code	IP20
Emergency Operation	
Central Emergency	No
Emergency lighting	-
Approval and Application	
Ambient temperature range	+10 to +35 °C
CE mark	Yes
ENEC mark	-
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated	Luminous		Optic type
		Color Temperature (Nom)	Efficacy (rated) (Nom)	Luminous Flux	
910505104945	PT332B 12S/PW930 PSU-E HMB GR 68 BK WH	3000 K	121 lm/W	1,200 lm	High-reflective metal reflector Medium beam 20 to 40 degrees
910505104926	PT332T 12S/PW940 PSU HWB BK	4000 K	124 lm/W	1,200 lm	High-reflective metal reflector Wide beam 40 to 80 degrees
910505104929	PT332T 17S/PW930 DIA HVWB BK	3000 K	128 lm/W	1,700 lm	High-reflective metal reflector very wide beam >80 degrees
910505104931	PT332T 22S/PC930 PSU HMB BK	3000 K	117 lm/W	2,200 lm	High-reflective metal reflector Medium beam 20 to 40 degrees
910505104933	PT332T 27S/PW930 PSU HWB BK	3000 K	144 lm/W	2,700 lm	High-reflective metal reflector Wide beam 40 to 80 degrees
910505104943	PT332B 12S/PC930 PSU-E HWB WH 68 WH WH	3000 K	121 lm/W	1,200 lm	High-reflective metal reflector Wide beam 40 to 80 degrees
910505104946	PT332B 17S/PW930 PSU-E HWB WH 68 WH WH	3000 K	144 lm/W	1,700 lm	High-reflective metal reflector Wide beam 40 to 80 degrees
910505104948	PT332B 22S/PW940 PSU-E HWB WH 68 WH WH	4000 K	124 lm/W	2,200 lm	High-reflective metal reflector Wide beam 40 to 80 degrees
910505104950	PT332B 27S/PW940 WIA-E HWB WH 68 WH WH	4000 K	135 lm/W	2,700 lm	High-reflective metal reflector Wide beam 40 to 80 degrees
910505104938	PT332C 17S/PW930 DIA HVWB BK BK BK	3000 K	143 lm/W	1,700 lm	High-reflective metal reflector very wide beam >80 degrees
910505104942	PT332C 27S/PW930 PSU HWB BK BK BK	3000 K	135 lm/W	2,700 lm	High-reflective metal reflector Wide beam 40 to 80 degrees
910505104936	PT332C 12S/PW930 PSU HMB GR BK GR	3000 K	121 lm/W	1,200 lm	High-reflective metal reflector Medium beam 20 to 40 degrees
910505104935	PT332C 12S/PW940 PSU HWB BK BK WH	4000 K	121 lm/W	1,200 lm	High-reflective metal reflector Wide beam 40 to 80 degrees
910505104940	PT332C 22S/PC930 PSU HMB BK BK WH	3000 K	110 lm/W	2,200 lm	High-reflective metal reflector Medium beam 20 to 40 degrees
910505104947	PT332B 17S/PW930 DIA-E HVWB BK 68 BK BK	3000 K	143 lm/W	1,700 lm	High-reflective metal reflector very wide beam >80 degrees
910505104951	PT332B 27S/PW930 PSU-E HWB BK 68 BK BK	3000 K	135 lm/W	2,700 lm	High-reflective metal reflector Wide beam 40 to 80 degrees

GreenSpace Evo Mini Pendant

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910505104927	PT332T 12S/PW930 PSU HMB FG GR	3000 K	124 lm/W	1,200 lm	High-reflective metal reflector Medium beam 20 to 40 degrees
910505104925	PT332T 12S/PC930 PSU HWB WH	3000 K	124 lm/W	1,200 lm	High-reflective metal reflector Wide beam 40 to 80 degrees
910505104928	PT332T 17S/PW930 PSU HWB WH	3000 K	145 lm/W	1,700 lm	High-reflective metal reflector Wide beam 40 to 80 degrees
910505104930	PT332T 22S/PW940 PSU HWB WH	4000 K	131 lm/W	2,200 lm	High-reflective metal reflector Wide beam 40 to 80 degrees
910505104932	PT332T 27S/PW940 WIA HWB WH	4000 K	122 lm/W	2,700 lm	High-reflective metal reflector Wide beam 40 to 80 degrees
910505104944	PT332B 12S/PW940 PSU-E HWB BK 68 BK WH	4000 K	121 lm/W	1,200 lm	High-reflective metal reflector Wide beam 40 to 80 degrees
910505104949	PT332B 22S/PC930 PSU-E HMB BK 68 BK WH	3000 K	110 lm/W	2,200 lm	High-reflective metal reflector Medium beam 20 to 40 degrees
910505104934	PT332C 12S/PC930 PSU HWB WH WH WH	3000 K	121 lm/W	1,200 lm	High-reflective metal reflector Wide beam 40 to 80 degrees
910505104937	PT332C 17S/PW930 PSU HWB WH WH WH	3000 K	144 lm/W	1,700 lm	High-reflective metal reflector Wide beam 40 to 80 degrees
910505104939	PT332C 22S/PW940 PSU HWB WH WH WH	4000 K	124 lm/W	2,200 lm	High-reflective metal reflector Wide beam 40 to 80 degrees
910505104941	PT332C 27S/PW940 WIA HWB WH WH WH	4000 K	135 lm/W	2,700 lm	High-reflective metal reflector Wide beam 40 to 80 degrees

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
910505104945	PT332B 12S/PW930 PSU-E HMB GR 68 BK WH	9 W	910505104935	PT332C 12S/PW940 PSU HWB BK BK WH	9 W
910505104926	PT332T 12S/PW940 PSU HWB BK	9 W	910505104940	PT332C 22S/PC930 PSU HMB BK BK WH	20 W
910505104929	PT332T 17S/PW930 DIA HVWB BK	13 W	910505104947	PT332B 17S/PW930 DIA-E HVWB BK 68 BK BK	11 W
910505104931	PT332T 22S/PC930 PSU HMB BK	18 W	910505104951	PT332B 27S/PW930 PSU-E HWB BK 68 BK BK	20 W
910505104933	PT332T 27S/PW930 PSU HWB BK	18 W	910505104927	PT332T 12S/PW930 PSU HMB FG GR	9 W
910505104943	PT332B 12S/PC930 PSU-E HWB WH 68 WH WH	9 W	910505104925	PT332T 12S/PC930 PSU HWB WH	9 W
910505104946	PT332B 17S/PW930 PSU-E HWB WH 68 WH WH	11 W	910505104928	PT332T 17S/PW930 PSU HWB WH	11 W
910505104948	PT332B 22S/PW940 PSU-E HWB WH 68 WH WH	17 W	910505104930	PT332T 22S/PW940 PSU HWB WH	16 W
910505104950	PT332B 27S/PW940 WIA-E HWB WH 68 WH WH	20 W	910505104932	PT332T 27S/PW940 WIA HWB WH	22 W
910505104938	PT332C 17S/PW930 DIA HVWB BK BK BK	11 W	910505104944	PT332B 12S/PW940 PSU-E HWB BK 68 BK WH	9 W
910505104942	PT332C 27S/PW930 PSU HWB BK BK BK	20 W	910505104949	PT332B 22S/PC930 PSU-E HMB BK 68 BK WH	20 W
910505104936	PT332C 12S/PW930 PSU HMB GR BK GR	9 W	910505104934	PT332C 12S/PC930 PSU HWB WH WH WH	9 W

GreenSpace Evo Mini Pendant

Order Code	Full Product Name	Power Consumption
910505104937	PT332C 17S/PW930 PSU HWB WH WH WH	11 W
910505104939	PT332C 22S/PW940 PSU HWB WH WH WH	17 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
910505104945	PT332B 12S/PW930 PSU-E HMB GR 68 BK WH	-
910505104926	PT332T 12S/PW940 PSU HWB BK	-
910505104929	PT332T 17S/PW930 DIA HVWB BK	DALI
910505104931	PT332T 22S/PC930 PSU HMB BK	-
910505104933	PT332T 27S/PW930 PSU HWB BK	-
910505104943	PT332B 12S/PC930 PSU-E HWB WH 68 WH WH	-
910505104946	PT332B 17S/PW930 PSU-E HWB WH 68 WH WH	-
910505104948	PT332B 22S/PW940 PSU-E HWB WH 68 WH WH	-
910505104950	PT332B 27S/PW940 WIA-E HWB WH 68 WH WH	Wireless Dim
910505104938	PT332C 17S/PW930 DIA HVWB BK BK BK	DALI
910505104942	PT332C 27S/PW930 PSU HWB BK BK BK	-
910505104936	PT332C 12S/PW930 PSU HMB GR BK GR	-
910505104935	PT332C 12S/PW940 PSU HWB BK BK WH	-
910505104940	PT332C 22S/PC930 PSU HMB BK BK WH	-

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910505104945	PT332B 12S/PW930 PSU-E HMB GR 68 BK WH	Grey
910505104926	PT332T 12S/PW940 PSU HWB BK	Black
910505104929	PT332T 17S/PW930 DIA HVWB BK	Black
910505104931	PT332T 22S/PC930 PSU HMB BK	Black
910505104933	PT332T 27S/PW930 PSU HWB BK	Black
910505104943	PT332B 12S/PC930 PSU-E HWB WH 68 WH WH	White
910505104946	PT332B 17S/PW930 PSU-E HWB WH 68 WH WH	White
910505104948	PT332B 22S/PW940 PSU-E HWB WH 68 WH WH	White
910505104950	PT332B 27S/PW940 WIA-E HWB WH 68 WH WH	White
910505104938	PT332C 17S/PW930 DIA HVWB BK BK BK	Black
910505104942	PT332C 27S/PW930 PSU HWB BK BK BK	Black
910505104936	PT332C 12S/PW930 PSU HMB GR BK GR	Grey
910505104935	PT332C 12S/PW940 PSU HWB BK BK WH	Black
910505104940	PT332C 22S/PC930 PSU HMB BK BK WH	Black

Approval and Application

Order Code	Full Product Name	Stroboscopic effect visibility measure (SVM)
910505104945	PT332B 12S/PW930 PSU-E HMB GR 68 BK WH	0.4
910505104926	PT332T 12S/PW940 PSU HWB BK	0.4
910505104929	PT332T 17S/PW930 DIA HVWB BK	0.4
910505104931	PT332T 22S/PC930 PSU HMB BK	0.4
910505104933	PT332T 27S/PW930 PSU HWB BK	0.4
910505104943	PT332B 12S/PC930 PSU-E HWB WH 68 WH WH	0.4
910505104946	PT332B 17S/PW930 PSU-E HWB WH 68 WH WH	0.4

Order Code	Full Product Name	Power Consumption
910505104941	PT332C 27S/PW940 WIA HWB WH WH WH	20 W

Order Code	Full Product Name	Dimmable
910505104947	PT332B 17S/PW930 DIA-E HVWB BK 68 BK BK	DALI
910505104951	PT332B 27S/PW930 PSU-E HWB BK 68 BK BK	-
910505104927	PT332T 12S/PW930 PSU HMB FG GR	-
910505104925	PT332T 12S/PC930 PSU HWB WH	-
910505104928	PT332T 17S/PW930 PSU HWB WH	-
910505104930	PT332T 22S/PW940 PSU HWB WH	-
910505104932	PT332T 27S/PW940 WIA HWB WH	Wireless Dim
910505104944	PT332B 12S/PW940 PSU-E HWB BK 68 BK WH	-
910505104949	PT332B 22S/PC930 PSU-E HMB BK 68 BK WH	-
910505104934	PT332C 12S/PC930 PSU HWB WH WH WH	-
910505104937	PT332C 17S/PW930 PSU HWB WH WH WH	-
910505104939	PT332C 22S/PW940 PSU HWB WH WH WH	-
910505104941	PT332C 27S/PW940 WIA HWB WH WH WH	Wireless Dim

Order Code	Full Product Name	Housing Color
910505104947	PT332B 17S/PW930 DIA-E HVWB BK 68 BK BK	Black
910505104951	PT332B 27S/PW930 PSU-E HWB BK 68 BK BK	Black
910505104927	PT332T 12S/PW930 PSU HMB FG GR	Grey
910505104925	PT332T 12S/PC930 PSU HWB WH	White
910505104928	PT332T 17S/PW930 PSU HWB WH	White
910505104930	PT332T 22S/PW940 PSU HWB WH	White
910505104932	PT332T 27S/PW940 WIA HWB WH	White
910505104944	PT332B 12S/PW940 PSU-E HWB BK 68 BK WH	Black
910505104949	PT332B 22S/PC930 PSU-E HMB BK 68 BK WH	Black
910505104934	PT332C 12S/PC930 PSU HWB WH WH WH	White
910505104937	PT332C 17S/PW930 PSU HWB WH WH WH	White
910505104939	PT332C 22S/PW940 PSU HWB WH WH WH	White
910505104941	PT332C 27S/PW940 WIA HWB WH WH WH	White

Order Code	Full Product Name	Stroboscopic effect visibility measure (SVM)
910505104948	PT332B 22S/PW940 PSU-E HWB WH 68 WH WH	0.4
910505104950	PT332B 27S/PW940 WIA-E HWB WH 68 WH WH	0.5
910505104938	PT332C 17S/PW930 DIA HVWB BK BK BK	0.4
910505104942	PT332C 27S/PW930 PSU HWB BK BK BK	0.4
910505104936	PT332C 12S/PW930 PSU HMB GR BK GR	0.4
910505104935	PT332C 12S/PW940 PSU HWB BK BK WH	0.4
910505104940	PT332C 22S/PC930 PSU HMB BK BK WH	0.4

GreenSpace Evo Mini Pendant

Order Code	Full Product Name	Stroboscopic effect visibility measure (SVM)
910505104947	PT332B 17S/PW930 DIA-E HVWB BK 68 BK BK	0.4
910505104951	PT332B 27S/PW930 PSU-E HWB BK 68 BK BK	0.4
910505104927	PT332T 12S/PW930 PSU HMB FG GR	0.4
910505104925	PT332T 12S/PC930 PSU HWB WH	0.4
910505104928	PT332T 17S/PW930 PSU HWB WH	0.4
910505104930	PT332T 22S/PW940 PSU HWB WH	0.4
910505104932	PT332T 27S/PW940 WIA HWB WH	0.4

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505104945	PT332B 12S/PW930 PSU-E HMB GR 68 BK WH	(0.422, 0.386)
910505104926	PT332T 12S/PW940 PSU HWB BK	(0.374, 0.364)
910505104929	PT332T 17S/PW930 DIA HVWB BK	(0.422, 0.386)
910505104931	PT332T 22S/PC930 PSU HMB BK	(0.422, 0.386)
910505104933	PT332T 27S/PW930 PSU HWB BK	(0.422, 0.386)
910505104943	PT332B 12S/PC930 PSU-E HWB WH 68 WH WH	(0.422, 0.386)
910505104946	PT332B 17S/PW930 PSU-E HWB WH 68 WH WH	(0.422, 0.386)
910505104948	PT332B 22S/PW940 PSU-E HWB WH 68 WH WH	(0.374, 0.364)
910505104950	PT332B 27S/PW940 WIA-E HWB WH 68 WH WH	(0.374, 0.364)
910505104938	PT332C 17S/PW930 DIA HVWB BK BK BK	(0.422, 0.386)
910505104942	PT332C 27S/PW930 PSU HWB BK BK BK	(0.422, 0.386)
910505104936	PT332C 12S/PW930 PSU HMB GR BK GR	(0.422, 0.386)
910505104935	PT332C 12S/PW940 PSU HWB BK BK WH	(0.374, 0.364)
910505104940	PT332C 22S/PC930 PSU HMB BK BK WH	(0.422, 0.386)

Product Data


Order Code	Full Product Name	Product family code
910505104945	PT332B 12S/PW930 PSU-E HMB GR 68 BK WH	PT332B
910505104926	PT332T 12S/PW940 PSU HWB BK	PT332T
910505104929	PT332T 17S/PW930 DIA HVWB BK	PT332T
910505104931	PT332T 22S/PC930 PSU HMB BK	PT332T
910505104933	PT332T 27S/PW930 PSU HWB BK	PT332T
910505104943	PT332B 12S/PC930 PSU-E HWB WH 68 WH WH	PT332B
910505104946	PT332B 17S/PW930 PSU-E HWB WH 68 WH WH	PT332B
910505104948	PT332B 22S/PW940 PSU-E HWB WH 68 WH WH	PT332B
910505104950	PT332B 27S/PW940 WIA-E HWB WH 68 WH WH	PT332B
910505104938	PT332C 17S/PW930 DIA HVWB BK BK BK	PT332C
910505104942	PT332C 27S/PW930 PSU HWB BK BK BK	PT332C
910505104936	PT332C 12S/PW930 PSU HMB GR BK GR	PT332C
910505104935	PT332C 12S/PW940 PSU HWB BK BK WH	PT332C
910505104940	PT332C 22S/PC930 PSU HMB BK BK WH	PT332C

Order Code	Full Product Name	Stroboscopic effect visibility measure (SVM)
910505104944	PT332B 12S/PW940 PSU-E HWB BK 68 BK WH	0.4
910505104949	PT332B 22S/PC930 PSU-E HMB BK 68 BK WH	0.4
910505104934	PT332C 12S/PC930 PSU HWB WH WH WH	0.4
910505104937	PT332C 17S/PW930 PSU HWB WH WH WH	0.4
910505104939	PT332C 22S/PW940 PSU HWB WH WH WH	0.4
910505104941	PT332C 27S/PW940 WIA HWB WH WH WH	0.5


Order Code	Full Product Name	Initial chromaticity
910505104947	PT332B 17S/PW930 DIA-E HVWB BK 68 BK BK	(0.422, 0.386)
910505104951	PT332B 27S/PW930 PSU-E HWB BK 68 BK BK	(0.422, 0.386)
910505104927	PT332T 12S/PW930 PSU HMB FG GR	(0.422, 0.386)
910505104925	PT332T 12S/PC930 PSU HWB WH	(0.422, 0.386)
910505104928	PT332T 17S/PW930 PSU HWB WH	(0.422, 0.386)
910505104930	PT332T 22S/PW940 PSU HWB WH	(0.374, 0.364)
910505104932	PT332T 27S/PW940 WIA HWB WH	(0.374, 0.364)
910505104944	PT332B 12S/PW940 PSU-E HWB BK 68 BK WH	(0.374, 0.364)
910505104949	PT332B 22S/PC930 PSU-E HMB BK 68 BK WH	(0.422, 0.386)
910505104934	PT332C 12S/PC930 PSU HWB WH WH WH	(0.422, 0.386)
910505104937	PT332C 17S/PW930 PSU HWB WH WH WH	(0.422, 0.386)
910505104939	PT332C 22S/PW940 PSU HWB WH WH WH	(0.374, 0.364)
910505104941	PT332C 27S/PW940 WIA HWB WH WH WH	(0.374, 0.364)

Order Code	Full Product Name	Product family code
910505104947	PT332B 17S/PW930 DIA-E HVWB BK 68 BK BK	PT332B
910505104951	PT332B 27S/PW930 PSU-E HWB BK 68 BK BK	PT332B
910505104927	PT332T 12S/PW930 PSU HMB FG GR	PT332T
910505104925	PT332T 12S/PC930 PSU HWB WH	PT332T
910505104928	PT332T 17S/PW930 PSU HWB WH	PT332T
910505104930	PT332T 22S/PW940 PSU HWB WH	PT332T
910505104932	PT332T 27S/PW940 WIA HWB WH	PT332T
910505104944	PT332B 12S/PW940 PSU-E HWB BK 68 BK WH	PT332B
910505104949	PT332B 22S/PC930 PSU-E HMB BK 68 BK WH	PT332B
910505104934	PT332C 12S/PC930 PSU HWB WH WH WH	PT332C
910505104937	PT332C 17S/PW930 PSU HWB WH WH WH	PT332C
910505104939	PT332C 22S/PW940 PSU HWB WH WH WH	PT332C
910505104941	PT332C 27S/PW940 WIA HWB WH WH WH	PT332C


Polar Wide Diagrams




Polar Normal (separate) - PT332TI - 910505104942




Polar Normal (separate) - PT332TI - 910505104936




Polar Normal (separate) - PT332TI - 910505104925




Polar Normal (separate) - PT332TI - 910505104937




Polar Normal (separate) - PT332TI - 910505104926




Polar Normal (separate) - PT332TI - 910505104927



Polar Normal (separate) - PT332TI - 910505104950




Polar Normal (separate) - PT332TI - 910505104940




Polar Normal (separate) - PT332TI - 910505104932


Polar Wide Diagrams




Polar Normal (separate) - PT332TI - 910505104928




Polar Normal (separate) - PT332TI - 910505104933




Polar Normal (separate) - PT332TI - 910505104948




Polar Normal (separate) - PT332TI - 910505104929




Polar Normal (separate) - PT332TI - 910505104949




Polar Normal (separate) - PT332TI - 910505104943



Polar Normal (separate) - PT332TI - 910505104939




Polar Normal (separate) - PT332TI - 910505104938




Polar Normal (separate) - PT332TI - 910505104947


Polar Wide Diagrams




Polar Normal (separate) - PT332TI - 910505104930




Polar Normal (separate) - PT332TI - 910505104951




Polar Normal (separate) - PT332TI - 910505104935




Polar Normal (separate) - PT332TI - 910505104945




Polar Normal (separate) - PT332TI - 910505104944




Polar Normal (separate) - PT332TI - 910505104934



Polar Normal (separate) - PT332TI - 910505104941



Polar Normal (separate) - PT332TI - 910505104946



Polar Normal (separate) - PT332TI - 910505104931

GreenSpace Evo Mini Pendant

