



Reliable non-maintained emergency light

Emergency Light LED Pathfinder

Safety is important for building owners, and therefore having proper emergency lighting in place is a major concern for them. The Emergency pathfinder offers an easy solution for stand-alone emergency lighting, with non-maintained mode and self-test function. The lithium battery (LiFePO4) has many advantages over nickel-based products, as it has a longer lifetime, better discharge behaviors, is produced in a more welfare friendly way and can be recycled.

Benefits

- Welfare friendly solution versus nickel-based products as the battery can be recycled.
- Lithium based battery type provides longer lifetime, low self-discharge and high temperature tolerance.

Features

- 3 hours battery duration when full charged
- Self-test function
- LFP is designed environmentally friendly
- Non-maintained mode
- Safety & reliable

Application

- Airports
- Offices
- Retail

Specifications

Emergency Light LED Pathfinder

Mounting type	Recessed
Operating Temperature range	+0 to +45 °C
Light Source	LED
Mains Voltage	220-240V/50-60Hz
Mechanical Accessories	Installation cover ring
Dimming	PSU
Emergency lighting	Emergency lighting Pro 3hrs
Material	PC
Main color of the luminaire	RAL 9003


Protection Class	class II
IEC61140	
Ingress protection	IP20
Light source replaceable	No
Driver replaceable	No
Overall diameter	95
Overall height	38.3
UGR	22
Installation	Recessed
Warranty	1 year

Versions



Emergency light LED pathfinder

Dimensional drawing



Product details



Emergency light LED pathfinder



Emergency light LED pathfinder

Emergency Light LED Pathfinder

