



# Philips SmartBright Plus Panel: Trusted performance. Everyday.

## SmartBright Plus Panel

The Philips SmartBright Plus panel (RC048B+) range features a selection of popular off-the-shelf LED luminaires that come with Philips high quality levels at a competitive price. Reliable, high energy efficient and affordable, this latest generation of SmartBright Plus LED panel lights are designed for diffuse, comfortable lighting in a wide range of general lighting applications. Our range of SmartBright Plus panel lighting is also available with accessories for easy installation on different types of ceilings – just what you need.

### Benefits

- Philips quality and reliability
- High energy saving
- Diffuse, comfortable light
- Suitable for office working place
- Diverse ceiling installation possible

### Features


- Modern, unobtrusive design
- Two lumen choices 3400 lumen & 4100 lumen for W60L60 & W30L120
- Offer 6000lm for W60L120
- Long lifetime of 50,000 hours @L60
- Energy efficient up to 130 lm/W
- Flicker free, RG0, R9
- Accessories for plaster ceiling, surface mounted and suspension available

# SmartBright Plus Panel

## Application

- Offices
- Hospitals and Care Centers
- Retail

## Dimensional drawing



# SmartBright Plus Panel

## Product details



SmartBright Plus Panel



SmartBright Plus Panel




SmartBright Plus Panel



SmartBright Plus Panel



SmartBright Plus Panel



SmartBright Plus Panel

SmartBright Plus Panel

General Information	
Gear	-
Operating and Electrical	
Protection class IEC	Safety class II
Line Frequency	50 or 60 Hz
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	White RAL 9003
Mech. impact protection code	IK02
Approval and Application	
CE mark	Yes
ENEC mark	-
Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%

General Information

Order Code	Full Product Name	Driver included	Number of gear units
911401880987	RC048B+ LED41S/840 PSU W30L120 G2	-	-
911401881087	RC048B+ LED41S/865 PSU W30L120 G2	-	-
911401845785	RC048B+ LED41S/865 PSU W603L603	Yes	1 unit
911401846185	RC048B+ LED41S/865 PSU W60L60	Yes	1 unit
911401880787	RC048B+ LED41S/840 PSU W60L60 G2	-	-
911401880887	RC048B+ LED41S/865 PSU W60L60 G2	-	-
911401881787	RC048B+ LED41S/840 PSU W603L603 G2	-	-
911401881887	RC048B+ LED41S/865 PSU W603L603 G2	-	-
911401845885	RC048B+ LED60S/840 PSU W603L1210	Yes	1 unit
911401845985	RC048B+ LED60S/865 PSU W603L1210	Yes	1 unit
911401881587	RC048B+ LED60S/840 PSU W60L120 G2	-	-
911401881687	RC048B+ LED60S/865 PSU W60L120 G2	-	-
911401881987	RC048B+ LED60S/840 PSU W603L1210 G2	-	-
911401882087	RC048B+ LED60S/865 PSU W603L1210 G2	-	-

Light Technical (1/2)

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401880987	RC048B+ LED41S/840 PSU W30L120 G2	-	4000 K	>80	130 lm/W
911401881087	RC048B+ LED41S/865 PSU W30L120 G2	-	6500 K	>80	130 lm/W
911401845785	RC048B+ LED41S/865 PSU W603L603	120 degree(s)	6500 K	80	120 lm/W
911401846185	RC048B+ LED41S/865 PSU W60L60	120 degree(s)	6500 K	80	120 lm/W
911401880787	RC048B+ LED41S/840 PSU W60L60 G2	-	4000 K	>80	130 lm/W
911401880887	RC048B+ LED41S/865 PSU W60L60 G2	-	6500 K	>80	130 lm/W
911401881787	RC048B+ LED41S/840 PSU W603L603 G2	-	4000 K	>80	130 lm/W
911401881887	RC048B+ LED41S/865 PSU W603L603 G2	-	6500 K	>80	130 lm/W
911401845885	RC048B+ LED60S/840 PSU W603L1210	120 degree(s)	4000 K	80	120 lm/W
911401845985	RC048B+ LED60S/865 PSU W603L1210	120 degree(s)	6500 K	80	120 lm/W
911401881587	RC048B+ LED60S/840 PSU W60L120 G2	-	4000 K	>80	130 lm/W
911401881687	RC048B+ LED60S/865 PSU W60L120 G2	-	6500 K	>80	130 lm/W
911401881987	RC048B+ LED60S/840 PSU W603L1210 G2	-	4000 K	>80	130 lm/W
911401882087	RC048B+ LED60S/865 PSU W603L1210 G2	-	6500 K	>80	130 lm/W

Light Technical (2/2)

SmartBright Plus Panel

Order Code	Full Product Name	Luminous Flux	Optic type
911401880987	RC048B+ LED41S/840 PSU W30L120 G2	4,100 lm	-
911401881087	RC048B+ LED41S/865 PSU W30L120 G2	4,100 lm	-
911401845785	RC048B+ LED41S/865 PSU W603L603	4,100 lm	Beam angle 120°
911401846185	RC048B+ LED41S/865 PSU W60L60	4,100 lm	Beam angle 120°
911401880787	RC048B+ LED41S/840 PSU W60L60 G2	4,100 lm	-
911401880887	RC048B+ LED41S/865 PSU W60L60 G2	4,100 lm	-
911401881787	RC048B+ LED41S/840 PSU W603L603 G2	4,100 lm	-
911401881887	RC048B+ LED41S/865 PSU W603L603 G2	4,100 lm	-

Operating and Electrical

Order Code	Full Product Name	Power		Suitable for random switching
		Input Voltage	Consumption	
911401880987	RC048B+ LED41S/840 PSU W30L120 G2	220-240 V	31.5 W	-
911401881087	RC048B+ LED41S/865 PSU W30L120 G2	220-240 V	31.5 W	-
911401845785	RC048B+ LED41S/865 PSU W603L603	220 to 240 V	34 W	Yes
911401846185	RC048B+ LED41S/865 PSU W60L60	220 to 240 V	34 W	Yes
911401880787	RC048B+ LED41S/840 PSU W60L60 G2	220-240 V	31.5 W	-
911401880887	RC048B+ LED41S/865 PSU W60L60 G2	220-240 V	31.5 W	-
911401881787	RC048B+ LED41S/840 PSU W603L603 G2	220-240 V	31.5 W	-

Controls and Dimming

Order Code	Full Product Name	Maximum dim level
911401880987	RC048B+ LED41S/840 PSU W30L120 G2	-
911401881087	RC048B+ LED41S/865 PSU W30L120 G2	-
911401845785	RC048B+ LED41S/865 PSU W603L603	Not applicable
911401846185	RC048B+ LED41S/865 PSU W60L60	Not applicable
911401880787	RC048B+ LED41S/840 PSU W60L60 G2	-
911401880887	RC048B+ LED41S/865 PSU W60L60 G2	-
911401881787	RC048B+ LED41S/840 PSU W603L603 G2	-

Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401880987	RC048B+ LED41S/840 PSU W30L120 G2	PS	IP20/40
911401881087	RC048B+ LED41S/865 PSU W30L120 G2	PS	IP20/40

Order Code	Full Product Name	Luminous Flux	Optic type
911401845885	RC048B+ LED60S/840 PSU W603L1210	6,000 lm	Beam angle 120°
911401845985	RC048B+ LED60S/865 PSU W603L1210	6,000 lm	Beam angle 120°
911401881587	RC048B+ LED60S/840 PSU W60L120 G2	6,000 lm	-
911401881687	RC048B+ LED60S/865 PSU W60L120 G2	6,000 lm	-
911401881987	RC048B+ LED60S/840 PSU W603L1210 G2	6,000 lm	-
911401882087	RC048B+ LED60S/865 PSU W603L1210 G2	6,000 lm	-

Order Code	Full Product Name	Power		Suitable for random switching
		Input Voltage	Consumption	
911401881887	RC048B+ LED41S/865 PSU W603L603 G2	220-240 V	31.5 W	-
911401845885	RC048B+ LED60S/840 PSU W603L1210	220 to 240 V	50 W	Yes
911401845985	RC048B+ LED60S/865 PSU W603L1210	220 to 240 V	50 W	Yes
911401881587	RC048B+ LED60S/840 PSU W60L120 G2	220-240 V	46 W	-
911401881687	RC048B+ LED60S/865 PSU W60L120 G2	220-240 V	46 W	-
911401881987	RC048B+ LED60S/840 PSU W603L1210 G2	220-240 V	46 W	-
911401882087	RC048B+ LED60S/865 PSU W603L1210 G2	220-240 V	46 W	-

Order Code	Full Product Name	Maximum dim level
911401881887	RC048B+ LED41S/865 PSU W603L603 G2	-
911401845885	RC048B+ LED60S/840 PSU W603L1210	Not applicable
911401845985	RC048B+ LED60S/865 PSU W603L1210	Not applicable
911401881587	RC048B+ LED60S/840 PSU W60L120 G2	-
911401881687	RC048B+ LED60S/865 PSU W60L120 G2	-
911401881987	RC048B+ LED60S/840 PSU W603L1210 G2	-
911401882087	RC048B+ LED60S/865 PSU W603L1210 G2	-

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401845785	RC048B+ LED41S/865 PSU W603L603	Opal	IP20
911401846185	RC048B+ LED41S/865 PSU W60L60	Opal	IP20

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401880787	RC048B+ LED41S/840 PSU W60L60 G2	PS	IP20/40
911401880887	RC048B+ LED41S/865 PSU W60L60 G2	PS	IP20/40
911401881787	RC048B+ LED41S/840 PSU W603L603 G2	PS	IP20/40
911401881887	RC048B+ LED41S/865 PSU W603L603 G2	PS	IP20/40
911401845885	RC048B+ LED60S/840 PSU W603L1210	Opal	IP20

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401845985	RC048B+ LED60S/865 PSU W603L1210	Opal	IP20
911401881587	RC048B+ LED60S/840 PSU W60L120 G2	PS	IP20/40
911401881687	RC048B+ LED60S/865 PSU W60L120 G2	PS	IP20/40
911401881987	RC048B+ LED60S/840 PSU W603L1210 G2	PS	IP20/40
911401882087	RC048B+ LED60S/865 PSU W603L1210 G2	PS	IP20/40

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Flammability mark	Glow-wire test
911401880987	RC048B+ LED41S/840 PSU W30L120 G2	-10 to +40 °C	-	-
911401881087	RC048B+ LED41S/865 PSU W30L120 G2	-10 to +40 °C	-	-
911401845785	RC048B+ LED41S/865 PSU W603L603	-10 to +35 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401846185	RC048B+ LED41S/865 PSU W60L60	-10 to +35 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401880787	RC048B+ LED41S/840 PSU W60L60 G2	-10 to +40 °C	-	-
911401880887	RC048B+ LED41S/865 PSU W60L60 G2	-10 to +40 °C	-	-
911401881787	RC048B+ LED41S/840 PSU W603L603 G2	-10 to +40 °C	-	-

Order Code	Full Product Name	Ambient temperature range	Flammability mark	Glow-wire test
911401881887	RC048B+ LED41S/865 PSU W603L603 G2	-10 to +40 °C	-	-
911401845885	RC048B+ LED60S/840 PSU W603L1210	-10 to +35 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401845985	RC048B+ LED60S/865 PSU W603L1210	-10 to +35 °C	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s
911401881587	RC048B+ LED60S/840 PSU W60L120 G2	-10 to +40 °C	-	-
911401881687	RC048B+ LED60S/865 PSU W60L120 G2	-10 to +40 °C	-	-
911401881987	RC048B+ LED60S/840 PSU W603L1210 G2	-10 to +40 °C	-	-
911401882087	RC048B+ LED60S/865 PSU W603L1210 G2	-10 to +40 °C	-	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401880987	RC048B+ LED41S/840 PSU W30L120 G2	-
911401881087	RC048B+ LED41S/865 PSU W30L120 G2	-
911401845785	RC048B+ LED41S/865 PSU W603L603	(0.31, 0.33) SDCM≤5
911401846185	RC048B+ LED41S/865 PSU W60L60	(0.31, 0.33) SDCM≤5
911401880787	RC048B+ LED41S/840 PSU W60L60 G2	-
911401880887	RC048B+ LED41S/865 PSU W60L60 G2	-
911401881787	RC048B+ LED41S/840 PSU W603L603 G2	-

Order Code	Full Product Name	Initial chromaticity
911401881887	RC048B+ LED41S/865 PSU W603L603 G2	-
911401845885	RC048B+ LED60S/840 PSU W603L1210	(0.38, 0.38) SDCM≤5
911401845985	RC048B+ LED60S/865 PSU W603L1210	(0.31, 0.33) SDCM≤5
911401881587	RC048B+ LED60S/840 PSU W60L120 G2	-
911401881687	RC048B+ LED60S/865 PSU W60L120 G2	-
911401881987	RC048B+ LED60S/840 PSU W603L1210 G2	-
911401882087	RC048B+ LED60S/865 PSU W603L1210 G2	-

## SmartBright Plus Panel

