



# When light really matters

## GreenPerform Panel RC099V G3

GreenPerform panel RC099V G3 is an affordable LED panel delivering comfortable light with excellent uniformity. It offers 3 types, 600x600, 300x1200, and 600x1200mm with max: 140lm/w. Its UGR19 brings more visual comfort in the office. Equipped with Dali, Interact and EcoSet, RC099V G2 offers easy connection to control system to bring better energy saving.

### Benefits

- Full range offer from 600x600, 300x1200 to 600x1200mm to cover key applications
- Low glare UGR19 to provide visual comfort
- Dali , Interact, EcoSet interface are available for system control

### Features

- System efficiency 140lm/W(max)
- 3800lm lumen output for 600x600 and 300x1200mm versions; 5400lm for 600x1200mm version
- CRI 80 and CRI90 are both available
- Higher lumen output 4800lm is available for 600\*600mm size

### Application

- Open plan office
- Public indoor area
- Meeting/training room

### Specifications

<b>Mounting type</b>	Recessed	<b>Mains Voltage</b>	220-240V / 50/60Hz
<b>Ceiling type</b>	T-Bar ceiling Concealed profile ceiling	<b>Dimming</b>	WIA: Wireless control, compatible with Interact Pro SIA: Wireless control, compatible with SNS210 sensor

# GreenPerform Panel RC099V G3

<b>Control system input</b>	Dali / WIA / SIA / EcoSet
<b>Integrated sensors</b>	SIA version with SNS210 sensor
<b>Lumen maintenance at median useful life 50.000h</b>	L70B50
<b>Luminaire efficacy</b>	140lm/w 120lm/w
<b>Correlated color temperature - CCT</b>	840 850 860 940 950 965

<b>Risk Group</b>	RG0
<b>Mechanical impact protection</b>	IK03
<b>Ingress protection</b>	IP20
<b>UGR</b>	22 19
<b>Installation</b>	Recessed
<b>Warranty</b>	5 years

## Versions



GreenPerform Panel RC099V G3

