



When light really matters

GreenPerform Panel RC099V G3

GreenPerform panel RC099V G3 is an affordable LED panel delivering comfortable light with excellent uniformity. It offers 3 types, 600x600,300x1200, and 600x1200mm with max: 140lm/w. Its UGR19 brings more visual comfort in the office. Equipped with Dali, Interact and EcoSet, RC099V G2 offers easy connection to control system to bring better energy saving.

Benefits

- Full range offer from 600x600, 300x1200 to 600x1200mm to cover key applications
- Low glare UGR19 to provide visual comfort
- Dali , Interact, EcoSet interface are available for system control

Features

- System efficiency 140lm/W(max)
- 3800lm lumen output for 600x600 and 300x1200mm versions; 5400lm for 600x1200mm version
- CRI 80 and CRI90 are both available
- Higher lumen output 4800lm is available for 600*600mm size

Application

- Open plan office
- Public indoor area
- Meeting/training room

Specifications

Mounting type	Recessed
Ceiling type	T-Bar ceiling
	Concealed profile ceiling

Mains Voltage	220-240V / 50/60Hz
Dimming	WIA: Wireless control, compatible with Interact Pro
	SIA: Wireless control, compatible with SNS210 sensor

GreenPerform Panel RC099V G3

Control system input	Dali / WIA / SIA / EcoSet
Integrated sensors	SIA version with SNS210 sensor
Lumen maintenance at median useful life 50.000h	L70B50
Luminaire efficacy	140lm/w 120lm/w
Correlated color temperature - CCT	840 850 860 940 950 965

Risk Group	RG0
Mechanical impact protection	IK03
Ingress protection	IP20
UGR	22 19
Installation	Recessed
Warranty	5 years

