



Energy saving without compromise.

GreenPerform Troffer

GreenPerform troffer improves the compact design of the last generation with performance improvement and more variants for different markets. Integrating with all available system: POE, InterAct office wireless, InterAct Office Pro, ActiLume controller, GreenPerform troffer offers additional energy saving and connected features.

Benefits

- Upgrade to smart office with more options
- Energy saving
- Slim housing
- Comfortable light
- Good light quality
- Office compliant
- Reliable performance

Features

- Compatible with all available Philips systems
- Efficacy up to 125lm/W
- Slim design with height less than 46mm
- Improved optical design without zebra effect
- CRI > 80, SDCM<4, Flicker free
- UGR 19 available
- Lifetime L70 50,000 hours

Application

- Open Office
- Public Area
- Meeting Room
- Training Room

GreenPerform Troffer

Specifications

Ceiling type	T-bar ceiling	Lumen maintenance at	L70B50
Mains Voltage	220-240V / 50-60Hz	median useful life	50.000h
Dimming	PSU: non-dimmable	Correlated color	840
	PSD: Dimmable via Dali-broadcasting	temperature - CCT	865
	WIA: Wireless control, compatible with Interact	UGR	19 is available through certain types
	SIA: Wireless control, compatible with Interact and with SNS210 sensor	Installation	Recessed
Control system input	Dali		

Versions



GreenPerform Troffer RC100B 60x60

Dimensional drawing

