



Philips CoreLine panel: easy installation, excellent illumination

CoreLine Panel gen6

Philips CoreLine panel Gen6 delivers on the CoreLine promise of innovation, easy installation, and excellent illumination. Designed as a direct replacement for functional luminaires in general lighting applications, this LED panel light's innovative All-in feature offers a choice of three lumen packages and three-color temperatures in a single luminaire. This makes it easy to select the right product, gives you the flexibility respond to customer preferences on site, and means fewer product codes on stock. Installing the CoreLine RC132V LED panel is quick and easy, using the product's quick connector or flywire. The CoreLine range includes Interact Ready luminaires with integrated wireless communications, ready to be used with Interact gateways, sensors, and software.

Benefits

- Low-risk, reliable products
- Work faster with these easy-to-install products
- No confusion with easy product selection
- Stay relevant by joining IoT / connected lighting systems

CoreLine Panel gen6

Features

- L90@50K hrs/ L80@100K hrs with 5-year warranty
- Quick connector (green/white, Flywire, WAGO, and Schuko)
- High lumen office-compliant and non-office compliant versions
- CRI 80/CRI 90 at SDCM <3
- CRI 80 4000 K 140 lm/W and 3000 K > 130 lm/W, CRI 90 >115 lm/W
- UltraEfficient 4000 K >160 lm/W
- All-in: multiple lumen packages and color temperatures in one luminaire

Application


- Offices
- Healthcare
- Municipal buildings
- Education

Versions



CoreLine panel G6 W60L60 RTP

Dimensional drawing




CoreLine Panel gen6

Product details

CoreLine panel G6 PSD driver
open DPP




CoreLine panel G6 side angle DPP




CoreLine panel G6 W60L60 OC
Optical window DPP



CoreLine panel G6 PSD driver DPP



Polar Wide Diagrams



Polar Normal (separate) - RC132VI - 910505102817

