



# Slim and reliable

## RC160V

GreenPerform Panel RC160V is an edge lit slim panel with high efficacy in the market. It offers 3 typical dimensions: 600x600; 300x1200 and 600x1200mm to fit most of indoor applications. Its lower UGR offers better visual comfort as well. In addition, RC160V offers easy connection to control system to bring better energy saving.

### Benefits

- High lm/w provides better energy saving
- Dali and Interact interfaces available for easy internet connection
- Lower UGR offer for WELL building certificate
- Multiple mountings to cater for various applications

### Features

- System efficiency: max 130lm/W
- CRI 80 and 90 available with SDCM 4
- UGR19 / 16 available for certain types
- IP54 front/IP20 back available for certain types

### Application

- Open plan office
- Public indoor area
- Meeting/training room

### Specifications

---

<b>Ingress protection</b>	IP20/IP54 front/IP20 back
---------------------------	---------------------------







---

---

<b>Installation</b>	Recessed
---------------------	----------

---

Dimensional drawing



## General Information

Driver included	Yes
Gear	-
Number of gear units	1 unit
Service tag	Yes

## Light Technical

Color rendering index (CRI)	80
Optic type	Beam angle 100°

## Operating and Electrical

Protection class IEC	Safety class II
Input Voltage	200 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable

## Mechanical and Housing

Optical cover type	PS
Housing Color	White RAL 9003
Mech. impact protection code	IK03

## Approval and Application

Ambient temperature range	-20 to +40 °C
CE mark	Yes
ENEC mark	-
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

## Light Technical

Order Code	Full Product Name	Correlated Color		Number of light sources	
		Temperature (Nom)	Luminous Efficacy (rated) (Nom)		
911401510132	RC160V LED37/830 W30L120 PSU	3000 K	122 lm/W	3,700 lm	288
911401510232	RC160V LED39/840 W30L120 PSU	4000 K	130 lm/W	3,900 lm	288
911401510332	RC160V LED39/865 W30L120 PSU	6500 K	130 lm/W	3,900 lm	288
911401511032	RC160V LED37/830 W30L120 PSU OC	3000 K	122 lm/W	3,700 lm	288
911401511132	RC160V LED39/840 W30L120 PSU OC	4000 K	130 lm/W	3,900 lm	288
911401511232	RC160V LED39/865 W30L120 PSU OC	6500 K	130 lm/W	3,900 lm	288
911401512832	RC160V LED37/830 W30L120 PSU 54	3000 K	122 lm/W	3,700 lm	288
911401512932	RC160V LED39/840 W30L120 PSU 54	4000 K	130 lm/W	3,900 lm	288
911401513032	RC160V LED39/865 W30L120 PSU 54	6500 K	130 lm/W	3,900 lm	288
911401513732	RC160V LED37/830 W30L120 PSU OC 54	3000 K	122 lm/W	3,700 lm	288
911401513832	RC160V LED39/840 W30L120 PSU OC 54	4000 K	130 lm/W	3,900 lm	288
911401513932	RC160V LED39/865 W30L120 PSU OC 54	6500 K	130 lm/W	3,900 lm	288
911401520932	RC160V LED37/830 W30L120 PSD	3000 K	122 lm/W	3,700 lm	288
911401521032	RC160V LED39/840 W30L120 PSD	4000 K	130 lm/W	3,900 lm	288
911401521132	RC160V LED39/865 W30L120 PSD	6500 K	130 lm/W	3,900 lm	288
911401521832	RC160V LED37/830 W30L120 PSD OC	3000 K	122 lm/W	3,700 lm	288
911401521932	RC160V LED39/840 W30L120 PSD OC	4000 K	130 lm/W	3,900 lm	288
911401522032	RC160V LED39/865 W30L120 PSD OC	6500 K	130 lm/W	3,900 lm	288
911401523632	RC160X LED37/830 W30L120 WIA	3000 K	122 lm/W	3,700 lm	288
911401523732	RC160X LED39/840 W30L120 WIA	4000 K	130 lm/W	3,900 lm	288
911401523832	RC160X LED39/865 W30L120 WIA	6500 K	130 lm/W	3,900 lm	288
911401526032	RC160V LED37/830 W30L120 PSU CAU	3000 K	122 lm/W	3,700 lm	288
911401526132	RC160V LED39/840 W30L120 PSU CAU	4000 K	130 lm/W	3,900 lm	288
911401526232	RC160V LED39/865 W30L120 PSU CAU	6500 K	130 lm/W	3,900 lm	288

Order Code	Full Product Name	Correlated Color		Luminous Flux	Number of light sources
		Temperature (Nom)	Luminous Efficacy (rated) (Nom)		
911401526932	RC160V LED37/830 W30L120 PSD CAU	3000 K	122 lm/W	3,700 lm	288
911401527032	RC160V LED39/840 W30L120 PSD CAU	4000 K	130 lm/W	3,900 lm	288
911401527132	RC160V LED39/865 W30L120 PSD CAU	6500 K	130 lm/W	3,900 lm	288
911401527832	RC160X LED37/830 W30L120 WIA CAU	3000 K	122 lm/W	3,700 lm	288
911401527932	RC160X LED39/840 W30L120 WIA CAU	4000 K	130 lm/W	3,900 lm	288
911401528032	RC160X LED39/865 W30L120 WIA CAU	6500 K	130 lm/W	3,900 lm	288
911401529332	RC160V LED37/830 W30L120 PSU OC CAU	3000 K	122 lm/W	3,700 lm	288
911401529432	RC160V LED39/840 W30L120 PSU OC CAU	4000 K	130 lm/W	3,900 lm	288
911401529532	RC160V LED39/865 W30L120 PSU OC CAU	6500 K	130 lm/W	3,900 lm	288
911401530232	RC160V LED37/830 W30L120 PSD OC CAU	3000 K	122 lm/W	3,700 lm	288
911401530332	RC160V LED39/840 W30L120 PSD OC CAU	4000 K	130 lm/W	3,900 lm	288
911401530432	RC160V LED39/865 W30L120 PSD OC CAU	6500 K	130 lm/W	3,900 lm	288
911401533532	RC160V LED37/830 W30L120 PSU 54 CAU	3000 K	122 lm/W	3,700 lm	288
911401533632	RC160V LED39/840 W30L120 PSU 54 CAU	4000 K	130 lm/W	3,900 lm	288
911401533732	RC160V LED39/865 W30L120 PSU 54 CAU	6500 K	130 lm/W	3,900 lm	288
911401534432	RC160V LED37/830 W30L120 PSU OC 54 CAU	3000 K	122 lm/W	3,700 lm	288
911401534532	RC160V LED39/840 W30L120 PSU OC 54 CAU	4000 K	130 lm/W	3,900 lm	288
911401534632	RC160V LED39/865 W30L120 PSU OC 54 CAU	6500 K	130 lm/W	3,900 lm	288
911401510432	RC160V LED57/830 W60L120 PSU	3000 K	123 lm/W	5,700 lm	384
911401510532	RC160V LED60/840 W60L120 PSU	4000 K	131 lm/W	6,000 lm	384
911401510632	RC160V LED60/865 W60L120 PSU	6500 K	131 lm/W	6,000 lm	384
911401511332	RC160V LED57/830 W60L120 PSU OC	3000 K	123 lm/W	5,700 lm	384
911401511432	RC160V LED60/840 W60L120 PSU OC	4000 K	131 lm/W	6,000 lm	384
911401511532	RC160V LED60/865 W60L120 PSU OC	6500 K	131 lm/W	6,000 lm	384
911401513132	RC160V LED57/830 W60L120 PSU 54	3000 K	123 lm/W	5,700 lm	384

Order Code	Full Product Name	Correlated Color		Luminous Flux	Number of light sources
		Temperature (Nom)	Luminous Efficacy (rated) (Nom)		
911401513232	RC160V LED60/840 W60L120 PSU 54	4000 K	131 lm/W	6,000 lm	384
911401513332	RC160V LED60/865 W60L120 PSU 54	6500 K	131 lm/W	6,000 lm	384
911401514032	RC160V LED57/830 W60L120 PSU OC 54	3000 K	123 lm/W	5,700 lm	384
911401514132	RC160V LED60/840 W60L120 PSU OC 54	4000 K	131 lm/W	6,000 lm	384
911401514232	RC160V LED60/865 W60L120 PSU OC 54	6500 K	131 lm/W	6,000 lm	384
911401521232	RC160V LED57/830 W60L120 PSD	3000 K	123 lm/W	5,700 lm	384
911401521332	RC160V LED60/840 W60L120 PSD	4000 K	131 lm/W	6,000 lm	384
911401521432	RC160V LED60/865 W60L120 PSD	6500 K	131 lm/W	6,000 lm	384
911401522132	RC160V LED57/830 W60L120 PSD OC	3000 K	123 lm/W	5,700 lm	384
911401522232	RC160V LED60/840 W60L120 PSD OC	4000 K	131 lm/W	6,000 lm	384
911401522332	RC160V LED60/865 W60L120 PSD OC	6500 K	131 lm/W	6,000 lm	384
911401526332	RC160V LED57/830 W60L120 PSU CAU	3000 K	123 lm/W	5,700 lm	384
911401526432	RC160V LED60/840 W60L120 PSU CAU	4000 K	131 lm/W	6,000 lm	384
911401526532	RC160V LED60/865 W60L120 PSU CAU	6500 K	131 lm/W	6,000 lm	384
911401527232	RC160V LED57/830 W60L120 PSD CAU	3000 K	123 lm/W	5,700 lm	384
911401527332	RC160V LED60/840 W60L120 PSD CAU	4000 K	131 lm/W	6,000 lm	384
911401527432	RC160V LED60/865 W60L120 PSD CAU	6500 K	131 lm/W	6,000 lm	384
911401529632	RC160V LED57/830 W60L120 PSU OC CAU	3000 K	123 lm/W	5,700 lm	384
911401529732	RC160V LED60/840 W60L120 PSU OC CAU	4000 K	131 lm/W	6,000 lm	384
911401529832	RC160V LED60/865 W60L120 PSU OC CAU	6500 K	131 lm/W	6,000 lm	384
911401530532	RC160V LED57/830 W60L120 PSD OC CAU	3000 K	123 lm/W	5,700 lm	384
911401530632	RC160V LED60/840 W60L120 PSD OC CAU	4000 K	131 lm/W	6,000 lm	384
911401530732	RC160V LED60/865 W60L120 PSD OC CAU	6500 K	131 lm/W	6,000 lm	384
911401533832	RC160V LED57/830 W60L120 PSU 54 CAU	3000 K	123 lm/W	5,700 lm	384
911401533932	RC160V LED60/840 W60L120 PSU 54 CAU	4000 K	131 lm/W	6,000 lm	384

Order Code	Full Product Name	Correlated Color		Luminous Flux	Number of light sources
		Temperature (Nom)	Luminous Efficacy (rated) (Nom)		
911401534032	RC160V LED60/865 W60L120 PSU 54 CAU	6500 K	131 lm/W	6,000 lm	384
911401534732	RC160V LED57/830 W60L120 PSU OC 54 CAU	3000 K	123 lm/W	5,700 lm	384
911401534832	RC160V LED60/840 W60L120 PSU OC 54 CAU	4000 K	131 lm/W	6,000 lm	384
911401534932	RC160V LED60/865 W60L120 PSU OC 54 CAU	6500 K	131 lm/W	6,000 lm	384
911401509832	RC160V LED37/830 W60L60 PSU	3000 K	122 lm/W	3,700 lm	240
911401509932	RC160V LED39/840 W60L60 PSU	4000 K	130 lm/W	3,900 lm	240
911401510032	RC160V LED39/865 W60L60 PSU	6500 K	130 lm/W	3,900 lm	240
911401510732	RC160V LED37/830 W60L60 PSU OC	3000 K	122 lm/W	3,700 lm	240
911401510832	RC160V LED39/840 W60L60 PSU OC	4000 K	130 lm/W	3,900 lm	240
911401510932	RC160V LED39/865 W60L60 PSU OC	6500 K	130 lm/W	3,900 lm	240
911401512532	RC160V LED37/830 W60L60 PSU 54	3000 K	122 lm/W	3,700 lm	240
911401512632	RC160V LED39/840 W60L60 PSU 54	4000 K	130 lm/W	3,900 lm	240
911401512732	RC160V LED39/865 W60L60 PSU 54	6500 K	130 lm/W	3,900 lm	240
911401513432	RC160V LED37/830 W60L60 PSU OC 54	3000 K	122 lm/W	3,700 lm	240
911401513532	RC160V LED39/840 W60L60 PSU OC 54	4000 K	130 lm/W	3,900 lm	240
911401513632	RC160V LED39/865 W60L60 PSU OC 54	6500 K	130 lm/W	3,900 lm	240
911401520632	RC160V LED37/830 W60L60 PSD	3000 K	122 lm/W	3,700 lm	240
911401520732	RC160V LED39/840 W60L60 PSD	4000 K	130 lm/W	3,900 lm	240
911401520832	RC160V LED39/865 W60L60 PSD	6500 K	130 lm/W	3,900 lm	240
911401521532	RC160V LED37/830 W60L60 PSD OC	3000 K	122 lm/W	3,700 lm	240
911401521632	RC160V LED39/840 W60L60 PSD OC	4000 K	130 lm/W	3,900 lm	240
911401521732	RC160V LED39/865 W60L60 PSD OC	6500 K	130 lm/W	3,900 lm	240
911401523332	RC160X LED37/830 W60L60 WIA	3000 K	122 lm/W	3,700 lm	240
911401523432	RC160X LED39/840 W60L60 WIA	4000 K	130 lm/W	3,900 lm	240
911401523532	RC160X LED39/865 W60L60 WIA	6500 K	130 lm/W	3,900 lm	240

Order Code	Full Product Name	Correlated Color		Luminous Flux	Number of light sources
		Temperature (Nom)	Luminous Efficacy (rated) (Nom)		
911401523932	RC160X LED37/830 W60L60 WIA OC	3000 K	122 lm/W	3,700 lm	240
911401524032	RC160X LED39/840 W60L60 WIA OC	4000 K	130 lm/W	3,900 lm	240
911401524132	RC160X LED39/865 W60L60 WIA OC	6500 K	130 lm/W	3,900 lm	240
911401525732	RC160V LED37/830 W60L60 PSU CAU	3000 K	122 lm/W	3,700 lm	240
911401525832	RC160V LED39/840 W60L60 PSU CAU	4000 K	130 lm/W	3,900 lm	240
911401525932	RC160V LED39/865 W60L60 PSU CAU	6500 K	130 lm/W	3,900 lm	240
911401526632	RC160V LED37/830 W60L60 PSD CAU	3000 K	122 lm/W	3,700 lm	240
911401526732	RC160V LED39/840 W60L60 PSD CAU	4000 K	130 lm/W	3,900 lm	240
911401526832	RC160V LED39/865 W60L60 PSD CAU	6500 K	130 lm/W	3,900 lm	240
911401527532	RC160X LED37/830 W60L60 WIA CAU	3000 K	122 lm/W	3,700 lm	240
911401527632	RC160X LED39/840 W60L60 WIA CAU	4000 K	130 lm/W	3,900 lm	240
911401527732	RC160X LED39/865 W60L60 WIA CAU	6500 K	130 lm/W	3,900 lm	240
911401529032	RC160V LED37/830 W60L60 PSU OC CAU	3000 K	122 lm/W	3,700 lm	240
911401529132	RC160V LED39/840 W60L60 PSU OC CAU	4000 K	130 lm/W	3,900 lm	240
911401529232	RC160V LED39/865 W60L60 PSU OC CAU	6500 K	130 lm/W	3,900 lm	240
911401529932	RC160V LED37/830 W60L60 PSD OC CAU	3000 K	122 lm/W	3,700 lm	240
911401530032	RC160V LED39/840 W60L60 PSD OC CAU	4000 K	130 lm/W	3,900 lm	240
911401530132	RC160V LED39/865 W60L60 PSD OC CAU	6500 K	130 lm/W	3,900 lm	240
911401530832	RC160X LED37/830 W60L60 WIA OC CAU	3000 K	122 lm/W	3,700 lm	240
911401530932	RC160X LED39/840 W60L60 WIA OC CAU	4000 K	130 lm/W	3,900 lm	240
911401531032	RC160X LED39/865 W60L60 WIA OC CAU	6500 K	130 lm/W	3,900 lm	240
911401533232	RC160V LED37/830 W60L60 PSU 54 CAU	3000 K	122 lm/W	3,700 lm	240
911401533332	RC160V LED39/840 W60L60 PSU 54 CAU	4000 K	130 lm/W	3,900 lm	240
911401533432	RC160V LED39/865 W60L60 PSU 54 CAU	6500 K	130 lm/W	3,900 lm	240
911401534132	RC160V LED37/830 W60L60 PSU OC 54 CAU	3000 K	122 lm/W	3,700 lm	240

Order Code	Full Product Name	Correlated Color		Luminous Flux	Number of light sources
		Temperature (Nom)	Luminous Efficacy (rated) (Nom)		
911401534232	RC160V LED39/840 W60L60 PSU OC 54 CAU	4000 K	130 lm/W	3,900 lm	240
911401534332	RC160V LED39/865 W60L60 PSU OC 54 CAU	6500 K	130 lm/W	3,900 lm	240
911401536732	RC160V LED37/965 W60L60 PSU	6500 K	125 lm/W	3,750 lm	240

## Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401510132	RC160V LED37/830 W30L120 PSU	30 W	911401534532	RC160V LED39/840 W30L120 PSU OC 54 CAU	30 W
911401510232	RC160V LED39/840 W30L120 PSU	30 W	911401534632	RC160V LED39/865 W30L120 PSU OC 54 CAU	30 W
911401510332	RC160V LED39/865 W30L120 PSU	30 W	911401510432	RC160V LED57/830 W60L120 PSU	46 W
911401511032	RC160V LED37/830 W30L120 PSU OC	30 W	911401510532	RC160V LED60/840 W60L120 PSU	46 W
911401511132	RC160V LED39/840 W30L120 PSU OC	30 W	911401510632	RC160V LED60/865 W60L120 PSU	46 W
911401511232	RC160V LED39/865 W30L120 PSU OC	30 W	911401511332	RC160V LED57/830 W60L120 PSU OC	46 W
911401512832	RC160V LED37/830 W30L120 PSU 54	30 W	911401511432	RC160V LED60/840 W60L120 PSU OC	46 W
911401512932	RC160V LED39/840 W30L120 PSU 54	30 W	911401511532	RC160V LED60/865 W60L120 PSU OC	46 W
911401513032	RC160V LED39/865 W30L120 PSU 54	30 W	911401513132	RC160V LED57/830 W60L120 PSU 54	46 W
911401513732	RC160V LED37/830 W30L120 PSU OC 54	30 W	911401513232	RC160V LED60/840 W60L120 PSU 54	46 W
911401513832	RC160V LED39/840 W30L120 PSU OC 54	30 W	911401513332	RC160V LED60/865 W60L120 PSU 54	46 W
911401513932	RC160V LED39/865 W30L120 PSU OC 54	30 W	911401514032	RC160V LED57/830 W60L120 PSU OC 54	46 W
911401520932	RC160V LED37/830 W30L120 PSD	30 W	911401514132	RC160V LED60/840 W60L120 PSU OC 54	46 W
911401521032	RC160V LED39/840 W30L120 PSD	30 W	911401514232	RC160V LED60/865 W60L120 PSU OC 54	46 W
911401521132	RC160V LED39/865 W30L120 PSD	30 W	911401521232	RC160V LED57/830 W60L120 PSD	46 W
911401521832	RC160V LED37/830 W30L120 PSD OC	30 W	911401521332	RC160V LED60/840 W60L120 PSD	46 W
911401521932	RC160V LED39/840 W30L120 PSD OC	30 W	911401521432	RC160V LED60/865 W60L120 PSD	46 W
911401522032	RC160V LED39/865 W30L120 PSD OC	30 W	911401522132	RC160V LED57/830 W60L120 PSD OC	46 W
911401523632	RC160X LED37/830 W30L120 WIA	30 W	911401522232	RC160V LED60/840 W60L120 PSD OC	46 W
911401523732	RC160X LED39/840 W30L120 WIA	30 W	911401522332	RC160V LED60/865 W60L120 PSD OC	46 W
911401523832	RC160X LED39/865 W30L120 WIA	30 W	911401526332	RC160V LED57/830 W60L120 PSU CAU	46 W
911401526032	RC160V LED37/830 W30L120 PSU CAU	30 W	911401526432	RC160V LED60/840 W60L120 PSU CAU	46 W
911401526132	RC160V LED39/840 W30L120 PSU CAU	30 W	911401526532	RC160V LED60/865 W60L120 PSU CAU	46 W
911401526232	RC160V LED39/865 W30L120 PSU CAU	30 W	911401527232	RC160V LED57/830 W60L120 PSD CAU	46 W
911401526932	RC160V LED37/830 W30L120 PSD CAU	30 W	911401527332	RC160V LED60/840 W60L120 PSD CAU	46 W
911401527032	RC160V LED39/840 W30L120 PSD CAU	30 W	911401527432	RC160V LED60/865 W60L120 PSD CAU	46 W
911401527132	RC160V LED39/865 W30L120 PSD CAU	30 W	911401529632	RC160V LED57/830 W60L120 PSU OC CAU	46 W
911401527832	RC160X LED37/830 W30L120 WIA CAU	30 W	911401529732	RC160V LED60/840 W60L120 PSU OC CAU	46 W
911401527932	RC160X LED39/840 W30L120 WIA CAU	30 W	911401529832	RC160V LED60/865 W60L120 PSU OC CAU	46 W
911401528032	RC160X LED39/865 W30L120 WIA CAU	30 W	911401530532	RC160V LED57/830 W60L120 PSD OC CAU	46 W
911401529332	RC160V LED37/830 W30L120 PSU OC CAU	30 W	911401530632	RC160V LED60/840 W60L120 PSD OC CAU	46 W
911401529432	RC160V LED39/840 W30L120 PSU OC CAU	30 W	911401530732	RC160V LED60/865 W60L120 PSD OC CAU	46 W
911401529532	RC160V LED39/865 W30L120 PSU OC CAU	30 W	911401533832	RC160V LED57/830 W60L120 PSU 54 CAU	46 W
911401530232	RC160V LED37/830 W30L120 PSD OC CAU	30 W	911401533932	RC160V LED60/840 W60L120 PSU 54 CAU	46 W
911401530332	RC160V LED39/840 W30L120 PSD OC CAU	30 W	911401534032	RC160V LED60/865 W60L120 PSU 54 CAU	46 W
911401530432	RC160V LED39/865 W30L120 PSD OC CAU	30 W	911401534732	RC160V LED57/830 W60L120 PSU OC 54 CAU	46 W
911401533532	RC160V LED37/830 W30L120 PSU 54 CAU	30 W	911401534832	RC160V LED60/840 W60L120 PSU OC 54 CAU	46 W
911401533632	RC160V LED39/840 W30L120 PSU 54 CAU	30 W	911401534932	RC160V LED60/865 W60L120 PSU OC 54 CAU	46 W
911401533732	RC160V LED39/865 W30L120 PSU 54 CAU	30 W	911401509832	RC160V LED37/830 W60L60 PSU	30 W
911401534432	RC160V LED37/830 W30L120 PSU OC 54 CAU	30 W	911401509932	RC160V LED39/840 W60L60 PSU	30 W

# RC160V

Order Code	Full Product Name	Power Consumption
911401510032	RC160V LED39/865 W60L60 PSU	30 W
911401510732	RC160V LED37/830 W60L60 PSU OC	30 W
911401510832	RC160V LED39/840 W60L60 PSU OC	30 W
911401510932	RC160V LED39/865 W60L60 PSU OC	30 W
911401512532	RC160V LED37/830 W60L60 PSU 54	30 W
911401512632	RC160V LED39/840 W60L60 PSU 54	30 W
911401512732	RC160V LED39/865 W60L60 PSU 54	30 W
911401513432	RC160V LED37/830 W60L60 PSU OC 54	30 W
911401513532	RC160V LED39/840 W60L60 PSU OC 54	30 W
911401513632	RC160V LED39/865 W60L60 PSU OC 54	30 W
911401520632	RC160V LED37/830 W60L60 PSD	30 W
911401520732	RC160V LED39/840 W60L60 PSD	30 W
911401520832	RC160V LED39/865 W60L60 PSD	30 W
911401521532	RC160V LED37/830 W60L60 PSD OC	30 W
911401521632	RC160V LED39/840 W60L60 PSD OC	30 W
911401521732	RC160V LED39/865 W60L60 PSD OC	30 W
911401523332	RC160X LED37/830 W60L60 WIA	30 W
911401523432	RC160X LED39/840 W60L60 WIA	30 W
911401523532	RC160X LED39/865 W60L60 WIA	30 W
911401523932	RC160X LED37/830 W60L60 WIA OC	30 W
911401524032	RC160X LED39/840 W60L60 WIA OC	30 W
911401524132	RC160X LED39/865 W60L60 WIA OC	30 W
911401525732	RC160V LED37/830 W60L60 PSU CAU	30 W
911401525832	RC160V LED39/840 W60L60 PSU CAU	30 W

Order Code	Full Product Name	Power Consumption
911401525932	RC160V LED39/865 W60L60 PSU CAU	30 W
911401526632	RC160V LED37/830 W60L60 PSD CAU	30 W
911401526732	RC160V LED39/840 W60L60 PSD CAU	30 W
911401526832	RC160V LED39/865 W60L60 PSD CAU	30 W
911401527532	RC160X LED37/830 W60L60 WIA CAU	30 W
911401527632	RC160X LED39/840 W60L60 WIA CAU	30 W
911401527732	RC160X LED39/865 W60L60 WIA CAU	30 W
911401529032	RC160V LED37/830 W60L60 PSU OC CAU	30 W
911401529132	RC160V LED39/840 W60L60 PSU OC CAU	30 W
911401529232	RC160V LED39/865 W60L60 PSU OC CAU	30 W
911401529932	RC160V LED37/830 W60L60 PSD OC CAU	30 W
911401530032	RC160V LED39/840 W60L60 PSD OC CAU	30 W
911401530132	RC160V LED39/865 W60L60 PSD OC CAU	30 W
911401530832	RC160X LED37/830 W60L60 WIA OC CAU	30 W
911401530932	RC160X LED39/840 W60L60 WIA OC CAU	30 W
911401531032	RC160X LED39/865 W60L60 WIA OC CAU	30 W
911401533232	RC160V LED37/830 W60L60 PSU 54 CAU	30 W
911401533332	RC160V LED39/840 W60L60 PSU 54 CAU	30 W
911401533432	RC160V LED39/865 W60L60 PSU 54 CAU	30 W
911401534132	RC160V LED37/830 W60L60 PSU OC 54 CAU	30 W
911401534232	RC160V LED39/840 W60L60 PSU OC 54 CAU	30 W
911401534332	RC160V LED39/865 W60L60 PSU OC 54 CAU	30 W
911401536732	RC160V LED37/965 W60L60 PSU	30 W

## Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
911401510132	RC160V LED37/830 W30L120 PSU	Fixed	0% (digital)
911401510232	RC160V LED39/840 W30L120 PSU	Fixed	0% (digital)
911401510332	RC160V LED39/865 W30L120 PSU	Fixed	0% (digital)
911401511032	RC160V LED37/830 W30L120 PSU OC	Fixed	0% (digital)
911401511132	RC160V LED39/840 W30L120 PSU OC	Fixed	0% (digital)
911401511232	RC160V LED39/865 W30L120 PSU OC	Fixed	0% (digital)
911401512832	RC160V LED37/830 W30L120 PSU 54	Fixed	0% (digital)
911401512932	RC160V LED39/840 W30L120 PSU 54	Fixed	0% (digital)
911401513032	RC160V LED39/865 W30L120 PSU 54	Fixed	0% (digital)
911401513732	RC160V LED37/830 W30L120 PSU OC 54	Fixed	0% (digital)
911401513832	RC160V LED39/840 W30L120 PSU OC 54	Fixed	0% (digital)
911401513932	RC160V LED39/865 W30L120 PSU OC 54	Fixed	0% (digital)
911401520932	RC160V LED37/830 W30L120 PSD	DALI	Programmable
911401521032	RC160V LED39/840 W30L120 PSD	DALI	Programmable
911401521132	RC160V LED39/865 W30L120 PSD	DALI	Programmable

Order Code	Full Product Name	Dimmable	Maximum dim level
911401521832	RC160V LED37/830 W30L120 PSD OC	DALI	Programmable
911401521932	RC160V LED39/840 W30L120 PSD OC	DALI	Programmable
911401522032	RC160V LED39/865 W30L120 PSD OC	DALI	Programmable
911401523632	RC160X LED37/830 W30L120 WIA	Wireless Dim	Programmable
911401523732	RC160X LED39/840 W30L120 WIA	Wireless Dim	Programmable
911401523832	RC160X LED39/865 W30L120 WIA	Wireless Dim	Programmable
911401526032	RC160V LED37/830 W30L120 PSU CAU	Fixed	0% (digital)
911401526132	RC160V LED39/840 W30L120 PSU CAU	Fixed	0% (digital)
911401526232	RC160V LED39/865 W30L120 PSU CAU	Fixed	0% (digital)
911401526932	RC160V LED37/830 W30L120 PSD CAU	DALI	Programmable
911401527032	RC160V LED39/840 W30L120 PSD CAU	DALI	Programmable
911401527132	RC160V LED39/865 W30L120 PSD CAU	DALI	Programmable
911401527832	RC160X LED37/830 W30L120 WIA CAU	Wireless Dim	Programmable

# RC160V

Order Code	Full Product Name	Dimmable	Maximum dim level	Order Code	Full Product Name	Dimmable	Maximum dim level
911401527932	RC160X LED39/840 W30L120 WIA CAU	Wireless Dim	Programmable	911401522132	RC160V LED57/830 W60L120 PSD OC	DALI	Programmable
911401528032	RC160X LED39/865 W30L120 WIA CAU	Wireless Dim	Programmable	911401522232	RC160V LED60/840 W60L120 PSD OC	DALI	Programmable
911401529332	RC160V LED37/830 W30L120 PSU OC CAU	Fixed	0% (digital)	911401522332	RC160V LED60/865 W60L120 PSD OC	DALI	Programmable
911401529432	RC160V LED39/840 W30L120 PSU OC CAU	Fixed	0% (digital)	911401526332	RC160V LED57/830 W60L120 PSU CAU	Fixed	0% (digital)
911401529532	RC160V LED39/865 W30L120 PSU OC CAU	Fixed	0% (digital)	911401526432	RC160V LED60/840 W60L120 PSU CAU	Fixed	0% (digital)
911401530232	RC160V LED37/830 W30L120 PSD OC CAU	DALI	Programmable	911401526532	RC160V LED60/865 W60L120 PSU CAU	Fixed	0% (digital)
911401530332	RC160V LED39/840 W30L120 PSD OC CAU	DALI	Programmable	911401527232	RC160V LED57/830 W60L120 PSD CAU	DALI	Programmable
911401530432	RC160V LED39/865 W30L120 PSD OC CAU	DALI	Programmable	911401527332	RC160V LED60/840 W60L120 PSD CAU	DALI	Programmable
911401533532	RC160V LED37/830 W30L120 PSU 54 CAU	Fixed	0% (digital)	911401527432	RC160V LED60/865 W60L120 PSD CAU	DALI	Programmable
911401533632	RC160V LED39/840 W30L120 PSU 54 CAU	Fixed	0% (digital)	911401529632	RC160V LED57/830 W60L120 PSU OC CAU	Fixed	0% (digital)
911401533732	RC160V LED39/865 W30L120 PSU 54 CAU	Fixed	0% (digital)	911401529732	RC160V LED60/840 W60L120 PSU OC CAU	Fixed	0% (digital)
911401534432	RC160V LED37/830 W30L120 PSU OC 54 CAU	Fixed	0% (digital)	911401529832	RC160V LED60/865 W60L120 PSU OC CAU	Fixed	0% (digital)
911401534532	RC160V LED39/840 W30L120 PSU OC 54 CAU	Fixed	0% (digital)	911401530532	RC160V LED57/830 W60L120 PSD OC CAU	DALI	Programmable
911401534632	RC160V LED39/865 W30L120 PSU OC 54 CAU	Fixed	0% (digital)	911401530632	RC160V LED60/840 W60L120 PSD OC CAU	DALI	Programmable
911401510432	RC160V LED57/830 W60L120 PSU	Fixed	0% (digital)	911401530732	RC160V LED60/865 W60L120 PSD OC CAU	DALI	Programmable
911401510532	RC160V LED60/840 W60L120 PSU	Fixed	0% (digital)	911401533832	RC160V LED57/830 W60L120 PSU 54 CAU	Fixed	0% (digital)
911401510632	RC160V LED60/865 W60L120 PSU	Fixed	0% (digital)	911401533932	RC160V LED60/840 W60L120 PSU 54 CAU	Fixed	0% (digital)
911401511332	RC160V LED57/830 W60L120 PSU OC	Fixed	0% (digital)	911401534032	RC160V LED60/865 W60L120 PSU 54 CAU	Fixed	0% (digital)
911401511432	RC160V LED60/840 W60L120 PSU OC	Fixed	0% (digital)	911401534732	RC160V LED57/830 W60L120 PSU OC 54 CAU	Fixed	0% (digital)
911401511532	RC160V LED60/865 W60L120 PSU OC	Fixed	0% (digital)	911401534832	RC160V LED60/840 W60L120 PSU OC 54 CAU	Fixed	0% (digital)
911401513132	RC160V LED57/830 W60L120 PSU 54	Fixed	0% (digital)	911401534932	RC160V LED60/865 W60L120 PSU OC 54 CAU	Fixed	0% (digital)
911401513232	RC160V LED60/840 W60L120 PSU 54	Fixed	0% (digital)	911401509832	RC160V LED37/830 W60L60 PSU	Fixed	0% (digital)
911401513332	RC160V LED60/865 W60L120 PSU 54	Fixed	0% (digital)	911401509932	RC160V LED39/840 W60L60 PSU	Fixed	0% (digital)
911401514032	RC160V LED57/830 W60L120 PSU OC 54	Fixed	0% (digital)	911401510032	RC160V LED39/865 W60L60 PSU	Fixed	0% (digital)
911401514132	RC160V LED60/840 W60L120 PSU OC 54	Fixed	0% (digital)	911401510732	RC160V LED37/830 W60L60 PSU OC	Fixed	0% (digital)
911401514232	RC160V LED60/865 W60L120 PSU OC 54	Fixed	0% (digital)	911401510832	RC160V LED39/840 W60L60 PSU OC	Fixed	0% (digital)
911401521232	RC160V LED57/830 W60L120 PSD	DALI	Programmable	911401510932	RC160V LED39/865 W60L60 PSU OC	Fixed	0% (digital)
911401521332	RC160V LED60/840 W60L120 PSD	DALI	Programmable	911401512532	RC160V LED37/830 W60L60 PSU 54	Fixed	0% (digital)
911401521432	RC160V LED60/865 W60L120 PSD	DALI	Programmable				

# RC160V

Order Code	Full Product Name	Dimmable	Maximum dim level
911401512632	RC160V LED39/840 W60L60 PSU 54	Fixed	0% (digital)
911401512732	RC160V LED39/865 W60L60 PSU 54	Fixed	0% (digital)
911401513432	RC160V LED37/830 W60L60 PSU OC 54	Fixed	0% (digital)
911401513532	RC160V LED39/840 W60L60 PSU OC 54	Fixed	0% (digital)
911401513632	RC160V LED39/865 W60L60 PSU OC 54	Fixed	0% (digital)
911401520632	RC160V LED37/830 W60L60 PSD	DALI	Programmable
911401520732	RC160V LED39/840 W60L60 PSD	DALI	Programmable
911401520832	RC160V LED39/865 W60L60 PSD	DALI	Programmable
911401521532	RC160V LED37/830 W60L60 PSD OC	DALI	Programmable
911401521632	RC160V LED39/840 W60L60 PSD OC	DALI	Programmable
911401521732	RC160V LED39/865 W60L60 PSD OC	DALI	Programmable
911401523332	RC160X LED37/830 W60L60 WIA	Wireless Dim	Programmable
911401523432	RC160X LED39/840 W60L60 WIA	Wireless Dim	Programmable
911401523532	RC160X LED39/865 W60L60 WIA	Wireless Dim	Programmable
911401523932	RC160X LED37/830 W60L60 WIA OC	Wireless Dim	Programmable
911401524032	RC160X LED39/840 W60L60 WIA OC	Wireless Dim	Programmable
911401524132	RC160X LED39/865 W60L60 WIA OC	Wireless Dim	Programmable
911401525732	RC160V LED37/830 W60L60 PSU CAU	Fixed	0% (digital)
911401525832	RC160V LED39/840 W60L60 PSU CAU	Fixed	0% (digital)
911401525932	RC160V LED39/865 W60L60 PSU CAU	Fixed	0% (digital)
911401526632	RC160V LED37/830 W60L60 PSD CAU	DALI	Programmable
911401526732	RC160V LED39/840 W60L60 PSD CAU	DALI	Programmable
911401526832	RC160V LED39/865 W60L60 PSD CAU	DALI	Programmable

Order Code	Full Product Name	Dimmable	Maximum dim level
911401527532	RC160X LED37/830 W60L60 WIA CAU	Wireless Dim	Programmable
911401527632	RC160X LED39/840 W60L60 WIA CAU	Wireless Dim	Programmable
911401527732	RC160X LED39/865 W60L60 WIA CAU	Wireless Dim	Programmable
911401529032	RC160V LED37/830 W60L60 PSU OC CAU	Fixed	0% (digital)
911401529132	RC160V LED39/840 W60L60 PSU OC CAU	Fixed	0% (digital)
911401529232	RC160V LED39/865 W60L60 PSU OC CAU	Fixed	0% (digital)
911401529932	RC160V LED37/830 W60L60 PSD OC CAU	DALI	Programmable
911401530032	RC160V LED39/840 W60L60 PSD OC CAU	DALI	Programmable
911401530132	RC160V LED39/865 W60L60 PSD OC CAU	DALI	Programmable
911401530832	RC160X LED37/830 W60L60 WIA OC CAU	Wireless Dim	Programmable
911401530932	RC160X LED39/840 W60L60 WIA OC CAU	Wireless Dim	Programmable
911401531032	RC160X LED39/865 W60L60 WIA OC CAU	Wireless Dim	Programmable
911401533232	RC160V LED37/830 W60L60 PSU 54 CAU	Fixed	0% (digital)
911401533332	RC160V LED39/840 W60L60 PSU 54 CAU	Fixed	0% (digital)
911401533432	RC160V LED39/865 W60L60 PSU 54 CAU	Fixed	0% (digital)
911401534132	RC160V LED37/830 W60L60 PSU OC 54 CAU	Fixed	0% (digital)
911401534232	RC160V LED39/840 W60L60 PSU OC 54 CAU	Fixed	0% (digital)
911401534332	RC160V LED39/865 W60L60 PSU OC 54 CAU	Fixed	0% (digital)
911401536732	RC160V LED37/965 W60L60 PSU	Fixed	0% (digital)

## Mechanical and Housing

Order Code	Full Product Name	Ingress protection code
911401510132	RC160V LED37/830 W30L120 PSU	IP20
911401510232	RC160V LED39/840 W30L120 PSU	IP20
911401510332	RC160V LED39/865 W30L120 PSU	IP20
911401511032	RC160V LED37/830 W30L120 PSU OC	IP20
911401511132	RC160V LED39/840 W30L120 PSU OC	IP20
911401511232	RC160V LED39/865 W30L120 PSU OC	IP20
911401512832	RC160V LED37/830 W30L120 PSU 54	IP54/20
911401512932	RC160V LED39/840 W30L120 PSU 54	IP54/20

Order Code	Full Product Name	Ingress protection code
911401513032	RC160V LED39/865 W30L120 PSU 54	IP54/20
911401513732	RC160V LED37/830 W30L120 PSU OC 54	IP54/20
911401513832	RC160V LED39/840 W30L120 PSU OC 54	IP54/20
911401513932	RC160V LED39/865 W30L120 PSU OC 54	IP54/20
911401520932	RC160V LED37/830 W30L120 PSD	IP20
911401521032	RC160V LED39/840 W30L120 PSD	IP20
911401521132	RC160V LED39/865 W30L120 PSD	IP20
911401521832	RC160V LED37/830 W30L120 PSD OC	IP20

# RC160V

Order Code	Full Product Name	Ingress protection code
911401521932	RC160V LED39/840 W30L120 PSD OC	IP20
911401522032	RC160V LED39/865 W30L120 PSD OC	IP20
911401523632	RC160X LED37/830 W30L120 WIA	IP20
911401523732	RC160X LED39/840 W30L120 WIA	IP20
911401523832	RC160X LED39/865 W30L120 WIA	IP20
911401526032	RC160V LED37/830 W30L120 PSU CAU	IP20
911401526132	RC160V LED39/840 W30L120 PSU CAU	IP20
911401526232	RC160V LED39/865 W30L120 PSU CAU	IP20
911401526932	RC160V LED37/830 W30L120 PSD CAU	IP20
911401527032	RC160V LED39/840 W30L120 PSD CAU	IP20
911401527132	RC160V LED39/865 W30L120 PSD CAU	IP20
911401527832	RC160X LED37/830 W30L120 WIA CAU	IP20
911401527932	RC160X LED39/840 W30L120 WIA CAU	IP20
911401528032	RC160X LED39/865 W30L120 WIA CAU	IP20
911401529332	RC160V LED37/830 W30L120 PSU OC CAU	IP20
911401529432	RC160V LED39/840 W30L120 PSU OC CAU	IP20
911401529532	RC160V LED39/865 W30L120 PSU OC CAU	IP20
911401530232	RC160V LED37/830 W30L120 PSD OC CAU	IP20
911401530332	RC160V LED39/840 W30L120 PSD OC CAU	IP20
911401530432	RC160V LED39/865 W30L120 PSD OC CAU	IP20
911401533532	RC160V LED37/830 W30L120 PSU 54 CAU	IP54/20
911401533632	RC160V LED39/840 W30L120 PSU 54 CAU	IP54/20
911401533732	RC160V LED39/865 W30L120 PSU 54 CAU	IP54/20
911401534432	RC160V LED37/830 W30L120 PSU OC 54 CAU	IP54/20
911401534532	RC160V LED39/840 W30L120 PSU OC 54 CAU	IP54/20
911401534632	RC160V LED39/865 W30L120 PSU OC 54 CAU	IP54/20
911401510432	RC160V LED57/830 W60L120 PSU	IP20
911401510532	RC160V LED60/840 W60L120 PSU	IP20
911401510632	RC160V LED60/865 W60L120 PSU	IP20
911401511332	RC160V LED57/830 W60L120 PSU OC	IP20
911401511432	RC160V LED60/840 W60L120 PSU OC	IP20
911401511532	RC160V LED60/865 W60L120 PSU OC	IP20
911401513132	RC160V LED57/830 W60L120 PSU 54	IP54/20
911401513232	RC160V LED60/840 W60L120 PSU 54	IP54/20
911401513332	RC160V LED60/865 W60L120 PSU 54	IP54/20
911401514032	RC160V LED57/830 W60L120 PSU OC 54	IP54/20
911401514132	RC160V LED60/840 W60L120 PSU OC 54	IP54/20
911401514232	RC160V LED60/865 W60L120 PSU OC 54	IP54/20
911401521232	RC160V LED57/830 W60L120 PSD	IP20
911401521332	RC160V LED60/840 W60L120 PSD	IP20
911401521432	RC160V LED60/865 W60L120 PSD	IP20
911401522132	RC160V LED57/830 W60L120 PSD OC	IP20
911401522232	RC160V LED60/840 W60L120 PSD OC	IP20
911401522332	RC160V LED60/865 W60L120 PSD OC	IP20
911401526332	RC160V LED57/830 W60L120 PSU CAU	IP20
911401526432	RC160V LED60/840 W60L120 PSU CAU	IP20
911401526532	RC160V LED60/865 W60L120 PSU CAU	IP20
911401527232	RC160V LED57/830 W60L120 PSD CAU	IP20
911401527332	RC160V LED60/840 W60L120 PSD CAU	IP20
911401527432	RC160V LED60/865 W60L120 PSD CAU	IP20
911401529632	RC160V LED57/830 W60L120 PSU OC CAU	IP20
911401529732	RC160V LED60/840 W60L120 PSU OC CAU	IP20

Order Code	Full Product Name	Ingress protection code
911401529832	RC160V LED60/865 W60L120 PSU OC CAU	IP20
911401530532	RC160V LED57/830 W60L120 PSD OC CAU	IP20
911401530632	RC160V LED60/840 W60L120 PSD OC CAU	IP20
911401530732	RC160V LED60/865 W60L120 PSD OC CAU	IP20
911401533832	RC160V LED57/830 W60L120 PSU 54 CAU	IP54/20
911401533932	RC160V LED60/840 W60L120 PSU 54 CAU	IP54/20
911401534032	RC160V LED60/865 W60L120 PSU 54 CAU	IP54/20
911401534732	RC160V LED57/830 W60L120 PSU OC 54 CAU	IP54/20
911401534832	RC160V LED60/840 W60L120 PSU OC 54 CAU	IP54/20
911401534932	RC160V LED60/865 W60L120 PSU OC 54 CAU	IP54/20
911401509832	RC160V LED37/830 W60L60 PSU	IP20
911401509932	RC160V LED39/840 W60L60 PSU	IP20
911401510032	RC160V LED39/865 W60L60 PSU	IP20
911401510732	RC160V LED37/830 W60L60 PSU OC	IP20
911401510832	RC160V LED39/840 W60L60 PSU OC	IP20
911401510932	RC160V LED39/865 W60L60 PSU OC	IP20
911401512532	RC160V LED37/830 W60L60 PSU 54	IP54/20
911401512632	RC160V LED39/840 W60L60 PSU 54	IP54/20
911401512732	RC160V LED39/865 W60L60 PSU 54	IP54/20
911401513432	RC160V LED37/830 W60L60 PSU OC 54	IP54/20
911401513532	RC160V LED39/840 W60L60 PSU OC 54	IP54/20
911401513632	RC160V LED39/865 W60L60 PSU OC 54	IP54/20
911401520632	RC160V LED37/830 W60L60 PSD	IP20
911401520732	RC160V LED39/840 W60L60 PSD	IP20
911401520832	RC160V LED39/865 W60L60 PSD	IP20
911401521532	RC160V LED37/830 W60L60 PSD OC	IP20
911401521632	RC160V LED39/840 W60L60 PSD OC	IP20
911401521732	RC160V LED39/865 W60L60 PSD OC	IP20
911401523332	RC160X LED37/830 W60L60 WIA	IP20
911401523432	RC160X LED39/840 W60L60 WIA	IP20
911401523532	RC160X LED39/865 W60L60 WIA	IP20
911401523932	RC160X LED37/830 W60L60 WIA OC	IP20
911401524032	RC160X LED39/840 W60L60 WIA OC	IP20
911401524132	RC160X LED39/865 W60L60 WIA OC	IP20
911401525732	RC160V LED37/830 W60L60 PSU CAU	IP20
911401525832	RC160V LED39/840 W60L60 PSU CAU	IP20
911401525932	RC160V LED39/865 W60L60 PSU CAU	IP20
911401526632	RC160V LED37/830 W60L60 PSD CAU	IP20
911401526732	RC160V LED39/840 W60L60 PSD CAU	IP20
911401526832	RC160V LED39/865 W60L60 PSD CAU	IP20
911401527532	RC160X LED37/830 W60L60 WIA CAU	IP20
911401527632	RC160X LED39/840 W60L60 WIA CAU	IP20
911401527732	RC160X LED39/865 W60L60 WIA CAU	IP20
911401529032	RC160V LED37/830 W60L60 PSU OC CAU	IP20
911401529132	RC160V LED39/840 W60L60 PSU OC CAU	IP20
911401529232	RC160V LED39/865 W60L60 PSU OC CAU	IP20
911401529932	RC160V LED37/830 W60L60 PSD OC CAU	IP20
911401530032	RC160V LED39/840 W60L60 PSD OC CAU	IP20
911401530132	RC160V LED39/865 W60L60 PSD OC CAU	IP20
911401530832	RC160X LED37/830 W60L60 WIA OC CAU	IP20
911401530932	RC160X LED39/840 W60L60 WIA OC CAU	IP20
911401531032	RC160X LED39/865 W60L60 WIA OC CAU	IP20

## RC160V

Order Code	Full Product Name	Ingress protection code
911401533232	RC160V LED37/830 W60L60 PSU 54 CAU	IP54/20
911401533332	RC160V LED39/840 W60L60 PSU 54 CAU	IP54/20
911401533432	RC160V LED39/865 W60L60 PSU 54 CAU	IP54/20
911401534132	RC160V LED37/830 W60L60 PSU OC 54 CAU	IP54/20

Order Code	Full Product Name	Ingress protection code
911401534232	RC160V LED39/840 W60L60 PSU OC 54 CAU	IP54/20
911401534332	RC160V LED39/865 W60L60 PSU OC 54 CAU	IP54/20
911401536732	RC160V LED37/965 W60L60 PSU	IP20

