



Slim and reliable

RC160V

GreenPerform Panel RC160V is an edge lit slim panel with high efficacy in the market. It offers 3 typical dimensions: 600x600; 300x1200 and 600x1200mm to fit most of indoor applications. Its lower UGR offers better visual comfort as well. In addition, RC160V offers easy connection to control system to bring better energy saving.

Benefits

- High lm/w provides better energy saving
- Dali and Interact interfaces available for easy internet connection
- Lower UGR offer for WELL building certificate
- Multiple mountings to cater for various applications

Features

- System efficiency: max 130lm/W
- CRI 80 and 90 available with SDCM 4
- UGR19 / 16 available for certain types
- IP54 front/IP20 back available for certain types


Application

- Open plan office
- Public indoor area
- Meeting/training room


Specifications

Ingress protection	IP20IP54 front/IP20 back	Installation	Recessed
--------------------	--------------------------	--------------	----------

Dimensional drawing



Dimensional drawing



General Information	
Driver included	Yes
Gear	-
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Color rendering index (CRI)	80
Optic type	Beam angle 100°
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	200 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable
Mechanical and Housing	
Housing Color	White RAL 9003
Mech. impact protection code	IK03
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	Yes
ENEC mark	-
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color		Luminous Flux	Number of light sources
		Temperature (Nom)	Luminous Efficacy (rated) (Nom)		
911401510132	RC160V LED37/830 W30L120 PSU	3000 K	122 lm/W	3,700 lm	288
911401510232	RC160V LED39/840 W30L120 PSU	4000 K	130 lm/W	3,900 lm	288
911401510332	RC160V LED39/865 W30L120 PSU	6500 K	130 lm/W	3,900 lm	288
911401511032	RC160V LED37/830 W30L120 PSU OC	3000 K	122 lm/W	3,700 lm	288
911401511132	RC160V LED39/840 W30L120 PSU OC	4000 K	130 lm/W	3,900 lm	288
911401511232	RC160V LED39/865 W30L120 PSU OC	6500 K	130 lm/W	3,900 lm	288
911401511932	RC160V LED27/830 W30L120 PSU 16	3000 K	125 lm/W	2,740 lm	288
911401512032	RC160V LED29/840 W30L120 PSU 16	4000 K	133 lm/W	2,900 lm	288
911401512132	RC160V LED29/865 W30L120 PSU 16	6500 K	133 lm/W	2,900 lm	288
911401512832	RC160V LED37/830 W30L120 PSU 54	3000 K	122 lm/W	3,700 lm	288
911401512932	RC160V LED39/840 W30L120 PSU 54	4000 K	130 lm/W	3,900 lm	288
911401513032	RC160V LED39/865 W30L120 PSU 54	6500 K	130 lm/W	3,900 lm	288
911401513732	RC160V LED37/830 W30L120 PSU OC 54	3000 K	122 lm/W	3,700 lm	288
911401513832	RC160V LED39/840 W30L120 PSU OC 54	4000 K	130 lm/W	3,900 lm	288
911401513932	RC160V LED39/865 W30L120 PSU OC 54	6500 K	130 lm/W	3,900 lm	288
911401514632	RC160V LED27/830 W30L120 PSU 16 54	3000 K	125 lm/W	2,740 lm	288
911401514732	RC160V LED29/840 W30L120 PSU 16 54	4000 K	133 lm/W	2,900 lm	288

Order Code	Full Product Name	Correlated Color	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources
		Temperature (Nom)			
911401514832	RC160V LED29/865 W30L120 PSU 16 54	6500 K	133 lm/W	2,900 lm	288
911401520932	RC160V LED37/830 W30L120 PSD	3000 K	122 lm/W	3,700 lm	288
911401521032	RC160V LED39/840 W30L120 PSD	4000 K	130 lm/W	3,900 lm	288
911401521132	RC160V LED39/865 W30L120 PSD	6500 K	130 lm/W	3,900 lm	288
911401521832	RC160V LED37/830 W30L120 PSD OC	3000 K	122 lm/W	3,700 lm	288
911401521932	RC160V LED39/840 W30L120 PSD OC	4000 K	130 lm/W	3,900 lm	288
911401522032	RC160V LED39/865 W30L120 PSD OC	6500 K	130 lm/W	3,900 lm	288
911401522732	RC160V LED27/830 W30L120 PSD 16	3000 K	125 lm/W	2,740 lm	288
911401522832	RC160V LED29/840 W30L120 PSD 16	4000 K	133 lm/W	2,900 lm	288
911401522932	RC160V LED29/865 W30L120 PSD 16	6500 K	133 lm/W	2,900 lm	288
911401523632	RC160X LED37/830 W30L120 WIA	3000 K	122 lm/W	3,700 lm	288
911401523732	RC160X LED39/840 W30L120 WIA	4000 K	130 lm/W	3,900 lm	288
911401523832	RC160X LED39/865 W30L120 WIA	6500 K	130 lm/W	3,900 lm	288
911401524832	RC160X LED37/830 W30L120 SIA	3000 K	122 lm/W	3,700 lm	288
911401524932	RC160X LED39/840 W30L120 SIA	4000 K	130 lm/W	3,900 lm	288
911401525032	RC160X LED39/865 W30L120 SIA	6500 K	130 lm/W	3,900 lm	288
911401536832	RC160V LED35/930 W30L120 PSU	3000 K	118 lm/W	3,500 lm	288
911401536932	RC160V LED37/940 W30L120 PSU	4000 K	126 lm/W	3,750 lm	288
911401537032	RC160V LED37/965 W30L120 PSU	6500 K	126 lm/W	3,750 lm	288
911401537732	RC160V LED35/930 W30L120 PSU 54	3000 K	118 lm/W	3,500 lm	288
911401537832	RC160V LED37/940 W30L120 PSU 54	4000 K	126 lm/W	3,750 lm	288
911401537932	RC160V LED37/965 W30L120 PSU 54	6500 K	126 lm/W	3,750 lm	288
911401538632	RC160V LED35/930 W30L120 PSD	3000 K	118 lm/W	3,500 lm	288
911401538732	RC160V LED37/940 W30L120 PSD	4000 K	126 lm/W	3,750 lm	288
911401538832	RC160V LED37/965 W30L120 PSD	6500 K	126 lm/W	3,750 lm	288

Order Code	Full Product Name	Correlated Color	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources
		Temperature (Nom)			
911401539532	RC160X LED35/930 W30L120 WIA	3000 K	118 lm/W	3,500 lm	288
911401539632	RC160X LED37/940 W30L120 WIA	4000 K	126 lm/W	3,750 lm	288
911401539732	RC160X LED37/965 W30L120 WIA	6500 K	126 lm/W	3,750 lm	288
911401540132	RC160X LED35/930 W30L120 SIA	3000 K	118 lm/W	3,500 lm	288
911401540232	RC160X LED37/940 W30L120 SIA	4000 K	126 lm/W	3,750 lm	288
911401540332	RC160X LED37/965 W30L120 SIA	6500 K	126 lm/W	3,750 lm	288
911401510432	RC160V LED57/830 W60L120 PSU	3000 K	123 lm/W	5,700 lm	384
911401510532	RC160V LED60/840 W60L120 PSU	4000 K	131 lm/W	6,000 lm	384
911401510632	RC160V LED60/865 W60L120 PSU	6500 K	131 lm/W	6,000 lm	384
911401511332	RC160V LED57/830 W60L120 PSU OC	3000 K	123 lm/W	5,700 lm	384
911401511432	RC160V LED60/840 W60L120 PSU OC	4000 K	131 lm/W	6,000 lm	384
911401511532	RC160V LED60/865 W60L120 PSU OC	6500 K	131 lm/W	6,000 lm	384
911401512232	RC160V LED54/830 W60L120 PSU 16	3000 K	119 lm/W	5,450 lm	384
911401512332	RC160V LED58/840 W60L120 PSU 16	4000 K	126 lm/W	5,800 lm	384
911401512432	RC160V LED58/865 W60L120 PSU 16	6500 K	126 lm/W	5,800 lm	384
911401513132	RC160V LED57/830 W60L120 PSU 54	3000 K	123 lm/W	5,700 lm	384
911401513232	RC160V LED60/840 W60L120 PSU 54	4000 K	131 lm/W	6,000 lm	384
911401513332	RC160V LED60/865 W60L120 PSU 54	6500 K	131 lm/W	6,000 lm	384
911401514032	RC160V LED57/830 W60L120 PSU OC 54	3000 K	123 lm/W	5,700 lm	384
911401514132	RC160V LED60/840 W60L120 PSU OC 54	4000 K	131 lm/W	6,000 lm	384
911401514232	RC160V LED60/865 W60L120 PSU OC 54	6500 K	131 lm/W	6,000 lm	384
911401514932	RC160V LED54/830 W60L120 PSU 16 54	3000 K	119 lm/W	5,450 lm	384
911401515032	RC160V LED58/840 W60L120 PSU 16 54	4000 K	126 lm/W	5,800 lm	384
911401515132	RC160V LED58/865 W60L120 PSU 16 54	6500 K	126 lm/W	5,800 lm	384
911401521232	RC160V LED57/830 W60L120 PSD	3000 K	123 lm/W	5,700 lm	384

Order Code	Full Product Name	Correlated Color	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources
		Temperature (Nom)			
911401521332	RC160V LED60/840 W60L120 PSD	4000 K	131 lm/W	6,000 lm	384
911401521432	RC160V LED60/865 W60L120 PSD	6500 K	131 lm/W	6,000 lm	384
911401522132	RC160V LED57/830 W60L120 PSD OC	3000 K	123 lm/W	5,700 lm	384
911401522232	RC160V LED60/840 W60L120 PSD OC	4000 K	131 lm/W	6,000 lm	384
911401522332	RC160V LED60/865 W60L120 PSD OC	6500 K	131 lm/W	6,000 lm	384
911401523032	RC160V LED54/830 W60L120 PSD 16	3000 K	119 lm/W	5,450 lm	384
911401523132	RC160V LED58/840 W60L120 PSD 16	4000 K	126 lm/W	5,800 lm	384
911401523232	RC160V LED58/865 W60L120 PSD 16	6500 K	126 lm/W	5,800 lm	384
911401525132	RC160X LED57/830 W60L120 SIA	3000 K	123 lm/W	5,700 lm	384
911401525232	RC160X LED60/840 W60L120 SIA	4000 K	131 lm/W	6,000 lm	384
911401525332	RC160X LED60/865 W60L120 SIA	6500 K	131 lm/W	6,000 lm	384
911401537132	RC160V LED54/930 W60L120 PSU	3000 K	119 lm/W	5,450 lm	384
911401537232	RC160V LED58/940 W60L120 PSU	4000 K	126 lm/W	5,800 lm	384
911401537332	RC160V LED58/965 W60L120 PSU	6500 K	126 lm/W	5,800 lm	384
911401538032	RC160V LED54/930 W60L120 PSU 54	3000 K	119 lm/W	5,450 lm	384
911401538132	RC160V LED58/940 W60L120 PSU 54	4000 K	126 lm/W	5,800 lm	384
911401538232	RC160V LED58/965 W60L120 PSU 54	6500 K	126 lm/W	5,800 lm	384
911401538932	RC160V LED54/930 W60L120 PSD	3000 K	119 lm/W	5,450 lm	384
911401539032	RC160V LED58/940 W60L120 PSD	4000 K	126 lm/W	5,800 lm	384
911401539132	RC160V LED58/965 W60L120 PSD	6500 K	126 lm/W	5,800 lm	384
911401540432	RC160X LED54/930 W60L120 SIA	3000 K	119 lm/W	5,450 lm	384
911401540532	RC160X LED58/940 W60L120 SIA	4000 K	126 lm/W	5,800 lm	384
911401540632	RC160X LED58/965 W60L120 SIA	6500 K	126 lm/W	5,800 lm	384
911401544932	RC160X LED48/930 W60L120 WIA	3000 K	121 lm/W	4,800 lm	384
911401545032	RC160X LED51/940 W60L120 WIA	4000 K	129 lm/W	5,100 lm	384

Order Code	Full Product Name	Correlated Color	Luminous Efficacy		Number of light sources
		Temperature (Nom)	(rated) (Nom)	Luminous Flux	
911401545132	RC160X LED51/965 W60L120 WIA	6500 K	129 lm/W	5,100 lm	384
911401509832	RC160V LED37/830 W60L60 PSU	3000 K	122 lm/W	3,700 lm	240
911401509932	RC160V LED39/840 W60L60 PSU	4000 K	130 lm/W	3,900 lm	240
911401510032	RC160V LED39/865 W60L60 PSU	6500 K	130 lm/W	3,900 lm	240
911401510732	RC160V LED37/830 W60L60 PSU OC	3000 K	122 lm/W	3,700 lm	240
911401510832	RC160V LED39/840 W60L60 PSU OC	4000 K	130 lm/W	3,900 lm	240
911401510932	RC160V LED39/865 W60L60 PSU OC	6500 K	130 lm/W	3,900 lm	240
911401511632	RC160V LED27/830 W60L60 PSU 16	3000 K	124 lm/W	2,740 lm	240
911401511732	RC160V LED29/840 W60L60 PSU 16	4000 K	132 lm/W	2,900 lm	240
911401511832	RC160V LED29/865 W60L60 PSU 16	6500 K	132 lm/W	2,900 lm	240
911401512532	RC160V LED37/830 W60L60 PSU 54	3000 K	122 lm/W	3,700 lm	240
911401512632	RC160V LED39/840 W60L60 PSU 54	4000 K	130 lm/W	3,900 lm	240
911401512732	RC160V LED39/865 W60L60 PSU 54	6500 K	130 lm/W	3,900 lm	240
911401513432	RC160V LED37/830 W60L60 PSU OC 54	3000 K	122 lm/W	3,700 lm	240
911401513532	RC160V LED39/840 W60L60 PSU OC 54	4000 K	130 lm/W	3,900 lm	240
911401513632	RC160V LED39/865 W60L60 PSU OC 54	6500 K	130 lm/W	3,900 lm	240
911401514332	RC160V LED27/830 W60L60 PSU 16 54	3000 K	124 lm/W	2,740 lm	240
911401514432	RC160V LED29/840 W60L60 PSU 16 54	4000 K	132 lm/W	2,900 lm	240
911401514532	RC160V LED29/865 W60L60 PSU 16 54	6500 K	132 lm/W	2,900 lm	240
911401520632	RC160V LED37/830 W60L60 PSD	3000 K	122 lm/W	3,700 lm	240
911401520732	RC160V LED39/840 W60L60 PSD	4000 K	130 lm/W	3,900 lm	240
911401520832	RC160V LED39/865 W60L60 PSD	6500 K	130 lm/W	3,900 lm	240
911401521532	RC160V LED37/830 W60L60 PSD OC	3000 K	122 lm/W	3,700 lm	240
911401521632	RC160V LED39/840 W60L60 PSD OC	4000 K	130 lm/W	3,900 lm	240
911401521732	RC160V LED39/865 W60L60 PSD OC	6500 K	130 lm/W	3,900 lm	240

Order Code	Full Product Name	Correlated Color	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources
		Temperature (Nom)			
911401522432	RC160V LED27/830 W60L60 PSD 16	3000 K	124 lm/W	2,740 lm	240
911401522532	RC160V LED29/840 W60L60 PSD 16	4000 K	132 lm/W	2,900 lm	240
911401522632	RC160V LED29/865 W60L60 PSD 16	6500 K	132 lm/W	2,900 lm	240
911401523332	RC160X LED37/830 W60L60 WIA	3000 K	122 lm/W	3,700 lm	240
911401523432	RC160X LED39/840 W60L60 WIA	4000 K	130 lm/W	3,900 lm	240
911401523532	RC160X LED39/865 W60L60 WIA	6500 K	130 lm/W	3,900 lm	240
911401523932	RC160X LED37/830 W60L60 WIA OC	3000 K	122 lm/W	3,700 lm	240
911401524032	RC160X LED39/840 W60L60 WIA OC	4000 K	130 lm/W	3,900 lm	240
911401524132	RC160X LED39/865 W60L60 WIA OC	6500 K	130 lm/W	3,900 lm	240
911401524232	RC160X LED27/830 W60L60 WIA 16	3000 K	124 lm/W	2,740 lm	240
911401524332	RC160X LED29/840 W60L60 WIA 16	4000 K	132 lm/W	2,900 lm	240
911401524432	RC160X LED29/865 W60L60 WIA 16	6500 K	132 lm/W	2,900 lm	240
911401524532	RC160X LED37/830 W60L60 SIA	3000 K	122 lm/W	3,700 lm	240
911401524632	RC160X LED39/840 W60L60 SIA	4000 K	130 lm/W	3,900 lm	240
911401524732	RC160X LED39/865 W60L60 SIA	6500 K	130 lm/W	3,900 lm	240
911401536532	RC160V LED35/930 W60L60 PSU	3000 K	118 lm/W	3,500 lm	240
911401536632	RC160V LED37/940 W60L60 PSU	4000 K	125 lm/W	3,750 lm	240
911401536732	RC160V LED37/965 W60L60 PSU	6500 K	125 lm/W	3,750 lm	240
911401537432	RC160V LED35/930 W60L60 PSU 54	3000 K	118 lm/W	3,500 lm	240
911401537532	RC160V LED37/940 W60L60 PSU 54	4000 K	125 lm/W	3,750 lm	240
911401537632	RC160V LED37/965 W60L60 PSU 54	6500 K	125 lm/W	3,750 lm	240
911401538332	RC160V LED35/930 W60L60 PSD	3000 K	118 lm/W	3,500 lm	240
911401538432	RC160V LED37/940 W60L60 PSD	4000 K	125 lm/W	3,750 lm	240
911401538532	RC160V LED37/965 W60L60 PSD	6500 K	125 lm/W	3,750 lm	240
911401539332	RC160X LED37/940 W60L60 WIA	4000 K	125 lm/W	3,750 lm	240

Order Code	Full Product Name	Correlated Color	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources
		Temperature (Nom)			
911401539432	RC160X LED37/965 W60L60 WIA	6500 K	125 lm/W	3,750 lm	240
911401539832	RC160X LED35/930 W60L60 SIA	3000 K	118 lm/W	3,500 lm	240
911401539932	RC160X LED37/940 W60L60 SIA	4000 K	125 lm/W	3,750 lm	240
911401540032	RC160X LED37/965 W60L60 SIA	6500 K	125 lm/W	3,750 lm	240
911401545532	RC160V LED36/9TW W60L60	2700 K	120 lm/W	3,600 lm	240

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401510132	RC160V LED37/830 W30L120 PSU	30 W	911401537732	RC160V LED35/930 W30L120 PSU 54	30 W
911401510232	RC160V LED39/840 W30L120 PSU	30 W	911401537832	RC160V LED37/940 W30L120 PSU 54	30 W
911401510332	RC160V LED39/865 W30L120 PSU	30 W	911401537932	RC160V LED37/965 W30L120 PSU 54	30 W
911401511032	RC160V LED37/830 W30L120 PSU OC	30 W	911401538632	RC160V LED35/930 W30L120 PSD	30 W
911401511132	RC160V LED39/840 W30L120 PSU OC	30 W	911401538732	RC160V LED37/940 W30L120 PSD	30 W
911401511232	RC160V LED39/865 W30L120 PSU OC	30 W	911401538832	RC160V LED37/965 W30L120 PSD	30 W
911401511932	RC160V LED27/830 W30L120 PSU 16	22 W	911401539532	RC160X LED35/930 W30L120 WIA	30 W
911401512032	RC160V LED29/840 W30L120 PSU 16	22 W	911401539632	RC160X LED37/940 W30L120 WIA	30 W
911401512132	RC160V LED29/865 W30L120 PSU 16	22 W	911401539732	RC160X LED37/965 W30L120 WIA	30 W
911401512832	RC160V LED37/830 W30L120 PSU 54	30 W	911401540132	RC160X LED35/930 W30L120 SIA	30 W
911401512932	RC160V LED39/840 W30L120 PSU 54	30 W	911401540232	RC160X LED37/940 W30L120 SIA	30 W
911401513032	RC160V LED39/865 W30L120 PSU 54	30 W	911401540332	RC160X LED37/965 W30L120 SIA	30 W
911401513732	RC160V LED37/830 W30L120 PSU OC 54	30 W	911401510432	RC160V LED57/830 W60L120 PSU	46 W
911401513832	RC160V LED39/840 W30L120 PSU OC 54	30 W	911401510532	RC160V LED60/840 W60L120 PSU	46 W
911401513932	RC160V LED39/865 W30L120 PSU OC 54	30 W	911401510632	RC160V LED60/865 W60L120 PSU	46 W
911401514632	RC160V LED27/830 W30L120 PSU 16 54	22 W	911401511332	RC160V LED57/830 W60L120 PSU OC	46 W
911401514732	RC160V LED29/840 W30L120 PSU 16 54	22 W	911401511432	RC160V LED60/840 W60L120 PSU OC	46 W
911401514832	RC160V LED29/865 W30L120 PSU 16 54	22 W	911401511532	RC160V LED60/865 W60L120 PSU OC	46 W
911401520932	RC160V LED37/830 W30L120 PSD	30 W	911401512232	RC160V LED54/830 W60L120 PSU 16	46 W
911401521032	RC160V LED39/840 W30L120 PSD	30 W	911401512332	RC160V LED58/840 W60L120 PSU 16	46 W
911401521132	RC160V LED39/865 W30L120 PSD	30 W	911401512432	RC160V LED58/865 W60L120 PSU 16	46 W
911401521832	RC160V LED37/830 W30L120 PSD OC	30 W	911401513132	RC160V LED57/830 W60L120 PSU 54	46 W
911401521932	RC160V LED39/840 W30L120 PSD OC	30 W	911401513232	RC160V LED60/840 W60L120 PSU 54	46 W
911401522032	RC160V LED39/865 W30L120 PSD OC	30 W	911401513332	RC160V LED60/865 W60L120 PSU 54	46 W
911401522732	RC160V LED27/830 W30L120 PSD 16	22 W	911401514032	RC160V LED57/830 W60L120 PSU OC 54	46 W
911401522832	RC160V LED29/840 W30L120 PSD 16	22 W	911401514132	RC160V LED60/840 W60L120 PSU OC 54	46 W
911401522932	RC160V LED29/865 W30L120 PSD 16	22 W	911401514232	RC160V LED60/865 W60L120 PSU OC 54	46 W
911401523632	RC160X LED37/830 W30L120 WIA	30 W	911401514932	RC160V LED54/830 W60L120 PSU 16 54	46 W
911401523732	RC160X LED39/840 W30L120 WIA	30 W	911401515032	RC160V LED58/840 W60L120 PSU 16 54	46 W
911401523832	RC160X LED39/865 W30L120 WIA	30 W	911401515132	RC160V LED58/865 W60L120 PSU 16 54	46 W
911401524832	RC160X LED37/830 W30L120 SIA	30 W	911401521232	RC160V LED57/830 W60L120 PSD	46 W
911401524932	RC160X LED39/840 W30L120 SIA	30 W	911401521332	RC160V LED60/840 W60L120 PSD	46 W
911401525032	RC160X LED39/865 W30L120 SIA	30 W	911401521432	RC160V LED60/865 W60L120 PSD	46 W
911401536832	RC160V LED35/930 W30L120 PSU	30 W	911401522132	RC160V LED57/830 W60L120 PSD OC	46 W
911401536932	RC160V LED37/940 W30L120 PSU	30 W	911401522232	RC160V LED60/840 W60L120 PSD OC	46 W
911401537032	RC160V LED37/965 W30L120 PSU	30 W	911401522332	RC160V LED60/865 W60L120 PSD OC	46 W

RC160V

Order Code	Full Product Name	Power Consumption
911401523032	RC160V LED54/830 W60L120 PSD 16	46 W
911401523132	RC160V LED58/840 W60L120 PSD 16	46 W
911401523232	RC160V LED58/865 W60L120 PSD 16	46 W
911401525132	RC160X LED57/830 W60L120 SIA	46 W
911401525232	RC160X LED60/840 W60L120 SIA	46 W
911401525332	RC160X LED60/865 W60L120 SIA	46 W
911401537132	RC160V LED54/930 W60L120 PSU	46 W
911401537232	RC160V LED58/940 W60L120 PSU	46 W
911401537332	RC160V LED58/965 W60L120 PSU	46 W
911401538032	RC160V LED54/930 W60L120 PSU 54	46 W
911401538132	RC160V LED58/940 W60L120 PSU 54	46 W
911401538232	RC160V LED58/965 W60L120 PSU 54	46 W
911401538932	RC160V LED54/930 W60L120 PSD	46 W
911401539032	RC160V LED58/940 W60L120 PSD	46 W
911401539132	RC160V LED58/965 W60L120 PSD	46 W
911401540432	RC160X LED54/930 W60L120 SIA	46 W
911401540532	RC160X LED58/940 W60L120 SIA	46 W
911401540632	RC160X LED58/965 W60L120 SIA	46 W
911401544932	RC160X LED48/930 W60L120 WIA	40 W
911401545032	RC160X LED51/940 W60L120 WIA	40 W
911401545132	RC160X LED51/965 W60L120 WIA	40 W
911401509832	RC160V LED37/830 W60L60 PSU	30 W
911401509932	RC160V LED39/840 W60L60 PSU	30 W
911401510032	RC160V LED39/865 W60L60 PSU	30 W
911401510732	RC160V LED37/830 W60L60 PSU OC	30 W
911401510832	RC160V LED39/840 W60L60 PSU OC	30 W
911401510932	RC160V LED39/865 W60L60 PSU OC	30 W
911401511632	RC160V LED27/830 W60L60 PSU 16	22 W
911401511732	RC160V LED29/840 W60L60 PSU 16	22 W
911401511832	RC160V LED29/865 W60L60 PSU 16	22 W
911401512532	RC160V LED37/830 W60L60 PSU 54	30 W
911401512632	RC160V LED39/840 W60L60 PSU 54	30 W
911401512732	RC160V LED39/865 W60L60 PSU 54	30 W
911401513432	RC160V LED37/830 W60L60 PSU OC 54	30 W
911401513532	RC160V LED39/840 W60L60 PSU OC 54	30 W
911401513632	RC160V LED39/865 W60L60 PSU OC 54	30 W
911401514332	RC160V LED27/830 W60L60 PSU 16 54	22 W
911401514432	RC160V LED29/840 W60L60 PSU 16 54	22 W

Order Code	Full Product Name	Power Consumption
911401514532	RC160V LED29/865 W60L60 PSU 16 54	22 W
911401520632	RC160V LED37/830 W60L60 PSD	30 W
911401520732	RC160V LED39/840 W60L60 PSD	30 W
911401520832	RC160V LED39/865 W60L60 PSD	30 W
911401521532	RC160V LED37/830 W60L60 PSD OC	30 W
911401521632	RC160V LED39/840 W60L60 PSD OC	30 W
911401521732	RC160V LED39/865 W60L60 PSD OC	30 W
911401522432	RC160V LED27/830 W60L60 PSD 16	22 W
911401522532	RC160V LED29/840 W60L60 PSD 16	22 W
911401522632	RC160V LED29/865 W60L60 PSD 16	22 W
911401523332	RC160X LED37/830 W60L60 WIA	30 W
911401523432	RC160X LED39/840 W60L60 WIA	30 W
911401523532	RC160X LED39/865 W60L60 WIA	30 W
911401523932	RC160X LED37/830 W60L60 WIA OC	30 W
911401524032	RC160X LED39/840 W60L60 WIA OC	30 W
911401524132	RC160X LED39/865 W60L60 WIA OC	30 W
911401524232	RC160X LED27/830 W60L60 WIA 16	22 W
911401524332	RC160X LED29/840 W60L60 WIA 16	22 W
911401524432	RC160X LED29/865 W60L60 WIA 16	22 W
911401524532	RC160X LED37/830 W60L60 SIA	30 W
911401524632	RC160X LED39/840 W60L60 SIA	30 W
911401524732	RC160X LED39/865 W60L60 SIA	30 W
911401536532	RC160V LED35/930 W60L60 PSU	30 W
911401536632	RC160V LED37/940 W60L60 PSU	30 W
911401536732	RC160V LED37/965 W60L60 PSU	30 W
911401537432	RC160V LED35/930 W60L60 PSU 54	30 W
911401537532	RC160V LED37/940 W60L60 PSU 54	30 W
911401537632	RC160V LED37/965 W60L60 PSU 54	30 W
911401538332	RC160V LED35/930 W60L60 PSD	30 W
911401538432	RC160V LED37/940 W60L60 PSD	30 W
911401538532	RC160V LED37/965 W60L60 PSD	30 W
911401539332	RC160X LED37/940 W60L60 WIA	30 W
911401539432	RC160X LED37/965 W60L60 WIA	30 W
911401539832	RC160X LED35/930 W60L60 SIA	30 W
911401539932	RC160X LED37/940 W60L60 SIA	30 W
911401540032	RC160X LED37/965 W60L60 SIA	30 W
911401545532	RC160V LED36/9TW W60L60	30 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
911401510132	RC160V LED37/830 W30L120 PSU	Fixed	0% (digital)
911401510232	RC160V LED39/840 W30L120 PSU	Fixed	0% (digital)
911401510332	RC160V LED39/865 W30L120 PSU	Fixed	0% (digital)
911401511032	RC160V LED37/830 W30L120 PSU OC	Fixed	0% (digital)
911401511132	RC160V LED39/840 W30L120 PSU OC	Fixed	0% (digital)
911401511232	RC160V LED39/865 W30L120 PSU OC	Fixed	0% (digital)
911401511932	RC160V LED27/830 W30L120 PSU 16	Fixed	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
911401512032	RC160V LED29/840 W30L120 PSU 16	Fixed	0% (digital)
911401512132	RC160V LED29/865 W30L120 PSU 16	Fixed	0% (digital)
911401512832	RC160V LED37/830 W30L120 PSU 54	Fixed	0% (digital)
911401512932	RC160V LED39/840 W30L120 PSU 54	Fixed	0% (digital)
911401513032	RC160V LED39/865 W30L120 PSU 54	Fixed	0% (digital)

RC160V

Order Code	Full Product Name	Dimmable	Maximum dim level
911401513732	RC160V LED37/830 W30L120 PSU OC 54	Fixed	0% (digital)
911401513832	RC160V LED39/840 W30L120 PSU OC 54	Fixed	0% (digital)
911401513932	RC160V LED39/865 W30L120 PSU OC 54	Fixed	0% (digital)
911401514632	RC160V LED27/830 W30L120 PSU 16 54	Fixed	0% (digital)
911401514732	RC160V LED29/840 W30L120 PSU 16 54	Fixed	0% (digital)
911401514832	RC160V LED29/865 W30L120 PSU 16 54	Fixed	0% (digital)
911401520932	RC160V LED37/830 W30L120 PSD	DALI	Programmable
911401521032	RC160V LED39/840 W30L120 PSD	DALI	Programmable
911401521132	RC160V LED39/865 W30L120 PSD	DALI	Programmable
911401521832	RC160V LED37/830 W30L120 PSD OC	DALI	Programmable
911401521932	RC160V LED39/840 W30L120 PSD OC	DALI	Programmable
911401522032	RC160V LED39/865 W30L120 PSD OC	DALI	Programmable
911401522732	RC160V LED27/830 W30L120 PSD 16	DALI	Programmable
911401522832	RC160V LED29/840 W30L120 PSD 16	DALI	Programmable
911401522932	RC160V LED29/865 W30L120 PSD 16	DALI	Programmable
911401523632	RC160X LED37/830 W30L120 WIA	Wireless Dim	Programmable
911401523732	RC160X LED39/840 W30L120 WIA	Wireless Dim	Programmable
911401523832	RC160X LED39/865 W30L120 WIA	Wireless Dim	Programmable
911401524832	RC160X LED37/830 W30L120 SIA	Auto-Dim	0% (digital)
911401524932	RC160X LED39/840 W30L120 SIA	Auto-Dim	0% (digital)
911401525032	RC160X LED39/865 W30L120 SIA	Auto-Dim	0% (digital)
911401536832	RC160V LED35/930 W30L120 PSU	Fixed	0% (digital)
911401536932	RC160V LED37/940 W30L120 PSU	Fixed	0% (digital)
911401537032	RC160V LED37/965 W30L120 PSU	Fixed	0% (digital)
911401537732	RC160V LED35/930 W30L120 PSU 54	Fixed	0% (digital)
911401537832	RC160V LED37/940 W30L120 PSU 54	Fixed	0% (digital)
911401537932	RC160V LED37/965 W30L120 PSU 54	Fixed	0% (digital)
911401538632	RC160V LED35/930 W30L120 PSD	DALI	Programmable
911401538732	RC160V LED37/940 W30L120 PSD	DALI	Programmable
911401538832	RC160V LED37/965 W30L120 PSD	DALI	Programmable
911401539532	RC160X LED35/930 W30L120 WIA	Wireless Dim	Programmable
911401539632	RC160X LED37/940 W30L120 WIA	Wireless Dim	Programmable
911401539732	RC160X LED37/965 W30L120 WIA	Wireless Dim	Programmable
911401540132	RC160X LED35/930 W30L120 SIA	Auto-Dim	0% (digital)
911401540232	RC160X LED37/940 W30L120 SIA	Auto-Dim	0% (digital)
911401540332	RC160X LED37/965 W30L120 SIA	Auto-Dim	0% (digital)
911401510432	RC160V LED57/830 W60L120 PSU	Fixed	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
911401510532	RC160V LED60/840 W60L120 PSU	Fixed	0% (digital)
911401510632	RC160V LED60/865 W60L120 PSU	Fixed	0% (digital)
911401511332	RC160V LED57/830 W60L120 PSU OC	Fixed	0% (digital)
911401511432	RC160V LED60/840 W60L120 PSU OC	Fixed	0% (digital)
911401511532	RC160V LED60/865 W60L120 PSU OC	Fixed	0% (digital)
911401512232	RC160V LED54/830 W60L120 PSU 16	Fixed	0% (digital)
911401512332	RC160V LED58/840 W60L120 PSU 16	Fixed	0% (digital)
911401512432	RC160V LED58/865 W60L120 PSU 16	Fixed	0% (digital)
911401513132	RC160V LED57/830 W60L120 PSU 54	Fixed	0% (digital)
911401513232	RC160V LED60/840 W60L120 PSU 54	Fixed	0% (digital)
911401513332	RC160V LED60/865 W60L120 PSU 54	Fixed	0% (digital)
911401514032	RC160V LED57/830 W60L120 PSU OC 54	Fixed	0% (digital)
911401514132	RC160V LED60/840 W60L120 PSU OC 54	Fixed	0% (digital)
911401514232	RC160V LED60/865 W60L120 PSU OC 54	Fixed	0% (digital)
911401514932	RC160V LED54/830 W60L120 PSU 16 54	Fixed	0% (digital)
911401515032	RC160V LED58/840 W60L120 PSU 16 54	Fixed	0% (digital)
911401515132	RC160V LED58/865 W60L120 PSU 16 54	Fixed	0% (digital)
911401521232	RC160V LED57/830 W60L120 PSD	DALI	Programmable
911401521332	RC160V LED60/840 W60L120 PSD	DALI	Programmable
911401521432	RC160V LED60/865 W60L120 PSD	DALI	Programmable
911401522132	RC160V LED57/830 W60L120 PSD OC	DALI	Programmable
911401522232	RC160V LED60/840 W60L120 PSD OC	DALI	Programmable
911401522332	RC160V LED60/865 W60L120 PSD OC	DALI	Programmable
911401523032	RC160V LED54/830 W60L120 PSD 16	DALI	Programmable
911401523132	RC160V LED58/840 W60L120 PSD 16	DALI	Programmable
911401523232	RC160V LED58/865 W60L120 PSD 16	DALI	Programmable
911401525132	RC160X LED57/830 W60L120 SIA	Auto-Dim	0% (digital)
911401525232	RC160X LED60/840 W60L120 SIA	Auto-Dim	0% (digital)
911401525332	RC160X LED60/865 W60L120 SIA	Auto-Dim	0% (digital)
911401537132	RC160V LED54/930 W60L120 PSU	Fixed	0% (digital)
911401537232	RC160V LED58/940 W60L120 PSU	Fixed	0% (digital)

RC160V

Order Code	Full Product Name	Dimmable	Maximum dim level
911401537332	RC160V LED58/965 W60L120 PSU	Fixed	0% (digital)
911401538032	RC160V LED54/930 W60L120 PSU	Fixed	0% (digital)
	54		
911401538132	RC160V LED58/940 W60L120 PSU	Fixed	0% (digital)
	54		
911401538232	RC160V LED58/965 W60L120 PSU	Fixed	0% (digital)
	54		
911401538932	RC160V LED54/930 W60L120 PSD	DALI	Programmable
911401539032	RC160V LED58/940 W60L120 PSD	DALI	Programmable
911401539132	RC160V LED58/965 W60L120 PSD	DALI	Programmable
911401540432	RC160X LED54/930 W60L120 SIA	Auto-Dim	0% (digital)
911401540532	RC160X LED58/940 W60L120 SIA	Auto-Dim	0% (digital)
911401540632	RC160X LED58/965 W60L120 SIA	Auto-Dim	0% (digital)
911401544932	RC160X LED48/930 W60L120 WIA	Wireless Dim	Programmable
911401545032	RC160X LED51/940 W60L120 WIA	Wireless Dim	Programmable
911401545132	RC160X LED51/965 W60L120 WIA	Wireless Dim	Programmable
911401509832	RC160V LED37/830 W60L60 PSU	Fixed	0% (digital)
911401509932	RC160V LED39/840 W60L60 PSU	Fixed	0% (digital)
911401510032	RC160V LED39/865 W60L60 PSU	Fixed	0% (digital)
911401510732	RC160V LED37/830 W60L60 PSU	Fixed	0% (digital)
	OC		
911401510832	RC160V LED39/840 W60L60 PSU	Fixed	0% (digital)
	OC		
911401510932	RC160V LED39/865 W60L60 PSU	Fixed	0% (digital)
	OC		
911401511632	RC160V LED27/830 W60L60 PSU 16	Fixed	0% (digital)
911401511732	RC160V LED29/840 W60L60 PSU 16	Fixed	0% (digital)
911401511832	RC160V LED29/865 W60L60 PSU 16	Fixed	0% (digital)
911401512532	RC160V LED37/830 W60L60 PSU 54	Fixed	0% (digital)
911401512632	RC160V LED39/840 W60L60 PSU	Fixed	0% (digital)
	54		
911401512732	RC160V LED39/865 W60L60 PSU	Fixed	0% (digital)
	54		
911401513432	RC160V LED37/830 W60L60 PSU	Fixed	0% (digital)
	OC 54		
911401513532	RC160V LED39/840 W60L60 PSU	Fixed	0% (digital)
	OC 54		
911401513632	RC160V LED39/865 W60L60 PSU	Fixed	0% (digital)
	OC 54		
911401514332	RC160V LED27/830 W60L60 PSU 16	Fixed	0% (digital)
	54		
911401514432	RC160V LED29/840 W60L60 PSU 16	Fixed	0% (digital)
	54		
911401514532	RC160V LED29/865 W60L60 PSU 16	Fixed	0% (digital)
	54		

Order Code	Full Product Name	Dimmable	Maximum dim level
911401520632	RC160V LED37/830 W60L60 PSD	DALI	Programmable
911401520732	RC160V LED39/840 W60L60 PSD	DALI	Programmable
911401520832	RC160V LED39/865 W60L60 PSD	DALI	Programmable
911401521532	RC160V LED37/830 W60L60 PSD	DALI	Programmable
	OC		
911401521632	RC160V LED39/840 W60L60 PSD	DALI	Programmable
	OC		
911401521732	RC160V LED39/865 W60L60 PSD	DALI	Programmable
	OC		
911401522432	RC160V LED27/830 W60L60 PSD 16	DALI	Programmable
911401522532	RC160V LED29/840 W60L60 PSD 16	DALI	Programmable
911401522632	RC160V LED29/865 W60L60 PSD 16	DALI	Programmable
911401523332	RC160X LED37/830 W60L60 WIA	Wireless Dim	Programmable
911401523432	RC160X LED39/840 W60L60 WIA	Wireless Dim	Programmable
911401523532	RC160X LED39/865 W60L60 WIA	Wireless Dim	Programmable
911401523932	RC160X LED37/830 W60L60 WIA	Wireless Dim	Programmable
	OC		
911401524032	RC160X LED39/840 W60L60 WIA	Wireless Dim	Programmable
	OC		
911401524132	RC160X LED39/865 W60L60 WIA	Wireless Dim	Programmable
	OC		
911401524232	RC160X LED27/830 W60L60 WIA 16	Wireless Dim	Programmable
911401524332	RC160X LED29/840 W60L60 WIA 16	Wireless Dim	Programmable
911401524432	RC160X LED29/865 W60L60 WIA 16	Wireless Dim	Programmable
911401524532	RC160X LED37/830 W60L60 SIA	Auto-Dim	0% (digital)
911401524632	RC160X LED39/840 W60L60 SIA	Auto-Dim	0% (digital)
911401524732	RC160X LED39/865 W60L60 SIA	Auto-Dim	0% (digital)
911401536532	RC160V LED35/930 W60L60 PSU	Fixed	0% (digital)
911401536632	RC160V LED37/940 W60L60 PSU	Fixed	0% (digital)
911401536732	RC160V LED37/965 W60L60 PSU	Fixed	0% (digital)
911401537432	RC160V LED35/930 W60L60 PSU	Fixed	0% (digital)
	54		
911401537532	RC160V LED37/940 W60L60 PSU 54	Fixed	0% (digital)
911401537632	RC160V LED37/965 W60L60 PSU 54	Fixed	0% (digital)
911401538332	RC160V LED35/930 W60L60 PSD	DALI	Programmable
911401538432	RC160V LED37/940 W60L60 PSD	DALI	Programmable
911401538532	RC160V LED37/965 W60L60 PSD	DALI	Programmable
911401539332	RC160X LED37/940 W60L60 WIA	Wireless Dim	Programmable
911401539432	RC160X LED37/965 W60L60 WIA	Wireless Dim	Programmable
911401539832	RC160X LED35/930 W60L60 SIA	Auto-Dim	0% (digital)
911401539932	RC160X LED37/940 W60L60 SIA	Auto-Dim	0% (digital)
911401540032	RC160X LED37/965 W60L60 SIA	Auto-Dim	0% (digital)
911401545532	RC160V LED36/9TW W60L60	DALI	Programmable

Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401510132	RC160V LED37/830 W30L120 PSU	PS	IP20
911401510232	RC160V LED39/840 W30L120 PSU	PS	IP20
911401510332	RC160V LED39/865 W30L120 PSU	PS	IP20
911401511032	RC160V LED37/830 W30L120 PSU OC	PS	IP20
911401511132	RC160V LED39/840 W30L120 PSU OC	PS	IP20
911401511232	RC160V LED39/865 W30L120 PSU OC	PS	IP20
911401511932	RC160V LED27/830 W30L120 PSU 16	Polycarbonate bowl/cover	IP20
911401512032	RC160V LED29/840 W30L120 PSU 16	Polycarbonate bowl/cover	IP20
911401512132	RC160V LED29/865 W30L120 PSU 16	Polycarbonate bowl/cover	IP20
911401512832	RC160V LED37/830 W30L120 PSU 54	PS	IP54/20
911401512932	RC160V LED39/840 W30L120 PSU 54	PS	IP54/20
911401513032	RC160V LED39/865 W30L120 PSU 54	PS	IP54/20
911401513732	RC160V LED37/830 W30L120 PSU OC 54	PS	IP54/20
911401513832	RC160V LED39/840 W30L120 PSU OC 54	PS	IP54/20
911401513932	RC160V LED39/865 W30L120 PSU OC 54	PS	IP54/20
911401514632	RC160V LED27/830 W30L120 PSU 16 54	Polycarbonate bowl/cover	IP54/20
911401514732	RC160V LED29/840 W30L120 PSU 16 54	Polycarbonate bowl/cover	IP54/20
911401514832	RC160V LED29/865 W30L120 PSU 16 54	Polycarbonate bowl/cover	IP54/20
911401520932	RC160V LED37/830 W30L120 PSD	PS	IP20
911401521032	RC160V LED39/840 W30L120 PSD	PS	IP20
911401521132	RC160V LED39/865 W30L120 PSD	PS	IP20
911401521832	RC160V LED37/830 W30L120 PSD OC	PS	IP20
911401521932	RC160V LED39/840 W30L120 PSD OC	PS	IP20
911401522032	RC160V LED39/865 W30L120 PSD OC	PS	IP20
911401522732	RC160V LED27/830 W30L120 PSD 16	Polycarbonate bowl/cover	IP20

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401522832	RC160V LED29/840 W30L120 PSD 16	Polycarbonate bowl/cover	IP20
911401522932	RC160V LED29/865 W30L120 PSD 16	Polycarbonate bowl/cover	IP20
911401523632	RC160X LED37/830 W30L120 WIA	PS	IP20
911401523732	RC160X LED39/840 W30L120 WIA	PS	IP20
911401523832	RC160X LED39/865 W30L120 WIA	PS	IP20
911401524832	RC160X LED37/830 W30L120 SIA	PS	IP20
911401524932	RC160X LED39/840 W30L120 SIA	PS	IP20
911401525032	RC160X LED39/865 W30L120 SIA	PS	IP20
911401536832	RC160V LED35/930 W30L120 PSU	PS	IP20
911401536932	RC160V LED37/940 W30L120 PSU	PS	IP20
911401537032	RC160V LED37/965 W30L120 PSU	PS	IP20
911401537732	RC160V LED35/930 W30L120 PSU 54	PS	IP54/20
911401537832	RC160V LED37/940 W30L120 PSU 54	PS	IP54/20
911401537932	RC160V LED37/965 W30L120 PSU 54	PS	IP54/20
911401538632	RC160V LED35/930 W30L120 PSD	PS	IP20
911401538732	RC160V LED37/940 W30L120 PSD	PS	IP20
911401538832	RC160V LED37/965 W30L120 PSD	PS	IP20
911401539532	RC160X LED35/930 W30L120 WIA	PS	IP20
911401539632	RC160X LED37/940 W30L120 WIA	PS	IP20
911401539732	RC160X LED37/965 W30L120 WIA	PS	IP20
911401540132	RC160X LED35/930 W30L120 SIA	PS	IP20
911401540232	RC160X LED37/940 W30L120 SIA	PS	IP20
911401540332	RC160X LED37/965 W30L120 SIA	PS	IP20
911401510432	RC160V LED57/830 W60L120 PSU	PS	IP20
911401510532	RC160V LED60/840 W60L120 PSU	PS	IP20
911401510632	RC160V LED60/865 W60L120 PSU	PS	IP20

RC160V

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401511332	RC160V LED57/830 W60L120 PSU OC	PS	IP20
911401511432	RC160V LED60/840 W60L120 PSU OC	PS	IP20
911401511532	RC160V LED60/865 W60L120 PSU OC	PS	IP20
911401512232	RC160V LED54/830 W60L120 PSU 16	Polycarbonate bowl/cover	IP20
911401512332	RC160V LED58/840 W60L120 PSU 16	Polycarbonate bowl/cover	IP20
911401512432	RC160V LED58/865 W60L120 PSU 16	Polycarbonate bowl/cover	IP20
911401513132	RC160V LED57/830 W60L120 PSU 54	PS	IP54/20
911401513232	RC160V LED60/840 W60L120 PSU 54	PS	IP54/20
911401513332	RC160V LED60/865 W60L120 PSU 54	PS	IP54/20
911401514032	RC160V LED57/830 W60L120 PSU OC 54	PS	IP54/20
911401514132	RC160V LED60/840 W60L120 PSU OC 54	PS	IP54/20
911401514232	RC160V LED60/865 W60L120 PSU OC 54	PS	IP54/20
911401514932	RC160V LED54/830 W60L120 PSU 16 54	Polycarbonate bowl/cover	IP54/20
911401515032	RC160V LED58/840 W60L120 PSU 16 54	Polycarbonate bowl/cover	IP54/20
911401515132	RC160V LED58/865 W60L120 PSU 16 54	Polycarbonate bowl/cover	IP54/20
911401521232	RC160V LED57/830 W60L120 PSD	PS	IP20
911401521332	RC160V LED60/840 W60L120 PSD	PS	IP20
911401521432	RC160V LED60/865 W60L120 PSD	PS	IP20
911401522132	RC160V LED57/830 W60L120 PSD OC	PS	IP20
911401522232	RC160V LED60/840 W60L120 PSD OC	PS	IP20
911401522332	RC160V LED60/865 W60L120 PSD OC	PS	IP20
911401523032	RC160V LED54/830 W60L120 PSD 16	Polycarbonate bowl/cover	IP20
911401523132	RC160V LED58/840 W60L120 PSD 16	Polycarbonate bowl/cover	IP20
911401523232	RC160V LED58/865 W60L120 PSD 16	Polycarbonate bowl/cover	IP20
911401525132	RC160X LED57/830 W60L120 SIA	PS	IP20

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401525232	RC160X LED60/840 W60L120 SIA	PS	IP20
911401525332	RC160X LED60/865 W60L120 SIA	PS	IP20
911401537132	RC160V LED54/930 W60L120 PSU	PS	IP20
911401537232	RC160V LED58/940 W60L120 PSU	PS	IP20
911401537332	RC160V LED58/965 W60L120 PSU	PS	IP20
911401538032	RC160V LED54/930 W60L120 PSU 54	PS	IP54/20
911401538132	RC160V LED58/940 W60L120 PSU 54	PS	IP54/20
911401538232	RC160V LED58/965 W60L120 PSU 54	PS	IP54/20
911401538932	RC160V LED54/930 W60L120 PSD	PS	IP20
911401539032	RC160V LED58/940 W60L120 PSD	PS	IP20
911401539132	RC160V LED58/965 W60L120 PSD	PS	IP20
911401540432	RC160X LED54/930 W60L120 SIA	PS	IP20
911401540532	RC160X LED58/940 W60L120 SIA	PS	IP20
911401540632	RC160X LED58/965 W60L120 SIA	PS	IP20
911401544932	RC160X LED48/930 W60L120 WIA	PS	IP20
911401545032	RC160X LED51/940 W60L120 WIA	PS	IP20
911401545132	RC160X LED51/965 W60L120 WIA	PS	IP20
911401509832	RC160V LED37/830 W60L60 PSU	PS	IP20
911401509932	RC160V LED39/840 W60L60 PSU	PS	IP20
911401510032	RC160V LED39/865 W60L60 PSU	PS	IP20
911401510732	RC160V LED37/830 W60L60 PSU OC	PS	IP20
911401510832	RC160V LED39/840 W60L60 PSU OC	PS	IP20
911401510932	RC160V LED39/865 W60L60 PSU OC	PS	IP20
911401511632	RC160V LED27/830 W60L60 PSU 16	Polycarbonate bowl/cover	IP20
911401511732	RC160V LED29/840 W60L60 PSU 16	Polycarbonate bowl/cover	IP20

RC160V

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401511832	RC160V LED29/865 W60L60 PSU 16	Polycarbonate bowl/cover	IP20
911401512532	RC160V LED37/830 W60L60 PSU 54	PS	IP54/20
911401512632	RC160V LED39/840 W60L60 PSU 54	PS	IP54/20
911401512732	RC160V LED39/865 W60L60 PSU 54	PS	IP54/20
911401513432	RC160V LED37/830 W60L60 PSU OC 54	PS	IP54/20
911401513532	RC160V LED39/840 W60L60 PSU OC 54	PS	IP54/20
911401513632	RC160V LED39/865 W60L60 PSU OC 54	PS	IP54/20
911401514332	RC160V LED27/830 W60L60 PSU 16 54	Polycarbonate bowl/cover	IP54/20
911401514432	RC160V LED29/840 W60L60 PSU 16 54	Polycarbonate bowl/cover	IP54/20
911401514532	RC160V LED29/865 W60L60 PSU 16 54	Polycarbonate bowl/cover	IP54/20
911401520632	RC160V LED37/830 W60L60 PSD	PS	IP20
911401520732	RC160V LED39/840 W60L60 PSD	PS	IP20
911401520832	RC160V LED39/865 W60L60 PSD	PS	IP20
911401521532	RC160V LED37/830 W60L60 PSD OC	PS	IP20
911401521632	RC160V LED39/840 W60L60 PSD OC	PS	IP20
911401521732	RC160V LED39/865 W60L60 PSD OC	PS	IP20
911401522432	RC160V LED27/830 W60L60 PSD 16	Polycarbonate bowl/cover	IP20
911401522532	RC160V LED29/840 W60L60 PSD 16	Polycarbonate bowl/cover	IP20
911401522632	RC160V LED29/865 W60L60 PSD 16	Polycarbonate bowl/cover	IP20
911401523332	RC160X LED37/830 W60L60 WIA	PS	IP20
911401523432	RC160X LED39/840 W60L60 WIA	PS	IP20
911401523532	RC160X LED39/865 W60L60 WIA	PS	IP20

Order Code	Full Product Name	Optical cover type	Ingress protection code
911401523932	RC160X LED37/830 W60L60 WIA OC	PS	IP20
911401524032	RC160X LED39/840 W60L60 WIA OC	PS	IP20
911401524132	RC160X LED39/865 W60L60 WIA OC	PS	IP20
911401524232	RC160X LED27/830 W60L60 WIA 16	Polycarbonate bowl/cover	IP20
911401524332	RC160X LED29/840 W60L60 WIA 16	Polycarbonate bowl/cover	IP20
911401524432	RC160X LED29/865 W60L60 WIA 16	Polycarbonate bowl/cover	IP20
911401524532	RC160X LED37/830 W60L60 SIA	PS	IP20
911401524632	RC160X LED39/840 W60L60 SIA	PS	IP20
911401524732	RC160X LED39/865 W60L60 SIA	PS	IP20
911401536532	RC160V LED35/930 W60L60 PSU	PS	IP20
911401536632	RC160V LED37/940 W60L60 PSU	PS	IP20
911401536732	RC160V LED37/965 W60L60 PSU	PS	IP20
911401537432	RC160V LED35/930 W60L60 PSU 54	PS	IP54/20
911401537532	RC160V LED37/940 W60L60 PSU 54	PS	IP54/20
911401537632	RC160V LED37/965 W60L60 PSU 54	PS	IP54/20
911401538332	RC160V LED35/930 W60L60 PSD	PS	IP20
911401538432	RC160V LED37/940 W60L60 PSD	PS	IP20
911401538532	RC160V LED37/965 W60L60 PSD	PS	IP20
911401539332	RC160X LED37/940 W60L60 WIA	PS	IP20
911401539432	RC160X LED37/965 W60L60 WIA	PS	IP20
911401539832	RC160X LED35/930 W60L60 SIA	PS	IP20
911401539932	RC160X LED37/940 W60L60 SIA	PS	IP20
911401540032	RC160X LED37/965 W60L60 SIA	PS	IP20
911401545532	RC160V LED36/9TW W60L60	PS	IP20

