



Ultra efficient and peace of mind

GreenPerform ultra efficient panel RC199B

GreenPerform ultra efficient panel is a direct lit panel with up to 170lm/w system efficacy (PSU driver) in the market. It offers 3 typical dimensions: 600x600; 300x1200 and 600x1200mm to fit most of indoor applications. Interact system option and Dali interface are available for wide option for system connection. Its lower UGR offers better visual comfort as well.

Benefits

- Ultra efficient lm/w provides better energy saving
- Interact and Dali interfaces available for easy system connection
- Lower UGR offer for better visual comfort
- Multiple mountings to cater for various applications

Features

- System efficacy up to 170lm/W (PSU driver / CRI80 / UGR22 version only)
- CRI 80 and 90 available
- Lifetime: 50k hours (L80@25deg)
- UGR19 available for certain types
- IP40 front side/IP20 back side available

Application






- Open plan office
- Public indoor area
- Meeting/Training room

Specifications

Ceiling type	T-bar ceiling	Dimming	PSD Dali dimmable
--------------	---------------	---------	-------------------

GreenPerform ultra efficient panel RC199B

Dimensional drawing



GreenPerform ultra efficient panel RC199B

General Information

Driver included	Yes
Gear	-
Number of gear units	1 unit

Light Technical

Correlated Color Temperature (Nom)	4000 K
Optic type	Beam angle 100°

Operating and Electrical

Protection class IEC	Safety class II
Input Voltage	200 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable

Controls and Dimming

Maximum dim level	0% (digital)
-------------------	--------------

Mechanical and Housing

Optical cover type	PS
Housing Color	White RAL 9003
Mech. impact protection code	IK02
Ingress protection code	IP20/40

Approval and Application

Ambient temperature range	-20 to +45 °C
CE mark	Yes
ENEC mark	-
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Light Technical

Order Code	Full Product Name	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Number of light sources
911401546744	RC199V LED36/840 PSU W60L60 OC UE	80	170 lm/W	3,900 lm	96
911401547044	RC199V LED39/840 PSU W60L60 UE	80	162 lm/W	3,750 lm	96
911401547344	RC199V LED35/840 PSD W60L60 OC UE	80	153 lm/W	3,500 lm	96
911401547644	RC199V LED37/840 PSD W60L60 UE	80	165 lm/W	3,750 lm	96
911401547944	RC199X LED35/840 WIA W60L60 OC UE	80	160 lm/W	3,520 lm	96
911401548244	RC199X LED38/840 WIA W60L60 UE	80	170 lm/W	3,800 lm	96
911401548544	RC199V LED36/840 PSU W60L60 OC CAU UE	80	170 lm/W	3,900 lm	96
911401548844	RC199V LED39/840 PSU W60L60 CAU UE	80	162 lm/W	3,750 lm	96
911401549144	RC199V LED35/840 PSD W60L60 OC CAU UE	80	155 lm/W	3,500 lm	96
911401549444	RC199V LED38/840 PSD W60L60 CAU UE	80	165 lm/W	3,800 lm	96
911401549744	RC199X LED36/840 WIA W60L60 OC CAU UE	80	160 lm/W	3,600 lm	96
911401550044	RC199X LED38/840 WIA W60L60 CAU UE	80	170 lm/W	3,800 lm	96
911401550344	RC199V LED35/940 PSU W60L60 OC UE	90	170 lm/W	3,900 lm	96
911401550644	RC199V LED37/940 PSU W60L60 UE	90	164 lm/W	3,780 lm	96
911401550944	RC199V LED34/940 PSD W60L60 OC UE	90	145 lm/W	3,400 lm	96
911401551244	RC199V LED35/940 PSD W60L60 UE	90	156 lm/W	3,580 lm	96
911401551544	RC199X LED33/940 WIA W60L60 OC UE	90	150 lm/W	3,350 lm	96
911401551844	RC199X LED35/940 WIA W60L60 UE	90	160 lm/W	3,550 lm	96
911401552144	RC199V LED35/940 PSU W60L60 OC CAU UE	90	170 lm/W	3,900 lm	96
911401552444	RC199V LED37/940 PSU W60L60 CAU UE	90	164 lm/W	3,780 lm	96
911401552744	RC199V LED34/940 PSD W60L60 OC CAU UE	90	145 lm/W	3,400 lm	96
911401553044	RC199V LED36/940 PSD W60L60 CAU UE	90	157 lm/W	3,600 lm	96
911401553344	RC199X LED34/940 WIA W60L60 OC CAU UE	90	150 lm/W	3,400 lm	96
911401553644	RC199X LED35/940 WIA W60L60 CAU UE	90	160 lm/W	3,550 lm	96

GreenPerform ultra efficient panel RC199B

Order Code	Full Product Name	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Number of light sources	
				Luminous Flux	
911401558944	RC199V LED36/840 PSU W60L60 OC UE CN	80	154 lm/W	5,100 lm	144
911401559244	RC199V LED39/840 PSU W60L60 UE CN	80	160 lm/W	5,400 lm	144
911401559544	RC199V LED35/840 PSD W60L60 OC UE CN	80	153 lm/W	3,500 lm	96
911401559844	RC199V LED37/840 PSD W60L60 UE CN	80	165 lm/W	3,750 lm	96
911401560144	RC199X LED35/840 WIA W60L60 OC UE CN	80	160 lm/W	3,520 lm	96
911401560444	RC199X LED38/840 WIA W60L60 UE CN	80	170 lm/W	3,800 lm	96
911401560744	RC199V LED35/940 PSU W60L60 OC UE CN	90	160 lm/W	5,450 lm	144
911401561044	RC199V LED37/940 PSU W60L60 UE CN	90	154 lm/W	5,150 lm	144
911401561344	RC199V LED34/940 PSD W60L60 OC UE CN	90	145 lm/W	3,400 lm	96
911401561644	RC199V LED35/940 PSD W60L60 UE CN	90	156 lm/W	3,580 lm	96
911401561944	RC199X LED33/940 WIA W60L60 OC UE CN	90	150 lm/W	3,350 lm	96
911401562244	RC199X LED35/940 WIA W60L60 UE CN	90	160 lm/W	3,550 lm	96
911401546544	RC199V LED54/840 PSU W60L120 OC UE	90	160 lm/W	5,400 lm	144
911401546844	RC199V LED57/840 PSU W60L120 UE	80	162 lm/W	5,380 lm	144
911401547144	RC199V LED54/840 PSD W60L120 OC UE	80	162 lm/W	5,400 lm	144
911401547444	RC199V LED56/840 PSD W60L120 UE	80	170 lm/W	5,650 lm	144
911401547744	RC199X LED54/840 WIA W60L120 OC UE	80	165 lm/W	5,400 lm	144
911401548044	RC199X LED57/840 WIA W60L120 UE	80	170 lm/W	5,720 lm	144
911401548344	RC199V LED54/840 PSU W60L120 OC CAU UE	80	154 lm/W	5,100 lm	144
911401548644	RC199V LED58/840 PSU W60L120 CAU UE	80	164 lm/W	3,780 lm	96
911401548944	RC199V LED54/840 PSD W60L120 OC CAU UE	80	163 lm/W	5,400 lm	144
911401549244	RC199V LED56/840 PSD W60L120 CAU UE	80	170 lm/W	5,600 lm	144
911401549544	RC199X LED54/840 WIA W60L120 OC CAU UE	80	165 lm/W	5,400 lm	144
911401549844	RC199X LED57/840 WIA W60L120 CAU UE	80	170 lm/W	5,700 lm	144
911401550144	RC199V LED51/940 PSU W60L120 OC UE	90	160 lm/W	3,650 lm	96

GreenPerform ultra efficient panel RC199B

Order Code	Full Product Name	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Number of light sources	
				Luminous Flux	
911401550444	RC199V LED53/940 PSU W60L120 UE	90	170 lm/W	3,900 lm	96
911401550744	RC199V LED50/940 PSD W60L120 OC UE	90	148 lm/W	5,000 lm	144
911401551044	RC199V LED53/940 PSD W60L120 UE	90	160 lm/W	5,350 lm	144
911401551344	RC199X LED50/940 WIA W60L120 OC UE	90	152 lm/W	5,080 lm	144
911401551644	RC199X LED53/940 WIA W60L120 UE	90	160 lm/W	5,350 lm	144
911401551944	RC199V LED51/940 PSU W60L120 OC CAU UE	90	160 lm/W	3,650 lm	96
911401552244	RC199V LED54/940 PSU W60L120 CAU UE	90	154 lm/W	3,520 lm	96
911401552544	RC199V LED50/940 PSD W60L120 OC CAU UE	90	145 lm/W	5,000 lm	144
911401552844	RC199V LED53/940 PSD W60L120 CAU UE	90	160 lm/W	5,350 lm	144
911401553144	RC199X LED50/940 WIA W60L120 OC CAU UE	90	152 lm/W	5,080 lm	144
911401553444	RC199X LED53/940 WIA W60L120 CAU UE	90	160 lm/W	5,350 lm	144
911401558744	RC199V LED54/840 PSU W60L120 OC UE CN	80	154 lm/W	3,520 lm	96
911401559044	RC199V LED57/840 PSU W60L120 UE CN	80	164 lm/W	3,780 lm	96
911401559344	RC199V LED54/840 PSD W60L120 OC UE CN	80	162 lm/W	5,400 lm	144
911401559644	RC199V LED56/840 PSD W60L120 UE CN	80	170 lm/W	5,650 lm	144
911401559944	RC199X LED54/840 WIA W60L120 OC UE CN	80	165 lm/W	5,400 lm	144
911401560244	RC199X LED57/840 WIA W60L120 UE CN	80	170 lm/W	5,720 lm	144
911401560544	RC199V LED51/940 PSU W60L120 OC UE CN	90	170 lm/W	5,700 lm	144
911401560844	RC199V LED53/940 PSU W60L120 UE CN	90	170 lm/W	3,900 lm	96
911401561144	RC199V LED50/940 PSD W60L120 OC UE CN	90	148 lm/W	5,000 lm	144
911401561444	RC199V LED53/940 PSD W60L120 UE CN	90	160 lm/W	5,350 lm	144
911401561744	RC199X LED50/940 WIA W60L120 OC UE CN	90	152 lm/W	5,080 lm	144
911401562044	RC199X LED53/940 WIA W60L120 UE CN	90	160 lm/W	5,350 lm	144
911401546644	RC199V LED36/840 PSU W30L120 OC UE	80	156 lm/W	3,620 lm	96
911401546944	RC199V LED39/840 PSU W30L120 UE	80	152 lm/W	3,500 lm	96

GreenPerform ultra efficient panel RC199B

Order Code	Full Product Name	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Number of light sources	
				Luminous Flux	
911401547244	RC199V LED35/840 PSD W30L120 OC UE	80	153 lm/W	3,500 lm	96
911401547544	RC199V LED37/840 PSD W30L120 UE	80	165 lm/W	3,750 lm	96
911401547844	RC199X LED35/840 WIA W30L120 OC UE	80	160 lm/W	3,520 lm	96
911401548144	RC199X LED38/840 WIA W30L120 UE	80	170 lm/W	3,800 lm	96
911401548444	RC199V LED36/840 PSU W30L120 OC CAU UE	80	156 lm/W	3,620 lm	96
911401548744	RC199V LED39/840 PSU W30L120 CAU UE	80	152 lm/W	3,500 lm	96
911401549044	RC199V LED35/840 PSD W30L120 OC CAU UE	80	155 lm/W	3,500 lm	96
911401549344	RC199V LED38/840 PSD W30L120 CAU UE	80	165 lm/W	3,800 lm	96
911401549644	RC199X LED36/840 WIA W30L120 OC CAU UE	80	160 lm/W	3,600 lm	96
911401549944	RC199X LED38/840 WIA W30L120 CAU UE	80	170 lm/W	3,800 lm	96
911401550244	RC199V LED35/940 PSU W30L120 OC UE	90	160 lm/W	3,650 lm	96
911401550544	RC199V LED37/940 PSU W30L120 UE	90	154 lm/W	3,520 lm	96
911401550844	RC199V LED34/940 PSD W30L120 OC UE	90	145 lm/W	3,400 lm	96
911401551144	RC199V LED35/940 PSD W30L120 UE	90	156 lm/W	3,580 lm	96
911401551444	RC199X LED33/940 WIA W30L120 OC UE	90	150 lm/W	3,350 lm	96
911401551744	RC199X LED35/940 WIA W30L120 UE	90	160 lm/W	3,550 lm	96
911401552044	RC199V LED35/940 PSU W30L120 OC CAU UE	90	160 lm/W	3,650 lm	96
911401552344	RC199V LED37/940 PSU W30L120 CAU UE	90	154 lm/W	3,520 lm	96
911401552644	RC199V LED34/940 PSD W30L120 OC CAU UE	90	145 lm/W	3,400 lm	96
911401552944	RC199V LED36/940 PSD W30L120 CAU UE	90	157 lm/W	3,600 lm	96
911401553244	RC199X LED34/940 WIA W30L120 OC CAU UE	90	150 lm/W	3,400 lm	96
911401553544	RC199X LED35/940 WIA W30L120 CAU UE	90	160 lm/W	3,550 lm	96
911401558844	RC199V LED36/840 PSU W30L120 OC UE CN	80	170 lm/W	5,800 lm	144
911401559144	RC199V LED39/840 PSU W30L120 UE CN	80	160 lm/W	5,450 lm	144
911401559444	RC199V LED35/840 PSD W30L120 OC UE CN	80	153 lm/W	3,500 lm	96

GreenPerform ultra efficient panel RC199B

Order Code	Full Product Name	Color rendering	Luminous Efficacy		Number of light sources
		index (CRI)	(rated) (Nom)	Luminous Flux	
911401559744	RC199V LED37/840 PSD W30L120 UE CN	80	165 lm/W	3,750 lm	96
911401560044	RC199X LED35/840 WIA W30L120 OC UE CN	80	160 lm/W	3,520 lm	96
911401560344	RC199X LED38/840 WIA W30L120 UE CN	80	170 lm/W	3,800 lm	96
911401560644	RC199V LED35/940 PSU W30L120 OC UE CN	90	170 lm/W	5,700 lm	144
911401560944	RC199V LED37/940 PSU W30L120 UE CN	90	162 lm/W	5,380 lm	144
911401561244	RC199V LED34/940 PSD W30L120 OC UE CN	90	145 lm/W	3,400 lm	96
911401561544	RC199V LED35/940 PSD W30L120 UE CN	90	156 lm/W	3,580 lm	96
911401561844	RC199X LED33/940 WIA W30L120 OC UE CN	90	150 lm/W	3,350 lm	96
911401562144	RC199X LED35/940 WIA W30L120 UE CN	90	160 lm/W	3,550 lm	96

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401546744	RC199V LED36/840 PSU W60L60 OC UE	23 W	911401560144	RC199X LED35/840 WIA W60L60 OC UE CN	22 W
911401547044	RC199V LED39/840 PSU W60L60 UE	23 W	911401560444	RC199X LED38/840 WIA W60L60 UE CN	22 W
911401547344	RC199V LED35/840 PSD W60L60 OC UE	23 W	911401560744	RC199V LED35/940 PSU W60L60 OC UE CN	33.5 W
911401547644	RC199V LED37/840 PSD W60L60 UE	23 W	911401561044	RC199V LED37/940 PSU W60L60 UE CN	33.5 W
911401547944	RC199X LED35/840 WIA W60L60 OC UE	22 W	911401561344	RC199V LED34/940 PSD W60L60 OC UE CN	23 W
911401548244	RC199X LED38/840 WIA W60L60 UE	22 W	911401561644	RC199V LED35/940 PSD W60L60 UE CN	23 W
911401548544	RC199V LED36/840 PSU W60L60 OC CAU UE	23 W	911401561944	RC199X LED33/940 WIA W60L60 OC UE CN	22 W
911401548844	RC199V LED39/840 PSU W60L60 CAU UE	23 W	911401562244	RC199X LED35/940 WIA W60L60 UE CN	22 W
911401549144	RC199V LED35/840 PSD W60L60 OC CAU UE	23 W	911401546544	RC199V LED54/840 PSU W60L120 OC UE	33 W
911401549444	RC199V LED38/840 PSD W60L60 CAU UE	23 W	911401546844	RC199V LED57/840 PSU W60L120 UE	33 W
911401549744	RC199X LED36/840 WIA W60L60 OC CAU UE	22 W	911401547144	RC199V LED54/840 PSD W60L120 OC UE	33.5 W
911401550044	RC199X LED38/840 WIA W60L60 CAU UE	22 W	911401547444	RC199V LED56/840 PSD W60L120 UE	33.5 W
911401550344	RC199V LED35/940 PSU W60L60 OC UE	23 W	911401547744	RC199X LED54/840 WIA W60L120 OC UE	33 W
911401550644	RC199V LED37/940 PSU W60L60 UE	23 W	911401548044	RC199X LED57/840 WIA W60L120 UE	33 W
911401550944	RC199V LED34/940 PSD W60L60 OC UE	23 W	911401548344	RC199V LED54/840 PSU W60L120 OC CAU UE	33 W
911401551244	RC199V LED35/940 PSD W60L60 UE	23 W	911401548644	RC199V LED58/840 PSU W60L120 CAU UE	23 W
911401551544	RC199X LED33/940 WIA W60L60 OC UE	22 W	911401548944	RC199V LED54/840 PSD W60L120 OC CAU UE	33 W
911401551844	RC199X LED35/940 WIA W60L60 UE	22 W	911401549244	RC199V LED56/840 PSD W60L120 CAU UE	33 W
911401552144	RC199V LED35/940 PSU W60L60 OC CAU UE	23 W	911401549544	RC199X LED54/840 WIA W60L120 OC CAU UE	33 W
911401552444	RC199V LED37/940 PSU W60L60 CAU UE	23 W	911401549844	RC199X LED57/840 WIA W60L120 CAU UE	33 W
911401552744	RC199V LED34/940 PSD W60L60 OC CAU UE	23 W	911401550144	RC199V LED51/940 PSU W60L120 OC UE	23 W
911401553044	RC199V LED36/940 PSD W60L60 CAU UE	23 W	911401550444	RC199V LED53/940 PSU W60L120 UE	23 W
911401553344	RC199X LED34/940 WIA W60L60 OC CAU UE	22 W	911401550744	RC199V LED50/940 PSD W60L120 OC UE	33.5 W
911401553644	RC199X LED35/940 WIA W60L60 CAU UE	22 W	911401551044	RC199V LED53/940 PSD W60L120 UE	33.5 W
911401558944	RC199V LED36/840 PSU W60L60 OC UE CN	33 W	911401551344	RC199X LED50/940 WIA W60L120 OC UE	33 W
911401559244	RC199V LED39/840 PSU W60L60 UE CN	33 W	911401551644	RC199X LED53/940 WIA W60L120 UE	33 W
911401559544	RC199V LED35/840 PSD W60L60 OC UE CN	23 W	911401551944	RC199V LED51/940 PSU W60L120 OC CAU UE	23 W
911401559844	RC199V LED37/840 PSD W60L60 UE CN	23 W	911401552244	RC199V LED54/940 PSU W60L120 CAU UE	23 W

GreenPerform ultra efficient panel RC199B

Order Code	Full Product Name	Power Consumption
911401552544	RC199V LED50/940 PSD W60L120 OC CAU UE	33 W
911401552844	RC199V LED53/940 PSD W60L120 CAU UE	33 W
911401553144	RC199X LED50/940 WIA W60L120 OC CAU UE	33 W
911401553444	RC199X LED53/940 WIA W60L120 CAU UE	33 W
911401558744	RC199V LED54/840 PSU W60L120 OC UE CN	23 W
911401559044	RC199V LED57/840 PSU W60L120 UE CN	23 W
911401559344	RC199V LED54/840 PSD W60L120 OC UE CN	33.5 W
911401559644	RC199V LED56/840 PSD W60L120 UE CN	33.5 W
911401559944	RC199X LED54/840 WIA W60L120 OC UE CN	33 W
911401560244	RC199X LED57/840 WIA W60L120 UE CN	33 W
911401560544	RC199V LED51/940 PSU W60L120 OC UE CN	33 W
911401560844	RC199V LED53/940 PSU W60L120 UE CN	23 W
911401561144	RC199V LED50/940 PSD W60L120 OC UE CN	33.5 W
911401561444	RC199V LED53/940 PSD W60L120 UE CN	33.5 W
911401561744	RC199X LED50/940 WIA W60L120 OC UE CN	33 W
911401562044	RC199X LED53/940 WIA W60L120 UE CN	33 W
911401546644	RC199V LED36/840 PSU W30L120 OC UE	23 W
911401546944	RC199V LED39/840 PSU W30L120 UE	23 W
911401547244	RC199V LED35/840 PSD W30L120 OC UE	23 W
911401547544	RC199V LED37/840 PSD W30L120 UE	23 W
911401547844	RC199X LED35/840 WIA W30L120 OC UE	22 W
911401548144	RC199X LED38/840 WIA W30L120 UE	22 W
911401548444	RC199V LED36/840 PSU W30L120 OC CAU UE	23 W
911401548744	RC199V LED39/840 PSU W30L120 CAU UE	23 W
911401549044	RC199V LED35/840 PSD W30L120 OC CAU UE	23 W
911401549344	RC199V LED38/840 PSD W30L120 CAU UE	23 W

Order Code	Full Product Name	Power Consumption
911401549644	RC199X LED36/840 WIA W30L120 OC CAU UE	22 W
911401549944	RC199X LED38/840 WIA W30L120 CAU UE	22 W
911401550244	RC199V LED35/940 PSU W30L120 OC UE	23 W
911401550544	RC199V LED37/940 PSU W30L120 UE	23 W
911401550844	RC199V LED34/940 PSD W30L120 OC UE	23 W
911401551144	RC199V LED35/940 PSD W30L120 UE	23 W
911401551444	RC199X LED33/940 WIA W30L120 OC UE	22 W
911401551744	RC199X LED35/940 WIA W30L120 UE	22 W
911401552044	RC199V LED35/940 PSU W30L120 OC CAU UE	23 W
911401552344	RC199V LED37/940 PSU W30L120 CAU UE	23 W
911401552644	RC199V LED34/940 PSD W30L120 OC CAU UE	23 W
911401552944	RC199V LED36/940 PSD W30L120 CAU UE	23 W
911401553244	RC199X LED34/940 WIA W30L120 OC CAU UE	22 W
911401553544	RC199X LED35/940 WIA W30L120 CAU UE	22 W
911401558844	RC199V LED36/840 PSU W30L120 OC UE CN	33.5 W
911401559144	RC199V LED39/840 PSU W30L120 UE CN	33.5 W
911401559444	RC199V LED35/840 PSD W30L120 OC UE CN	23 W
911401559744	RC199V LED37/840 PSD W30L120 UE CN	23 W
911401560044	RC199X LED35/840 WIA W30L120 OC UE CN	22 W
911401560344	RC199X LED38/840 WIA W30L120 UE CN	22 W
911401560644	RC199V LED35/940 PSU W30L120 OC UE CN	33 W
911401560944	RC199V LED37/940 PSU W30L120 UE CN	33 W
911401561244	RC199V LED34/940 PSD W30L120 OC UE CN	23 W
911401561544	RC199V LED35/940 PSD W30L120 UE CN	23 W
911401561844	RC199X LED33/940 WIA W30L120 OC UE CN	22 W
911401562144	RC199X LED35/940 WIA W30L120 UE CN	22 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401546744	RC199V LED36/840 PSU W60L60 OC UE	Fixed
911401547044	RC199V LED39/840 PSU W60L60 UE	Fixed
911401547344	RC199V LED35/840 PSD W60L60 OC UE	DALI
911401547644	RC199V LED37/840 PSD W60L60 UE	DALI
911401547944	RC199X LED35/840 WIA W60L60 OC UE	Wireless Dim
911401548244	RC199X LED38/840 WIA W60L60 UE	Wireless Dim
911401548544	RC199V LED36/840 PSU W60L60 OC CAU UE	Fixed
911401548844	RC199V LED39/840 PSU W60L60 CAU UE	Fixed
911401549144	RC199V LED35/840 PSD W60L60 OC CAU UE	DALI
911401549444	RC199V LED38/840 PSD W60L60 CAU UE	DALI
911401549744	RC199X LED36/840 WIA W60L60 OC CAU UE	Wireless Dim
911401550044	RC199X LED38/840 WIA W60L60 CAU UE	Wireless Dim
911401550344	RC199V LED35/940 PSU W60L60 OC UE	Fixed
911401550644	RC199V LED37/940 PSU W60L60 UE	Fixed
911401550944	RC199V LED34/940 PSD W60L60 OC UE	DALI
911401551244	RC199V LED35/940 PSD W60L60 UE	DALI
911401551544	RC199X LED33/940 WIA W60L60 OC UE	Wireless Dim
911401551844	RC199X LED35/940 WIA W60L60 UE	Wireless Dim
911401552144	RC199V LED35/940 PSU W60L60 OC CAU UE	Fixed
911401552444	RC199V LED37/940 PSU W60L60 CAU UE	Fixed
911401552744	RC199V LED34/940 PSD W60L60 OC CAU UE	DALI
911401553044	RC199V LED36/940 PSD W60L60 CAU UE	DALI

Order Code	Full Product Name	Dimmable
911401553344	RC199X LED34/940 WIA W60L60 OC CAU UE	Wireless Dim
911401553644	RC199X LED35/940 WIA W60L60 CAU UE	Wireless Dim
911401558944	RC199V LED36/840 PSU W60L60 OC UE CN	Fixed
911401559244	RC199V LED39/840 PSU W60L60 UE CN	Fixed
911401559544	RC199V LED35/840 PSD W60L60 OC UE CN	DALI
911401559844	RC199V LED37/840 PSD W60L60 UE CN	DALI
911401560144	RC199X LED35/840 WIA W60L60 OC UE CN	Wireless Dim
911401560444	RC199X LED38/840 WIA W60L60 UE CN	Wireless Dim
911401560744	RC199V LED35/940 PSU W60L60 OC UE CN	Fixed
911401561044	RC199V LED37/940 PSU W60L60 UE CN	Fixed
911401561344	RC199V LED34/940 PSD W60L60 OC UE CN	DALI
911401561644	RC199V LED35/940 PSD W60L60 UE CN	DALI
911401561944	RC199X LED33/940 WIA W60L60 OC UE CN	Wireless Dim
911401562244	RC199X LED35/940 WIA W60L60 UE CN	Wireless Dim
911401546544	RC199V LED54/840 PSU W60L120 OC UE	DALI
911401546844	RC199V LED57/840 PSU W60L120 UE	Fixed
911401547144	RC199V LED54/840 PSD W60L120 OC UE	DALI
911401547444	RC199V LED56/840 PSD W60L120 UE	DALI
911401547744	RC199X LED54/840 WIA W60L120 OC UE	Wireless Dim
911401548044	RC199X LED57/840 WIA W60L120 UE	Wireless Dim
911401548344	RC199V LED54/840 PSU W60L120 OC CAU UE	Fixed
911401548644	RC199V LED58/840 PSU W60L120 CAU UE	Fixed

GreenPerform ultra efficient panel RC199B

Order Code	Full Product Name	Dimmable
911401548944	RC199V LED54/840 PSD W60L120 OC CAU UE	DALI
911401549244	RC199V LED56/840 PSD W60L120 CAU UE	DALI
911401549544	RC199X LED54/840 WIA W60L120 OC CAU UE	Wireless Dim
911401549844	RC199X LED57/840 WIA W60L120 CAU UE	Wireless Dim
911401550144	RC199V LED51/940 PSU W60L120 OC UE	Fixed
911401550444	RC199V LED53/940 PSU W60L120 UE	Fixed
911401550744	RC199V LED50/940 PSD W60L120 OC UE	DALI
911401551044	RC199V LED53/940 PSD W60L120 UE	DALI
911401551344	RC199X LED50/940 WIA W60L120 OC UE	Wireless Dim
911401551644	RC199X LED53/940 WIA W60L120 UE	Wireless Dim
911401551944	RC199V LED51/940 PSU W60L120 OC CAU UE	Fixed
911401552244	RC199V LED54/940 PSU W60L120 CAU UE	Fixed
911401552544	RC199V LED50/940 PSD W60L120 OC CAU UE	DALI
911401552844	RC199V LED53/940 PSD W60L120 CAU UE	DALI
911401553144	RC199X LED50/940 WIA W60L120 OC CAU UE	Wireless Dim
911401553444	RC199X LED53/940 WIA W60L120 CAU UE	Wireless Dim
911401558744	RC199V LED54/840 PSU W60L120 OC UE CN	Fixed
911401559044	RC199V LED57/840 PSU W60L120 UE CN	Fixed
911401559344	RC199V LED54/840 PSD W60L120 OC UE CN	DALI
911401559644	RC199V LED56/840 PSD W60L120 UE CN	DALI
911401559944	RC199X LED54/840 WIA W60L120 OC UE CN	Wireless Dim
911401560244	RC199X LED57/840 WIA W60L120 UE CN	Wireless Dim
911401560544	RC199V LED51/940 PSU W60L120 OC UE CN	Fixed
911401560844	RC199V LED53/940 PSU W60L120 UE CN	Fixed
911401561144	RC199V LED50/940 PSD W60L120 OC UE CN	DALI
911401561444	RC199V LED53/940 PSD W60L120 UE CN	DALI
911401561744	RC199X LED50/940 WIA W60L120 OC UE CN	Wireless Dim
911401562044	RC199X LED53/940 WIA W60L120 UE CN	Wireless Dim
911401546644	RC199V LED36/840 PSU W30L120 OC UE	Fixed
911401546944	RC199V LED39/840 PSU W30L120 UE	Fixed
911401547244	RC199V LED35/840 PSD W30L120 OC UE	DALI
911401547544	RC199V LED37/840 PSD W30L120 UE	DALI

Order Code	Full Product Name	Dimmable
911401547844	RC199X LED35/840 WIA W30L120 OC UE	Wireless Dim
911401548144	RC199X LED38/840 WIA W30L120 UE	Wireless Dim
911401548444	RC199V LED36/840 PSU W30L120 OC CAU UE	Fixed
911401548744	RC199V LED39/840 PSU W30L120 CAU UE	Fixed
911401549044	RC199V LED35/840 PSD W30L120 OC CAU UE	DALI
911401549344	RC199V LED38/840 PSD W30L120 CAU UE	DALI
911401549644	RC199X LED36/840 WIA W30L120 OC CAU UE	Wireless Dim
911401549944	RC199X LED38/840 WIA W30L120 CAU UE	Wireless Dim
911401550244	RC199V LED35/940 PSU W30L120 OC UE	Fixed
911401550544	RC199V LED37/940 PSU W30L120 UE	Fixed
911401550844	RC199V LED34/940 PSD W30L120 OC UE	DALI
911401551144	RC199V LED35/940 PSD W30L120 UE	DALI
911401551444	RC199X LED33/940 WIA W30L120 OC UE	Wireless Dim
911401551744	RC199X LED35/940 WIA W30L120 UE	Wireless Dim
911401552044	RC199V LED35/940 PSU W30L120 OC CAU UE	Fixed
911401552344	RC199V LED37/940 PSU W30L120 CAU UE	Fixed
911401552644	RC199V LED34/940 PSD W30L120 OC CAU UE	DALI
911401552944	RC199V LED36/940 PSD W30L120 CAU UE	DALI
911401553244	RC199X LED34/940 WIA W30L120 OC CAU UE	Wireless Dim
911401553544	RC199X LED35/940 WIA W30L120 CAU UE	Wireless Dim
911401558844	RC199V LED36/840 PSU W30L120 OC UE CN	Fixed
911401559144	RC199V LED39/840 PSU W30L120 UE CN	Fixed
911401559444	RC199V LED35/840 PSD W30L120 OC UE CN	DALI
911401559744	RC199V LED37/840 PSD W30L120 UE CN	DALI
911401560044	RC199X LED35/840 WIA W30L120 OC UE CN	Wireless Dim
911401560344	RC199X LED38/840 WIA W30L120 UE CN	Wireless Dim
911401560644	RC199V LED35/940 PSU W30L120 OC UE CN	Fixed
911401560944	RC199V LED37/940 PSU W30L120 UE CN	Fixed
911401561244	RC199V LED34/940 PSD W30L120 OC UE CN	DALI
911401561544	RC199V LED35/940 PSD W30L120 UE CN	DALI
911401561844	RC199X LED33/940 WIA W30L120 OC UE CN	Wireless Dim
911401562144	RC199X LED35/940 WIA W30L120 UE CN	Wireless Dim

