



# Ultra efficient and peace of mind

## GreenPerform ultra efficient panel RC199B

GreenPerform ultra efficient panel is a direct lit panel with up to 170lm/w system efficacy (PSU driver) in the market. It offers 3 typical dimensions: 600x600; 300x1200 and 600x1200mm to fit most of indoor applications. Interact system option and Dali interface are available for wide option for system connection. Its lower UGR offers better visual comfort as well.

### Benefits

- Ultra efficient lm/w provides better energy saving
- Interact and Dali interfaces available for easy system connection
- Lower UGR offer for better visual comfort
- Multiple mountings to cater for various applications

### Features

- System efficacy up to 170lm/W (PSU driver / CRI80 / UGR22 version only)
- CRI 80 and 90 available
- Lifetime: 50k hours (L80@25deg)
- UGR19 available for certain types
- IP40 front side/IP20 back side available

### Application

- Open plan office
- Public indoor area
- Meeting/Training room

### Specifications

Ceiling type	T-bar ceiling	Dimming	PSD Dali dimmable
--------------	---------------	---------	-------------------



# GreenPerform ultra efficient panel RC199B

## Versions



GreenPerform UE panel

## Dimensional drawing



GreenPerform ultra efficient panel RC199B

General Information	
Driver included	Yes
Gear	-
Number of gear units	1 unit
Light Technical	
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	90
Optic type	Beam angle 100°
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	200 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable
Controls and Dimming	
Maximum dim level	0% (digital)
Mechanical and Housing	
Optical cover type	PS
Housing Color	White RAL 9003
Mech. impact protection code	IK02
Ingress protection code	IP20/40
Approval and Application	
Ambient temperature range	-20 to +45 °C
CE mark	Yes
ENEC mark	-
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Luminous Efficacy	Luminous Flux	Number of
		(rated) (Nom)		light sources
911401552144	RC199V LED35/940 PSU W60L60 OC CAU UE	170 lm/W	3,900 lm	96
911401552744	RC199V LED34/940 PSD W60L60 OC CAU UE	145 lm/W	3,400 lm	96
911401553344	RC199X LED34/940 WIA W60L60 OC CAU UE	150 lm/W	3,400 lm	96
911401551944	RC199V LED51/940 PSU W60L120 OC CAU UE	160 lm/W	3,650 lm	96
911401552544	RC199V LED50/940 PSD W60L120 OC CAU UE	145 lm/W	5,000 lm	144
911401553144	RC199X LED50/940 WIA W60L120 OC CAU UE	152 lm/W	5,080 lm	144
911401550244	RC199V LED35/940 PSU W30L120 OC UE	160 lm/W	3,650 lm	96
911401552044	RC199V LED35/940 PSU W30L120 OC CAU UE	160 lm/W	3,650 lm	96
911401552644	RC199V LED34/940 PSD W30L120 OC CAU UE	145 lm/W	3,400 lm	96
911401553244	RC199X LED34/940 WIA W30L120 OC CAU UE	150 lm/W	3,400 lm	96

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401552144	RC199V LED35/940 PSU W60L60 OC CAU UE	23 W
911401552744	RC199V LED34/940 PSD W60L60 OC CAU UE	23 W
911401553344	RC199X LED34/940 WIA W60L60 OC CAU UE	22 W
911401551944	RC199V LED51/940 PSU W60L120 OC CAU UE	23 W
911401552544	RC199V LED50/940 PSD W60L120 OC CAU UE	33 W

Order Code	Full Product Name	Power Consumption
911401553144	RC199X LED50/940 WIA W60L120 OC CAU UE	33 W
911401550244	RC199V LED35/940 PSU W30L120 OC UE	23 W
911401552044	RC199V LED35/940 PSU W30L120 OC CAU UE	23 W
911401552644	RC199V LED34/940 PSD W30L120 OC CAU UE	23 W
911401553244	RC199X LED34/940 WIA W30L120 OC CAU UE	22 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401552144	RC199V LED35/940 PSU W60L60 OC CAU UE	Fixed
911401552744	RC199V LED34/940 PSD W60L60 OC CAU UE	DALI
911401553344	RC199X LED34/940 WIA W60L60 OC CAU UE	Wireless Dim
911401551944	RC199V LED51/940 PSU W60L120 OC CAU UE	Fixed
911401552544	RC199V LED50/940 PSD W60L120 OC CAU UE	DALI

Order Code	Full Product Name	Dimmable
911401553144	RC199X LED50/940 WIA W60L120 OC CAU UE	Wireless Dim
911401550244	RC199V LED35/940 PSU W30L120 OC UE	Fixed
911401552044	RC199V LED35/940 PSU W30L120 OC CAU UE	Fixed
911401552644	RC199V LED34/940 PSD W30L120 OC CAU UE	DALI

GreenPerform ultra efficient panel RC199B

Order Code	Full Product Name	Dimmable
911401553244	RC199X LED34/940 WIA W30L120 OC CAU UE	Wireless Dim

