

FlexBlend – Unlocking the potential of LED lighting in offices

FlexBlend Recessed

Office owners and staff responsible for lighting operations are searching for high quality yet energy-efficient lighting that complies with norms and regulations. Designed to support these needs, Philips FlexBlend is enabling building owners to fully optimize their lighting operations, by offering office-compliant lighting with an attractive return on investment. Furthermore, FlexBlend provides the required flexibility by being easy applied on different ceiling types as well as in different office spaces like open office or meeting rooms. Though technology is changing fast, the ideal lighting solution is also expected to be ready to incorporate innovations and future advances that can help optimize operations further. For this reason, Philips FlexBlend is also ready to be connected to controls such as Actilume or used together with the Philips SpaceWise lighting system. It can also be connected to software-based lighting systems like Interact Office, which provides the luminaire with further intelligence and enables it to collect valuable data about its environment

Benefits

- High-quality office-compliant lighting
- Choice of three different exit-windows
- Fast return on investment
- Application flexibility
- Scalable and ready to be connected to controls and lighting systems

FlexBlend Recessed

Features

- Fully office-compliant (UGR <19)
- Homogenous and uniform light effect
- Dimensional variety, local options
- Various mounting options
- Integrated sensors
- Can be combined with Philips ActiLume and SpaceWise systems
- Ready to be connected to software based lighting systems such as Interact Office

Application

- Offices
- Education
- Healthcare
- Banks

Versions



FlexBlend Recessed RC340B
W60L60 MLO CPC




0 FlexBlend Recessed-RC340B
W30L120 MLO VPC


Upgradable sensor



Dimensional drawing




Dimensional drawing



FlexBlend Recessed

Dimensional drawing




Product details



Upgradable sensor



FlexBlend Recessed-
RC340B_MLO_ DPP



FlexBlend Recessed-
RC340B_W60L60_CPC brackets



O_FlexBlend Recessed-
RC342B_W62L62_MLO_VPC




FlexBlend Recessed-
RC340B_W60L60_Backcover_VP
C



FlexBlend Recessed-
RC340B_W60L60_CPC
brackets_B

FlexBlend Recessed

Product details



FlexBlend Recessed-
RC340B_OPA_DPP



FlexBlend Recessed-
RC340B_PCS_DPP




O_FlexBlend Recessed-
RC340B_W60L60_PCS_VPC



FlexBlend Recessed-
RC340B_W60L60_CPC
brackets_A



FlexBlend Recessed RC340B PIP
Open



FlexBlend Recessed-
RC340B_W60L60_backcover_PC
V



O_FlexBlend Recessed-
RC340B_W60L60_MLO_VPC



O_FlexBlend Recessed-
RC340B_W60L60_MLO_CPC

FlexBlend Recessed

Product details



FlexBlend Recessed-RC340B PIP
Closed



FlexBlend_RC340B_W30L120_U4
_DPP



FlexBlend Recessed-
RC340B_W60L60_backcover_CP
C

FlexBlend Recessed

General Information	
Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Color rendering index (CRI)	≥90
Optic type	Wide beam
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Controls and Dimming	
Maximum dim level	1%
Mechanical and Housing	
Housing Color	White
Mech. impact protection code	IK02
Approval and Application	
Ambient temperature range	+10 to +40 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.38, 0.37) SDCM ≤3
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925867015	RC340B 36S/940 PSU W15L120 VPC MLO	4000 K	96 lm/W	3,600 lm
910925867016	RC340B 36S/940 PSD W15L120 VPC MLO	4000 K	97.5 lm/W	3,600 lm
910925867017	RC340B 42S/940 PSU W15L120 VPC MLO	4000 K	95.5 lm/W	4,200 lm
910925867018	RC340B 42S/940 PSD W15L120 VPC MLO	4000 K	94.5 lm/W	4,200 lm
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	4000 K	88 lm/W	3,600 lm
910925867020	RC340B 36S/940 PSD W15L120 VPC MLO ELP3	4000 K	86.5 lm/W	3,600 lm
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	4000 K	87.5 lm/W	4,200 lm
910925867022	RC340B 42S/940 PSD W15L120 VPC MLO ELP3	4000 K	85.5 lm/W	4,200 lm
910925867024	RC340B 36S/940 PSD W15L120 VPC MLO ELD3	4000 K	96 lm/W	3,600 lm
910925867026	RC340B 42S/940 PSD W15L120 VPC MLO EL	4000 K	94.5 lm/W	4,200 lm
910925867149	RC342B 28S/940 PSD W15L125 VPC MLO	4000 K	100 lm/W	2,800 lm
910925867150	RC342B 36S/940 PSD W15L125 VPC MLO	4000 K	97.5 lm/W	3,600 lm
910925867153	RC342B 36S/940 PSD W17L125 PCV MLO	4000 K	97.5 lm/W	3,600 lm
910925867164	RC342B 28S/940 PSD W15L125 VPC PCS	4000 K	140 lm/W	2,800 lm
910925867165	RC342B 36S/940 PSD W15L125 VPC PCS	4000 K	138 lm/W	3,600 lm
910925867166	RC342B 42S/940 PSD W15L125 VPC PCS	4000 K	140 lm/W	4,200 lm
910925867169	RC342B 36S/940 PSD W17L125 PCV PCS	4000 K	144 lm/W	3,600 lm
910925867180	RC342B 28S/940 PSD W15L125 VPC O	4000 K	124 lm/W	2,800 lm
910925867181	RC342B 36S/940 PSD W15L125 VPC O	4000 K	124 lm/W	3,600 lm
910925867182	RC342B 42S/940 PSD W15L125 VPC O	4000 K	125 lm/W	4,200 lm
910925866979	RC340B 36S/940 PSD W30L120 VPC MLO	4000 K	97.5 lm/W	3,600 lm
910925866982	RC342B 36S/940 PSU W31L125 VPC MLO	4000 K	97.5 lm/W	3,600 lm
910925866983	RC342B 36S/940 PSD W31L125 VPC MLO	4000 K	97.5 lm/W	3,600 lm
910925867030	RC340B 42S/940 PSD W30L120 VPC MLO W3W2	4000 K	94.5 lm/W	4,200 lm
910925867031	RC340B 42S/940 PSD W30L120 CPC MLO W3W2	4000 K	94.5 lm/W	4,200 lm

FlexBlend Recessed

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
910925867032	RC340B 42S/930 PSD W30L120 VPC MLO W3W2	3000 K	88.5 lm/W	4,200 lm
910925867033	RC340B 42S/930 PSD W30L120 CPC MLO W3W2	3000 K	88.5 lm/W	4,200 lm
910925867038	RC340B 42S/940 PSD W30L120 VPC PCS W3W2	4000 K	140 lm/W	4,200 lm
910925867039	RC340B 42S/940 PSD W30L120 CPC PCS W3W2	4000 K	140 lm/W	4,200 lm
910925867042	RC340B 42S/930 PSD W30L120 VPC PCS W3W2	3000 K	136 lm/W	4,200 lm
910925867147	RC342B 28S/940 PSD W31L125 VPC MLO	4000 K	100 lm/W	2,800 lm
910925867161	RC342B 28S/940 PSD W31L125 VPC PCS	4000 K	140 lm/W	2,800 lm
910925867162	RC342B 36S/940 PSD W31L125 VPC PCS	4000 K	138 lm/W	3,600 lm
910925867163	RC342B 42S/940 PSD W31L125 VPC PCS	4000 K	140 lm/W	4,200 lm
910925867177	RC342B 28S/940 PSD W31L125 VPC O	4000 K	124 lm/W	2,800 lm
910925867178	RC342B 36S/940 PSD W31L125 VPC O	4000 K	124 lm/W	3,600 lm
910925867179	RC342B 42S/940 PSD W31L125 VPC O	4000 K	125 lm/W	4,200 lm
910925868910	RC340B 36S/930 SRD W60L60 VPC MLO U4	3000 K	93.5 lm/W	3,600 lm
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	3000 K	93.5 lm/W	3,600 lm
910925868912	RC340B 36S/930 SRD W60L60 VPC PCS U4	3000 K	136 lm/W	3,600 lm
910925868913	RC340B 36S/930 SRD W60L60 VPC PCS U4	3000 K	136 lm/W	3,600 lm
910925868914	RC340B 36S/940 SRD W60L60 VPC MLO U4	4000 K	97.5 lm/W	3,600 lm
910925868915	RC340B 36S/940 SRD W60L60 VPC MLO U4	4000 K	97.5 lm/W	3,600 lm
910925868916	RC340B 36S/940 SRD W60L60 VPC PCS U4	4000 K	141 lm/W	3,600 lm
910925868917	RC340B 36S/940 SRD W60L60 VPC PCS U4	4000 K	141 lm/W	3,600 lm
910925868918	RC340B 36S/940 SRD W60L60 VPC PCS U4 W3	4000 K	141 lm/W	3,600 lm
910925868920	RC340B 42S/940 SRD W60L60 VPC PCS U4 W3	4000 K	140 lm/W	4,200 lm
910925868921	RC342B 28S/940 SRD W62L62 VPC MLO U4	4000 K	100 lm/W	2,800 lm
910925868922	RC342B 28S/940 SRD W62L62 VPC PCS U4	4000 K	140 lm/W	2,800 lm
910925868924	RC342B 36S/940 SRD W62L62 VPC MLO U4	4000 K	97.5 lm/W	3,600 lm

FlexBlend Recessed

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
910925868925	RC342B 36S/940 SRD W62L62 VPC PCS U4	4000 K	141 lm/W	3,600 lm
910925868927	RC342B 42S/940 SRD W62L62 VPC MLO U4	4000 K	94.5 lm/W	4,200 lm
910925868928	RC342B 42S/940 SRD W62L62 VPC PCS U4	4000 K	140 lm/W	4,200 lm
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	4000 K	111 lm/W	3,600 lm
910925866987	RC340B 36S/940 PSD W60L60 VPC O ELP3	4000 K	109 lm/W	3,600 lm
910925867001	RC340B 42S/940 PSU W60L60 VPC O	4000 K	127 lm/W	4,200 lm
910925867002	RC340B 42S/940 PSD W60L60 VPC O	4000 K	125 lm/W	4,200 lm
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	4000 K	114 lm/W	4,200 lm
910925867007	RC340B 42S/940 PSD W60L60 VPC O ELP3	4000 K	112 lm/W	4,200 lm
910925867012	RC340B 42S/940 PSD W60L60 VPC O ELD3	4000 K	125 lm/W	4,200 lm
910925867061	RC340B 36S/940 PSU W60L60 VPC O SC	4000 K	120 lm/W	3,600 lm
910925867062	RC340B 36S/940 PSD W60L60 VPC O SC	4000 K	124 lm/W	3,600 lm
910925868919	RC340B 42S/940 SRD W30L120 VPC PCS U4 W3	4000 K	140 lm/W	4,200 lm
910925868923	RC342B 36S/940 SRD W31L125 VPC PCS U4	4000 K	141 lm/W	3,600 lm
910925868926	RC342B 42S/940 SRD W31L125 VPC PCS U4	4000 K	140 lm/W	4,200 lm
910925866969	RC340B 36S/940 PSD W60L60 VPC MLO	4000 K	97.5 lm/W	3,600 lm
910925867023	RC340B 42S/930 PSD W60L60 CPC MLO W3W2	3000 K	88.5 lm/W	4,200 lm
910925867028	RC340B 42S/940 PSD W60L60 CPC MLO W3W2	4000 K	94.5 lm/W	4,200 lm
910925867036	RC340B 42S/940 PSD W60L60 CPC PCS W3W2	4000 K	140 lm/W	4,200 lm
910925867040	RC340B 42S/930 PSD W60L60 CPC PCS W3W2	3000 K	136 lm/W	4,200 lm
910925867046	RC340B 36S/940 PSU W60L60 CPC MLO	4000 K	96 lm/W	3,600 lm
910925867047	RC340B 42S/940 PSU W60L60 CPC MLO	4000 K	95.5 lm/W	4,200 lm
910925867048	RC340B 42S/940 PSD W60L60 CPC MLO	4000 K	94.5 lm/W	4,200 lm
910925867167	RC342B 42S/940 PSD W62L62 CPC PCS	4000 K	140 lm/W	4,200 lm
910925867068	RC340B 42S/930 PSD W30L120 CPC PCS W3W2	3000 K	136 lm/W	4,200 lm

FlexBlend Recessed

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
910925866967	RC340B 36S/940 PSD W60L60 VPC O	4000 K	124 lm/W	3,600 lm
910925866972	RC340B 36S/940 PSU W60L60 VPC PCS	4000 K	144 lm/W	3,600 lm
910925866973	RC340B 36S/940 PSD W60L60 VPC PCS	4000 K	144 lm/W	3,600 lm
910925866977	RC340B 36S/940 PSD W60L60 CPC MLO	4000 K	97.5 lm/W	3,600 lm
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	4000 K	124 lm/W	3,600 lm
910925866991	RC340B 36S/940 PSD W60L60 VPC PCS ELP	4000 K	122 lm/W	3,600 lm
910925866997	RC340B 36S/940 PSD W60L60 VPC PCS ELD3	4000 K	141 lm/W	3,600 lm
910925867003	RC340B 42S/940 PSU W60L60 VPC PCS	4000 K	140 lm/W	4,200 lm
910925867004	RC340B 42S/940 PSD W60L60 VPC PCS	4000 K	140 lm/W	4,200 lm
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	4000 K	125 lm/W	4,200 lm
910925867009	RC340B 42S/940 PSD W60L60 VPC PCS ELP3	4000 K	124 lm/W	4,200 lm
910925867034	RC340B 42S/930 PSD W60L60 VPC PCS W3W2	3000 K	136 lm/W	4,200 lm
910925867035	RC340B 42S/940 PSD W60L60 VPC PCS W3W2	4000 K	140 lm/W	4,200 lm
910925867044	RC340B 36S/940 PSU W60L60 CPC PCS	4000 K	144 lm/W	3,600 lm
910925867045	RC340B 36S/940 PSD W60L60 CPC PCS	4000 K	144 lm/W	3,600 lm
910925867049	RC340B 42S/940 PSU W60L60 CPC PCS	4000 K	140 lm/W	4,200 lm
910925867050	RC340B 42S/940 PSD W60L60 CPC PCS	4000 K	140 lm/W	4,200 lm
910925867065	RC340B 36S/940 PSU W60L60 VPC PCS	4000 K	144 lm/W	3,600 lm
910925867066	RC340B 36S/940 PSD W60L60 VPC PCS	4000 K	144 lm/W	3,600 lm
910925866966	RC340B 36S/940 PSU W60L60 VPC O	4000 K	120 lm/W	3,600 lm
910925866980	RC342B 36S/940 PSU W62L62 VPC MLO	4000 K	97.5 lm/W	3,600 lm
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	4000 K	88 lm/W	3,600 lm
910925866989	RC340B 36S/940 PSD W60L60 VPC MLO ELP3	4000 K	86.5 lm/W	3,600 lm
910925866993	RC340B 36S/940 PSD W60L60 VPC O ELD3	4000 K	124 lm/W	3,600 lm
910925866995	RC340B 36S/940 PSD W60L60 VPC MLO ELD3	4000 K	96 lm/W	3,600 lm

FlexBlend Recessed

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
910925866999	RC340B 42S/940 PSD W60L60 VPC MLO	4000 K	94.5 lm/W	4,200 lm
910925867010	RC340B 42S/940 PSD W60L60 VPC MLO ELD3	4000 K	94.5 lm/W	4,200 lm
910925867013	RC340B 42S/930 PSD W60L60 VPC MLO W3W2	3000 K	88.5 lm/W	4,200 lm
910925867027	RC340B 42S/940 PSD W60L60 VPC MLO W3W2	4000 K	94.5 lm/W	4,200 lm
910925867043	RC340B 42S/940 PSU W60L60 VPC MLO	4000 K	95.5 lm/W	4,200 lm
910925867063	RC340B 36S/940 PSU W60L60 VPC MLO	4000 K	96 lm/W	3,600 lm
910925867064	RC340B 36S/940 PSD W60L60 VPC MLO	4000 K	97.5 lm/W	3,600 lm
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	4000 K	97.5 lm/W	3,600 lm
910925867014	RC340B 42S/940 PSD W60L60 VPC PCS ELD3	4000 K	142 lm/W	4,200 lm
910925867025	RC340B 42S/930 PSD W60L60 PCV MLO W3W2	3000 K	88.5 lm/W	4,200 lm
910925867029	RC340B 42S/940 PSD W60L60 PCV MLO W3W2	4000 K	94.5 lm/W	4,200 lm
910925867037	RC340B 42S/940 PSD W60L60 PCV PCS W3W2	4000 K	140 lm/W	4,200 lm
910925867041	RC340B 42S/930 PSD W60L60 PCV PCS W3W2	3000 K	136 lm/W	4,200 lm
910925867168	RC340B 36S/940 PSD W60L60 PCV PCS	4000 K	144 lm/W	3,600 lm
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	4000 K	97.5 lm/W	3,600 lm
910925867224	RC340B 36S/940 POE W60L60 VPC PCS U0	4000 K	144 lm/W	3,600 lm
910925866968	RC340B 36S/940 PSU W60L60 VPC MLO	4000 K	96 lm/W	3,600 lm
910925866978	RC340B 36S/940 PSD W60L60 PCV MLO	4000 K	97.5 lm/W	3,600 lm
910925866981	RC342B 36S/940 PSD W62L62 VPC MLO	4000 K	97.5 lm/W	3,600 lm
910925867145	RC342B 28S/940 PSD W62L62 VPC MLO	4000 K	100 lm/W	2,800 lm
910925867158	RC342B 28S/940 PSD W62L62 VPC PCS	4000 K	140 lm/W	2,800 lm
910925867159	RC342B 36S/940 PSD W62L62 VPC PCS	4000 K	144 lm/W	3,600 lm
910925867160	RC342B 42S/940 PSD W62L62 VPC PCS	4000 K	140 lm/W	4,200 lm
910925867174	RC342B 28S/940 PSD W62L62 VPC O	4000 K	124 lm/W	2,800 lm
910925867175	RC342B 36S/940 PSD W62L62 VPC O	4000 K	124 lm/W	3,600 lm

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
910925867176	RC342B 42S/940 PSD W62L62 VPC O	4000 K	125 lm/W	4,200 lm

Operating and Electrical

Order Code	Full Product Name	Protection class IEC	Power Consumption	Suitable for random switching
910925867015	RC340B 36S/940 PSU W15L120 VPC MLO	Safety class I	37.5 W	Yes
910925867016	RC340B 36S/940 PSD W15L120 VPC MLO	Safety class I	37 W	Yes
910925867017	RC340B 42S/940 PSU W15L120 VPC MLO	Safety class I	44 W	Yes
910925867018	RC340B 42S/940 PSD W15L120 VPC MLO	Safety class I	44.5 W	Yes
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	Safety class I	41 W	Yes
910925867020	RC340B 36S/940 PSD W15L120 VPC MLO ELP3	Safety class I	41.5 W	Yes
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	Safety class I	48 W	Yes
910925867022	RC340B 42S/940 PSD W15L120 VPC MLO ELP3	Safety class I	49 W	Yes
910925867024	RC340B 36S/940 PSD W15L120 VPC MLO ELD3	Safety class I	37.5 W	Yes
910925867026	RC340B 42S/940 PSD W15L120 VPC MLO EL	Safety class I	44.5 W	Yes
910925867149	RC342B 28S/940 PSD W15L125 VPC MLO	Safety class I	28 W	Yes
910925867150	RC342B 36S/940 PSD W15L125 VPC MLO	Safety class I	37 W	Yes
910925867153	RC342B 36S/940 PSD W17L125 PCV MLO	Safety class I	37 W	Yes
910925867164	RC342B 28S/940 PSD W15L125 VPC PCS	Safety class I	20 W	Yes
910925867165	RC342B 36S/940 PSD W15L125 VPC PCS	Safety class I	26 W	Yes
910925867166	RC342B 42S/940 PSD W15L125 VPC PCS	Safety class I	30 W	Yes
910925867169	RC342B 36S/940 PSD W17L125 PCV PCS	Safety class I	25 W	Yes
910925867180	RC342B 28S/940 PSD W15L125 VPC O	Safety class I	22.5 W	Yes
910925867181	RC342B 36S/940 PSD W15L125 VPC O	Safety class I	29 W	Yes
910925867182	RC342B 42S/940 PSD W15L125 VPC O	Safety class I	33.5 W	Yes
910925866979	RC340B 36S/940 PSD W30L120 VPC MLO	Safety class I	37 W	Yes
910925866982	RC342B 36S/940 PSU W31L125 VPC MLO	Safety class I	37 W	Yes
910925866983	RC342B 36S/940 PSD W31L125 VPC MLO	Safety class I	37 W	Yes
910925867030	RC340B 42S/940 PSD W30L120 VPC MLO W3W2	Safety class I	44.5 W	Yes
910925867031	RC340B 42S/940 PSD W30L120 CPC MLO W3W2	Safety class I	44.5 W	Yes
910925867032	RC340B 42S/930 PSD W30L120 VPC MLO W3W2	Safety class I	47.5 W	Yes
910925867033	RC340B 42S/930 PSD W30L120 CPC MLO W3W2	Safety class I	47.5 W	Yes
910925867038	RC340B 42S/940 PSD W30L120 VPC PCS W3W2	Safety class I	30 W	Yes
910925867039	RC340B 42S/940 PSD W30L120 CPC PCS W3W2	Safety class I	30 W	Yes
910925867042	RC340B 42S/930 PSD W30L120 VPC PCS W3W2	Safety class I	31 W	Yes
910925867147	RC342B 28S/940 PSD W31L125 VPC MLO	Safety class I	28 W	Yes
910925867161	RC342B 28S/940 PSD W31L125 VPC PCS	Safety class I	20 W	Yes
910925867162	RC342B 36S/940 PSD W31L125 VPC PCS	Safety class I	26 W	Yes
910925867163	RC342B 42S/940 PSD W31L125 VPC PCS	Safety class I	30 W	Yes
910925867177	RC342B 28S/940 PSD W31L125 VPC O	Safety class I	22.5 W	Yes
910925867178	RC342B 36S/940 PSD W31L125 VPC O	Safety class I	29 W	Yes
910925867179	RC342B 42S/940 PSD W31L125 VPC O	Safety class I	33.5 W	Yes

FlexBlend Recessed

Order Code	Full Product Name	Protection class IEC	Power Consumption	Suitable for random switching
910925868910	RC340B 36S/930 SRD W60L60 VPC MLO U4	Safety class I	38.5 W	No
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	Safety class I	38.5 W	No
910925868912	RC340B 36S/930 SRD W60L60 VPC PCS U4	Safety class I	26.5 W	No
910925868913	RC340B 36S/930 SRD W60L60 VPC PCS U4	Safety class I	26.5 W	No
910925868914	RC340B 36S/940 SRD W60L60 VPC MLO U4	Safety class I	37 W	No
910925868915	RC340B 36S/940 SRD W60L60 VPC MLO U4	Safety class I	37 W	No
910925868916	RC340B 36S/940 SRD W60L60 VPC PCS U4	Safety class I	25.5 W	No
910925868917	RC340B 36S/940 SRD W60L60 VPC PCS U4	Safety class I	25.5 W	No
910925868918	RC340B 36S/940 SRD W60L60 VPC PCS U4 W3	Safety class I	25.5 W	No
910925868920	RC340B 42S/940 SRD W60L60 VPC PCS U4 W3	Safety class I	30 W	No
910925868921	RC342B 28S/940 SRD W62L62 VPC MLO U4	Safety class I	28 W	No
910925868922	RC342B 28S/940 SRD W62L62 VPC PCS U4	Safety class I	20 W	No
910925868924	RC342B 36S/940 SRD W62L62 VPC MLO U4	Safety class I	37 W	No
910925868925	RC342B 36S/940 SRD W62L62 VPC PCS U4	Safety class I	25 W	No
910925868927	RC342B 42S/940 SRD W62L62 VPC MLO U4	Safety class I	44.5 W	No
910925868928	RC342B 42S/940 SRD W62L62 VPC PCS U4	Safety class I	30 W	No
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	Safety class I	32.5 W	Yes
910925866987	RC340B 36S/940 PSD W60L60 VPC O ELP3	Safety class I	33 W	Yes
910925867001	RC340B 42S/940 PSU W60L60 VPC O	Safety class I	33 W	Yes
910925867002	RC340B 42S/940 PSD W60L60 VPC O	Safety class I	33.5 W	Yes
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	Safety class I	37 W	Yes
910925867007	RC340B 42S/940 PSD W60L60 VPC O ELP3	Safety class I	37.5 W	Yes
910925867012	RC340B 42S/940 PSD W60L60 VPC O ELD3	Safety class I	33.5 W	Yes
910925867061	RC340B 36S/940 PSU W60L60 VPC O SC	Safety class I	30 W	Yes

Order Code	Full Product Name	Protection class IEC	Power Consumption	Suitable for random switching
910925867062	RC340B 36S/940 PSD W60L60 VPC O SC	Safety class I	29 W	Yes
910925868919	RC340B 42S/940 SRD W30L120 VPC PCS U4 W3	Safety class I	30 W	No
910925868923	RC342B 36S/940 SRD W31L125 VPC PCS U4	Safety class I	24 W	No
910925868926	RC342B 42S/940 SRD W31L125 VPC PCS U4	Safety class I	30 W	No
910925866969	RC340B 36S/940 PSD W60L60 VPC MLO	Safety class I	37 W	Yes
910925867023	RC340B 42S/930 PSD W60L60 CPC MLO W3W2	Safety class I	47.5 W	Yes
910925867028	RC340B 42S/940 PSD W60L60 CPC MLO W3W2	Safety class I	44.5 W	Yes
910925867036	RC340B 42S/940 PSD W60L60 CPC PCS W3W2	Safety class I	30 W	Yes
910925867040	RC340B 42S/930 PSD W60L60 CPC PCS W3W2	Safety class I	31 W	Yes
910925867046	RC340B 36S/940 PSU W60L60 CPC MLO	Safety class I	37.5 W	Yes
910925867047	RC340B 42S/940 PSU W60L60 CPC MLO	Safety class I	44 W	Yes
910925867048	RC340B 42S/940 PSD W60L60 CPC MLO	Safety class I	44.5 W	Yes
910925867167	RC342B 42S/940 PSD W62L62 CPC PCS	Safety class I	30 W	Yes
910925867068	RC340B 42S/930 PSD W30L120 CPC PCS W3W2	Safety class I	31 W	Yes
910925866967	RC340B 36S/940 PSD W60L60 VPC O	Safety class I	29 W	Yes
910925866972	RC340B 36S/940 PSU W60L60 VPC PCS	Safety class I	25 W	Yes
910925866973	RC340B 36S/940 PSD W60L60 VPC PCS	Safety class I	25 W	Yes
910925866977	RC340B 36S/940 PSD W60L60 CPC MLO	Safety class I	37 W	Yes
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	Safety class I	29 W	Yes
910925866991	RC340B 36S/940 PSD W60L60 VPC PCS ELP	Safety class I	29.5 W	Yes

FlexBlend Recessed

Order Code	Full Product Name	Protection class IEC	Power Consumption	Suitable for random switching
910925866997	RC340B 36S/940 PSD W60L60 VPC PCS ELD3	Safety class I	25.5 W	Yes
910925867003	RC340B 42S/940 PSU W60L60 VPC PCS	Safety class I	30 W	Yes
910925867004	RC340B 42S/940 PSD W60L60 VPC PCS	Safety class I	30 W	Yes
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	Safety class I	33.5 W	Yes
910925867009	RC340B 42S/940 PSD W60L60 VPC PCS ELP3	Safety class I	34 W	Yes
910925867034	RC340B 42S/930 PSD W60L60 VPC PCS W3W2	Safety class I	31 W	Yes
910925867035	RC340B 42S/940 PSD W60L60 VPC PCS W3W2	Safety class I	30 W	Yes
910925867044	RC340B 36S/940 PSU W60L60 CPC PCS	Safety class I	25 W	Yes
910925867045	RC340B 36S/940 PSD W60L60 CPC PCS	Safety class I	25 W	Yes
910925867049	RC340B 42S/940 PSU W60L60 CPC PCS	Safety class I	30 W	Yes
910925867050	RC340B 42S/940 PSD W60L60 CPC PCS	Safety class I	30 W	Yes
910925867065	RC340B 36S/940 PSU W60L60 VPC PCS	Safety class I	25 W	Yes
910925867066	RC340B 36S/940 PSD W60L60 VPC PCS	Safety class I	25 W	Yes
910925866966	RC340B 36S/940 PSU W60L60 VPC O	Safety class I	30 W	Yes
910925866980	RC342B 36S/940 PSU W62L62 VPC MLO	Safety class I	37 W	Yes
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	Safety class I	41 W	Yes
910925866989	RC340B 36S/940 PSD W60L60 VPC MLO ELP3	Safety class I	41.5 W	Yes
910925866993	RC340B 36S/940 PSD W60L60 VPC O ELD3	Safety class I	29 W	Yes
910925866995	RC340B 36S/940 PSD W60L60 VPC MLO ELD3	Safety class I	37.5 W	Yes
910925866999	RC340B 42S/940 PSD W60L60 VPC MLO	Safety class I	44.5 W	Yes

Order Code	Full Product Name	Protection class IEC	Power Consumption	Suitable for random switching
910925867010	RC340B 42S/940 PSD W60L60 VPC MLO ELD3	Safety class I	44.5 W	Yes
910925867013	RC340B 42S/930 PSD W60L60 VPC MLO W3W2	Safety class I	47.5 W	Yes
910925867027	RC340B 42S/940 PSD W60L60 VPC MLO W3W2	Safety class I	44.5 W	Yes
910925867043	RC340B 42S/940 PSU W60L60 VPC MLO	Safety class I	44 W	Yes
910925867063	RC340B 36S/940 PSU W60L60 VPC MLO	Safety class I	37.5 W	Yes
910925867064	RC340B 36S/940 PSD W60L60 VPC MLO	Safety class I	37 W	Yes
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	Safety class I	37 W	Yes
910925867014	RC340B 42S/940 PSD W60L60 VPC PCS ELD3	Safety class I	29.5 W	Yes
910925867025	RC340B 42S/930 PSD W60L60 PCV MLO W3W2	Safety class I	47.5 W	Yes
910925867029	RC340B 42S/940 PSD W60L60 PCV MLO W3W2	Safety class I	44.5 W	Yes
910925867037	RC340B 42S/940 PSD W60L60 PCV PCS W3W2	Safety class I	30 W	Yes
910925867041	RC340B 42S/930 PSD W60L60 PCV PCS W3W2	Safety class I	31 W	Yes
910925867168	RC340B 36S/940 PSD W60L60 PCV PCS	Safety class I	25 W	Yes
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	Safety class III	37 W	Yes (relates to presence/ movement detection and daylight harvesting)
910925867224	RC340B 36S/940 POE W60L60 VPC PCS U0	Safety class III	25 W	Yes (relates to presence/ movement detection and

FlexBlend Recessed

Order Code	Full Product Name	Protection class IEC	Power Consumption	Suitable for random switching
				daylight harvesting)
910925866968	RC340B 36S/940 PSU W60L60 VPC MLO	Safety class I	37.5 W	Yes
910925866978	RC340B 36S/940 PSD W60L60 PCV MLO	Safety class I	37 W	Yes
910925866981	RC342B 36S/940 PSD W62L62 VPC MLO	Safety class I	37 W	Yes
910925867145	RC342B 28S/940 PSD W62L62 VPC MLO	Safety class I	28 W	Yes
910925867158	RC342B 28S/940 PSD W62L62 VPC PCS	Safety class I	20 W	Yes

Controls and Dimming

Order Code	Full Product Name	Dimmable	Embedded control
910925867015	RC340B 36S/940 PSU W15L120 VPC MLO	No	-
910925867016	RC340B 36S/940 PSD W15L120 VPC MLO	Yes	-
910925867017	RC340B 42S/940 PSU W15L120 VPC MLO	No	-
910925867018	RC340B 42S/940 PSD W15L120 VPC MLO	Yes	-
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	No	-
910925867020	RC340B 36S/940 PSD W15L120 VPC MLO ELP3	Yes	-
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	No	-
910925867022	RC340B 42S/940 PSD W15L120 VPC MLO ELP3	Yes	-
910925867024	RC340B 36S/940 PSD W15L120 VPC MLO ELD3	Yes	-
910925867026	RC340B 42S/940 PSD W15L120 VPC MLO EL	Yes	-
910925867149	RC342B 28S/940 PSD W15L125 VPC MLO	Yes	-
910925867150	RC342B 36S/940 PSD W15L125 VPC MLO	Yes	-
910925867153	RC342B 36S/940 PSD W17L125 PCV MLO	Yes	-
910925867164	RC342B 28S/940 PSD W15L125 VPC PCS	Yes	-
910925867165	RC342B 36S/940 PSD W15L125 VPC PCS	Yes	-
910925867166	RC342B 42S/940 PSD W15L125 VPC PCS	Yes	-
910925867169	RC342B 36S/940 PSD W17L125 PCV PCS	Yes	-

Order Code	Full Product Name	Protection class IEC	Power Consumption	Suitable for random switching
910925867159	RC342B 36S/940 PSD W62L62 VPC PCS	Safety class I	25 W	Yes
910925867160	RC342B 42S/940 PSD W62L62 VPC PCS	Safety class I	30 W	Yes
910925867174	RC342B 28S/940 PSD W62L62 VPC O	Safety class I	22.5 W	Yes
910925867175	RC342B 36S/940 PSD W62L62 VPC O	Safety class I	29 W	Yes
910925867176	RC342B 42S/940 PSD W62L62 VPC O	Safety class I	33.5 W	Yes

Order Code	Full Product Name	Dimmable	Embedded control
910925867180	RC342B 28S/940 PSD W15L125 VPC O	Yes	-
910925867181	RC342B 36S/940 PSD W15L125 VPC O	Yes	-
910925867182	RC342B 42S/940 PSD W15L125 VPC O	Yes	-
910925866979	RC340B 36S/940 PSD W30L120 VPC MLO	Yes	-
910925866982	RC342B 36S/940 PSU W31L125 VPC MLO	No	-
910925866983	RC342B 36S/940 PSD W31L125 VPC MLO	Yes	-
910925867030	RC340B 42S/940 PSD W30L120 VPC MLO W3W2	Yes	-
910925867031	RC340B 42S/940 PSD W30L120 CPC MLO W3W2	Yes	-
910925867032	RC340B 42S/930 PSD W30L120 VPC MLO W3W2	Yes	-
910925867033	RC340B 42S/930 PSD W30L120 CPC MLO W3W2	Yes	-
910925867038	RC340B 42S/940 PSD W30L120 VPC PCS W3W2	Yes	-
910925867039	RC340B 42S/940 PSD W30L120 CPC PCS W3W2	Yes	-
910925867042	RC340B 42S/930 PSD W30L120 VPC PCS W3W2	Yes	-
910925867147	RC342B 28S/940 PSD W31L125 VPC MLO	Yes	-
910925867161	RC342B 28S/940 PSD W31L125 VPC PCS	Yes	-
910925867162	RC342B 36S/940 PSD W31L125 VPC PCS	Yes	-
910925867163	RC342B 42S/940 PSD W31L125 VPC PCS	Yes	-
910925867177	RC342B 28S/940 PSD W31L125 VPC O	Yes	-
910925867178	RC342B 36S/940 PSD W31L125 VPC O	Yes	-
910925867179	RC342B 42S/940 PSD W31L125 VPC O	Yes	-

FlexBlend Recessed

Order Code	Full Product Name	Dimmable	Embedded control
910925868910	RC340B 36S/930 SRD W60L60 VPC MLO U4	Yes	Upgradable sensor slot with SNS210 sensor
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	Yes	Upgradable sensor slot with SNS210 sensor
910925868912	RC340B 36S/930 SRD W60L60 VPC PCS U4	Yes	Upgradable sensor slot with SNS210 sensor
910925868913	RC340B 36S/930 SRD W60L60 VPC PCS U4	Yes	Upgradable sensor slot with SNS210 sensor
910925868914	RC340B 36S/940 SRD W60L60 VPC MLO U4	Yes	Upgradable sensor slot with SNS210 sensor
910925868915	RC340B 36S/940 SRD W60L60 VPC MLO U4	Yes	Upgradable sensor slot with SNS210 sensor
910925868916	RC340B 36S/940 SRD W60L60 VPC PCS U4	Yes	Upgradable sensor slot with SNS210 sensor
910925868917	RC340B 36S/940 SRD W60L60 VPC PCS U4	Yes	Upgradable sensor slot with SNS210 sensor
910925868918	RC340B 36S/940 SRD W60L60 VPC PCS U4 W3	Yes	Upgradable sensor slot with SNS210 sensor
910925868920	RC340B 42S/940 SRD W60L60 VPC PCS U4 W3	Yes	Upgradable sensor slot with SNS210 sensor
910925868921	RC342B 28S/940 SRD W62L62 VPC MLO U4	Yes	Upgradable sensor slot with SNS210 sensor
910925868922	RC342B 28S/940 SRD W62L62 VPC PCS U4	Yes	Upgradable sensor slot with SNS210 sensor
910925868924	RC342B 36S/940 SRD W62L62 VPC MLO U4	Yes	Upgradable sensor slot with SNS210 sensor
910925868925	RC342B 36S/940 SRD W62L62 VPC PCS U4	Yes	Upgradable sensor slot with SNS210 sensor
910925868927	RC342B 42S/940 SRD W62L62 VPC MLO U4	Yes	Upgradable sensor slot with SNS210 sensor
910925868928	RC342B 42S/940 SRD W62L62 VPC PCS U4	Yes	Upgradable sensor slot with SNS210 sensor
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	No	-
910925866987	RC340B 36S/940 PSD W60L60 VPC O ELP3	Yes	-

Order Code	Full Product Name	Dimmable	Embedded control
910925867001	RC340B 42S/940 PSU W60L60 VPC O	No	-
910925867002	RC340B 42S/940 PSD W60L60 VPC O	Yes	-
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	No	-
910925867007	RC340B 42S/940 PSD W60L60 VPC O ELP3	Yes	-
910925867012	RC340B 42S/940 PSD W60L60 VPC O ELD3	Yes	-
910925867061	RC340B 36S/940 PSU W60L60 VPC O SC	No	-
910925867062	RC340B 36S/940 PSD W60L60 VPC O SC	Yes	-
910925868919	RC340B 42S/940 SRD W30L120 VPC PCS U4 W3	Yes	Upgradable sensor slot with SNS210 sensor
910925868923	RC342B 36S/940 SRD W31L125 VPC PCS U4	Yes	Upgradable sensor slot with SNS210 sensor
910925868926	RC342B 42S/940 SRD W31L125 VPC PCS U4	Yes	Upgradable sensor slot with SNS210 sensor
910925866969	RC340B 36S/940 PSD W60L60 VPC MLO	Yes	-
910925867023	RC340B 42S/930 PSD W60L60 CPC MLO W3W2	Yes	-
910925867028	RC340B 42S/940 PSD W60L60 CPC MLO W3W2	Yes	-
910925867036	RC340B 42S/940 PSD W60L60 CPC PCS W3W2	Yes	-
910925867040	RC340B 42S/930 PSD W60L60 CPC PCS W3W2	Yes	-
910925867046	RC340B 36S/940 PSU W60L60 CPC MLO	No	-
910925867047	RC340B 42S/940 PSU W60L60 CPC MLO	No	-
910925867048	RC340B 42S/940 PSD W60L60 CPC MLO	Yes	-
910925867167	RC342B 42S/940 PSD W62L62 CPC PCS	Yes	-
910925867068	RC340B 42S/930 PSD W30L120 CPC PCS W3W2	Yes	-
910925866967	RC340B 36S/940 PSD W60L60 VPC O	Yes	-
910925866972	RC340B 36S/940 PSU W60L60 VPC PCS	No	-
910925866973	RC340B 36S/940 PSD W60L60 VPC PCS	Yes	-
910925866977	RC340B 36S/940 PSD W60L60 CPC MLO	Yes	-
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	No	-

FlexBlend Recessed

Order Code	Full Product Name	Dimmable	Embedded control
910925866991	RC340B 36S/940 PSD W60L60 VPC PCS ELP	Yes	-
910925866997	RC340B 36S/940 PSD W60L60 VPC PCS ELD3	Yes	-
910925867003	RC340B 42S/940 PSU W60L60 VPC PCS	No	-
910925867004	RC340B 42S/940 PSD W60L60 VPC PCS	Yes	-
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	No	-
910925867009	RC340B 42S/940 PSD W60L60 VPC PCS ELP3	Yes	-
910925867034	RC340B 42S/930 PSD W60L60 VPC PCS W3W2	Yes	-
910925867035	RC340B 42S/940 PSD W60L60 VPC PCS W3W2	Yes	-
910925867044	RC340B 36S/940 PSU W60L60 CPC PCS	No	-
910925867045	RC340B 36S/940 PSD W60L60 CPC PCS	Yes	-
910925867049	RC340B 42S/940 PSU W60L60 CPC PCS	No	-
910925867050	RC340B 42S/940 PSD W60L60 CPC PCS	Yes	-
910925867065	RC340B 36S/940 PSU W60L60 VPC PCS	No	-
910925867066	RC340B 36S/940 PSD W60L60 VPC PCS	Yes	-
910925866966	RC340B 36S/940 PSU W60L60 VPC O	No	-
910925866980	RC342B 36S/940 PSU W62L62 VPC MLO	No	-
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	No	-
910925866989	RC340B 36S/940 PSD W60L60 VPC MLO ELP3	Yes	-
910925866993	RC340B 36S/940 PSD W60L60 VPC O ELD3	Yes	-
910925866995	RC340B 36S/940 PSD W60L60 VPC MLO ELD3	Yes	-
910925866999	RC340B 42S/940 PSD W60L60 VPC MLO	Yes	-
910925867010	RC340B 42S/940 PSD W60L60 VPC MLO ELD3	Yes	-
910925867013	RC340B 42S/930 PSD W60L60 VPC MLO W3W2	Yes	-

Order Code	Full Product Name	Dimmable	Embedded control
910925867027	RC340B 42S/940 PSD W60L60 VPC MLO W3W2	Yes	-
910925867043	RC340B 42S/940 PSU W60L60 VPC MLO	No	-
910925867063	RC340B 36S/940 PSU W60L60 VPC MLO	No	-
910925867064	RC340B 36S/940 PSD W60L60 VPC MLO	Yes	-
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	Yes	-
910925867014	RC340B 42S/940 PSD W60L60 VPC PCS ELD3	Yes	-
910925867025	RC340B 42S/930 PSD W60L60 PCV MLO W3W2	Yes	-
910925867029	RC340B 42S/940 PSD W60L60 PCV MLO W3W2	Yes	-
910925867037	RC340B 42S/940 PSD W60L60 PCV PCS W3W2	Yes	-
910925867041	RC340B 42S/930 PSD W60L60 PCV PCS W3W2	Yes	-
910925867168	RC340B 36S/940 PSD W60L60 PCV PCS	Yes	-
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	Yes	Upgradable sensor slot empty with cover
910925867224	RC340B 36S/940 POE W60L60 VPC PCS U0	Yes	Upgradable sensor slot empty with cover
910925866968	RC340B 36S/940 PSU W60L60 VPC MLO	No	-
910925866978	RC340B 36S/940 PSD W60L60 PCV MLO	Yes	-
910925866981	RC342B 36S/940 PSD W62L62 VPC MLO	Yes	-
910925867145	RC342B 28S/940 PSD W62L62 VPC MLO	Yes	-
910925867158	RC342B 28S/940 PSD W62L62 VPC PCS	Yes	-
910925867159	RC342B 36S/940 PSD W62L62 VPC PCS	Yes	-
910925867160	RC342B 42S/940 PSD W62L62 VPC PCS	Yes	-
910925867174	RC342B 28S/940 PSD W62L62 VPC O	Yes	-
910925867175	RC342B 36S/940 PSD W62L62 VPC O	Yes	-
910925867176	RC342B 42S/940 PSD W62L62 VPC O	Yes	-

Mechanical and Housing

Order Code	Full Product Name	Ingress protection code
910925867015	RC340B 36S/940 PSU W15L120 VPC MLO	IP20/40

Order Code	Full Product Name	Ingress protection code
910925867016	RC340B 36S/940 PSD W15L120 VPC MLO	IP20/40

FlexBlend Recessed

Order Code	Full Product Name	Ingress protection code
910925867017	RC340B 42S/940 PSU W15L120 VPC MLO	IP20/40
910925867018	RC340B 42S/940 PSD W15L120 VPC MLO	IP20/40
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	IP20
910925867020	RC340B 36S/940 PSD W15L120 VPC MLO ELP3	IP20
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	IP20
910925867022	RC340B 42S/940 PSD W15L120 VPC MLO ELP3	IP20
910925867024	RC340B 36S/940 PSD W15L120 VPC MLO ELD3	IP20
910925867026	RC340B 42S/940 PSD W15L120 VPC MLO EL	IP20
910925867149	RC342B 28S/940 PSD W15L125 VPC MLO	IP20/40
910925867150	RC342B 36S/940 PSD W15L125 VPC MLO	IP20/40
910925867153	RC342B 36S/940 PSD W17L125 PCV MLO	IP20/40
910925867164	RC342B 28S/940 PSD W15L125 VPC PCS	IP20/54
910925867165	RC342B 36S/940 PSD W15L125 VPC PCS	IP20/54
910925867166	RC342B 42S/940 PSD W15L125 VPC PCS	IP20/54
910925867169	RC342B 36S/940 PSD W17L125 PCV PCS	IP20/54
910925867180	RC342B 28S/940 PSD W15L125 VPC O	IP20/54
910925867181	RC342B 36S/940 PSD W15L125 VPC O	IP20/54
910925867182	RC342B 42S/940 PSD W15L125 VPC O	IP20/54
910925866979	RC340B 36S/940 PSD W30L120 VPC MLO	IP20/40
910925866982	RC342B 36S/940 PSU W31L125 VPC MLO	IP20/40
910925866983	RC342B 36S/940 PSD W31L125 VPC MLO	IP20/40
910925867030	RC340B 42S/940 PSD W30L120 VPC MLO W3W2	IP20/40
910925867031	RC340B 42S/940 PSD W30L120 CPC MLO W3W2	IP20/40
910925867032	RC340B 42S/930 PSD W30L120 VPC MLO W3W2	IP20/40
910925867033	RC340B 42S/930 PSD W30L120 CPC MLO W3W2	IP20/40
910925867038	RC340B 42S/940 PSD W30L120 VPC PCS W3W2	IP20/54
910925867039	RC340B 42S/940 PSD W30L120 CPC PCS W3W2	IP20/54
910925867042	RC340B 42S/930 PSD W30L120 VPC PCS W3W2	IP20/54
910925867147	RC342B 28S/940 PSD W31L125 VPC MLO	IP20/40
910925867161	RC342B 28S/940 PSD W31L125 VPC PCS	IP20/54
910925867162	RC342B 36S/940 PSD W31L125 VPC PCS	IP20/54
910925867163	RC342B 42S/940 PSD W31L125 VPC PCS	IP20/54
910925867177	RC342B 28S/940 PSD W31L125 VPC O	IP20/54
910925867178	RC342B 36S/940 PSD W31L125 VPC O	IP20/54
910925867179	RC342B 42S/940 PSD W31L125 VPC O	IP20/54
910925868910	RC340B 36S/930 SRD W60L60 VPC MLO U4	IP20
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	IP20
910925868912	RC340B 36S/930 SRD W60L60 VPC PCS U4	IP20/54
910925868913	RC340B 36S/930 SRD W60L60 VPC PCS U4	IP20/54
910925868914	RC340B 36S/940 SRD W60L60 VPC MLO U4	IP20
910925868915	RC340B 36S/940 SRD W60L60 VPC MLO U4	IP20
910925868916	RC340B 36S/940 SRD W60L60 VPC PCS U4	IP20/54
910925868917	RC340B 36S/940 SRD W60L60 VPC PCS U4	IP20/54
910925868918	RC340B 36S/940 SRD W60L60 VPC PCS U4 W3	IP20/54
910925868920	RC340B 42S/940 SRD W60L60 VPC PCS U4 W3	IP20/54
910925868921	RC342B 28S/940 SRD W62L62 VPC MLO U4	IP20
910925868922	RC342B 28S/940 SRD W62L62 VPC PCS U4	IP20/54
910925868924	RC342B 36S/940 SRD W62L62 VPC MLO U4	IP20
910925868925	RC342B 36S/940 SRD W62L62 VPC PCS U4	IP20/54
910925868927	RC342B 42S/940 SRD W62L62 VPC MLO U4	IP20
910925868928	RC342B 42S/940 SRD W62L62 VPC PCS U4	IP20/54

Order Code	Full Product Name	Ingress protection code
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	IP54
910925866987	RC340B 36S/940 PSD W60L60 VPC O ELP3	IP54
910925867001	RC340B 42S/940 PSU W60L60 VPC O	IP20/54
910925867002	RC340B 42S/940 PSD W60L60 VPC O	IP20/54
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	IP20/54
910925867007	RC340B 42S/940 PSD W60L60 VPC O ELP3	IP20/54
910925867012	RC340B 42S/940 PSD W60L60 VPC O ELD3	IP54
910925867061	RC340B 36S/940 PSU W60L60 VPC O SC	IP20/54
910925867062	RC340B 36S/940 PSD W60L60 VPC O SC	IP20/54
910925868919	RC340B 42S/940 SRD W30L120 VPC PCS U4 W3	IP20/54
910925868923	RC342B 36S/940 SRD W31L125 VPC PCS U4	IP20/54
910925868926	RC342B 42S/940 SRD W31L125 VPC PCS U4	IP20/54
910925866969	RC340B 36S/940 PSD W60L60 VPC MLO	IP20/40
910925867023	RC340B 42S/930 PSD W60L60 CPC MLO W3W2	IP20/40
910925867028	RC340B 42S/940 PSD W60L60 CPC MLO W3W2	IP20/40
910925867036	RC340B 42S/940 PSD W60L60 CPC PCS W3W2	IP20/54
910925867040	RC340B 42S/930 PSD W60L60 CPC PCS W3W2	IP20/54
910925867046	RC340B 36S/940 PSU W60L60 CPC MLO	IP20/40
910925867047	RC340B 42S/940 PSU W60L60 CPC MLO	IP20/40
910925867048	RC340B 42S/940 PSD W60L60 CPC MLO	IP20/40
910925867167	RC342B 42S/940 PSD W62L62 CPC PCS	IP20/54
910925867068	RC340B 42S/930 PSD W30L120 CPC PCS W3W2	IP20/54
910925866967	RC340B 36S/940 PSD W60L60 VPC O	IP20/54
910925866972	RC340B 36S/940 PSU W60L60 VPC PCS	IP20/54
910925866973	RC340B 36S/940 PSD W60L60 VPC PCS	IP20/54
910925866977	RC340B 36S/940 PSD W60L60 CPC MLO	IP20/40
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	IP20/54
910925866991	RC340B 36S/940 PSD W60L60 VPC PCS ELP	IP20/54
910925866997	RC340B 36S/940 PSD W60L60 VPC PCS ELD3	IP20/54
910925867003	RC340B 42S/940 PSU W60L60 VPC PCS	IP20/54
910925867004	RC340B 42S/940 PSD W60L60 VPC PCS	IP20/54
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	IP20/54
910925867009	RC340B 42S/940 PSD W60L60 VPC PCS ELP3	IP20/54
910925867034	RC340B 42S/930 PSD W60L60 VPC PCS W3W2	IP20/54
910925867035	RC340B 42S/940 PSD W60L60 VPC PCS W3W2	IP20/54
910925867044	RC340B 36S/940 PSU W60L60 CPC PCS	IP20/54
910925867045	RC340B 36S/940 PSD W60L60 CPC PCS	IP20/54
910925867049	RC340B 42S/940 PSU W60L60 CPC PCS	IP20/54
910925867050	RC340B 42S/940 PSD W60L60 CPC PCS	IP20/54
910925867065	RC340B 36S/940 PSU W60L60 VPC PCS	IP20/54
910925867066	RC340B 36S/940 PSD W60L60 VPC PCS	IP20/54
910925866966	RC340B 36S/940 PSU W60L60 VPC O	IP20/54
910925866980	RC342B 36S/940 PSU W62L62 VPC MLO	IP20/40
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	IP20
910925866989	RC340B 36S/940 PSD W60L60 VPC MLO ELP3	IP20/54
910925866993	RC340B 36S/940 PSD W60L60 VPC O ELD3	IP54
910925866995	RC340B 36S/940 PSD W60L60 VPC MLO ELD3	IP20/54
910925866999	RC340B 42S/940 PSD W60L60 VPC MLO	IP20/40
910925867010	RC340B 42S/940 PSD W60L60 VPC MLO ELD3	IP20
910925867013	RC340B 42S/930 PSD W60L60 VPC MLO W3W2	IP20/40
910925867027	RC340B 42S/940 PSD W60L60 VPC MLO W3W2	IP20/40

FlexBlend Recessed

Order Code	Full Product Name	Ingress protection code
910925867043	RC340B 42S/940 PSU W60L60 VPC MLO	IP20/40
910925867063	RC340B 36S/940 PSU W60L60 VPC MLO	IP20/40
910925867064	RC340B 36S/940 PSD W60L60 VPC MLO	IP20/40
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	IP20/40
910925867014	RC340B 42S/940 PSD W60L60 VPC PCS ELD3	IP20/54
910925867025	RC340B 42S/930 PSD W60L60 PCV MLO W3W2	IP20/40
910925867029	RC340B 42S/940 PSD W60L60 PCV MLO W3W2	IP20/40
910925867037	RC340B 42S/940 PSD W60L60 PCV PCS W3W2	IP20/54
910925867041	RC340B 42S/930 PSD W60L60 PCV PCS W3W2	IP20/54
910925867168	RC340B 36S/940 PSD W60L60 PCV PCS	IP20/54
910925867221	RC340B 36S/940 POE W60L60 VPC MLO UO	IP20

Order Code	Full Product Name	Ingress protection code
910925867224	RC340B 36S/940 POE W60L60 VPC PCS UO	IP20/54
910925866968	RC340B 36S/940 PSU W60L60 VPC MLO	IP20/40
910925866978	RC340B 36S/940 PSD W60L60 PCV MLO	IP20/40
910925866981	RC342B 36S/940 PSD W62L62 VPC MLO	IP20/40
910925867145	RC342B 28S/940 PSD W62L62 VPC MLO	IP20/40
910925867158	RC342B 28S/940 PSD W62L62 VPC PCS	IP20/54
910925867159	RC342B 36S/940 PSD W62L62 VPC PCS	IP20/54
910925867160	RC342B 42S/940 PSD W62L62 VPC PCS	IP20/54
910925867174	RC342B 28S/940 PSD W62L62 VPC O	IP20/54
910925867175	RC342B 36S/940 PSD W62L62 VPC O	IP20/54
910925867176	RC342B 42S/940 PSD W62L62 VPC O	IP20/54

Emergency Operation

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867015	RC340B 36S/940 PSU W15L120 VPC MLO	-	-
910925867016	RC340B 36S/940 PSD W15L120 VPC MLO	-	-
910925867017	RC340B 42S/940 PSU W15L120 VPC MLO	-	-
910925867018	RC340B 42S/940 PSD W15L120 VPC MLO	-	-
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867020	RC340B 36S/940 PSD W15L120 VPC MLO ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867022	RC340B 42S/940 PSD W15L120 VPC MLO ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867024	RC340B 36S/940 PSD W15L120 VPC MLO ELD3	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867026	RC340B 42S/940 PSD W15L120 VPC MLO EL	Emergency lighting 3 hours duration Pro version	3 hour(s)

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867149	RC342B 28S/940 PSD W15L125 VPC MLO	-	-
910925867150	RC342B 36S/940 PSD W15L125 VPC MLO	-	-
910925867153	RC342B 36S/940 PSD W17L125 PCV MLO	-	-
910925867164	RC342B 28S/940 PSD W15L125 VPC PCS	-	-
910925867165	RC342B 36S/940 PSD W15L125 VPC PCS	-	-
910925867166	RC342B 42S/940 PSD W15L125 VPC PCS	-	-
910925867169	RC342B 36S/940 PSD W17L125 PCV PCS	-	-
910925867180	RC342B 28S/940 PSD W15L125 VPC O	-	-
910925867181	RC342B 36S/940 PSD W15L125 VPC O	-	-
910925867182	RC342B 42S/940 PSD W15L125 VPC O	-	-
910925866979	RC340B 36S/940 PSD W30L120 VPC MLO	-	-
910925866982	RC342B 36S/940 PSU W31L125 VPC MLO	-	-
910925866983	RC342B 36S/940 PSD W31L125 VPC MLO	-	-
910925867030	RC340B 42S/940 PSD W30L120 VPC MLO W3W2	-	-
910925867031	RC340B 42S/940 PSD W30L120 CPC MLO W3W2	-	-
910925867032	RC340B 42S/930 PSD W30L120 VPC MLO W3W2	-	-

FlexBlend Recessed

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867033	RC340B 42S/930 PSD W30L120 CPC MLO W3W2	-	-
910925867038	RC340B 42S/940 PSD W30L120 VPC PCS W3W2	-	-
910925867039	RC340B 42S/940 PSD W30L120 CPC PCS W3W2	-	-
910925867042	RC340B 42S/930 PSD W30L120 VPC PCS W3W2	-	-
910925867147	RC342B 28S/940 PSD W31L125 VPC MLO	-	-
910925867161	RC342B 28S/940 PSD W31L125 VPC PCS	-	-
910925867162	RC342B 36S/940 PSD W31L125 VPC PCS	-	-
910925867163	RC342B 42S/940 PSD W31L125 VPC PCS	-	-
910925867177	RC342B 28S/940 PSD W31L125 VPC O	-	-
910925867178	RC342B 36S/940 PSD W31L125 VPC O	-	-
910925867179	RC342B 42S/940 PSD W31L125 VPC O	-	-
910925868910	RC340B 36S/930 SRD W60L60 VPC MLO U4	-	-
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	-	-
910925868912	RC340B 36S/930 SRD W60L60 VPC PCS U4	-	-
910925868913	RC340B 36S/930 SRD W60L60 VPC PCS U4	-	-
910925868914	RC340B 36S/940 SRD W60L60 VPC MLO U4	-	-
910925868915	RC340B 36S/940 SRD W60L60 VPC MLO U4	-	-
910925868916	RC340B 36S/940 SRD W60L60 VPC PCS U4	-	-
910925868917	RC340B 36S/940 SRD W60L60 VPC PCS U4	-	-
910925868918	RC340B 36S/940 SRD W60L60 VPC PCS U4 W3	-	-
910925868920	RC340B 42S/940 SRD W60L60 VPC PCS U4 W3	-	-
910925868921	RC342B 28S/940 SRD W62L62 VPC MLO U4	-	-
910925868922	RC342B 28S/940 SRD W62L62 VPC PCS U4	-	-
910925868924	RC342B 36S/940 SRD W62L62 VPC MLO U4	-	-

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925868925	RC342B 36S/940 SRD W62L62 VPC PCS U4	-	-
910925868927	RC342B 42S/940 SRD W62L62 VPC MLO U4	-	-
910925868928	RC342B 42S/940 SRD W62L62 VPC PCS U4	-	-
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925866987	RC340B 36S/940 PSD W60L60 VPC O ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867001	RC340B 42S/940 PSU W60L60 VPC O	-	-
910925867002	RC340B 42S/940 PSD W60L60 VPC O	-	-
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867007	RC340B 42S/940 PSD W60L60 VPC O ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867012	RC340B 42S/940 PSD W60L60 VPC O ELD3	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910925867061	RC340B 36S/940 PSU W60L60 VPC O SC	-	-
910925867062	RC340B 36S/940 PSD W60L60 VPC O SC	-	-
910925868919	RC340B 42S/940 SRD W30L120 VPC PCS U4 W3	-	-
910925868923	RC342B 36S/940 SRD W31L125 VPC PCS U4	-	-
910925868926	RC342B 42S/940 SRD W31L125 VPC PCS U4	-	-
910925866969	RC340B 36S/940 PSD W60L60 VPC MLO	-	-
910925867023	RC340B 42S/930 PSD W60L60 CPC MLO W3W2	-	-
910925867028	RC340B 42S/940 PSD W60L60 CPC MLO W3W2	-	-
910925867036	RC340B 42S/940 PSD W60L60 CPC PCS W3W2	-	-

FlexBlend Recessed

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867040	RC340B 42S/930 PSD W60L60 CPC PCS W3W2	-	-
910925867046	RC340B 36S/940 PSU W60L60 CPC MLO	-	-
910925867047	RC340B 42S/940 PSU W60L60 CPC MLO	-	-
910925867048	RC340B 42S/940 PSD W60L60 CPC MLO	-	-
910925867167	RC342B 42S/940 PSD W62L62 CPC PCS	-	-
910925867068	RC340B 42S/930 PSD W30L120 CPC PCS W3W2	-	-
910925866967	RC340B 36S/940 PSD W60L60 VPC O	-	-
910925866972	RC340B 36S/940 PSU W60L60 VPC PCS	-	-
910925866973	RC340B 36S/940 PSD W60L60 VPC PCS	-	-
910925866977	RC340B 36S/940 PSD W60L60 CPC MLO	-	-
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925866991	RC340B 36S/940 PSD W60L60 VPC PCS ELP	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925866997	RC340B 36S/940 PSD W60L60 VPC PCS ELD3	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910925867003	RC340B 42S/940 PSU W60L60 VPC PCS	-	-
910925867004	RC340B 42S/940 PSD W60L60 VPC PCS	-	-
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867009	RC340B 42S/940 PSD W60L60 VPC PCS ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925867034	RC340B 42S/930 PSD W60L60 VPC PCS W3W2	-	-
910925867035	RC340B 42S/940 PSD W60L60 VPC PCS W3W2	-	-

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925867044	RC340B 36S/940 PSU W60L60 CPC PCS	-	-
910925867045	RC340B 36S/940 PSD W60L60 CPC PCS	-	-
910925867049	RC340B 42S/940 PSU W60L60 CPC PCS	-	-
910925867050	RC340B 42S/940 PSD W60L60 CPC PCS	-	-
910925867065	RC340B 36S/940 PSU W60L60 VPC PCS	-	-
910925867066	RC340B 36S/940 PSD W60L60 VPC PCS	-	-
910925866966	RC340B 36S/940 PSU W60L60 VPC O	-	-
910925866980	RC342B 36S/940 PSU W62L62 VPC MLO	-	-
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925866989	RC340B 36S/940 PSD W60L60 VPC MLO ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
910925866993	RC340B 36S/940 PSD W60L60 VPC O ELD3	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910925866995	RC340B 36S/940 PSD W60L60 VPC MLO ELD3	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910925866999	RC340B 42S/940 PSD W60L60 VPC MLO	-	-
910925867010	RC340B 42S/940 PSD W60L60 VPC MLO ELD3	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910925867013	RC340B 42S/930 PSD W60L60 VPC MLO W3W2	-	-
910925867027	RC340B 42S/940 PSD W60L60 VPC MLO W3W2	-	-
910925867043	RC340B 42S/940 PSU W60L60 VPC MLO	-	-
910925867063	RC340B 36S/940 PSU W60L60 VPC MLO	-	-
910925867064	RC340B 36S/940 PSD W60L60 VPC MLO	-	-

FlexBlend Recessed

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	-	-
910925867014	RC340B 42S/940 PSD W60L60 VPC PCS ELD3	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
910925867025	RC340B 42S/930 PSD W60L60 PCV MLO W3W2	-	-
910925867029	RC340B 42S/940 PSD W60L60 PCV MLO W3W2	-	-
910925867037	RC340B 42S/940 PSD W60L60 PCV PCS W3W2	-	-
910925867041	RC340B 42S/930 PSD W60L60 PCV PCS W3W2	-	-
910925867168	RC340B 36S/940 PSD W60L60 PCV PCS	-	-
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	-	-
910925867224	RC340B 36S/940 POE W60L60 VPC PCS U0	-	-

Approval and Application

Order Code	Full Product Name	Glow-wire test
910925867015	RC340B 36S/940 PSU W15L120 VPC MLO	Temperature 650 °C, duration 30 s
910925867016	RC340B 36S/940 PSD W15L120 VPC MLO	Temperature 650 °C, duration 30 s
910925867017	RC340B 42S/940 PSU W15L120 VPC MLO	Temperature 650 °C, duration 30 s
910925867018	RC340B 42S/940 PSD W15L120 VPC MLO	Temperature 650 °C, duration 30 s
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s
910925867020	RC340B 36S/940 PSD W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s
910925867022	RC340B 42S/940 PSD W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s
910925867024	RC340B 36S/940 PSD W15L120 VPC MLO ELD3	Temperature 650 °C, duration 30 s
910925867026	RC340B 42S/940 PSD W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s
910925867149	RC342B 28S/940 PSD W15L125 VPC MLO	Temperature 650 °C, duration 30 s
910925867150	RC342B 36S/940 PSD W15L125 VPC MLO	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
910925866968	RC340B 36S/940 PSU W60L60 VPC MLO	-	-
910925866978	RC340B 36S/940 PSD W60L60 PCV MLO	-	-
910925866981	RC342B 36S/940 PSD W62L62 VPC MLO	-	-
910925867145	RC342B 28S/940 PSD W62L62 VPC MLO	-	-
910925867158	RC342B 28S/940 PSD W62L62 VPC PCS	-	-
910925867159	RC342B 36S/940 PSD W62L62 VPC PCS	-	-
910925867160	RC342B 42S/940 PSD W62L62 VPC PCS	-	-
910925867174	RC342B 28S/940 PSD W62L62 VPC O	-	-
910925867175	RC342B 36S/940 PSD W62L62 VPC O	-	-
910925867176	RC342B 42S/940 PSD W62L62 VPC O	-	-

Order Code	Full Product Name	Glow-wire test
910925867153	RC342B 36S/940 PSD W17L125 PCV MLO	Temperature 650 °C, duration 30 s
910925867164	RC342B 28S/940 PSD W15L125 VPC PCS	Temperature 850 °C, duration 30 s
910925867165	RC342B 36S/940 PSD W15L125 VPC PCS	Temperature 850 °C, duration 30 s
910925867166	RC342B 42S/940 PSD W15L125 VPC PCS	Temperature 850 °C, duration 30 s
910925867169	RC342B 36S/940 PSD W17L125 PCV PCS	Temperature 850 °C, duration 30 s
910925867180	RC342B 28S/940 PSD W15L125 VPC O	Temperature 850 °C, duration 30 s
910925867181	RC342B 36S/940 PSD W15L125 VPC O	Temperature 850 °C, duration 30 s
910925867182	RC342B 42S/940 PSD W15L125 VPC O	Temperature 850 °C, duration 30 s
910925866979	RC340B 36S/940 PSD W30L120 VPC MLO	Temperature 650 °C, duration 30 s
910925866982	RC342B 36S/940 PSU W31L125 VPC MLO	Temperature 650 °C, duration 30 s
910925866983	RC342B 36S/940 PSD W31L125 VPC MLO	Temperature 650 °C, duration 30 s
910925867030	RC340B 42S/940 PSD W30L120 VPC MLO W3W2	Temperature 650 °C, duration 30 s

FlexBlend Recessed

Order Code	Full Product Name	Glow-wire test
910925867031	RC340B 42S/940 PSD W30L120 CPC MLO W3W2	Temperature 650 °C, duration 30 s
910925867032	RC340B 42S/930 PSD W30L120 VPC MLO W3W2	Temperature 650 °C, duration 30 s
910925867033	RC340B 42S/930 PSD W30L120 CPC MLO W3W2	Temperature 650 °C, duration 30 s
910925867038	RC340B 42S/940 PSD W30L120 VPC PCS W3W2	Temperature 850 °C, duration 30 s
910925867039	RC340B 42S/940 PSD W30L120 CPC PCS W3W2	Temperature 850 °C, duration 30 s
910925867042	RC340B 42S/930 PSD W30L120 VPC PCS W3W2	Temperature 850 °C, duration 30 s
910925867147	RC342B 28S/940 PSD W31L125 VPC MLO	Temperature 650 °C, duration 30 s
910925867161	RC342B 28S/940 PSD W31L125 VPC PCS	Temperature 850 °C, duration 30 s
910925867162	RC342B 36S/940 PSD W31L125 VPC PCS	Temperature 850 °C, duration 30 s
910925867163	RC342B 42S/940 PSD W31L125 VPC PCS	Temperature 850 °C, duration 30 s
910925867177	RC342B 28S/940 PSD W31L125 VPC O	Temperature 850 °C, duration 30 s
910925867178	RC342B 36S/940 PSD W31L125 VPC O	Temperature 850 °C, duration 30 s
910925867179	RC342B 42S/940 PSD W31L125 VPC O	Temperature 850 °C, duration 30 s
910925868910	RC340B 36S/930 SRD W60L60 VPC MLO U4	Temperature 650 °C, duration 30 s
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	Temperature 650 °C, duration 30 s
910925868912	RC340B 36S/930 SRD W60L60 VPC PCS U4	Temperature 850 °C, duration 30 s
910925868913	RC340B 36S/930 SRD W60L60 VPC PCS U4	Temperature 850 °C, duration 30 s
910925868914	RC340B 36S/940 SRD W60L60 VPC MLO U4	Temperature 650 °C, duration 30 s
910925868915	RC340B 36S/940 SRD W60L60 VPC MLO U4	Temperature 650 °C, duration 30 s
910925868916	RC340B 36S/940 SRD W60L60 VPC PCS U4	Temperature 850 °C, duration 30 s
910925868917	RC340B 36S/940 SRD W60L60 VPC PCS U4	Temperature 850 °C, duration 30 s
910925868918	RC340B 36S/940 SRD W60L60 VPC PCS U4 W3	Temperature 850 °C, duration 30 s
910925868920	RC340B 42S/940 SRD W60L60 VPC PCS U4 W3	Temperature 850 °C, duration 30 s
910925868921	RC342B 28S/940 SRD W62L62 VPC MLO U4	Temperature 650 °C, duration 30 s
910925868922	RC342B 28S/940 SRD W62L62 VPC PCS U4	Temperature 850 °C, duration 30 s
910925868924	RC342B 36S/940 SRD W62L62 VPC MLO U4	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
910925868925	RC342B 36S/940 SRD W62L62 VPC PCS U4	Temperature 850 °C, duration 30 s
910925868927	RC342B 42S/940 SRD W62L62 VPC MLO U4	Temperature 650 °C, duration 30 s
910925868928	RC342B 42S/940 SRD W62L62 VPC PCS U4	Temperature 850 °C, duration 30 s
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s
910925866987	RC340B 36S/940 PSD W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s
910925867001	RC340B 42S/940 PSU W60L60 VPC O	Temperature 850 °C, duration 30 s
910925867002	RC340B 42S/940 PSD W60L60 VPC O	Temperature 850 °C, duration 30 s
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s
910925867007	RC340B 42S/940 PSD W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s
910925867012	RC340B 42S/940 PSD W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s
910925867061	RC340B 36S/940 PSU W60L60 VPC O SC	Temperature 850 °C, duration 30 s
910925867062	RC340B 36S/940 PSD W60L60 VPC O SC	Temperature 850 °C, duration 30 s
910925868919	RC340B 42S/940 SRD W30L120 VPC PCS U4 W3	Temperature 850 °C, duration 30 s
910925868923	RC342B 36S/940 SRD W31L125 VPC PCS U4	Temperature 850 °C, duration 30 s
910925868926	RC342B 42S/940 SRD W31L125 VPC PCS U4	Temperature 850 °C, duration 30 s
910925866969	RC340B 36S/940 PSD W60L60 VPC MLO	Temperature 650 °C, duration 30 s
910925867023	RC340B 42S/930 PSD W60L60 CPC MLO W3W2	Temperature 650 °C, duration 30 s
910925867028	RC340B 42S/940 PSD W60L60 CPC MLO W3W2	Temperature 650 °C, duration 30 s
910925867036	RC340B 42S/940 PSD W60L60 CPC PCS W3W2	Temperature 850 °C, duration 30 s
910925867040	RC340B 42S/930 PSD W60L60 CPC PCS W3W2	Temperature 850 °C, duration 30 s
910925867046	RC340B 36S/940 PSU W60L60 CPC MLO	Temperature 650 °C, duration 30 s
910925867047	RC340B 42S/940 PSU W60L60 CPC MLO	Temperature 650 °C, duration 30 s
910925867048	RC340B 42S/940 PSD W60L60 CPC MLO	Temperature 650 °C, duration 30 s
910925867167	RC342B 42S/940 PSD W62L62 CPC PCS	Temperature 850 °C, duration 30 s
910925867068	RC340B 42S/930 PSD W30L120 CPC PCS W3W2	Temperature 850 °C, duration 30 s
910925866967	RC340B 36S/940 PSD W60L60 VPC O	Temperature 850 °C, duration 30 s

FlexBlend Recessed

Order Code	Full Product Name	Glow-wire test
910925866972	RC340B 36S/940 PSU W60L60 VPC PCS	Temperature 850 °C, duration 30 s
910925866973	RC340B 36S/940 PSD W60L60 VPC PCS	Temperature 850 °C, duration 30 s
910925866977	RC340B 36S/940 PSD W60L60 CPC MLO	Temperature 650 °C, duration 30 s
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s
910925866991	RC340B 36S/940 PSD W60L60 VPC PCS ELP	Temperature 850 °C, duration 30 s
910925866997	RC340B 36S/940 PSD W60L60 VPC PCS ELD3	Temperature 850 °C, duration 30 s
910925867003	RC340B 42S/940 PSU W60L60 VPC PCS	Temperature 850 °C, duration 30 s
910925867004	RC340B 42S/940 PSD W60L60 VPC PCS	Temperature 850 °C, duration 30 s
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s
910925867009	RC340B 42S/940 PSD W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s
910925867034	RC340B 42S/930 PSD W60L60 VPC PCS W3W2	Temperature 850 °C, duration 30 s
910925867035	RC340B 42S/940 PSD W60L60 VPC PCS W3W2	Temperature 850 °C, duration 30 s
910925867044	RC340B 36S/940 PSU W60L60 CPC PCS	Temperature 850 °C, duration 30 s
910925867045	RC340B 36S/940 PSD W60L60 CPC PCS	Temperature 850 °C, duration 30 s
910925867049	RC340B 42S/940 PSU W60L60 CPC PCS	Temperature 850 °C, duration 30 s
910925867050	RC340B 42S/940 PSD W60L60 CPC PCS	Temperature 850 °C, duration 30 s
910925867065	RC340B 36S/940 PSU W60L60 VPC PCS	Temperature 850 °C, duration 30 s
910925867066	RC340B 36S/940 PSD W60L60 VPC PCS	Temperature 850 °C, duration 30 s
910925866966	RC340B 36S/940 PSU W60L60 VPC O	Temperature 850 °C, duration 30 s
910925866980	RC342B 36S/940 PSU W62L62 VPC MLO	Temperature 650 °C, duration 30 s
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	Temperature 650 °C, duration 30 s
910925866989	RC340B 36S/940 PSD W60L60 VPC MLO ELP3	Temperature 650 °C, duration 30 s
910925866993	RC340B 36S/940 PSD W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s
910925866995	RC340B 36S/940 PSD W60L60 VPC MLO ELD3	Temperature 650 °C, duration 30 s
910925866999	RC340B 42S/940 PSD W60L60 VPC MLO	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
910925867010	RC340B 42S/940 PSD W60L60 VPC MLO ELD3	Temperature 650 °C, duration 30 s
910925867013	RC340B 42S/930 PSD W60L60 VPC MLO W3W2	Temperature 650 °C, duration 30 s
910925867027	RC340B 42S/940 PSD W60L60 VPC MLO W3W2	Temperature 650 °C, duration 30 s
910925867043	RC340B 42S/940 PSU W60L60 VPC MLO	Temperature 650 °C, duration 30 s
910925867063	RC340B 36S/940 PSU W60L60 VPC MLO	Temperature 650 °C, duration 30 s
910925867064	RC340B 36S/940 PSD W60L60 VPC MLO	Temperature 650 °C, duration 30 s
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	Temperature 650 °C, duration 30 s
910925867014	RC340B 42S/940 PSD W60L60 VPC PCS ELD3	Temperature 850 °C, duration 30 s
910925867025	RC340B 42S/930 PSD W60L60 PCV MLO W3W2	Temperature 650 °C, duration 30 s
910925867029	RC340B 42S/940 PSD W60L60 PCV MLO W3W2	Temperature 650 °C, duration 30 s
910925867037	RC340B 42S/940 PSD W60L60 PCV PCS W3W2	Temperature 850 °C, duration 30 s
910925867041	RC340B 42S/930 PSD W60L60 PCV PCS W3W2	Temperature 850 °C, duration 30 s
910925867168	RC340B 36S/940 PSD W60L60 PCV PCS	Temperature 850 °C, duration 30 s
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	Temperature 650 °C, duration 30 s
910925867224	RC340B 36S/940 POE W60L60 VPC PCS U0	Temperature 850 °C, duration 30 s
910925866968	RC340B 36S/940 PSU W60L60 VPC MLO	Temperature 650 °C, duration 30 s
910925866978	RC340B 36S/940 PSD W60L60 PCV MLO	Temperature 650 °C, duration 30 s
910925866981	RC342B 36S/940 PSD W62L62 VPC MLO	Temperature 650 °C, duration 30 s
910925867145	RC342B 28S/940 PSD W62L62 VPC MLO	Temperature 650 °C, duration 30 s
910925867158	RC342B 28S/940 PSD W62L62 VPC PCS	Temperature 850 °C, duration 30 s
910925867159	RC342B 36S/940 PSD W62L62 VPC PCS	Temperature 850 °C, duration 30 s
910925867160	RC342B 42S/940 PSD W62L62 VPC PCS	Temperature 850 °C, duration 30 s
910925867174	RC342B 28S/940 PSD W62L62 VPC O	Temperature 850 °C, duration 30 s
910925867175	RC342B 36S/940 PSD W62L62 VPC O	Temperature 850 °C, duration 30 s
910925867176	RC342B 42S/940 PSD W62L62 VPC O	Temperature 850 °C, duration 30 s

Over Time Performance (IEC Compliant)

FlexBlend Recessed

Order Code	Full Product Name	Driver failure rate at 5000 h
910925867015	RC340B 36S/940 PSU W15L120 VPC MLO	0.01 %
910925867016	RC340B 36S/940 PSD W15L120 VPC MLO	0.01 %
910925867017	RC340B 42S/940 PSU W15L120 VPC MLO	0.01 %
910925867018	RC340B 42S/940 PSD W15L120 VPC MLO	0.01 %
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	0.01 %
910925867020	RC340B 36S/940 PSD W15L120 VPC MLO ELP3	0.01 %
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	0.01 %
910925867022	RC340B 42S/940 PSD W15L120 VPC MLO ELP3	0.01 %
910925867024	RC340B 36S/940 PSD W15L120 VPC MLO ELD3	0.01 %
910925867026	RC340B 42S/940 PSD W15L120 VPC MLO EL	0.01 %
910925867149	RC342B 28S/940 PSD W15L125 VPC MLO	-
910925867150	RC342B 36S/940 PSD W15L125 VPC MLO	-
910925867153	RC342B 36S/940 PSD W17L125 PCV MLO	-
910925867164	RC342B 28S/940 PSD W15L125 VPC PCS	-
910925867165	RC342B 36S/940 PSD W15L125 VPC PCS	-
910925867166	RC342B 42S/940 PSD W15L125 VPC PCS	-
910925867169	RC342B 36S/940 PSD W17L125 PCV PCS	-
910925867180	RC342B 28S/940 PSD W15L125 VPC O	-
910925867181	RC342B 36S/940 PSD W15L125 VPC O	-
910925867182	RC342B 42S/940 PSD W15L125 VPC O	-
910925866979	RC340B 36S/940 PSD W30L120 VPC MLO	0.01 %
910925866982	RC342B 36S/940 PSU W31L125 VPC MLO	0.01 %
910925866983	RC342B 36S/940 PSD W31L125 VPC MLO	0.01 %
910925867030	RC340B 42S/940 PSD W30L120 VPC MLO W3W2	0.01 %
910925867031	RC340B 42S/940 PSD W30L120 CPC MLO W3W2	0.01 %
910925867032	RC340B 42S/930 PSD W30L120 VPC MLO W3W2	0.01 %
910925867033	RC340B 42S/930 PSD W30L120 CPC MLO W3W2	0.01 %
910925867038	RC340B 42S/940 PSD W30L120 VPC PCS W3W2	0.01 %
910925867039	RC340B 42S/940 PSD W30L120 CPC PCS W3W2	0.01 %
910925867042	RC340B 42S/930 PSD W30L120 VPC PCS W3W2	0.01 %
910925867147	RC342B 28S/940 PSD W31L125 VPC MLO	-
910925867161	RC342B 28S/940 PSD W31L125 VPC PCS	-
910925867162	RC342B 36S/940 PSD W31L125 VPC PCS	-
910925867163	RC342B 42S/940 PSD W31L125 VPC PCS	-
910925867177	RC342B 28S/940 PSD W31L125 VPC O	-
910925867178	RC342B 36S/940 PSD W31L125 VPC O	-
910925867179	RC342B 42S/940 PSD W31L125 VPC O	-
910925868910	RC340B 36S/930 SRD W60L60 VPC MLO U4	-
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	-
910925868912	RC340B 36S/930 SRD W60L60 VPC PCS U4	-
910925868913	RC340B 36S/930 SRD W60L60 VPC PCS U4	-
910925868914	RC340B 36S/940 SRD W60L60 VPC MLO U4	-
910925868915	RC340B 36S/940 SRD W60L60 VPC MLO U4	-
910925868916	RC340B 36S/940 SRD W60L60 VPC PCS U4	-
910925868917	RC340B 36S/940 SRD W60L60 VPC PCS U4	-
910925868918	RC340B 36S/940 SRD W60L60 VPC PCS U4 W3	-
910925868920	RC340B 42S/940 SRD W60L60 VPC PCS U4 W3	-
910925868921	RC342B 28S/940 SRD W62L62 VPC MLO U4	-
910925868922	RC342B 28S/940 SRD W62L62 VPC PCS U4	-
910925868924	RC342B 36S/940 SRD W62L62 VPC MLO U4	-
910925868925	RC342B 36S/940 SRD W62L62 VPC PCS U4	-

Order Code	Full Product Name	Driver failure rate at 5000 h
910925868927	RC342B 42S/940 SRD W62L62 VPC MLO U4	-
910925868928	RC342B 42S/940 SRD W62L62 VPC PCS U4	-
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	0.01 %
910925866987	RC340B 36S/940 PSD W60L60 VPC O ELP3	0.01 %
910925867001	RC340B 42S/940 PSU W60L60 VPC O	0.01 %
910925867002	RC340B 42S/940 PSD W60L60 VPC O	0.01 %
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	0.01 %
910925867007	RC340B 42S/940 PSD W60L60 VPC O ELP3	0.01 %
910925867012	RC340B 42S/940 PSD W60L60 VPC O ELD3	0.01 %
910925867061	RC340B 36S/940 PSU W60L60 VPC O SC	0.01 %
910925867062	RC340B 36S/940 PSD W60L60 VPC O SC	0.01 %
910925868919	RC340B 42S/940 SRD W30L120 VPC PCS U4 W3	-
910925868923	RC342B 36S/940 SRD W31L125 VPC PCS U4	-
910925868926	RC342B 42S/940 SRD W31L125 VPC PCS U4	-
910925866969	RC340B 36S/940 PSD W60L60 VPC MLO	0.01 %
910925867023	RC340B 42S/930 PSD W60L60 CPC MLO W3W2	0.01 %
910925867028	RC340B 42S/940 PSD W60L60 CPC MLO W3W2	0.01 %
910925867036	RC340B 42S/940 PSD W60L60 CPC PCS W3W2	0.01 %
910925867040	RC340B 42S/930 PSD W60L60 CPC PCS W3W2	0.01 %
910925867046	RC340B 36S/940 PSU W60L60 CPC MLO	0.01 %
910925867047	RC340B 42S/940 PSU W60L60 CPC MLO	0.01 %
910925867048	RC340B 42S/940 PSD W60L60 CPC MLO	0.01 %
910925867167	RC342B 42S/940 PSD W62L62 CPC PCS	-
910925867068	RC340B 42S/930 PSD W30L120 CPC PCS W3W2	0.01 %
910925866967	RC340B 36S/940 PSD W60L60 VPC O	0.01 %
910925866972	RC340B 36S/940 PSU W60L60 VPC PCS	0.01 %
910925866973	RC340B 36S/940 PSD W60L60 VPC PCS	0.01 %
910925866977	RC340B 36S/940 PSD W60L60 CPC MLO	0.01 %
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	0.01 %
910925866991	RC340B 36S/940 PSD W60L60 VPC PCS ELP	0.01 %
910925866997	RC340B 36S/940 PSD W60L60 VPC PCS ELD3	0.01 %
910925867003	RC340B 42S/940 PSU W60L60 VPC PCS	0.01 %
910925867004	RC340B 42S/940 PSD W60L60 VPC PCS	0.01 %
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	0.01 %
910925867009	RC340B 42S/940 PSD W60L60 VPC PCS ELP3	0.01 %
910925867034	RC340B 42S/930 PSD W60L60 VPC PCS W3W2	0.01 %
910925867035	RC340B 42S/940 PSD W60L60 VPC PCS W3W2	0.01 %
910925867044	RC340B 36S/940 PSU W60L60 CPC PCS	0.01 %
910925867045	RC340B 36S/940 PSD W60L60 CPC PCS	0.01 %
910925867049	RC340B 42S/940 PSU W60L60 CPC PCS	0.01 %
910925867050	RC340B 42S/940 PSD W60L60 CPC PCS	0.01 %
910925867065	RC340B 36S/940 PSU W60L60 VPC PCS	0.01 %
910925867066	RC340B 36S/940 PSD W60L60 VPC PCS	0.01 %
910925866966	RC340B 36S/940 PSU W60L60 VPC O	0.01 %
910925866980	RC342B 36S/940 PSU W62L62 VPC MLO	0.01 %
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	0.01 %
910925866989	RC340B 36S/940 PSD W60L60 VPC MLO ELP3	0.01 %
910925866993	RC340B 36S/940 PSD W60L60 VPC O ELD3	0.01 %
910925866995	RC340B 36S/940 PSD W60L60 VPC MLO ELD3	0.01 %
910925866999	RC340B 42S/940 PSD W60L60 VPC MLO	0.01 %
910925867010	RC340B 42S/940 PSD W60L60 VPC MLO ELD3	0.01 %

FlexBlend Recessed

Order Code	Full Product Name	Driver failure rate at 5000 h
910925867013	RC340B 42S/930 PSD W60L60 VPC MLO W3W2	0.01 %
910925867027	RC340B 42S/940 PSD W60L60 VPC MLO W3W2	0.01 %
910925867043	RC340B 42S/940 PSU W60L60 VPC MLO	0.01 %
910925867063	RC340B 36S/940 PSU W60L60 VPC MLO	0.01 %
910925867064	RC340B 36S/940 PSD W60L60 VPC MLO	0.01 %
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	0.01 %
910925867014	RC340B 42S/940 PSD W60L60 VPC PCS ELD3	0.01 %
910925867025	RC340B 42S/930 PSD W60L60 PCV MLO W3W2	0.01 %
910925867029	RC340B 42S/940 PSD W60L60 PCV MLO W3W2	0.01 %
910925867037	RC340B 42S/940 PSD W60L60 PCV PCS W3W2	0.01 %
910925867041	RC340B 42S/930 PSD W60L60 PCV PCS W3W2	0.01 %
910925867168	RC340B 36S/940 PSD W60L60 PCV PCS	-

Order Code	Full Product Name	Driver failure rate at 5000 h
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	-
910925867224	RC340B 36S/940 POE W60L60 VPC PCS U0	-
910925866968	RC340B 36S/940 PSU W60L60 VPC MLO	0.01 %
910925866978	RC340B 36S/940 PSD W60L60 PCV MLO	0.01 %
910925866981	RC342B 36S/940 PSD W62L62 VPC MLO	0.01 %
910925867145	RC342B 28S/940 PSD W62L62 VPC MLO	-
910925867158	RC342B 28S/940 PSD W62L62 VPC PCS	-
910925867159	RC342B 36S/940 PSD W62L62 VPC PCS	-
910925867160	RC342B 42S/940 PSD W62L62 VPC PCS	-
910925867174	RC342B 28S/940 PSD W62L62 VPC O	-
910925867175	RC342B 36S/940 PSD W62L62 VPC O	-
910925867176	RC342B 42S/940 PSD W62L62 VPC O	-

Product Data

Order Code	Full Product Name	Product family code
910925867015	RC340B 36S/940 PSU W15L120 VPC MLO	RC340B
910925867016	RC340B 36S/940 PSD W15L120 VPC MLO	RC340B
910925867017	RC340B 42S/940 PSU W15L120 VPC MLO	RC340B
910925867018	RC340B 42S/940 PSD W15L120 VPC MLO	RC340B
910925867019	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	RC340B
910925867020	RC340B 36S/940 PSD W15L120 VPC MLO ELP3	RC340B
910925867021	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	RC340B
910925867022	RC340B 42S/940 PSD W15L120 VPC MLO ELP3	RC340B
910925867024	RC340B 36S/940 PSD W15L120 VPC MLO ELD3	RC340B
910925867026	RC340B 42S/940 PSD W15L120 VPC MLO EL	RC340B
910925867149	RC342B 28S/940 PSD W15L125 VPC MLO	RC342B
910925867150	RC342B 36S/940 PSD W15L125 VPC MLO	RC342B
910925867153	RC342B 36S/940 PSD W17L125 PCV MLO	RC342B
910925867164	RC342B 28S/940 PSD W15L125 VPC PCS	RC342B
910925867165	RC342B 36S/940 PSD W15L125 VPC PCS	RC342B
910925867166	RC342B 42S/940 PSD W15L125 VPC PCS	RC342B
910925867169	RC342B 36S/940 PSD W17L125 PCV PCS	RC342B
910925867180	RC342B 28S/940 PSD W15L125 VPC O	RC342B
910925867181	RC342B 36S/940 PSD W15L125 VPC O	RC342B
910925867182	RC342B 42S/940 PSD W15L125 VPC O	RC342B
910925866979	RC340B 36S/940 PSD W30L120 VPC MLO	RC340B
910925866982	RC342B 36S/940 PSU W31L125 VPC MLO	RC342B
910925866983	RC342B 36S/940 PSD W31L125 VPC MLO	RC342B
910925867030	RC340B 42S/940 PSD W30L120 VPC MLO W3W2	RC340B
910925867031	RC340B 42S/940 PSD W30L120 CPC MLO W3W2	RC340B
910925867032	RC340B 42S/930 PSD W30L120 VPC MLO W3W2	RC340B
910925867033	RC340B 42S/930 PSD W30L120 CPC MLO W3W2	RC340B
910925867038	RC340B 42S/940 PSD W30L120 VPC PCS W3W2	RC340B
910925867039	RC340B 42S/940 PSD W30L120 CPC PCS W3W2	RC340B
910925867042	RC340B 42S/930 PSD W30L120 VPC PCS W3W2	RC340B
910925867147	RC342B 28S/940 PSD W31L125 VPC MLO	RC342B
910925867161	RC342B 28S/940 PSD W31L125 VPC PCS	RC342B
910925867162	RC342B 36S/940 PSD W31L125 VPC PCS	RC342B
910925867163	RC342B 42S/940 PSD W31L125 VPC PCS	RC342B
910925867177	RC342B 28S/940 PSD W31L125 VPC O	RC342B


Order Code	Full Product Name	Product family code
910925867178	RC342B 36S/940 PSD W31L125 VPC O	RC342B
910925867179	RC342B 42S/940 PSD W31L125 VPC O	RC342B
910925868910	RC340B 36S/930 SRD W60L60 VPC MLO U4	RC340B
910925868911	RC340B 36S/930 SRD W60L60 VPC MLO U4	RC340B
910925868912	RC340B 36S/930 SRD W60L60 VPC PCS U4	RC340B
910925868913	RC340B 36S/930 SRD W60L60 VPC PCS U4	RC340B
910925868914	RC340B 36S/940 SRD W60L60 VPC MLO U4	RC340B
910925868915	RC340B 36S/940 SRD W60L60 VPC MLO U4	RC340B
910925868916	RC340B 36S/940 SRD W60L60 VPC PCS U4	RC340B
910925868917	RC340B 36S/940 SRD W60L60 VPC PCS U4	RC340B
910925868918	RC340B 36S/940 SRD W60L60 VPC PCS U4 W3	RC340B
910925868920	RC340B 42S/940 SRD W60L60 VPC PCS U4 W3	RC340B
910925868921	RC342B 28S/940 SRD W62L62 VPC MLO U4	RC342B
910925868922	RC342B 28S/940 SRD W62L62 VPC PCS U4	RC342B
910925868924	RC342B 36S/940 SRD W62L62 VPC MLO U4	RC342B
910925868925	RC342B 36S/940 SRD W62L62 VPC PCS U4	RC342B
910925868927	RC342B 42S/940 SRD W62L62 VPC MLO U4	RC342B
910925868928	RC342B 42S/940 SRD W62L62 VPC PCS U4	RC342B
910925866986	RC340B 36S/940 PSU W60L60 VPC O ELP3	RC340B
910925866987	RC340B 36S/940 PSD W60L60 VPC O ELP3	RC340B
910925867001	RC340B 42S/940 PSU W60L60 VPC O	RC340B
910925867002	RC340B 42S/940 PSD W60L60 VPC O	RC340B
910925867006	RC340B 42S/940 PSU W60L60 VPC O ELP3	RC340B
910925867007	RC340B 42S/940 PSD W60L60 VPC O ELP3	RC340B
910925867012	RC340B 42S/940 PSD W60L60 VPC O ELD3	RC340B
910925867061	RC340B 36S/940 PSU W60L60 VPC O SC	RC340B
910925867062	RC340B 36S/940 PSD W60L60 VPC O SC	RC340B
910925868919	RC340B 42S/940 SRD W30L120 VPC PCS U4 W3	RC340B
910925868923	RC342B 36S/940 SRD W31L125 VPC PCS U4	RC342B
910925868926	RC342B 42S/940 SRD W31L125 VPC PCS U4	RC342B
910925866969	RC340B 36S/940 PSD W60L60 VPC MLO	RC340B
910925867023	RC340B 42S/930 PSD W60L60 CPC MLO W3W2	RC340B
910925867028	RC340B 42S/940 PSD W60L60 CPC MLO W3W2	RC340B
910925867036	RC340B 42S/940 PSD W60L60 CPC PCS W3W2	RC340B
910925867040	RC340B 42S/930 PSD W60L60 CPC PCS W3W2	RC340B

FlexBlend Recessed


Order Code	Full Product Name	Product family code
910925867046	RC340B 36S/940 PSU W60L60 CPC MLO	RC340B
910925867047	RC340B 42S/940 PSU W60L60 CPC MLO	RC340B
910925867048	RC340B 42S/940 PSD W60L60 CPC MLO	RC340B
910925867167	RC342B 42S/940 PSD W62L62 CPC PCS	RC342B
910925867068	RC340B 42S/930 PSD W30L120 CPC PCS W3W2	RC340B
910925866967	RC340B 36S/940 PSD W60L60 VPC O	RC340B
910925866972	RC340B 36S/940 PSU W60L60 VPC PCS	RC340B
910925866973	RC340B 36S/940 PSD W60L60 VPC PCS	RC340B
910925866977	RC340B 36S/940 PSD W60L60 CPC MLO	RC340B
910925866990	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	RC340B
910925866991	RC340B 36S/940 PSD W60L60 VPC PCS ELP	RC340B
910925866997	RC340B 36S/940 PSD W60L60 VPC PCS ELD3	RC340B
910925867003	RC340B 42S/940 PSU W60L60 VPC PCS	RC340B
910925867004	RC340B 42S/940 PSD W60L60 VPC PCS	RC340B
910925867008	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	RC340B
910925867009	RC340B 42S/940 PSD W60L60 VPC PCS ELP3	RC340B
910925867034	RC340B 42S/930 PSD W60L60 VPC PCS W3W2	RC340B
910925867035	RC340B 42S/940 PSD W60L60 VPC PCS W3W2	RC340B
910925867044	RC340B 36S/940 PSU W60L60 CPC PCS	RC340B
910925867045	RC340B 36S/940 PSD W60L60 CPC PCS	RC340B
910925867049	RC340B 42S/940 PSU W60L60 CPC PCS	RC340B
910925867050	RC340B 42S/940 PSD W60L60 CPC PCS	RC340B
910925867065	RC340B 36S/940 PSU W60L60 VPC PCS	RC340B
910925867066	RC340B 36S/940 PSD W60L60 VPC PCS	RC340B
910925866966	RC340B 36S/940 PSU W60L60 VPC O	RC340B
910925866980	RC342B 36S/940 PSU W62L62 VPC MLO	RC342B
910925866988	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	RC340B
910925866989	RC340B 36S/940 PSD W60L60 VPC MLO ELP3	RC340B

Order Code	Full Product Name	Product family code
910925866993	RC340B 36S/940 PSD W60L60 VPC O ELD3	RC340B
910925866995	RC340B 36S/940 PSD W60L60 VPC MLO ELD3	RC340B
910925866999	RC340B 42S/940 PSD W60L60 VPC MLO	RC340B
910925867010	RC340B 42S/940 PSD W60L60 VPC MLO ELD3	RC340B
910925867013	RC340B 42S/930 PSD W60L60 VPC MLO W3W2	RC340B
910925867027	RC340B 42S/940 PSD W60L60 VPC MLO W3W2	RC340B
910925867043	RC340B 42S/940 PSU W60L60 VPC MLO	RC340B
910925867063	RC340B 36S/940 PSU W60L60 VPC MLO	RC340B
910925867064	RC340B 36S/940 PSD W60L60 VPC MLO	RC340B
910925866970	RC340B 36S/940 POE W60L60 VPC MLO	RC340B
910925867014	RC340B 42S/940 PSD W60L60 VPC PCS ELD3	RC340B
910925867025	RC340B 42S/930 PSD W60L60 PCV MLO W3W2	RC340B
910925867029	RC340B 42S/940 PSD W60L60 PCV MLO W3W2	RC340B
910925867037	RC340B 42S/940 PSD W60L60 PCV PCS W3W2	RC340B
910925867041	RC340B 42S/930 PSD W60L60 PCV PCS W3W2	RC340B
910925867168	RC340B 36S/940 PSD W60L60 PCV PCS	RC340B
910925867221	RC340B 36S/940 POE W60L60 VPC MLO U0	RC340B
910925867224	RC340B 36S/940 POE W60L60 VPC PCS U0	RC340B
910925866968	RC340B 36S/940 PSU W60L60 VPC MLO	RC340B
910925866978	RC340B 36S/940 PSD W60L60 PCV MLO	RC340B
910925866981	RC342B 36S/940 PSD W62L62 VPC MLO	RC342B
910925867145	RC342B 28S/940 PSD W62L62 VPC MLO	RC342B
910925867158	RC342B 28S/940 PSD W62L62 VPC PCS	RC342B
910925867159	RC342B 36S/940 PSD W62L62 VPC PCS	RC342B
910925867160	RC342B 42S/940 PSD W62L62 VPC PCS	RC342B
910925867174	RC342B 28S/940 PSD W62L62 VPC O	RC342B
910925867175	RC342B 36S/940 PSD W62L62 VPC O	RC342B
910925867176	RC342B 42S/940 PSD W62L62 VPC O	RC342B


Polar Wide Diagrams



Polar Normal (separate) - RC340BI -
910925866978




Polar Normal (separate) - RC340BI -
910925866989




Polar Normal (separate) - RC340BI -
910925867030


Polar Wide Diagrams




**Polar Normal (separate) - RC340BI -
910925867031**




Polar Normal (separate) - RC340BI - 910925866987




Polar Normal (separate) - RC340BI - 910925868912




Polar Normal (separate) - RC340BI - 910925868924




Polar Normal (separate) - RC340BI - 910925868915




Polar Normal (separate) - RC340BI - 910925868917



Polar Normal (separate) - RC340BI - 910925868928




Polar Normal (separate) - RC340BI - 910925868910




Polar Normal (separate) - RC340BI - 910925868927


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925868921




Polar Normal (separate) - RC340BI - 910925868926




Polar Normal (separate) - RC340BI - 910925868914




Polar Normal (separate) - RC340BI - 910925868923




Polar Normal (separate) - RC340BI - 910925868911




Polar Normal (separate) - RC340BI - 910925868922



Polar Normal (separate) - RC340BI - 910925868925




Polar Normal (separate) - RC340BI - 910925868920




Polar Normal (separate) - RC340BI - 910925866969


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925866968




Polar Normal (separate) - RC340BI - 910925866970




Polar Normal (separate) - RC340BI - 910925866979




Polar Normal (separate) - RC340BI - 910925866981




Polar Normal (separate) - RC340BI - 910925867038




Polar Normal (separate) - RC340BI - 910925867040



Polar Normal (separate) - RC340BI - 910925867050




Polar Normal (separate) - RC340BI - 910925866973




Polar Normal (separate) - RC340BI - 910925866991


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925866993




Polar Normal (separate) - RC340BI - 910925867002




Polar Normal (separate) - RC340BI - 910925867003




Polar Normal (separate) - RC340BI - 910925866977




Polar Normal (separate) - RC340BI - 910925866995




Polar Normal (separate) - RC340BI - 910925867012




Polar Normal (separate) - RC340BI - 910925867017




Polar Normal (separate) - RC340BI - 910925867019




Polar Normal (separate) - RC340BI - 910925867033



Polar Normal (separate) - RC340BI - 910925867024	Polar Normal (separate) - RC340BI - 910925867043	Polar Normal (separate) - RC340BI - 910925867049
---	---	---




Polar Normal (separate) - RC340BI - 910925866967	Polar Normal (separate) - RC340BI - 910925867010	Polar Normal (separate) - RC340BI - 910925867013
---	---	---




Polar Normal (separate) - RC340BI - 910925867022	Polar Normal (separate) - RC340BI - 910925867034	Polar Normal (separate) - RC340BI - 910925867039
--	--	--


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867032




Polar Normal (separate) - RC340BI - 910925867064




Polar Normal (separate) - RC340BI - 910925866980




Polar Normal (separate) - RC340BI - 910925866982




Polar Normal (separate) - RC340BI - 910925866983




Polar Normal (separate) - RC340BI - 910925866988




Polar Normal (separate) - RC340BI - 910925866997




Polar Normal (separate) - RC340BI - 910925867006




Polar Normal (separate) - RC340BI - 910925867009



Polar Normal (separate) - RC340BI - 910925867047	Polar Normal (separate) - RC340BI - 910925867062	Polar Normal (separate) - RC340BI - 910925867063
---	---	---




Polar Normal (separate) - RC340BI - 910925866966	Polar Normal (separate) - RC340BI - 910925867008	Polar Normal (separate) - RC340BI - 910925867018
---	---	---




Polar Normal (separate) - RC340BI - 910925867016	Polar Normal (separate) - RC340BI - 910925867021	Polar Normal (separate) - RC340BI - 910925867025
--	--	--


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867028




Polar Normal (separate) - RC340BI - 910925867014




**Polar Normal (separate) - RC340BI -
910925867145**




**Polar Normal (separate) - RC340BI -
910925867147**




Polar Normal (separate) - RC340BI - 910925867020




Polar Normal (separate) - RC340BI - 910925867026



Polar Normal (separate) - RC340BI - 910925867035






**Polar Normal (separate) - RC340BI -
910925867036**



Polar Normal (separate) - RC340BI - 910925867044




Polar Wide Diagrams



Polar Normal (separate) - RC340BI - 910925867045

Polar Normal (separate) - RC340BI - 910925867048




Polar Normal (separate) - RC340BI - 910925867065



Polar Normal (separate) - RC340BI - 910925867149

Polar Normal (separate) - RC340BI - 910925867159

Polar Normal (separate) - RC340BI - 910925867158




Polar Normal (separate) - RC340BI - 910925867165


Polar Normal (separate) - RC340BI - 910925867166

Polar Normal (separate) - RC340BI - 910925867167


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867177




Polar Normal (separate) - RC340BI - 910925867178




Polar Normal (separate) - RC340BI - 910925867221




Polar Normal (separate) - RC340BI - 910925867041




Polar Normal (separate) - RC340BI - 910925867066




Polar Normal (separate) - RC340BI - 910925867162



Polar Normal (separate) - RC340BI - 910925867160




Polar Normal (separate) - RC340BI - 910925867153




Polar Normal (separate) - RC340BI - 910925867175


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867179




Polar Normal (separate) - RC340BI - 910925867182




Polar Normal (separate) - RC340BI - 910925867163




Polar Normal (separate) - RC340BI - 910925867174




Polar Normal (separate) - RC340BI - 910925867176




Polar Normal (separate) - RC340BI - 910925866972



Polar Normal (separate) - RC340BI - 910925866986




Polar Normal (separate) - RC340BI - 910925866990




Polar Normal (separate) - RC340BI - 910925866999


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867001




Polar Normal (separate) - RC340BI - 910925867004




Polar Normal (separate) - RC340BI - 910925867007




Polar Normal (separate) - RC340BI - 910925867015




Polar Normal (separate) - RC340BI - 910925867023




Polar Normal (separate) - RC340BI - 910925867027



Polar Normal (separate) - RC340BI - 910925867029




Polar Normal (separate) - RC340BI - 910925867037




Polar Normal (separate) - RC340BI - 910925867046


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867042




Polar Normal (separate) - RC340BI - 910925867061




Polar Normal (separate) - RC340BI - 910925867068




Polar Normal (separate) - RC340BI - 910925867150




**Polar Normal (separate) - RC340BI -
910925867161**




Polar Normal (separate) - RC340BI - 910925867164



Polar Normal (separate) - RC340BI - 910925867168




Polar Normal (separate) - RC340BI - 910925867169




Polar Normal (separate) - RC340BI - 910925867181


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867180




Polar Normal (separate) - RC340BI - 910925867224




Polar Normal (separate) - RC340BI - 910925868913



Polar Normal (separate) - RC340BI - 910925868916



Polar Normal (separate) - RC340BI - 910925868918



Polar Normal (separate) - RC340BI - 910925868919

