

FlexBlend - Unlocking the potential of LED lighting in offices

FlexBlend Recessed

Office owners and staff responsible for lighting operations are searching for high-quality yet energy-efficient lighting that complies with norms and regulations. Designed to support these needs, Philips FlexBlend is enabling building owners to fully optimise their lighting operations, by offering office-compliant lighting with an attractive return on investment. Furthermore, FlexBlend provides the required flexibility by being easy to use with different ceiling lights, as well as in different office spaces like open office or meeting rooms. Though technology is changing fast, the ideal lighting solution is also expected to be ready to incorporate innovations and future advances that can help optimise operations further. For this reason, Philips FlexBlend is also ready to be connected to controls such as Actilume or used together with the Philips SpaceWise lighting system. It can also be connected to software-based lighting systems like Interact Office, which provides the luminaire with further intelligence and enables it to collect valuable data about its environment

Benefits

- High-quality office-compliant lighting
- Choice of three different exit-windows
- Fast return on investment
- Application flexibility
- Scalable and ready to be connected to controls and lighting systems

FlexBlend Recessed

Features

- Fully office-compliant (UGR <19)
- Homogenous and uniform light effect
- Dimensional variety, local options
- Various mounting options
- Integrated sensors
- Can be combined with Philips ActiLume and SpaceWise systems
- Ready to be connected to software based lighting systems such as Interact Office

Application

- Offices
- Education
- Healthcare
- Banks

Versions





FlexBlend Recessed RC340B
W60L60 MLO CPC




FlexBlend Recessed RC340B
W60L60 PCS VPC

Dimensional drawing



Dimensional drawing



FlexBlend Recessed

Product details



Upgradable sensor




O_FlexBlend Recessed-
RC342B_W62L62_MLO_VPC



FlexBlend Recessed-
RC340B_MLO_DPP




FlexBlend Recessed-
RC340B_W60L60_Backcover_VP
C



FlexBlend Recessed-
RC340B_W60L60_CPC brackets



FlexBlend Recessed-
RC340B_W60L60_CPC
brackets_B



FlexBlend Recessed-
RC340B_OPA_DPP



FlexBlend Recessed-
RC340B_PCS_DPP

FlexBlend Recessed

Product details

O_FlexBlend Recessed-
RC340B_W60L60_PCS_VPC



FlexBlend Recessed-
RC340B_W60L60_CPC
brackets_A



FlexBlend Recessed RC340B PIP
Open



FlexBlend Recessed-
RC340B_W60L60_backcover_PC
V



O_FlexBlend Recessed-
RC340B_W60L60_MLO_VPC



O_FlexBlend Recessed-
RC340B_W60L60_MLO_CPC



FlexBlend Recessed-RC340B PIP
Closed



FlexBlend Recessed-
RC340B_W60L60_backcover_CP
C



FlexBlend Recessed

General Information	
Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	≥90
Optic type	Wide beam
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Controls and Dimming	
Maximum dim level	1%
Mechanical and Housing	
Housing Color	White
Mech. impact protection code	IK02
Approval and Application	
Ambient temperature range	+10 to +40 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.38, 0.37) SDCM ≤3
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
10277400	RC340B 36S/940 PSU W15L120 VPC MLO	96 lm/W	3,600 lm
10278100	RC340B 36S/940 PSD W15L120 VPC MLO	97.5 lm/W	3,600 lm
10279800	RC340B 42S/940 PSU W15L120 VPC MLO	95.5 lm/W	4,200 lm
10280400	RC340B 42S/940 PSD W15L120 VPC MLO	94.5 lm/W	4,200 lm
10281100	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	88 lm/W	3,600 lm
10282800	RC340B 36S/940 PSD W15L120 VPC MLO ELP3	86.5 lm/W	3,600 lm
10283500	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	87.5 lm/W	4,200 lm
10284200	RC340B 42S/940 PSD W15L120 VPC MLO ELP3	85.5 lm/W	4,200 lm
10286600	RC340B 36S/940 PSD W15L120 VPC MLO ELD3	96 lm/W	3,600 lm
10288000	RC340B 42S/940 PSD W15L120 VPC MLO EL	94.5 lm/W	4,200 lm
10410500	RC342B 28S/940 PSD W15L125 VPC MLO	100 lm/W	2,800 lm
10411200	RC342B 36S/940 PSD W15L125 VPC MLO	97.5 lm/W	3,600 lm
10414300	RC342B 36S/940 PSD W17L125 PCV MLO	97.5 lm/W	3,600 lm
10425900	RC342B 28S/940 PSD W15L125 VPC PCS	140 lm/W	2,800 lm
10426600	RC342B 36S/940 PSD W15L125 VPC PCS	138 lm/W	3,600 lm
10427300	RC342B 42S/940 PSD W15L125 VPC PCS	140 lm/W	4,200 lm
10430300	RC342B 36S/940 PSD W17L125 PCV PCS	144 lm/W	3,600 lm
10441900	RC342B 28S/940 PSD W15L125 VPC O	124 lm/W	2,800 lm
10442600	RC342B 36S/940 PSD W15L125 VPC O	124 lm/W	3,600 lm
10443300	RC342B 42S/940 PSD W15L125 VPC O	125 lm/W	4,200 lm
10242200	RC340B 36S/940 PSD W30L120 VPC MLO	97.5 lm/W	3,600 lm
10245300	RC342B 36S/940 PSU W31L125 VPC MLO	97.5 lm/W	3,600 lm
10246000	RC342B 36S/940 PSD W31L125 VPC MLO	97.5 lm/W	3,600 lm
10408200	RC342B 28S/940 PSD W31L125 VPC MLO	100 lm/W	2,800 lm
10422800	RC342B 28S/940 PSD W31L125 VPC PCS	140 lm/W	2,800 lm
10423500	RC342B 36S/940 PSD W31L125 VPC PCS	138 lm/W	3,600 lm
10424200	RC342B 42S/940 PSD W31L125 VPC PCS	140 lm/W	4,200 lm
10438900	RC342B 28S/940 PSD W31L125 VPC O	124 lm/W	2,800 lm
10439600	RC342B 36S/940 PSD W31L125 VPC O	124 lm/W	3,600 lm
10440200	RC342B 42S/940 PSD W31L125 VPC O	125 lm/W	4,200 lm
10249100	RC340B 36S/940 PSU W60L60 VPC O ELP3	111 lm/W	3,600 lm
10250700	RC340B 36S/940 PSD W60L60 VPC O ELP3	109 lm/W	3,600 lm
10263700	RC340B 42S/940 PSU W60L60 VPC O	127 lm/W	4,200 lm
10264400	RC340B 42S/940 PSD W60L60 VPC O	125 lm/W	4,200 lm
10268200	RC340B 42S/940 PSU W60L60 VPC O ELP3	114 lm/W	4,200 lm
10269900	RC340B 42S/940 PSD W60L60 VPC O ELP3	112 lm/W	4,200 lm
10274300	RC340B 42S/940 PSD W60L60 VPC O ELD3	125 lm/W	4,200 lm
10323800	RC340B 36S/940 PSU W60L60 VPC O SC	120 lm/W	3,600 lm
10324500	RC340B 36S/940 PSD W60L60 VPC O SC	124 lm/W	3,600 lm
10232300	RC340B 36S/940 PSD W60L60 VPC MLO	97.5 lm/W	3,600 lm
10308500	RC340B 36S/940 PSU W60L60 CPC MLO	96 lm/W	3,600 lm
10309200	RC340B 42S/940 PSU W60L60 CPC MLO	95.5 lm/W	4,200 lm
10310800	RC340B 42S/940 PSD W60L60 CPC MLO	94.5 lm/W	4,200 lm
10428000	RC342B 42S/940 PSD W62L62 CPC PCS	140 lm/W	4,200 lm
10230900	RC340B 36S/940 PSD W60L60 VPC O	124 lm/W	3,600 lm
10235400	RC340B 36S/940 PSU W60L60 VPC PCS	144 lm/W	3,600 lm
10236100	RC340B 36S/940 PSD W60L60 VPC PCS	144 lm/W	3,600 lm
10240800	RC340B 36S/940 PSD W60L60 CPC MLO	97.5 lm/W	3,600 lm
10253800	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	124 lm/W	3,600 lm
10254500	RC340B 36S/940 PSD W60L60 VPC PCS ELP	122 lm/W	3,600 lm
10260600	RC340B 36S/940 PSD W60L60 VPC PCS ELD3	141 lm/W	3,600 lm

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
10265100	RC340B 42S/940 PSU W60L60 VPC PCS	140 lm/W	4,200 lm
10266800	RC340B 42S/940 PSD W60L60 VPC PCS	140 lm/W	4,200 lm
10270500	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	125 lm/W	4,200 lm
10271200	RC340B 42S/940 PSD W60L60 VPC PCS ELP3	124 lm/W	4,200 lm
10306100	RC340B 36S/940 PSU W60L60 CPC PCS	144 lm/W	3,600 lm
10307800	RC340B 36S/940 PSD W60L60 CPC PCS	144 lm/W	3,600 lm
10311500	RC340B 42S/940 PSU W60L60 CPC PCS	140 lm/W	4,200 lm
10312200	RC340B 42S/940 PSD W60L60 CPC PCS	140 lm/W	4,200 lm
10327600	RC340B 36S/940 PSU W60L60 VPC PCS	144 lm/W	3,600 lm
10328300	RC340B 36S/940 PSD W60L60 VPC PCS	144 lm/W	3,600 lm
10229300	RC340B 36S/940 PSU W60L60 VPC O	120 lm/W	3,600 lm
10243900	RC342B 36S/940 PSU W62L62 VPC MLO	97.5 lm/W	3,600 lm
10251400	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	88 lm/W	3,600 lm
10252100	RC340B 36S/940 PSD W60L60 VPC MLO ELP3	86.5 lm/W	3,600 lm
10256900	RC340B 36S/940 PSD W60L60 VPC O ELD3	124 lm/W	3,600 lm
10258300	RC340B 36S/940 PSD W60L60 VPC MLO ELD3	96 lm/W	3,600 lm
10262000	RC340B 42S/940 PSD W60L60 VPC MLO	94.5 lm/W	4,200 lm
10272900	RC340B 42S/940 PSD W60L60 VPC MLO ELD3	94.5 lm/W	4,200 lm
10305400	RC340B 42S/940 PSU W60L60 VPC MLO	95.5 lm/W	4,200 lm
10325200	RC340B 36S/940 PSU W60L60 VPC MLO	96 lm/W	3,600 lm
10326900	RC340B 36S/940 PSD W60L60 VPC MLO	97.5 lm/W	3,600 lm
10233000	RC340B 36S/940 POE W60L60 VPC MLO	97.5 lm/W	3,600 lm
10276700	RC340B 42S/940 PSD W60L60 VPC PCS ELD3	142 lm/W	4,200 lm
10481500	RC340B 36S/940 POE W60L60 VPC MLO U0	97.5 lm/W	3,600 lm
10484600	RC340B 36S/940 POE W60L60 VPC PCS U0	144 lm/W	3,600 lm
10231600	RC340B 36S/940 PSU W60L60 VPC MLO	96 lm/W	3,600 lm
10241500	RC340B 36S/940 PSD W60L60 PCV MLO	97.5 lm/W	3,600 lm
10244600	RC342B 36S/940 PSD W62L62 VPC MLO	97.5 lm/W	3,600 lm
10406800	RC342B 28S/940 PSD W62L62 VPC MLO	100 lm/W	2,800 lm
10419800	RC342B 28S/940 PSD W62L62 VPC PCS	140 lm/W	2,800 lm
10420400	RC342B 36S/940 PSD W62L62 VPC PCS	144 lm/W	3,600 lm
10421100	RC342B 42S/940 PSD W62L62 VPC PCS	140 lm/W	4,200 lm
10435800	RC342B 28S/940 PSD W62L62 VPC O	124 lm/W	2,800 lm
10436500	RC342B 36S/940 PSD W62L62 VPC O	124 lm/W	3,600 lm
10437200	RC342B 42S/940 PSD W62L62 VPC O	125 lm/W	4,200 lm

Operating and Electrical

Order Code	Full Product Name	Protection class IEC	Power Consumption	Suitable for random switching
10277400	RC340B 36S/940 PSU W15L120 VPC MLO	Safety class I	37.5 W	Yes
10278100	RC340B 36S/940 PSD W15L120 VPC MLO	Safety class I	37 W	Yes
10279800	RC340B 42S/940 PSU W15L120 VPC MLO	Safety class I	44 W	Yes
10280400	RC340B 42S/940 PSD W15L120 VPC MLO	Safety class I	44.5 W	Yes
10281100	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	Safety class I	41 W	Yes

Order Code	Full Product Name	Protection class IEC	Power Consumption	Suitable for random switching
10282800	RC340B 36S/940 PSD W15L120 VPC MLO ELP3	Safety class I	41.5 W	Yes
10283500	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	Safety class I	48 W	Yes
10284200	RC340B 42S/940 PSD W15L120 VPC MLO ELP3	Safety class I	49 W	Yes

FlexBlend Recessed

Order Code	Full Product Name	Protection class IEC	Power Consumption	Suitable for random switching
10286600	RC340B 36S/940 PSD W15L120 VPC MLO ELD3	Safety class I	37.5 W	Yes
10288000	RC340B 42S/940 PSD W15L120 VPC MLO EL	Safety class I	44.5 W	Yes
10410500	RC342B 28S/940 PSD W15L125 VPC MLO	Safety class I	28 W	Yes
10411200	RC342B 36S/940 PSD W15L125 VPC MLO	Safety class I	37 W	Yes
10414300	RC342B 36S/940 PSD W17L125 PCV MLO	Safety class I	37 W	Yes
10425900	RC342B 28S/940 PSD W15L125 VPC PCS	Safety class I	20 W	Yes
10426600	RC342B 36S/940 PSD W15L125 VPC PCS	Safety class I	26 W	Yes
10427300	RC342B 42S/940 PSD W15L125 VPC PCS	Safety class I	30 W	Yes
10430300	RC342B 36S/940 PSD W17L125 PCV PCS	Safety class I	25 W	Yes
10441900	RC342B 28S/940 PSD W15L125 VPC O	Safety class I	22.5 W	Yes
10442600	RC342B 36S/940 PSD W15L125 VPC O	Safety class I	29 W	Yes
10443300	RC342B 42S/940 PSD W15L125 VPC O	Safety class I	33.5 W	Yes
10242200	RC340B 36S/940 PSD W30L120 VPC MLO	Safety class I	37 W	Yes
10245300	RC342B 36S/940 PSU W31L125 VPC MLO	Safety class I	37 W	Yes
10246000	RC342B 36S/940 PSD W31L125 VPC MLO	Safety class I	37 W	Yes
10408200	RC342B 28S/940 PSD W31L125 VPC MLO	Safety class I	28 W	Yes
10422800	RC342B 28S/940 PSD W31L125 VPC PCS	Safety class I	20 W	Yes
10423500	RC342B 36S/940 PSD W31L125 VPC PCS	Safety class I	26 W	Yes
10424200	RC342B 42S/940 PSD W31L125 VPC PCS	Safety class I	30 W	Yes
10438900	RC342B 28S/940 PSD W31L125 VPC O	Safety class I	22.5 W	Yes
10439600	RC342B 36S/940 PSD W31L125 VPC O	Safety class I	29 W	Yes
10440200	RC342B 42S/940 PSD W31L125 VPC O	Safety class I	33.5 W	Yes
10249100	RC340B 36S/940 PSU W60L60 VPC O ELP3	Safety class I	32.5 W	Yes
10250700	RC340B 36S/940 PSD W60L60 VPC O ELP3	Safety class I	33 W	Yes

Order Code	Full Product Name	Protection class IEC	Power Consumption	Suitable for random switching
10263700	RC340B 42S/940 PSU W60L60 VPC O	Safety class I	33 W	Yes
10264400	RC340B 42S/940 PSD W60L60 VPC O	Safety class I	33.5 W	Yes
10268200	RC340B 42S/940 PSU W60L60 VPC O ELP3	Safety class I	37 W	Yes
10269900	RC340B 42S/940 PSD W60L60 VPC O ELP3	Safety class I	37.5 W	Yes
10274300	RC340B 42S/940 PSD W60L60 VPC O ELD3	Safety class I	33.5 W	Yes
10323800	RC340B 36S/940 PSU W60L60 VPC O SC	Safety class I	30 W	Yes
10324500	RC340B 36S/940 PSD W60L60 VPC O SC	Safety class I	29 W	Yes
10232300	RC340B 36S/940 PSD W60L60 VPC MLO	Safety class I	37 W	Yes
10308500	RC340B 36S/940 PSU W60L60 CPC MLO	Safety class I	37.5 W	Yes
10309200	RC340B 42S/940 PSU W60L60 CPC MLO	Safety class I	44 W	Yes
10310800	RC340B 42S/940 PSD W60L60 CPC MLO	Safety class I	44.5 W	Yes
10428000	RC342B 42S/940 PSD W62L62 CPC PCS	Safety class I	30 W	Yes
10230900	RC340B 36S/940 PSD W60L60 VPC O	Safety class I	29 W	Yes
10235400	RC340B 36S/940 PSU W60L60 VPC PCS	Safety class I	25 W	Yes
10236100	RC340B 36S/940 PSD W60L60 VPC PCS	Safety class I	25 W	Yes
10240800	RC340B 36S/940 PSD W60L60 CPC MLO	Safety class I	37 W	Yes
10253800	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	Safety class I	29 W	Yes
10254500	RC340B 36S/940 PSD W60L60 VPC PCS ELP	Safety class I	29.5 W	Yes
10260600	RC340B 36S/940 PSD W60L60 VPC PCS ELD3	Safety class I	25.5 W	Yes
10265100	RC340B 42S/940 PSU W60L60 VPC PCS	Safety class I	30 W	Yes
10266800	RC340B 42S/940 PSD W60L60 VPC PCS	Safety class I	30 W	Yes
10270500	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	Safety class I	33.5 W	Yes
10271200	RC340B 42S/940 PSD W60L60 VPC PCS ELP3	Safety class I	34 W	Yes

FlexBlend Recessed

Order Code	Full Product Name	Protection class	Power	Suitable for random switching
		IEC	Consumption	
10306100	RC340B 36S/940 PSU W60L60 CPC PCS	Safety class I	25 W	Yes
10307800	RC340B 36S/940 PSD W60L60 CPC PCS	Safety class I	25 W	Yes
10311500	RC340B 42S/940 PSU W60L60 CPC PCS	Safety class I	30 W	Yes
10312200	RC340B 42S/940 PSD W60L60 CPC PCS	Safety class I	30 W	Yes
10327600	RC340B 36S/940 PSU W60L60 VPC PCS	Safety class I	25 W	Yes
10328300	RC340B 36S/940 PSD W60L60 VPC PCS	Safety class I	25 W	Yes
10229300	RC340B 36S/940 PSU W60L60 VPC O	Safety class I	30 W	Yes
10243900	RC342B 36S/940 PSU W62L62 VPC MLO	Safety class I	37 W	Yes
10251400	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	Safety class I	41 W	Yes
10252100	RC340B 36S/940 PSD W60L60 VPC MLO ELP3	Safety class I	41.5 W	Yes
10256900	RC340B 36S/940 PSD W60L60 VPC O ELD3	Safety class I	29 W	Yes
10258300	RC340B 36S/940 PSD W60L60 VPC MLO ELD3	Safety class I	37.5 W	Yes
10262000	RC340B 42S/940 PSD W60L60 VPC MLO	Safety class I	44.5 W	Yes
10272900	RC340B 42S/940 PSD W60L60 VPC MLO ELD3	Safety class I	44.5 W	Yes
10305400	RC340B 42S/940 PSU W60L60 VPC MLO	Safety class I	44 W	Yes
10325200	RC340B 36S/940 PSU W60L60 VPC MLO	Safety class I	37.5 W	Yes
10326900	RC340B 36S/940 PSD W60L60 VPC MLO	Safety class I	37 W	Yes

Controls and Dimming

Order Code	Full Product Name	Embedded	
		Dimmable	control
10277400	RC340B 36S/940 PSU W15L120 VPC MLO	No	-
10278100	RC340B 36S/940 PSD W15L120 VPC MLO	Yes	-
10279800	RC340B 42S/940 PSU W15L120 VPC MLO	No	-
10280400	RC340B 42S/940 PSD W15L120 VPC MLO	Yes	-
10281100	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	No	-

Order Code	Full Product Name	Protection class	Power	Suitable for random switching
		IEC	Consumption	
10233000	RC340B 36S/940 POE W60L60 VPC MLO	Safety class I	37 W	Yes
10276700	RC340B 42S/940 PSD W60L60 VPC PCS ELD3	Safety class I	29.5 W	Yes
10481500	RC340B 36S/940 POE W60L60 VPC MLO U0	Safety class III	37 W	Yes (relates to presence/ movement detection and daylight harvesting)
10484600	RC340B 36S/940 POE W60L60 VPC PCS U0	Safety class III	25 W	Yes (relates to presence/ movement detection and daylight harvesting)
10231600	RC340B 36S/940 PSU W60L60 VPC MLO	Safety class I	37.5 W	Yes
10241500	RC340B 36S/940 PSD W60L60 PCV MLO	Safety class I	37 W	Yes
10244600	RC342B 36S/940 PSD W62L62 VPC MLO	Safety class I	37 W	Yes
10406800	RC342B 28S/940 PSD W62L62 VPC MLO	Safety class I	28 W	Yes
10419800	RC342B 28S/940 PSD W62L62 VPC PCS	Safety class I	20 W	Yes
10420400	RC342B 36S/940 PSD W62L62 VPC PCS	Safety class I	25 W	Yes
10421100	RC342B 42S/940 PSD W62L62 VPC PCS	Safety class I	30 W	Yes
10435800	RC342B 28S/940 PSD W62L62 VPC O	Safety class I	22.5 W	Yes
10436500	RC342B 36S/940 PSD W62L62 VPC O	Safety class I	29 W	Yes
10437200	RC342B 42S/940 PSD W62L62 VPC O	Safety class I	33.5 W	Yes

Order Code	Full Product Name	Embedded	
		Dimmable	control
10282800	RC340B 36S/940 PSD W15L120 VPC MLO ELP3	Yes	-
10283500	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	No	-
10284200	RC340B 42S/940 PSD W15L120 VPC MLO ELP3	Yes	-

FlexBlend Recessed

Order Code	Full Product Name	Embedded	
		Dimmable	control
10286600	RC340B 36S/940 PSD W15L120 VPC MLO ELD3	Yes	-
10288000	RC340B 42S/940 PSD W15L120 VPC MLO EL	Yes	-
10410500	RC342B 28S/940 PSD W15L125 VPC MLO	Yes	-
10411200	RC342B 36S/940 PSD W15L125 VPC MLO	Yes	-
10414300	RC342B 36S/940 PSD W17L125 PCV MLO	Yes	-
10425900	RC342B 28S/940 PSD W15L125 VPC PCS	Yes	-
10426600	RC342B 36S/940 PSD W15L125 VPC PCS	Yes	-
10427300	RC342B 42S/940 PSD W15L125 VPC PCS	Yes	-
10430300	RC342B 36S/940 PSD W17L125 PCV PCS	Yes	-
10441900	RC342B 28S/940 PSD W15L125 VPC O	Yes	-
10442600	RC342B 36S/940 PSD W15L125 VPC O	Yes	-
10443300	RC342B 42S/940 PSD W15L125 VPC O	Yes	-
10242200	RC340B 36S/940 PSD W30L120 VPC MLO	Yes	-
10245300	RC342B 36S/940 PSU W31L125 VPC MLO	No	-
10246000	RC342B 36S/940 PSD W31L125 VPC MLO	Yes	-
10408200	RC342B 28S/940 PSD W31L125 VPC MLO	Yes	-
10422800	RC342B 28S/940 PSD W31L125 VPC PCS	Yes	-
10423500	RC342B 36S/940 PSD W31L125 VPC PCS	Yes	-
10424200	RC342B 42S/940 PSD W31L125 VPC PCS	Yes	-
10438900	RC342B 28S/940 PSD W31L125 VPC O	Yes	-
10439600	RC342B 36S/940 PSD W31L125 VPC O	Yes	-
10440200	RC342B 42S/940 PSD W31L125 VPC O	Yes	-
10249100	RC340B 36S/940 PSU W60L60 VPC O ELP3	No	-
10250700	RC340B 36S/940 PSD W60L60 VPC O ELP3	Yes	-
10263700	RC340B 42S/940 PSU W60L60 VPC O	No	-
10264400	RC340B 42S/940 PSD W60L60 VPC O	Yes	-
10268200	RC340B 42S/940 PSU W60L60 VPC O ELP3	No	-
10269900	RC340B 42S/940 PSD W60L60 VPC O ELP3	Yes	-
10274300	RC340B 42S/940 PSD W60L60 VPC O ELD3	Yes	-
10323800	RC340B 36S/940 PSU W60L60 VPC O SC	No	-
10324500	RC340B 36S/940 PSD W60L60 VPC O SC	Yes	-
10232300	RC340B 36S/940 PSD W60L60 VPC MLO	Yes	-
10308500	RC340B 36S/940 PSU W60L60 CPC MLO	No	-
10309200	RC340B 42S/940 PSU W60L60 CPC MLO	No	-
10310800	RC340B 42S/940 PSD W60L60 CPC MLO	Yes	-
10428000	RC342B 42S/940 PSD W62L62 CPC PCS	Yes	-
10230900	RC340B 36S/940 PSD W60L60 VPC O	Yes	-
10235400	RC340B 36S/940 PSU W60L60 VPC PCS	No	-
10236100	RC340B 36S/940 PSD W60L60 VPC PCS	Yes	-
10240800	RC340B 36S/940 PSD W60L60 CPC MLO	Yes	-
10253800	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	No	-
10254500	RC340B 36S/940 PSD W60L60 VPC PCS ELP	Yes	-
10260600	RC340B 36S/940 PSD W60L60 VPC PCS ELD3	Yes	-

Order Code	Full Product Name	Embedded	
		Dimmable	control
10265100	RC340B 42S/940 PSU W60L60 VPC PCS	No	-
10266800	RC340B 42S/940 PSD W60L60 VPC PCS	Yes	-
10270500	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	No	-
10271200	RC340B 42S/940 PSD W60L60 VPC PCS ELP3	Yes	-
10306100	RC340B 36S/940 PSU W60L60 CPC PCS	No	-
10307800	RC340B 36S/940 PSD W60L60 CPC PCS	Yes	-
10311500	RC340B 42S/940 PSU W60L60 CPC PCS	No	-
10312200	RC340B 42S/940 PSD W60L60 CPC PCS	Yes	-
10327600	RC340B 36S/940 PSU W60L60 VPC PCS	No	-
10328300	RC340B 36S/940 PSD W60L60 VPC PCS	Yes	-
10229300	RC340B 36S/940 PSU W60L60 VPC O	No	-
10243900	RC342B 36S/940 PSU W62L62 VPC MLO	No	-
10251400	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	No	-
10252100	RC340B 36S/940 PSD W60L60 VPC MLO ELP3	Yes	-
10256900	RC340B 36S/940 PSD W60L60 VPC O ELD3	Yes	-
10258300	RC340B 36S/940 PSD W60L60 VPC MLO ELD3	Yes	-
10262000	RC340B 42S/940 PSD W60L60 VPC MLO	Yes	-
10272900	RC340B 42S/940 PSD W60L60 VPC MLO ELD3	Yes	-
10305400	RC340B 42S/940 PSU W60L60 VPC MLO	No	-
10325200	RC340B 36S/940 PSU W60L60 VPC MLO	No	-
10326900	RC340B 36S/940 PSD W60L60 VPC MLO	Yes	-
10233000	RC340B 36S/940 POE W60L60 VPC MLO	Yes	-
10276700	RC340B 42S/940 PSD W60L60 VPC PCS ELD3	Yes	-
10481500	RC340B 36S/940 POE W60L60 VPC MLO UO	Yes	Upgradable sensor slot empty with cover
10484600	RC340B 36S/940 POE W60L60 VPC PCS UO	Yes	Upgradable sensor slot empty with cover
10231600	RC340B 36S/940 PSU W60L60 VPC MLO	No	-
10241500	RC340B 36S/940 PSD W60L60 PCV MLO	Yes	-
10244600	RC342B 36S/940 PSD W62L62 VPC MLO	Yes	-
10406800	RC342B 28S/940 PSD W62L62 VPC MLO	Yes	-
10419800	RC342B 28S/940 PSD W62L62 VPC PCS	Yes	-
10420400	RC342B 36S/940 PSD W62L62 VPC PCS	Yes	-
10421100	RC342B 42S/940 PSD W62L62 VPC PCS	Yes	-
10435800	RC342B 28S/940 PSD W62L62 VPC O	Yes	-
10436500	RC342B 36S/940 PSD W62L62 VPC O	Yes	-
10437200	RC342B 42S/940 PSD W62L62 VPC O	Yes	-

Mechanical and Housing

FlexBlend Recessed

Order Code	Full Product Name	Ingress protection code
10277400	RC340B 36S/940 PSU W15L120 VPC MLO	IP20/40
10278100	RC340B 36S/940 PSD W15L120 VPC MLO	IP20/40
10279800	RC340B 42S/940 PSU W15L120 VPC MLO	IP20/40
10280400	RC340B 42S/940 PSD W15L120 VPC MLO	IP20/40
10281100	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	IP20
10282800	RC340B 36S/940 PSD W15L120 VPC MLO ELP3	IP20
10283500	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	IP20
10284200	RC340B 42S/940 PSD W15L120 VPC MLO ELP3	IP20
10286600	RC340B 36S/940 PSD W15L120 VPC MLO ELD3	IP20
10288000	RC340B 42S/940 PSD W15L120 VPC MLO EL	IP20
10410500	RC342B 28S/940 PSD W15L125 VPC MLO	IP20/40
10411200	RC342B 36S/940 PSD W15L125 VPC MLO	IP20/40
10414300	RC342B 36S/940 PSD W17L125 PCV MLO	IP20/40
10425900	RC342B 28S/940 PSD W15L125 VPC PCS	IP20/54
10426600	RC342B 36S/940 PSD W15L125 VPC PCS	IP20/54
10427300	RC342B 42S/940 PSD W15L125 VPC PCS	IP20/54
10430300	RC342B 36S/940 PSD W17L125 PCV PCS	IP20/54
10441900	RC342B 28S/940 PSD W15L125 VPC O	IP20/54
10442600	RC342B 36S/940 PSD W15L125 VPC O	IP20/54
10443300	RC342B 42S/940 PSD W15L125 VPC O	IP20/54
10242200	RC340B 36S/940 PSD W30L120 VPC MLO	IP20/40
10245300	RC342B 36S/940 PSU W31L125 VPC MLO	IP20/40
10246000	RC342B 36S/940 PSD W31L125 VPC MLO	IP20/40
10408200	RC342B 28S/940 PSD W31L125 VPC MLO	IP20/40
10422800	RC342B 28S/940 PSD W31L125 VPC PCS	IP20/54
10423500	RC342B 36S/940 PSD W31L125 VPC PCS	IP20/54
10424200	RC342B 42S/940 PSD W31L125 VPC PCS	IP20/54
10438900	RC342B 28S/940 PSD W31L125 VPC O	IP20/54
10439600	RC342B 36S/940 PSD W31L125 VPC O	IP20/54
10440200	RC342B 42S/940 PSD W31L125 VPC O	IP20/54
10249100	RC340B 36S/940 PSU W60L60 VPC O ELP3	IP54
10250700	RC340B 36S/940 PSD W60L60 VPC O ELP3	IP54
10263700	RC340B 42S/940 PSU W60L60 VPC O	IP20/54
10264400	RC340B 42S/940 PSD W60L60 VPC O	IP20/54
10268200	RC340B 42S/940 PSU W60L60 VPC O ELP3	IP20/54
10269900	RC340B 42S/940 PSD W60L60 VPC O ELP3	IP20/54
10274300	RC340B 42S/940 PSD W60L60 VPC O ELD3	IP54
10323800	RC340B 36S/940 PSU W60L60 VPC O SC	IP20/54
10324500	RC340B 36S/940 PSD W60L60 VPC O SC	IP20/54
10232300	RC340B 36S/940 PSD W60L60 VPC MLO	IP20/40
10308500	RC340B 36S/940 PSU W60L60 CPC MLO	IP20/40
10309200	RC340B 42S/940 PSU W60L60 CPC MLO	IP20/40
10310800	RC340B 42S/940 PSD W60L60 CPC MLO	IP20/40

Order Code	Full Product Name	Ingress protection code
10428000	RC342B 42S/940 PSD W62L62 CPC PCS	IP20/54
10230900	RC340B 36S/940 PSD W60L60 VPC O	IP20/54
10235400	RC340B 36S/940 PSU W60L60 VPC PCS	IP20/54
10236100	RC340B 36S/940 PSD W60L60 VPC PCS	IP20/54
10240800	RC340B 36S/940 PSD W60L60 CPC MLO	IP20/40
10253800	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	IP20/54
10254500	RC340B 36S/940 PSD W60L60 VPC PCS ELP	IP20/54
10260600	RC340B 36S/940 PSD W60L60 VPC PCS ELD3	IP20/54
10265100	RC340B 42S/940 PSU W60L60 VPC PCS	IP20/54
10266800	RC340B 42S/940 PSD W60L60 VPC PCS	IP20/54
10270500	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	IP20/54
10271200	RC340B 42S/940 PSD W60L60 VPC PCS ELP3	IP20/54
10306100	RC340B 36S/940 PSU W60L60 CPC PCS	IP20/54
10307800	RC340B 36S/940 PSD W60L60 CPC PCS	IP20/54
10311500	RC340B 42S/940 PSU W60L60 CPC PCS	IP20/54
10312200	RC340B 42S/940 PSD W60L60 CPC PCS	IP20/54
10327600	RC340B 36S/940 PSU W60L60 VPC PCS	IP20/54
10328300	RC340B 36S/940 PSD W60L60 VPC PCS	IP20/54
10229300	RC340B 36S/940 PSU W60L60 VPC O	IP20/54
10243900	RC342B 36S/940 PSU W62L62 VPC MLO	IP20/40
10251400	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	IP20
10252100	RC340B 36S/940 PSD W60L60 VPC MLO ELP3	IP20/54
10256900	RC340B 36S/940 PSD W60L60 VPC O ELD3	IP54
10258300	RC340B 36S/940 PSD W60L60 VPC MLO ELD3	IP20/54
10262000	RC340B 42S/940 PSD W60L60 VPC MLO	IP20/40
10272900	RC340B 42S/940 PSD W60L60 VPC MLO ELD3	IP20
10305400	RC340B 42S/940 PSU W60L60 VPC MLO	IP20/40
10325200	RC340B 36S/940 PSU W60L60 VPC MLO	IP20/40
10326900	RC340B 36S/940 PSD W60L60 VPC MLO	IP20/40
10233000	RC340B 36S/940 POE W60L60 VPC MLO	IP20/40
10276700	RC340B 42S/940 PSD W60L60 VPC PCS ELD3	IP20/54
10481500	RC340B 36S/940 POE W60L60 VPC MLO U0	IP20
10484600	RC340B 36S/940 POE W60L60 VPC PCS U0	IP20/54
10231600	RC340B 36S/940 PSU W60L60 VPC MLO	IP20/40
10241500	RC340B 36S/940 PSD W60L60 PCV MLO	IP20/40
10244600	RC342B 36S/940 PSD W62L62 VPC MLO	IP20/40
10406800	RC342B 28S/940 PSD W62L62 VPC MLO	IP20/40
10419800	RC342B 28S/940 PSD W62L62 VPC PCS	IP20/54
10420400	RC342B 36S/940 PSD W62L62 VPC PCS	IP20/54
10421100	RC342B 42S/940 PSD W62L62 VPC PCS	IP20/54
10435800	RC342B 28S/940 PSD W62L62 VPC O	IP20/54
10436500	RC342B 36S/940 PSD W62L62 VPC O	IP20/54
10437200	RC342B 42S/940 PSD W62L62 VPC O	IP20/54

Emergency Operation

FlexBlend Recessed

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
10277400	RC340B 36S/940 PSU W15L120 VPC MLO	-	-
10278100	RC340B 36S/940 PSD W15L120 VPC MLO	-	-
10279800	RC340B 42S/940 PSU W15L120 VPC MLO	-	-
10280400	RC340B 42S/940 PSD W15L120 VPC MLO	-	-
10281100	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
10282800	RC340B 36S/940 PSD W15L120 VPC MLO ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
10283500	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
10284200	RC340B 42S/940 PSD W15L120 VPC MLO ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
10286600	RC340B 36S/940 PSD W15L120 VPC MLO ELD3	Emergency lighting 3 hours duration Pro version	3 hour(s)
10288000	RC340B 42S/940 PSD W15L120 VPC MLO EL	Emergency lighting 3 hours duration Pro version	3 hour(s)
10410500	RC342B 28S/940 PSD W15L125 VPC MLO	-	-
10411200	RC342B 36S/940 PSD W15L125 VPC MLO	-	-
10414300	RC342B 36S/940 PSD W17L125 PCV MLO	-	-
10425900	RC342B 28S/940 PSD W15L125 VPC PCS	-	-
10426600	RC342B 36S/940 PSD W15L125 VPC PCS	-	-
10427300	RC342B 42S/940 PSD W15L125 VPC PCS	-	-
10430300	RC342B 36S/940 PSD W17L125 PCV PCS	-	-
10441900	RC342B 28S/940 PSD W15L125 VPC O	-	-
10442600	RC342B 36S/940 PSD W15L125 VPC O	-	-
10443300	RC342B 42S/940 PSD W15L125 VPC O	-	-
10242200	RC340B 36S/940 PSD W30L120 VPC MLO	-	-

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
10245300	RC342B 36S/940 PSU W31L125 VPC MLO	-	-
10246000	RC342B 36S/940 PSD W31L125 VPC MLO	-	-
10408200	RC342B 28S/940 PSD W31L125 VPC MLO	-	-
10422800	RC342B 28S/940 PSD W31L125 VPC PCS	-	-
10423500	RC342B 36S/940 PSD W31L125 VPC PCS	-	-
10424200	RC342B 42S/940 PSD W31L125 VPC PCS	-	-
10438900	RC342B 28S/940 PSD W31L125 VPC O	-	-
10439600	RC342B 36S/940 PSD W31L125 VPC O	-	-
10440200	RC342B 42S/940 PSD W31L125 VPC O	-	-
10249100	RC340B 36S/940 PSU W60L60 VPC O ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
10250700	RC340B 36S/940 PSD W60L60 VPC O ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
10263700	RC340B 42S/940 PSU W60L60 VPC O	-	-
10264400	RC340B 42S/940 PSD W60L60 VPC O	-	-
10268200	RC340B 42S/940 PSU W60L60 VPC O ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
10269900	RC340B 42S/940 PSD W60L60 VPC O ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
10274300	RC340B 42S/940 PSD W60L60 VPC O ELD3	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
10323800	RC340B 36S/940 PSU W60L60 VPC O SC	-	-
10324500	RC340B 36S/940 PSD W60L60 VPC O SC	-	-
10232300	RC340B 36S/940 PSD W60L60 VPC MLO	-	-
10308500	RC340B 36S/940 PSU W60L60 CPC MLO	-	-
10309200	RC340B 42S/940 PSU W60L60 CPC MLO	-	-

FlexBlend Recessed

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
10310800	RC340B 42S/940 PSD W60L60 CPC MLO	-	-
10428000	RC342B 42S/940 PSD W62L62 CPC PCS	-	-
10230900	RC340B 36S/940 PSD W60L60 VPC O	-	-
10235400	RC340B 36S/940 PSU W60L60 VPC PCS	-	-
10236100	RC340B 36S/940 PSD W60L60 VPC PCS	-	-
10240800	RC340B 36S/940 PSD W60L60 CPC MLO	-	-
10253800	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
10254500	RC340B 36S/940 PSD W60L60 VPC PCS ELP	Emergency lighting 3 hours duration Pro version	3 hour(s)
10260600	RC340B 36S/940 PSD W60L60 VPC PCS ELD3	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
10265100	RC340B 42S/940 PSU W60L60 VPC PCS	-	-
10266800	RC340B 42S/940 PSD W60L60 VPC PCS	-	-
10270500	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
10271200	RC340B 42S/940 PSD W60L60 VPC PCS ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
10306100	RC340B 36S/940 PSU W60L60 CPC PCS	-	-
10307800	RC340B 36S/940 PSD W60L60 CPC PCS	-	-
10311500	RC340B 42S/940 PSU W60L60 CPC PCS	-	-
10312200	RC340B 42S/940 PSD W60L60 CPC PCS	-	-
10327600	RC340B 36S/940 PSU W60L60 VPC PCS	-	-
10328300	RC340B 36S/940 PSD W60L60 VPC PCS	-	-
10229300	RC340B 36S/940 PSU W60L60 VPC O	-	-
10243900	RC342B 36S/940 PSU W62L62 VPC MLO	-	-
10251400	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
10252100	RC340B 36S/940 PSD W60L60 VPC MLO ELP3	Emergency lighting 3 hours duration Pro version	3 hour(s)
10256900	RC340B 36S/940 PSD W60L60 VPC O ELD3	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
10258300	RC340B 36S/940 PSD W60L60 VPC MLO ELD3	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
10262000	RC340B 42S/940 PSD W60L60 VPC MLO	-	-
10272900	RC340B 42S/940 PSD W60L60 VPC MLO ELD3	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
10305400	RC340B 42S/940 PSU W60L60 VPC MLO	-	-
10325200	RC340B 36S/940 PSU W60L60 VPC MLO	-	-
10326900	RC340B 36S/940 PSD W60L60 VPC MLO	-	-
10233000	RC340B 36S/940 POE W60L60 VPC MLO	-	-
10276700	RC340B 42S/940 PSD W60L60 VPC PCS ELD3	Emergency lighting 3 hours duration with DALI interface	3 hour(s)
10481500	RC340B 36S/940 POE W60L60 VPC MLO U0	-	-
10484600	RC340B 36S/940 POE W60L60 VPC PCS U0	-	-
10231600	RC340B 36S/940 PSU W60L60 VPC MLO	-	-
10241500	RC340B 36S/940 PSD W60L60 PCV MLO	-	-
10244600	RC342B 36S/940 PSD W62L62 VPC MLO	-	-
10406800	RC342B 28S/940 PSD W62L62 VPC MLO	-	-
10419800	RC342B 28S/940 PSD W62L62 VPC PCS	-	-
10420400	RC342B 36S/940 PSD W62L62 VPC PCS	-	-
10421100	RC342B 42S/940 PSD W62L62 VPC PCS	-	-
10435800	RC342B 28S/940 PSD W62L62 VPC O	-	-
10436500	RC342B 36S/940 PSD W62L62 VPC O	-	-

FlexBlend Recessed

Order Code	Full Product Name	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
10437200	RC342B 42S/940 PSD W62L62 VPC O	-	-

Approval and Application

Order Code	Full Product Name	Glow-wire test
10277400	RC340B 36S/940 PSU W15L120 VPC MLO	Temperature 650 °C, duration 30 s
10278100	RC340B 36S/940 PSD W15L120 VPC MLO	Temperature 650 °C, duration 30 s
10279800	RC340B 42S/940 PSU W15L120 VPC MLO	Temperature 650 °C, duration 30 s
10280400	RC340B 42S/940 PSD W15L120 VPC MLO	Temperature 650 °C, duration 30 s
10281100	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s
10282800	RC340B 36S/940 PSD W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s
10283500	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s
10284200	RC340B 42S/940 PSD W15L120 VPC MLO ELP3	Temperature 650 °C, duration 30 s
10286600	RC340B 36S/940 PSD W15L120 VPC MLO ELD3	Temperature 650 °C, duration 30 s
10288000	RC340B 42S/940 PSD W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s
10410500	RC342B 28S/940 PSD W15L125 VPC MLO	Temperature 650 °C, duration 30 s
10411200	RC342B 36S/940 PSD W15L125 VPC MLO	Temperature 650 °C, duration 30 s
10414300	RC342B 36S/940 PSD W17L125 PCV MLO	Temperature 650 °C, duration 30 s
10425900	RC342B 28S/940 PSD W15L125 VPC PCS	Temperature 850 °C, duration 30 s
10426600	RC342B 36S/940 PSD W15L125 VPC PCS	Temperature 850 °C, duration 30 s
10427300	RC342B 42S/940 PSD W15L125 VPC PCS	Temperature 850 °C, duration 30 s
10430300	RC342B 36S/940 PSD W17L125 PCV PCS	Temperature 850 °C, duration 30 s
10441900	RC342B 28S/940 PSD W15L125 VPC O	Temperature 850 °C, duration 30 s
10442600	RC342B 36S/940 PSD W15L125 VPC O	Temperature 850 °C, duration 30 s
10443300	RC342B 42S/940 PSD W15L125 VPC O	Temperature 850 °C, duration 30 s
10242200	RC340B 36S/940 PSD W30L120 VPC MLO	Temperature 650 °C, duration 30 s
10245300	RC342B 36S/940 PSU W31L125 VPC MLO	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
10246000	RC342B 36S/940 PSD W31L125 VPC MLO	Temperature 650 °C, duration 30 s
10408200	RC342B 28S/940 PSD W31L125 VPC MLO	Temperature 650 °C, duration 30 s
10422800	RC342B 28S/940 PSD W31L125 VPC PCS	Temperature 850 °C, duration 30 s
10423500	RC342B 36S/940 PSD W31L125 VPC PCS	Temperature 850 °C, duration 30 s
10424200	RC342B 42S/940 PSD W31L125 VPC PCS	Temperature 850 °C, duration 30 s
10438900	RC342B 28S/940 PSD W31L125 VPC O	Temperature 850 °C, duration 30 s
10439600	RC342B 36S/940 PSD W31L125 VPC O	Temperature 850 °C, duration 30 s
10440200	RC342B 42S/940 PSD W31L125 VPC O	Temperature 850 °C, duration 30 s
10249100	RC340B 36S/940 PSU W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s
10250700	RC340B 36S/940 PSD W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s
10263700	RC340B 42S/940 PSU W60L60 VPC O	Temperature 850 °C, duration 30 s
10264400	RC340B 42S/940 PSD W60L60 VPC O	Temperature 850 °C, duration 30 s
10268200	RC340B 42S/940 PSU W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s
10269900	RC340B 42S/940 PSD W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s
10274300	RC340B 42S/940 PSD W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s
10323800	RC340B 36S/940 PSU W60L60 VPC O SC	Temperature 850 °C, duration 30 s
10324500	RC340B 36S/940 PSD W60L60 VPC O SC	Temperature 850 °C, duration 30 s
10232300	RC340B 36S/940 PSD W60L60 VPC MLO	Temperature 650 °C, duration 30 s
10308500	RC340B 36S/940 PSU W60L60 CPC MLO	Temperature 650 °C, duration 30 s
10309200	RC340B 42S/940 PSU W60L60 CPC MLO	Temperature 650 °C, duration 30 s
10310800	RC340B 42S/940 PSD W60L60 CPC MLO	Temperature 650 °C, duration 30 s
10428000	RC342B 42S/940 PSD W62L62 CPC PCS	Temperature 850 °C, duration 30 s
10230900	RC340B 36S/940 PSD W60L60 VPC O	Temperature 850 °C, duration 30 s
10235400	RC340B 36S/940 PSU W60L60 VPC PCS	Temperature 850 °C, duration 30 s

FlexBlend Recessed

Order Code	Full Product Name	Glow-wire test
10236100	RC340B 36S/940 PSD W60L60 VPC PCS	Temperature 850 °C, duration 30 s
10240800	RC340B 36S/940 PSD W60L60 CPC MLO	Temperature 650 °C, duration 30 s
10253800	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s
10254500	RC340B 36S/940 PSD W60L60 VPC PCS ELP	Temperature 850 °C, duration 30 s
10260600	RC340B 36S/940 PSD W60L60 VPC PCS ELD3	Temperature 850 °C, duration 30 s
10265100	RC340B 42S/940 PSU W60L60 VPC PCS	Temperature 850 °C, duration 30 s
10266800	RC340B 42S/940 PSD W60L60 VPC PCS	Temperature 850 °C, duration 30 s
10270500	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s
10271200	RC340B 42S/940 PSD W60L60 VPC PCS ELP3	Temperature 850 °C, duration 30 s
10306100	RC340B 36S/940 PSU W60L60 CPC PCS	Temperature 850 °C, duration 30 s
10307800	RC340B 36S/940 PSD W60L60 CPC PCS	Temperature 850 °C, duration 30 s
10311500	RC340B 42S/940 PSU W60L60 CPC PCS	Temperature 850 °C, duration 30 s
10312200	RC340B 42S/940 PSD W60L60 CPC PCS	Temperature 850 °C, duration 30 s
10327600	RC340B 36S/940 PSU W60L60 VPC PCS	Temperature 850 °C, duration 30 s
10328300	RC340B 36S/940 PSD W60L60 VPC PCS	Temperature 850 °C, duration 30 s
10229300	RC340B 36S/940 PSU W60L60 VPC O	Temperature 850 °C, duration 30 s
10243900	RC342B 36S/940 PSU W62L62 VPC MLO	Temperature 650 °C, duration 30 s
10251400	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	Temperature 650 °C, duration 30 s
10252100	RC340B 36S/940 PSD W60L60 VPC MLO ELP3	Temperature 650 °C, duration 30 s
10256900	RC340B 36S/940 PSD W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s

Order Code	Full Product Name	Glow-wire test
10258300	RC340B 36S/940 PSD W60L60 VPC MLO ELD3	Temperature 650 °C, duration 30 s
10262000	RC340B 42S/940 PSD W60L60 VPC MLO	Temperature 650 °C, duration 30 s
10272900	RC340B 42S/940 PSD W60L60 VPC MLO ELD3	Temperature 650 °C, duration 30 s
10305400	RC340B 42S/940 PSU W60L60 VPC MLO	Temperature 650 °C, duration 30 s
10325200	RC340B 36S/940 PSU W60L60 VPC MLO	Temperature 650 °C, duration 30 s
10326900	RC340B 36S/940 PSD W60L60 VPC MLO	Temperature 650 °C, duration 30 s
10233000	RC340B 36S/940 POE W60L60 VPC MLO	Temperature 650 °C, duration 30 s
10276700	RC340B 42S/940 PSD W60L60 VPC PCS ELD3	Temperature 850 °C, duration 30 s
10481500	RC340B 36S/940 POE W60L60 VPC MLO U0	Temperature 650 °C, duration 30 s
10484600	RC340B 36S/940 POE W60L60 VPC PCS U0	Temperature 850 °C, duration 30 s
10231600	RC340B 36S/940 PSU W60L60 VPC MLO	Temperature 650 °C, duration 30 s
10241500	RC340B 36S/940 PSD W60L60 PCV MLO	Temperature 650 °C, duration 30 s
10244600	RC342B 36S/940 PSD W62L62 VPC MLO	Temperature 650 °C, duration 30 s
10406800	RC342B 28S/940 PSD W62L62 VPC MLO	Temperature 650 °C, duration 30 s
10419800	RC342B 28S/940 PSD W62L62 VPC PCS	Temperature 850 °C, duration 30 s
10420400	RC342B 36S/940 PSD W62L62 VPC PCS	Temperature 850 °C, duration 30 s
10421100	RC342B 42S/940 PSD W62L62 VPC PCS	Temperature 850 °C, duration 30 s
10435800	RC342B 28S/940 PSD W62L62 VPC O	Temperature 850 °C, duration 30 s
10436500	RC342B 36S/940 PSD W62L62 VPC O	Temperature 850 °C, duration 30 s
10437200	RC342B 42S/940 PSD W62L62 VPC O	Temperature 850 °C, duration 30 s

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
10277400	RC340B 36S/940 PSU W15L120 VPC MLO	0.01 %
10278100	RC340B 36S/940 PSD W15L120 VPC MLO	0.01 %
10279800	RC340B 42S/940 PSU W15L120 VPC MLO	0.01 %
10280400	RC340B 42S/940 PSD W15L120 VPC MLO	0.01 %
10281100	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	0.01 %
10282800	RC340B 36S/940 PSD W15L120 VPC MLO ELP3	0.01 %
10283500	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	0.01 %
10284200	RC340B 42S/940 PSD W15L120 VPC MLO ELP3	0.01 %

Order Code	Full Product Name	Driver failure rate at 5000 h
10286600	RC340B 36S/940 PSD W15L120 VPC MLO ELD3	0.01 %
10288000	RC340B 42S/940 PSD W15L120 VPC MLO EL	0.01 %
10410500	RC342B 28S/940 PSD W15L125 VPC MLO	-
10411200	RC342B 36S/940 PSD W15L125 VPC MLO	-
10414300	RC342B 36S/940 PSD W17L125 PCV MLO	-
10425900	RC342B 28S/940 PSD W15L125 VPC PCS	-
10426600	RC342B 36S/940 PSD W15L125 VPC PCS	-
10427300	RC342B 42S/940 PSD W15L125 VPC PCS	-

FlexBlend Recessed

Order Code	Full Product Name	Driver failure rate at 5000 h
10430300	RC342B 36S/940 PSD W17L125 PCV PCS	-
10441900	RC342B 28S/940 PSD W15L125 VPC O	-
10442600	RC342B 36S/940 PSD W15L125 VPC O	-
10443300	RC342B 42S/940 PSD W15L125 VPC O	-
10242200	RC340B 36S/940 PSD W30L120 VPC MLO	0.01 %
10245300	RC342B 36S/940 PSU W31L125 VPC MLO	0.01 %
10246000	RC342B 36S/940 PSD W31L125 VPC MLO	0.01 %
10408200	RC342B 28S/940 PSD W31L125 VPC MLO	-
10422800	RC342B 28S/940 PSD W31L125 VPC PCS	-
10423500	RC342B 36S/940 PSD W31L125 VPC PCS	-
10424200	RC342B 42S/940 PSD W31L125 VPC PCS	-
10438900	RC342B 28S/940 PSD W31L125 VPC O	-
10439600	RC342B 36S/940 PSD W31L125 VPC O	-
10440200	RC342B 42S/940 PSD W31L125 VPC O	-
10249100	RC340B 36S/940 PSU W60L60 VPC O ELP3	0.01 %
10250700	RC340B 36S/940 PSD W60L60 VPC O ELP3	0.01 %
10263700	RC340B 42S/940 PSU W60L60 VPC O	0.01 %
10264400	RC340B 42S/940 PSD W60L60 VPC O	0.01 %
10268200	RC340B 42S/940 PSU W60L60 VPC O ELP3	0.01 %
10269900	RC340B 42S/940 PSD W60L60 VPC O ELP3	0.01 %
10274300	RC340B 42S/940 PSD W60L60 VPC O ELD3	0.01 %
10323800	RC340B 36S/940 PSU W60L60 VPC O SC	0.01 %
10324500	RC340B 36S/940 PSD W60L60 VPC O SC	0.01 %
10232300	RC340B 36S/940 PSD W60L60 VPC MLO	0.01 %
10308500	RC340B 36S/940 PSU W60L60 CPC MLO	0.01 %
10309200	RC340B 42S/940 PSU W60L60 CPC MLO	0.01 %
10310800	RC340B 42S/940 PSD W60L60 CPC MLO	0.01 %
10428000	RC342B 42S/940 PSD W62L62 CPC PCS	-
10230900	RC340B 36S/940 PSD W60L60 VPC O	0.01 %
10235400	RC340B 36S/940 PSU W60L60 VPC PCS	0.01 %
10236100	RC340B 36S/940 PSD W60L60 VPC PCS	0.01 %
10240800	RC340B 36S/940 PSD W60L60 CPC MLO	0.01 %
10253800	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	0.01 %
10254500	RC340B 36S/940 PSD W60L60 VPC PCS ELP	0.01 %
10260600	RC340B 36S/940 PSD W60L60 VPC PCS ELD3	0.01 %

Order Code	Full Product Name	Driver failure rate at 5000 h
10265100	RC340B 42S/940 PSU W60L60 VPC PCS	0.01 %
10266800	RC340B 42S/940 PSD W60L60 VPC PCS	0.01 %
10270500	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	0.01 %
10271200	RC340B 42S/940 PSD W60L60 VPC PCS ELP3	0.01 %
10306100	RC340B 36S/940 PSU W60L60 CPC PCS	0.01 %
10307800	RC340B 36S/940 PSD W60L60 CPC PCS	0.01 %
10311500	RC340B 42S/940 PSU W60L60 CPC PCS	0.01 %
10312200	RC340B 42S/940 PSD W60L60 CPC PCS	0.01 %
10327600	RC340B 36S/940 PSU W60L60 VPC PCS	0.01 %
10328300	RC340B 36S/940 PSD W60L60 VPC PCS	0.01 %
10229300	RC340B 36S/940 PSU W60L60 VPC O	0.01 %
10243900	RC342B 36S/940 PSU W62L62 VPC MLO	0.01 %
10251400	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	0.01 %
10252100	RC340B 36S/940 PSD W60L60 VPC MLO ELP3	0.01 %
10256900	RC340B 36S/940 PSD W60L60 VPC O ELD3	0.01 %
10258300	RC340B 36S/940 PSD W60L60 VPC MLO ELD3	0.01 %
10262000	RC340B 42S/940 PSD W60L60 VPC MLO	0.01 %
10272900	RC340B 42S/940 PSD W60L60 VPC MLO ELD3	0.01 %
10305400	RC340B 42S/940 PSU W60L60 VPC MLO	0.01 %
10325200	RC340B 36S/940 PSU W60L60 VPC MLO	0.01 %
10326900	RC340B 36S/940 PSD W60L60 VPC MLO	0.01 %
10233000	RC340B 36S/940 POE W60L60 VPC MLO	0.01 %
10276700	RC340B 42S/940 PSD W60L60 VPC PCS ELD3	0.01 %
10481500	RC340B 36S/940 POE W60L60 VPC MLO U0	-
10484600	RC340B 36S/940 POE W60L60 VPC PCS U0	-
10231600	RC340B 36S/940 PSU W60L60 VPC MLO	0.01 %
10241500	RC340B 36S/940 PSD W60L60 PCV MLO	0.01 %
10244600	RC342B 36S/940 PSD W62L62 VPC MLO	0.01 %
10406800	RC342B 28S/940 PSD W62L62 VPC MLO	-
10419800	RC342B 28S/940 PSD W62L62 VPC PCS	-
10420400	RC342B 36S/940 PSD W62L62 VPC PCS	-
10421100	RC342B 42S/940 PSD W62L62 VPC PCS	-
10435800	RC342B 28S/940 PSD W62L62 VPC O	-
10436500	RC342B 36S/940 PSD W62L62 VPC O	-
10437200	RC342B 42S/940 PSD W62L62 VPC O	-

Product Data

Order Code	Full Product Name	Product family code
10277400	RC340B 36S/940 PSU W15L120 VPC MLO	RC340B
10278100	RC340B 36S/940 PSD W15L120 VPC MLO	RC340B
10279800	RC340B 42S/940 PSU W15L120 VPC MLO	RC340B
10280400	RC340B 42S/940 PSD W15L120 VPC MLO	RC340B
10281100	RC340B 36S/940 PSU W15L120 VPC MLO ELP3	RC340B
10282800	RC340B 36S/940 PSD W15L120 VPC MLO ELP3	RC340B
10283500	RC340B 42S/940 PSU W15L120 VPC MLO ELP3	RC340B
10284200	RC340B 42S/940 PSD W15L120 VPC MLO ELP3	RC340B
10286600	RC340B 36S/940 PSD W15L120 VPC MLO ELD3	RC340B
10288000	RC340B 42S/940 PSD W15L120 VPC MLO EL	RC340B
10410500	RC342B 28S/940 PSD W15L125 VPC MLO	RC342B
10411200	RC342B 36S/940 PSD W15L125 VPC MLO	RC342B


Order Code	Full Product Name	Product family code
10414300	RC342B 36S/940 PSD W17L125 PCV MLO	RC342B
10425900	RC342B 28S/940 PSD W15L125 VPC PCS	RC342B
10426600	RC342B 36S/940 PSD W15L125 VPC PCS	RC342B
10427300	RC342B 42S/940 PSD W15L125 VPC PCS	RC342B
10430300	RC342B 36S/940 PSD W17L125 PCV PCS	RC342B
10441900	RC342B 28S/940 PSD W15L125 VPC O	RC342B
10442600	RC342B 36S/940 PSD W15L125 VPC O	RC342B
10443300	RC342B 42S/940 PSD W15L125 VPC O	RC342B
10242200	RC340B 36S/940 PSD W30L120 VPC MLO	RC340B
10245300	RC342B 36S/940 PSU W31L125 VPC MLO	RC342B
10246000	RC342B 36S/940 PSD W31L125 VPC MLO	RC342B
10408200	RC342B 28S/940 PSD W31L125 VPC MLO	RC342B

FlexBlend Recessed


Order Code	Full Product Name	Product family code
10422800	RC342B 28S/940 PSD W31L125 VPC PCS	RC342B
10423500	RC342B 36S/940 PSD W31L125 VPC PCS	RC342B
10424200	RC342B 42S/940 PSD W31L125 VPC PCS	RC342B
10438900	RC342B 28S/940 PSD W31L125 VPC O	RC342B
10439600	RC342B 36S/940 PSD W31L125 VPC O	RC342B
10440200	RC342B 42S/940 PSD W31L125 VPC O	RC342B
10249100	RC340B 36S/940 PSU W60L60 VPC O ELP3	RC340B
10250700	RC340B 36S/940 PSD W60L60 VPC O ELP3	RC340B
10263700	RC340B 42S/940 PSU W60L60 VPC O	RC340B
10264400	RC340B 42S/940 PSD W60L60 VPC O	RC340B
10268200	RC340B 42S/940 PSU W60L60 VPC O ELP3	RC340B
10269900	RC340B 42S/940 PSD W60L60 VPC O ELP3	RC340B
10274300	RC340B 42S/940 PSD W60L60 VPC O ELD3	RC340B
10323800	RC340B 36S/940 PSU W60L60 VPC O SC	RC340B
10324500	RC340B 36S/940 PSD W60L60 VPC O SC	RC340B
10232300	RC340B 36S/940 PSD W60L60 VPC MLO	RC340B
10308500	RC340B 36S/940 PSU W60L60 CPC MLO	RC340B
10309200	RC340B 42S/940 PSU W60L60 CPC MLO	RC340B
10310800	RC340B 42S/940 PSD W60L60 CPC MLO	RC340B
10428000	RC342B 42S/940 PSD W62L62 CPC PCS	RC342B
10230900	RC340B 36S/940 PSD W60L60 VPC O	RC340B
10235400	RC340B 36S/940 PSU W60L60 VPC PCS	RC340B
10236100	RC340B 36S/940 PSD W60L60 VPC PCS	RC340B
10240800	RC340B 36S/940 PSD W60L60 CPC MLO	RC340B
10253800	RC340B 36S/940 PSU W60L60 VPC PCS ELP3	RC340B
10254500	RC340B 36S/940 PSD W60L60 VPC PCS ELP	RC340B
10260600	RC340B 36S/940 PSD W60L60 VPC PCS ELD3	RC340B
10265100	RC340B 42S/940 PSU W60L60 VPC PCS	RC340B
10266800	RC340B 42S/940 PSD W60L60 VPC PCS	RC340B
10270500	RC340B 42S/940 PSU W60L60 VPC PCS ELP3	RC340B
10271200	RC340B 42S/940 PSD W60L60 VPC PCS ELP3	RC340B

Order Code	Full Product Name	Product family code
10306100	RC340B 36S/940 PSU W60L60 CPC PCS	RC340B
10307800	RC340B 36S/940 PSD W60L60 CPC PCS	RC340B
10311500	RC340B 42S/940 PSU W60L60 CPC PCS	RC340B
10312200	RC340B 42S/940 PSD W60L60 CPC PCS	RC340B
10327600	RC340B 36S/940 PSU W60L60 VPC PCS	RC340B
10328300	RC340B 36S/940 PSD W60L60 VPC PCS	RC340B
10229300	RC340B 36S/940 PSU W60L60 VPC O	RC340B
10243900	RC342B 36S/940 PSU W62L62 VPC MLO	RC342B
10251400	RC340B 36S/940 PSU W60L60 VPC MLO ELP3	RC340B
10252100	RC340B 36S/940 PSD W60L60 VPC MLO ELP3	RC340B
10256900	RC340B 36S/940 PSD W60L60 VPC O ELD3	RC340B
10258300	RC340B 36S/940 PSD W60L60 VPC MLO ELD3	RC340B
10262000	RC340B 42S/940 PSD W60L60 VPC MLO	RC340B
10272900	RC340B 42S/940 PSD W60L60 VPC MLO ELD3	RC340B
10305400	RC340B 42S/940 PSU W60L60 VPC MLO	RC340B
10325200	RC340B 36S/940 PSU W60L60 VPC MLO	RC340B
10326900	RC340B 36S/940 PSD W60L60 VPC MLO	RC340B
10233000	RC340B 36S/940 POE W60L60 VPC MLO	RC340B
10276700	RC340B 42S/940 PSD W60L60 VPC PCS ELD3	RC340B
10481500	RC340B 36S/940 POE W60L60 VPC MLO UO	RC340B
10484600	RC340B 36S/940 POE W60L60 VPC PCS UO	RC340B
10231600	RC340B 36S/940 PSU W60L60 VPC MLO	RC340B
10241500	RC340B 36S/940 PSD W60L60 PCV MLO	RC340B
10244600	RC342B 36S/940 PSD W62L62 VPC MLO	RC342B
10406800	RC342B 28S/940 PSD W62L62 VPC MLO	RC342B
10419800	RC342B 28S/940 PSD W62L62 VPC PCS	RC342B
10420400	RC342B 36S/940 PSD W62L62 VPC PCS	RC342B
10421100	RC342B 42S/940 PSD W62L62 VPC PCS	RC342B
10435800	RC342B 28S/940 PSD W62L62 VPC O	RC342B
10436500	RC342B 36S/940 PSD W62L62 VPC O	RC342B
10437200	RC342B 42S/940 PSD W62L62 VPC O	RC342B


Polar Wide Diagrams



Polar Normal (separate) - RC340BI - 910925866978




Polar Normal (separate) - RC340BI - 910925866978




Polar Normal (separate) - RC340BI - 910925866978


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925866969




Polar Normal (separate) - RC340BI - 910925866968




Polar Normal (separate) - RC340BI - 910925866970




Polar Normal (separate) - RC340BI - 910925866979




Polar Normal (separate) - RC340BI - 910925866981




Polar Normal (separate) - RC340BI - 910925867050



Polar Normal (separate) - RC340BI - 910925866973




Polar Normal (separate) - RC340BI - 910925866991




Polar Normal (separate) - RC340BI - 910925866993


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867002




Polar Normal (separate) - RC340BI - 910925867003




**Polar Normal (separate) - RC340BI -
910925866977**




Polar Normal (separate) - RC340BI - 910925866995




Polar Normal (separate) - RC340BI - 910925867012




Polar Normal (separate) - RC340BI - 910925867017



Polar Normal (separate) - RC340BI - 910925867019




**Polar Normal (separate) - RC340BI -
910925867024**




Polar Normal (separate) - RC340BI - 910925867043


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867049




Polar Normal (separate) - RC340BI - 910925866967




Polar Normal (separate) - RC340BI - 910925867010




**Polar Normal (separate) - RC340BI -
910925867022**




Polar Normal (separate) - RC340BI - 910925867064




Polar Normal (separate) - RC340BI - 910925866980



Polar Normal (separate) - RC340BI - 910925866982




Polar Normal (separate) - RC340BI - 910925866983




Polar Normal (separate) - RC340BI - 910925866988


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925866997




Polar Normal (separate) - RC340BI - 910925867006




Polar Normal (separate) - RC340BI - 910925867009




Polar Normal (separate) - RC340BI - 910925867047




Polar Normal (separate) - RC340BI - 910925867062




Polar Normal (separate) - RC340BI - 910925867063



Polar Normal (separate) - RC340BI - 910925866966




Polar Normal (separate) - RC340BI - 910925867008




Polar Normal (separate) - RC340BI - 910925867018


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867016




Polar Normal (separate) - RC340BI - 910925867021




Polar Normal (separate) - RC340BI - 910925867014




Polar Normal (separate) - RC340BI - 910925867145




Polar Normal (separate) - RC340BI - 910925867147




Polar Normal (separate) - RC340BI - 910925867020



Polar Normal (separate) - RC340BI - 910925867026




Polar Normal (separate) - RC340BI - 910925867044




Polar Normal (separate) - RC340BI - 910925867045


Polar Wide Diagrams




Polar Normal (separate) - RC340BI - 910925867048




Polar Normal (separate) - RC340BI - 910925867065




Polar Normal (separate) - RC340BI - 910925867149




Polar Normal (separate) - RC340BI - 910925867159




Polar Normal (separate) - RC340BI - 910925867158




Polar Normal (separate) - RC340BI - 910925867165




Polar Normal (separate) - RC340BI - 910925867166




Polar Normal (separate) - RC340BI - 910925867167




Polar Normal (separate) - RC340BI - 910925867177



Polar Normal (separate) - RC340BI - 910925867178	Polar Normal (separate) - RC340BI - 910925867221	Polar Normal (separate) - RC340BI - 910925867066
---	---	---




Polar Normal (separate) - RC340BI - 910925867162	Polar Normal (separate) - RC340BI - 910925867160	Polar Normal (separate) - RC340BI - 910925867153
---	---	---




Polar Normal (separate) - RC340BI - 910925867175	Polar Normal (separate) - RC340BI - 910925867179	Polar Normal (separate) - RC340BI - 910925867182
--	--	--


Polar Wide Diagrams




**Polar Normal (separate) - RC340BI -
910925867163**




**Polar Normal (separate) - RC340BI -
910925867174**




Polar Normal (separate) - RC340BI - 910925867176




Polar Normal (separate) - RC340BI - 910925866972




Polar Normal (separate) - RC340BI - 910925866986




Polar Normal (separate) - RC340BI - 910925866990



**Polar Normal (separate) - RC340BI -
910925866999**




**Polar Normal (separate) - RC340BI -
910925867001**




Polar Normal (separate) - RC340BI - 910925867004


Polar Wide Diagrams




**Polar Normal (separate) - RC340BI -
910925867007**




Polar Normal (separate) - RC340BI - 910925867015




Polar Normal (separate) - RC340BI - 910925867046




**Polar Normal (separate) - RC340BI -
910925867061**




**Polar Normal (separate) - RC340BI -
910925867150**




Polar Normal (separate) - RC340BI - 910925867161



**Polar Normal (separate) - RC340BI -
910925867164**




Polar Normal (separate) - RC340BI - 910925867169




Polar Normal (separate) - RC340BI - 910925867181

Polar Wide Diagrams



**Polar Normal (separate) - RC340BI -
910925867180**



**Polar Normal (separate) - RC340BI -
910925867224**

