



RCS750 3-circuit square track system – flexible and multifunctional

3-circuit square RCS750

The RCS750 3-circuit square track system is made up of a solid aluminium track available in lengths of 1, 2, 3 and 4 m with four electrical conductors. Any given configuration can be created easily: horizontal or vertical, mounted on or in the ceiling, on the wall or on free-standing panels. The system can also be used as a floating structure. All luminaires have a separate power supply and can be switched selectively. They can be moved easily to change the lighting and presentation. In this way, a multifunctional track system can be created for accent lighting as well as for suspending advertising and decorative material. A range of adaptors, power supply connections and mounting accessories is also available.

Benefits

- Flexible 3-circuit track system for the professional user, allowing any required configuration to be created relatively easily
- All luminaires have separate power switching so they can easily be moved, for example to create changing atmospheres in shop windows or interiors
- Can be applied as a 'floating' structure using the suspension tubes and clamps provided

Features

- Can be used with all Philips LED 3C track spots
- Available in lengths of 1, 2, 3 and 4 m
- Available in three finishes – white, black, aluminum
- Range of adaptors, power supply connections and mounting accessories available

3-circuit square RCS750

Application

- Retail
- Indoor architectural lighting

Versions



ZRS750 CPF BK (XTS23-2)



ZRS750 CPS BK (XTS14-2)



ZRS750 TCPR WH (XTS36-3)



ZRS750 CCPE BK (XTS35-2)



RBS750 recessed track, white



ZRS750 CPF WH (XTS23-3)



ZRS750 EPSR BK (XTS11-2+41-2)



ZRS750 EPSL BK (XTS12-2+41-2)



ZRS750 CPS WH (XTS14-3)



ZRS750 CCPI WH (XTS34-3)



ZRS750 CPX WH (XTS38-3)



ZRS750 EP BK (XTS41-2)

3-circuit square RCS750

Versions



ZRS750 EP WH (XTS41-3)



ZRS750 ICP WH (XTS21-3)



ZRS750 TCPL WH (XTS39-3)



ZRS750 CS WH (XTSP11-3)



ZRS750 ACP WH (XTS24-3)



ZRS750 3C BA WH (GA70-3)



ZRS750 CCPE WH (XTS35-3)



ZRS750 EPSL WH (XTS12-3+41-3)



ZRS750 TCPR BK (XTS36-2)




ZCS750 5C6 CPF BK (XTSC623-2)




ZRS750 ICP BK (XTS21-2)

Dimensional drawing




3-circuit square RCS750

Dimensional drawing



3-circuit square RCS750

Dimensional drawing



3-circuit square RCS750

Dimensional drawing

Product details



Coupling piece with suspension set



Power supply connector end left



Fish plate connection



Flexible coupling/corner piece



External earth coupling/corner piece outer 90°



End piece

3-circuit square RCS750

Approval and Application

CE mark	Yes
CE mark	Yes

Operating and Electrical

Order Code	Full Product Name	Protection class IEC	Protection class IEC	Input Voltage	Input Voltage
79855499	ZRS750 CPF BK (XTS23-2)	-	-	250 V	250 V
14155899	ZRS750 CPS BK (XTS14-2)	-	-	250 V	250 V
38130599	ZRS750 TCPR WH (XTS36-3)	-	-	-	-
14152799	ZRS750 CCPE BK (XTS35-2)	-	-	-	-
14153499	ZRS750 CCPI BK (XTS34-2)	-	-	-	-
14980600	RBS750 3C L2000 WH (XTSF4200-3)	Safety class I	Safety class I	-	-
14982000	RBS750 3C L3000 WH (XTSF4300-3)	Safety class I	Safety class I	-	-
38120699	ZRS750 CPF WH (XTS23-3)	-	-	-	-
14149799	ZRS750 EPSR BK (XTS11-2+41-2)	-	-	250 V	250 V
38110700	RCS750 3C L1000 WH (XTS4100-3)	Safety class I	Safety class I	-	-
38111400	RCS750 3C L2000 WH (XTS4200-3)	Safety class I	Safety class I	-	-
38112100	RCS750 3C L3000 WH (XTS4300-3)	Safety class I	Safety class I	-	-
38113800	RCS750 3C L4000 WH (XTS4400-3)	Safety class I	Safety class I	-	-
14148099	ZRS750 EPSL BK (XTS12-2+41-2)	-	-	250 V	250 V
38122099	ZRS750 CPS WH (XTS14-3)	-	-	250 V	250 V
38126899	ZRS750 CCPI WH (XTS34-3)	-	-	-	-
38134399	ZRS750 CPX WH (XTS38-3)	-	-	-	-
14150399	ZRS750 EP BK (XTS41-2)	-	-	-	-
38124499	ZRS750 EP WH (XTS41-3)	-	-	-	-
Order Code	Full Product Name	Protection class IEC	Protection class IEC	Input Voltage	Input Voltage
38106000	RCS750 3C L1000 ALU (XTS4100-1)	Safety class I	Safety class I	-	-
38107700	RCS750 3C L2000 ALU (XTS4200-1)	Safety class I	Safety class I	-	-
38108400	RCS750 3C L3000 ALU (XTS4300-1)	Safety class I	Safety class I	-	-
38109100	RCS750 3C L4000 ALU (XTS4400-1)	Safety class I	Safety class I	-	-
38118399	ZRS750 ICP WH (XTS21-3)	-	-	-	-
38132999	ZRS750 TCPL WH (XTS39-3)	-	-	-	-
14984499	ZRS750 CS WH (XTSP11-3)	-	-	-	-
38136799	ZRS750 ACP WH (XTS24-3)	-	-	-	-
14715499	ZRS750 3C BA WH (GA70-3)	-	-	250 V	250 V
38128299	ZRS750 CCPE WH (XTS35-3)	-	-	-	-
38116999	ZRS750 EPSL WH (XTS12-3+41-3)	-	-	250 V	250 V
14154199	ZRS750 TCPR BK (XTS36-2)	-	-	-	-
79851600	RCS750 3C L1000 BK (XTS4100-2)	Safety class I	Safety class I	-	-
79852300	RCS750 3C L2000 BK (XTS4200-2)	Safety class I	Safety class I	-	-
79853000	RCS750 3C L3000 BK (XTS4300-2)	Safety class I	Safety class I	-	-
79854700	RCS750 3C L4000 BK (XTS4400-2)	Safety class I	Safety class I	-	-
06744499	ZCS750 5C6 CPF BK (XTSC623-2)	-	-	-	-
14151099	ZRS750 ICP BK (XTS21-2)	-	-	250 V	250 V

Mechanical and Housing

3-circuit square RCS750

Order Code	Full Product Name	Accessory colour	Ingress protection code	Ingress protection code
79855499	ZRS750 CPF BK (XTS23-2)	Black	-	-
14155899	ZRS750 CPS BK (XTS14-2)	Black	-	-
38130599	ZRS750 TCPR WH (XTS36-3)	White	-	-
14152799	ZRS750 CCPE BK (XTS35-2)	Black	-	-
14153499	ZRS750 CCPI BK (XTS34-2)	Black	-	-
14980600	RBS750 3C L2000 WH (XTSF4200-3)	White	IP30	IP30
14982000	RBS750 3C L3000 WH (XTSF4300-3)	White	IP30	IP30
38120699	ZRS750 CPF WH (XTS23-3)	White	-	-
14149799	ZRS750 EPSR BK (XTS11-2+41-2)	Black	-	-
38110700	RCS750 3C L1000 WH (XTS4100-3)	White	IP30	IP30
38111400	RCS750 3C L2000 WH (XTS4200-3)	White	IP30	IP30
38112100	RCS750 3C L3000 WH (XTS4300-3)	White	IP30	IP30
38113800	RCS750 3C L4000 WH (XTS4400-3)	White	IP30	IP30
14148099	ZRS750 EPSL BK (XTS12-2+41-2)	Black	-	-
38122099	ZRS750 CPS WH (XTS14-3)	White	-	-
38126899	ZRS750 CCPI WH (XTS34-3)	White	-	-
38134399	ZRS750 CPX WH (XTS38-3)	White	-	-
14150399	ZRS750 EP BK (XTS41-2)	Black	-	-
38124499	ZRS750 EP WH (XTS41-3)	White	-	-
38106000	RCS750 3C L1000 ALU (XTS4100-1)	Aluminium	IP30	IP30

Approval and Application

Order Code	Full Product Name	Glow-wire test	Glow-wire test
79855499	ZRS750 CPF BK (XTS23-2)	-	-
14155899	ZRS750 CPS BK (XTS14-2)	-	-
38130599	ZRS750 TCPR WH (XTS36-3)	-	-
14152799	ZRS750 CCPE BK (XTS35-2)	-	-
14153499	ZRS750 CCPI BK (XTS34-2)	-	-
14980600	RBS750 3C L2000 WH (XTSF4200-3)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
14982000	RBS750 3C L3000 WH (XTSF4300-3)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
38120699	ZRS750 CPF WH (XTS23-3)	-	-
14149799	ZRS750 EPSR BK (XTS11-2+41-2)	-	-
38110700	RCS750 3C L1000 WH (XTS4100-3)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
38111400	RCS750 3C L2000 WH (XTS4200-3)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s

Order Code	Full Product Name	Accessory colour	Ingress protection code	Ingress protection code
38107700	RCS750 3C L2000 ALU (XTS4200-1)	Aluminium	IP30	IP30
38108400	RCS750 3C L3000 ALU (XTS4300-1)	Aluminium	IP30	IP30
38109100	RCS750 3C L4000 ALU (XTS4400-1)	Aluminium	IP30	IP30
38118399	ZRS750 ICP WH (XTS21-3)	White	-	-
38132999	ZRS750 TCPL WH (XTS39-3)	White	-	-
14984499	ZRS750 CS WH (XTSP11-3)	White	-	-
38136799	ZRS750 ACP WH (XTS24-3)	White	-	-
14715499	ZRS750 3C BA WH (GA70-3)	White	-	-
38128299	ZRS750 CCPE WH (XTS35-3)	White	-	-
38116999	ZRS750 EPSL WH (XTS12-3+41-3)	White	-	-
14154199	ZRS750 TCPR BK (XTS36-2)	Black	-	-
79851600	RCS750 3C L1000 BK (XTS4100-2)	Black	IP30	IP30
79852300	RCS750 3C L2000 BK (XTS4200-2)	Black	IP30	IP30
79853000	RCS750 3C L3000 BK (XTS4300-2)	Black	IP30	IP30
79854700	RCS750 3C L4000 BK (XTS4400-2)	Black	IP30	IP30
06744499	ZCS750 5C6 CPF BK (XTSC623-2)	Black	-	-
14151099	ZRS750 ICP BK (XTS21-2)	Black	-	-

Order Code	Full Product Name	Glow-wire test	Glow-wire test
38112100	RCS750 3C L3000 WH (XTS4300-3)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
38113800	RCS750 3C L4000 WH (XTS4400-3)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
14148099	ZRS750 EPSL BK (XTS12-2+41-2)	-	-
38122099	ZRS750 CPS WH (XTS14-3)	-	-
38126899	ZRS750 CCPI WH (XTS34-3)	-	-
38134399	ZRS750 CPX WH (XTS38-3)	-	-
14150399	ZRS750 EP BK (XTS41-2)	-	-
38124499	ZRS750 EP WH (XTS41-3)	-	-
38106000	RCS750 3C L1000 ALU (XTS4100-1)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
38107700	RCS750 3C L2000 ALU (XTS4200-1)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
38108400	RCS750 3C L3000 ALU (XTS4300-1)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s

3-circuit square RCS750

Order Code	Full Product Name	Glow-wire test	Glow-wire test
38109100	RCS750 3C L4000 ALU (XTS4400-1)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
38118399	ZRS750 ICP WH (XTS21-3)	-	-
38132999	ZRS750 TCPL WH (XTS39-3)	-	-
14984499	ZRS750 CS WH (XTSP11-3)	-	-
38136799	ZRS750 ACP WH (XTS24-3)	-	-
14715499	ZRS750 3C BA WH (GA70-3)	-	-
38128299	ZRS750 CCPE WH (XTS35-3)	-	-
38116999	ZRS750 EPSL WH (XTS12-3+41-3)	-	-
14154199	ZRS750 TCPR BK (XTS36-2)	-	-

Order Code	Full Product Name	Glow-wire test	Glow-wire test
79851600	RCS750 3C L1000 BK (XTS4100-2)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
79852300	RCS750 3C L2000 BK (XTS4200-2)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
79853000	RCS750 3C L3000 BK (XTS4300-2)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
79854700	RCS750 3C L4000 BK (XTS4400-2)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
06744499	ZCS750 5C6 CPF BK (XTSC623-2)	-	-
14151099	ZRS750 ICP BK (XTS21-2)	-	-

