



Flexible & Affordable - Tailored for retail and hospitality

GreenSpace Accent Elbow GCGM

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Accent Elbow is a product family with full choices in terms of optic choices, lumen diversities, control availability and wide range of tiltable angles, tailored for retail and hospitality applications.

Benefits

- Comprehensive offerings to meet various application requirements.
- Comfort lighting environment with good color quality.
- Ensured quality and reliability.

Features

- Multiple options of lumen output, wattage and optics.
- Full control availability including on/off, 1-10v, triac and DALI.
- Tiltable & rotatable
- CRI 90 & SDCM≤3

Application

- Retail
- Hospitality
- Fashion


GreenSpace Accent Elbow GCGM

Versions



GreenUp Accent Elbow

Dimensional drawing



Light Technical	
Color rendering index (CRI)	>90
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	200 to 240 V
Line Frequency	50 to 60 Hz
Mechanical and Housing	
Optical cover type	Acrylate
Housing Color	White
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	No
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

		Correlated Color	Luminous Efficacy	Luminous Flux
Order Code	Full Product Name	Temperature (Nom)	(rated) (Nom)	
911401508212	RS305B P12 940 PSD-E WB	4000 K	86 lm/W	1,030 lm
911401563502	RS305B P6 930 PSU-E VWB	3000 K	91 lm/W	590 lm
911401564102	RS305B P6 940 PSU-E MB	4000 K	100 lm/W	650 lm
911401575302	RS305B P6 930 PSD-E MB	3000 K	93 lm/W	610 lm
911401580202	RS305B P9 940 PSU-E WB	4000 K	98 lm/W	880 lm
911401580302	RS305B P9 940 PSU-E VWB	4000 K	96 lm/W	860 lm
911401596102	RS305B P12 940 PSU-E MB	4000 K	86 lm/W	1,030 lm
911401596202	RS305B P12 940 PSU-E WB	4000 K	86 lm/W	1,030 lm

Operating and Electrical

GreenSpace Accent Elbow GCGM

Order Code	Full Product Name	Power Consumption
911401508212	RS305B P12 940 PSD-E WB	10.8 W
911401563502	RS305B P6 930 PSU-E VWB	5.4 W
911401564102	RS305B P6 940 PSU-E MB	5.4 W
911401575302	RS305B P6 930 PSD-E MB	5.4 W

Order Code	Full Product Name	Power Consumption
911401580202	RS305B P9 940 PSU-E WB	8.1 W
911401580302	RS305B P9 940 PSU-E VWB	8.1 W
911401596102	RS305B P12 940 PSU-E MB	10.8 W
911401596202	RS305B P12 940 PSU-E WB	10.8 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401508212	RS305B P12 940 PSD-E WB	Yes
911401563502	RS305B P6 930 PSU-E VWB	No
911401564102	RS305B P6 940 PSU-E MB	No
911401575302	RS305B P6 930 PSD-E MB	Yes

Order Code	Full Product Name	Dimmable
911401580202	RS305B P9 940 PSU-E WB	No
911401580302	RS305B P9 940 PSU-E VWB	No
911401596102	RS305B P12 940 PSU-E MB	No
911401596202	RS305B P12 940 PSU-E WB	No

