



Flexible & Affordable - Tailored for retail and hospitality

GreenSpace Accent Elbow GCGM

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Accent Elbow is a product family with full choices in terms of optic choices, lumen diversities, control availability and wide range of tiltable angles, tailored for retail and hospitality applications.

Benefits

- Comprehensive offerings to meet various application requirements.
- Comfort lighting environment with good color quality.
- Ensured quality and reliability.

Features


- Multiple options of lumen output, wattage and optics.
- Full control availability including on/off, 1-10v, triac and DALI.
- Tiltable & rotatable
- CRI 90 & SDCM≤3

Application

- Retail
- Hospitality
- Fashion

GreenSpace Accent Elbow GCGM

Dimensional drawing



Light Technical

Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>90

Operating and Electrical

Protection class IEC	Safety class II
Input Voltage	200 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	8.1 W

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Optical cover type	Acrylate
Housing Color	White
Mech. impact protection code	IK03
Ingress protection code	IP20

Approval and Application

Ambient temperature range	-20 to +40 °C
CE mark	No

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401580202	RS305B P9 940 PSU-E WB	98 lm/W	880 lm
911401580302	RS305B P9 940 PSU-E VWB	96 lm/W	860 lm

