



# GreenSpace Flex Luna – Bringing moonlight inside.

## GreenSpace Flex Luna

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

### Benefits

- Sustainable, more light with less energy consumption, up to 120lm/W.
- Silent brilliance with superior visual comfort.
- Deliver light that speaks luxury, supported by superior color consistency and beam control.
- Comprehensive family offering, maintain effortlessly with ceiling proof design.


### Features

- Leading lm/W, up to 120lm/W on luminaire level.
- 40° cut off angle and UGR19 for major variants.
- Leading color performance, with CRI92, R9>50.
- Super color consistency, SDCM 3 on luminaire level and SDCM 2 on COB level.
- Modular design concept, supporting strong customization and flexibility on family level, covering cut out(D35 to D100), optics (12° to 55°), controls (PSU, PSD, 1-10V, WIA) and customized reflector and front ring color options.

### Application

- Hospitality
- Retail
- Offices
- General indoor space

Dimensional drawing



| Operating and Electrical            |                 |
|-------------------------------------|-----------------|
| Protection class IEC                | Safety class II |
| Input Voltage                       | 220 to 240 V    |
| Line Frequency                      | 50 or 60 Hz     |
|                                     |                 |
| Mechanical and Housing              |                 |
| Optical cover type                  | Lens            |
| Housing Color                       | Black           |
| Mech. impact protection code        | IK03            |
|                                     |                 |
| Approval and Application            |                 |
| Ambient temperature range           | -20 to +45 °C   |
|                                     |                 |
| Initial Performance (IEC Compliant) |                 |
| Luminous flux tolerance             | -10% / +10%     |

Light Technical

| Order Code   | Full Product Name                          | Correlated Color | Color       | Luminous         |          |
|--------------|--------------------------------------------|------------------|-------------|------------------|----------|
|              |                                            | Temperature      | rendering   | Efficacy (rated) | Luminous |
| (Nom)        |                                            | (Nom)            | index (CRI) | (Nom)            | Flux     |
| 911401521646 | SM378B R P8 927 PSU-E NB<br>D100 G-TT PRO  | 2700 K           | 92          | 120 lm/W         | 935 lm   |
| 911401521746 | SM378B R P8 930 PSU-E NB<br>D100 G-TT PRO  | 3000 K           | 92          | 125 lm/W         | 975 lm   |
| 911401521846 | SM378B R P8 940 PSU-E NB<br>D100 G-TT PRO  | 4000 K           | 92          | 128 lm/W         | 995 lm   |
| 911401521946 | SM378B R P8 927 PSU-E MB<br>D100 G-TT PRO  | 2700 K           | 92          | 118 lm/W         | 920 lm   |
| 911401522046 | SM378B R P8 930 PSU-E MB<br>D100 G-TT PRO  | 3000 K           | 92          | 123 lm/W         | 960 lm   |
| 911401522146 | SM378B R P8 940 PSU-E MB<br>D100 G-TT PRO  | 4000 K           | 92          | 126 lm/W         | 980 lm   |
| 911401522246 | SM378B R P8 927 PSU-E WB<br>D100 G-TT PRO  | 2700 K           | 92          | 113 lm/W         | 885 lm   |
| 911401522346 | SM378B R P8 930 PSU-E WB<br>D100 G-TT PRO  | 3000 K           | 92          | 119 lm/W         | 925 lm   |
| 911401522446 | SM378B R P8 940 PSU-E WB<br>D100 G-TT PRO  | 4000 K           | 92          | 121 lm/W         | 945 lm   |
| 911401522546 | SM378B R P11 927 PSU-E NB<br>D100 G-TT PRO | 2700 K           | 92          | 117 lm/W         | 1,340 lm |
| 911401522646 | SM378B R P11 930 PSU-E NB<br>D100 G-TT PRO | 3000 K           | 92          | 120 lm/W         | 1,380 lm |
| 911401522746 | SM378B R P11 940 PSU-E NB<br>D100 G-TT PRO | 4000 K           | 92          | 122 lm/W         | 1,400 lm |
| 911401522846 | SM378B R P11 927 PSU-E MB<br>D100 G-TT PRO | 2700 K           | 92          | 115 lm/W         | 1,325 lm |
| 911401522946 | SM378B R P11 930 PSU-E MB<br>D100 G-TT PRO | 3000 K           | 92          | 119 lm/W         | 1,365 lm |
| 911401523046 | SM378B R P11 940 PSU-E MB<br>D100 G-TT PRO | 4000 K           | 92          | 120 lm/W         | 1,385 lm |
| 911401523146 | SM378B R P11 927 PSU-E WB<br>D100 G-TT PRO | 2700 K           | 92          | 110 lm/W         | 1,270 lm |
| 911401523246 | SM378B R P11 930 PSU-E WB<br>D100 G-TT PRO | 3000 K           | 92          | 114 lm/W         | 1,310 lm |
| 911401523346 | SM378B R P11 940 PSU-E WB<br>D100 G-TT PRO | 4000 K           | 92          | 116 lm/W         | 1,330 lm |
| 911401523446 | SM378B R P13 927 PSU-E NB<br>D100 G-TT PRO | 2700 K           | 92          | 114 lm/W         | 1,540 lm |
| 911401523546 | SM378B R P13 930 PSU-E NB<br>D100 G-TT PRO | 3000 K           | 92          | 117 lm/W         | 1,580 lm |
| 911401523646 | SM378B R P13 940 PSU-E NB<br>D100 G-TT PRO | 4000 K           | 92          | 119 lm/W         | 1,600 lm |
| 911401523746 | SM378B R P13 927 PSU-E MB<br>D100 G-TT PRO | 2700 K           | 92          | 113 lm/W         | 1,520 lm |
| 911401523846 | SM378B R P13 930 PSU-E MB<br>D100 G-TT PRO | 3000 K           | 92          | 116 lm/W         | 1,560 lm |
| 911401523946 | SM378B R P13 940 PSU-E MB<br>D100 G-TT PRO | 4000 K           | 92          | 117 lm/W         | 1,580 lm |

| Order Code   | Full Product Name                       | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|-----------------------------------------|------------------------------------|-----------------------------|---------------------------------|---------------|
| 911401524046 | SM378B R P13 927 PSU-E WB D100 G-TT PRO | 2700 K                             | 92                          | 108 lm/W                        | 1,460 lm      |
| 911401524146 | SM378B R P13 930 PSU-E WB D100 G-TT PRO | 3000 K                             | 92                          | 111 lm/W                        | 1,500 lm      |
| 911401524246 | SM378B R P13 940 PSU-E WB D100 G-TT PRO | 4000 K                             | 92                          | 113 lm/W                        | 1,520 lm      |
| 911401524346 | SM378B R P20 927 PSU-E NB D100 G-TT PRO | 2700 K                             | 92                          | 107 lm/W                        | 2,140 lm      |
| 911401524446 | SM378B R P20 930 PSU-E NB D100 G-TT PRO | 3000 K                             | 92                          | 109 lm/W                        | 2,180 lm      |
| 911401524546 | SM378B R P20 940 PSU-E NB D100 G-TT PRO | 4000 K                             | 92                          | 110 lm/W                        | 2,200 lm      |
| 911401524646 | SM378B R P20 927 PSU-E MB D100 G-TT PRO | 2700 K                             | 92                          | 106 lm/W                        | 2,110 lm      |
| 911401524746 | SM378B R P20 930 PSU-E MB D100 G-TT PRO | 3000 K                             | 92                          | 108 lm/W                        | 2,150 lm      |
| 911401524846 | SM378B R P20 940 PSU-E MB D100 G-TT PRO | 4000 K                             | 92                          | 109 lm/W                        | 2,170 lm      |
| 911401524946 | SM378B R P20 927 PSU-E WB D100 G-TT PRO | 2700 K                             | 92                          | 102 lm/W                        | 2,040 lm      |
| 911401525046 | SM378B R P20 930 PSU-E WB D100 G-TT PRO | 3000 K                             | 92                          | 104 lm/W                        | 2,080 lm      |
| 911401525146 | SM378B R P20 940 PSU-E WB D100 G-TT PRO | 4000 K                             | 92                          | 105 lm/W                        | 2,100 lm      |
| 911401525246 | SM378B R P20 927 PSD-E NB D100 G-TT PRO | 2700 K                             | 92                          | 104 lm/W                        | 2,140 lm      |
| 911401525346 | SM378B R P20 930 PSD-E NB D100 G-TT PRO | 3000 K                             | 92                          | 106 lm/W                        | 2,180 lm      |
| 911401525446 | SM378B R P20 940 PSD-E NB D100 G-TT PRO | 4000 K                             | 92                          | 107 lm/W                        | 2,200 lm      |
| 911401525546 | SM378B R P20 927 PSD-E MB D100 G-TT PRO | 2700 K                             | 92                          | 103 lm/W                        | 2,110 lm      |
| 911401525646 | SM378B R P20 930 PSD-E MB D100 G-TT PRO | 3000 K                             | 92                          | 105 lm/W                        | 2,150 lm      |
| 911401525746 | SM378B R P20 940 PSD-E MB D100 G-TT PRO | 4000 K                             | 92                          | 106 lm/W                        | 2,170 lm      |
| 911401525846 | SM378B R P20 927 PSD-E WB D100 G-TT PRO | 2700 K                             | 92                          | 100 lm/W                        | 2,040 lm      |
| 911401525946 | SM378B R P20 930 PSD-E WB D100 G-TT PRO | 3000 K                             | 92                          | 101 lm/W                        | 2,080 lm      |
| 911401526046 | SM378B R P20 940 PSD-E WB D100 G-TT PRO | 4000 K                             | 92                          | 102 lm/W                        | 2,100 lm      |
| 911401526146 | SM378B R P8 927 PSD-E NB D100 G-TT PRO  | 2700 K                             | 92                          | 104 lm/W                        | 935 lm        |
| 911401526246 | SM378B R P8 930 PSD-E NB D100 G-TT PRO  | 3000 K                             | 92                          | 108 lm/W                        | 975 lm        |
| 911401526346 | SM378B R P8 940 PSD-E NB D100 G-TT PRO  | 4000 K                             | 92                          | 111 lm/W                        | 995 lm        |
| 911401526446 | SM378B R P8 927 PSD-E MB D100 G-TT PRO  | 2700 K                             | 92                          | 102 lm/W                        | 920 lm        |

| Order Code   | Full Product Name                          | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|--------------------------------------------|------------------------------------|-----------------------------|---------------------------------|---------------|
| 911401526546 | SM378B R P8 930 PSD-E MB<br>D100 G-TT PRO  | 3000 K                             | 92                          | 107 lm/W                        | 960 lm        |
| 911401526646 | SM378B R P8 940 PSD-E MB<br>D100 G-TT PRO  | 4000 K                             | 92                          | 109 lm/W                        | 980 lm        |
| 911401526746 | SM378B R P8 927 PSD-E WB<br>D100 G-TT PRO  | 2700 K                             | 92                          | 98 lm/W                         | 885 lm        |
| 911401526846 | SM378B R P8 930 PSD-E WB<br>D100 G-TT PRO  | 3000 K                             | 92                          | 103 lm/W                        | 925 lm        |
| 911401526946 | SM378B R P8 940 PSD-E WB<br>D100 G-TT PRO  | 4000 K                             | 92                          | 105 lm/W                        | 945 lm        |
| 911401527046 | SM378B R P12 927 PSD-E NB<br>D100 G-TT PRO | 2700 K                             | 92                          | 103 lm/W                        | 1,340 lm      |
| 911401527146 | SM378B R P12 930 PSD-E NB<br>D100 G-TT PRO | 3000 K                             | 92                          | 106 lm/W                        | 1,380 lm      |
| 911401527246 | SM378B R P12 940 PSD-E NB<br>D100 G-TT PRO | 4000 K                             | 92                          | 108 lm/W                        | 1,400 lm      |
| 911401527346 | SM378B R P12 927 PSD-E MB<br>D100 G-TT PRO | 2700 K                             | 92                          | 102 lm/W                        | 1,325 lm      |
| 911401527446 | SM378B R P12 930 PSD-E MB<br>D100 G-TT PRO | 3000 K                             | 92                          | 105 lm/W                        | 1,365 lm      |
| 911401527546 | SM378B R P12 940 PSD-E MB<br>D100 G-TT PRO | 4000 K                             | 92                          | 107 lm/W                        | 1,385 lm      |
| 911401527646 | SM378B R P12 927 PSD-E WB<br>D100 G-TT PRO | 2700 K                             | 92                          | 98 lm/W                         | 1,270 lm      |
| 911401527746 | SM378B R P12 930 PSD-E WB<br>D100 G-TT PRO | 3000 K                             | 92                          | 101 lm/W                        | 1,310 lm      |
| 911401527846 | SM378B R P12 940 PSD-E WB<br>D100 G-TT PRO | 4000 K                             | 92                          | 102 lm/W                        | 1,330 lm      |
| 911401527946 | SM378B R P14 927 PSD-E NB<br>D100 G-TT PRO | 2700 K                             | 92                          | 106 lm/W                        | 1,540 lm      |
| 911401528046 | SM378B R P14 930 PSD-E NB<br>D100 G-TT PRO | 3000 K                             | 92                          | 109 lm/W                        | 1,580 lm      |
| 911401528146 | SM378B R P14 940 PSD-E NB<br>D100 G-TT PRO | 4000 K                             | 92                          | 110 lm/W                        | 1,600 lm      |
| 911401528246 | SM378B R P14 927 PSD-E MB<br>D100 G-TT PRO | 2700 K                             | 92                          | 105 lm/W                        | 1,520 lm      |
| 911401528346 | SM378B R P14 930 PSD-E MB<br>D100 G-TT PRO | 3000 K                             | 92                          | 108 lm/W                        | 1,560 lm      |
| 911401528446 | SM378B R P14 940 PSD-E MB<br>D100 G-TT PRO | 4000 K                             | 92                          | 109 lm/W                        | 1,580 lm      |
| 911401528546 | SM378B R P14 927 PSD-E WB<br>D100 G-TT PRO | 2700 K                             | 92                          | 101 lm/W                        | 1,460 lm      |
| 911401528646 | SM378B R P14 930 PSD-E WB<br>D100 G-TT PRO | 3000 K                             | 92                          | 103 lm/W                        | 1,500 lm      |
| 911401528746 | SM378B R P14 940 PSD-E WB<br>D100 G-TT PRO | 4000 K                             | 92                          | 105 lm/W                        | 1,520 lm      |
| 911401528846 | SM378X R P8 930 WIA MB<br>D100 G-TT PRO    | 3000 K                             | 92                          | 117 lm/W                        | 960 lm        |
| 911401528946 | SM378X R P8 930 WIA WB<br>D100 G-TT PRO    | 3000 K                             | 92                          | 113 lm/W                        | 925 lm        |

| Order Code   | Full Product Name                        | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|------------------------------------------|------------------------------------|-----------------------------|---------------------------------|---------------|
| 911401529046 | SM378X R P12 930 WIA MB<br>D100 G-TT PRO | 3000 K                             | 92                          | 114 lm/W                        | 1,365 lm      |
| 911401529146 | SM378X R P12 930 WIA WB<br>D100 G-TT PRO | 3000 K                             | 92                          | 109 lm/W                        | 1,310 lm      |
| 911401529246 | SM378X R P14 930 WIA MB<br>D100 G-TT PRO | 3000 K                             | 92                          | 111 lm/W                        | 1,560 lm      |
| 911401529346 | SM378X R P14 930 WIA WB<br>D100 G-TT PRO | 3000 K                             | 92                          | 107 lm/W                        | 1,500 lm      |
| 911401529446 | SM378X R P20 930 WIA MB<br>D100 G-TT PRO | 3000 K                             | 92                          | 108 lm/W                        | 2,150 lm      |
| 911401529546 | SM378X R P20 930 WIA WB<br>D100 G-TT PRO | 3000 K                             | 92                          | 104 lm/W                        | 2,080 lm      |
| 911401529646 | SM378B R P9 PSD-TNW NB<br>D100 G-TT PRO  | Tunable White                      | 90                          | 86 lm/W                         | 770 lm        |
| 911401529746 | SM378B R P9 PSD-TNW MB<br>D100 G-TT PRO  | Tunable White                      | 90                          | 86 lm/W                         | 770 lm        |
| 911401529846 | SM378B R P9 PSD-TNW WB<br>D100 G-TT PRO  | Tunable White                      | 90                          | 83 lm/W                         | 750 lm        |
| 911401529946 | SM378B R P12 PSD-TNW NB<br>D100 G-TT PRO | Tunable White                      | 90                          | 85 lm/W                         | 1,110 lm      |
| 911401530046 | SM378B R P12 PSD-TNW MB<br>D100 G-TT PRO | Tunable White                      | 90                          | 84 lm/W                         | 1,090 lm      |
| 911401530146 | SM378B R P12 PSD-TNW WB<br>D100 G-TT PRO | Tunable White                      | 90                          | 82 lm/W                         | 1,070 lm      |
| 911401530246 | SM378B R P15 PSD-TNW NB<br>D100 G-TT PRO | Tunable White                      | 90                          | 85 lm/W                         | 1,320 lm      |
| 911401530346 | SM378B R P15 PSD-TNW MB<br>D100 G-TT PRO | Tunable White                      | 90                          | 84 lm/W                         | 1,300 lm      |
| 911401530446 | SM378B R P15 PSD-TNW WB<br>D100 G-TT PRO | Tunable White                      | 90                          | 82 lm/W                         | 1,270 lm      |
| 911401530546 | SM378B R P22 PSD-TNW NB<br>D100 G-TT PRO | Tunable White                      | 90                          | 82 lm/W                         | 1,800 lm      |
| 911401530646 | SM378B R P22 PSD-TNW MB<br>D100 G-TT PRO | Tunable White                      | 90                          | 81 lm/W                         | 1,780 lm      |
| 911401530746 | SM378B R P22 PSD-TNW WB<br>D100 G-TT PRO | Tunable White                      | 90                          | 79 lm/W                         | 1,740 lm      |
| 911401500046 | RS378B P7 930 PSD-E WB<br>M43 PRO        | 3000 K                             | 92                          | 91 lm/W                         | 675 lm        |
| 911401500146 | RS378B P7 940 PSD-E WB<br>M43 PRO        | 4000 K                             | 92                          | 93 lm/W                         | 685 lm        |
| 911401500246 | RS378B P6 930 PSU-E MB<br>M43 WP PRO     | 3000 K                             | 92                          | 92 lm/W                         | 545 lm        |
| 911401500346 | RS378B P6 930 PSU-E WB<br>M43 WP PRO     | 3000 K                             | 92                          | 92 lm/W                         | 545 lm        |
| 911401500446 | RS378B P8 930 PSU-E MB<br>M43 WP PRO     | 3000 K                             | 92                          | 88 lm/W                         | 705 lm        |
| 911401500546 | RS378B P8 930 PSU-E WB<br>M43 WP PRO     | 3000 K                             | 92                          | 88 lm/W                         | 705 lm        |
| 911401520146 | RS378B P7 PSD-TNW NB M43<br>PRO          | Tunable White                      | 90                          | 71 lm/W                         | 530 lm        |

| Order Code   | Full Product Name               | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|---------------------------------|------------------------------------|-----------------------------|---------------------------------|---------------|
| 911401520246 | RS378B P7 PSD-TNW MB M43 PRO    | Tunable White                      | 90                          | 71 lm/W                         | 530 lm        |
| 911401520346 | RS378B P7 PSD-TNW WB M43 PRO    | Tunable White                      | 90                          | 77 lm/W                         | 580 lm        |
| 911401596945 | RS378B P6 927 PSU-E SNB M43 PRO | 2700 K                             | 92                          | 72 lm/W                         | 465 lm        |
| 911401597045 | RS378B P6 930 PSU-E SNB M43 PRO | 3000 K                             | 92                          | 79 lm/W                         | 515 lm        |
| 911401597145 | RS378B P6 940 PSU-E SNB M43 PRO | 4000 K                             | 92                          | 81 lm/W                         | 525 lm        |
| 911401597245 | RS378B P6 927 PSU-E NB M43 PRO  | 2700 K                             | 92                          | 86 lm/W                         | 505 lm        |
| 911401597345 | RS378B P6 930 PSU-E NB M43 PRO  | 3000 K                             | 92                          | 92 lm/W                         | 545 lm        |
| 911401597445 | RS378B P6 940 PSU-E NB M43 PRO  | 4000 K                             | 92                          | 94 lm/W                         | 555 lm        |
| 911401597545 | RS378B P6 927 PSU-E MB M43 PRO  | 2700 K                             | 92                          | 86 lm/W                         | 505 lm        |
| 911401597645 | RS378B P6 930 PSU-E MB M43 PRO  | 3000 K                             | 92                          | 92 lm/W                         | 545 lm        |
| 911401597745 | RS378B P6 940 PSU-E MB M43 PRO  | 4000 K                             | 92                          | 94 lm/W                         | 555 lm        |
| 911401597845 | RS378B P6 927 PSU-E WB M43 PRO  | 2700 K                             | 92                          | 86 lm/W                         | 505 lm        |
| 911401597945 | RS378B P6 930 PSU-E WB M43 PRO  | 3000 K                             | 92                          | 92 lm/W                         | 545 lm        |
| 911401598045 | RS378B P6 940 PSU-E WB M43 PRO  | 4000 K                             | 92                          | 94 lm/W                         | 555 lm        |
| 911401598145 | RS378B P8 927 PSU-E NB M43 PRO  | 2700 K                             | 92                          | 83 lm/W                         | 660 lm        |
| 911401598245 | RS378B P8 930 PSU-E NB M43 PRO  | 3000 K                             | 92                          | 88 lm/W                         | 705 lm        |
| 911401598345 | RS378B P8 940 PSU-E NB M43 PRO  | 4000 K                             | 92                          | 90 lm/W                         | 720 lm        |
| 911401598445 | RS378B P8 927 PSU-E MB M43 PRO  | 2700 K                             | 92                          | 83 lm/W                         | 660 lm        |
| 911401598545 | RS378B P8 930 PSU-E MB M43 PRO  | 3000 K                             | 92                          | 88 lm/W                         | 705 lm        |
| 911401598645 | RS378B P8 940 PSU-E MB M43 PRO  | 4000 K                             | 92                          | 90 lm/W                         | 720 lm        |
| 911401598745 | RS378B P8 927 PSU-E WB M43 PRO  | 2700 K                             | 92                          | 83 lm/W                         | 660 lm        |
| 911401598845 | RS378B P8 930 PSU-E WB M43 PRO  | 3000 K                             | 92                          | 88 lm/W                         | 705 lm        |
| 911401598945 | RS378B P8 940 PSU-E WB M43 PRO  | 4000 K                             | 92                          | 90 lm/W                         | 720 lm        |
| 911401599045 | RS378B P7 927 PSD-E SNB M43 PRO | 2700 K                             | 92                          | 70 lm/W                         | 525 lm        |
| 911401599145 | RS378B P7 930 PSD-E SNB M43 PRO | 3000 K                             | 92                          | 76 lm/W                         | 570 lm        |

| Order Code   | Full Product Name               | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|---------------------------------|------------------------------------|-----------------------------|---------------------------------|---------------|
| 911401599245 | RS378B P7 940 PSD-E SNB M43 PRO | 4000 K                             | 92                          | 79 lm/W                         | 590 lm        |
| 911401599345 | RS378B P7 927 PSD-E NB M43 PRO  | 2700 K                             | 92                          | 84 lm/W                         | 625 lm        |
| 911401599445 | RS378B P7 930 PSD-E NB M43 PRO  | 3000 K                             | 92                          | 91 lm/W                         | 675 lm        |
| 911401599545 | RS378B P7 940 PSD-E NB M43 PRO  | 4000 K                             | 92                          | 93 lm/W                         | 685 lm        |
| 911401599645 | RS378B P7 927 PSD-E MB M43 PRO  | 2700 K                             | 92                          | 84 lm/W                         | 625 lm        |
| 911401599745 | RS378B P7 930 PSD-E MB M43 PRO  | 3000 K                             | 92                          | 91 lm/W                         | 675 lm        |
| 911401599845 | RS378B P7 940 PSD-E MB M43 PRO  | 4000 K                             | 92                          | 93 lm/W                         | 685 lm        |
| 911401599945 | RS378B P7 927 PSD-E WB M43 PRO  | 2700 K                             | 92                          | 84 lm/W                         | 625 lm        |
| 911401500646 | RS378B P7 927 PSU-E SNB M55 PRO | 2700 K                             | 92                          | 83 lm/W                         | 600 lm        |
| 911401500746 | RS378B P7 930 PSU-E SNB M55 PRO | 3000 K                             | 92                          | 92 lm/W                         | 665 lm        |
| 911401500846 | RS378B P7 940 PSU-E SNB M55 PRO | 4000 K                             | 92                          | 94 lm/W                         | 675 lm        |
| 911401500946 | RS378B P7 927 PSU-E NB M55 PRO  | 2700 K                             | 92                          | 94 lm/W                         | 665 lm        |
| 911401501046 | RS378B P7 930 PSU-E NB M55 PRO  | 3000 K                             | 92                          | 103 lm/W                        | 730 lm        |
| 911401501146 | RS378B P7 940 PSU-E NB M55 PRO  | 4000 K                             | 92                          | 104 lm/W                        | 735 lm        |
| 911401501246 | RS378B P7 927 PSU-E MB M55 PRO  | 2700 K                             | 92                          | 101 lm/W                        | 715 lm        |
| 911401501346 | RS378B P7 930 PSU-E MB M55 PRO  | 3000 K                             | 92                          | 110 lm/W                        | 780 lm        |
| 911401501446 | RS378B P7 940 PSU-E MB M55 PRO  | 4000 K                             | 92                          | 111 lm/W                        | 785 lm        |
| 911401501546 | RS378B P7 927 PSU-E WB M55 PRO  | 2700 K                             | 92                          | 101 lm/W                        | 715 lm        |
| 911401501646 | RS378B P7 930 PSU-E WB M55 PRO  | 3000 K                             | 92                          | 110 lm/W                        | 780 lm        |
| 911401501746 | RS378B P7 940 PSU-E WB M55 PRO  | 4000 K                             | 92                          | 111 lm/W                        | 785 lm        |
| 911401501846 | RS378B P8 927 PSU-E SNB M55 PRO | 2700 K                             | 92                          | 83 lm/W                         | 665 lm        |
| 911401501946 | RS378B P8 930 PSU-E SNB M55 PRO | 3000 K                             | 92                          | 91 lm/W                         | 730 lm        |
| 911401502046 | RS378B P8 940 PSU-E SNB M55 PRO | 4000 K                             | 92                          | 93 lm/W                         | 740 lm        |
| 911401502146 | RS378B P9 927 PSU-E NB M55 PRO  | 2700 K                             | 92                          | 94 lm/W                         | 845 lm        |
| 911401502246 | RS378B P9 930 PSU-E NB M55 PRO  | 3000 K                             | 92                          | 102 lm/W                        | 920 lm        |



| Order Code   | Full Product Name               | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|---------------------------------|------------------------------------|-----------------------------|---------------------------------|---------------|
| 911401502346 | RS378B P9 940 PSU-E NB M55 PRO  | 4000 K                             | 92                          | 103 lm/W                        | 930 lm        |
| 911401502446 | RS378B P9 927 PSU-E MB M55 PRO  | 2700 K                             | 92                          | 101 lm/W                        | 910 lm        |
| 911401502546 | RS378B P9 930 PSU-E MB M55 PRO  | 3000 K                             | 92                          | 109 lm/W                        | 985 lm        |
| 911401502646 | RS378B P9 940 PSU-E MB M55 PRO  | 4000 K                             | 92                          | 111 lm/W                        | 995 lm        |
| 911401502746 | RS378B P9 927 PSU-E WB M55 PRO  | 2700 K                             | 92                          | 101 lm/W                        | 910 lm        |
| 911401502846 | RS378B P9 930 PSU-E WB M55 PRO  | 3000 K                             | 92                          | 109 lm/W                        | 985 lm        |
| 911401502946 | RS378B P9 940 PSU-E WB M55 PRO  | 4000 K                             | 92                          | 111 lm/W                        | 995 lm        |
| 911401504846 | RS378B P7 927 PSD-E SNB M55 PRO | 2700 K                             | 92                          | 84 lm/W                         | 630 lm        |
| 911401504946 | RS378B P7 930 PSD-E SNB M55 PRO | 3000 K                             | 92                          | 93 lm/W                         | 695 lm        |
| 911401505046 | RS378B P7 940 PSD-E SNB M55 PRO | 4000 K                             | 92                          | 94 lm/W                         | 705 lm        |
| 911401505146 | RS378B P7 927 PSD-E NB M55 PRO  | 2700 K                             | 92                          | 88 lm/W                         | 645 lm        |
| 911401505246 | RS378B P7 930 PSD-E NB M55 PRO  | 3000 K                             | 92                          | 94 lm/W                         | 685 lm        |
| 911401505346 | RS378B P7 940 PSD-E NB M55 PRO  | 4000 K                             | 92                          | 97 lm/W                         | 705 lm        |
| 911401505446 | RS378B P7 927 PSD-E MB M55 PRO  | 2700 K                             | 92                          | 91 lm/W                         | 665 lm        |
| 911401505546 | RS378B P7 930 PSD-E MB M55 PRO  | 3000 K                             | 92                          | 95 lm/W                         | 695 lm        |
| 911401505646 | RS378B P7 940 PSD-E MB M55 PRO  | 4000 K                             | 92                          | 98 lm/W                         | 715 lm        |
| 911401505746 | RS378B P7 927 PSD-E WB M55 PRO  | 2700 K                             | 92                          | 98 lm/W                         | 715 lm        |
| 911401505846 | RS378B P7 930 PSD-E WB M55 PRO  | 3000 K                             | 92                          | 103 lm/W                        | 755 lm        |
| 911401505946 | RS378B P7 940 PSD-E WB M55 PRO  | 4000 K                             | 92                          | 107 lm/W                        | 780 lm        |
| 911401506046 | RS378B P9 927 PSD-E NB M55 PRO  | 2700 K                             | 92                          | 89 lm/W                         | 845 lm        |
| 911401506146 | RS378B P9 930 PSD-E NB M55 PRO  | 3000 K                             | 92                          | 97 lm/W                         | 920 lm        |
| 911401506246 | RS378B P9 940 PSD-E NB M55 PRO  | 4000 K                             | 92                          | 98 lm/W                         | 930 lm        |
| 911401506346 | RS378B P9 927 PSD-E MB M55 PRO  | 2700 K                             | 92                          | 96 lm/W                         | 910 lm        |
| 911401506446 | RS378B P9 930 PSD-E MB M55 PRO  | 3000 K                             | 92                          | 104 lm/W                        | 985 lm        |
| 911401506546 | RS378B P9 940 PSD-E MB M55 PRO  | 4000 K                             | 92                          | 105 lm/W                        | 995 lm        |

| Order Code   | Full Product Name                   | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|-------------------------------------|------------------------------------|-----------------------------|---------------------------------|---------------|
| 911401506646 | RS378B P9 927 PSD-E WB M55 PRO      | 2700 K                             | 92                          | 96 lm/W                         | 910 lm        |
| 911401506746 | RS378B P9 930 PSD-E WB M55 PRO      | 3000 K                             | 92                          | 104 lm/W                        | 985 lm        |
| 911401506846 | RS378B P9 940 PSD-E WB M55 PRO      | 4000 K                             | 92                          | 105 lm/W                        | 995 lm        |
| 911401508746 | RS378X P9 930 WIA MB M55 PRO        | 3000 K                             | 92                          | 113 lm/W                        | 985 lm        |
| 911401508846 | RS378X P9 930 WIA WB M55 PRO        | 3000 K                             | 92                          | 113 lm/W                        | 985 lm        |
| 911401509346 | RS378B P7 930 PSU-E MB M55 WP PRO   | 3000 K                             | 92                          | 110 lm/W                        | 780 lm        |
| 911401509446 | RS378B P7 930 PSU-E WB M55 WP PRO   | 3000 K                             | 92                          | 110 lm/W                        | 780 lm        |
| 911401509546 | RS378B P9 930 PSU-E MB M55 WP PRO   | 3000 K                             | 92                          | 109 lm/W                        | 985 lm        |
| 911401509646 | RS378B P9 930 PSU-E WB M55 WP PRO   | 3000 K                             | 92                          | 109 lm/W                        | 985 lm        |
| 911401518946 | RS378B P7 PSD-TNW NB M55 PRO        | Tunable White                      | 90                          | 73 lm/W                         | 520 lm        |
| 911401519046 | RS378B P7 PSD-TNW MB M55 PRO        | Tunable White                      | 90                          | 75 lm/W                         | 530 lm        |
| 911401519146 | RS378B P7 PSD-TNW WB M55 PRO        | Tunable White                      | 90                          | 77 lm/W                         | 550 lm        |
| 911401519246 | RS378B P9 PSD-TNW NB M55 PRO        | Tunable White                      | 90                          | 72 lm/W                         | 650 lm        |
| 911401519346 | RS378B P9 PSD-TNW MB M55 PRO        | Tunable White                      | 90                          | 74 lm/W                         | 670 lm        |
| 911401519446 | RS378B P9 PSD-TNW WB M55 PRO        | Tunable White                      | 90                          | 77 lm/W                         | 690 lm        |
| 911401595145 | RS378B P3 927 PSU-E MB D35 G-TT PRO | 2700 K                             | 92                          | 66 lm/W                         | 205 lm        |
| 911401595245 | RS378B P3 930 PSU-E MB D35 G-TT PRO | 3000 K                             | 92                          | 71 lm/W                         | 220 lm        |
| 911401595345 | RS378B P3 940 PSU-E MB D35 G-TT PRO | 4000 K                             | 92                          | 71 lm/W                         | 220 lm        |
| 911401595445 | RS378B P3 927 PSU-E WB D35 G-TT PRO | 2700 K                             | 92                          | 66 lm/W                         | 205 lm        |
| 911401595545 | RS378B P3 930 PSU-E WB D35 G-TT PRO | 3000 K                             | 92                          | 71 lm/W                         | 220 lm        |
| 911401595645 | RS378B P3 940 PSU-E WB D35 G-TT PRO | 4000 K                             | 92                          | 71 lm/W                         | 220 lm        |
| 911401595745 | RS378B P5 927 PSU-E MB D35 G-TT PRO | 2700 K                             | 92                          | 70 lm/W                         | 330 lm        |
| 911401595845 | RS378B P5 930 PSU-E MB D35 G-TT PRO | 3000 K                             | 92                          | 79 lm/W                         | 370 lm        |
| 911401595945 | RS378B P5 940 PSU-E MB D35 G-TT PRO | 4000 K                             | 92                          | 79 lm/W                         | 370 lm        |
| 911401596045 | RS378B P5 927 PSU-E WB D35 G-TT PRO | 2700 K                             | 92                          | 68 lm/W                         | 320 lm        |

| Order Code   | Full Product Name                      | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|----------------------------------------|------------------------------------|-----------------------------|---------------------------------|---------------|
| 911401596145 | RS378B P5 930 PSU-E WB<br>D35 G-TT PRO | 3000 K                             | 92                          | 78 lm/W                         | 365 lm        |
| 911401596245 | RS378B P5 940 PSU-E WB<br>D35 G-TT PRO | 4000 K                             | 92                          | 78 lm/W                         | 365 lm        |
| 911401596345 | RS378B P5 927 PSD-E MB<br>D35 G-TT PRO | 2700 K                             | 92                          | 56 lm/W                         | 330 lm        |
| 911401596445 | RS378B P5 930 PSD-E MB<br>D35 G-TT PRO | 3000 K                             | 92                          | 70 lm/W                         | 370 lm        |
| 911401596545 | RS378B P5 940 PSD-E MB<br>D35 G-TT PRO | 4000 K                             | 92                          | 70 lm/W                         | 370 lm        |
| 911401596645 | RS378B P5 927 PSD-E WB<br>D35 G-TT PRO | 2700 K                             | 92                          | 60 lm/W                         | 320 lm        |
| 911401596745 | RS378B P5 930 PSD-E WB<br>D35 G-TT PRO | 3000 K                             | 92                          | 69 lm/W                         | 365 lm        |
| 911401596845 | RS378B P5 940 PSD-E WB<br>D35 G-TT PRO | 4000 K                             | 92                          | 69 lm/W                         | 365 lm        |
| 911401510146 | RS378B P12 927 PSU-E NB<br>M70 PRO     | 2700 K                             | 92                          | 100 lm/W                        | 1,205 lm      |
| 911401510246 | RS378B P12 930 PSU-E NB<br>M70 PRO     | 3000 K                             | 92                          | 108 lm/W                        | 1,295 lm      |
| 911401510346 | RS378B P12 940 PSU-E NB<br>M70 PRO     | 4000 K                             | 92                          | 110 lm/W                        | 1,315 lm      |
| 911401510446 | RS378B P12 927 PSU-E MB<br>M70 PRO     | 2700 K                             | 92                          | 114 lm/W                        | 1,365 lm      |
| 911401510546 | RS378B P12 930 PSU-E MB<br>M70 PRO     | 3000 K                             | 92                          | 122 lm/W                        | 1,465 lm      |
| 911401510646 | RS378B P12 940 PSU-E MB<br>M70 PRO     | 4000 K                             | 92                          | 124 lm/W                        | 1,490 lm      |
| 911401510746 | RS378B P12 927 PSU-E WB<br>M70 PRO     | 2700 K                             | 92                          | 115 lm/W                        | 1,380 lm      |
| 911401510846 | RS378B P12 930 PSU-E WB<br>M70 PRO     | 3000 K                             | 92                          | 124 lm/W                        | 1,490 lm      |
| 911401510946 | RS378B P12 940 PSU-E WB<br>M70 PRO     | 4000 K                             | 92                          | 126 lm/W                        | 1,515 lm      |
| 911401511046 | RS378B P17 927 PSU-E NB<br>M70 PRO     | 2700 K                             | 92                          | 101 lm/W                        | 1,770 lm      |
| 911401511146 | RS378B P17 930 PSU-E NB<br>M70 PRO     | 3000 K                             | 92                          | 109 lm/W                        | 1,905 lm      |
| 911401511246 | RS378B P17 940 PSU-E NB<br>M70 PRO     | 4000 K                             | 92                          | 111 lm/W                        | 1,935 lm      |
| 911401511346 | RS378B P17 927 PSU-E MB<br>M70 PRO     | 2700 K                             | 92                          | 115 lm/W                        | 2,010 lm      |
| 911401511446 | RS378B P17 930 PSU-E MB<br>M70 PRO     | 3000 K                             | 92                          | 123 lm/W                        | 2,155 lm      |
| 911401511546 | RS378B P17 940 PSU-E MB<br>M70 PRO     | 4000 K                             | 92                          | 125 lm/W                        | 2,195 lm      |
| 911401511646 | RS378B P17 927 PSU-E WB<br>M70 PRO     | 2700 K                             | 92                          | 117 lm/W                        | 2,040 lm      |
| 911401511746 | RS378B P17 930 PSU-E WB<br>M70 PRO     | 3000 K                             | 92                          | 125 lm/W                        | 2,195 lm      |

| Order Code   | Full Product Name               | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|---------------------------------|------------------------------------|-----------------------------|---------------------------------|---------------|
| 911401511846 | RS378B P17 940 PSU-E WB M70 PRO | 4000 K                             | 92                          | 128 lm/W                        | 2,235 lm      |
| 911401511946 | RS378B P19 927 PSU-E NB M70 PRO | 2700 K                             | 92                          | 100 lm/W                        | 1,950 lm      |
| 911401512046 | RS378B P19 930 PSU-E NB M70 PRO | 3000 K                             | 92                          | 107 lm/W                        | 2,095 lm      |
| 911401512146 | RS378B P19 940 PSU-E NB M70 PRO | 4000 K                             | 92                          | 109 lm/W                        | 2,135 lm      |
| 911401512246 | RS378B P19 927 PSU-E MB M70 PRO | 2700 K                             | 92                          | 113 lm/W                        | 2,210 lm      |
| 911401512346 | RS378B P19 930 PSU-E MB M70 PRO | 3000 K                             | 92                          | 122 lm/W                        | 2,375 lm      |
| 911401512446 | RS378B P19 940 PSU-E MB M70 PRO | 4000 K                             | 92                          | 124 lm/W                        | 2,420 lm      |
| 911401512546 | RS378B P19 927 PSU-E WB M70 PRO | 2700 K                             | 92                          | 115 lm/W                        | 2,245 lm      |
| 911401512646 | RS378B P19 930 PSU-E WB M70 PRO | 3000 K                             | 92                          | 124 lm/W                        | 2,415 lm      |
| 911401512746 | RS378B P19 940 PSU-E WB M70 PRO | 4000 K                             | 92                          | 126 lm/W                        | 2,465 lm      |
| 911401513746 | RS378B P12 927 PSD-E NB M70 PRO | 2700 K                             | 92                          | 94 lm/W                         | 1,205 lm      |
| 911401513846 | RS378B P12 930 PSD-E NB M70 PRO | 3000 K                             | 92                          | 101 lm/W                        | 1,295 lm      |
| 911401513946 | RS378B P12 940 PSD-E NB M70 PRO | 4000 K                             | 92                          | 103 lm/W                        | 1,315 lm      |
| 911401514046 | RS378B P12 927 PSD-E MB M70 PRO | 2700 K                             | 92                          | 107 lm/W                        | 1,365 lm      |
| 911401514146 | RS378B P12 930 PSD-E MB M70 PRO | 3000 K                             | 92                          | 114 lm/W                        | 1,465 lm      |
| 911401514246 | RS378B P12 940 PSD-E MB M70 PRO | 4000 K                             | 92                          | 116 lm/W                        | 1,490 lm      |
| 911401514346 | RS378B P12 927 PSD-E WB M70 PRO | 2700 K                             | 92                          | 108 lm/W                        | 1,380 lm      |
| 911401514446 | RS378B P12 930 PSD-E WB M70 PRO | 3000 K                             | 92                          | 116 lm/W                        | 1,490 lm      |
| 911401514546 | RS378B P12 940 PSD-E WB M70 PRO | 4000 K                             | 92                          | 118 lm/W                        | 1,515 lm      |
| 911401514646 | RS378B P18 927 PSD-E NB M70 PRO | 2700 K                             | 92                          | 96 lm/W                         | 1,770 lm      |
| 911401514746 | RS378B P18 930 PSD-E NB M70 PRO | 3000 K                             | 92                          | 103 lm/W                        | 1,905 lm      |
| 911401514846 | RS378B P18 940 PSD-E NB M70 PRO | 4000 K                             | 92                          | 105 lm/W                        | 1,935 lm      |
| 911401514946 | RS378B P18 927 PSD-E MB M70 PRO | 2700 K                             | 92                          | 109 lm/W                        | 2,010 lm      |
| 911401515046 | RS378B P18 930 PSD-E MB M70 PRO | 3000 K                             | 92                          | 116 lm/W                        | 2,155 lm      |
| 911401515146 | RS378B P18 940 PSD-E MB M70 PRO | 4000 K                             | 92                          | 119 lm/W                        | 2,195 lm      |

| Order Code   | Full Product Name                  | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|------------------------------------|------------------------------------|-----------------------------|---------------------------------|---------------|
| 911401515246 | RS378B P18 927 PSD-E WB M70 PRO    | 2700 K                             | 92                          | 110 lm/W                        | 2,040 lm      |
| 911401515346 | RS378B P18 930 PSD-E WB M70 PRO    | 3000 K                             | 92                          | 119 lm/W                        | 2,195 lm      |
| 911401515446 | RS378B P18 940 PSD-E WB M70 PRO    | 4000 K                             | 92                          | 121 lm/W                        | 2,235 lm      |
| 911401515546 | RS378B P20 927 PSD-E NB M70 PRO    | 2700 K                             | 92                          | 95 lm/W                         | 1,950 lm      |
| 911401515646 | RS378B P20 930 PSD-E NB M70 PRO    | 3000 K                             | 92                          | 102 lm/W                        | 2,095 lm      |
| 911401515746 | RS378B P20 940 PSD-E NB M70 PRO    | 4000 K                             | 92                          | 104 lm/W                        | 2,135 lm      |
| 911401515846 | RS378B P20 927 PSD-E MB M70 PRO    | 2700 K                             | 92                          | 108 lm/W                        | 2,210 lm      |
| 911401515946 | RS378B P20 930 PSD-E MB M70 PRO    | 3000 K                             | 92                          | 116 lm/W                        | 2,375 lm      |
| 911401516046 | RS378B P20 940 PSD-E MB M70 PRO    | 4000 K                             | 92                          | 118 lm/W                        | 2,420 lm      |
| 911401516146 | RS378B P20 927 PSD-E WB M70 PRO    | 2700 K                             | 92                          | 110 lm/W                        | 2,245 lm      |
| 911401516246 | RS378B P20 930 PSD-E WB M70 PRO    | 3000 K                             | 92                          | 118 lm/W                        | 2,415 lm      |
| 911401516346 | RS378B P20 940 PSD-E WB M70 PRO    | 4000 K                             | 92                          | 120 lm/W                        | 2,465 lm      |
| 911401517346 | RS378X P12 930 WIA MB M70 PRO      | 3000 K                             | 92                          | 122 lm/W                        | 1,465 lm      |
| 911401517446 | RS378X P12 930 WIA WB M70 PRO      | 3000 K                             | 92                          | 124 lm/W                        | 1,490 lm      |
| 911401517546 | RS378X P19 930 WIA MB M70 PRO      | 3000 K                             | 92                          | 119 lm/W                        | 2,375 lm      |
| 911401517646 | RS378X P19 930 WIA WB M70 PRO      | 3000 K                             | 92                          | 121 lm/W                        | 2,415 lm      |
| 911401517746 | RS378X P18 930 WIA MB M70 PRO      | 3000 K                             | 92                          | 120 lm/W                        | 2,155 lm      |
| 911401517846 | RS378X P18 930 WIA WB M70 PRO      | 3000 K                             | 92                          | 122 lm/W                        | 2,195 lm      |
| 911401518146 | RS378B P12 930 PSU-E MB M70 WP PRO | 3000 K                             | 92                          | 122 lm/W                        | 1,465 lm      |
| 911401518246 | RS378B P12 930 PSU-E WB M70 WP PRO | 3000 K                             | 92                          | 124 lm/W                        | 1,490 lm      |
| 911401518346 | RS378B P17 930 PSU-E MB M70 WP PRO | 3000 K                             | 92                          | 123 lm/W                        | 2,155 lm      |
| 911401518446 | RS378B P17 930 PSU-E WB M70 WP PRO | 3000 K                             | 92                          | 125 lm/W                        | 2,195 lm      |
| 911401518546 | RS378B P19 930 PSU-E MB M70 WP PRO | 3000 K                             | 92                          | 122 lm/W                        | 2,375 lm      |
| 911401518646 | RS378B P19 930 PSU-E WB M70 WP PRO | 3000 K                             | 92                          | 124 lm/W                        | 2,415 lm      |
| 911401520446 | RS378B P13 PSD-TNW NB M70 PRO      | Tunable White                      | 90                          | 83 lm/W                         | 1,120 lm      |

| Order Code   | Full Product Name               | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|---------------------------------|------------------------------------|-----------------------------|---------------------------------|---------------|
| 911401520546 | RS378B P13 PSD-TNW MB M70 PRO   | Tunable White                      | 90                          | 82 lm/W                         | 1,110 lm      |
| 911401520646 | RS378B P13 PSD-TNW WB M70 PRO   | Tunable White                      | 90                          | 82 lm/W                         | 1,110 lm      |
| 911401520746 | RS378B P19 PSD-TNW NB M70 PRO   | Tunable White                      | 90                          | 81 lm/W                         | 1,620 lm      |
| 911401520846 | RS378B P19 PSD-TNW MB M70 PRO   | Tunable White                      | 90                          | 80 lm/W                         | 1,600 lm      |
| 911401520946 | RS378B P19 PSD-TNW WB M70 PRO   | Tunable White                      | 90                          | 80 lm/W                         | 1,600 lm      |
| 911401521046 | RS378B P22 PSD-TNW NB M70 PRO   | Tunable White                      | 90                          | 81 lm/W                         | 1,780 lm      |
| 911401521146 | RS378B P22 PSD-TNW MB M70 PRO   | Tunable White                      | 90                          | 80 lm/W                         | 1,760 lm      |
| 911401521246 | RS378B P22 PSD-TNW WB M70 PRO   | Tunable White                      | 90                          | 80 lm/W                         | 1,760 lm      |
| 911401512846 | RS378B P27 927 PSU-E NB M70 PRO | 2700 K                             | 92                          | 97 lm/W                         | 2,655 lm      |
| 911401512946 | RS378B P27 930 PSU-E NB M70 PRO | 3000 K                             | 92                          | 104 lm/W                        | 2,855 lm      |
| 911401513046 | RS378B P27 940 PSU-E NB M70 PRO | 4000 K                             | 92                          | 106 lm/W                        | 2,910 lm      |
| 911401513146 | RS378B P27 927 PSU-E MB M70 PRO | 2700 K                             | 92                          | 109 lm/W                        | 3,010 lm      |
| 911401513246 | RS378B P27 930 PSU-E MB M70 PRO | 3000 K                             | 92                          | 118 lm/W                        | 3,235 lm      |
| 911401513346 | RS378B P27 940 PSU-E MB M70 PRO | 4000 K                             | 92                          | 120 lm/W                        | 3,295 lm      |
| 911401513446 | RS378B P27 927 PSU-E WB M70 PRO | 2700 K                             | 92                          | 111 lm/W                        | 3,060 lm      |
| 911401513546 | RS378B P27 930 PSU-E WB M70 PRO | 3000 K                             | 92                          | 119 lm/W                        | 3,285 lm      |
| 911401513646 | RS378B P27 940 PSU-E WB M70 PRO | 4000 K                             | 92                          | 122 lm/W                        | 3,360 lm      |
| 911401516446 | RS378B P27 927 PSD-E NB M70 PRO | 2700 K                             | 92                          | 91 lm/W                         | 2,470 lm      |
| 911401516546 | RS378B P27 930 PSD-E NB M70 PRO | 3000 K                             | 92                          | 98 lm/W                         | 2,645 lm      |
| 911401516646 | RS378B P27 940 PSD-E NB M70 PRO | 4000 K                             | 92                          | 100 lm/W                        | 2,700 lm      |
| 911401516746 | RS378B P27 927 PSD-E MB M70 PRO | 2700 K                             | 92                          | 103 lm/W                        | 2,790 lm      |
| 911401516846 | RS378B P27 930 PSD-E MB M70 PRO | 3000 K                             | 92                          | 111 lm/W                        | 3,000 lm      |
| 911401516946 | RS378B P27 940 PSD-E MB M70 PRO | 4000 K                             | 92                          | 113 lm/W                        | 3,060 lm      |
| 911401517046 | RS378B P27 927 PSD-E WB M70 PRO | 2700 K                             | 92                          | 105 lm/W                        | 2,845 lm      |
| 911401517146 | RS378B P27 930 PSD-E WB M70 PRO | 3000 K                             | 92                          | 113 lm/W                        | 3,050 lm      |

| Order Code   | Full Product Name                       | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|-----------------------------------------|------------------------------------|-----------------------------|---------------------------------|---------------|
| 911401517246 | RS378B P27 940 PSD-E WB M70 PRO         | 4000 K                             | 92                          | 115 lm/W                        | 3,115 lm      |
| 911401517946 | RS378X P28 930 WIA MB M70 PRO           | 3000 K                             | 92                          | 114 lm/W                        | 3,235 lm      |
| 911401518046 | RS378X P28 930 WIA WB M70 PRO           | 3000 K                             | 92                          | 115 lm/W                        | 3,285 lm      |
| 911401518746 | RS378B P27 930 PSU-E MB M70 WP PRO      | 3000 K                             | 92                          | 118 lm/W                        | 3,235 lm      |
| 911401518846 | RS378B P27 930 PSU-E WB M70 WP PRO      | 3000 K                             | 92                          | 119 lm/W                        | 3,285 lm      |
| 911401521346 | RS378B P29 PSD-TNW NB M70 PRO           | Tunable White                      | 90                          | 80 lm/W                         | 2,240 lm      |
| 911401521446 | RS378B P29 PSD-TNW MB M70 PRO           | Tunable White                      | 90                          | 79 lm/W                         | 2,210 lm      |
| 911401521546 | RS378B P29 PSD-TNW WB M70 PRO           | Tunable White                      | 90                          | 79 lm/W                         | 2,210 lm      |
| 911401530846 | SM378B S P8 927 PSU-E NB D100 G-TT PRO  | 2700 K                             | 92                          | 120 lm/W                        | 935 lm        |
| 911401530946 | SM378B S P8 930 PSU-E NB D100 G-TT PRO  | 3000 K                             | 92                          | 125 lm/W                        | 975 lm        |
| 911401531046 | SM378B S P8 940 PSU-E NB D100 G-TT PRO  | 4000 K                             | 92                          | 128 lm/W                        | 995 lm        |
| 911401531146 | SM378B S P8 927 PSU-E MB D100 G-TT PRO  | 2700 K                             | 92                          | 118 lm/W                        | 920 lm        |
| 911401531246 | SM378B S P8 930 PSU-E MB D100 G-TT PRO  | 3000 K                             | 92                          | 123 lm/W                        | 960 lm        |
| 911401531346 | SM378B S P8 940 PSU-E MB D100 G-TT PRO  | 4000 K                             | 92                          | 126 lm/W                        | 980 lm        |
| 911401531446 | SM378B S P8 927 PSU-E WB D100 G-TT PRO  | 2700 K                             | 92                          | 113 lm/W                        | 885 lm        |
| 911401531546 | SM378B S P8 930 PSU-E WB D100 G-TT PRO  | 3000 K                             | 92                          | 119 lm/W                        | 925 lm        |
| 911401531646 | SM378B S P8 940 PSU-E WB D100 G-TT PRO  | 4000 K                             | 92                          | 121 lm/W                        | 945 lm        |
| 911401531746 | SM378B S P11 927 PSU-E NB D100 G-TT PRO | 2700 K                             | 92                          | 117 lm/W                        | 1,340 lm      |
| 911401531846 | SM378B S P11 930 PSU-E NB D100 G-TT PRO | 3000 K                             | 92                          | 120 lm/W                        | 1,380 lm      |
| 911401531946 | SM378B S P11 940 PSU-E NB D100 G-TT PRO | 4000 K                             | 92                          | 122 lm/W                        | 1,400 lm      |
| 911401532046 | SM378B S P11 927 PSU-E MB D100 G-TT PRO | 2700 K                             | 92                          | 115 lm/W                        | 1,325 lm      |
| 911401532146 | SM378B S P11 930 PSU-E MB D100 G-TT PRO | 3000 K                             | 92                          | 119 lm/W                        | 1,365 lm      |
| 911401532246 | SM378B S P11 940 PSU-E MB D100 G-TT PRO | 4000 K                             | 92                          | 120 lm/W                        | 1,385 lm      |
| 911401532346 | SM378B S P11 927 PSU-E WB D100 G-TT PRO | 2700 K                             | 92                          | 110 lm/W                        | 1,270 lm      |
| 911401532446 | SM378B S P11 930 PSU-E WB D100 G-TT PRO | 3000 K                             | 92                          | 114 lm/W                        | 1,310 lm      |

| Order Code   | Full Product Name                          | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|--------------------------------------------|------------------------------------|-----------------------------|---------------------------------|---------------|
| 911401532546 | SM378B S P11 940 PSU-E WB<br>D100 G-TT PRO | 4000 K                             | 92                          | 116 lm/W                        | 1,330 lm      |
| 911401532646 | SM378B S P13 927 PSU-E NB<br>D100 G-TT PRO | 2700 K                             | 92                          | 114 lm/W                        | 1,540 lm      |
| 911401532746 | SM378B S P13 930 PSU-E NB<br>D100 G-TT PRO | 3000 K                             | 92                          | 117 lm/W                        | 1,580 lm      |
| 911401532846 | SM378B S P13 940 PSU-E NB<br>D100 G-TT PRO | 4000 K                             | 92                          | 119 lm/W                        | 1,600 lm      |
| 911401532946 | SM378B S P13 927 PSU-E MB<br>D100 G-TT PRO | 2700 K                             | 92                          | 113 lm/W                        | 1,520 lm      |
| 911401533046 | SM378B S P13 930 PSU-E MB<br>D100 G-TT PRO | 3000 K                             | 92                          | 116 lm/W                        | 1,560 lm      |
| 911401533146 | SM378B S P13 940 PSU-E MB<br>D100 G-TT PRO | 4000 K                             | 92                          | 117 lm/W                        | 1,580 lm      |
| 911401533246 | SM378B S P13 927 PSU-E WB<br>D100 G-TT PRO | 2700 K                             | 92                          | 108 lm/W                        | 1,460 lm      |
| 911401533346 | SM378B S P13 930 PSU-E WB<br>D100 G-TT PRO | 3000 K                             | 92                          | 111 lm/W                        | 1,500 lm      |
| 911401533446 | SM378B S P13 940 PSU-E WB<br>D100 G-TT PRO | 4000 K                             | 92                          | 113 lm/W                        | 1,520 lm      |
| 911401533546 | SM378B S P20 927 PSU-E NB<br>D100 G-TT PRO | 2700 K                             | 92                          | 107 lm/W                        | 2,140 lm      |
| 911401533646 | SM378B S P20 930 PSU-E NB<br>D100 G-TT PRO | 3000 K                             | 92                          | 109 lm/W                        | 2,180 lm      |
| 911401533746 | SM378B S P20 940 PSU-E NB<br>D100 G-TT PRO | 4000 K                             | 92                          | 110 lm/W                        | 2,200 lm      |
| 911401533846 | SM378B S P20 927 PSU-E MB<br>D100 G-TT PRO | 2700 K                             | 92                          | 106 lm/W                        | 2,110 lm      |
| 911401533946 | SM378B S P20 930 PSU-E MB<br>D100 G-TT PRO | 3000 K                             | 92                          | 108 lm/W                        | 2,150 lm      |
| 911401534046 | SM378B S P20 940 PSU-E MB<br>D100 G-TT PRO | 4000 K                             | 92                          | 109 lm/W                        | 2,170 lm      |
| 911401534146 | SM378B S P20 927 PSU-E WB<br>D100 G-TT PRO | 2700 K                             | 92                          | 102 lm/W                        | 2,040 lm      |
| 911401534246 | SM378B S P20 930 PSU-E<br>WB D100 G-TT PRO | 3000 K                             | 92                          | 104 lm/W                        | 2,080 lm      |
| 911401534346 | SM378B S P20 940 PSU-E<br>WB D100 G-TT PRO | 4000 K                             | 92                          | 105 lm/W                        | 2,100 lm      |
| 911401534446 | SM378B S P20 927 PSD-E NB<br>D100 G-TT PRO | 2700 K                             | 92                          | 104 lm/W                        | 2,140 lm      |
| 911401534546 | SM378B S P20 930 PSD-E NB<br>D100 G-TT PRO | 3000 K                             | 92                          | 106 lm/W                        | 2,180 lm      |
| 911401534646 | SM378B S P20 940 PSD-E NB<br>D100 G-TT PRO | 4000 K                             | 92                          | 107 lm/W                        | 2,200 lm      |
| 911401534746 | SM378B S P20 927 PSD-E MB<br>D100 G-TT PRO | 2700 K                             | 92                          | 103 lm/W                        | 2,110 lm      |
| 911401534846 | SM378B S P20 930 PSD-E MB<br>D100 G-TT PRO | 3000 K                             | 92                          | 105 lm/W                        | 2,150 lm      |
| 911401534946 | SM378B S P20 940 PSD-E<br>MB D100 G-TT PRO | 4000 K                             | 92                          | 106 lm/W                        | 2,170 lm      |



| Order Code   | Full Product Name                       | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|-----------------------------------------|------------------------------------|-----------------------------|---------------------------------|---------------|
| 911401535046 | SM378B S P20 927 PSD-E WB D100 G-TT PRO | 2700 K                             | 92                          | 100 lm/W                        | 2,040 lm      |
| 911401535146 | SM378B S P20 930 PSD-E WB D100 G-TT PRO | 3000 K                             | 92                          | 101 lm/W                        | 2,080 lm      |
| 911401535246 | SM378B S P20 940 PSD-E WB D100 G-TT PRO | 4000 K                             | 92                          | 102 lm/W                        | 2,100 lm      |
| 911401535446 | SM378B S P8 927 PSD-E NB D100 G-TT PRO  | 2700 K                             | 92                          | 104 lm/W                        | 935 lm        |
| 911401535546 | SM378B S P8 930 PSD-E NB D100 G-TT PRO  | 3000 K                             | 92                          | 108 lm/W                        | 975 lm        |
| 911401535646 | SM378B S P8 940 PSD-E NB D100 G-TT PRO  | 4000 K                             | 92                          | 111 lm/W                        | 995 lm        |
| 911401535746 | SM378B S P8 927 PSD-E MB D100 G-TT PRO  | 2700 K                             | 92                          | 102 lm/W                        | 920 lm        |
| 911401535846 | SM378B S P8 930 PSD-E MB D100 G-TT PRO  | 3000 K                             | 92                          | 107 lm/W                        | 960 lm        |
| 911401535946 | SM378B S P8 940 PSD-E MB D100 G-TT PRO  | 4000 K                             | 92                          | 109 lm/W                        | 980 lm        |
| 911401536046 | SM378B S P8 927 PSD-E WB D100 G-TT PRO  | 2700 K                             | 92                          | 98 lm/W                         | 885 lm        |
| 911401536146 | SM378B S P8 930 PSD-E WB D100 G-TT PRO  | 3000 K                             | 92                          | 103 lm/W                        | 925 lm        |
| 911401536246 | SM378B S P8 940 PSD-E WB D100 G-TT PRO  | 4000 K                             | 92                          | 105 lm/W                        | 945 lm        |
| 911401536346 | SM378B S P12 927 PSD-E NB D100 G-TT PRO | 2700 K                             | 92                          | 103 lm/W                        | 1,340 lm      |
| 911401536446 | SM378B S P12 930 PSD-E NB D100 G-TT PRO | 3000 K                             | 92                          | 106 lm/W                        | 1,380 lm      |
| 911401536546 | SM378B S P12 940 PSD-E NB D100 G-TT PRO | 4000 K                             | 92                          | 108 lm/W                        | 1,400 lm      |
| 911401536646 | SM378B S P12 927 PSD-E MB D100 G-TT PRO | 2700 K                             | 92                          | 102 lm/W                        | 1,325 lm      |
| 911401536746 | SM378B S P12 930 PSD-E MB D100 G-TT PRO | 3000 K                             | 92                          | 105 lm/W                        | 1,365 lm      |
| 911401536846 | SM378B S P12 940 PSD-E MB D100 G-TT PRO | 4000 K                             | 92                          | 107 lm/W                        | 1,385 lm      |
| 911401536946 | SM378B S P12 927 PSD-E WB D100 G-TT PRO | 2700 K                             | 92                          | 98 lm/W                         | 1,270 lm      |
| 911401537046 | SM378B S P12 930 PSD-E WB D100 G-TT PRO | 3000 K                             | 92                          | 101 lm/W                        | 1,310 lm      |
| 911401537146 | SM378B S P12 940 PSD-E WB D100 G-TT PRO | 4000 K                             | 92                          | 102 lm/W                        | 1,330 lm      |
| 911401537246 | SM378B S P14 927 PSD-E NB D100 G-TT PRO | 2700 K                             | 92                          | 106 lm/W                        | 1,540 lm      |
| 911401537346 | SM378B S P14 930 PSD-E NB D100 G-TT PRO | 3000 K                             | 92                          | 109 lm/W                        | 1,580 lm      |
| 911401537446 | SM378B S P14 940 PSD-E NB D100 G-TT PRO | 4000 K                             | 92                          | 110 lm/W                        | 1,600 lm      |
| 911401537546 | SM378B S P14 927 PSD-E MB D100 G-TT PRO | 2700 K                             | 92                          | 105 lm/W                        | 1,520 lm      |

| Order Code   | Full Product Name                          | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|--------------------------------------------|------------------------------------|-----------------------------|---------------------------------|---------------|
| 911401537646 | SM378B S P14 930 PSD-E MB<br>D100 G-TT PRO | 3000 K                             | 92                          | 108 lm/W                        | 1,560 lm      |
| 911401537746 | SM378B S P14 940 PSD-E MB<br>D100 G-TT PRO | 4000 K                             | 92                          | 109 lm/W                        | 1,580 lm      |
| 911401537846 | SM378B S P14 927 PSD-E WB<br>D100 G-TT PRO | 2700 K                             | 92                          | 101 lm/W                        | 1,460 lm      |
| 911401537946 | SM378B S P14 930 PSD-E WB<br>D100 G-TT PRO | 3000 K                             | 92                          | 103 lm/W                        | 1,500 lm      |
| 911401538046 | SM378B S P14 940 PSD-E WB<br>D100 G-TT PRO | 4000 K                             | 92                          | 105 lm/W                        | 1,520 lm      |
| 911401538146 | SM378X S P8 930 WIA MB<br>D100 G-TT PRO    | 3000 K                             | 92                          | 117 lm/W                        | 960 lm        |
| 911401538246 | SM378X S P8 930 WIA WB<br>D100 G-TT PRO    | 3000 K                             | 92                          | 113 lm/W                        | 925 lm        |
| 911401538346 | SM378X S P12 930 WIA MB<br>D100 G-TT PRO   | 3000 K                             | 92                          | 114 lm/W                        | 1,365 lm      |
| 911401538446 | SM378X S P12 930 WIA WB<br>D100 G-TT PRO   | 3000 K                             | 92                          | 109 lm/W                        | 1,310 lm      |
| 911401538546 | SM378X S P14 930 WIA MB<br>D100 G-TT PRO   | 3000 K                             | 92                          | 111 lm/W                        | 1,560 lm      |
| 911401538646 | SM378X S P14 930 WIA WB<br>D100 G-TT PRO   | 3000 K                             | 92                          | 107 lm/W                        | 1,500 lm      |
| 911401538746 | SM378X S P20 930 WIA MB<br>D100 G-TT PRO   | 3000 K                             | 92                          | 108 lm/W                        | 2,150 lm      |
| 911401538846 | SM378X S P20 930 WIA WB<br>D100 G-TT PRO   | 3000 K                             | 92                          | 104 lm/W                        | 2,080 lm      |
| 911401538946 | SM378B S P9 PSD-TNW NB<br>D100 G-TT PRO    | Tunable White                      | 90                          | 86 lm/W                         | 770 lm        |
| 911401539046 | SM378B S P9 PSD-TNW MB<br>D100 G-TT PRO    | Tunable White                      | 90                          | 86 lm/W                         | 770 lm        |
| 911401539146 | SM378B S P9 PSD-TNW WB<br>D100 G-TT PRO    | Tunable White                      | 90                          | 83 lm/W                         | 750 lm        |
| 911401539246 | SM378B S P12 PSD-TNW NB<br>D100 G-TT PRO   | Tunable White                      | 90                          | 85 lm/W                         | 1,110 lm      |
| 911401539346 | SM378B S P12 PSD-TNW MB<br>D100 G-TT PRO   | Tunable White                      | 90                          | 84 lm/W                         | 1,090 lm      |
| 911401539446 | SM378B S P12 PSD-TNW WB<br>D100 G-TT PRO   | Tunable White                      | 90                          | 82 lm/W                         | 1,070 lm      |
| 911401539546 | SM378B S P15 PSD-TNW NB<br>D100 G-TT PRO   | Tunable White                      | 90                          | 85 lm/W                         | 1,320 lm      |
| 911401539646 | SM378B S P15 PSD-TNW MB<br>D100 G-TT PRO   | Tunable White                      | 90                          | 84 lm/W                         | 1,300 lm      |
| 911401539746 | SM378B S P15 PSD-TNW WB<br>D100 G-TT PRO   | Tunable White                      | 90                          | 82 lm/W                         | 1,270 lm      |
| 911401539846 | SM378B S P22 PSD-TNW NB<br>D100 G-TT PRO   | Tunable White                      | 90                          | 82 lm/W                         | 1,800 lm      |
| 911401539946 | SM378B S P22 PSD-TNW MB<br>D100 G-TT PRO   | Tunable White                      | 90                          | 81 lm/W                         | 1,780 lm      |
| 911401540046 | SM378B S P22 PSD-TNW WB<br>D100 G-TT PRO   | Tunable White                      | 90                          | 79 lm/W                         | 1,740 lm      |

| Order Code   | Full Product Name                  | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|------------------------------------|------------------------------------|-----------------------------|---------------------------------|---------------|
| 911401503046 | RS378B P12 927 PSU-E NB<br>M55 PRO | 2700 K                             | 92                          | 97 lm/W                         | 1,220 lm      |
| 911401503146 | RS378B P12 930 PSU-E NB<br>M55 PRO | 3000 K                             | 92                          | 107 lm/W                        | 1,350 lm      |
| 911401503246 | RS378B P12 940 PSU-E NB<br>M55 PRO | 4000 K                             | 92                          | 109 lm/W                        | 1,375 lm      |
| 911401503346 | RS378B P12 927 PSU-E MB<br>M55 PRO | 2700 K                             | 92                          | 98 lm/W                         | 1,240 lm      |
| 911401503446 | RS378B P12 930 PSU-E MB<br>M55 PRO | 3000 K                             | 92                          | 108 lm/W                        | 1,360 lm      |
| 911401503546 | RS378B P12 940 PSU-E MB<br>M55 PRO | 4000 K                             | 92                          | 110 lm/W                        | 1,380 lm      |
| 911401503646 | RS378B P12 927 PSU-E WB<br>M55 PRO | 2700 K                             | 92                          | 107 lm/W                        | 1,345 lm      |
| 911401503746 | RS378B P12 930 PSU-E WB<br>M55 PRO | 3000 K                             | 92                          | 117 lm/W                        | 1,475 lm      |
| 911401503846 | RS378B P12 940 PSU-E WB<br>M55 PRO | 4000 K                             | 92                          | 119 lm/W                        | 1,500 lm      |
| 911401503946 | RS378B P14 927 PSU-E NB<br>M55 PRO | 2700 K                             | 92                          | 98 lm/W                         | 1,425 lm      |
| 911401504046 | RS378B P14 930 PSU-E NB<br>M55 PRO | 3000 K                             | 92                          | 108 lm/W                        | 1,560 lm      |
| 911401504146 | RS378B P14 940 PSU-E NB<br>M55 PRO | 4000 K                             | 92                          | 110 lm/W                        | 1,595 lm      |
| 911401504246 | RS378B P14 927 PSU-E MB<br>M55 PRO | 2700 K                             | 92                          | 99 lm/W                         | 1,435 lm      |
| 911401504346 | RS378B P14 930 PSU-E MB<br>M55 PRO | 3000 K                             | 92                          | 109 lm/W                        | 1,575 lm      |
| 911401504446 | RS378B P14 940 PSU-E MB<br>M55 PRO | 4000 K                             | 92                          | 111 lm/W                        | 1,605 lm      |
| 911401504546 | RS378B P14 927 PSU-E WB<br>M55 PRO | 2700 K                             | 92                          | 107 lm/W                        | 1,550 lm      |
| 911401504646 | RS378B P14 930 PSU-E WB<br>M55 PRO | 3000 K                             | 92                          | 118 lm/W                        | 1,710 lm      |
| 911401504746 | RS378B P14 940 PSU-E WB<br>M55 PRO | 4000 K                             | 92                          | 120 lm/W                        | 1,745 lm      |
| 911401506946 | RS378B P13 927 PSD-E NB<br>M55 PRO | 2700 K                             | 92                          | 90 lm/W                         | 1,220 lm      |
| 911401507046 | RS378B P13 930 PSD-E NB<br>M55 PRO | 3000 K                             | 92                          | 100 lm/W                        | 1,350 lm      |
| 911401507146 | RS378B P13 940 PSD-E NB<br>M55 PRO | 4000 K                             | 92                          | 102 lm/W                        | 1,375 lm      |
| 911401507246 | RS378B P13 927 PSD-E MB<br>M55 PRO | 2700 K                             | 92                          | 92 lm/W                         | 1,240 lm      |
| 911401507346 | RS378B P13 930 PSD-E MB<br>M55 PRO | 3000 K                             | 92                          | 101 lm/W                        | 1,360 lm      |
| 911401507446 | RS378B P13 940 PSD-E MB<br>M55 PRO | 4000 K                             | 92                          | 102 lm/W                        | 1,380 lm      |
| 911401507546 | RS378B P13 927 PSD-E WB<br>M55 PRO | 2700 K                             | 92                          | 100 lm/W                        | 1,345 lm      |

| Order Code   | Full Product Name                  | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|--------------|------------------------------------|------------------------------------|-----------------------------|---------------------------------|---------------|
| 911401507646 | RS378B P13 930 PSD-E WB M55 PRO    | 3000 K                             | 92                          | 109 lm/W                        | 1,475 lm      |
| 911401507746 | RS378B P13 940 PSD-E WB M55 PRO    | 4000 K                             | 92                          | 111 lm/W                        | 1,500 lm      |
| 911401507846 | RS378B P15 927 PSD-E NB M55 PRO    | 2700 K                             | 92                          | 92 lm/W                         | 1,425 lm      |
| 911401507946 | RS378B P15 930 PSD-E NB M55 PRO    | 3000 K                             | 92                          | 101 lm/W                        | 1,560 lm      |
| 911401508046 | RS378B P15 940 PSD-E NB M55 PRO    | 4000 K                             | 92                          | 103 lm/W                        | 1,595 lm      |
| 911401508146 | RS378B P15 927 PSD-E MB M55 PRO    | 2700 K                             | 92                          | 93 lm/W                         | 1,435 lm      |
| 911401508246 | RS378B P15 930 PSD-E MB M55 PRO    | 3000 K                             | 92                          | 102 lm/W                        | 1,575 lm      |
| 911401508346 | RS378B P15 940 PSD-E MB M55 PRO    | 4000 K                             | 92                          | 104 lm/W                        | 1,605 lm      |
| 911401508446 | RS378B P15 927 PSD-E WB M55 PRO    | 2700 K                             | 92                          | 100 lm/W                        | 1,550 lm      |
| 911401508546 | RS378B P15 930 PSD-E WB M55 PRO    | 3000 K                             | 92                          | 110 lm/W                        | 1,710 lm      |
| 911401508646 | RS378B P15 940 PSD-E WB M55 PRO    | 4000 K                             | 92                          | 113 lm/W                        | 1,745 lm      |
| 911401508946 | RS378X P12 930 WIA MB M55 PRO      | 3000 K                             | 92                          | 106 lm/W                        | 1,360 lm      |
| 911401509046 | RS378X P12 930 WIA WB M55 PRO      | 3000 K                             | 92                          | 115 lm/W                        | 1,475 lm      |
| 911401509146 | RS378X P14 930 WIA MB M55 PRO      | 3000 K                             | 92                          | 105 lm/W                        | 1,575 lm      |
| 911401509246 | RS378X P14 930 WIA WB M55 PRO      | 3000 K                             | 92                          | 114 lm/W                        | 1,710 lm      |
| 911401509746 | RS378B P12 930 PSU-E MB M55 WP PRO | 3000 K                             | 92                          | 108 lm/W                        | 1,360 lm      |
| 911401509846 | RS378B P12 930 PSU-E WB M55 WP PRO | 3000 K                             | 92                          | 117 lm/W                        | 1,475 lm      |
| 911401509946 | RS378B P14 930 PSU-E MB M55 WP PRO | 3000 K                             | 92                          | 109 lm/W                        | 1,575 lm      |
| 911401510046 | RS378B P14 930 PSU-E WB M55 WP PRO | 3000 K                             | 92                          | 118 lm/W                        | 1,710 lm      |
| 911401519546 | RS378B P13 PSD-TNW NB M55 PRO      | Tunable White                      | 90                          | 71 lm/W                         | 960 lm        |
| 911401519646 | RS378B P13 PSD-TNW MB M55 PRO      | Tunable White                      | 90                          | 73 lm/W                         | 990 lm        |
| 911401519746 | RS378B P13 PSD-TNW WB M55 PRO      | Tunable White                      | 90                          | 76 lm/W                         | 1,030 lm      |
| 911401519846 | RS378B P15 PSD-TNW NB M55 PRO      | Tunable White                      | 90                          | 71 lm/W                         | 1,070 lm      |
| 911401519946 | RS378B P15 PSD-TNW MB M55 PRO      | Tunable White                      | 90                          | 73 lm/W                         | 1,100 lm      |
| 911401520046 | RS378B P15 PSD-TNW WB M55 PRO      | Tunable White                      | 90                          | 76 lm/W                         | 1,140 lm      |

Operating and Electrical

| Order Code   | Full Product Name                       | Power Consumption |
|--------------|-----------------------------------------|-------------------|
| 911401521646 | SM378B R P8 927 PSU-E NB D100 G-TT PRO  | 7.8 W             |
| 911401521746 | SM378B R P8 930 PSU-E NB D100 G-TT PRO  | 7.8 W             |
| 911401521846 | SM378B R P8 940 PSU-E NB D100 G-TT PRO  | 7.8 W             |
| 911401521946 | SM378B R P8 927 PSU-E MB D100 G-TT PRO  | 7.8 W             |
| 911401522046 | SM378B R P8 930 PSU-E MB D100 G-TT PRO  | 7.8 W             |
| 911401522146 | SM378B R P8 940 PSU-E MB D100 G-TT PRO  | 7.8 W             |
| 911401522246 | SM378B R P8 927 PSU-E WB D100 G-TT PRO  | 7.8 W             |
| 911401522346 | SM378B R P8 930 PSU-E WB D100 G-TT PRO  | 7.8 W             |
| 911401522446 | SM378B R P8 940 PSU-E WB D100 G-TT PRO  | 7.8 W             |
| 911401522546 | SM378B R P11 927 PSU-E NB D100 G-TT PRO | 11.5 W            |
| 911401522646 | SM378B R P11 930 PSU-E NB D100 G-TT PRO | 11.5 W            |
| 911401522746 | SM378B R P11 940 PSU-E NB D100 G-TT PRO | 11.5 W            |
| 911401522846 | SM378B R P11 927 PSU-E MB D100 G-TT PRO | 11.5 W            |
| 911401522946 | SM378B R P11 930 PSU-E MB D100 G-TT PRO | 11.5 W            |
| 911401523046 | SM378B R P11 940 PSU-E MB D100 G-TT PRO | 11.5 W            |
| 911401523146 | SM378B R P11 927 PSU-E WB D100 G-TT PRO | 11.5 W            |
| 911401523246 | SM378B R P11 930 PSU-E WB D100 G-TT PRO | 11.5 W            |
| 911401523346 | SM378B R P11 940 PSU-E WB D100 G-TT PRO | 11.5 W            |
| 911401523446 | SM378B R P13 927 PSU-E NB D100 G-TT PRO | 13.5 W            |
| 911401523546 | SM378B R P13 930 PSU-E NB D100 G-TT PRO | 13.5 W            |
| 911401523646 | SM378B R P13 940 PSU-E NB D100 G-TT PRO | 13.5 W            |
| 911401523746 | SM378B R P13 927 PSU-E MB D100 G-TT PRO | 13.5 W            |
| 911401523846 | SM378B R P13 930 PSU-E MB D100 G-TT PRO | 13.5 W            |
| 911401523946 | SM378B R P13 940 PSU-E MB D100 G-TT PRO | 13.5 W            |
| 911401524046 | SM378B R P13 927 PSU-E WB D100 G-TT PRO | 13.5 W            |
| 911401524146 | SM378B R P13 930 PSU-E WB D100 G-TT PRO | 13.5 W            |
| 911401524246 | SM378B R P13 940 PSU-E WB D100 G-TT PRO | 13.5 W            |
| 911401524346 | SM378B R P20 927 PSU-E NB D100 G-TT PRO | 20 W              |
| 911401524446 | SM378B R P20 930 PSU-E NB D100 G-TT PRO | 20 W              |
| 911401524546 | SM378B R P20 940 PSU-E NB D100 G-TT PRO | 20 W              |
| 911401524646 | SM378B R P20 927 PSU-E MB D100 G-TT PRO | 20 W              |
| 911401524746 | SM378B R P20 930 PSU-E MB D100 G-TT PRO | 20 W              |
| 911401524846 | SM378B R P20 940 PSU-E MB D100 G-TT PRO | 20 W              |
| 911401524946 | SM378B R P20 927 PSU-E WB D100 G-TT PRO | 20 W              |
| 911401525046 | SM378B R P20 930 PSU-E WB D100 G-TT PRO | 20 W              |
| 911401525146 | SM378B R P20 940 PSU-E WB D100 G-TT PRO | 20 W              |
| 911401525246 | SM378B R P20 927 PSD-E NB D100 G-TT PRO | 20.5 W            |
| 911401525346 | SM378B R P20 930 PSD-E NB D100 G-TT PRO | 20.5 W            |
| 911401525446 | SM378B R P20 940 PSD-E NB D100 G-TT PRO | 20.5 W            |
| 911401525546 | SM378B R P20 927 PSD-E MB D100 G-TT PRO | 20.5 W            |
| 911401525646 | SM378B R P20 930 PSD-E MB D100 G-TT PRO | 20.5 W            |
| 911401525746 | SM378B R P20 940 PSD-E MB D100 G-TT PRO | 20.5 W            |
| 911401525846 | SM378B R P20 927 PSD-E WB D100 G-TT PRO | 20.5 W            |
| 911401525946 | SM378B R P20 930 PSD-E WB D100 G-TT PRO | 20.5 W            |
| 911401526046 | SM378B R P20 940 PSD-E WB D100 G-TT PRO | 20.5 W            |
| 911401526146 | SM378B R P8 927 PSD-E NB D100 G-TT PRO  | 9 W               |
| 911401526246 | SM378B R P8 930 PSD-E NB D100 G-TT PRO  | 9 W               |
| 911401526346 | SM378B R P8 940 PSD-E NB D100 G-TT PRO  | 9 W               |
| 911401526446 | SM378B R P8 927 PSD-E MB D100 G-TT PRO  | 9 W               |
| 911401526546 | SM378B R P8 930 PSD-E MB D100 G-TT PRO  | 9 W               |
| 911401526646 | SM378B R P8 940 PSD-E MB D100 G-TT PRO  | 9 W               |

| Order Code   | Full Product Name                       | Power Consumption |
|--------------|-----------------------------------------|-------------------|
| 911401526746 | SM378B R P8 927 PSD-E WB D100 G-TT PRO  | 9 W               |
| 911401526846 | SM378B R P8 930 PSD-E WB D100 G-TT PRO  | 9 W               |
| 911401526946 | SM378B R P8 940 PSD-E WB D100 G-TT PRO  | 9 W               |
| 911401527046 | SM378B R P12 927 PSD-E NB D100 G-TT PRO | 13 W              |
| 911401527146 | SM378B R P12 930 PSD-E NB D100 G-TT PRO | 13 W              |
| 911401527246 | SM378B R P12 940 PSD-E NB D100 G-TT PRO | 13 W              |
| 911401527346 | SM378B R P12 927 PSD-E MB D100 G-TT PRO | 13 W              |
| 911401527446 | SM378B R P12 930 PSD-E MB D100 G-TT PRO | 13 W              |
| 911401527546 | SM378B R P12 940 PSD-E MB D100 G-TT PRO | 13 W              |
| 911401527646 | SM378B R P12 927 PSD-E WB D100 G-TT PRO | 13 W              |
| 911401527746 | SM378B R P12 930 PSD-E WB D100 G-TT PRO | 13 W              |
| 911401527846 | SM378B R P12 940 PSD-E WB D100 G-TT PRO | 13 W              |
| 911401527946 | SM378B R P14 927 PSD-E NB D100 G-TT PRO | 14.5 W            |
| 911401528046 | SM378B R P14 930 PSD-E NB D100 G-TT PRO | 14.5 W            |
| 911401528146 | SM378B R P14 940 PSD-E NB D100 G-TT PRO | 14.5 W            |
| 911401528246 | SM378B R P14 927 PSD-E MB D100 G-TT PRO | 14.5 W            |
| 911401528346 | SM378B R P14 930 PSD-E MB D100 G-TT PRO | 14.5 W            |
| 911401528446 | SM378B R P14 940 PSD-E MB D100 G-TT PRO | 14.5 W            |
| 911401528546 | SM378B R P14 927 PSD-E WB D100 G-TT PRO | 14.5 W            |
| 911401528646 | SM378B R P14 930 PSD-E WB D100 G-TT PRO | 14.5 W            |
| 911401528746 | SM378B R P14 940 PSD-E WB D100 G-TT PRO | 14.5 W            |
| 911401528846 | SM378X R P8 930 WIA MB D100 G-TT PRO    | 8.2 W             |
| 911401528946 | SM378X R P8 930 WIA WB D100 G-TT PRO    | 8.2 W             |
| 911401529046 | SM378X R P12 930 WIA MB D100 G-TT PRO   | 12 W              |
| 911401529146 | SM378X R P12 930 WIA WB D100 G-TT PRO   | 12 W              |
| 911401529246 | SM378X R P14 930 WIA MB D100 G-TT PRO   | 14 W              |
| 911401529346 | SM378X R P14 930 WIA WB D100 G-TT PRO   | 14 W              |
| 911401529446 | SM378X R P20 930 WIA MB D100 G-TT PRO   | 20 W              |
| 911401529546 | SM378X R P20 930 WIA WB D100 G-TT PRO   | 20 W              |
| 911401529646 | SM378B R P9 PSD-TNW NB D100 G-TT PRO    | 9 W               |
| 911401529746 | SM378B R P9 PSD-TNW MB D100 G-TT PRO    | 9 W               |
| 911401529846 | SM378B R P9 PSD-TNW WB D100 G-TT PRO    | 9 W               |
| 911401529946 | SM378B R P12 PSD-TNW NB D100 G-TT PRO   | 13 W              |
| 911401530046 | SM378B R P12 PSD-TNW MB D100 G-TT PRO   | 13 W              |
| 911401530146 | SM378B R P12 PSD-TNW WB D100 G-TT PRO   | 13 W              |
| 911401530246 | SM378B R P15 PSD-TNW NB D100 G-TT PRO   | 15.5 W            |
| 911401530346 | SM378B R P15 PSD-TNW MB D100 G-TT PRO   | 15.5 W            |
| 911401530446 | SM378B R P15 PSD-TNW WB D100 G-TT PRO   | 15.5 W            |
| 911401530546 | SM378B R P22 PSD-TNW NB D100 G-TT PRO   | 22 W              |
| 911401530646 | SM378B R P22 PSD-TNW MB D100 G-TT PRO   | 22 W              |
| 911401530746 | SM378B R P22 PSD-TNW WB D100 G-TT PRO   | 22 W              |
| 911401500046 | RS378B P7 930 PSD-E WB M43 PRO          | 7.4 W             |
| 911401500146 | RS378B P7 940 PSD-E WB M43 PRO          | 7.4 W             |
| 911401500246 | RS378B P6 930 PSU-E MB M43 WP PRO       | 5.9 W             |
| 911401500346 | RS378B P6 930 PSU-E WB M43 WP PRO       | 5.9 W             |
| 911401500446 | RS378B P8 930 PSU-E MB M43 WP PRO       | 8 W               |
| 911401500546 | RS378B P8 930 PSU-E WB M43 WP PRO       | 8 W               |
| 911401520146 | RS378B P7 PSD-TNW NB M43 PRO            | 7.5 W             |
| 911401520246 | RS378B P7 PSD-TNW MB M43 PRO            | 7.5 W             |
| 911401520346 | RS378B P7 PSD-TNW WB M43 PRO            | 7.5 W             |
| 911401596945 | RS378B P6 927 PSU-E SNB M43 PRO         | 6.5 W             |

| Order Code   | Full Product Name               | Power Consumption |
|--------------|---------------------------------|-------------------|
| 911401597045 | RS378B P6 930 PSU-E SNB M43 PRO | 6.5 W             |
| 911401597145 | RS378B P6 940 PSU-E SNB M43 PRO | 6.5 W             |
| 911401597245 | RS378B P6 927 PSU-E NB M43 PRO  | 5.9 W             |
| 911401597345 | RS378B P6 930 PSU-E NB M43 PRO  | 5.9 W             |
| 911401597445 | RS378B P6 940 PSU-E NB M43 PRO  | 5.9 W             |
| 911401597545 | RS378B P6 927 PSU-E MB M43 PRO  | 5.9 W             |
| 911401597645 | RS378B P6 930 PSU-E MB M43 PRO  | 5.9 W             |
| 911401597745 | RS378B P6 940 PSU-E MB M43 PRO  | 5.9 W             |
| 911401597845 | RS378B P6 927 PSU-E WB M43 PRO  | 5.9 W             |
| 911401597945 | RS378B P6 930 PSU-E WB M43 PRO  | 5.9 W             |
| 911401598045 | RS378B P6 940 PSU-E WB M43 PRO  | 5.9 W             |
| 911401598145 | RS378B P8 927 PSU-E NB M43 PRO  | 8 W               |
| 911401598245 | RS378B P8 930 PSU-E NB M43 PRO  | 8 W               |
| 911401598345 | RS378B P8 940 PSU-E NB M43 PRO  | 8 W               |
| 911401598445 | RS378B P8 927 PSU-E MB M43 PRO  | 8 W               |
| 911401598545 | RS378B P8 930 PSU-E MB M43 PRO  | 8 W               |
| 911401598645 | RS378B P8 940 PSU-E MB M43 PRO  | 8 W               |
| 911401598745 | RS378B P8 927 PSU-E WB M43 PRO  | 8 W               |
| 911401598845 | RS378B P8 930 PSU-E WB M43 PRO  | 8 W               |
| 911401598945 | RS378B P8 940 PSU-E WB M43 PRO  | 8 W               |
| 911401599045 | RS378B P7 927 PSD-E SNB M43 PRO | 7.5 W             |
| 911401599145 | RS378B P7 930 PSD-E SNB M43 PRO | 7.5 W             |
| 911401599245 | RS378B P7 940 PSD-E SNB M43 PRO | 7.5 W             |
| 911401599345 | RS378B P7 927 PSD-E NB M43 PRO  | 7.4 W             |
| 911401599445 | RS378B P7 930 PSD-E NB M43 PRO  | 7.4 W             |
| 911401599545 | RS378B P7 940 PSD-E NB M43 PRO  | 7.4 W             |
| 911401599645 | RS378B P7 927 PSD-E MB M43 PRO  | 7.4 W             |
| 911401599745 | RS378B P7 930 PSD-E MB M43 PRO  | 7.4 W             |
| 911401599845 | RS378B P7 940 PSD-E MB M43 PRO  | 7.4 W             |
| 911401599945 | RS378B P7 927 PSD-E WB M43 PRO  | 7.4 W             |
| 911401500646 | RS378B P7 927 PSU-E SNB M55 PRO | 7.2 W             |
| 911401500746 | RS378B P7 930 PSU-E SNB M55 PRO | 7.2 W             |
| 911401500846 | RS378B P7 940 PSU-E SNB M55 PRO | 7.2 W             |
| 911401500946 | RS378B P7 927 PSU-E NB M55 PRO  | 7.1 W             |
| 911401501046 | RS378B P7 930 PSU-E NB M55 PRO  | 7.1 W             |
| 911401501146 | RS378B P7 940 PSU-E NB M55 PRO  | 7.1 W             |
| 911401501246 | RS378B P7 927 PSU-E MB M55 PRO  | 7.1 W             |
| 911401501346 | RS378B P7 930 PSU-E MB M55 PRO  | 7.1 W             |
| 911401501446 | RS378B P7 940 PSU-E MB M55 PRO  | 7.1 W             |
| 911401501546 | RS378B P7 927 PSU-E WB M55 PRO  | 7.1 W             |
| 911401501646 | RS378B P7 930 PSU-E WB M55 PRO  | 7.1 W             |
| 911401501746 | RS378B P7 940 PSU-E WB M55 PRO  | 7.1 W             |
| 911401501846 | RS378B P8 927 PSU-E SNB M55 PRO | 8 W               |
| 911401501946 | RS378B P8 930 PSU-E SNB M55 PRO | 8 W               |
| 911401502046 | RS378B P8 940 PSU-E SNB M55 PRO | 8 W               |
| 911401502146 | RS378B P9 927 PSU-E NB M55 PRO  | 9 W               |
| 911401502246 | RS378B P9 930 PSU-E NB M55 PRO  | 9 W               |
| 911401502346 | RS378B P9 940 PSU-E NB M55 PRO  | 9 W               |
| 911401502446 | RS378B P9 927 PSU-E MB M55 PRO  | 9 W               |
| 911401502546 | RS378B P9 930 PSU-E MB M55 PRO  | 9 W               |
| 911401502646 | RS378B P9 940 PSU-E MB M55 PRO  | 9 W               |
| 911401502746 | RS378B P9 927 PSU-E WB M55 PRO  | 9 W               |

| Order Code   | Full Product Name                   | Power Consumption |
|--------------|-------------------------------------|-------------------|
| 911401502846 | RS378B P9 930 PSU-E WB M55 PRO      | 9 W               |
| 911401502946 | RS378B P9 940 PSU-E WB M55 PRO      | 9 W               |
| 911401504846 | RS378B P7 927 PSD-E SNB M55 PRO     | 7.5 W             |
| 911401504946 | RS378B P7 930 PSD-E SNB M55 PRO     | 7.5 W             |
| 911401505046 | RS378B P7 940 PSD-E SNB M55 PRO     | 7.5 W             |
| 911401505146 | RS378B P7 927 PSD-E NB M55 PRO      | 7.3 W             |
| 911401505246 | RS378B P7 930 PSD-E NB M55 PRO      | 7.3 W             |
| 911401505346 | RS378B P7 940 PSD-E NB M55 PRO      | 7.3 W             |
| 911401505446 | RS378B P7 927 PSD-E MB M55 PRO      | 7.3 W             |
| 911401505546 | RS378B P7 930 PSD-E MB M55 PRO      | 7.3 W             |
| 911401505646 | RS378B P7 940 PSD-E MB M55 PRO      | 7.3 W             |
| 911401505746 | RS378B P7 927 PSD-E WB M55 PRO      | 7.3 W             |
| 911401505846 | RS378B P7 930 PSD-E WB M55 PRO      | 7.3 W             |
| 911401505946 | RS378B P7 940 PSD-E WB M55 PRO      | 7.3 W             |
| 911401506046 | RS378B P9 927 PSD-E NB M55 PRO      | 9.5 W             |
| 911401506146 | RS378B P9 930 PSD-E NB M55 PRO      | 9.5 W             |
| 911401506246 | RS378B P9 940 PSD-E NB M55 PRO      | 9.5 W             |
| 911401506346 | RS378B P9 927 PSD-E MB M55 PRO      | 9.5 W             |
| 911401506446 | RS378B P9 930 PSD-E MB M55 PRO      | 9.5 W             |
| 911401506546 | RS378B P9 940 PSD-E MB M55 PRO      | 9.5 W             |
| 911401506646 | RS378B P9 927 PSD-E WB M55 PRO      | 9.5 W             |
| 911401506746 | RS378B P9 930 PSD-E WB M55 PRO      | 9.5 W             |
| 911401506846 | RS378B P9 940 PSD-E WB M55 PRO      | 9.5 W             |
| 911401508746 | RS378X P9 930 WIA MB M55 PRO        | 8.7 W             |
| 911401508846 | RS378X P9 930 WIA WB M55 PRO        | 8.7 W             |
| 911401509346 | RS378B P7 930 PSU-E MB M55 WP PRO   | 7.1 W             |
| 911401509446 | RS378B P7 930 PSU-E WB M55 WP PRO   | 7.1 W             |
| 911401509546 | RS378B P9 930 PSU-E MB M55 WP PRO   | 9 W               |
| 911401509646 | RS378B P9 930 PSU-E WB M55 WP PRO   | 9 W               |
| 911401518946 | RS378B P7 PSD-TNW NB M55 PRO        | 7.1 W             |
| 911401519046 | RS378B P7 PSD-TNW MB M55 PRO        | 7.1 W             |
| 911401519146 | RS378B P7 PSD-TNW WB M55 PRO        | 7.1 W             |
| 911401519246 | RS378B P9 PSD-TNW NB M55 PRO        | 9 W               |
| 911401519346 | RS378B P9 PSD-TNW MB M55 PRO        | 9 W               |
| 911401519446 | RS378B P9 PSD-TNW WB M55 PRO        | 9 W               |
| 911401595145 | RS378B P3 927 PSU-E MB D35 G-TT PRO | 3.1 W             |
| 911401595245 | RS378B P3 930 PSU-E MB D35 G-TT PRO | 3.1 W             |
| 911401595345 | RS378B P3 940 PSU-E MB D35 G-TT PRO | 3.1 W             |
| 911401595445 | RS378B P3 927 PSU-E WB D35 G-TT PRO | 3.1 W             |
| 911401595545 | RS378B P3 930 PSU-E WB D35 G-TT PRO | 3.1 W             |
| 911401595645 | RS378B P3 940 PSU-E WB D35 G-TT PRO | 3.1 W             |
| 911401595745 | RS378B P5 927 PSU-E MB D35 G-TT PRO | 4.7 W             |
| 911401595845 | RS378B P5 930 PSU-E MB D35 G-TT PRO | 4.7 W             |
| 911401595945 | RS378B P5 940 PSU-E MB D35 G-TT PRO | 4.7 W             |
| 911401596045 | RS378B P5 927 PSU-E WB D35 G-TT PRO | 4.7 W             |
| 911401596145 | RS378B P5 930 PSU-E WB D35 G-TT PRO | 4.7 W             |
| 911401596245 | RS378B P5 940 PSU-E WB D35 G-TT PRO | 4.7 W             |
| 911401596345 | RS378B P5 927 PSD-E MB D35 G-TT PRO | 5.9 W             |
| 911401596445 | RS378B P5 930 PSD-E MB D35 G-TT PRO | 5.3 W             |
| 911401596545 | RS378B P5 940 PSD-E MB D35 G-TT PRO | 5.3 W             |
| 911401596645 | RS378B P5 927 PSD-E WB D35 G-TT PRO | 5.3 W             |
| 911401596745 | RS378B P5 930 PSD-E WB D35 G-TT PRO | 5.3 W             |

| Order Code   | Full Product Name                   | Power Consumption |
|--------------|-------------------------------------|-------------------|
| 911401596845 | RS378B P5 940 PSD-E WB D35 G-TT PRO | 5.3 W             |
| 911401510146 | RS378B P12 927 PSU-E NB M70 PRO     | 12 W              |
| 911401510246 | RS378B P12 930 PSU-E NB M70 PRO     | 12 W              |
| 911401510346 | RS378B P12 940 PSU-E NB M70 PRO     | 12 W              |
| 911401510446 | RS378B P12 927 PSU-E MB M70 PRO     | 12 W              |
| 911401510546 | RS378B P12 930 PSU-E MB M70 PRO     | 12 W              |
| 911401510646 | RS378B P12 940 PSU-E MB M70 PRO     | 12 W              |
| 911401510746 | RS378B P12 927 PSU-E WB M70 PRO     | 12 W              |
| 911401510846 | RS378B P12 930 PSU-E WB M70 PRO     | 12 W              |
| 911401510946 | RS378B P12 940 PSU-E WB M70 PRO     | 12 W              |
| 911401511046 | RS378B P17 927 PSU-E NB M70 PRO     | 17.5 W            |
| 911401511146 | RS378B P17 930 PSU-E NB M70 PRO     | 17.5 W            |
| 911401511246 | RS378B P17 940 PSU-E NB M70 PRO     | 17.5 W            |
| 911401511346 | RS378B P17 927 PSU-E MB M70 PRO     | 17.5 W            |
| 911401511446 | RS378B P17 930 PSU-E MB M70 PRO     | 17.5 W            |
| 911401511546 | RS378B P17 940 PSU-E MB M70 PRO     | 17.5 W            |
| 911401511646 | RS378B P17 927 PSU-E WB M70 PRO     | 17.5 W            |
| 911401511746 | RS378B P17 930 PSU-E WB M70 PRO     | 17.5 W            |
| 911401511846 | RS378B P17 940 PSU-E WB M70 PRO     | 17.5 W            |
| 911401511946 | RS378B P19 927 PSU-E NB M70 PRO     | 19.5 W            |
| 911401512046 | RS378B P19 930 PSU-E NB M70 PRO     | 19.5 W            |
| 911401512146 | RS378B P19 940 PSU-E NB M70 PRO     | 19.5 W            |
| 911401512246 | RS378B P19 927 PSU-E MB M70 PRO     | 19.5 W            |
| 911401512346 | RS378B P19 930 PSU-E MB M70 PRO     | 19.5 W            |
| 911401512446 | RS378B P19 940 PSU-E MB M70 PRO     | 19.5 W            |
| 911401512546 | RS378B P19 927 PSU-E WB M70 PRO     | 19.5 W            |
| 911401512646 | RS378B P19 930 PSU-E WB M70 PRO     | 19.5 W            |
| 911401512746 | RS378B P19 940 PSU-E WB M70 PRO     | 19.5 W            |
| 911401513746 | RS378B P12 927 PSD-E NB M70 PRO     | 12.8 W            |
| 911401513846 | RS378B P12 930 PSD-E NB M70 PRO     | 12.8 W            |
| 911401513946 | RS378B P12 940 PSD-E NB M70 PRO     | 12.8 W            |
| 911401514046 | RS378B P12 927 PSD-E MB M70 PRO     | 12.8 W            |
| 911401514146 | RS378B P12 930 PSD-E MB M70 PRO     | 12.8 W            |
| 911401514246 | RS378B P12 940 PSD-E MB M70 PRO     | 12.8 W            |
| 911401514346 | RS378B P12 927 PSD-E WB M70 PRO     | 12.8 W            |
| 911401514446 | RS378B P12 930 PSD-E WB M70 PRO     | 12.8 W            |
| 911401514546 | RS378B P12 940 PSD-E WB M70 PRO     | 12.8 W            |
| 911401514646 | RS378B P18 927 PSD-E NB M70 PRO     | 18.5 W            |
| 911401514746 | RS378B P18 930 PSD-E NB M70 PRO     | 18.5 W            |
| 911401514846 | RS378B P18 940 PSD-E NB M70 PRO     | 18.5 W            |
| 911401514946 | RS378B P18 927 PSD-E MB M70 PRO     | 18.5 W            |
| 911401515046 | RS378B P18 930 PSD-E MB M70 PRO     | 18.5 W            |
| 911401515146 | RS378B P18 940 PSD-E MB M70 PRO     | 18.5 W            |
| 911401515246 | RS378B P18 927 PSD-E WB M70 PRO     | 18.5 W            |
| 911401515346 | RS378B P18 930 PSD-E WB M70 PRO     | 18.5 W            |
| 911401515446 | RS378B P18 940 PSD-E WB M70 PRO     | 18.5 W            |
| 911401515546 | RS378B P20 927 PSD-E NB M70 PRO     | 20.5 W            |
| 911401515646 | RS378B P20 930 PSD-E NB M70 PRO     | 20.5 W            |
| 911401515746 | RS378B P20 940 PSD-E NB M70 PRO     | 20.5 W            |
| 911401515846 | RS378B P20 927 PSD-E MB M70 PRO     | 20.5 W            |
| 911401515946 | RS378B P20 930 PSD-E MB M70 PRO     | 20.5 W            |
| 911401516046 | RS378B P20 940 PSD-E MB M70 PRO     | 20.5 W            |

| Order Code   | Full Product Name                      | Power Consumption |
|--------------|----------------------------------------|-------------------|
| 911401516146 | RS378B P20 927 PSD-E WB M70 PRO        | 20.5 W            |
| 911401516246 | RS378B P20 930 PSD-E WB M70 PRO        | 20.5 W            |
| 911401516346 | RS378B P20 940 PSD-E WB M70 PRO        | 20.5 W            |
| 911401517346 | RS378X P12 930 WIA MB M70 PRO          | 12 W              |
| 911401517446 | RS378X P12 930 WIA WB M70 PRO          | 12 W              |
| 911401517546 | RS378X P19 930 WIA MB M70 PRO          | 20 W              |
| 911401517646 | RS378X P19 930 WIA WB M70 PRO          | 20 W              |
| 911401517746 | RS378X P18 930 WIA MB M70 PRO          | 18 W              |
| 911401517846 | RS378X P18 930 WIA WB M70 PRO          | 18 W              |
| 911401518146 | RS378B P12 930 PSU-E MB M70 WP PRO     | 12 W              |
| 911401518246 | RS378B P12 930 PSU-E WB M70 WP PRO     | 12 W              |
| 911401518346 | RS378B P17 930 PSU-E MB M70 WP PRO     | 17.5 W            |
| 911401518446 | RS378B P17 930 PSU-E WB M70 WP PRO     | 17.5 W            |
| 911401518546 | RS378B P19 930 PSU-E MB M70 WP PRO     | 19.5 W            |
| 911401518646 | RS378B P19 930 PSU-E WB M70 WP PRO     | 19.5 W            |
| 911401520446 | RS378B P13 PSD-TNW NB M70 PRO          | 13.5 W            |
| 911401520546 | RS378B P13 PSD-TNW MB M70 PRO          | 13.5 W            |
| 911401520646 | RS378B P13 PSD-TNW WB M70 PRO          | 13.5 W            |
| 911401520746 | RS378B P19 PSD-TNW NB M70 PRO          | 20 W              |
| 911401520846 | RS378B P19 PSD-TNW MB M70 PRO          | 20 W              |
| 911401520946 | RS378B P19 PSD-TNW WB M70 PRO          | 20 W              |
| 911401521046 | RS378B P22 PSD-TNW NB M70 PRO          | 22 W              |
| 911401521146 | RS378B P22 PSD-TNW MB M70 PRO          | 22 W              |
| 911401521246 | RS378B P22 PSD-TNW WB M70 PRO          | 22 W              |
| 911401512846 | RS378B P27 927 PSU-E NB M70 PRO        | 27.5 W            |
| 911401512946 | RS378B P27 930 PSU-E NB M70 PRO        | 27.5 W            |
| 911401513046 | RS378B P27 940 PSU-E NB M70 PRO        | 27.5 W            |
| 911401513146 | RS378B P27 927 PSU-E MB M70 PRO        | 27.5 W            |
| 911401513246 | RS378B P27 930 PSU-E MB M70 PRO        | 27.5 W            |
| 911401513346 | RS378B P27 940 PSU-E MB M70 PRO        | 27.5 W            |
| 911401513446 | RS378B P27 927 PSU-E WB M70 PRO        | 27.5 W            |
| 911401513546 | RS378B P27 930 PSU-E WB M70 PRO        | 27.5 W            |
| 911401513646 | RS378B P27 940 PSU-E WB M70 PRO        | 27.5 W            |
| 911401516446 | RS378B P27 927 PSD-E NB M70 PRO        | 27 W              |
| 911401516546 | RS378B P27 930 PSD-E NB M70 PRO        | 27 W              |
| 911401516646 | RS378B P27 940 PSD-E NB M70 PRO        | 27 W              |
| 911401516746 | RS378B P27 927 PSD-E MB M70 PRO        | 27 W              |
| 911401516846 | RS378B P27 930 PSD-E MB M70 PRO        | 27 W              |
| 911401516946 | RS378B P27 940 PSD-E MB M70 PRO        | 27 W              |
| 911401517046 | RS378B P27 927 PSD-E WB M70 PRO        | 27 W              |
| 911401517146 | RS378B P27 930 PSD-E WB M70 PRO        | 27 W              |
| 911401517246 | RS378B P27 940 PSD-E WB M70 PRO        | 27 W              |
| 911401517946 | RS378X P28 930 WIA MB M70 PRO          | 28.5 W            |
| 911401518046 | RS378X P28 930 WIA WB M70 PRO          | 28.5 W            |
| 911401518746 | RS378B P27 930 PSU-E MB M70 WP PRO     | 27.5 W            |
| 911401518846 | RS378B P27 930 PSU-E WB M70 WP PRO     | 27.5 W            |
| 911401521346 | RS378B P29 PSD-TNW NB M70 PRO          | 28 W              |
| 911401521446 | RS378B P29 PSD-TNW MB M70 PRO          | 28 W              |
| 911401521546 | RS378B P29 PSD-TNW WB M70 PRO          | 28 W              |
| 911401530846 | SM378B S P8 927 PSU-E NB D100 G-TT PRO | 7.8 W             |
| 911401530946 | SM378B S P8 930 PSU-E NB D100 G-TT PRO | 7.8 W             |
| 911401531046 | SM378B S P8 940 PSU-E NB D100 G-TT PRO | 7.8 W             |



| Order Code   | Full Product Name                       | Power Consumption |
|--------------|-----------------------------------------|-------------------|
| 911401531146 | SM378B S P8 927 PSU-E MB D100 G-TT PRO  | 7.8 W             |
| 911401531246 | SM378B S P8 930 PSU-E MB D100 G-TT PRO  | 7.8 W             |
| 911401531346 | SM378B S P8 940 PSU-E MB D100 G-TT PRO  | 7.8 W             |
| 911401531446 | SM378B S P8 927 PSU-E WB D100 G-TT PRO  | 7.8 W             |
| 911401531546 | SM378B S P8 930 PSU-E WB D100 G-TT PRO  | 7.8 W             |
| 911401531646 | SM378B S P8 940 PSU-E WB D100 G-TT PRO  | 7.8 W             |
| 911401531746 | SM378B S P11 927 PSU-E NB D100 G-TT PRO | 11.5 W            |
| 911401531846 | SM378B S P11 930 PSU-E NB D100 G-TT PRO | 11.5 W            |
| 911401531946 | SM378B S P11 940 PSU-E NB D100 G-TT PRO | 11.5 W            |
| 911401532046 | SM378B S P11 927 PSU-E MB D100 G-TT PRO | 11.5 W            |
| 911401532146 | SM378B S P11 930 PSU-E MB D100 G-TT PRO | 11.5 W            |
| 911401532246 | SM378B S P11 940 PSU-E MB D100 G-TT PRO | 11.5 W            |
| 911401532346 | SM378B S P11 927 PSU-E WB D100 G-TT PRO | 11.5 W            |
| 911401532446 | SM378B S P11 930 PSU-E WB D100 G-TT PRO | 11.5 W            |
| 911401532546 | SM378B S P11 940 PSU-E WB D100 G-TT PRO | 11.5 W            |
| 911401532646 | SM378B S P13 927 PSU-E NB D100 G-TT PRO | 13.5 W            |
| 911401532746 | SM378B S P13 930 PSU-E NB D100 G-TT PRO | 13.5 W            |
| 911401532846 | SM378B S P13 940 PSU-E NB D100 G-TT PRO | 13.5 W            |
| 911401532946 | SM378B S P13 927 PSU-E MB D100 G-TT PRO | 13.5 W            |
| 911401533046 | SM378B S P13 930 PSU-E MB D100 G-TT PRO | 13.5 W            |
| 911401533146 | SM378B S P13 940 PSU-E MB D100 G-TT PRO | 13.5 W            |
| 911401533246 | SM378B S P13 927 PSU-E WB D100 G-TT PRO | 13.5 W            |
| 911401533346 | SM378B S P13 930 PSU-E WB D100 G-TT PRO | 13.5 W            |
| 911401533446 | SM378B S P13 940 PSU-E WB D100 G-TT PRO | 13.5 W            |
| 911401533546 | SM378B S P20 927 PSU-E NB D100 G-TT PRO | 20 W              |
| 911401533646 | SM378B S P20 930 PSU-E NB D100 G-TT PRO | 20 W              |
| 911401533746 | SM378B S P20 940 PSU-E NB D100 G-TT PRO | 20 W              |
| 911401533846 | SM378B S P20 927 PSU-E MB D100 G-TT PRO | 20 W              |
| 911401533946 | SM378B S P20 930 PSU-E MB D100 G-TT PRO | 20 W              |
| 911401534046 | SM378B S P20 940 PSU-E MB D100 G-TT PRO | 20 W              |
| 911401534146 | SM378B S P20 927 PSU-E WB D100 G-TT PRO | 20 W              |
| 911401534246 | SM378B S P20 930 PSU-E WB D100 G-TT PRO | 20 W              |
| 911401534346 | SM378B S P20 940 PSU-E WB D100 G-TT PRO | 20 W              |
| 911401534446 | SM378B S P20 927 PSD-E NB D100 G-TT PRO | 20.5 W            |
| 911401534546 | SM378B S P20 930 PSD-E NB D100 G-TT PRO | 20.5 W            |
| 911401534646 | SM378B S P20 940 PSD-E NB D100 G-TT PRO | 20.5 W            |
| 911401534746 | SM378B S P20 927 PSD-E MB D100 G-TT PRO | 20.5 W            |
| 911401534846 | SM378B S P20 930 PSD-E MB D100 G-TT PRO | 20.5 W            |
| 911401534946 | SM378B S P20 940 PSD-E MB D100 G-TT PRO | 20.5 W            |
| 911401535046 | SM378B S P20 927 PSD-E WB D100 G-TT PRO | 20.5 W            |
| 911401535146 | SM378B S P20 930 PSD-E WB D100 G-TT PRO | 20.5 W            |
| 911401535246 | SM378B S P20 940 PSD-E WB D100 G-TT PRO | 20.5 W            |
| 911401535446 | SM378B S P8 927 PSD-E NB D100 G-TT PRO  | 9 W               |
| 911401535546 | SM378B S P8 930 PSD-E NB D100 G-TT PRO  | 9 W               |
| 911401535646 | SM378B S P8 940 PSD-E NB D100 G-TT PRO  | 9 W               |
| 911401535746 | SM378B S P8 927 PSD-E MB D100 G-TT PRO  | 9 W               |
| 911401535846 | SM378B S P8 930 PSD-E MB D100 G-TT PRO  | 9 W               |
| 911401535946 | SM378B S P8 940 PSD-E MB D100 G-TT PRO  | 9 W               |
| 911401536046 | SM378B S P8 927 PSD-E WB D100 G-TT PRO  | 9 W               |
| 911401536146 | SM378B S P8 930 PSD-E WB D100 G-TT PRO  | 9 W               |
| 911401536246 | SM378B S P8 940 PSD-E WB D100 G-TT PRO  | 9 W               |
| 911401536346 | SM378B S P12 927 PSD-E NB D100 G-TT PRO | 13 W              |

| Order Code   | Full Product Name                       | Power Consumption |
|--------------|-----------------------------------------|-------------------|
| 911401536446 | SM378B S P12 930 PSD-E NB D100 G-TT PRO | 13 W              |
| 911401536546 | SM378B S P12 940 PSD-E NB D100 G-TT PRO | 13 W              |
| 911401536646 | SM378B S P12 927 PSD-E MB D100 G-TT PRO | 13 W              |
| 911401536746 | SM378B S P12 930 PSD-E MB D100 G-TT PRO | 13 W              |
| 911401536846 | SM378B S P12 940 PSD-E MB D100 G-TT PRO | 13 W              |
| 911401536946 | SM378B S P12 927 PSD-E WB D100 G-TT PRO | 13 W              |
| 911401537046 | SM378B S P12 930 PSD-E WB D100 G-TT PRO | 13 W              |
| 911401537146 | SM378B S P12 940 PSD-E WB D100 G-TT PRO | 13 W              |
| 911401537246 | SM378B S P14 927 PSD-E NB D100 G-TT PRO | 14.5 W            |
| 911401537346 | SM378B S P14 930 PSD-E NB D100 G-TT PRO | 14.5 W            |
| 911401537446 | SM378B S P14 940 PSD-E NB D100 G-TT PRO | 14.5 W            |
| 911401537546 | SM378B S P14 927 PSD-E MB D100 G-TT PRO | 14.5 W            |
| 911401537646 | SM378B S P14 930 PSD-E MB D100 G-TT PRO | 14.5 W            |
| 911401537746 | SM378B S P14 940 PSD-E MB D100 G-TT PRO | 14.5 W            |
| 911401537846 | SM378B S P14 927 PSD-E WB D100 G-TT PRO | 14.5 W            |
| 911401537946 | SM378B S P14 930 PSD-E WB D100 G-TT PRO | 14.5 W            |
| 911401538046 | SM378B S P14 940 PSD-E WB D100 G-TT PRO | 14.5 W            |
| 911401538146 | SM378X S P8 930 WIA MB D100 G-TT PRO    | 8.2 W             |
| 911401538246 | SM378X S P8 930 WIA WB D100 G-TT PRO    | 8.2 W             |
| 911401538346 | SM378X S P12 930 WIA MB D100 G-TT PRO   | 12 W              |
| 911401538446 | SM378X S P12 930 WIA WB D100 G-TT PRO   | 12 W              |
| 911401538546 | SM378X S P14 930 WIA MB D100 G-TT PRO   | 14 W              |
| 911401538646 | SM378X S P14 930 WIA WB D100 G-TT PRO   | 14 W              |
| 911401538746 | SM378X S P20 930 WIA MB D100 G-TT PRO   | 20 W              |
| 911401538846 | SM378X S P20 930 WIA WB D100 G-TT PRO   | 20 W              |
| 911401538946 | SM378B S P9 PSD-TNW NB D100 G-TT PRO    | 9 W               |
| 911401539046 | SM378B S P9 PSD-TNW MB D100 G-TT PRO    | 9 W               |
| 911401539146 | SM378B S P9 PSD-TNW WB D100 G-TT PRO    | 9 W               |
| 911401539246 | SM378B S P12 PSD-TNW NB D100 G-TT PRO   | 13 W              |
| 911401539346 | SM378B S P12 PSD-TNW MB D100 G-TT PRO   | 13 W              |
| 911401539446 | SM378B S P12 PSD-TNW WB D100 G-TT PRO   | 13 W              |
| 911401539546 | SM378B S P15 PSD-TNW NB D100 G-TT PRO   | 15.5 W            |
| 911401539646 | SM378B S P15 PSD-TNW MB D100 G-TT PRO   | 15.5 W            |
| 911401539746 | SM378B S P15 PSD-TNW WB D100 G-TT PRO   | 15.5 W            |
| 911401539846 | SM378B S P22 PSD-TNW NB D100 G-TT PRO   | 22 W              |
| 911401539946 | SM378B S P22 PSD-TNW MB D100 G-TT PRO   | 22 W              |
| 911401540046 | SM378B S P22 PSD-TNW WB D100 G-TT PRO   | 22 W              |
| 911401503046 | RS378B P12 927 PSU-E NB M55 PRO         | 12.6 W            |
| 911401503146 | RS378B P12 930 PSU-E NB M55 PRO         | 12.6 W            |
| 911401503246 | RS378B P12 940 PSU-E NB M55 PRO         | 12.6 W            |
| 911401503346 | RS378B P12 927 PSU-E MB M55 PRO         | 12.6 W            |
| 911401503446 | RS378B P12 930 PSU-E MB M55 PRO         | 12.6 W            |
| 911401503546 | RS378B P12 940 PSU-E MB M55 PRO         | 12.6 W            |
| 911401503646 | RS378B P12 927 PSU-E WB M55 PRO         | 12.6 W            |
| 911401503746 | RS378B P12 930 PSU-E WB M55 PRO         | 12.6 W            |
| 911401503846 | RS378B P12 940 PSU-E WB M55 PRO         | 12.6 W            |
| 911401503946 | RS378B P14 927 PSU-E NB M55 PRO         | 14.5 W            |
| 911401504046 | RS378B P14 930 PSU-E NB M55 PRO         | 14.5 W            |
| 911401504146 | RS378B P14 940 PSU-E NB M55 PRO         | 14.5 W            |
| 911401504246 | RS378B P14 927 PSU-E MB M55 PRO         | 14.5 W            |
| 911401504346 | RS378B P14 930 PSU-E MB M55 PRO         | 14.5 W            |
| 911401504446 | RS378B P14 940 PSU-E MB M55 PRO         | 14.5 W            |



| Order Code   | Full Product Name               | Power Consumption |
|--------------|---------------------------------|-------------------|
| 911401504546 | RS378B P14 927 PSU-E WB M55 PRO | 14.5 W            |
| 911401504646 | RS378B P14 930 PSU-E WB M55 PRO | 14.5 W            |
| 911401504746 | RS378B P14 940 PSU-E WB M55 PRO | 14.5 W            |
| 911401506946 | RS378B P13 927 PSD-E NB M55 PRO | 13.5 W            |
| 911401507046 | RS378B P13 930 PSD-E NB M55 PRO | 13.5 W            |
| 911401507146 | RS378B P13 940 PSD-E NB M55 PRO | 13.5 W            |
| 911401507246 | RS378B P13 927 PSD-E MB M55 PRO | 13.5 W            |
| 911401507346 | RS378B P13 930 PSD-E MB M55 PRO | 13.5 W            |
| 911401507446 | RS378B P13 940 PSD-E MB M55 PRO | 13.5 W            |
| 911401507546 | RS378B P13 927 PSD-E WB M55 PRO | 13.5 W            |
| 911401507646 | RS378B P13 930 PSD-E WB M55 PRO | 13.5 W            |
| 911401507746 | RS378B P13 940 PSD-E WB M55 PRO | 13.5 W            |
| 911401507846 | RS378B P15 927 PSD-E NB M55 PRO | 15.5 W            |
| 911401507946 | RS378B P15 930 PSD-E NB M55 PRO | 15.5 W            |
| 911401508046 | RS378B P15 940 PSD-E NB M55 PRO | 15.5 W            |
| 911401508146 | RS378B P15 927 PSD-E MB M55 PRO | 15.5 W            |
| 911401508246 | RS378B P15 930 PSD-E MB M55 PRO | 15.5 W            |
| 911401508346 | RS378B P15 940 PSD-E MB M55 PRO | 15.5 W            |

| Order Code   | Full Product Name                  | Power Consumption |
|--------------|------------------------------------|-------------------|
| 911401508446 | RS378B P15 927 PSD-E WB M55 PRO    | 15.5 W            |
| 911401508546 | RS378B P15 930 PSD-E WB M55 PRO    | 15.5 W            |
| 911401508646 | RS378B P15 940 PSD-E WB M55 PRO    | 15.5 W            |
| 911401508946 | RS378X P12 930 WIA MB M55 PRO      | 12.8 W            |
| 911401509046 | RS378X P12 930 WIA WB M55 PRO      | 12.8 W            |
| 911401509146 | RS378X P14 930 WIA MB M55 PRO      | 15 W              |
| 911401509246 | RS378X P14 930 WIA WB M55 PRO      | 15 W              |
| 911401509746 | RS378B P12 930 PSU-E MB M55 WP PRO | 12.6 W            |
| 911401509846 | RS378B P12 930 PSU-E WB M55 WP PRO | 12.6 W            |
| 911401509946 | RS378B P14 930 PSU-E MB M55 WP PRO | 14.5 W            |
| 911401510046 | RS378B P14 930 PSU-E WB M55 WP PRO | 14.5 W            |
| 911401519546 | RS378B P13 PSD-TNW NB M55 PRO      | 13.5 W            |
| 911401519646 | RS378B P13 PSD-TNW MB M55 PRO      | 13.5 W            |
| 911401519746 | RS378B P13 PSD-TNW WB M55 PRO      | 13.5 W            |
| 911401519846 | RS378B P15 PSD-TNW NB M55 PRO      | 15 W              |
| 911401519946 | RS378B P15 PSD-TNW MB M55 PRO      | 15 W              |
| 911401520046 | RS378B P15 PSD-TNW WB M55 PRO      | 15 W              |

Controls and Dimming

| Order Code   | Full Product Name                       | Dimmable |
|--------------|-----------------------------------------|----------|
| 911401521646 | SM378B R P8 927 PSU-E NB D100 G-TT PRO  | -        |
| 911401521746 | SM378B R P8 930 PSU-E NB D100 G-TT PRO  | -        |
| 911401521846 | SM378B R P8 940 PSU-E NB D100 G-TT PRO  | -        |
| 911401521946 | SM378B R P8 927 PSU-E MB D100 G-TT PRO  | -        |
| 911401522046 | SM378B R P8 930 PSU-E MB D100 G-TT PRO  | -        |
| 911401522146 | SM378B R P8 940 PSU-E MB D100 G-TT PRO  | -        |
| 911401522246 | SM378B R P8 927 PSU-E WB D100 G-TT PRO  | -        |
| 911401522346 | SM378B R P8 930 PSU-E WB D100 G-TT PRO  | -        |
| 911401522446 | SM378B R P8 940 PSU-E WB D100 G-TT PRO  | -        |
| 911401522546 | SM378B R P11 927 PSU-E NB D100 G-TT PRO | -        |
| 911401522646 | SM378B R P11 930 PSU-E NB D100 G-TT PRO | -        |
| 911401522746 | SM378B R P11 940 PSU-E NB D100 G-TT PRO | -        |
| 911401522846 | SM378B R P11 927 PSU-E MB D100 G-TT PRO | -        |
| 911401522946 | SM378B R P11 930 PSU-E MB D100 G-TT PRO | -        |
| 911401523046 | SM378B R P11 940 PSU-E MB D100 G-TT PRO | -        |
| 911401523146 | SM378B R P11 927 PSU-E WB D100 G-TT PRO | -        |
| 911401523246 | SM378B R P11 930 PSU-E WB D100 G-TT PRO | -        |
| 911401523346 | SM378B R P11 940 PSU-E WB D100 G-TT PRO | -        |
| 911401523446 | SM378B R P13 927 PSU-E NB D100 G-TT PRO | -        |
| 911401523546 | SM378B R P13 930 PSU-E NB D100 G-TT PRO | -        |
| 911401523646 | SM378B R P13 940 PSU-E NB D100 G-TT PRO | -        |
| 911401523746 | SM378B R P13 927 PSU-E MB D100 G-TT PRO | -        |
| 911401523846 | SM378B R P13 930 PSU-E MB D100 G-TT PRO | -        |
| 911401523946 | SM378B R P13 940 PSU-E MB D100 G-TT PRO | -        |
| 911401524046 | SM378B R P13 927 PSU-E WB D100 G-TT PRO | -        |
| 911401524146 | SM378B R P13 930 PSU-E WB D100 G-TT PRO | -        |
| 911401524246 | SM378B R P13 940 PSU-E WB D100 G-TT PRO | -        |
| 911401524346 | SM378B R P20 927 PSU-E NB D100 G-TT PRO | -        |
| 911401524446 | SM378B R P20 930 PSU-E NB D100 G-TT PRO | -        |
| 911401524546 | SM378B R P20 940 PSU-E NB D100 G-TT PRO | -        |

| Order Code   | Full Product Name                       | Dimmable |
|--------------|-----------------------------------------|----------|
| 911401524646 | SM378B R P20 927 PSU-E MB D100 G-TT PRO | -        |
| 911401524746 | SM378B R P20 930 PSU-E MB D100 G-TT PRO | -        |
| 911401524846 | SM378B R P20 940 PSU-E MB D100 G-TT PRO | -        |
| 911401524946 | SM378B R P20 927 PSU-E WB D100 G-TT PRO | -        |
| 911401525046 | SM378B R P20 930 PSU-E WB D100 G-TT PRO | -        |
| 911401525146 | SM378B R P20 940 PSU-E WB D100 G-TT PRO | -        |
| 911401525246 | SM378B R P20 927 PSD-E NB D100 G-TT PRO | DALI     |
| 911401525346 | SM378B R P20 930 PSD-E NB D100 G-TT PRO | DALI     |
| 911401525446 | SM378B R P20 940 PSD-E NB D100 G-TT PRO | DALI     |
| 911401525546 | SM378B R P20 927 PSD-E MB D100 G-TT PRO | DALI     |
| 911401525646 | SM378B R P20 930 PSD-E MB D100 G-TT PRO | DALI     |
| 911401525746 | SM378B R P20 940 PSD-E MB D100 G-TT PRO | DALI     |
| 911401525846 | SM378B R P20 927 PSD-E WB D100 G-TT PRO | DALI     |
| 911401525946 | SM378B R P20 930 PSD-E WB D100 G-TT PRO | DALI     |
| 911401526046 | SM378B R P20 940 PSD-E WB D100 G-TT PRO | DALI     |
| 911401526146 | SM378B R P8 927 PSD-E NB D100 G-TT PRO  | DALI     |
| 911401526246 | SM378B R P8 930 PSD-E NB D100 G-TT PRO  | DALI     |
| 911401526346 | SM378B R P8 940 PSD-E NB D100 G-TT PRO  | DALI     |
| 911401526446 | SM378B R P8 927 PSD-E MB D100 G-TT PRO  | DALI     |
| 911401526546 | SM378B R P8 930 PSD-E MB D100 G-TT PRO  | DALI     |
| 911401526646 | SM378B R P8 940 PSD-E MB D100 G-TT PRO  | DALI     |
| 911401526746 | SM378B R P8 927 PSD-E WB D100 G-TT PRO  | DALI     |
| 911401526846 | SM378B R P8 930 PSD-E WB D100 G-TT PRO  | DALI     |
| 911401526946 | SM378B R P8 940 PSD-E WB D100 G-TT PRO  | DALI     |
| 911401527046 | SM378B R P12 927 PSD-E NB D100 G-TT PRO | DALI     |
| 911401527146 | SM378B R P12 930 PSD-E NB D100 G-TT PRO | DALI     |
| 911401527246 | SM378B R P12 940 PSD-E NB D100 G-TT PRO | DALI     |
| 911401527346 | SM378B R P12 927 PSD-E MB D100 G-TT PRO | DALI     |
| 911401527446 | SM378B R P12 930 PSD-E MB D100 G-TT PRO | DALI     |
| 911401527546 | SM378B R P12 940 PSD-E MB D100 G-TT PRO | DALI     |

| Order Code   | Full Product Name                       | Dimmable     |
|--------------|-----------------------------------------|--------------|
| 911401527646 | SM378B R P12 927 PSD-E WB D100 G-TT PRO | DALI         |
| 911401527746 | SM378B R P12 930 PSD-E WB D100 G-TT PRO | DALI         |
| 911401527846 | SM378B R P12 940 PSD-E WB D100 G-TT PRO | DALI         |
| 911401527946 | SM378B R P14 927 PSD-E NB D100 G-TT PRO | DALI         |
| 911401528046 | SM378B R P14 930 PSD-E NB D100 G-TT PRO | DALI         |
| 911401528146 | SM378B R P14 940 PSD-E NB D100 G-TT PRO | DALI         |
| 911401528246 | SM378B R P14 927 PSD-E MB D100 G-TT PRO | DALI         |
| 911401528346 | SM378B R P14 930 PSD-E MB D100 G-TT PRO | DALI         |
| 911401528446 | SM378B R P14 940 PSD-E MB D100 G-TT PRO | DALI         |
| 911401528546 | SM378B R P14 927 PSD-E WB D100 G-TT PRO | DALI         |
| 911401528646 | SM378B R P14 930 PSD-E WB D100 G-TT PRO | DALI         |
| 911401528746 | SM378B R P14 940 PSD-E WB D100 G-TT PRO | DALI         |
| 911401528846 | SM378X R P8 930 WIA MB D100 G-TT PRO    | Wireless Dim |
| 911401528946 | SM378X R P8 930 WIA WB D100 G-TT PRO    | Wireless Dim |
| 911401529046 | SM378X R P12 930 WIA MB D100 G-TT PRO   | Wireless Dim |
| 911401529146 | SM378X R P12 930 WIA WB D100 G-TT PRO   | Wireless Dim |
| 911401529246 | SM378X R P14 930 WIA MB D100 G-TT PRO   | Wireless Dim |
| 911401529346 | SM378X R P14 930 WIA WB D100 G-TT PRO   | Wireless Dim |
| 911401529446 | SM378X R P20 930 WIA MB D100 G-TT PRO   | Wireless Dim |
| 911401529546 | SM378X R P20 930 WIA WB D100 G-TT PRO   | Wireless Dim |
| 911401529646 | SM378B R P9 PSD-TNW NB D100 G-TT PRO    | DALI         |
| 911401529746 | SM378B R P9 PSD-TNW MB D100 G-TT PRO    | DALI         |
| 911401529846 | SM378B R P9 PSD-TNW WB D100 G-TT PRO    | DALI         |
| 911401529946 | SM378B R P12 PSD-TNW NB D100 G-TT PRO   | DALI         |
| 911401530046 | SM378B R P12 PSD-TNW MB D100 G-TT PRO   | DALI         |
| 911401530146 | SM378B R P12 PSD-TNW WB D100 G-TT PRO   | DALI         |
| 911401530246 | SM378B R P15 PSD-TNW NB D100 G-TT PRO   | DALI         |
| 911401530346 | SM378B R P15 PSD-TNW MB D100 G-TT PRO   | DALI         |
| 911401530446 | SM378B R P15 PSD-TNW WB D100 G-TT PRO   | DALI         |
| 911401530546 | SM378B R P22 PSD-TNW NB D100 G-TT PRO   | DALI         |
| 911401530646 | SM378B R P22 PSD-TNW MB D100 G-TT PRO   | DALI         |
| 911401530746 | SM378B R P22 PSD-TNW WB D100 G-TT PRO   | DALI         |
| 911401500046 | RS378B P7 930 PSD-E WB M43 PRO          | DALI         |
| 911401500146 | RS378B P7 940 PSD-E WB M43 PRO          | DALI         |
| 911401500246 | RS378B P6 930 PSU-E MB M43 WP PRO       | -            |
| 911401500346 | RS378B P6 930 PSU-E WB M43 WP PRO       | -            |
| 911401500446 | RS378B P8 930 PSU-E MB M43 WP PRO       | -            |
| 911401500546 | RS378B P8 930 PSU-E WB M43 WP PRO       | -            |
| 911401520146 | RS378B P7 PSD-TNW NB M43 PRO            | DALI         |
| 911401520246 | RS378B P7 PSD-TNW MB M43 PRO            | DALI         |
| 911401520346 | RS378B P7 PSD-TNW WB M43 PRO            | DALI         |
| 911401596945 | RS378B P6 927 PSU-E SNB M43 PRO         | -            |
| 911401597045 | RS378B P6 930 PSU-E SNB M43 PRO         | -            |
| 911401597145 | RS378B P6 940 PSU-E SNB M43 PRO         | -            |
| 911401597245 | RS378B P6 927 PSU-E NB M43 PRO          | -            |
| 911401597345 | RS378B P6 930 PSU-E NB M43 PRO          | -            |
| 911401597445 | RS378B P6 940 PSU-E NB M43 PRO          | -            |
| 911401597545 | RS378B P6 927 PSU-E MB M43 PRO          | -            |
| 911401597645 | RS378B P6 930 PSU-E MB M43 PRO          | -            |
| 911401597745 | RS378B P6 940 PSU-E MB M43 PRO          | -            |
| 911401597845 | RS378B P6 927 PSU-E WB M43 PRO          | -            |
| 911401597945 | RS378B P6 930 PSU-E WB M43 PRO          | -            |

| Order Code   | Full Product Name               | Dimmable |
|--------------|---------------------------------|----------|
| 911401598045 | RS378B P6 940 PSU-E WB M43 PRO  | -        |
| 911401598145 | RS378B P8 927 PSU-E NB M43 PRO  | -        |
| 911401598245 | RS378B P8 930 PSU-E NB M43 PRO  | -        |
| 911401598345 | RS378B P8 940 PSU-E NB M43 PRO  | -        |
| 911401598445 | RS378B P8 927 PSU-E MB M43 PRO  | -        |
| 911401598545 | RS378B P8 930 PSU-E MB M43 PRO  | -        |
| 911401598645 | RS378B P8 940 PSU-E MB M43 PRO  | -        |
| 911401598745 | RS378B P8 927 PSU-E WB M43 PRO  | -        |
| 911401598845 | RS378B P8 930 PSU-E WB M43 PRO  | -        |
| 911401598945 | RS378B P8 940 PSU-E WB M43 PRO  | -        |
| 911401599045 | RS378B P7 927 PSD-E SNB M43 PRO | DALI     |
| 911401599145 | RS378B P7 930 PSD-E SNB M43 PRO | DALI     |
| 911401599245 | RS378B P7 940 PSD-E SNB M43 PRO | DALI     |
| 911401599345 | RS378B P7 927 PSD-E NB M43 PRO  | DALI     |
| 911401599445 | RS378B P7 930 PSD-E NB M43 PRO  | DALI     |
| 911401599545 | RS378B P7 940 PSD-E NB M43 PRO  | DALI     |
| 911401599645 | RS378B P7 927 PSD-E MB M43 PRO  | DALI     |
| 911401599745 | RS378B P7 930 PSD-E MB M43 PRO  | DALI     |
| 911401599845 | RS378B P7 940 PSD-E MB M43 PRO  | DALI     |
| 911401599945 | RS378B P7 927 PSD-E WB M43 PRO  | DALI     |
| 911401500646 | RS378B P7 927 PSU-E SNB M55 PRO | -        |
| 911401500746 | RS378B P7 930 PSU-E SNB M55 PRO | -        |
| 911401500846 | RS378B P7 940 PSU-E SNB M55 PRO | -        |
| 911401500946 | RS378B P7 927 PSU-E NB M55 PRO  | -        |
| 911401501046 | RS378B P7 930 PSU-E NB M55 PRO  | -        |
| 911401501146 | RS378B P7 940 PSU-E NB M55 PRO  | -        |
| 911401501246 | RS378B P7 927 PSU-E MB M55 PRO  | -        |
| 911401501346 | RS378B P7 930 PSU-E MB M55 PRO  | -        |
| 911401501446 | RS378B P7 940 PSU-E MB M55 PRO  | -        |
| 911401501546 | RS378B P7 927 PSU-E WB M55 PRO  | -        |
| 911401501646 | RS378B P7 930 PSU-E WB M55 PRO  | -        |
| 911401501746 | RS378B P7 940 PSU-E WB M55 PRO  | -        |
| 911401501846 | RS378B P8 927 PSU-E SNB M55 PRO | -        |
| 911401501946 | RS378B P8 930 PSU-E SNB M55 PRO | -        |
| 911401502046 | RS378B P8 940 PSU-E SNB M55 PRO | -        |
| 911401502146 | RS378B P9 927 PSU-E NB M55 PRO  | -        |
| 911401502246 | RS378B P9 930 PSU-E NB M55 PRO  | -        |
| 911401502346 | RS378B P9 940 PSU-E NB M55 PRO  | -        |
| 911401502446 | RS378B P9 927 PSU-E MB M55 PRO  | -        |
| 911401502546 | RS378B P9 930 PSU-E MB M55 PRO  | -        |
| 911401502646 | RS378B P9 940 PSU-E MB M55 PRO  | -        |
| 911401502746 | RS378B P9 927 PSU-E WB M55 PRO  | -        |
| 911401502846 | RS378B P9 930 PSU-E WB M55 PRO  | -        |
| 911401502946 | RS378B P9 940 PSU-E WB M55 PRO  | -        |
| 911401504846 | RS378B P7 927 PSD-E SNB M55 PRO | DALI     |
| 911401504946 | RS378B P7 930 PSD-E SNB M55 PRO | DALI     |
| 911401505046 | RS378B P7 940 PSD-E SNB M55 PRO | DALI     |
| 911401505146 | RS378B P7 927 PSD-E NB M55 PRO  | DALI     |
| 911401505246 | RS378B P7 930 PSD-E NB M55 PRO  | DALI     |
| 911401505346 | RS378B P7 940 PSD-E NB M55 PRO  | DALI     |
| 911401505446 | RS378B P7 927 PSD-E MB M55 PRO  | DALI     |
| 911401505546 | RS378B P7 930 PSD-E MB M55 PRO  | DALI     |

| Order Code   | Full Product Name                   | Dimmable     |
|--------------|-------------------------------------|--------------|
| 911401505646 | RS378B P7 940 PSD-E MB M55 PRO      | DALI         |
| 911401505746 | RS378B P7 927 PSD-E WB M55 PRO      | DALI         |
| 911401505846 | RS378B P7 930 PSD-E WB M55 PRO      | DALI         |
| 911401505946 | RS378B P7 940 PSD-E WB M55 PRO      | DALI         |
| 911401506046 | RS378B P9 927 PSD-E NB M55 PRO      | DALI         |
| 911401506146 | RS378B P9 930 PSD-E NB M55 PRO      | DALI         |
| 911401506246 | RS378B P9 940 PSD-E NB M55 PRO      | DALI         |
| 911401506346 | RS378B P9 927 PSD-E MB M55 PRO      | DALI         |
| 911401506446 | RS378B P9 930 PSD-E MB M55 PRO      | DALI         |
| 911401506546 | RS378B P9 940 PSD-E MB M55 PRO      | DALI         |
| 911401506646 | RS378B P9 927 PSD-E WB M55 PRO      | DALI         |
| 911401506746 | RS378B P9 930 PSD-E WB M55 PRO      | DALI         |
| 911401506846 | RS378B P9 940 PSD-E WB M55 PRO      | DALI         |
| 911401508746 | RS378X P9 930 WIA MB M55 PRO        | Wireless Dim |
| 911401508846 | RS378X P9 930 WIA WB M55 PRO        | Wireless Dim |
| 911401509346 | RS378B P7 930 PSU-E MB M55 WP PRO   | -            |
| 911401509446 | RS378B P7 930 PSU-E WB M55 WP PRO   | -            |
| 911401509546 | RS378B P9 930 PSU-E MB M55 WP PRO   | -            |
| 911401509646 | RS378B P9 930 PSU-E WB M55 WP PRO   | -            |
| 911401518946 | RS378B P7 PSD-TNW NB M55 PRO        | DALI         |
| 911401519046 | RS378B P7 PSD-TNW MB M55 PRO        | DALI         |
| 911401519146 | RS378B P7 PSD-TNW WB M55 PRO        | DALI         |
| 911401519246 | RS378B P9 PSD-TNW NB M55 PRO        | DALI         |
| 911401519346 | RS378B P9 PSD-TNW MB M55 PRO        | DALI         |
| 911401519446 | RS378B P9 PSD-TNW WB M55 PRO        | DALI         |
| 911401595145 | RS378B P3 927 PSU-E MB D35 G-TT PRO | -            |
| 911401595245 | RS378B P3 930 PSU-E MB D35 G-TT PRO | -            |
| 911401595345 | RS378B P3 940 PSU-E MB D35 G-TT PRO | -            |
| 911401595445 | RS378B P3 927 PSU-E WB D35 G-TT PRO | -            |
| 911401595545 | RS378B P3 930 PSU-E WB D35 G-TT PRO | -            |
| 911401595645 | RS378B P3 940 PSU-E WB D35 G-TT PRO | -            |
| 911401595745 | RS378B P5 927 PSU-E MB D35 G-TT PRO | -            |
| 911401595845 | RS378B P5 930 PSU-E MB D35 G-TT PRO | -            |
| 911401595945 | RS378B P5 940 PSU-E MB D35 G-TT PRO | -            |
| 911401596045 | RS378B P5 927 PSU-E WB D35 G-TT PRO | -            |
| 911401596145 | RS378B P5 930 PSU-E WB D35 G-TT PRO | -            |
| 911401596245 | RS378B P5 940 PSU-E WB D35 G-TT PRO | -            |
| 911401596345 | RS378B P5 927 PSD-E MB D35 G-TT PRO | DALI         |
| 911401596445 | RS378B P5 930 PSD-E MB D35 G-TT PRO | DALI         |
| 911401596545 | RS378B P5 940 PSD-E MB D35 G-TT PRO | DALI         |
| 911401596645 | RS378B P5 927 PSD-E WB D35 G-TT PRO | DALI         |
| 911401596745 | RS378B P5 930 PSD-E WB D35 G-TT PRO | DALI         |
| 911401596845 | RS378B P5 940 PSD-E WB D35 G-TT PRO | DALI         |
| 911401510146 | RS378B P12 927 PSU-E NB M70 PRO     | -            |
| 911401510246 | RS378B P12 930 PSU-E NB M70 PRO     | -            |
| 911401510346 | RS378B P12 940 PSU-E NB M70 PRO     | -            |
| 911401510446 | RS378B P12 927 PSU-E MB M70 PRO     | -            |
| 911401510546 | RS378B P12 930 PSU-E MB M70 PRO     | -            |
| 911401510646 | RS378B P12 940 PSU-E MB M70 PRO     | -            |
| 911401510746 | RS378B P12 927 PSU-E WB M70 PRO     | -            |
| 911401510846 | RS378B P12 930 PSU-E WB M70 PRO     | -            |
| 911401510946 | RS378B P12 940 PSU-E WB M70 PRO     | -            |

| Order Code   | Full Product Name                  | Dimmable     |
|--------------|------------------------------------|--------------|
| 911401511046 | RS378B P17 927 PSU-E NB M70 PRO    | -            |
| 911401511146 | RS378B P17 930 PSU-E NB M70 PRO    | -            |
| 911401511246 | RS378B P17 940 PSU-E NB M70 PRO    | -            |
| 911401511346 | RS378B P17 927 PSU-E MB M70 PRO    | -            |
| 911401511446 | RS378B P17 930 PSU-E MB M70 PRO    | -            |
| 911401511546 | RS378B P17 940 PSU-E MB M70 PRO    | -            |
| 911401511646 | RS378B P17 927 PSU-E WB M70 PRO    | -            |
| 911401511746 | RS378B P17 930 PSU-E WB M70 PRO    | -            |
| 911401511846 | RS378B P17 940 PSU-E WB M70 PRO    | -            |
| 911401511946 | RS378B P19 927 PSU-E NB M70 PRO    | -            |
| 911401512046 | RS378B P19 930 PSU-E NB M70 PRO    | -            |
| 911401512146 | RS378B P19 940 PSU-E NB M70 PRO    | -            |
| 911401512246 | RS378B P19 927 PSU-E MB M70 PRO    | -            |
| 911401512346 | RS378B P19 930 PSU-E MB M70 PRO    | -            |
| 911401512446 | RS378B P19 940 PSU-E MB M70 PRO    | -            |
| 911401512546 | RS378B P19 927 PSU-E WB M70 PRO    | -            |
| 911401512646 | RS378B P19 930 PSU-E WB M70 PRO    | -            |
| 911401512746 | RS378B P19 940 PSU-E WB M70 PRO    | -            |
| 911401513746 | RS378B P12 927 PSD-E NB M70 PRO    | DALI         |
| 911401513846 | RS378B P12 930 PSD-E NB M70 PRO    | DALI         |
| 911401513946 | RS378B P12 940 PSD-E NB M70 PRO    | DALI         |
| 911401514046 | RS378B P12 927 PSD-E MB M70 PRO    | DALI         |
| 911401514146 | RS378B P12 930 PSD-E MB M70 PRO    | DALI         |
| 911401514246 | RS378B P12 940 PSD-E MB M70 PRO    | DALI         |
| 911401514346 | RS378B P12 927 PSD-E WB M70 PRO    | DALI         |
| 911401514446 | RS378B P12 930 PSD-E WB M70 PRO    | DALI         |
| 911401514546 | RS378B P12 940 PSD-E WB M70 PRO    | DALI         |
| 911401514646 | RS378B P18 927 PSD-E NB M70 PRO    | DALI         |
| 911401514746 | RS378B P18 930 PSD-E NB M70 PRO    | DALI         |
| 911401514846 | RS378B P18 940 PSD-E NB M70 PRO    | DALI         |
| 911401514946 | RS378B P18 927 PSD-E MB M70 PRO    | DALI         |
| 911401515046 | RS378B P18 930 PSD-E MB M70 PRO    | DALI         |
| 911401515146 | RS378B P18 940 PSD-E MB M70 PRO    | DALI         |
| 911401515246 | RS378B P18 927 PSD-E WB M70 PRO    | DALI         |
| 911401515346 | RS378B P18 930 PSD-E WB M70 PRO    | DALI         |
| 911401515446 | RS378B P18 940 PSD-E WB M70 PRO    | DALI         |
| 911401515546 | RS378B P20 927 PSD-E NB M70 PRO    | DALI         |
| 911401515646 | RS378B P20 930 PSD-E NB M70 PRO    | DALI         |
| 911401515746 | RS378B P20 940 PSD-E NB M70 PRO    | DALI         |
| 911401515846 | RS378B P20 927 PSD-E MB M70 PRO    | DALI         |
| 911401515946 | RS378B P20 930 PSD-E MB M70 PRO    | DALI         |
| 911401516046 | RS378B P20 940 PSD-E MB M70 PRO    | DALI         |
| 911401516146 | RS378B P20 927 PSD-E WB M70 PRO    | DALI         |
| 911401516246 | RS378B P20 930 PSD-E WB M70 PRO    | DALI         |
| 911401516346 | RS378B P20 940 PSD-E WB M70 PRO    | DALI         |
| 911401517346 | RS378X P12 930 WIA MB M70 PRO      | Wireless Dim |
| 911401517446 | RS378X P12 930 WIA WB M70 PRO      | Wireless Dim |
| 911401517546 | RS378X P19 930 WIA MB M70 PRO      | Wireless Dim |
| 911401517646 | RS378X P19 930 WIA WB M70 PRO      | Wireless Dim |
| 911401517746 | RS378X P18 930 WIA MB M70 PRO      | Wireless Dim |
| 911401517846 | RS378X P18 930 WIA WB M70 PRO      | Wireless Dim |
| 911401518146 | RS378B P12 930 PSU-E MB M70 WP PRO | -            |

| Order Code   | Full Product Name                       | Dimmable     |
|--------------|-----------------------------------------|--------------|
| 911401518246 | RS378B P12 930 PSU-E WB M70 WP PRO      | -            |
| 911401518346 | RS378B P17 930 PSU-E MB M70 WP PRO      | -            |
| 911401518446 | RS378B P17 930 PSU-E WB M70 WP PRO      | -            |
| 911401518546 | RS378B P19 930 PSU-E MB M70 WP PRO      | -            |
| 911401518646 | RS378B P19 930 PSU-E WB M70 WP PRO      | -            |
| 911401520446 | RS378B P13 PSD-TNW NB M70 PRO           | DALI         |
| 911401520546 | RS378B P13 PSD-TNW MB M70 PRO           | DALI         |
| 911401520646 | RS378B P13 PSD-TNW WB M70 PRO           | DALI         |
| 911401520746 | RS378B P19 PSD-TNW NB M70 PRO           | DALI         |
| 911401520846 | RS378B P19 PSD-TNW MB M70 PRO           | DALI         |
| 911401520946 | RS378B P19 PSD-TNW WB M70 PRO           | DALI         |
| 911401521046 | RS378B P22 PSD-TNW NB M70 PRO           | DALI         |
| 911401521146 | RS378B P22 PSD-TNW MB M70 PRO           | DALI         |
| 911401521246 | RS378B P22 PSD-TNW WB M70 PRO           | DALI         |
| 911401512846 | RS378B P27 927 PSU-E NB M70 PRO         | -            |
| 911401512946 | RS378B P27 930 PSU-E NB M70 PRO         | -            |
| 911401513046 | RS378B P27 940 PSU-E NB M70 PRO         | -            |
| 911401513146 | RS378B P27 927 PSU-E MB M70 PRO         | -            |
| 911401513246 | RS378B P27 930 PSU-E MB M70 PRO         | -            |
| 911401513346 | RS378B P27 940 PSU-E MB M70 PRO         | -            |
| 911401513446 | RS378B P27 927 PSU-E WB M70 PRO         | -            |
| 911401513546 | RS378B P27 930 PSU-E WB M70 PRO         | -            |
| 911401513646 | RS378B P27 940 PSU-E WB M70 PRO         | -            |
| 911401516446 | RS378B P27 927 PSD-E NB M70 PRO         | DALI         |
| 911401516546 | RS378B P27 930 PSD-E NB M70 PRO         | DALI         |
| 911401516646 | RS378B P27 940 PSD-E NB M70 PRO         | DALI         |
| 911401516746 | RS378B P27 927 PSD-E MB M70 PRO         | DALI         |
| 911401516846 | RS378B P27 930 PSD-E MB M70 PRO         | DALI         |
| 911401516946 | RS378B P27 940 PSD-E MB M70 PRO         | DALI         |
| 911401517046 | RS378B P27 927 PSD-E WB M70 PRO         | DALI         |
| 911401517146 | RS378B P27 930 PSD-E WB M70 PRO         | DALI         |
| 911401517246 | RS378B P27 940 PSD-E WB M70 PRO         | DALI         |
| 911401517946 | RS378X P28 930 WIA MB M70 PRO           | Wireless Dim |
| 911401518046 | RS378X P28 930 WIA WB M70 PRO           | Wireless Dim |
| 911401518746 | RS378B P27 930 PSU-E MB M70 WP PRO      | -            |
| 911401518846 | RS378B P27 930 PSU-E WB M70 WP PRO      | -            |
| 911401521346 | RS378B P29 PSD-TNW NB M70 PRO           | DALI         |
| 911401521446 | RS378B P29 PSD-TNW MB M70 PRO           | DALI         |
| 911401521546 | RS378B P29 PSD-TNW WB M70 PRO           | DALI         |
| 911401530846 | SM378B S P8 927 PSU-E NB D100 G-TT PRO  | -            |
| 911401530946 | SM378B S P8 930 PSU-E NB D100 G-TT PRO  | -            |
| 911401531046 | SM378B S P8 940 PSU-E NB D100 G-TT PRO  | -            |
| 911401531146 | SM378B S P8 927 PSU-E MB D100 G-TT PRO  | -            |
| 911401531246 | SM378B S P8 930 PSU-E MB D100 G-TT PRO  | -            |
| 911401531346 | SM378B S P8 940 PSU-E MB D100 G-TT PRO  | -            |
| 911401531446 | SM378B S P8 927 PSU-E WB D100 G-TT PRO  | -            |
| 911401531546 | SM378B S P8 930 PSU-E WB D100 G-TT PRO  | -            |
| 911401531646 | SM378B S P8 940 PSU-E WB D100 G-TT PRO  | -            |
| 911401531746 | SM378B S P11 927 PSU-E NB D100 G-TT PRO | -            |
| 911401531846 | SM378B S P11 930 PSU-E NB D100 G-TT PRO | -            |
| 911401531946 | SM378B S P11 940 PSU-E NB D100 G-TT PRO | -            |
| 911401532046 | SM378B S P11 927 PSU-E MB D100 G-TT PRO | -            |

| Order Code   | Full Product Name                       | Dimmable |
|--------------|-----------------------------------------|----------|
| 911401532146 | SM378B S P11 930 PSU-E MB D100 G-TT PRO | -        |
| 911401532246 | SM378B S P11 940 PSU-E MB D100 G-TT PRO | -        |
| 911401532346 | SM378B S P11 927 PSU-E WB D100 G-TT PRO | -        |
| 911401532446 | SM378B S P11 930 PSU-E WB D100 G-TT PRO | -        |
| 911401532546 | SM378B S P11 940 PSU-E WB D100 G-TT PRO | -        |
| 911401532646 | SM378B S P13 927 PSU-E NB D100 G-TT PRO | -        |
| 911401532746 | SM378B S P13 930 PSU-E NB D100 G-TT PRO | -        |
| 911401532846 | SM378B S P13 940 PSU-E NB D100 G-TT PRO | -        |
| 911401532946 | SM378B S P13 927 PSU-E MB D100 G-TT PRO | -        |
| 911401533046 | SM378B S P13 930 PSU-E MB D100 G-TT PRO | -        |
| 911401533146 | SM378B S P13 940 PSU-E MB D100 G-TT PRO | -        |
| 911401533246 | SM378B S P13 927 PSU-E WB D100 G-TT PRO | -        |
| 911401533346 | SM378B S P13 930 PSU-E WB D100 G-TT PRO | -        |
| 911401533446 | SM378B S P13 940 PSU-E WB D100 G-TT PRO | -        |
| 911401533546 | SM378B S P20 927 PSU-E NB D100 G-TT PRO | -        |
| 911401533646 | SM378B S P20 930 PSU-E NB D100 G-TT PRO | -        |
| 911401533746 | SM378B S P20 940 PSU-E NB D100 G-TT PRO | -        |
| 911401533846 | SM378B S P20 927 PSU-E MB D100 G-TT PRO | -        |
| 911401533946 | SM378B S P20 930 PSU-E MB D100 G-TT PRO | -        |
| 911401534046 | SM378B S P20 940 PSU-E MB D100 G-TT PRO | -        |
| 911401534146 | SM378B S P20 927 PSU-E WB D100 G-TT PRO | -        |
| 911401534246 | SM378B S P20 930 PSU-E WB D100 G-TT PRO | -        |
| 911401534346 | SM378B S P20 940 PSU-E WB D100 G-TT PRO | -        |
| 911401534446 | SM378B S P20 927 PSD-E NB D100 G-TT PRO | DALI     |
| 911401534546 | SM378B S P20 930 PSD-E NB D100 G-TT PRO | DALI     |
| 911401534646 | SM378B S P20 940 PSD-E NB D100 G-TT PRO | DALI     |
| 911401534746 | SM378B S P20 927 PSD-E MB D100 G-TT PRO | DALI     |
| 911401534846 | SM378B S P20 930 PSD-E MB D100 G-TT PRO | DALI     |
| 911401534946 | SM378B S P20 940 PSD-E MB D100 G-TT PRO | DALI     |
| 911401535046 | SM378B S P20 927 PSD-E WB D100 G-TT PRO | DALI     |
| 911401535146 | SM378B S P20 930 PSD-E WB D100 G-TT PRO | DALI     |
| 911401535246 | SM378B S P20 940 PSD-E WB D100 G-TT PRO | DALI     |
| 911401535446 | SM378B S P8 927 PSD-E NB D100 G-TT PRO  | DALI     |
| 911401535546 | SM378B S P8 930 PSD-E NB D100 G-TT PRO  | DALI     |
| 911401535646 | SM378B S P8 940 PSD-E NB D100 G-TT PRO  | DALI     |
| 911401535746 | SM378B S P8 927 PSD-E MB D100 G-TT PRO  | DALI     |
| 911401535846 | SM378B S P8 930 PSD-E MB D100 G-TT PRO  | DALI     |
| 911401535946 | SM378B S P8 940 PSD-E MB D100 G-TT PRO  | DALI     |
| 911401536046 | SM378B S P8 927 PSD-E WB D100 G-TT PRO  | DALI     |
| 911401536146 | SM378B S P8 930 PSD-E WB D100 G-TT PRO  | DALI     |
| 911401536246 | SM378B S P8 940 PSD-E WB D100 G-TT PRO  | DALI     |
| 911401536346 | SM378B S P12 927 PSD-E NB D100 G-TT PRO | DALI     |
| 911401536446 | SM378B S P12 930 PSD-E NB D100 G-TT PRO | DALI     |
| 911401536546 | SM378B S P12 940 PSD-E NB D100 G-TT PRO | DALI     |
| 911401536646 | SM378B S P12 927 PSD-E MB D100 G-TT PRO | DALI     |
| 911401536746 | SM378B S P12 930 PSD-E MB D100 G-TT PRO | DALI     |
| 911401536846 | SM378B S P12 940 PSD-E MB D100 G-TT PRO | DALI     |
| 911401536946 | SM378B S P12 927 PSD-E WB D100 G-TT PRO | DALI     |
| 911401537046 | SM378B S P12 930 PSD-E WB D100 G-TT PRO | DALI     |
| 911401537146 | SM378B S P12 940 PSD-E WB D100 G-TT PRO | DALI     |
| 911401537246 | SM378B S P14 927 PSD-E NB D100 G-TT PRO | DALI     |
| 911401537346 | SM378B S P14 930 PSD-E NB D100 G-TT PRO | DALI     |

| Order Code   | Full Product Name                       | Dimmable     |
|--------------|-----------------------------------------|--------------|
| 911401537446 | SM378B S P14 940 PSD-E NB D100 G-TT PRO | DALI         |
| 911401537546 | SM378B S P14 927 PSD-E MB D100 G-TT PRO | DALI         |
| 911401537646 | SM378B S P14 930 PSD-E MB D100 G-TT PRO | DALI         |
| 911401537746 | SM378B S P14 940 PSD-E MB D100 G-TT PRO | DALI         |
| 911401537846 | SM378B S P14 927 PSD-E WB D100 G-TT PRO | DALI         |
| 911401537946 | SM378B S P14 930 PSD-E WB D100 G-TT PRO | DALI         |
| 911401538046 | SM378B S P14 940 PSD-E WB D100 G-TT PRO | DALI         |
| 911401538146 | SM378X S P8 930 WIA MB D100 G-TT PRO    | Wireless Dim |
| 911401538246 | SM378X S P8 930 WIA WB D100 G-TT PRO    | Wireless Dim |
| 911401538346 | SM378X S P12 930 WIA MB D100 G-TT PRO   | Wireless Dim |
| 911401538446 | SM378X S P12 930 WIA WB D100 G-TT PRO   | Wireless Dim |
| 911401538546 | SM378X S P14 930 WIA MB D100 G-TT PRO   | Wireless Dim |
| 911401538646 | SM378X S P14 930 WIA WB D100 G-TT PRO   | Wireless Dim |
| 911401538746 | SM378X S P20 930 WIA MB D100 G-TT PRO   | Wireless Dim |
| 911401538846 | SM378X S P20 930 WIA WB D100 G-TT PRO   | Wireless Dim |
| 911401538946 | SM378B S P9 PSD-TNW NB D100 G-TT PRO    | DALI         |
| 911401539046 | SM378B S P9 PSD-TNW MB D100 G-TT PRO    | DALI         |
| 911401539146 | SM378B S P9 PSD-TNW WB D100 G-TT PRO    | DALI         |
| 911401539246 | SM378B S P12 PSD-TNW NB D100 G-TT PRO   | DALI         |
| 911401539346 | SM378B S P12 PSD-TNW MB D100 G-TT PRO   | DALI         |
| 911401539446 | SM378B S P12 PSD-TNW WB D100 G-TT PRO   | DALI         |
| 911401539546 | SM378B S P15 PSD-TNW NB D100 G-TT PRO   | DALI         |
| 911401539646 | SM378B S P15 PSD-TNW MB D100 G-TT PRO   | DALI         |
| 911401539746 | SM378B S P15 PSD-TNW WB D100 G-TT PRO   | DALI         |
| 911401539846 | SM378B S P22 PSD-TNW NB D100 G-TT PRO   | DALI         |
| 911401539946 | SM378B S P22 PSD-TNW MB D100 G-TT PRO   | DALI         |
| 911401540046 | SM378B S P22 PSD-TNW WB D100 G-TT PRO   | DALI         |
| 911401503046 | RS378B P12 927 PSU-E NB M55 PRO         | -            |
| 911401503146 | RS378B P12 930 PSU-E NB M55 PRO         | -            |
| 911401503246 | RS378B P12 940 PSU-E NB M55 PRO         | -            |
| 911401503346 | RS378B P12 927 PSU-E MB M55 PRO         | -            |
| 911401503446 | RS378B P12 930 PSU-E MB M55 PRO         | -            |
| 911401503546 | RS378B P12 940 PSU-E MB M55 PRO         | -            |
| 911401503646 | RS378B P12 927 PSU-E WB M55 PRO         | -            |
| 911401503746 | RS378B P12 930 PSU-E WB M55 PRO         | -            |
| 911401503846 | RS378B P12 940 PSU-E WB M55 PRO         | -            |
| 911401503946 | RS378B P14 927 PSU-E NB M55 PRO         | -            |
| 911401504046 | RS378B P14 930 PSU-E NB M55 PRO         | -            |
| 911401504146 | RS378B P14 940 PSU-E NB M55 PRO         | -            |

| Order Code   | Full Product Name                  | Dimmable     |
|--------------|------------------------------------|--------------|
| 911401504246 | RS378B P14 927 PSU-E MB M55 PRO    | -            |
| 911401504346 | RS378B P14 930 PSU-E MB M55 PRO    | -            |
| 911401504446 | RS378B P14 940 PSU-E MB M55 PRO    | -            |
| 911401504546 | RS378B P14 927 PSU-E WB M55 PRO    | -            |
| 911401504646 | RS378B P14 930 PSU-E WB M55 PRO    | -            |
| 911401504746 | RS378B P14 940 PSU-E WB M55 PRO    | -            |
| 911401506946 | RS378B P13 927 PSD-E NB M55 PRO    | DALI         |
| 911401507046 | RS378B P13 930 PSD-E NB M55 PRO    | DALI         |
| 911401507146 | RS378B P13 940 PSD-E NB M55 PRO    | DALI         |
| 911401507246 | RS378B P13 927 PSD-E MB M55 PRO    | DALI         |
| 911401507346 | RS378B P13 930 PSD-E MB M55 PRO    | DALI         |
| 911401507446 | RS378B P13 940 PSD-E MB M55 PRO    | DALI         |
| 911401507546 | RS378B P13 927 PSD-E WB M55 PRO    | DALI         |
| 911401507646 | RS378B P13 930 PSD-E WB M55 PRO    | DALI         |
| 911401507746 | RS378B P13 940 PSD-E WB M55 PRO    | DALI         |
| 911401507846 | RS378B P15 927 PSD-E NB M55 PRO    | DALI         |
| 911401507946 | RS378B P15 930 PSD-E NB M55 PRO    | DALI         |
| 911401508046 | RS378B P15 940 PSD-E NB M55 PRO    | DALI         |
| 911401508146 | RS378B P15 927 PSD-E MB M55 PRO    | DALI         |
| 911401508246 | RS378B P15 930 PSD-E MB M55 PRO    | DALI         |
| 911401508346 | RS378B P15 940 PSD-E MB M55 PRO    | DALI         |
| 911401508446 | RS378B P15 927 PSD-E WB M55 PRO    | DALI         |
| 911401508546 | RS378B P15 930 PSD-E WB M55 PRO    | DALI         |
| 911401508646 | RS378B P15 940 PSD-E WB M55 PRO    | DALI         |
| 911401508946 | RS378X P12 930 WIA MB M55 PRO      | Wireless Dim |
| 911401509046 | RS378X P12 930 WIA WB M55 PRO      | Wireless Dim |
| 911401509146 | RS378X P14 930 WIA MB M55 PRO      | Wireless Dim |
| 911401509246 | RS378X P14 930 WIA WB M55 PRO      | Wireless Dim |
| 911401509746 | RS378B P12 930 PSU-E MB M55 WP PRO | -            |
| 911401509846 | RS378B P12 930 PSU-E WB M55 WP PRO | -            |
| 911401509946 | RS378B P14 930 PSU-E MB M55 WP PRO | -            |
| 911401510046 | RS378B P14 930 PSU-E WB M55 WP PRO | -            |
| 911401519546 | RS378B P13 PSD-TNW NB M55 PRO      | DALI         |
| 911401519646 | RS378B P13 PSD-TNW MB M55 PRO      | DALI         |
| 911401519746 | RS378B P13 PSD-TNW WB M55 PRO      | DALI         |
| 911401519846 | RS378B P15 PSD-TNW NB M55 PRO      | DALI         |
| 911401519946 | RS378B P15 PSD-TNW MB M55 PRO      | DALI         |
| 911401520046 | RS378B P15 PSD-TNW WB M55 PRO      | DALI         |

Mechanical and Housing

| Order Code   | Full Product Name                      | Ingress protection code |
|--------------|----------------------------------------|-------------------------|
| 911401521646 | SM378B R P8 927 PSU-E NB D100 G-TT PRO | IP20                    |
| 911401521746 | SM378B R P8 930 PSU-E NB D100 G-TT PRO | IP20                    |
| 911401521846 | SM378B R P8 940 PSU-E NB D100 G-TT PRO | IP20                    |
| 911401521946 | SM378B R P8 927 PSU-E MB D100 G-TT PRO | IP20                    |
| 911401522046 | SM378B R P8 930 PSU-E MB D100 G-TT PRO | IP20                    |
| 911401522146 | SM378B R P8 940 PSU-E MB D100 G-TT PRO | IP20                    |
| 911401522246 | SM378B R P8 927 PSU-E WB D100 G-TT PRO | IP20                    |
| 911401522346 | SM378B R P8 930 PSU-E WB D100 G-TT PRO | IP20                    |

| Order Code   | Full Product Name                       | Ingress protection code |
|--------------|-----------------------------------------|-------------------------|
| 911401522446 | SM378B R P8 940 PSU-E WB D100 G-TT PRO  | IP20                    |
| 911401522546 | SM378B R P11 927 PSU-E NB D100 G-TT PRO | IP20                    |
| 911401522646 | SM378B R P11 930 PSU-E NB D100 G-TT PRO | IP20                    |
| 911401522746 | SM378B R P11 940 PSU-E NB D100 G-TT PRO | IP20                    |
| 911401522846 | SM378B R P11 927 PSU-E MB D100 G-TT PRO | IP20                    |
| 911401522946 | SM378B R P11 930 PSU-E MB D100 G-TT PRO | IP20                    |
| 911401523046 | SM378B R P11 940 PSU-E MB D100 G-TT PRO | IP20                    |
| 911401523146 | SM378B R P11 927 PSU-E WB D100 G-TT PRO | IP20                    |



| Order Code   | Full Product Name                       | Ingress protection<br>code |
|--------------|-----------------------------------------|----------------------------|
| 911401523246 | SM378B R P11 930 PSU-E WB D100 G-TT PRO | IP20                       |
| 911401523346 | SM378B R P11 940 PSU-E WB D100 G-TT PRO | IP20                       |
| 911401523446 | SM378B R P13 927 PSU-E NB D100 G-TT PRO | IP20                       |
| 911401523546 | SM378B R P13 930 PSU-E NB D100 G-TT PRO | IP20                       |
| 911401523646 | SM378B R P13 940 PSU-E NB D100 G-TT PRO | IP20                       |
| 911401523746 | SM378B R P13 927 PSU-E MB D100 G-TT PRO | IP20                       |
| 911401523846 | SM378B R P13 930 PSU-E MB D100 G-TT PRO | IP20                       |
| 911401523946 | SM378B R P13 940 PSU-E MB D100 G-TT PRO | IP20                       |
| 911401524046 | SM378B R P13 927 PSU-E WB D100 G-TT PRO | IP20                       |
| 911401524146 | SM378B R P13 930 PSU-E WB D100 G-TT PRO | IP20                       |
| 911401524246 | SM378B R P13 940 PSU-E WB D100 G-TT PRO | IP20                       |
| 911401524346 | SM378B R P20 927 PSU-E NB D100 G-TT PRO | IP20                       |
| 911401524446 | SM378B R P20 930 PSU-E NB D100 G-TT PRO | IP20                       |
| 911401524546 | SM378B R P20 940 PSU-E NB D100 G-TT PRO | IP20                       |
| 911401524646 | SM378B R P20 927 PSU-E MB D100 G-TT PRO | IP20                       |
| 911401524746 | SM378B R P20 930 PSU-E MB D100 G-TT PRO | IP20                       |
| 911401524846 | SM378B R P20 940 PSU-E MB D100 G-TT PRO | IP20                       |
| 911401524946 | SM378B R P20 927 PSU-E WB D100 G-TT PRO | IP20                       |
| 911401525046 | SM378B R P20 930 PSU-E WB D100 G-TT PRO | IP20                       |
| 911401525146 | SM378B R P20 940 PSU-E WB D100 G-TT PRO | IP20                       |
| 911401525246 | SM378B R P20 927 PSD-E NB D100 G-TT PRO | IP20                       |
| 911401525346 | SM378B R P20 930 PSD-E NB D100 G-TT PRO | IP20                       |
| 911401525446 | SM378B R P20 940 PSD-E NB D100 G-TT PRO | IP20                       |
| 911401525546 | SM378B R P20 927 PSD-E MB D100 G-TT PRO | IP20                       |
| 911401525646 | SM378B R P20 930 PSD-E MB D100 G-TT PRO | IP20                       |
| 911401525746 | SM378B R P20 940 PSD-E MB D100 G-TT PRO | IP20                       |
| 911401525846 | SM378B R P20 927 PSD-E WB D100 G-TT PRO | IP20                       |
| 911401525946 | SM378B R P20 930 PSD-E WB D100 G-TT PRO | IP20                       |
| 911401526046 | SM378B R P20 940 PSD-E WB D100 G-TT PRO | IP20                       |
| 911401526146 | SM378B R P8 927 PSD-E NB D100 G-TT PRO  | IP20                       |
| 911401526246 | SM378B R P8 930 PSD-E NB D100 G-TT PRO  | IP20                       |
| 911401526346 | SM378B R P8 940 PSD-E NB D100 G-TT PRO  | IP20                       |
| 911401526446 | SM378B R P8 927 PSD-E MB D100 G-TT PRO  | IP20                       |
| 911401526546 | SM378B R P8 930 PSD-E MB D100 G-TT PRO  | IP20                       |
| 911401526646 | SM378B R P8 940 PSD-E MB D100 G-TT PRO  | IP20                       |
| 911401526746 | SM378B R P8 927 PSD-E WB D100 G-TT PRO  | IP20                       |
| 911401526846 | SM378B R P8 930 PSD-E WB D100 G-TT PRO  | IP20                       |
| 911401526946 | SM378B R P8 940 PSD-E WB D100 G-TT PRO  | IP20                       |
| 911401527046 | SM378B R P12 927 PSD-E NB D100 G-TT PRO | IP20                       |
| 911401527146 | SM378B R P12 930 PSD-E NB D100 G-TT PRO | IP20                       |
| 911401527246 | SM378B R P12 940 PSD-E NB D100 G-TT PRO | IP20                       |
| 911401527346 | SM378B R P12 927 PSD-E MB D100 G-TT PRO | IP20                       |
| 911401527446 | SM378B R P12 930 PSD-E MB D100 G-TT PRO | IP20                       |
| 911401527546 | SM378B R P12 940 PSD-E MB D100 G-TT PRO | IP20                       |
| 911401527646 | SM378B R P12 927 PSD-E WB D100 G-TT PRO | IP20                       |
| 911401527746 | SM378B R P12 930 PSD-E WB D100 G-TT PRO | IP20                       |
| 911401527846 | SM378B R P12 940 PSD-E WB D100 G-TT PRO | IP20                       |
| 911401527946 | SM378B R P14 927 PSD-E NB D100 G-TT PRO | IP20                       |
| 911401528046 | SM378B R P14 930 PSD-E NB D100 G-TT PRO | IP20                       |
| 911401528146 | SM378B R P14 940 PSD-E NB D100 G-TT PRO | IP20                       |
| 911401528246 | SM378B R P14 927 PSD-E MB D100 G-TT PRO | IP20                       |

| Order Code   | Full Product Name                       | Ingress protection<br>code |
|--------------|-----------------------------------------|----------------------------|
| 911401528346 | SM378B R P14 930 PSD-E MB D100 G-TT PRO | IP20                       |
| 911401528446 | SM378B R P14 940 PSD-E MB D100 G-TT PRO | IP20                       |
| 911401528546 | SM378B R P14 927 PSD-E WB D100 G-TT PRO | IP20                       |
| 911401528646 | SM378B R P14 930 PSD-E WB D100 G-TT PRO | IP20                       |
| 911401528746 | SM378B R P14 940 PSD-E WB D100 G-TT PRO | IP20                       |
| 911401528846 | SM378X R P8 930 WIA MB D100 G-TT PRO    | IP20                       |
| 911401528946 | SM378X R P8 930 WIA WB D100 G-TT PRO    | IP20                       |
| 911401529046 | SM378X R P12 930 WIA MB D100 G-TT PRO   | IP20                       |
| 911401529146 | SM378X R P12 930 WIA WB D100 G-TT PRO   | IP20                       |
| 911401529246 | SM378X R P14 930 WIA MB D100 G-TT PRO   | IP20                       |
| 911401529346 | SM378X R P14 930 WIA WB D100 G-TT PRO   | IP20                       |
| 911401529446 | SM378X R P20 930 WIA MB D100 G-TT PRO   | IP20                       |
| 911401529546 | SM378X R P20 930 WIA WB D100 G-TT PRO   | IP20                       |
| 911401529646 | SM378B R P9 PSD-TNW NB D100 G-TT PRO    | IP20                       |
| 911401529746 | SM378B R P9 PSD-TNW MB D100 G-TT PRO    | IP20                       |
| 911401529846 | SM378B R P9 PSD-TNW WB D100 G-TT PRO    | IP20                       |
| 911401529946 | SM378B R P12 PSD-TNW NB D100 G-TT PRO   | IP20                       |
| 911401530046 | SM378B R P12 PSD-TNW MB D100 G-TT PRO   | IP20                       |
| 911401530146 | SM378B R P12 PSD-TNW WB D100 G-TT PRO   | IP20                       |
| 911401530246 | SM378B R P15 PSD-TNW NB D100 G-TT PRO   | IP20                       |
| 911401530346 | SM378B R P15 PSD-TNW MB D100 G-TT PRO   | IP20                       |
| 911401530446 | SM378B R P15 PSD-TNW WB D100 G-TT PRO   | IP20                       |
| 911401530546 | SM378B R P22 PSD-TNW NB D100 G-TT PRO   | IP20                       |
| 911401530646 | SM378B R P22 PSD-TNW MB D100 G-TT PRO   | IP20                       |
| 911401530746 | SM378B R P22 PSD-TNW WB D100 G-TT PRO   | IP20                       |
| 911401500046 | RS378B P7 930 PSD-E WB M43 PRO          | IP20                       |
| 911401500146 | RS378B P7 940 PSD-E WB M43 PRO          | IP20                       |
| 911401500246 | RS378B P6 930 PSU-E MB M43 WP PRO       | IP20/54                    |
| 911401500346 | RS378B P6 930 PSU-E WB M43 WP PRO       | IP20/54                    |
| 911401500446 | RS378B P8 930 PSU-E MB M43 WP PRO       | IP20/54                    |
| 911401500546 | RS378B P8 930 PSU-E WB M43 WP PRO       | IP20/54                    |
| 911401520146 | RS378B P7 PSD-TNW NB M43 PRO            | IP20                       |
| 911401520246 | RS378B P7 PSD-TNW MB M43 PRO            | IP20                       |
| 911401520346 | RS378B P7 PSD-TNW WB M43 PRO            | IP20                       |
| 911401596945 | RS378B P6 927 PSU-E SNB M43 PRO         | IP20                       |
| 911401597045 | RS378B P6 930 PSU-E SNB M43 PRO         | IP20                       |
| 911401597145 | RS378B P6 940 PSU-E SNB M43 PRO         | IP20                       |
| 911401597245 | RS378B P6 927 PSU-E NB M43 PRO          | IP20                       |
| 911401597345 | RS378B P6 930 PSU-E NB M43 PRO          | IP20                       |
| 911401597445 | RS378B P6 940 PSU-E NB M43 PRO          | IP20                       |
| 911401597545 | RS378B P6 927 PSU-E MB M43 PRO          | IP20                       |
| 911401597645 | RS378B P6 930 PSU-E MB M43 PRO          | IP20                       |
| 911401597745 | RS378B P6 940 PSU-E MB M43 PRO          | IP20                       |
| 911401597845 | RS378B P6 927 PSU-E WB M43 PRO          | IP20                       |
| 911401597945 | RS378B P6 930 PSU-E WB M43 PRO          | IP20                       |
| 911401598045 | RS378B P6 940 PSU-E WB M43 PRO          | IP20                       |
| 911401598145 | RS378B P8 927 PSU-E NB M43 PRO          | IP20                       |
| 911401598245 | RS378B P8 930 PSU-E NB M43 PRO          | IP20                       |
| 911401598345 | RS378B P8 940 PSU-E NB M43 PRO          | IP20                       |
| 911401598445 | RS378B P8 927 PSU-E MB M43 PRO          | IP20                       |
| 911401598545 | RS378B P8 930 PSU-E MB M43 PRO          | IP20                       |

| Order Code   | Full Product Name               | Ingress protection<br>code |
|--------------|---------------------------------|----------------------------|
| 911401598645 | RS378B P8 940 PSU-E MB M43 PRO  | IP20                       |
| 911401598745 | RS378B P8 927 PSU-E WB M43 PRO  | IP20                       |
| 911401598845 | RS378B P8 930 PSU-E WB M43 PRO  | IP20                       |
| 911401598945 | RS378B P8 940 PSU-E WB M43 PRO  | IP20                       |
| 911401599045 | RS378B P7 927 PSD-E SNB M43 PRO | IP20                       |
| 911401599145 | RS378B P7 930 PSD-E SNB M43 PRO | IP20                       |
| 911401599245 | RS378B P7 940 PSD-E SNB M43 PRO | IP20                       |
| 911401599345 | RS378B P7 927 PSD-E NB M43 PRO  | IP20                       |
| 911401599445 | RS378B P7 930 PSD-E NB M43 PRO  | IP20                       |
| 911401599545 | RS378B P7 940 PSD-E NB M43 PRO  | IP20                       |
| 911401599645 | RS378B P7 927 PSD-E MB M43 PRO  | IP20                       |
| 911401599745 | RS378B P7 930 PSD-E MB M43 PRO  | IP20                       |
| 911401599845 | RS378B P7 940 PSD-E MB M43 PRO  | IP20                       |
| 911401599945 | RS378B P7 927 PSD-E WB M43 PRO  | IP20                       |
| 911401500646 | RS378B P7 927 PSU-E SNB M55 PRO | IP20                       |
| 911401500746 | RS378B P7 930 PSU-E SNB M55 PRO | IP20                       |
| 911401500846 | RS378B P7 940 PSU-E SNB M55 PRO | IP20                       |
| 911401500946 | RS378B P7 927 PSU-E NB M55 PRO  | IP20                       |
| 911401501046 | RS378B P7 930 PSU-E NB M55 PRO  | IP20                       |
| 911401501146 | RS378B P7 940 PSU-E NB M55 PRO  | IP20                       |
| 911401501246 | RS378B P7 927 PSU-E MB M55 PRO  | IP20                       |
| 911401501346 | RS378B P7 930 PSU-E MB M55 PRO  | IP20                       |
| 911401501446 | RS378B P7 940 PSU-E MB M55 PRO  | IP20                       |
| 911401501546 | RS378B P7 927 PSU-E WB M55 PRO  | IP20                       |
| 911401501646 | RS378B P7 930 PSU-E WB M55 PRO  | IP20                       |
| 911401501746 | RS378B P7 940 PSU-E WB M55 PRO  | IP20                       |
| 911401501846 | RS378B P8 927 PSU-E SNB M55 PRO | IP20                       |
| 911401501946 | RS378B P8 930 PSU-E SNB M55 PRO | IP20                       |
| 911401502046 | RS378B P8 940 PSU-E SNB M55 PRO | IP20                       |
| 911401502146 | RS378B P9 927 PSU-E NB M55 PRO  | IP20                       |
| 911401502246 | RS378B P9 930 PSU-E NB M55 PRO  | IP20                       |
| 911401502346 | RS378B P9 940 PSU-E NB M55 PRO  | IP20                       |
| 911401502446 | RS378B P9 927 PSU-E MB M55 PRO  | IP20                       |
| 911401502546 | RS378B P9 930 PSU-E MB M55 PRO  | IP20                       |
| 911401502646 | RS378B P9 940 PSU-E MB M55 PRO  | IP20                       |
| 911401502746 | RS378B P9 927 PSU-E WB M55 PRO  | IP20                       |
| 911401502846 | RS378B P9 930 PSU-E WB M55 PRO  | IP20                       |
| 911401502946 | RS378B P9 940 PSU-E WB M55 PRO  | IP20                       |
| 911401504846 | RS378B P7 927 PSD-E SNB M55 PRO | IP20                       |
| 911401504946 | RS378B P7 930 PSD-E SNB M55 PRO | IP20                       |
| 911401505046 | RS378B P7 940 PSD-E SNB M55 PRO | IP20                       |
| 911401505146 | RS378B P7 927 PSD-E NB M55 PRO  | IP20                       |
| 911401505246 | RS378B P7 930 PSD-E NB M55 PRO  | IP20                       |
| 911401505346 | RS378B P7 940 PSD-E NB M55 PRO  | IP20                       |
| 911401505446 | RS378B P7 927 PSD-E MB M55 PRO  | IP20                       |
| 911401505546 | RS378B P7 930 PSD-E MB M55 PRO  | IP20                       |
| 911401505646 | RS378B P7 940 PSD-E MB M55 PRO  | IP20                       |
| 911401505746 | RS378B P7 927 PSD-E WB M55 PRO  | IP20                       |
| 911401505846 | RS378B P7 930 PSD-E WB M55 PRO  | IP20                       |
| 911401505946 | RS378B P7 940 PSD-E WB M55 PRO  | IP20                       |
| 911401506046 | RS378B P9 927 PSD-E NB M55 PRO  | IP20                       |

| Order Code   | Full Product Name                   | Ingress protection<br>code |
|--------------|-------------------------------------|----------------------------|
| 911401506146 | RS378B P9 930 PSD-E NB M55 PRO      | IP20                       |
| 911401506246 | RS378B P9 940 PSD-E NB M55 PRO      | IP20                       |
| 911401506346 | RS378B P9 927 PSD-E MB M55 PRO      | IP20                       |
| 911401506446 | RS378B P9 930 PSD-E MB M55 PRO      | IP20                       |
| 911401506546 | RS378B P9 940 PSD-E MB M55 PRO      | IP20                       |
| 911401506646 | RS378B P9 927 PSD-E WB M55 PRO      | IP20                       |
| 911401506746 | RS378B P9 930 PSD-E WB M55 PRO      | IP20                       |
| 911401506846 | RS378B P9 940 PSD-E WB M55 PRO      | IP20                       |
| 911401508746 | RS378X P9 930 WIA MB M55 PRO        | IP20                       |
| 911401508846 | RS378X P9 930 WIA WB M55 PRO        | IP20                       |
| 911401509346 | RS378B P7 930 PSU-E MB M55 WP PRO   | IP20/54                    |
| 911401509446 | RS378B P7 930 PSU-E WB M55 WP PRO   | IP20/54                    |
| 911401509546 | RS378B P9 930 PSU-E MB M55 WP PRO   | IP20/54                    |
| 911401509646 | RS378B P9 930 PSU-E WB M55 WP PRO   | IP20/54                    |
| 911401518946 | RS378B P7 PSD-TNW NB M55 PRO        | IP20                       |
| 911401519046 | RS378B P7 PSD-TNW MB M55 PRO        | IP20                       |
| 911401519146 | RS378B P7 PSD-TNW WB M55 PRO        | IP20                       |
| 911401519246 | RS378B P9 PSD-TNW NB M55 PRO        | IP20                       |
| 911401519346 | RS378B P9 PSD-TNW MB M55 PRO        | IP20                       |
| 911401519446 | RS378B P9 PSD-TNW WB M55 PRO        | IP20                       |
| 911401595145 | RS378B P3 927 PSU-E MB D35 G-TT PRO | IP20                       |
| 911401595245 | RS378B P3 930 PSU-E MB D35 G-TT PRO | IP20                       |
| 911401595345 | RS378B P3 940 PSU-E MB D35 G-TT PRO | IP20                       |
| 911401595445 | RS378B P3 927 PSU-E WB D35 G-TT PRO | IP20                       |
| 911401595545 | RS378B P3 930 PSU-E WB D35 G-TT PRO | IP20                       |
| 911401595645 | RS378B P3 940 PSU-E WB D35 G-TT PRO | IP20                       |
| 911401595745 | RS378B P5 927 PSU-E MB D35 G-TT PRO | IP20                       |
| 911401595845 | RS378B P5 930 PSU-E MB D35 G-TT PRO | IP20                       |
| 911401595945 | RS378B P5 940 PSU-E MB D35 G-TT PRO | IP20                       |
| 911401596045 | RS378B P5 927 PSU-E WB D35 G-TT PRO | IP20                       |
| 911401596145 | RS378B P5 930 PSU-E WB D35 G-TT PRO | IP20                       |
| 911401596245 | RS378B P5 940 PSU-E WB D35 G-TT PRO | IP20                       |
| 911401596345 | RS378B P5 927 PSD-E MB D35 G-TT PRO | IP20                       |
| 911401596445 | RS378B P5 930 PSD-E MB D35 G-TT PRO | IP20                       |
| 911401596545 | RS378B P5 940 PSD-E MB D35 G-TT PRO | IP20                       |
| 911401596645 | RS378B P5 927 PSD-E WB D35 G-TT PRO | IP20                       |
| 911401596745 | RS378B P5 930 PSD-E WB D35 G-TT PRO | IP20                       |
| 911401596845 | RS378B P5 940 PSD-E WB D35 G-TT PRO | IP20                       |
| 911401510146 | RS378B P12 927 PSU-E NB M70 PRO     | IP20                       |
| 911401510246 | RS378B P12 930 PSU-E NB M70 PRO     | IP20                       |
| 911401510346 | RS378B P12 940 PSU-E NB M70 PRO     | IP20                       |
| 911401510446 | RS378B P12 927 PSU-E MB M70 PRO     | IP20                       |
| 911401510546 | RS378B P12 930 PSU-E MB M70 PRO     | IP20                       |
| 911401510646 | RS378B P12 940 PSU-E MB M70 PRO     | IP20                       |
| 911401510746 | RS378B P12 927 PSU-E WB M70 PRO     | IP20                       |
| 911401510846 | RS378B P12 930 PSU-E WB M70 PRO     | IP20                       |
| 911401510946 | RS378B P12 940 PSU-E WB M70 PRO     | IP20                       |
| 911401511046 | RS378B P17 927 PSU-E NB M70 PRO     | IP20                       |
| 911401511146 | RS378B P17 930 PSU-E NB M70 PRO     | IP20                       |
| 911401511246 | RS378B P17 940 PSU-E NB M70 PRO     | IP20                       |
| 911401511346 | RS378B P17 927 PSU-E MB M70 PRO     | IP20                       |

| Order Code   | Full Product Name                  | Ingress protection<br>code |
|--------------|------------------------------------|----------------------------|
| 911401511446 | RS378B P17 930 PSU-E MB M70 PRO    | IP20                       |
| 911401511546 | RS378B P17 940 PSU-E MB M70 PRO    | IP20                       |
| 911401511646 | RS378B P17 927 PSU-E WB M70 PRO    | IP20                       |
| 911401511746 | RS378B P17 930 PSU-E WB M70 PRO    | IP20                       |
| 911401511846 | RS378B P17 940 PSU-E WB M70 PRO    | IP20                       |
| 911401511946 | RS378B P19 927 PSU-E NB M70 PRO    | IP20                       |
| 911401512046 | RS378B P19 930 PSU-E NB M70 PRO    | IP20                       |
| 911401512146 | RS378B P19 940 PSU-E NB M70 PRO    | IP20                       |
| 911401512246 | RS378B P19 927 PSU-E MB M70 PRO    | IP20                       |
| 911401512346 | RS378B P19 930 PSU-E MB M70 PRO    | IP20                       |
| 911401512446 | RS378B P19 940 PSU-E MB M70 PRO    | IP20                       |
| 911401512546 | RS378B P19 927 PSU-E WB M70 PRO    | IP20                       |
| 911401512646 | RS378B P19 930 PSU-E WB M70 PRO    | IP20                       |
| 911401512746 | RS378B P19 940 PSU-E WB M70 PRO    | IP20                       |
| 911401513746 | RS378B P12 927 PSD-E NB M70 PRO    | IP20                       |
| 911401513846 | RS378B P12 930 PSD-E NB M70 PRO    | IP20                       |
| 911401513946 | RS378B P12 940 PSD-E NB M70 PRO    | IP20                       |
| 911401514046 | RS378B P12 927 PSD-E MB M70 PRO    | IP20                       |
| 911401514146 | RS378B P12 930 PSD-E MB M70 PRO    | IP20                       |
| 911401514246 | RS378B P12 940 PSD-E MB M70 PRO    | IP20                       |
| 911401514346 | RS378B P12 927 PSD-E WB M70 PRO    | IP20                       |
| 911401514446 | RS378B P12 930 PSD-E WB M70 PRO    | IP20                       |
| 911401514546 | RS378B P12 940 PSD-E WB M70 PRO    | IP20                       |
| 911401514646 | RS378B P18 927 PSD-E NB M70 PRO    | IP20                       |
| 911401514746 | RS378B P18 930 PSD-E NB M70 PRO    | IP20                       |
| 911401514846 | RS378B P18 940 PSD-E NB M70 PRO    | IP20                       |
| 911401514946 | RS378B P18 927 PSD-E MB M70 PRO    | IP20                       |
| 911401515046 | RS378B P18 930 PSD-E MB M70 PRO    | IP20                       |
| 911401515146 | RS378B P18 940 PSD-E MB M70 PRO    | IP20                       |
| 911401515246 | RS378B P18 927 PSD-E WB M70 PRO    | IP20                       |
| 911401515346 | RS378B P18 930 PSD-E WB M70 PRO    | IP20                       |
| 911401515446 | RS378B P18 940 PSD-E WB M70 PRO    | IP20                       |
| 911401515546 | RS378B P20 927 PSD-E NB M70 PRO    | IP20                       |
| 911401515646 | RS378B P20 930 PSD-E NB M70 PRO    | IP20                       |
| 911401515746 | RS378B P20 940 PSD-E NB M70 PRO    | IP20                       |
| 911401515846 | RS378B P20 927 PSD-E MB M70 PRO    | IP20                       |
| 911401515946 | RS378B P20 930 PSD-E MB M70 PRO    | IP20                       |
| 911401516046 | RS378B P20 940 PSD-E MB M70 PRO    | IP20                       |
| 911401516146 | RS378B P20 927 PSD-E WB M70 PRO    | IP20                       |
| 911401516246 | RS378B P20 930 PSD-E WB M70 PRO    | IP20                       |
| 911401516346 | RS378B P20 940 PSD-E WB M70 PRO    | IP20                       |
| 911401517346 | RS378X P12 930 WIA MB M70 PRO      | IP20                       |
| 911401517446 | RS378X P12 930 WIA WB M70 PRO      | IP20                       |
| 911401517546 | RS378X P19 930 WIA MB M70 PRO      | IP20                       |
| 911401517646 | RS378X P19 930 WIA WB M70 PRO      | IP20                       |
| 911401517746 | RS378X P18 930 WIA MB M70 PRO      | IP20                       |
| 911401517846 | RS378X P18 930 WIA WB M70 PRO      | IP20                       |
| 911401518146 | RS378B P12 930 PSU-E MB M70 WP PRO | IP20/54                    |
| 911401518246 | RS378B P12 930 PSU-E WB M70 WP PRO | IP20/54                    |
| 911401518346 | RS378B P17 930 PSU-E MB M70 WP PRO | IP20/54                    |
| 911401518446 | RS378B P17 930 PSU-E WB M70 WP PRO | IP20/54                    |

| Order Code   | Full Product Name                       | Ingress protection<br>code |
|--------------|-----------------------------------------|----------------------------|
| 911401518546 | RS378B P19 930 PSU-E MB M70 WP PRO      | IP20/54                    |
| 911401518646 | RS378B P19 930 PSU-E WB M70 WP PRO      | IP20/54                    |
| 911401520446 | RS378B P13 PSD-TNW NB M70 PRO           | IP20                       |
| 911401520546 | RS378B P13 PSD-TNW MB M70 PRO           | IP20                       |
| 911401520646 | RS378B P13 PSD-TNW WB M70 PRO           | IP20                       |
| 911401520746 | RS378B P19 PSD-TNW NB M70 PRO           | IP20                       |
| 911401520846 | RS378B P19 PSD-TNW MB M70 PRO           | IP20                       |
| 911401520946 | RS378B P19 PSD-TNW WB M70 PRO           | IP20                       |
| 911401521046 | RS378B P22 PSD-TNW NB M70 PRO           | IP20                       |
| 911401521146 | RS378B P22 PSD-TNW MB M70 PRO           | IP20                       |
| 911401521246 | RS378B P22 PSD-TNW WB M70 PRO           | IP20                       |
| 911401512846 | RS378B P27 927 PSU-E NB M70 PRO         | IP20                       |
| 911401512946 | RS378B P27 930 PSU-E NB M70 PRO         | IP20                       |
| 911401513046 | RS378B P27 940 PSU-E NB M70 PRO         | IP20                       |
| 911401513146 | RS378B P27 927 PSU-E MB M70 PRO         | IP20                       |
| 911401513246 | RS378B P27 930 PSU-E MB M70 PRO         | IP20                       |
| 911401513346 | RS378B P27 940 PSU-E MB M70 PRO         | IP20                       |
| 911401513446 | RS378B P27 927 PSU-E WB M70 PRO         | IP20                       |
| 911401513546 | RS378B P27 930 PSU-E WB M70 PRO         | IP20                       |
| 911401513646 | RS378B P27 940 PSU-E WB M70 PRO         | IP20                       |
| 911401516446 | RS378B P27 927 PSD-E NB M70 PRO         | IP20                       |
| 911401516546 | RS378B P27 930 PSD-E NB M70 PRO         | IP20                       |
| 911401516646 | RS378B P27 940 PSD-E NB M70 PRO         | IP20                       |
| 911401516746 | RS378B P27 927 PSD-E MB M70 PRO         | IP20                       |
| 911401516846 | RS378B P27 930 PSD-E MB M70 PRO         | IP20                       |
| 911401516946 | RS378B P27 940 PSD-E MB M70 PRO         | IP20                       |
| 911401517046 | RS378B P27 927 PSD-E WB M70 PRO         | IP20                       |
| 911401517146 | RS378B P27 930 PSD-E WB M70 PRO         | IP20                       |
| 911401517246 | RS378B P27 940 PSD-E WB M70 PRO         | IP20                       |
| 911401517946 | RS378X P28 930 WIA MB M70 PRO           | IP20                       |
| 911401518046 | RS378X P28 930 WIA WB M70 PRO           | IP20                       |
| 911401518746 | RS378B P27 930 PSU-E MB M70 WP PRO      | IP20/54                    |
| 911401518846 | RS378B P27 930 PSU-E WB M70 WP PRO      | IP20/54                    |
| 911401521346 | RS378B P29 PSD-TNW NB M70 PRO           | IP20                       |
| 911401521446 | RS378B P29 PSD-TNW MB M70 PRO           | IP20                       |
| 911401521546 | RS378B P29 PSD-TNW WB M70 PRO           | IP20                       |
| 911401530846 | SM378B S P8 927 PSU-E NB D100 G-TT PRO  | IP20                       |
| 911401530946 | SM378B S P8 930 PSU-E NB D100 G-TT PRO  | IP20                       |
| 911401531046 | SM378B S P8 940 PSU-E NB D100 G-TT PRO  | IP20                       |
| 911401531146 | SM378B S P8 927 PSU-E MB D100 G-TT PRO  | IP20                       |
| 911401531246 | SM378B S P8 930 PSU-E MB D100 G-TT PRO  | IP20                       |
| 911401531346 | SM378B S P8 940 PSU-E MB D100 G-TT PRO  | IP20                       |
| 911401531446 | SM378B S P8 927 PSU-E WB D100 G-TT PRO  | IP20                       |
| 911401531546 | SM378B S P8 930 PSU-E WB D100 G-TT PRO  | IP20                       |
| 911401531646 | SM378B S P8 940 PSU-E WB D100 G-TT PRO  | IP20                       |
| 911401531746 | SM378B S P11 927 PSU-E NB D100 G-TT PRO | IP20                       |
| 911401531846 | SM378B S P11 930 PSU-E NB D100 G-TT PRO | IP20                       |
| 911401531946 | SM378B S P11 940 PSU-E NB D100 G-TT PRO | IP20                       |
| 911401532046 | SM378B S P11 927 PSU-E MB D100 G-TT PRO | IP20                       |
| 911401532146 | SM378B S P11 930 PSU-E MB D100 G-TT PRO | IP20                       |
| 911401532246 | SM378B S P11 940 PSU-E MB D100 G-TT PRO | IP20                       |



| Order Code   | Full Product Name                       | Ingress protection |
|--------------|-----------------------------------------|--------------------|
|              |                                         | code               |
| 911401532346 | SM378B S P11 927 PSU-E WB D100 G-TT PRO | IP20               |
| 911401532446 | SM378B S P11 930 PSU-E WB D100 G-TT PRO | IP20               |
| 911401532546 | SM378B S P11 940 PSU-E WB D100 G-TT PRO | IP20               |
| 911401532646 | SM378B S P13 927 PSU-E NB D100 G-TT PRO | IP20               |
| 911401532746 | SM378B S P13 930 PSU-E NB D100 G-TT PRO | IP20               |
| 911401532846 | SM378B S P13 940 PSU-E NB D100 G-TT PRO | IP20               |
| 911401532946 | SM378B S P13 927 PSU-E MB D100 G-TT PRO | IP20               |
| 911401533046 | SM378B S P13 930 PSU-E MB D100 G-TT PRO | IP20               |
| 911401533146 | SM378B S P13 940 PSU-E MB D100 G-TT PRO | IP20               |
| 911401533246 | SM378B S P13 927 PSU-E WB D100 G-TT PRO | IP20               |
| 911401533346 | SM378B S P13 930 PSU-E WB D100 G-TT PRO | IP20               |
| 911401533446 | SM378B S P13 940 PSU-E WB D100 G-TT PRO | IP20               |
| 911401533546 | SM378B S P20 927 PSU-E NB D100 G-TT PRO | IP20               |
| 911401533646 | SM378B S P20 930 PSU-E NB D100 G-TT PRO | IP20               |
| 911401533746 | SM378B S P20 940 PSU-E NB D100 G-TT PRO | IP20               |
| 911401533846 | SM378B S P20 927 PSU-E MB D100 G-TT PRO | IP20               |
| 911401533946 | SM378B S P20 930 PSU-E MB D100 G-TT PRO | IP20               |
| 911401534046 | SM378B S P20 940 PSU-E MB D100 G-TT PRO | IP20               |
| 911401534146 | SM378B S P20 927 PSU-E WB D100 G-TT PRO | IP20               |
| 911401534246 | SM378B S P20 930 PSU-E WB D100 G-TT PRO | IP20               |
| 911401534346 | SM378B S P20 940 PSU-E WB D100 G-TT PRO | IP20               |
| 911401534446 | SM378B S P20 927 PSD-E NB D100 G-TT PRO | IP20               |
| 911401534546 | SM378B S P20 930 PSD-E NB D100 G-TT PRO | IP20               |
| 911401534646 | SM378B S P20 940 PSD-E NB D100 G-TT PRO | IP20               |
| 911401534746 | SM378B S P20 927 PSD-E MB D100 G-TT PRO | IP20               |
| 911401534846 | SM378B S P20 930 PSD-E MB D100 G-TT PRO | IP20               |
| 911401534946 | SM378B S P20 940 PSD-E MB D100 G-TT PRO | IP20               |
| 911401535046 | SM378B S P20 927 PSD-E WB D100 G-TT PRO | IP20               |
| 911401535146 | SM378B S P20 930 PSD-E WB D100 G-TT PRO | IP20               |
| 911401535246 | SM378B S P20 940 PSD-E WB D100 G-TT PRO | IP20               |
| 911401535446 | SM378B S P8 927 PSD-E NB D100 G-TT PRO  | IP20               |
| 911401535546 | SM378B S P8 930 PSD-E NB D100 G-TT PRO  | IP20               |
| 911401535646 | SM378B S P8 940 PSD-E NB D100 G-TT PRO  | IP20               |
| 911401535746 | SM378B S P8 927 PSD-E MB D100 G-TT PRO  | IP20               |
| 911401535846 | SM378B S P8 930 PSD-E MB D100 G-TT PRO  | IP20               |
| 911401535946 | SM378B S P8 940 PSD-E MB D100 G-TT PRO  | IP20               |
| 911401536046 | SM378B S P8 927 PSD-E WB D100 G-TT PRO  | IP20               |
| 911401536146 | SM378B S P8 930 PSD-E WB D100 G-TT PRO  | IP20               |
| 911401536246 | SM378B S P8 940 PSD-E WB D100 G-TT PRO  | IP20               |
| 911401536346 | SM378B S P12 927 PSD-E NB D100 G-TT PRO | IP20               |
| 911401536446 | SM378B S P12 930 PSD-E NB D100 G-TT PRO | IP20               |
| 911401536546 | SM378B S P12 940 PSD-E NB D100 G-TT PRO | IP20               |
| 911401536646 | SM378B S P12 927 PSD-E MB D100 G-TT PRO | IP20               |
| 911401536746 | SM378B S P12 930 PSD-E MB D100 G-TT PRO | IP20               |
| 911401536846 | SM378B S P12 940 PSD-E MB D100 G-TT PRO | IP20               |
| 911401536946 | SM378B S P12 927 PSD-E WB D100 G-TT PRO | IP20               |
| 911401537046 | SM378B S P12 930 PSD-E WB D100 G-TT PRO | IP20               |
| 911401537146 | SM378B S P12 940 PSD-E WB D100 G-TT PRO | IP20               |
| 911401537246 | SM378B S P14 927 PSD-E NB D100 G-TT PRO | IP20               |
| 911401537346 | SM378B S P14 930 PSD-E NB D100 G-TT PRO | IP20               |
| 911401537446 | SM378B S P14 940 PSD-E NB D100 G-TT PRO | IP20               |

| Order Code   | Full Product Name                       | Ingress protection |
|--------------|-----------------------------------------|--------------------|
|              |                                         | code               |
| 911401537546 | SM378B S P14 927 PSD-E MB D100 G-TT PRO | IP20               |
| 911401537646 | SM378B S P14 930 PSD-E MB D100 G-TT PRO | IP20               |
| 911401537746 | SM378B S P14 940 PSD-E MB D100 G-TT PRO | IP20               |
| 911401537846 | SM378B S P14 927 PSD-E WB D100 G-TT PRO | IP20               |
| 911401537946 | SM378B S P14 930 PSD-E WB D100 G-TT PRO | IP20               |
| 911401538046 | SM378B S P14 940 PSD-E WB D100 G-TT PRO | IP20               |
| 911401538146 | SM378X S P8 930 WIA MB D100 G-TT PRO    | IP20               |
| 911401538246 | SM378X S P8 930 WIA WB D100 G-TT PRO    | IP20               |
| 911401538346 | SM378X S P12 930 WIA MB D100 G-TT PRO   | IP20               |
| 911401538446 | SM378X S P12 930 WIA WB D100 G-TT PRO   | IP20               |
| 911401538546 | SM378X S P14 930 WIA MB D100 G-TT PRO   | IP20               |
| 911401538646 | SM378X S P14 930 WIA WB D100 G-TT PRO   | IP20               |
| 911401538746 | SM378X S P20 930 WIA MB D100 G-TT PRO   | IP20               |
| 911401538846 | SM378X S P20 930 WIA WB D100 G-TT PRO   | IP20               |
| 911401538946 | SM378B S P9 PSD-TNW NB D100 G-TT PRO    | IP20               |
| 911401539046 | SM378B S P9 PSD-TNW MB D100 G-TT PRO    | IP20               |
| 911401539146 | SM378B S P9 PSD-TNW WB D100 G-TT PRO    | IP20               |
| 911401539246 | SM378B S P12 PSD-TNW NB D100 G-TT PRO   | IP20               |
| 911401539346 | SM378B S P12 PSD-TNW MB D100 G-TT PRO   | IP20               |
| 911401539446 | SM378B S P12 PSD-TNW WB D100 G-TT PRO   | IP20               |
| 911401539546 | SM378B S P15 PSD-TNW NB D100 G-TT PRO   | IP20               |
| 911401539646 | SM378B S P15 PSD-TNW MB D100 G-TT PRO   | IP20               |
| 911401539746 | SM378B S P15 PSD-TNW WB D100 G-TT PRO   | IP20               |
| 911401539846 | SM378B S P22 PSD-TNW NB D100 G-TT PRO   | IP20               |
| 911401539946 | SM378B S P22 PSD-TNW MB D100 G-TT PRO   | IP20               |
| 911401540046 | SM378B S P22 PSD-TNW WB D100 G-TT PRO   | IP20               |
| 911401503046 | RS378B P12 927 PSU-E NB M55 PRO         | IP20               |
| 911401503146 | RS378B P12 930 PSU-E NB M55 PRO         | IP20               |
| 911401503246 | RS378B P12 940 PSU-E NB M55 PRO         | IP20               |
| 911401503346 | RS378B P12 927 PSU-E MB M55 PRO         | IP20               |
| 911401503446 | RS378B P12 930 PSU-E MB M55 PRO         | IP20               |
| 911401503546 | RS378B P12 940 PSU-E MB M55 PRO         | IP20               |
| 911401503646 | RS378B P12 927 PSU-E WB M55 PRO         | IP20               |
| 911401503746 | RS378B P12 930 PSU-E WB M55 PRO         | IP20               |
| 911401503846 | RS378B P12 940 PSU-E WB M55 PRO         | IP20               |
| 911401503946 | RS378B P14 927 PSU-E NB M55 PRO         | IP20               |
| 911401504046 | RS378B P14 930 PSU-E NB M55 PRO         | IP20               |
| 911401504146 | RS378B P14 940 PSU-E NB M55 PRO         | IP20               |
| 911401504246 | RS378B P14 927 PSU-E MB M55 PRO         | IP20               |
| 911401504346 | RS378B P14 930 PSU-E MB M55 PRO         | IP20               |
| 911401504446 | RS378B P14 940 PSU-E MB M55 PRO         | IP20               |
| 911401504546 | RS378B P14 927 PSU-E WB M55 PRO         | IP20               |
| 911401504646 | RS378B P14 930 PSU-E WB M55 PRO         | IP20               |
| 911401504746 | RS378B P14 940 PSU-E WB M55 PRO         | IP20               |
| 911401506946 | RS378B P13 927 PSD-E NB M55 PRO         | IP20               |
| 911401507046 | RS378B P13 930 PSD-E NB M55 PRO         | IP20               |
| 911401507146 | RS378B P13 940 PSD-E NB M55 PRO         | IP20               |
| 911401507246 | RS378B P13 927 PSD-E MB M55 PRO         | IP20               |
| 911401507346 | RS378B P13 930 PSD-E MB M55 PRO         | IP20               |
| 911401507446 | RS378B P13 940 PSD-E MB M55 PRO         | IP20               |
| 911401507546 | RS378B P13 927 PSD-E WB M55 PRO         | IP20               |

| Order Code   | Full Product Name               | Ingress protection |
|--------------|---------------------------------|--------------------|
|              |                                 | code               |
| 911401507646 | RS378B P13 930 PSD-E WB M55 PRO | IP20               |
| 911401507746 | RS378B P13 940 PSD-E WB M55 PRO | IP20               |
| 911401507846 | RS378B P15 927 PSD-E NB M55 PRO | IP20               |
| 911401507946 | RS378B P15 930 PSD-E NB M55 PRO | IP20               |
| 911401508046 | RS378B P15 940 PSD-E NB M55 PRO | IP20               |
| 911401508146 | RS378B P15 927 PSD-E MB M55 PRO | IP20               |
| 911401508246 | RS378B P15 930 PSD-E MB M55 PRO | IP20               |
| 911401508346 | RS378B P15 940 PSD-E MB M55 PRO | IP20               |
| 911401508446 | RS378B P15 927 PSD-E WB M55 PRO | IP20               |
| 911401508546 | RS378B P15 930 PSD-E WB M55 PRO | IP20               |
| 911401508646 | RS378B P15 940 PSD-E WB M55 PRO | IP20               |
| 911401508946 | RS378X P12 930 WIA MB M55 PRO   | IP20               |
| 911401509046 | RS378X P12 930 WIA WB M55 PRO   | IP20               |

Approval and Application

| Order Code   | Full Product Name                       | CE mark |
|--------------|-----------------------------------------|---------|
| 911401521646 | SM378B R P8 927 PSU-E NB D100 G-TT PRO  | Yes     |
| 911401521746 | SM378B R P8 930 PSU-E NB D100 G-TT PRO  | Yes     |
| 911401521846 | SM378B R P8 940 PSU-E NB D100 G-TT PRO  | Yes     |
| 911401521946 | SM378B R P8 927 PSU-E MB D100 G-TT PRO  | Yes     |
| 911401522046 | SM378B R P8 930 PSU-E MB D100 G-TT PRO  | Yes     |
| 911401522146 | SM378B R P8 940 PSU-E MB D100 G-TT PRO  | Yes     |
| 911401522246 | SM378B R P8 927 PSU-E WB D100 G-TT PRO  | Yes     |
| 911401522346 | SM378B R P8 930 PSU-E WB D100 G-TT PRO  | Yes     |
| 911401522446 | SM378B R P8 940 PSU-E WB D100 G-TT PRO  | Yes     |
| 911401522546 | SM378B R P11 927 PSU-E NB D100 G-TT PRO | Yes     |
| 911401522646 | SM378B R P11 930 PSU-E NB D100 G-TT PRO | Yes     |
| 911401522746 | SM378B R P11 940 PSU-E NB D100 G-TT PRO | Yes     |
| 911401522846 | SM378B R P11 927 PSU-E MB D100 G-TT PRO | Yes     |
| 911401522946 | SM378B R P11 930 PSU-E MB D100 G-TT PRO | Yes     |
| 911401523046 | SM378B R P11 940 PSU-E MB D100 G-TT PRO | Yes     |
| 911401523146 | SM378B R P11 927 PSU-E WB D100 G-TT PRO | Yes     |
| 911401523246 | SM378B R P11 930 PSU-E WB D100 G-TT PRO | Yes     |
| 911401523346 | SM378B R P11 940 PSU-E WB D100 G-TT PRO | Yes     |
| 911401523446 | SM378B R P13 927 PSU-E NB D100 G-TT PRO | Yes     |
| 911401523546 | SM378B R P13 930 PSU-E NB D100 G-TT PRO | Yes     |
| 911401523646 | SM378B R P13 940 PSU-E NB D100 G-TT PRO | Yes     |
| 911401523746 | SM378B R P13 927 PSU-E MB D100 G-TT PRO | Yes     |
| 911401523846 | SM378B R P13 930 PSU-E MB D100 G-TT PRO | Yes     |
| 911401523946 | SM378B R P13 940 PSU-E MB D100 G-TT PRO | Yes     |
| 911401524046 | SM378B R P13 927 PSU-E WB D100 G-TT PRO | Yes     |
| 911401524146 | SM378B R P13 930 PSU-E WB D100 G-TT PRO | Yes     |
| 911401524246 | SM378B R P13 940 PSU-E WB D100 G-TT PRO | Yes     |
| 911401524346 | SM378B R P20 927 PSU-E NB D100 G-TT PRO | Yes     |
| 911401524446 | SM378B R P20 930 PSU-E NB D100 G-TT PRO | Yes     |
| 911401524546 | SM378B R P20 940 PSU-E NB D100 G-TT PRO | Yes     |
| 911401524646 | SM378B R P20 927 PSU-E MB D100 G-TT PRO | Yes     |
| 911401524746 | SM378B R P20 930 PSU-E MB D100 G-TT PRO | Yes     |
| 911401524846 | SM378B R P20 940 PSU-E MB D100 G-TT PRO | Yes     |
| 911401524946 | SM378B R P20 927 PSU-E WB D100 G-TT PRO | Yes     |

| Order Code   | Full Product Name                  | Ingress protection |
|--------------|------------------------------------|--------------------|
|              |                                    | code               |
| 911401509146 | RS378X P14 930 WIA MB M55 PRO      | IP20               |
| 911401509246 | RS378X P14 930 WIA WB M55 PRO      | IP20               |
| 911401509746 | RS378B P12 930 PSU-E MB M55 WP PRO | IP20/54            |
| 911401509846 | RS378B P12 930 PSU-E WB M55 WP PRO | IP20/54            |
| 911401509946 | RS378B P14 930 PSU-E MB M55 WP PRO | IP20/54            |
| 911401510046 | RS378B P14 930 PSU-E WB M55 WP PRO | IP20/54            |
| 911401519546 | RS378B P13 PSD-TNW NB M55 PRO      | IP20               |
| 911401519646 | RS378B P13 PSD-TNW MB M55 PRO      | IP20               |
| 911401519746 | RS378B P13 PSD-TNW WB M55 PRO      | IP20               |
| 911401519846 | RS378B P15 PSD-TNW NB M55 PRO      | IP20               |
| 911401519946 | RS378B P15 PSD-TNW MB M55 PRO      | IP20               |
| 911401520046 | RS378B P15 PSD-TNW WB M55 PRO      | IP20               |

| Order Code   | Full Product Name                       | CE mark |
|--------------|-----------------------------------------|---------|
| 911401528446 | SM378B R P14 940 PSD-E MB D100 G-TT PRO | Yes     |
| 911401528546 | SM378B R P14 927 PSD-E WB D100 G-TT PRO | Yes     |
| 911401528646 | SM378B R P14 930 PSD-E WB D100 G-TT PRO | Yes     |
| 911401528746 | SM378B R P14 940 PSD-E WB D100 G-TT PRO | Yes     |
| 911401528846 | SM378X R P8 930 WIA MB D100 G-TT PRO    | Yes     |
| 911401528946 | SM378X R P8 930 WIA WB D100 G-TT PRO    | Yes     |
| 911401529046 | SM378X R P12 930 WIA MB D100 G-TT PRO   | Yes     |
| 911401529146 | SM378X R P12 930 WIA WB D100 G-TT PRO   | Yes     |
| 911401529246 | SM378X R P14 930 WIA MB D100 G-TT PRO   | Yes     |
| 911401529346 | SM378X R P14 930 WIA WB D100 G-TT PRO   | Yes     |
| 911401529446 | SM378X R P20 930 WIA MB D100 G-TT PRO   | Yes     |
| 911401529546 | SM378X R P20 930 WIA WB D100 G-TT PRO   | Yes     |
| 911401529646 | SM378B R P9 PSD-TNW NB D100 G-TT PRO    | No      |
| 911401529746 | SM378B R P9 PSD-TNW MB D100 G-TT PRO    | No      |
| 911401529846 | SM378B R P9 PSD-TNW WB D100 G-TT PRO    | No      |
| 911401529946 | SM378B R P12 PSD-TNW NB D100 G-TT PRO   | No      |
| 911401530046 | SM378B R P12 PSD-TNW MB D100 G-TT PRO   | No      |
| 911401530146 | SM378B R P12 PSD-TNW WB D100 G-TT PRO   | No      |
| 911401530246 | SM378B R P15 PSD-TNW NB D100 G-TT PRO   | No      |
| 911401530346 | SM378B R P15 PSD-TNW MB D100 G-TT PRO   | No      |
| 911401530446 | SM378B R P15 PSD-TNW WB D100 G-TT PRO   | No      |
| 911401530546 | SM378B R P22 PSD-TNW NB D100 G-TT PRO   | No      |
| 911401530646 | SM378B R P22 PSD-TNW MB D100 G-TT PRO   | No      |
| 911401530746 | SM378B R P22 PSD-TNW WB D100 G-TT PRO   | No      |
| 911401500046 | RS378B P7 930 PSD-E WB M43 PRO          | Yes     |
| 911401500146 | RS378B P7 940 PSD-E WB M43 PRO          | Yes     |
| 911401500246 | RS378B P6 930 PSU-E MB M43 WP PRO       | Yes     |
| 911401500346 | RS378B P6 930 PSU-E WB M43 WP PRO       | Yes     |
| 911401500446 | RS378B P8 930 PSU-E MB M43 WP PRO       | Yes     |
| 911401500546 | RS378B P8 930 PSU-E WB M43 WP PRO       | Yes     |
| 911401520146 | RS378B P7 PSD-TNW NB M43 PRO            | No      |
| 911401520246 | RS378B P7 PSD-TNW MB M43 PRO            | No      |
| 911401520346 | RS378B P7 PSD-TNW WB M43 PRO            | No      |
| 911401596945 | RS378B P6 927 PSU-E SNB M43 PRO         | Yes     |
| 911401597045 | RS378B P6 930 PSU-E SNB M43 PRO         | Yes     |
| 911401597145 | RS378B P6 940 PSU-E SNB M43 PRO         | Yes     |
| 911401597245 | RS378B P6 927 PSU-E NB M43 PRO          | Yes     |
| 911401597345 | RS378B P6 930 PSU-E NB M43 PRO          | Yes     |
| 911401597445 | RS378B P6 940 PSU-E NB M43 PRO          | Yes     |
| 911401597545 | RS378B P6 927 PSU-E MB M43 PRO          | Yes     |
| 911401597645 | RS378B P6 930 PSU-E MB M43 PRO          | Yes     |
| 911401597745 | RS378B P6 940 PSU-E MB M43 PRO          | Yes     |
| 911401597845 | RS378B P6 927 PSU-E WB M43 PRO          | Yes     |
| 911401597945 | RS378B P6 930 PSU-E WB M43 PRO          | Yes     |
| 911401598045 | RS378B P6 940 PSU-E WB M43 PRO          | Yes     |
| 911401598145 | RS378B P8 927 PSU-E NB M43 PRO          | Yes     |
| 911401598245 | RS378B P8 930 PSU-E NB M43 PRO          | Yes     |
| 911401598345 | RS378B P8 940 PSU-E NB M43 PRO          | Yes     |
| 911401598445 | RS378B P8 927 PSU-E MB M43 PRO          | Yes     |
| 911401598545 | RS378B P8 930 PSU-E MB M43 PRO          | Yes     |
| 911401598645 | RS378B P8 940 PSU-E MB M43 PRO          | Yes     |
| 911401598745 | RS378B P8 927 PSU-E WB M43 PRO          | Yes     |

| Order Code   | Full Product Name               | CE mark |
|--------------|---------------------------------|---------|
| 911401598845 | RS378B P8 930 PSU-E WB M43 PRO  | Yes     |
| 911401598945 | RS378B P8 940 PSU-E WB M43 PRO  | Yes     |
| 911401599045 | RS378B P7 927 PSD-E SNB M43 PRO | Yes     |
| 911401599145 | RS378B P7 930 PSD-E SNB M43 PRO | Yes     |
| 911401599245 | RS378B P7 940 PSD-E SNB M43 PRO | Yes     |
| 911401599345 | RS378B P7 927 PSD-E NB M43 PRO  | Yes     |
| 911401599445 | RS378B P7 930 PSD-E NB M43 PRO  | Yes     |
| 911401599545 | RS378B P7 940 PSD-E NB M43 PRO  | Yes     |
| 911401599645 | RS378B P7 927 PSD-E MB M43 PRO  | Yes     |
| 911401599745 | RS378B P7 930 PSD-E MB M43 PRO  | Yes     |
| 911401599845 | RS378B P7 940 PSD-E MB M43 PRO  | Yes     |
| 911401599945 | RS378B P7 927 PSD-E WB M43 PRO  | Yes     |
| 911401500646 | RS378B P7 927 PSU-E SNB M55 PRO | Yes     |
| 911401500746 | RS378B P7 930 PSU-E SNB M55 PRO | Yes     |
| 911401500846 | RS378B P7 940 PSU-E SNB M55 PRO | Yes     |
| 911401500946 | RS378B P7 927 PSU-E NB M55 PRO  | Yes     |
| 911401501046 | RS378B P7 930 PSU-E NB M55 PRO  | Yes     |
| 911401501146 | RS378B P7 940 PSU-E NB M55 PRO  | Yes     |
| 911401501246 | RS378B P7 927 PSU-E MB M55 PRO  | Yes     |
| 911401501346 | RS378B P7 930 PSU-E MB M55 PRO  | Yes     |
| 911401501446 | RS378B P7 940 PSU-E MB M55 PRO  | Yes     |
| 911401501546 | RS378B P7 927 PSU-E WB M55 PRO  | Yes     |
| 911401501646 | RS378B P7 930 PSU-E WB M55 PRO  | Yes     |
| 911401501746 | RS378B P7 940 PSU-E WB M55 PRO  | Yes     |
| 911401501846 | RS378B P8 927 PSU-E SNB M55 PRO | Yes     |
| 911401501946 | RS378B P8 930 PSU-E SNB M55 PRO | Yes     |
| 911401502046 | RS378B P8 940 PSU-E SNB M55 PRO | Yes     |
| 911401502146 | RS378B P9 927 PSU-E NB M55 PRO  | Yes     |
| 911401502246 | RS378B P9 930 PSU-E NB M55 PRO  | Yes     |
| 911401502346 | RS378B P9 940 PSU-E NB M55 PRO  | Yes     |
| 911401502446 | RS378B P9 927 PSU-E MB M55 PRO  | Yes     |
| 911401502546 | RS378B P9 930 PSU-E MB M55 PRO  | Yes     |
| 911401502646 | RS378B P9 940 PSU-E MB M55 PRO  | Yes     |
| 911401502746 | RS378B P9 927 PSU-E WB M55 PRO  | Yes     |
| 911401502846 | RS378B P9 930 PSU-E WB M55 PRO  | Yes     |
| 911401502946 | RS378B P9 940 PSU-E WB M55 PRO  | Yes     |
| 911401504846 | RS378B P7 927 PSD-E SNB M55 PRO | Yes     |
| 911401504946 | RS378B P7 930 PSD-E SNB M55 PRO | Yes     |
| 911401505046 | RS378B P7 940 PSD-E SNB M55 PRO | Yes     |
| 911401505146 | RS378B P7 927 PSD-E NB M55 PRO  | Yes     |
| 911401505246 | RS378B P7 930 PSD-E NB M55 PRO  | Yes     |
| 911401505346 | RS378B P7 940 PSD-E NB M55 PRO  | Yes     |
| 911401505446 | RS378B P7 927 PSD-E MB M55 PRO  | Yes     |
| 911401505546 | RS378B P7 930 PSD-E MB M55 PRO  | Yes     |
| 911401505646 | RS378B P7 940 PSD-E MB M55 PRO  | Yes     |
| 911401505746 | RS378B P7 927 PSD-E WB M55 PRO  | Yes     |
| 911401505846 | RS378B P7 930 PSD-E WB M55 PRO  | Yes     |
| 911401505946 | RS378B P7 940 PSD-E WB M55 PRO  | Yes     |
| 911401506046 | RS378B P9 927 PSD-E NB M55 PRO  | Yes     |
| 911401506146 | RS378B P9 930 PSD-E NB M55 PRO  | Yes     |
| 911401506246 | RS378B P9 940 PSD-E NB M55 PRO  | Yes     |
| 911401506346 | RS378B P9 927 PSD-E MB M55 PRO  | Yes     |

| Order Code   | Full Product Name                   | CE mark |
|--------------|-------------------------------------|---------|
| 911401506446 | RS378B P9 930 PSD-E MB M55 PRO      | Yes     |
| 911401506546 | RS378B P9 940 PSD-E MB M55 PRO      | Yes     |
| 911401506646 | RS378B P9 927 PSD-E WB M55 PRO      | Yes     |
| 911401506746 | RS378B P9 930 PSD-E WB M55 PRO      | Yes     |
| 911401506846 | RS378B P9 940 PSD-E WB M55 PRO      | Yes     |
| 911401508746 | RS378X P9 930 WIA MB M55 PRO        | Yes     |
| 911401508846 | RS378X P9 930 WIA WB M55 PRO        | Yes     |
| 911401509346 | RS378B P7 930 PSU-E MB M55 WP PRO   | Yes     |
| 911401509446 | RS378B P7 930 PSU-E WB M55 WP PRO   | Yes     |
| 911401509546 | RS378B P9 930 PSU-E MB M55 WP PRO   | Yes     |
| 911401509646 | RS378B P9 930 PSU-E WB M55 WP PRO   | Yes     |
| 911401518946 | RS378B P7 PSD-TNW NB M55 PRO        | No      |
| 911401519046 | RS378B P7 PSD-TNW MB M55 PRO        | No      |
| 911401519146 | RS378B P7 PSD-TNW WB M55 PRO        | No      |
| 911401519246 | RS378B P9 PSD-TNW NB M55 PRO        | No      |
| 911401519346 | RS378B P9 PSD-TNW MB M55 PRO        | No      |
| 911401519446 | RS378B P9 PSD-TNW WB M55 PRO        | No      |
| 911401595145 | RS378B P3 927 PSU-E MB D35 G-TT PRO | Yes     |
| 911401595245 | RS378B P3 930 PSU-E MB D35 G-TT PRO | Yes     |
| 911401595345 | RS378B P3 940 PSU-E MB D35 G-TT PRO | Yes     |
| 911401595445 | RS378B P3 927 PSU-E WB D35 G-TT PRO | Yes     |
| 911401595545 | RS378B P3 930 PSU-E WB D35 G-TT PRO | Yes     |
| 911401595645 | RS378B P3 940 PSU-E WB D35 G-TT PRO | Yes     |
| 911401595745 | RS378B P5 927 PSU-E MB D35 G-TT PRO | Yes     |
| 911401595845 | RS378B P5 930 PSU-E MB D35 G-TT PRO | Yes     |
| 911401595945 | RS378B P5 940 PSU-E MB D35 G-TT PRO | Yes     |
| 911401596045 | RS378B P5 927 PSU-E WB D35 G-TT PRO | Yes     |
| 911401596145 | RS378B P5 930 PSU-E WB D35 G-TT PRO | Yes     |
| 911401596245 | RS378B P5 940 PSU-E WB D35 G-TT PRO | Yes     |
| 911401596345 | RS378B P5 927 PSD-E MB D35 G-TT PRO | Yes     |
| 911401596445 | RS378B P5 930 PSD-E MB D35 G-TT PRO | Yes     |
| 911401596545 | RS378B P5 940 PSD-E MB D35 G-TT PRO | Yes     |
| 911401596645 | RS378B P5 927 PSD-E WB D35 G-TT PRO | Yes     |
| 911401596745 | RS378B P5 930 PSD-E WB D35 G-TT PRO | Yes     |
| 911401596845 | RS378B P5 940 PSD-E WB D35 G-TT PRO | Yes     |
| 911401510146 | RS378B P12 927 PSU-E NB M70 PRO     | Yes     |
| 911401510246 | RS378B P12 930 PSU-E NB M70 PRO     | Yes     |
| 911401510346 | RS378B P12 940 PSU-E NB M70 PRO     | Yes     |
| 911401510446 | RS378B P12 927 PSU-E MB M70 PRO     | Yes     |
| 911401510546 | RS378B P12 930 PSU-E MB M70 PRO     | Yes     |
| 911401510646 | RS378B P12 940 PSU-E MB M70 PRO     | Yes     |
| 911401510746 | RS378B P12 927 PSU-E WB M70 PRO     | Yes     |
| 911401510846 | RS378B P12 930 PSU-E WB M70 PRO     | Yes     |
| 911401510946 | RS378B P12 940 PSU-E WB M70 PRO     | Yes     |
| 911401511046 | RS378B P17 927 PSU-E NB M70 PRO     | Yes     |
| 911401511146 | RS378B P17 930 PSU-E NB M70 PRO     | Yes     |
| 911401511246 | RS378B P17 940 PSU-E NB M70 PRO     | Yes     |
| 911401511346 | RS378B P17 927 PSU-E MB M70 PRO     | Yes     |
| 911401511446 | RS378B P17 930 PSU-E MB M70 PRO     | Yes     |
| 911401511546 | RS378B P17 940 PSU-E MB M70 PRO     | Yes     |
| 911401511646 | RS378B P17 927 PSU-E WB M70 PRO     | Yes     |
| 911401511746 | RS378B P17 930 PSU-E WB M70 PRO     | Yes     |

| Order Code   | Full Product Name                  | CE mark |
|--------------|------------------------------------|---------|
| 911401511846 | RS378B P17 940 PSU-E WB M70 PRO    | Yes     |
| 911401511946 | RS378B P19 927 PSU-E NB M70 PRO    | Yes     |
| 911401512046 | RS378B P19 930 PSU-E NB M70 PRO    | Yes     |
| 911401512146 | RS378B P19 940 PSU-E NB M70 PRO    | Yes     |
| 911401512246 | RS378B P19 927 PSU-E MB M70 PRO    | Yes     |
| 911401512346 | RS378B P19 930 PSU-E MB M70 PRO    | Yes     |
| 911401512446 | RS378B P19 940 PSU-E MB M70 PRO    | Yes     |
| 911401512546 | RS378B P19 927 PSU-E WB M70 PRO    | Yes     |
| 911401512646 | RS378B P19 930 PSU-E WB M70 PRO    | Yes     |
| 911401512746 | RS378B P19 940 PSU-E WB M70 PRO    | Yes     |
| 911401513746 | RS378B P12 927 PSD-E NB M70 PRO    | Yes     |
| 911401513846 | RS378B P12 930 PSD-E NB M70 PRO    | Yes     |
| 911401513946 | RS378B P12 940 PSD-E NB M70 PRO    | Yes     |
| 911401514046 | RS378B P12 927 PSD-E MB M70 PRO    | Yes     |
| 911401514146 | RS378B P12 930 PSD-E MB M70 PRO    | Yes     |
| 911401514246 | RS378B P12 940 PSD-E MB M70 PRO    | Yes     |
| 911401514346 | RS378B P12 927 PSD-E WB M70 PRO    | Yes     |
| 911401514446 | RS378B P12 930 PSD-E WB M70 PRO    | Yes     |
| 911401514546 | RS378B P12 940 PSD-E WB M70 PRO    | Yes     |
| 911401514646 | RS378B P18 927 PSD-E NB M70 PRO    | Yes     |
| 911401514746 | RS378B P18 930 PSD-E NB M70 PRO    | Yes     |
| 911401514846 | RS378B P18 940 PSD-E NB M70 PRO    | Yes     |
| 911401514946 | RS378B P18 927 PSD-E MB M70 PRO    | Yes     |
| 911401515046 | RS378B P18 930 PSD-E MB M70 PRO    | Yes     |
| 911401515146 | RS378B P18 940 PSD-E MB M70 PRO    | Yes     |
| 911401515246 | RS378B P18 927 PSD-E WB M70 PRO    | Yes     |
| 911401515346 | RS378B P18 930 PSD-E WB M70 PRO    | Yes     |
| 911401515446 | RS378B P18 940 PSD-E WB M70 PRO    | Yes     |
| 911401515546 | RS378B P20 927 PSD-E NB M70 PRO    | Yes     |
| 911401515646 | RS378B P20 930 PSD-E NB M70 PRO    | Yes     |
| 911401515746 | RS378B P20 940 PSD-E NB M70 PRO    | Yes     |
| 911401515846 | RS378B P20 927 PSD-E MB M70 PRO    | Yes     |
| 911401515946 | RS378B P20 930 PSD-E MB M70 PRO    | Yes     |
| 911401516046 | RS378B P20 940 PSD-E MB M70 PRO    | Yes     |
| 911401516146 | RS378B P20 927 PSD-E WB M70 PRO    | Yes     |
| 911401516246 | RS378B P20 930 PSD-E WB M70 PRO    | Yes     |
| 911401516346 | RS378B P20 940 PSD-E WB M70 PRO    | Yes     |
| 911401517346 | RS378X P12 930 WIA MB M70 PRO      | Yes     |
| 911401517446 | RS378X P12 930 WIA WB M70 PRO      | Yes     |
| 911401517546 | RS378X P19 930 WIA MB M70 PRO      | Yes     |
| 911401517646 | RS378X P19 930 WIA WB M70 PRO      | Yes     |
| 911401517746 | RS378X P18 930 WIA MB M70 PRO      | Yes     |
| 911401517846 | RS378X P18 930 WIA WB M70 PRO      | Yes     |
| 911401518146 | RS378B P12 930 PSU-E MB M70 WP PRO | Yes     |
| 911401518246 | RS378B P12 930 PSU-E WB M70 WP PRO | Yes     |
| 911401518346 | RS378B P17 930 PSU-E MB M70 WP PRO | Yes     |
| 911401518446 | RS378B P17 930 PSU-E WB M70 WP PRO | Yes     |
| 911401518546 | RS378B P19 930 PSU-E MB M70 WP PRO | Yes     |
| 911401518646 | RS378B P19 930 PSU-E WB M70 WP PRO | Yes     |
| 911401520446 | RS378B P13 PSD-TNW NB M70 PRO      | No      |
| 911401520546 | RS378B P13 PSD-TNW MB M70 PRO      | No      |
| 911401520646 | RS378B P13 PSD-TNW WB M70 PRO      | No      |

| Order Code   | Full Product Name                       | CE mark |
|--------------|-----------------------------------------|---------|
| 911401520746 | RS378B P19 PSD-TNW NB M70 PRO           | No      |
| 911401520846 | RS378B P19 PSD-TNW MB M70 PRO           | No      |
| 911401520946 | RS378B P19 PSD-TNW WB M70 PRO           | No      |
| 911401521046 | RS378B P22 PSD-TNW NB M70 PRO           | No      |
| 911401521146 | RS378B P22 PSD-TNW MB M70 PRO           | No      |
| 911401521246 | RS378B P22 PSD-TNW WB M70 PRO           | No      |
| 911401512846 | RS378B P27 927 PSU-E NB M70 PRO         | Yes     |
| 911401512946 | RS378B P27 930 PSU-E NB M70 PRO         | Yes     |
| 911401513046 | RS378B P27 940 PSU-E NB M70 PRO         | Yes     |
| 911401513146 | RS378B P27 927 PSU-E MB M70 PRO         | Yes     |
| 911401513246 | RS378B P27 930 PSU-E MB M70 PRO         | Yes     |
| 911401513346 | RS378B P27 940 PSU-E MB M70 PRO         | Yes     |
| 911401513446 | RS378B P27 927 PSU-E WB M70 PRO         | Yes     |
| 911401513546 | RS378B P27 930 PSU-E WB M70 PRO         | Yes     |
| 911401513646 | RS378B P27 940 PSU-E WB M70 PRO         | Yes     |
| 911401516446 | RS378B P27 927 PSD-E NB M70 PRO         | Yes     |
| 911401516546 | RS378B P27 930 PSD-E NB M70 PRO         | Yes     |
| 911401516646 | RS378B P27 940 PSD-E NB M70 PRO         | Yes     |
| 911401516746 | RS378B P27 927 PSD-E MB M70 PRO         | Yes     |
| 911401516846 | RS378B P27 930 PSD-E MB M70 PRO         | Yes     |
| 911401516946 | RS378B P27 940 PSD-E MB M70 PRO         | Yes     |
| 911401517046 | RS378B P27 927 PSD-E WB M70 PRO         | Yes     |
| 911401517146 | RS378B P27 930 PSD-E WB M70 PRO         | Yes     |
| 911401517246 | RS378B P27 940 PSD-E WB M70 PRO         | Yes     |
| 911401517946 | RS378X P28 930 WIA MB M70 PRO           | Yes     |
| 911401518046 | RS378X P28 930 WIA WB M70 PRO           | Yes     |
| 911401518746 | RS378B P27 930 PSU-E MB M70 WP PRO      | Yes     |
| 911401518846 | RS378B P27 930 PSU-E WB M70 WP PRO      | Yes     |
| 911401521346 | RS378B P29 PSD-TNW NB M70 PRO           | No      |
| 911401521446 | RS378B P29 PSD-TNW MB M70 PRO           | No      |
| 911401521546 | RS378B P29 PSD-TNW WB M70 PRO           | No      |
| 911401530846 | SM378B S P8 927 PSU-E NB D100 G-TT PRO  | Yes     |
| 911401530946 | SM378B S P8 930 PSU-E NB D100 G-TT PRO  | Yes     |
| 911401531046 | SM378B S P8 940 PSU-E NB D100 G-TT PRO  | Yes     |
| 911401531146 | SM378B S P8 927 PSU-E MB D100 G-TT PRO  | Yes     |
| 911401531246 | SM378B S P8 930 PSU-E MB D100 G-TT PRO  | Yes     |
| 911401531346 | SM378B S P8 940 PSU-E MB D100 G-TT PRO  | Yes     |
| 911401531446 | SM378B S P8 927 PSU-E WB D100 G-TT PRO  | Yes     |
| 911401531546 | SM378B S P8 930 PSU-E WB D100 G-TT PRO  | Yes     |
| 911401531646 | SM378B S P8 940 PSU-E WB D100 G-TT PRO  | Yes     |
| 911401531746 | SM378B S P11 927 PSU-E NB D100 G-TT PRO | Yes     |
| 911401531846 | SM378B S P11 930 PSU-E NB D100 G-TT PRO | Yes     |
| 911401531946 | SM378B S P11 940 PSU-E NB D100 G-TT PRO | Yes     |
| 911401532046 | SM378B S P11 927 PSU-E MB D100 G-TT PRO | Yes     |
| 911401532146 | SM378B S P11 930 PSU-E MB D100 G-TT PRO | Yes     |
| 911401532246 | SM378B S P11 940 PSU-E MB D100 G-TT PRO | Yes     |
| 911401532346 | SM378B S P11 927 PSU-E WB D100 G-TT PRO | Yes     |
| 911401532446 | SM378B S P11 930 PSU-E WB D100 G-TT PRO | Yes     |
| 911401532546 | SM378B S P11 940 PSU-E WB D100 G-TT PRO | Yes     |
| 911401532646 | SM378B S P13 927 PSU-E NB D100 G-TT PRO | Yes     |
| 911401532746 | SM378B S P13 930 PSU-E NB D100 G-TT PRO | Yes     |
| 911401532846 | SM378B S P13 940 PSU-E NB D100 G-TT PRO | Yes     |

| Order Code   | Full Product Name                       | CE mark |
|--------------|-----------------------------------------|---------|
| 911401532946 | SM378B S P13 927 PSU-E MB D100 G-TT PRO | Yes     |
| 911401533046 | SM378B S P13 930 PSU-E MB D100 G-TT PRO | Yes     |
| 911401533146 | SM378B S P13 940 PSU-E MB D100 G-TT PRO | Yes     |
| 911401533246 | SM378B S P13 927 PSU-E WB D100 G-TT PRO | Yes     |
| 911401533346 | SM378B S P13 930 PSU-E WB D100 G-TT PRO | Yes     |
| 911401533446 | SM378B S P13 940 PSU-E WB D100 G-TT PRO | Yes     |
| 911401533546 | SM378B S P20 927 PSU-E NB D100 G-TT PRO | Yes     |
| 911401533646 | SM378B S P20 930 PSU-E NB D100 G-TT PRO | Yes     |
| 911401533746 | SM378B S P20 940 PSU-E NB D100 G-TT PRO | Yes     |
| 911401533846 | SM378B S P20 927 PSU-E MB D100 G-TT PRO | Yes     |
| 911401533946 | SM378B S P20 930 PSU-E MB D100 G-TT PRO | Yes     |
| 911401534046 | SM378B S P20 940 PSU-E MB D100 G-TT PRO | Yes     |
| 911401534146 | SM378B S P20 927 PSU-E WB D100 G-TT PRO | Yes     |
| 911401534246 | SM378B S P20 930 PSU-E WB D100 G-TT PRO | Yes     |
| 911401534346 | SM378B S P20 940 PSU-E WB D100 G-TT PRO | Yes     |
| 911401534446 | SM378B S P20 927 PSD-E NB D100 G-TT PRO | Yes     |
| 911401534546 | SM378B S P20 930 PSD-E NB D100 G-TT PRO | Yes     |
| 911401534646 | SM378B S P20 940 PSD-E NB D100 G-TT PRO | Yes     |
| 911401534746 | SM378B S P20 927 PSD-E MB D100 G-TT PRO | Yes     |
| 911401534846 | SM378B S P20 930 PSD-E MB D100 G-TT PRO | Yes     |
| 911401534946 | SM378B S P20 940 PSD-E MB D100 G-TT PRO | Yes     |
| 911401535046 | SM378B S P20 927 PSD-E WB D100 G-TT PRO | Yes     |
| 911401535146 | SM378B S P20 930 PSD-E WB D100 G-TT PRO | Yes     |
| 911401535246 | SM378B S P20 940 PSD-E WB D100 G-TT PRO | Yes     |
| 911401535446 | SM378B S P8 927 PSD-E NB D100 G-TT PRO  | Yes     |
| 911401535546 | SM378B S P8 930 PSD-E NB D100 G-TT PRO  | Yes     |
| 911401535646 | SM378B S P8 940 PSD-E NB D100 G-TT PRO  | Yes     |
| 911401535746 | SM378B S P8 927 PSD-E MB D100 G-TT PRO  | Yes     |
| 911401535846 | SM378B S P8 930 PSD-E MB D100 G-TT PRO  | Yes     |
| 911401535946 | SM378B S P8 940 PSD-E MB D100 G-TT PRO  | Yes     |
| 911401536046 | SM378B S P8 927 PSD-E WB D100 G-TT PRO  | Yes     |
| 911401536146 | SM378B S P8 930 PSD-E WB D100 G-TT PRO  | Yes     |
| 911401536246 | SM378B S P8 940 PSD-E WB D100 G-TT PRO  | Yes     |
| 911401536346 | SM378B S P12 927 PSD-E NB D100 G-TT PRO | Yes     |
| 911401536446 | SM378B S P12 930 PSD-E NB D100 G-TT PRO | Yes     |
| 911401536546 | SM378B S P12 940 PSD-E NB D100 G-TT PRO | Yes     |
| 911401536646 | SM378B S P12 927 PSD-E MB D100 G-TT PRO | Yes     |
| 911401536746 | SM378B S P12 930 PSD-E MB D100 G-TT PRO | Yes     |
| 911401536846 | SM378B S P12 940 PSD-E MB D100 G-TT PRO | Yes     |
| 911401536946 | SM378B S P12 927 PSD-E WB D100 G-TT PRO | Yes     |
| 911401537046 | SM378B S P12 930 PSD-E WB D100 G-TT PRO | Yes     |
| 911401537146 | SM378B S P12 940 PSD-E WB D100 G-TT PRO | Yes     |
| 911401537246 | SM378B S P14 927 PSD-E NB D100 G-TT PRO | Yes     |
| 911401537346 | SM378B S P14 930 PSD-E NB D100 G-TT PRO | Yes     |
| 911401537446 | SM378B S P14 940 PSD-E NB D100 G-TT PRO | Yes     |
| 911401537546 | SM378B S P14 927 PSD-E MB D100 G-TT PRO | Yes     |
| 911401537646 | SM378B S P14 930 PSD-E MB D100 G-TT PRO | Yes     |
| 911401537746 | SM378B S P14 940 PSD-E MB D100 G-TT PRO | Yes     |
| 911401537846 | SM378B S P14 927 PSD-E WB D100 G-TT PRO | Yes     |
| 911401537946 | SM378B S P14 930 PSD-E WB D100 G-TT PRO | Yes     |
| 911401538046 | SM378B S P14 940 PSD-E WB D100 G-TT PRO | Yes     |
| 911401538146 | SM378X S P8 930 WIA MB D100 G-TT PRO    | Yes     |



| Order Code   | Full Product Name                     | CE mark |
|--------------|---------------------------------------|---------|
| 911401538246 | SM378X S P8 930 WIA WB D100 G-TT PRO  | Yes     |
| 911401538346 | SM378X S P12 930 WIA MB D100 G-TT PRO | Yes     |
| 911401538446 | SM378X S P12 930 WIA WB D100 G-TT PRO | Yes     |
| 911401538546 | SM378X S P14 930 WIA MB D100 G-TT PRO | Yes     |
| 911401538646 | SM378X S P14 930 WIA WB D100 G-TT PRO | Yes     |
| 911401538746 | SM378X S P20 930 WIA MB D100 G-TT PRO | Yes     |
| 911401538846 | SM378X S P20 930 WIA WB D100 G-TT PRO | Yes     |
| 911401538946 | SM378B S P9 PSD-TNW NB D100 G-TT PRO  | No      |
| 911401539046 | SM378B S P9 PSD-TNW MB D100 G-TT PRO  | No      |
| 911401539146 | SM378B S P9 PSD-TNW WB D100 G-TT PRO  | No      |
| 911401539246 | SM378B S P12 PSD-TNW NB D100 G-TT PRO | No      |
| 911401539346 | SM378B S P12 PSD-TNW MB D100 G-TT PRO | No      |
| 911401539446 | SM378B S P12 PSD-TNW WB D100 G-TT PRO | No      |
| 911401539546 | SM378B S P15 PSD-TNW NB D100 G-TT PRO | No      |
| 911401539646 | SM378B S P15 PSD-TNW MB D100 G-TT PRO | No      |
| 911401539746 | SM378B S P15 PSD-TNW WB D100 G-TT PRO | No      |
| 911401539846 | SM378B S P22 PSD-TNW NB D100 G-TT PRO | No      |
| 911401539946 | SM378B S P22 PSD-TNW MB D100 G-TT PRO | No      |
| 911401540046 | SM378B S P22 PSD-TNW WB D100 G-TT PRO | No      |
| 911401503046 | RS378B P12 927 PSU-E NB M55 PRO       | Yes     |
| 911401503146 | RS378B P12 930 PSU-E NB M55 PRO       | Yes     |
| 911401503246 | RS378B P12 940 PSU-E NB M55 PRO       | Yes     |
| 911401503346 | RS378B P12 927 PSU-E MB M55 PRO       | Yes     |
| 911401503446 | RS378B P12 930 PSU-E MB M55 PRO       | Yes     |
| 911401503546 | RS378B P12 940 PSU-E MB M55 PRO       | Yes     |
| 911401503646 | RS378B P12 927 PSU-E WB M55 PRO       | Yes     |
| 911401503746 | RS378B P12 930 PSU-E WB M55 PRO       | Yes     |
| 911401503846 | RS378B P12 940 PSU-E WB M55 PRO       | Yes     |
| 911401503946 | RS378B P14 927 PSU-E NB M55 PRO       | Yes     |
| 911401504046 | RS378B P14 930 PSU-E NB M55 PRO       | Yes     |
| 911401504146 | RS378B P14 940 PSU-E NB M55 PRO       | Yes     |
| 911401504246 | RS378B P14 927 PSU-E MB M55 PRO       | Yes     |
| 911401504346 | RS378B P14 930 PSU-E MB M55 PRO       | Yes     |
| 911401504446 | RS378B P14 940 PSU-E MB M55 PRO       | Yes     |
| 911401504546 | RS378B P14 927 PSU-E WB M55 PRO       | Yes     |

| Order Code   | Full Product Name                  | CE mark |
|--------------|------------------------------------|---------|
| 911401504646 | RS378B P14 930 PSU-E WB M55 PRO    | Yes     |
| 911401504746 | RS378B P14 940 PSU-E WB M55 PRO    | Yes     |
| 911401506946 | RS378B P13 927 PSD-E NB M55 PRO    | Yes     |
| 911401507046 | RS378B P13 930 PSD-E NB M55 PRO    | Yes     |
| 911401507146 | RS378B P13 940 PSD-E NB M55 PRO    | Yes     |
| 911401507246 | RS378B P13 927 PSD-E MB M55 PRO    | Yes     |
| 911401507346 | RS378B P13 930 PSD-E MB M55 PRO    | Yes     |
| 911401507446 | RS378B P13 940 PSD-E MB M55 PRO    | Yes     |
| 911401507546 | RS378B P13 927 PSD-E WB M55 PRO    | Yes     |
| 911401507646 | RS378B P13 930 PSD-E WB M55 PRO    | Yes     |
| 911401507746 | RS378B P13 940 PSD-E WB M55 PRO    | Yes     |
| 911401507846 | RS378B P15 927 PSD-E NB M55 PRO    | Yes     |
| 911401507946 | RS378B P15 930 PSD-E NB M55 PRO    | Yes     |
| 911401508046 | RS378B P15 940 PSD-E NB M55 PRO    | Yes     |
| 911401508146 | RS378B P15 927 PSD-E MB M55 PRO    | Yes     |
| 911401508246 | RS378B P15 930 PSD-E MB M55 PRO    | Yes     |
| 911401508346 | RS378B P15 940 PSD-E MB M55 PRO    | Yes     |
| 911401508446 | RS378B P15 927 PSD-E WB M55 PRO    | Yes     |
| 911401508546 | RS378B P15 930 PSD-E WB M55 PRO    | Yes     |
| 911401508646 | RS378B P15 940 PSD-E WB M55 PRO    | Yes     |
| 911401508946 | RS378X P12 930 WIA MB M55 PRO      | Yes     |
| 911401509046 | RS378X P12 930 WIA WB M55 PRO      | Yes     |
| 911401509146 | RS378X P14 930 WIA MB M55 PRO      | Yes     |
| 911401509246 | RS378X P14 930 WIA WB M55 PRO      | Yes     |
| 911401509746 | RS378B P12 930 PSU-E MB M55 WP PRO | Yes     |
| 911401509846 | RS378B P12 930 PSU-E WB M55 WP PRO | Yes     |
| 911401509946 | RS378B P14 930 PSU-E MB M55 WP PRO | Yes     |
| 911401510046 | RS378B P14 930 PSU-E WB M55 WP PRO | Yes     |
| 911401519546 | RS378B P13 PSD-TNW NB M55 PRO      | No      |
| 911401519646 | RS378B P13 PSD-TNW MB M55 PRO      | No      |
| 911401519746 | RS378B P13 PSD-TNW WB M55 PRO      | No      |
| 911401519846 | RS378B P15 PSD-TNW NB M55 PRO      | No      |
| 911401519946 | RS378B P15 PSD-TNW MB M55 PRO      | No      |
| 911401520046 | RS378B P15 PSD-TNW WB M55 PRO      | No      |

