



# A powerful discreet spots with an accent on sustainability

## LuxSpace Accent Compact Adjustable

With LuxSpace Accent Compact Adjustable, retailers and building operators can enjoy the superior quality of light and market-leading energy efficiency of PerfectAccent optics in a refined and neutral spot design. Powerful and discreet, LuxSpace Accent combines a high luminous flux in a compact form factor. Design-in and installation are easy due to its small built-in dimensions. Maintenance and upgrades of the optics is fast and requires no tools. Furthermore, LuxSpace Compact Adjustable spots are certified as circular lighting products and offer multiple system integration and dimming options, including wired as well as wireless. LuxSpace Accent Compact Adjustable allows spot head rotation and two-directional tilting for maximum aiming flexibility. For prolonged shelf life and better visual representation of food, reducing food waste and increasing sales, fresh food LED lighting recipes are available. Check out our Fashion and Food catalog pages to find out more about PremiumWhite, PremiumColor, Fresh Meat, Rosé, Frost and Champagne.

### Benefits

- More sparkle and enhanced shopper eye comfort with PerfectAccent optics
- Best-in-class efficacy to reduce carbon footprint and save on energy use
- Certified as circular lighting with PerfectAccent high-efficacy reflectors
- Easy maintenance and upgrades with tool-less access to driver and optics
- The clean and refined product design helps the spots blend in with ceilings

# LuxSpace Accent Compact Adjustable

## Features

- RS771B offers high maximum flux (4900lm) in a very compact housing with limited built-in dimensions
- Available with PerfectAccent high-efficacy reflectors
- Optional front glass (advised in dusty environments)
- Two-directional tilt for great light control
- Available with fresh food LED lighting recipes and LED flavors
- Wired (DALI) and wireless connectivity options

## Application

- Convenience stores
- Supermarkets & hypermarkets
- Offices and hospitality areas

## Warnings and Safety

- All photometrical data is calculated without optional front glass. Flux should be reduced by 3.5% when using a front glass
- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For food preparation areas and areas with high levels of dust, the use of the optional front glass is strongly advised, as it can be cleaned with a (dry) microfiber cloth
- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove

## Versions





RS771B LuxSpace Accent Compact  
Adjustable Black



RS771B LuxSpace Accent Compact  
Adjustable Silver

## Dimensional drawing



# LuxSpace Accent Compact Adjustable

## Product details

LuxSpace Accent Adjustable  
luminaires offer 2-way tilting for  
easy aiming in any installation

Step5 (optional): Add or remove  
the front glass



Step4: Replace the reflector

RS771B LuxSpace Accent Compact  
Adjustable Back View



Step1; Press the button to unlock  
the front face



Step2: Remove the optical  
assembly from the luminaire

Step3: Pull the clip of the frontface  
to release the reflector



# LuxSpace Accent Compact Adjustable

## Product details



PerfectAccent reflector and front glass maintenance and upgrading is easy with an integrated button

### General Information

|                          |        |
|--------------------------|--------|
| Driver included          | Yes    |
| Light source replaceable | No     |
| Number of gear units     | 1 unit |
| Service tag              | Yes    |

### Light Technical

|                            |               |
|----------------------------|---------------|
| Beam angle of light source | 120 degree(s) |
|----------------------------|---------------|

### Operating and Electrical

|                               |                 |
|-------------------------------|-----------------|
| Protection class IEC          | Safety class II |
| Input Voltage                 | 220 to 240 V    |
| Line Frequency                | 50 to 60 Hz     |
| Suitable for random switching | No              |

### Mechanical and Housing

|                              |      |
|------------------------------|------|
| Mech. impact protection code | IK02 |
| Ingress protection code      | IP20 |

### Approval and Application

|                                                                 |                                             |
|-----------------------------------------------------------------|---------------------------------------------|
| Ambient temperature range                                       | +10 to +35 °C                               |
| CE mark                                                         | Yes                                         |
| ENEC mark                                                       | ENEC mark                                   |
| Flammability mark                                               | For mounting on normally flammable surfaces |
| Glow-wire test                                                  | Temperature 650 °C, duration 30 s           |
| Flickering value (PstLM) - Flickering value as per EN 61000-3-3 | 1                                           |
| Stroboscopic effect visibility measure (SVM)                    | 0.5                                         |

### Initial Performance (IEC Compliant)

|                         |        |
|-------------------------|--------|
| Luminous flux tolerance | +/-10% |
|-------------------------|--------|

### Product Data

|                     |        |
|---------------------|--------|
| Product family code | RS771B |
|---------------------|--------|

## Light Technical (1/2)

| Order Code | Full Product Name               | Correlated Color Temperature (Nom) | Color rendering index (CRI) | Luminous Efficacy (rated) (Nom) | Luminous Flux |
|------------|---------------------------------|------------------------------------|-----------------------------|---------------------------------|---------------|
| 97880800   | RS771B 17S/930 PSU-E HWB WH     | 3000 K                             | >90                         | 128 lm/W                        | 1,950 lm      |
| 97884600   | RS771B 19S/ROSE PSU-E HWB FG WH | 2200 K                             | >80                         | 97 lm/W                         | 2,000 lm      |
| 97886000   | RS771B 19S/FMT PSU-E HWB FG WH  | 3000 K                             | >90                         | 86 lm/W                         | 1,900 lm      |
| 97887700   | RS771B 20S/830 PSU-E NB WH      | 3000 K                             | >80                         | 105 lm/W                        | 2,200 lm      |
| 97888400   | RS771B 27S/827 PSU-E WB WH      | 2700 K                             | >80                         | 115 lm/W                        | 2,700 lm      |
| 97889100   | RS771B 27S/830 PSU-E MB WH      | 3000 K                             | >80                         | 121 lm/W                        | 2,850 lm      |
| 97890700   | RS771B 27S/830 DIA-VLC-E HMB WH | 3000 K                             | >80                         | 138 lm/W                        | 2,850 lm      |
| 97891400   | RS771B 27S/830 WIA-E MB WH      | 3000 K                             | >80                         | 121 lm/W                        | 2,850 lm      |
| 97892100   | RS771B 27S/840 PSU-E WB WH      | 4000 K                             | >80                         | 125 lm/W                        | 2,950 lm      |
| 97894500   | RS771B 27S/PW930 PSU-E HWB WH   | 3000 K                             | >90                         | 138 lm/W                        | 2,600 lm      |
| 97895200   | RS771B 27S/PC930 PSU-E HWB WH   | 3000 K                             | >90                         | 123 lm/W                        | 2,850 lm      |
| 97896900   | RS771B 27S/ROSE PSU-E HWB FG WH | 2200 K                             | >80                         | 99 lm/W                         | 2,900 lm      |
| 97897600   | RS771B 27S/FMT PSU-E HWB FG WH  | 3000 K                             | >90                         | 81 lm/W                         | 2,600 lm      |
| 97898300   | RS771B 27S/CH PSU-E HWB FG WH   | 2700 K                             | >80                         | 115 lm/W                        | 2,700 lm      |
| 97899000   | RS771B 27S/FR PSU-E HWB FG WH   | 5000 K                             | >90                         | 98 lm/W                         | 2,700 lm      |
| 97901000   | RS771B 39S/830 PSU-E VWB WH     | 3000 K                             | >80                         | 129 lm/W                        | 4,000 lm      |
| 97902700   | RS771B 39S/840 PSU-E WB WH      | 4000 K                             | >80                         | 135 lm/W                        | 4,000 lm      |

## LuxSpace Accent Compact Adjustable

| Order Code | Full Product Name             | Correlated Color     | Color                    | Luminous Efficacy<br>(rated) (Nom) | Luminous Flux |
|------------|-------------------------------|----------------------|--------------------------|------------------------------------|---------------|
|            |                               | Temperature<br>(Nom) | rendering<br>index (CRI) |                                    |               |
| 97903400   | RS771B 39S/930 PSU-E WB WH    | 3000 K               | >90                      | 124 lm/W                           | 3,850 lm      |
| 97904100   | RS771B 39S/PW930 PSU-E WB WH  | 3000 K               | >90                      | 124 lm/W                           | 3,850 lm      |
| 97905800   | RS771B 49S/827 PSU-E HWB WH   | 2700 K               | >80                      | 126 lm/W                           | 4,850 lm      |
| 97906500   | RS771B 49S/830 PSU-E HWB WH   | 3000 K               | >80                      | 129 lm/W                           | 5,000 lm      |
| 97907200   | RS771B 49S/840 PSU-E HWB WH   | 4000 K               | >80                      | 136 lm/W                           | 5,250 lm      |
| 97908900   | RS771B 49S/930 PSU-E HWB WH   | 3000 K               | >90                      | 125 lm/W                           | 4,900 lm      |
| 97909600   | RS771B 49S/PW930 PSU-E HWB WH | 3000 K               | >90                      | 125 lm/W                           | 4,900 lm      |
| 97893800   | RS771B 27S/930 PSU-E WB BK    | 3000 K               | >90                      | 122 lm/W                           | 2,800 lm      |
| 97900300   | RS771B 39S/827 PSU-E WB SI    | 2700 K               | >80                      | 124 lm/W                           | 3,900 lm      |

### Light Technical (2/2)

| Order Code | Full Product Name               | Optic type                                                   | Order Code | Full Product Name             | Optic type                                                 |
|------------|---------------------------------|--------------------------------------------------------------|------------|-------------------------------|------------------------------------------------------------|
| 97880800   | RS771B 17S/930 PSU-E HWB WH     | High-reflective metal reflector Wide beam 40 to 80 degrees   | 97898300   | RS771B 27S/CH PSU-E HWB FG WH | High-reflective metal reflector Wide beam 40 to 80 degrees |
| 97884600   | RS771B 19S/ROSE PSU-E HWB FG WH | High-reflective metal reflector Wide beam 40 to 80 degrees   | 97899000   | RS771B 27S/FR PSU-E HWB FG WH | High-reflective metal reflector Wide beam 40 to 80 degrees |
| 97886000   | RS771B 19S/FMT PSU-E HWB FG WH  | High-reflective metal reflector Wide beam 40 to 80 degrees   | 97901000   | RS771B 39S/830 PSU-E VWB WH   | Very wide beam                                             |
| 97887700   | RS771B 20S/830 PSU-E NB WH      | Narrow beam                                                  | 97902700   | RS771B 39S/840 PSU-E WB WH    | Wide beam                                                  |
| 97888400   | RS771B 27S/827 PSU-E WB WH      | Wide beam                                                    | 97903400   | RS771B 39S/930 PSU-E WB WH    | Wide beam                                                  |
| 97889100   | RS771B 27S/830 PSU-E MB WH      | Medium beam                                                  | 97904100   | RS771B 39S/PW930 PSU-E WB WH  | Wide beam                                                  |
| 97890700   | RS771B 27S/830 DIA-VLC-E HMB WH | High-reflective metal reflector Medium beam 20 to 40 degrees | 97905800   | RS771B 49S/827 PSU-E HWB WH   | High-reflective metal reflector Wide beam 40 to 80 degrees |
| 97891400   | RS771B 27S/830 WIA-E MB WH      | Medium beam                                                  | 97906500   | RS771B 49S/830 PSU-E HWB WH   | High-reflective metal reflector Wide beam 40 to 80 degrees |
| 97892100   | RS771B 27S/840 PSU-E WB WH      | Wide beam                                                    | 97907200   | RS771B 49S/840 PSU-E HWB WH   | High-reflective metal reflector Wide beam 40 to 80 degrees |
| 97894500   | RS771B 27S/PW930 PSU-E HWB WH   | High-reflective metal reflector Wide beam 40 to 80 degrees   | 97908900   | RS771B 49S/930 PSU-E HWB WH   | High-reflective metal reflector Wide beam 40 to 80 degrees |
| 97895200   | RS771B 27S/PC930 PSU-E HWB WH   | High-reflective metal reflector Wide beam 40 to 80 degrees   | 97909600   | RS771B 49S/PW930 PSU-E HWB WH | High-reflective metal reflector Wide beam 40 to 80 degrees |
| 97896900   | RS771B 27S/ROSE PSU-E HWB FG WH | High-reflective metal reflector Wide beam 40 to 80 degrees   | 97893800   | RS771B 27S/930 PSU-E WB BK    | Wide beam                                                  |
| 97897600   | RS771B 27S/FMT PSU-E HWB FG WH  | High-reflective metal reflector Wide beam 40 to 80 degrees   | 97900300   | RS771B 39S/827 PSU-E WB SI    | Wide beam                                                  |

### Operating and Electrical

| Order Code | Full Product Name               | Power Consumption | Order Code | Full Product Name              | Power Consumption |
|------------|---------------------------------|-------------------|------------|--------------------------------|-------------------|
| 97880800   | RS771B 17S/930 PSU-E HWB WH     | 14 W              | 97886000   | RS771B 19S/FMT PSU-E HWB FG WH | 22 W              |
| 97884600   | RS771B 19S/ROSE PSU-E HWB FG WH | 20.5 W            | 97887700   | RS771B 20S/830 PSU-E NB WH     | 20.5 W            |

LuxSpace Accent Compact Adjustable

| Order Code | Full Product Name               | Power Consumption |
|------------|---------------------------------|-------------------|
| 97888400   | RS771B 27S/827 PSU-E WB WH      | 23.5 W            |
| 97889100   | RS771B 27S/830 PSU-E MB WH      | 23.5 W            |
| 97890700   | RS771B 27S/830 DIA-VLC-E HMB WH | 19 W              |
| 97891400   | RS771B 27S/830 WIA-E MB WH      | 23.5 W            |
| 97892100   | RS771B 27S/840 PSU-E WB WH      | 23.5 W            |
| 97894500   | RS771B 27S/PW930 PSU-E HWB WH   | 18.8 W            |
| 97895200   | RS771B 27S/PC930 PSU-E HWB WH   | 23 W              |
| 97896900   | RS771B 27S/ROSE PSU-E HWB FG WH | 29 W              |
| 97897600   | RS771B 27S/FMT PSU-E HWB FG WH  | 31.5 W            |
| 97898300   | RS771B 27S/CH PSU-E HWB FG WH   | 23.5 W            |
| 97899000   | RS771B 27S/FR PSU-E HWB FG WH   | 28.5 W            |

| Order Code | Full Product Name             | Power Consumption |
|------------|-------------------------------|-------------------|
| 97901000   | RS771B 39S/830 PSU-E VWB WH   | 31.5 W            |
| 97902700   | RS771B 39S/840 PSU-E WB WH    | 29.5 W            |
| 97903400   | RS771B 39S/930 PSU-E WB WH    | 31 W              |
| 97904100   | RS771B 39S/PW930 PSU-E WB WH  | 31 W              |
| 97905800   | RS771B 49S/827 PSU-E HWB WH   | 38.5 W            |
| 97906500   | RS771B 49S/830 PSU-E HWB WH   | 38.5 W            |
| 97907200   | RS771B 49S/840 PSU-E HWB WH   | 38.5 W            |
| 97908900   | RS771B 49S/930 PSU-E HWB WH   | 39 W              |
| 97909600   | RS771B 49S/PW930 PSU-E HWB WH | 39 W              |
| 97893800   | RS771B 27S/930 PSU-E WB BK    | 23 W              |
| 97900300   | RS771B 39S/827 PSU-E WB SI    | 31.5 W            |

Controls and Dimming

| Order Code | Full Product Name               | Dimmable | Maximum dim level |
|------------|---------------------------------|----------|-------------------|
| 97880800   | RS771B 17S/930 PSU-E HWB WH     | No       | Not applicable    |
| 97884600   | RS771B 19S/ROSE PSU-E HWB FG WH | No       | Not applicable    |
| 97886000   | RS771B 19S/FMT PSU-E HWB FG WH  | No       | Not applicable    |
| 97887700   | RS771B 20S/830 PSU-E NB WH      | No       | Not applicable    |
| 97888400   | RS771B 27S/827 PSU-E WB WH      | No       | Not applicable    |
| 97889100   | RS771B 27S/830 PSU-E MB WH      | No       | Not applicable    |
| 97890700   | RS771B 27S/830 DIA-VLC-E HMB WH | Yes      | 1%                |
| 97891400   | RS771B 27S/830 WIA-E MB WH      | Yes      | Not applicable    |
| 97892100   | RS771B 27S/840 PSU-E WB WH      | No       | Not applicable    |
| 97894500   | RS771B 27S/PW930 PSU-E HWB WH   | No       | Not applicable    |
| 97895200   | RS771B 27S/PC930 PSU-E HWB WH   | No       | Not applicable    |
| 97896900   | RS771B 27S/ROSE PSU-E HWB FG WH | No       | Not applicable    |
| 97897600   | RS771B 27S/FMT PSU-E HWB FG WH  | No       | Not applicable    |

| Order Code | Full Product Name             | Dimmable | Maximum dim level |
|------------|-------------------------------|----------|-------------------|
| 97898300   | RS771B 27S/CH PSU-E HWB FG WH | No       | Not applicable    |
| 97899000   | RS771B 27S/FR PSU-E HWB FG WH | No       | Not applicable    |
| 97901000   | RS771B 39S/830 PSU-E VWB WH   | No       | Not applicable    |
| 97902700   | RS771B 39S/840 PSU-E WB WH    | No       | Not applicable    |
| 97903400   | RS771B 39S/930 PSU-E WB WH    | No       | Not applicable    |
| 97904100   | RS771B 39S/PW930 PSU-E WB WH  | No       | Not applicable    |
| 97905800   | RS771B 49S/827 PSU-E HWB WH   | No       | Not applicable    |
| 97906500   | RS771B 49S/830 PSU-E HWB WH   | No       | Not applicable    |
| 97907200   | RS771B 49S/840 PSU-E HWB WH   | No       | Not applicable    |
| 97908900   | RS771B 49S/930 PSU-E HWB WH   | No       | Not applicable    |
| 97909600   | RS771B 49S/PW930 PSU-E HWB WH | No       | Not applicable    |
| 97893800   | RS771B 27S/930 PSU-E WB BK    | No       | Not applicable    |
| 97900300   | RS771B 39S/827 PSU-E WB SI    | No       | Not applicable    |

Mechanical and Housing

| Order Code | Full Product Name               | Housing Color |
|------------|---------------------------------|---------------|
| 97880800   | RS771B 17S/930 PSU-E HWB WH     | White         |
| 97884600   | RS771B 19S/ROSE PSU-E HWB FG WH | White         |
| 97886000   | RS771B 19S/FMT PSU-E HWB FG WH  | White         |
| 97887700   | RS771B 20S/830 PSU-E NB WH      | White         |
| 97888400   | RS771B 27S/827 PSU-E WB WH      | White         |
| 97889100   | RS771B 27S/830 PSU-E MB WH      | White         |
| 97890700   | RS771B 27S/830 DIA-VLC-E HMB WH | White         |
| 97891400   | RS771B 27S/830 WIA-E MB WH      | White         |
| 97892100   | RS771B 27S/840 PSU-E WB WH      | White         |
| 97894500   | RS771B 27S/PW930 PSU-E HWB WH   | White         |
| 97895200   | RS771B 27S/PC930 PSU-E HWB WH   | White         |
| 97896900   | RS771B 27S/ROSE PSU-E HWB FG WH | White         |
| 97897600   | RS771B 27S/FMT PSU-E HWB FG WH  | White         |

| Order Code | Full Product Name             | Housing Color |
|------------|-------------------------------|---------------|
| 97898300   | RS771B 27S/CH PSU-E HWB FG WH | White         |
| 97899000   | RS771B 27S/FR PSU-E HWB FG WH | White         |
| 97901000   | RS771B 39S/830 PSU-E VWB WH   | White         |
| 97902700   | RS771B 39S/840 PSU-E WB WH    | White         |
| 97903400   | RS771B 39S/930 PSU-E WB WH    | White         |
| 97904100   | RS771B 39S/PW930 PSU-E WB WH  | White         |
| 97905800   | RS771B 49S/827 PSU-E HWB WH   | White         |
| 97906500   | RS771B 49S/830 PSU-E HWB WH   | White         |
| 97907200   | RS771B 49S/840 PSU-E HWB WH   | White         |
| 97908900   | RS771B 49S/930 PSU-E HWB WH   | White         |
| 97909600   | RS771B 49S/PW930 PSU-E HWB WH | White         |
| 97893800   | RS771B 27S/930 PSU-E WB BK    | Black         |
| 97900300   | RS771B 39S/827 PSU-E WB SI    | Silver        |

Initial Performance (IEC Compliant)

| Order Code | Full Product Name               | Initial chromaticity |
|------------|---------------------------------|----------------------|
| 97880800   | RS771B 17S/930 PSU-E HWB WH     | (0.434,0.403)<2      |
| 97884600   | RS771B 19S/ROSE PSU-E HWB FG WH | (0.478,0.382)<2      |




| Order Code | Full Product Name              | Initial chromaticity |
|------------|--------------------------------|----------------------|
| 97886000   | RS771B 19S/FMT PSU-E HWB FG WH | (0.457,0.385)<3      |
| 97887700   | RS771B 20S/830 PSU-E NB WH     | (0.434,0.403)<3      |

LuxSpace Accent Compact Adjustable

| Order Code | Full Product Name               | Initial chromaticity |
|------------|---------------------------------|----------------------|
| 97888400   | RS771B 27S/827 PSU-E WB WH      | (0.458,0.410)<3      |
| 97889100   | RS771B 27S/830 PSU-E MB WH      | (0.434,0.403)<3      |
| 97890700   | RS771B 27S/830 DIA-VLC-E HMB WH | (0.434,0.403)<3      |
| 97891400   | RS771B 27S/830 WIA-E MB WH      | (0.434,0.403)<3      |
| 97892100   | RS771B 27S/840 PSU-E WB WH      | (0.382,0.380)<3      |
| 97894500   | RS771B 27S/PW930 PSU-E HWB WH   | (0.422,0.386)<2      |
| 97895200   | RS771B 27S/PC930 PSU-E HWB WH   | (0.422,0.386)<2      |
| 97896900   | RS771B 27S/ROSE PSU-E HWB FG WH | (0.478,0.382)<2      |
| 97897600   | RS771B 27S/FMT PSU-E HWB FG WH  | (0.457,0.385)<3      |
| 97898300   | RS771B 27S/CH PSU-E HWB FG WH   | (0.458,0.410)<3      |
| 97899000   | RS771B 27S/FR PSU-E HWB FG WH   | (0.343,0.331)<3      |

| Order Code | Full Product Name             | Initial chromaticity |
|------------|-------------------------------|----------------------|
| 97901000   | RS771B 39S/830 PSU-E VWB WH   | (0.434,0.403)<3      |
| 97902700   | RS771B 39S/840 PSU-E WB WH    | (0.382,0.380)<3      |
| 97903400   | RS771B 39S/930 PSU-E WB WH    | (0.434,0.403)<2      |
| 97904100   | RS771B 39S/PW930 PSU-E WB WH  | (0.422,0.386)<2      |
| 97905800   | RS771B 49S/827 PSU-E HWB WH   | (0.458,0.410)<3      |
| 97906500   | RS771B 49S/830 PSU-E HWB WH   | (0.434,0.403)<3      |
| 97907200   | RS771B 49S/840 PSU-E HWB WH   | (0.382,0.380)<3      |
| 97908900   | RS771B 49S/930 PSU-E HWB WH   | (0.434,0.403)<2      |
| 97909600   | RS771B 49S/PW930 PSU-E HWB WH | (0.422,0.386)<2      |
| 97893800   | RS771B 27S/930 PSU-E WB BK    | (0.434,0.403)<2      |
| 97900300   | RS771B 39S/827 PSU-E WB SI    | (0.458,0.410)<3      |




Polar Wide Diagrams



Polar Normal (separate) - RS770BI - 910505101575

Polar Normal (separate) - RS770BI - 910505101576

Polar Normal (separate) - RS770BI - 910505101577




Polar Normal (separate) - RS770BI - 910505101581

Polar Normal (separate) - RS770BI - 910505101582


Polar Normal (separate) - RS770BI - 910505101572

# LuxSpace Accent Compact Adjustable


## Polar Wide Diagrams




Polar Normal (separate) - RS770BI - 910505101585




Polar Normal (separate) - RS770BI - 910505101586




Polar Normal (separate) - RS770BI - 910505101584




Polar Normal (separate) - RS770BI - 910505101579




Polar Normal (separate) - RS770BI - 910505101589




Polar Normal (separate) - RS770BI - 910505101593



Polar Normal (separate) - RS770BI - 910505101591




Polar Normal (separate) - RS770BI - 910505101580




Polar Normal (separate) - RS770BI - 910505101573

LuxSpace Accent Compact Adjustable


Polar Wide Diagrams




Polar Normal (separate) - RS770BI - 910505101587




Polar Normal (separate) - RS770BI - 910505101583




Polar Normal (separate) - RS770BI - 910505101592




Polar Normal (separate) - RS770BI - 910505101578




Polar Normal (separate) - RS770BI - 910505101566




Polar Normal (separate) - RS770BI - 910505101571



Polar Normal (separate) - RS770BI - 910505101588




Polar Normal (separate) - RS770BI - 910505101594




Polar Normal (separate) - RS770BI - 910505101574

# LuxSpace Accent Compact Adjustable

## Polar Wide Diagrams



Polar Normal (separate) - RS770BI -  
910505101570



Polar Normal (separate) - RS770BI -  
910505101590

