



The flexible light line

KeyLine, Surface & Suspended

These days, many office owners and office lighting designers prefer lines of light. The reason is simple. Not only do light lines come in a minimalistic design; they also offer far more choice and flexibility. Short or long lines and luminaires, standalone luminaires, different optics including asymmetric, different shapes and even a variety of colors; anything is possible. And with KeyLine, all these benefits come at a competitive price while still complying with office lighting norms. KeyLine is a superb light line range with a slim, minimalistic design and a high lumen output to illuminate the brightest office spaces. But with comfortable, low levels of glare it's also easy on the eye and complies with UGR19. That makes KeyLine ideal for linear applications, as well as standalone suspended or surface-mounted luminaires (Accessories to be ordered separately). A range that offers the ultimate flexibility and unlimited possibilities. KeyLine design flexibility comes in the form of different lengths, colors and light outputs - including L-shapes, as well as straight lines. All with high efficiency up to 142 lm/W, and the option to upgrade with wireless connectivity and control. Add to that attractive pricing, and with KeyLine you can also enjoy excellent value that ensures a superb total cost of ownership.

Benefits

- Suitable for office applications
- Excellent total cost of ownership
- Wide range of options to suit the demands of different offices

Features

- Comfortable, low glare: <UGR19 for the full range
- High lumen output, up to 4000lm for 1.2m version
- Interact Connectivity ready with wireless drivers
- Standard options in different lengths, colors and light outputs
- Customization options

KeyLine, Surface & Suspended


Application

- Offices
- Retail
- Education

Warnings and Safety

- KeyLine luminaires have an IP20 classification and are not protected against water ingress. We strongly recommend that the installation environment is checked for suitability.
- If – despite the IPX0 classification warning – luminaires are subject to water ingress, Philips and Signify cannot guarantee safety or prevent failure. In this case the product warranty does not apply and becomes void.

Versions




KeyLine L-corner, black

KeyLine L-corner, alu

KeyLine L-corner, white

KeyLine Asymmetric SM531C SPP

Dimensional drawing



KeyLine, Surface & Suspended


Product details



KeyLine line coupling, alu



KeyLine black with ceiling bracket
accessory for surface mounting



KeyLine black with coupling piece
accessory for line mounting



KeyLine Asymmetric SM531C
detailed



KeyLine_SM350C_WIA_DPP1



KeyLine line configuration, white



KeyLine SM350C, white



KeyLine configuration with L-
corner SM350X



KeyLine black with end-cap
accessory




KeyLine line coupling, white

KeyLine, Surface & Suspended

Product details



KeyLine alu with suspension set
for suspended mounting



KeyLine white line coupling with
coupling piece accessory



KeyLine_SM350C_WIA_DPP3



KeyLine alu with end-cap
accessory



KeyLine white with coupling piece
accessory for line mounting



KeyLine structured optics UGR19
(PCS)



KeyLine line coupling, black



KeyLine SM350C, alu



KeyLine alu line coupling with
coupling piece accessory

KeyLine, Surface & Suspended

Product details



KeyLine line configuration, black



KeyLine alu with ceiling bracket accessory for surface mounting



KeyLine white with suspension set for suspended mounting



KeyLine white with ceiling bracket accessory for surface mounting



KeyLine white with end-cap accessory




KeyLine alu with coupling piece accessory for line mounting



KeyLine SM350C, black



KeyLine L-corner, black



KeyLine black line coupling with coupling piece accessory



KeyLine black with suspension set for suspended mounting



KeyLine_SM350C_WIA_DPP2


KeyLine, Surface & Suspended

Product details

KeyLine L-corner, alu



KeyLine L-corner, white



General Information

Driver included	Yes
Number of gear units	1 unit
Service tag	Yes

Light Technical

Color rendering index (CRI)	>80
-----------------------------	-----

Operating and Electrical

Protection class IEC	Safety class I
Line Frequency	50 to 60 Hz

Mechanical and Housing

Ingress protection code	IP20
-------------------------	------

Approval and Application

Ambient temperature range	+10 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 30 s
Stroboscopic effect visibility measure (SVM)	0.4

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

General Information

Order Code	Full Product Name	Light source replaceable
62454200	SM350X 27S/840 PSD PCS N BK	No
62442900	SM350C 34S/840 PSU PCS L1500 BK	No
62445000	SM350C 50S/840 PSU PCS L1500 BK	No
62448100	SM350C 34S/840 PSD PCS L1500 BK	No
62451100	SM350C 50S/840 PSD PCS L1500 BK	No
62367500	SM350C 27S/840 PSU PCS L1200 ALU	No
62417700	SM350C 40S/840 PSU PCS L1200 ALU	No
62420700	SM350C 27S/840 PSD PCS L1200 ALU	No
62423800	SM350C 40S/840 PSD PCS L1200 ALU	No
62432000	SM350C 27S/830 PSU PCS L1200 ALU	No
62434400	SM350C 40S/830 PSU PCS L1200 ALU	No
62436800	SM350C 27S/830 PSD PCS L1200 ALU	No
62438200	SM350C 40S/830 PSD PCS L1200 ALU	No
62452800	SM350X 27S/840 PSD L60L60 PCS ALU	No
62440500	SM350C 34S/840 PSU PCS L1500 ALU	No
62443600	SM350C 50S/840 PSU PCS L1500 ALU	No
62446700	SM350C 34S/840 PSD PCS L1500 ALU	No
62449800	SM350C 50S/840 PSD PCS L1500 ALU	No
62441200	SM350C 34S/840 PSU PCS L1500 WH	No
62444300	SM350C 50S/840 PSU PCS L1500 WH	No
62447400	SM350C 34S/840 PSD PCS L1500 WH	No
62450400	SM350C 50S/840 PSD PCS L1500 WH	No
62430600	SM350C 40S/840 WIA PCS L1200 WH	No
62431300	SM350C 40S/840 WIA PCS L1200 BK	No
62415300	SM350C 27S/840 PSU PCS L1200 WH	No
62418400	SM350C 40S/840 PSU PCS L1200 WH	No
62421400	SM350C 27S/840 PSD PCS L1200 WH	No
62424500	SM350C 40S/840 PSD PCS L1200 WH	No
62433700	SM350C 27S/830 PSU PCS L1200 WH	No
62435100	SM350C 40S/830 PSU PCS L1200 WH	No
62437500	SM350C 27S/830 PSD PCS L1200 WH	No
62439900	SM350C 40S/830 PSD PCS L1200 WH	No
62416000	SM350C 27S/840 PSU PCS L1200 BK	No
62419100	SM350C 40S/840 PSU PCS L1200 BK	No
62422100	SM350C 27S/840 PSD PCS L1200 BK	No
62425200	SM350C 40S/840 PSD PCS L1200 BK	No
62453500	SM350X 27S/840 PSD L60L60 PCS WH	No
61518200	SM351C 40S/840 PSU A PCS L1200 WH	-
61519900	SM351C 40S/840 PSD A PCS L1200 WH	-

KeyLine, Surface & Suspended

Order Code	Full Product Name	Light source replaceable
61520500	SM351C 50S/840 PSU A PCS L1500 WH	-
61521200	SM351C 50S/840 PSD A PCS L1500 WH	-

Light Technical (1/2)

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
62454200	SM350X 27S/840 PSD PCS N BK	120 degree(s)	4000 K	138 lm/W	2,900 lm
62442900	SM350C 34S/840 PSU PCS L1500 BK	120 degree(s)	4000 K	144 lm/W	3,600 lm
62445000	SM350C 50S/840 PSU PCS L1500 BK	120 degree(s)	4000 K	142 lm/W	5,200 lm
62448100	SM350C 34S/840 PSD PCS L1500 BK	120 degree(s)	4000 K	138 lm/W	3,600 lm
62451100	SM350C 50S/840 PSD PCS L1500 BK	120 degree(s)	4000 K	137 lm/W	5,200 lm
62367500	SM350C 27S/840 PSU PCS L1200 ALU	120 degree(s)	4000 K	141 lm/W	2,900 lm
62417700	SM350C 40S/840 PSU PCS L1200 ALU	120 degree(s)	4000 K	140 lm/W	4,200 lm
62420700	SM350C 27S/840 PSD PCS L1200 ALU	120 degree(s)	4000 K	138 lm/W	2,900 lm
62423800	SM350C 40S/840 PSD PCS L1200 ALU	120 degree(s)	4000 K	135 lm/W	4,200 lm
62432000	SM350C 27S/830 PSU PCS L1200 ALU	120 degree(s)	3000 K	132 lm/W	2,600 lm
62434400	SM350C 40S/830 PSU PCS L1200 ALU	120 degree(s)	3000 K	133 lm/W	4,000 lm
62436800	SM350C 27S/830 PSD PCS L1200 ALU	120 degree(s)	3000 K	130 lm/W	2,600 lm
62438200	SM350C 40S/830 PSD PCS L1200 ALU	120 degree(s)	3000 K	129 lm/W	4,000 lm
62452800	SM350X 27S/840 PSD L60L60 PCS ALU	120 degree(s)	4000 K	138 lm/W	2,900 lm
62440500	SM350C 34S/840 PSU PCS L1500 ALU	120 degree(s)	4000 K	144 lm/W	3,600 lm
62443600	SM350C 50S/840 PSU PCS L1500 ALU	120 degree(s)	4000 K	142 lm/W	5,200 lm
62446700	SM350C 34S/840 PSD PCS L1500 ALU	120 degree(s)	4000 K	138 lm/W	3,600 lm
62449800	SM350C 50S/840 PSD PCS L1500 ALU	120 degree(s)	4000 K	137 lm/W	5,200 lm
62441200	SM350C 34S/840 PSU PCS L1500 WH	120 degree(s)	4000 K	144 lm/W	3,600 lm
62444300	SM350C 50S/840 PSU PCS L1500 WH	120 degree(s)	4000 K	142 lm/W	5,200 lm
62447400	SM350C 34S/840 PSD PCS L1500 WH	120 degree(s)	4000 K	138 lm/W	3,600 lm
62450400	SM350C 50S/840 PSD PCS L1500 WH	120 degree(s)	4000 K	137 lm/W	5,200 lm
62430600	SM350C 40S/840 WIA PCS L1200 WH	120 degree(s)	4000 K	140 lm/W	4,200 lm
62431300	SM350C 40S/840 WIA PCS L1200 BK	120 degree(s)	4000 K	140 lm/W	4,200 lm
62415300	SM350C 27S/840 PSU PCS L1200 WH	120 degree(s)	4000 K	141 lm/W	2,900 lm
62418400	SM350C 40S/840 PSU PCS L1200 WH	120 degree(s)	4000 K	140 lm/W	4,200 lm
62421400	SM350C 27S/840 PSD PCS L1200 WH	120 degree(s)	4000 K	138 lm/W	2,900 lm
62424500	SM350C 40S/840 PSD PCS L1200 WH	120 degree(s)	4000 K	135 lm/W	4,200 lm

KeyLine, Surface & Suspended

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
62433700	SM350C 27S/830 PSU PCS L1200 WH	120 degree(s)	3000 K	132 lm/W	2,600 lm
62435100	SM350C 40S/830 PSU PCS L1200 WH	120 degree(s)	3000 K	133 lm/W	4,000 lm
62437500	SM350C 27S/830 PSD PCS L1200 WH	120 degree(s)	3000 K	130 lm/W	2,600 lm
62439900	SM350C 40S/830 PSD PCS L1200 WH	120 degree(s)	3000 K	129 lm/W	4,000 lm
62416000	SM350C 27S/840 PSU PCS L1200 BK	120 degree(s)	4000 K	141 lm/W	2,900 lm
62419100	SM350C 40S/840 PSU PCS L1200 BK	120 degree(s)	4000 K	140 lm/W	4,200 lm
62422100	SM350C 27S/840 PSD PCS L1200 BK	120 degree(s)	4000 K	138 lm/W	2,900 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
62425200	SM350C 40S/840 PSD PCS L1200 BK	120 degree(s)	4000 K	135 lm/W	4,200 lm
62453500	SM350X 27S/840 PSD L60L60 PCS WH	120 degree(s)	4000 K	138 lm/W	2,900 lm
61518200	SM351C 40S/840 PSU A PCS L1200 WH	-	4000 K	133 lm/W	4,000 lm
61519900	SM351C 40S/840 PSD A PCS L1200 WH	-	4000 K	129 lm/W	4,000 lm
61520500	SM351C 50S/840 PSU A PCS L1500 WH	-	4000 K	135 lm/W	5,000 lm
61521200	SM351C 50S/840 PSD A PCS L1500 WH	-	4000 K	132 lm/W	5,000 lm

Light Technical (2/2)

Order Code	Full Product Name	Optic type
62454200	SM350X 27S/840 PSD PCS N BK	Medium beam
62442900	SM350C 34S/840 PSU PCS L1500 BK	Medium beam
62445000	SM350C 50S/840 PSU PCS L1500 BK	Medium beam
62448100	SM350C 34S/840 PSD PCS L1500 BK	Medium beam
62451100	SM350C 50S/840 PSD PCS L1500 BK	Medium beam
62367500	SM350C 27S/840 PSU PCS L1200 ALU	Medium beam
62417700	SM350C 40S/840 PSU PCS L1200 ALU	Medium beam
62420700	SM350C 27S/840 PSD PCS L1200 ALU	Medium beam
62423800	SM350C 40S/840 PSD PCS L1200 ALU	Medium beam
62432000	SM350C 27S/830 PSU PCS L1200 ALU	Medium beam
62434400	SM350C 40S/830 PSU PCS L1200 ALU	Medium beam
62436800	SM350C 27S/830 PSD PCS L1200 ALU	Medium beam
62438200	SM350C 40S/830 PSD PCS L1200 ALU	Medium beam
62452800	SM350X 27S/840 PSD L60L60 PCS ALU	Medium beam
62440500	SM350C 34S/840 PSU PCS L1500 ALU	Medium beam
62443600	SM350C 50S/840 PSU PCS L1500 ALU	Medium beam
62446700	SM350C 34S/840 PSD PCS L1500 ALU	Medium beam
62449800	SM350C 50S/840 PSD PCS L1500 ALU	Medium beam
62441200	SM350C 34S/840 PSU PCS L1500 WH	Medium beam
62444300	SM350C 50S/840 PSU PCS L1500 WH	Medium beam
62447400	SM350C 34S/840 PSD PCS L1500 WH	Medium beam

Order Code	Full Product Name	Optic type
62450400	SM350C 50S/840 PSD PCS L1500 WH	Medium beam
62430600	SM350C 40S/840 WIA PCS L1200 WH	Medium beam
62431300	SM350C 40S/840 WIA PCS L1200 BK	Medium beam
62415300	SM350C 27S/840 PSU PCS L1200 WH	Medium beam
62418400	SM350C 40S/840 PSU PCS L1200 WH	Medium beam
62421400	SM350C 27S/840 PSD PCS L1200 WH	Medium beam
62424500	SM350C 40S/840 PSD PCS L1200 WH	Medium beam
62433700	SM350C 27S/830 PSU PCS L1200 WH	Medium beam
62435100	SM350C 40S/830 PSU PCS L1200 WH	Medium beam
62437500	SM350C 27S/830 PSD PCS L1200 WH	Medium beam
62439900	SM350C 40S/830 PSD PCS L1200 WH	Medium beam
62416000	SM350C 27S/840 PSU PCS L1200 BK	Medium beam
62419100	SM350C 40S/840 PSU PCS L1200 BK	Medium beam
62422100	SM350C 27S/840 PSD PCS L1200 BK	Medium beam
62425200	SM350C 40S/840 PSD PCS L1200 BK	Medium beam
62453500	SM350X 27S/840 PSD L60L60 PCS WH	Medium beam
61518200	SM351C 40S/840 PSU A PCS L1200 WH	Assymetric Beam angle
61519900	SM351C 40S/840 PSD A PCS L1200 WH	Assymetric Beam angle
61520500	SM351C 50S/840 PSU A PCS L1500 WH	Assymetric Beam angle
61521200	SM351C 50S/840 PSD A PCS L1500 WH	Assymetric Beam angle

Operating and Electrical

KeyLine, Surface & Suspended

Order Code	Full Product Name	Input Voltage	Power	Suitable for random switching
			Consumption	
62454200	SM350X 27S/840 PSD PCS N BK	220 to 240 V	21 W	No
62442900	SM350C 34S/840 PSU PCS L1500 BK	220 to 240 V	25 W	No
62445000	SM350C 50S/840 PSU PCS L1500 BK	220 to 240 V	36.5 W	No
62448100	SM350C 34S/840 PSD PCS L1500 BK	220 to 240 V	26 W	No
62451100	SM350C 50S/840 PSD PCS L1500 BK	220 to 240 V	38 W	No
62367500	SM350C 27S/840 PSU PCS L1200 ALU	220 to 240 V	20.5 W	No
62417700	SM350C 40S/840 PSU PCS L1200 ALU	220 to 240 V	30 W	No
62420700	SM350C 27S/840 PSD PCS L1200 ALU	220 to 240 V	21 W	No
62423800	SM350C 40S/840 PSD PCS L1200 ALU	220 to 240 V	31 W	No
62432000	SM350C 27S/830 PSU PCS L1200 ALU	220 to 240 V	20.5 W	No
62434400	SM350C 40S/830 PSU PCS L1200 ALU	220 to 240 V	30 W	No
62436800	SM350C 27S/830 PSD PCS L1200 ALU	220 to 240 V	21 W	No
62438200	SM350C 40S/830 PSD PCS L1200 ALU	220 to 240 V	31 W	No
62452800	SM350X 27S/840 PSD L60L60 PCS ALU	220 to 240 V	21 W	No
62440500	SM350C 34S/840 PSU PCS L1500 ALU	220 to 240 V	25 W	No
62443600	SM350C 50S/840 PSU PCS L1500 ALU	220 to 240 V	36.5 W	No
62446700	SM350C 34S/840 PSD PCS L1500 ALU	220 to 240 V	26 W	No
62449800	SM350C 50S/840 PSD PCS L1500 ALU	220 to 240 V	38 W	No
62441200	SM350C 34S/840 PSU PCS L1500 WH	220 to 240 V	25 W	No
62444300	SM350C 50S/840 PSU PCS L1500 WH	220 to 240 V	36.5 W	No
62447400	SM350C 34S/840 PSD PCS L1500 WH	220 to 240 V	26 W	No

Order Code	Full Product Name	Input Voltage	Power	Suitable for random switching
			Consumption	
62450400	SM350C 50S/840 PSD PCS L1500 WH	220 to 240 V	38 W	No
62430600	SM350C 40S/840 WIA PCS L1200 WH	220 to 240 V	30 W	No
62431300	SM350C 40S/840 WIA PCS L1200 BK	220 to 240 V	30 W	No
62415300	SM350C 27S/840 PSU PCS L1200 WH	220 to 240 V	20.5 W	No
62418400	SM350C 40S/840 PSU PCS L1200 WH	220 to 240 V	30 W	No
62421400	SM350C 27S/840 PSD PCS L1200 WH	220 to 240 V	21 W	No
62424500	SM350C 40S/840 PSD PCS L1200 WH	220 to 240 V	31 W	No
62433700	SM350C 27S/830 PSU PCS L1200 WH	220 to 240 V	20.5 W	No
62435100	SM350C 40S/830 PSU PCS L1200 WH	220 to 240 V	30 W	No
62437500	SM350C 27S/830 PSD PCS L1200 WH	220 to 240 V	21 W	No
62439900	SM350C 40S/830 PSD PCS L1200 WH	220 to 240 V	31 W	No
62416000	SM350C 27S/840 PSU PCS L1200 BK	220 to 240 V	20.5 W	No
62419100	SM350C 40S/840 PSU PCS L1200 BK	220 to 240 V	30 W	No
62422100	SM350C 27S/840 PSD PCS L1200 BK	220 to 240 V	21 W	No
62425200	SM350C 40S/840 PSD PCS L1200 BK	220 to 240 V	31 W	No
62453500	SM350X 27S/840 PSD L60L60 PCS WH	220 to 240 V	21 W	No
61518200	SM351C 40S/840 PSU A PCS L1200 WH	220-240 V	30 W	Not applicable
61519900	SM351C 40S/840 PSD A PCS L1200 WH	220-240 V	31 W	Not applicable
61520500	SM351C 50S/840 PSU A PCS L1500 WH	220-240 V	37 W	Not applicable
61521200	SM351C 50S/840 PSD A PCS L1500 WH	220-240 V	38 W	Not applicable

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
62454200	SM350X 27S/840 PSD PCS N BK	Yes	1%
62442900	SM350C 34S/840 PSU PCS L1500 BK	No	Not applicable
62445000	SM350C 50S/840 PSU PCS L1500 BK	No	Not applicable
62448100	SM350C 34S/840 PSD PCS L1500 BK	Yes	1%

Order Code	Full Product Name	Dimmable	Maximum dim level
62451100	SM350C 50S/840 PSD PCS L1500 BK	Yes	1%
62367500	SM350C 27S/840 PSU PCS L1200 ALU	No	Not applicable
62417700	SM350C 40S/840 PSU PCS L1200 ALU	No	Not applicable
62420700	SM350C 27S/840 PSD PCS L1200 ALU	Yes	1%

KeyLine, Surface & Suspended

Order Code	Full Product Name	Dimmable	Maximum dim level
62423800	SM350C 40S/840 PSD PCS L1200 ALU	Yes	1%
62432000	SM350C 27S/830 PSU PCS L1200 ALU	No	Not applicable
62434400	SM350C 40S/830 PSU PCS L1200 ALU	No	Not applicable
62436800	SM350C 27S/830 PSD PCS L1200 ALU	Yes	1%
62438200	SM350C 40S/830 PSD PCS L1200 ALU	Yes	1%
62452800	SM350X 27S/840 PSD L60L60 PCS ALU	Yes	1%
62440500	SM350C 34S/840 PSU PCS L1500 ALU	No	Not applicable
62443600	SM350C 50S/840 PSU PCS L1500 ALU	No	Not applicable
62446700	SM350C 34S/840 PSD PCS L1500 ALU	Yes	1%
62449800	SM350C 50S/840 PSD PCS L1500 ALU	Yes	1%
62441200	SM350C 34S/840 PSU PCS L1500 WH	No	Not applicable
62444300	SM350C 50S/840 PSU PCS L1500 WH	No	Not applicable
62447400	SM350C 34S/840 PSD PCS L1500 WH	Yes	1%
62450400	SM350C 50S/840 PSD PCS L1500 WH	Yes	1%
62430600	SM350C 40S/840 WIA PCS L1200 WH	Yes	1%
62431300	SM350C 40S/840 WIA PCS L1200 BK	Yes	1%
62415300	SM350C 27S/840 PSU PCS L1200 WH	No	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
62418400	SM350C 40S/840 PSU PCS L1200 WH	No	Not applicable
62421400	SM350C 27S/840 PSD PCS L1200 WH	Yes	1%
62424500	SM350C 40S/840 PSD PCS L1200 WH	Yes	1%
62433700	SM350C 27S/830 PSU PCS L1200 WH	No	Not applicable
62435100	SM350C 40S/830 PSU PCS L1200 WH	No	Not applicable
62437500	SM350C 27S/830 PSD PCS L1200 WH	Yes	1%
62439900	SM350C 40S/830 PSD PCS L1200 WH	Yes	1%
62416000	SM350C 27S/840 PSU PCS L1200 BK	No	Not applicable
62419100	SM350C 40S/840 PSU PCS L1200 BK	No	Not applicable
62422100	SM350C 27S/840 PSD PCS L1200 BK	Yes	1%
62425200	SM350C 40S/840 PSD PCS L1200 BK	Yes	1%
62453500	SM350X 27S/840 PSD L60L60 PCS WH	Yes	1%
61518200	SM351C 40S/840 PSU A PCS L1200 WH	No	Not applicable
61519900	SM351C 40S/840 PSD A PCS L1200 WH	Yes	1%
61520500	SM351C 50S/840 PSU A PCS L1500 WH	No	Not applicable
61521200	SM351C 50S/840 PSD A PCS L1500 WH	Yes	1%

Mechanical and Housing

Order Code	Full Product Name	Mech. impact	
		Housing Color	protection code
62454200	SM350X 27S/840 PSD PCS N BK	Black	IK06
62442900	SM350C 34S/840 PSU PCS L1500 BK	Black	IK06
62445000	SM350C 50S/840 PSU PCS L1500 BK	Black	IK06
62448100	SM350C 34S/840 PSD PCS L1500 BK	Black	IK06
62451100	SM350C 50S/840 PSD PCS L1500 BK	Black	IK06
62367500	SM350C 27S/840 PSU PCS L1200 ALU	Aluminum	IK06
62417700	SM350C 40S/840 PSU PCS L1200 ALU	Aluminum	IK06
62420700	SM350C 27S/840 PSD PCS L1200 ALU	Aluminum	IK06
62423800	SM350C 40S/840 PSD PCS L1200 ALU	Aluminum	IK06
62432000	SM350C 27S/830 PSU PCS L1200 ALU	Aluminum	IK06
62434400	SM350C 40S/830 PSU PCS L1200 ALU	Aluminum	IK06
62436800	SM350C 27S/830 PSD PCS L1200 ALU	Aluminum	IK06
62438200	SM350C 40S/830 PSD PCS L1200 ALU	Aluminum	IK06
62452800	SM350X 27S/840 PSD L60L60 PCS ALU	Aluminum	IK06
62440500	SM350C 34S/840 PSU PCS L1500 ALU	Aluminum	IK06
62443600	SM350C 50S/840 PSU PCS L1500 ALU	Aluminum	IK06
62446700	SM350C 34S/840 PSD PCS L1500 ALU	Aluminum	IK06
62449800	SM350C 50S/840 PSD PCS L1500 ALU	Aluminum	IK06
62441200	SM350C 34S/840 PSU PCS L1500 WH	White	IK06
62444300	SM350C 50S/840 PSU PCS L1500 WH	White	IK06
62447400	SM350C 34S/840 PSD PCS L1500 WH	White	IK06

Order Code	Full Product Name	Mech. impact	
		Housing Color	protection code
62450400	SM350C 50S/840 PSD PCS L1500 WH	White	IK06
62430600	SM350C 40S/840 WIA PCS L1200 WH	White	IK06
62431300	SM350C 40S/840 WIA PCS L1200 BK	Black	IK06
62415300	SM350C 27S/840 PSU PCS L1200 WH	White	IK06
62418400	SM350C 40S/840 PSU PCS L1200 WH	White	IK06
62421400	SM350C 27S/840 PSD PCS L1200 WH	White	IK06
62424500	SM350C 40S/840 PSD PCS L1200 WH	White	IK06
62433700	SM350C 27S/830 PSU PCS L1200 WH	White	IK06
62435100	SM350C 40S/830 PSU PCS L1200 WH	White	IK06
62437500	SM350C 27S/830 PSD PCS L1200 WH	White	IK06
62439900	SM350C 40S/830 PSD PCS L1200 WH	White	IK06
62416000	SM350C 27S/840 PSU PCS L1200 BK	Black	IK06
62419100	SM350C 40S/840 PSU PCS L1200 BK	Black	IK06
62422100	SM350C 27S/840 PSD PCS L1200 BK	Black	IK06
62425200	SM350C 40S/840 PSD PCS L1200 BK	Black	IK06
62453500	SM350X 27S/840 PSD L60L60 PCS WH	White	IK06
61518200	SM351C 40S/840 PSU A PCS L1200 WH	White	IK02
61519900	SM351C 40S/840 PSD A PCS L1200 WH	White	IK02
61520500	SM351C 50S/840 PSU A PCS L1500 WH	White	IK02
61521200	SM351C 50S/840 PSD A PCS L1500 WH	White	IK02

Emergency Operation

Order Code	Full Product Name	Central Emergency
62454200	SM350X 27S/840 PSD PCS N BK	-
62442900	SM350C 34S/840 PSU PCS L1500 BK	-
62445000	SM350C 50S/840 PSU PCS L1500 BK	-
62448100	SM350C 34S/840 PSD PCS L1500 BK	-

Order Code	Full Product Name	Central Emergency
62451100	SM350C 50S/840 PSD PCS L1500 BK	-
62367500	SM350C 27S/840 PSU PCS L1200 ALU	-
62417700	SM350C 40S/840 PSU PCS L1200 ALU	-
62420700	SM350C 27S/840 PSD PCS L1200 ALU	-

KeyLine, Surface & Suspended

Order Code	Full Product Name	Central Emergency
62423800	SM350C 40S/840 PSD PCS L1200 ALU	-
62432000	SM350C 27S/830 PSU PCS L1200 ALU	-
62434400	SM350C 40S/830 PSU PCS L1200 ALU	-
62436800	SM350C 27S/830 PSD PCS L1200 ALU	-
62438200	SM350C 40S/830 PSD PCS L1200 ALU	-
62452800	SM350X 27S/840 PSD L60L60 PCS ALU	-
62440500	SM350C 34S/840 PSU PCS L1500 ALU	-
62443600	SM350C 50S/840 PSU PCS L1500 ALU	-
62446700	SM350C 34S/840 PSD PCS L1500 ALU	-
62449800	SM350C 50S/840 PSD PCS L1500 ALU	-
62441200	SM350C 34S/840 PSU PCS L1500 WH	-
62444300	SM350C 50S/840 PSU PCS L1500 WH	-
62447400	SM350C 34S/840 PSD PCS L1500 WH	-
62450400	SM350C 50S/840 PSD PCS L1500 WH	-
62430600	SM350C 40S/840 WIA PCS L1200 WH	-
62431300	SM350C 40S/840 WIA PCS L1200 BK	-
62415300	SM350C 27S/840 PSU PCS L1200 WH	-

Order Code	Full Product Name	Central Emergency
62418400	SM350C 40S/840 PSU PCS L1200 WH	-
62421400	SM350C 27S/840 PSD PCS L1200 WH	-
62424500	SM350C 40S/840 PSD PCS L1200 WH	-
62433700	SM350C 27S/830 PSU PCS L1200 WH	-
62435100	SM350C 40S/830 PSU PCS L1200 WH	-
62437500	SM350C 27S/830 PSD PCS L1200 WH	-
62439900	SM350C 40S/830 PSD PCS L1200 WH	-
62416000	SM350C 27S/840 PSU PCS L1200 BK	-
62419100	SM350C 40S/840 PSU PCS L1200 BK	-
62422100	SM350C 27S/840 PSD PCS L1200 BK	-
62425200	SM350C 40S/840 PSD PCS L1200 BK	-
62453500	SM350X 27S/840 PSD L60L60 PCS WH	-
61518200	SM351C 40S/840 PSU A PCS L1200 WH	No
61519900	SM351C 40S/840 PSD A PCS L1200 WH	No
61520500	SM351C 50S/840 PSU A PCS L1500 WH	No
61521200	SM351C 50S/840 PSD A PCS L1500 WH	No

Approval and Application

Order Code	Full Product Name	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3
62454200	SM350X 27S/840 PSD PCS N BK	For mounting on normally flammable surfaces	1
62442900	SM350C 34S/840 PSU PCS L1500 BK	For mounting on normally flammable surfaces	1
62445000	SM350C 50S/840 PSU PCS L1500 BK	For mounting on normally flammable surfaces	1
62448100	SM350C 34S/840 PSD PCS L1500 BK	For mounting on normally flammable surfaces	1
62451100	SM350C 50S/840 PSD PCS L1500 BK	For mounting on normally flammable surfaces	1
62367500	SM350C 27S/840 PSU PCS L1200 ALU	For mounting on normally flammable surfaces	1
62417700	SM350C 40S/840 PSU PCS L1200 ALU	For mounting on normally flammable surfaces	1
62420700	SM350C 27S/840 PSD PCS L1200 ALU	For mounting on normally flammable surfaces	1
62423800	SM350C 40S/840 PSD PCS L1200 ALU	For mounting on normally flammable surfaces	1
62432000	SM350C 27S/830 PSU PCS L1200 ALU	For mounting on normally flammable surfaces	1
62434400	SM350C 40S/830 PSU PCS L1200 ALU	For mounting on normally flammable surfaces	1
62436800	SM350C 27S/830 PSD PCS L1200 ALU	For mounting on normally flammable surfaces	1
62438200	SM350C 40S/830 PSD PCS L1200 ALU	For mounting on normally flammable surfaces	1

Order Code	Full Product Name	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3
62452800	SM350X 27S/840 PSD L60L60 PCS ALU	For mounting on normally flammable surfaces	1
62440500	SM350C 34S/840 PSU PCS L1500 ALU	For mounting on normally flammable surfaces	1
62443600	SM350C 50S/840 PSU PCS L1500 ALU	For mounting on normally flammable surfaces	1
62446700	SM350C 34S/840 PSD PCS L1500 ALU	For mounting on normally flammable surfaces	1
62449800	SM350C 50S/840 PSD PCS L1500 ALU	For mounting on normally flammable surfaces	1
62441200	SM350C 34S/840 PSU PCS L1500 WH	For mounting on normally flammable surfaces	1
62444300	SM350C 50S/840 PSU PCS L1500 WH	For mounting on normally flammable surfaces	1
62447400	SM350C 34S/840 PSD PCS L1500 WH	For mounting on normally flammable surfaces	1
62450400	SM350C 50S/840 PSD PCS L1500 WH	For mounting on normally flammable surfaces	1
62430600	SM350C 40S/840 WIA PCS L1200 WH	For mounting on normally flammable surfaces	1
62431300	SM350C 40S/840 WIA PCS L1200 BK	For mounting on normally flammable surfaces	1
62415300	SM350C 27S/840 PSU PCS L1200 WH	For mounting on normally flammable surfaces	1
62418400	SM350C 40S/840 PSU PCS L1200 WH	For mounting on normally flammable surfaces	1

KeyLine, Surface & Suspended

Order Code	Full Product Name	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3
62421400	SM350C 27S/840 PSD PCS L1200 WH	For mounting on normally flammable surfaces	1
62424500	SM350C 40S/840 PSD PCS L1200 WH	For mounting on normally flammable surfaces	1
62433700	SM350C 27S/830 PSU PCS L1200 WH	For mounting on normally flammable surfaces	1
62435100	SM350C 40S/830 PSU PCS L1200 WH	For mounting on normally flammable surfaces	1
62437500	SM350C 27S/830 PSD PCS L1200 WH	For mounting on normally flammable surfaces	1
62439900	SM350C 40S/830 PSD PCS L1200 WH	For mounting on normally flammable surfaces	1
62416000	SM350C 27S/840 PSU PCS L1200 BK	For mounting on normally flammable surfaces	1
62419100	SM350C 40S/840 PSU PCS L1200 BK	For mounting on normally flammable surfaces	1

Order Code	Full Product Name	Flammability mark	Flickering value (PstLM) - Flickering value as per EN 61000-3-3
62422100	SM350C 27S/840 PSD PCS L1200 BK	For mounting on normally flammable surfaces	1
62425200	SM350C 40S/840 PSD PCS L1200 BK	For mounting on normally flammable surfaces	1
62453500	SM350X 27S/840 PSD L60L60 PCS WH	For mounting on normally flammable surfaces	1
61518200	SM351C 40S/840 PSU A PCS L1200 WH	-	-
61519900	SM351C 40S/840 PSD A PCS L1200 WH	-	-
61520500	SM351C 50S/840 PSU A PCS L1500 WH	-	-
61521200	SM351C 50S/840 PSD A PCS L1500 WH	-	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
62454200	SM350X 27S/840 PSD PCS N BK	(0.39, 0.38) SDCM <3
62442900	SM350C 34S/840 PSU PCS L1500 BK	(0.39, 0.38) SDCM <3
62445000	SM350C 50S/840 PSU PCS L1500 BK	(0.39, 0.38) SDCM <3
62448100	SM350C 34S/840 PSD PCS L1500 BK	(0.39, 0.38) SDCM <3
62451100	SM350C 50S/840 PSD PCS L1500 BK	(0.39, 0.38) SDCM <3
62367500	SM350C 27S/840 PSU PCS L1200 ALU	(0.39, 0.38) SDCM <3
62417700	SM350C 40S/840 PSU PCS L1200 ALU	(0.39, 0.38) SDCM <3
62420700	SM350C 27S/840 PSD PCS L1200 ALU	(0.39, 0.38) SDCM <3
62423800	SM350C 40S/840 PSD PCS L1200 ALU	(0.39, 0.38) SDCM <3
62432000	SM350C 27S/830 PSU PCS L1200 ALU	(0.43, 0.40) SDCM <3
62434400	SM350C 40S/830 PSU PCS L1200 ALU	(0.43, 0.40) SDCM <3
62436800	SM350C 27S/830 PSD PCS L1200 ALU	(0.43, 0.40) SDCM <3
62438200	SM350C 40S/830 PSD PCS L1200 ALU	(0.43, 0.40) SDCM <3
62452800	SM350X 27S/840 PSD L60L60 PCS ALU	(0.39, 0.38) SDCM <3
62440500	SM350C 34S/840 PSU PCS L1500 ALU	(0.39, 0.38) SDCM <3
62443600	SM350C 50S/840 PSU PCS L1500 ALU	(0.39, 0.38) SDCM <3
62446700	SM350C 34S/840 PSD PCS L1500 ALU	(0.39, 0.38) SDCM <3
62449800	SM350C 50S/840 PSD PCS L1500 ALU	(0.39, 0.38) SDCM <3
62441200	SM350C 34S/840 PSU PCS L1500 WH	(0.39, 0.38) SDCM <3
62444300	SM350C 50S/840 PSU PCS L1500 WH	(0.39, 0.38) SDCM <3
62447400	SM350C 34S/840 PSD PCS L1500 WH	(0.39, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
62450400	SM350C 50S/840 PSD PCS L1500 WH	(0.39, 0.38) SDCM <3
62430600	SM350C 40S/840 WIA PCS L1200 WH	(0.39, 0.38) SDCM <3
62431300	SM350C 40S/840 WIA PCS L1200 BK	(0.39, 0.38) SDCM <3
62415300	SM350C 27S/840 PSU PCS L1200 WH	(0.39, 0.38) SDCM <3
62418400	SM350C 40S/840 PSU PCS L1200 WH	(0.39, 0.38) SDCM <3
62421400	SM350C 27S/840 PSD PCS L1200 WH	(0.39, 0.38) SDCM <3
62424500	SM350C 40S/840 PSD PCS L1200 WH	(0.39, 0.38) SDCM <3
62433700	SM350C 27S/830 PSU PCS L1200 WH	(0.43, 0.40) SDCM <3
62435100	SM350C 40S/830 PSU PCS L1200 WH	(0.43, 0.40) SDCM <3
62437500	SM350C 27S/830 PSD PCS L1200 WH	(0.43, 0.40) SDCM <3
62439900	SM350C 40S/830 PSD PCS L1200 WH	(0.43, 0.40) SDCM <3
62416000	SM350C 27S/840 PSU PCS L1200 BK	(0.39, 0.38) SDCM <3
62419100	SM350C 40S/840 PSU PCS L1200 BK	(0.39, 0.38) SDCM <3
62422100	SM350C 27S/840 PSD PCS L1200 BK	(0.39, 0.38) SDCM <3
62425200	SM350C 40S/840 PSD PCS L1200 BK	(0.39, 0.38) SDCM <3
62453500	SM350X 27S/840 PSD L60L60 PCS WH	(0.39, 0.38) SDCM <3
61518200	SM351C 40S/840 PSU A PCS L1200 WH	(0.39, 0.38) SDCM <3
61519900	SM351C 40S/840 PSD A PCS L1200 WH	(0.39, 0.38) SDCM <3
61520500	SM351C 50S/840 PSU A PCS L1500 WH	(0.39, 0.38) SDCM <3
61521200	SM351C 50S/840 PSD A PCS L1500 WH	(0.39, 0.38) SDCM <3

Product Data

Order Code	Full Product Name	Product family code
62454200	SM350X 27S/840 PSD PCS N BK	SM350X


Order Code	Full Product Name	Product family code
62442900	SM350C 34S/840 PSU PCS L1500 BK	SM350C

KeyLine, Surface & Suspended


Order Code	Full Product Name	Product family code
62445000	SM350C 50S/840 PSU PCS L1500 BK	SM350C
62448100	SM350C 34S/840 PSD PCS L1500 BK	SM350C
62451100	SM350C 50S/840 PSD PCS L1500 BK	SM350C
62367500	SM350C 27S/840 PSU PCS L1200 ALU	SM350C
62417700	SM350C 40S/840 PSU PCS L1200 ALU	SM350C
62420700	SM350C 27S/840 PSD PCS L1200 ALU	SM350C
62423800	SM350C 40S/840 PSD PCS L1200 ALU	SM350C
62432000	SM350C 27S/830 PSU PCS L1200 ALU	SM350C
62434400	SM350C 40S/830 PSU PCS L1200 ALU	SM350C
62436800	SM350C 27S/830 PSD PCS L1200 ALU	SM350C
62438200	SM350C 40S/830 PSD PCS L1200 ALU	SM350C
62452800	SM350X 27S/840 PSD L60L60 PCS ALU	SM350X
62440500	SM350C 34S/840 PSU PCS L1500 ALU	SM350C
62443600	SM350C 50S/840 PSU PCS L1500 ALU	SM350C
62446700	SM350C 34S/840 PSD PCS L1500 ALU	SM350C
62449800	SM350C 50S/840 PSD PCS L1500 ALU	SM350C
62441200	SM350C 34S/840 PSU PCS L1500 WH	SM350C
62444300	SM350C 50S/840 PSU PCS L1500 WH	SM350C
62447400	SM350C 34S/840 PSD PCS L1500 WH	SM350C
62450400	SM350C 50S/840 PSD PCS L1500 WH	SM350C

Order Code	Full Product Name	Product family code
62430600	SM350C 40S/840 WIA PCS L1200 WH	SM350C
62431300	SM350C 40S/840 WIA PCS L1200 BK	SM350C
62415300	SM350C 27S/840 PSU PCS L1200 WH	SM350C
62418400	SM350C 40S/840 PSU PCS L1200 WH	SM350C
62421400	SM350C 27S/840 PSD PCS L1200 WH	SM350C
62424500	SM350C 40S/840 PSD PCS L1200 WH	SM350C
62433700	SM350C 27S/830 PSU PCS L1200 WH	SM350C
62435100	SM350C 40S/830 PSU PCS L1200 WH	SM350C
62437500	SM350C 27S/830 PSD PCS L1200 WH	SM350C
62439900	SM350C 40S/830 PSD PCS L1200 WH	SM350C
62416000	SM350C 27S/840 PSU PCS L1200 BK	SM350C
62419100	SM350C 40S/840 PSU PCS L1200 BK	SM350C
62422100	SM350C 27S/840 PSD PCS L1200 BK	SM350C
62425200	SM350C 40S/840 PSD PCS L1200 BK	SM350C
62453500	SM350X 27S/840 PSD L60L60 PCS WH	SM350X
61518200	SM351C 40S/840 PSU A PCS L1200 WH	SM350C
61519900	SM351C 40S/840 PSD A PCS L1200 WH	SM350C
61520500	SM351C 50S/840 PSU A PCS L1500 WH	SM350C
61521200	SM351C 50S/840 PSD A PCS L1500 WH	SM350C


Polar Wide Diagrams




Polar Normal (separate) - SM350CI -
910925868303




Polar Normal (separate) - SM350CI -
910925868353




Polar Normal (separate) - SM350CI -
910925868366



Polar Normal (separate) - SM350CI -
910925868379




Polar Normal (separate) - SM350CI -
910925868355




Polar Normal (separate) - SM350CI -
910925868356


Polar Wide Diagrams




Polar Normal (separate) - SM350CI - 910925868383




Polar Normal (separate) - SM350CI - 910925868352




Polar Normal (separate) - SM350CI - 910925868359




Polar Normal (separate) - SM350CI - 910925868375




Polar Normal (separate) - SM350CI - 910925868381




Polar Normal (separate) - SM350CI - 910925868385



Polar Normal (separate) - SM350CI - 910925868388




Polar Normal (separate) - SM350CI - 910925868389




Polar Normal (separate) - SM350CI - 910925868354


Polar Wide Diagrams




Polar Normal (separate) - SM350CI - 910925868387




Polar Normal (separate) - SM350CI - 910925868370




Polar Normal (separate) - SM350CI - 910925868384




Polar Normal (separate) - SM350CI - 910925868386




Polar Normal (separate) - SM350CI - 910925868360




Polar Normal (separate) - SM350CI - 910925868361



Polar Normal (separate) - SM350CI - 910925868367




Polar Normal (separate) - SM350CI - 910925868357




Polar Normal (separate) - SM350CI - 910925868368


Polar Wide Diagrams




Polar Normal (separate) - SM350CI - 910925868358




Polar Normal (separate) - SM350CI - 910925868372




Polar Normal (separate) - SM350CI - 910925868376




Polar Normal (separate) - SM350CI - 910925868378




Polar Normal (separate) - SM350CI - 910925868380




Polar Normal (separate) - SM350CI - 910925868351



Polar Normal (separate) - SM350CI - 910925868369




Polar Normal (separate) - SM350CI - 910925868371




Polar Normal (separate) - SM350CI - 910925868374


Polar Wide Diagrams




Polar Normal (separate) - SM350CI - 910925868373




Polar Normal (separate) - SM350CI - 910925868377




Polar Normal (separate) - SM350CI - 910925868382




Polar Normal (separate) - SM350CI - 910925868390




Polar Normal (separate) - null - 910505103701



Polar Normal (separate) - null - 910505103702



Polar Normal (separate) - null - 910505103703



Polar Normal (separate) - null - 910505103704

