



Philips TrueLine Surface: True line of light

TrueLine, surface mounted

Architects need a lighting solution that matches the interior architecture of the property they are working on. They want a light line with an elegant design and very high light levels. Specifiers need luminaires that enable them to save energy while at the same time providing the right level of light, in compliance with office lighting norms. And office workers want visually comfortable lighting conditions that help them perform better. TrueLine Recessed is able to meet all of these different requirements. TrueLine is also available in recessed and suspended versions.

Benefits

- Extremely high efficacy for a line luminaire
- Office compliant lighting
- Future-ready, scalable smart office capabilities
- Compatible with the Interact connected lighting system
- Supports sustainable building design and energy-saving subsidy criteria

Features

- Highly-uniform lighting with excellent glare control ($UGR < 19$, $L65 < 3000 \text{cd/m}^2$)
- Best-in-class efficacy up to 140 lm/W
- 3000K, 4000K, and Tunable White versions, all CRI > 90
- Long lifetime L90@50,000 hours
- Integrated sensors/wireless drivers for data collection, occupancy, daylight regulation and wayfinding
- Environmental Product Declaration (EPD)
- Recessed, suspended and surface mounted options, including all accessories

TrueLine, surface mounted

Application

- Offices
- Education
- Retail

Warnings and Safety

- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

Versions

	TrueLine-SM534C		TrueLine surface mounted-SM530C L1130 WH
	TrueLine-SM530 L570 WH		TrueLine-SM530 L2810 Alu
	TrueLine-SM530 L570 Alu		SP530P with U4 BK sensor
			TrueLine-SM530 L2810 BK
			TrueLine-SM530 U3 SNS210 L2850 Alu

TrueLine, surface mounted

Versions


TrueLine-SM530 L570 BK



TrueLine-SM530 L2810 WH




Dimensional drawing



TrueLine, surface mounted

Dimensional drawing



Product details



TrueLine-SP534_SM534P-DPP.tif



TrueLine-RC534B_SM534C_SP534P-DPP.tif



TrueLine_SM-line-U3



TrueLine Surface Mounted black housing

TrueLine, surface mounted

Product details



TrueLine_SM_SP-line-coupling-
piece-side-view



TrueLine_SM_SP-line-connection-
top-view-2



TrueLine_Surface-Mounted-line-
side-view



SP530P U4 BK DPP



TrueLine_SM_SP-line-connection-
side-view-2

TrueLine, surface mounted

General Information

Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes

Light Technical

Beam angle of light source	120 degree(s)
Color rendering index (CRI)	>90

Operating and Electrical

Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No

Controls and Dimming

Dimmable	Yes
Maximum dim level	1%

Mechanical and Housing

Mech. impact protection code	IK03
Ingress protection code	IP20

Approval and Application

Ambient temperature range	+10 to +40 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4

Initial Performance (IEC Compliant)

Initial chromaticity	(0.38, 0.38) SDCM <3
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
910505103218	SM530C 40S/940 PSD L1130 ALU	4000 K	138 lm/W	4,000 lm	Wide beam
910505103219	SM530C 34S/940 PSD L1130 ALU	4000 K	143 lm/W	3,400 lm	Wide beam
910505103220	SM530C 19S/940 PSD L1410 ALU	4000 K	139 lm/W	1,900 lm	Wide beam
910505103223	SM531C 19S/940 PSD L1410 ALU	4000 K	110 lm/W	1,900 lm	Wide beam
910505103224	SM531C 19S/930 PSD L1410 ALU	3000 K	104 lm/W	1,900 lm	Wide beam
910505103227	SM530C 43S/940 PSD L1410 ALU	4000 K	144 lm/W	4,300 lm	Wide beam
910505103228	SM530C 34S/930 PSD L1130 ALU	3000 K	133 lm/W	3,400 lm	Wide beam
910505103229	SM531C 31S/940 PSD L1410 ALU	4000 K	148 lm/W	3,100 lm	Wide beam
910505103233	SM530C 50S/940 PSD L1410 ALU	4000 K	142 lm/W	5,000 lm	Wide beam
910505103275	SM530C 40S/TW9 DIA L1130 ALU	Tunable white 2700-6500 K	121 lm/W	4,000 lm	Wide beam
910505103221	SM534C 40S/940 PSD L1130 ALU	4000 K	130 lm/W	4,000 lm	Asymmetrical mirror
910505103222	SM534C 50S/940 PSD L1410 ALU	4000 K	132 lm/W	5,000 lm	Asymmetrical mirror
910505103217	SM530C 19S/940 PSD L1410 WH	4000 K	139 lm/W	1,900 lm	Wide beam
910505103225	SM530C 43S/940 PSD L1410 WH	4000 K	144 lm/W	4,300 lm	Wide beam
910505103226	SM530C 50S/940 PSD L1410 WH	4000 K	142 lm/W	5,000 lm	Wide beam
910505103230	SM530C 31S/940 PSD L1410 WH	4000 K	148 lm/W	3,100 lm	Wide beam
910505103231	SM531C 19S/930 PSD L1410 WH	3000 K	104 lm/W	1,900 lm	Wide beam
910505103232	SM531C 19S/940 PSD L1410 WH	4000 K	110 lm/W	1,900 lm	Wide beam
910505103277	SM531C 31S/TW9 DIA L1410 WH	Tunable white 2700-6500 K	91 lm/W	3,100 lm	Wide beam
910505103242	SM531C 12S/940 PSD LE2 L570 WH	4000 K	102 lm/W	1,250 lm	Wide beam
910505103250	SM530C 30S/940 PSD L2250 ALU	4000 K	136 lm/W	3,000 lm	Wide beam
910505103253	SM530C 50S/930 PSD L2250 ALU	3000 K	141 lm/W	5,000 lm	Wide beam
910505103254	SM530C 30S/940 PSD LF1 L2250 ALU	4000 K	136 lm/W	3,000 lm	Wide beam
910505103255	SM530C 68S/940 PSD L2250 ALU	4000 K	146 lm/W	6,800 lm	Wide beam

Order Code	Full Product Name	Correlated Color	Luminous	Luminous Flux	Optic type
		Temperature (Nom)	Efficacy (rated) (Nom)		
910505103264	SM530C 62S/930 PSD L2810 ALU	3000 K	140 lm/W	6,200 lm	Wide beam
910505103267	SM530C 38S/940 PSD LF1 L2810 ALU	4000 K	141 lm/W	3,800 lm	Wide beam
910505103252	SM530C 50S/940 SIA U4 L2290 BK	4000 K	141 lm/W	5,000 lm	Wide beam
910505103236	SM530C 31S/940 PSD L1410 BK	4000 K	148 lm/W	3,100 lm	Wide beam
910505103276	SM530C 34S/TW9 DIA L1130 BK	Tunable white 2700-6500 K	124 lm/W	3,400 lm	Wide beam
910505103241	SM530C 12S/940 PSD LE2 L570 ALU	4000 K	143 lm/W	1,250 lm	Wide beam
910505103251	SM531C 30S/940 PSD L2250 BK	4000 K	115 lm/W	3,000 lm	Wide beam
910505103265	SM530C 62S/940 PSD L2810 BK	4000 K	150 lm/W	6,200 lm	Wide beam
910505103268	SM530C 86S/940 SIA U4LF1 L2850 ALU	4000 K	141 lm/W	8,600 lm	Wide beam
910505103243	SM530C 17S/940 PSD LE2 L570 BK	4000 K	143 lm/W	1,700 lm	Wide beam
910505103237	SM530C 40S/940 SIA U4 L1170 ALU	4000 K	143 lm/W	4,000 lm	Wide beam
910505103238	SM530C 34S/930 SIA U4 L1170 ALU	3000 K	138 lm/W	3,400 lm	Wide beam
910505103239	SM530C 43S/940 SIA U4 L1450 ALU	4000 K	141 lm/W	4,300 lm	Wide beam
910505103240	SM530C 31S/940 SIA U4 L1450 ALU	4000 K	144 lm/W	3,100 lm	Wide beam
910505103278	SM530C 43S/TW9 SIA U4 L1450 ALU	Tunable white 2700-6500 K	121 lm/W	4,300 lm	Wide beam
910505103266	SM531C 62S/940 PSD L2810 WH	4000 K	111 lm/W	6,200 lm	Wide beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
910505103218	SM530C 40S/940 PSD L1130 ALU	28.5 W	910505103226	SM530C 50S/940 PSD L1410 WH	36 W
910505103219	SM530C 34S/940 PSD L1130 ALU	24.5 W	910505103230	SM530C 31S/940 PSD L1410 WH	22 W
910505103220	SM530C 19S/940 PSD L1410 ALU	14 W	910505103231	SM531C 19S/930 PSD L1410 WH	18.6 W
910505103223	SM531C 19S/940 PSD L1410 ALU	17.8 W	910505103232	SM531C 19S/940 PSD L1410 WH	17.8 W
910505103224	SM531C 19S/930 PSD L1410 ALU	18.6 W	910505103277	SM531C 31S/TW9 DIA L1410 WH	34 W
910505103227	SM530C 43S/940 PSD L1410 ALU	30.5 W	910505103242	SM531C 12S/940 PSD LE2 L570 WH	11.8 W
910505103228	SM530C 34S/930 PSD L1130 ALU	26 W	910505103250	SM530C 30S/940 PSD L2250 ALU	22 W
910505103229	SM531C 31S/940 PSD L1410 ALU	22 W	910505103253	SM530C 50S/930 PSD L2250 ALU	37.5 W
910505103233	SM530C 50S/940 PSD L1410 ALU	36 W	910505103254	SM530C 30S/940 PSD LF1 L2250 ALU	22 W
910505103275	SM530C 40S/TW9 DIA L1130 ALU	33 W	910505103255	SM530C 68S/940 PSD L2250 ALU	48.5 W
910505103221	SM534C 40S/940 PSD L1130 ALU	28.5 W	910505103264	SM530C 62S/930 PSD L2810 ALU	46 W
910505103222	SM534C 50S/940 PSD L1410 ALU	38.5 W	910505103267	SM530C 38S/940 PSD LF1 L2810 ALU	27 W
910505103217	SM530C 19S/940 PSD L1410 WH	14 W	910505103252	SM530C 50S/940 SIA U4 L2290 BK	35.5 W
910505103225	SM530C 43S/940 PSD L1410 WH	30.5 W	910505103236	SM530C 31S/940 PSD L1410 BK	22 W

TrueLine, surface mounted

Order Code	Full Product Name	Power Consumption
910505103276	SM530C 34S/TW9 DIA L1130 BK	27.5 W
910505103241	SM530C 12S/940 PSD LE2 L570 ALU	9.1 W
910505103251	SM531C 30S/940 PSD L2250 BK	26.5 W
910505103265	SM530C 62S/940 PSD L2810 BK	44 W
910505103268	SM530C 86S/940 SIA U4LF1 L2850 ALU	61 W
910505103243	SM530C 17S/940 PSD LE2 L570 BK	12.2 W

Order Code	Full Product Name	Power Consumption
910505103237	SM530C 40S/940 SIA U4 L1170 ALU	28.5 W
910505103238	SM530C 34S/930 SIA U4 L1170 ALU	25.5 W
910505103239	SM530C 43S/940 SIA U4 L1450 ALU	30.5 W
910505103240	SM530C 31S/940 SIA U4 L1450 ALU	21.5 W
910505103278	SM530C 43S/TW9 SIA U4 L1450 ALU	35.5 W
910505103266	SM531C 62S/940 PSD L2810 WH	56 W

Controls and Dimming

Order Code	Full Product Name	Embedded control
910505103218	SM530C 40S/940 PSD L1130 ALU	-
910505103219	SM530C 34S/940 PSD L1130 ALU	-
910505103220	SM530C 19S/940 PSD L1410 ALU	-
910505103223	SM531C 19S/940 PSD L1410 ALU	-
910505103224	SM531C 19S/930 PSD L1410 ALU	-
910505103227	SM530C 43S/940 PSD L1410 ALU	-
910505103228	SM530C 34S/930 PSD L1130 ALU	-
910505103229	SM531C 31S/940 PSD L1410 ALU	-
910505103233	SM530C 50S/940 PSD L1410 ALU	-
910505103275	SM530C 40S/TW9 DIA L1130 ALU	-
910505103221	SM534C 40S/940 PSD L1130 ALU	-
910505103222	SM534C 50S/940 PSD L1410 ALU	-
910505103217	SM530C 19S/940 PSD L1410 WH	-
910505103225	SM530C 43S/940 PSD L1410 WH	-
910505103226	SM530C 50S/940 PSD L1410 WH	-
910505103230	SM530C 31S/940 PSD L1410 WH	-
910505103231	SM531C 19S/930 PSD L1410 WH	-
910505103232	SM531C 19S/940 PSD L1410 WH	-
910505103277	SM531C 31S/TW9 DIA L1410 WH	-
910505103242	SM531C 12S/940 PSD LE2 L570 WH	-
910505103250	SM530C 30S/940 PSD L2250 ALU	-
910505103253	SM530C 50S/930 PSD L2250 ALU	-
910505103254	SM530C 30S/940 PSD LF1 L2250 ALU	-
910505103255	SM530C 68S/940 PSD L2250 ALU	-

Order Code	Full Product Name	Embedded control
910505103264	SM530C 62S/930 PSD L2810 ALU	-
910505103267	SM530C 38S/940 PSD LF1 L2810 ALU	-
910505103252	SM530C 50S/940 SIA U4 L2290 BK	Upgradable sensor slot with SNS210 sensor
910505103236	SM530C 31S/940 PSD L1410 BK	-
910505103276	SM530C 34S/TW9 DIA L1130 BK	-
910505103241	SM530C 12S/940 PSD LE2 L570 ALU	-
910505103251	SM531C 30S/940 PSD L2250 BK	-
910505103265	SM530C 62S/940 PSD L2810 BK	-
910505103268	SM530C 86S/940 SIA U4LF1 L2850 ALU	Upgradable sensor slot with SNS210 sensor
910505103243	SM530C 17S/940 PSD LE2 L570 BK	-
910505103237	SM530C 40S/940 SIA U4 L1170 ALU	Upgradable sensor slot with SNS210 sensor
910505103238	SM530C 34S/930 SIA U4 L1170 ALU	Upgradable sensor slot with SNS210 sensor
910505103239	SM530C 43S/940 SIA U4 L1450 ALU	Upgradable sensor slot with SNS210 sensor
910505103240	SM530C 31S/940 SIA U4 L1450 ALU	Upgradable sensor slot with SNS210 sensor
910505103278	SM530C 43S/TW9 SIA U4 L1450 ALU	Upgradable sensor slot with SNS210 sensor
910505103266	SM531C 62S/940 PSD L2810 WH	-

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910505103218	SM530C 40S/940 PSD L1130 ALU	Aluminum
910505103219	SM530C 34S/940 PSD L1130 ALU	Aluminum
910505103220	SM530C 19S/940 PSD L1410 ALU	Aluminum
910505103223	SM531C 19S/940 PSD L1410 ALU	Aluminum
910505103224	SM531C 19S/930 PSD L1410 ALU	Aluminum
910505103227	SM530C 43S/940 PSD L1410 ALU	Aluminum
910505103228	SM530C 34S/930 PSD L1130 ALU	Aluminum
910505103229	SM531C 31S/940 PSD L1410 ALU	Aluminum
910505103233	SM530C 50S/940 PSD L1410 ALU	Aluminum
910505103275	SM530C 40S/TW9 DIA L1130 ALU	Aluminum
910505103221	SM534C 40S/940 PSD L1130 ALU	Aluminum
910505103222	SM534C 50S/940 PSD L1410 ALU	Aluminum
910505103217	SM530C 19S/940 PSD L1410 WH	White

Order Code	Full Product Name	Housing Color
910505103225	SM530C 43S/940 PSD L1410 WH	White
910505103226	SM530C 50S/940 PSD L1410 WH	White
910505103230	SM530C 31S/940 PSD L1410 WH	White
910505103231	SM531C 19S/930 PSD L1410 WH	White
910505103232	SM531C 19S/940 PSD L1410 WH	White
910505103277	SM531C 31S/TW9 DIA L1410 WH	White
910505103242	SM531C 12S/940 PSD LE2 L570 WH	White
910505103250	SM530C 30S/940 PSD L2250 ALU	Aluminum
910505103253	SM530C 50S/930 PSD L2250 ALU	Aluminum
910505103254	SM530C 30S/940 PSD LF1 L2250 ALU	Aluminum
910505103255	SM530C 68S/940 PSD L2250 ALU	Aluminum
910505103264	SM530C 62S/930 PSD L2810 ALU	Aluminum
910505103267	SM530C 38S/940 PSD LF1 L2810 ALU	Aluminum

TrueLine, surface mounted

Order Code	Full Product Name	Housing Color
910505103252	SM530C 50S/940 SIA U4 L2290 BK	Black
910505103236	SM530C 31S/940 PSD L1410 BK	Black
910505103276	SM530C 34S/TW9 DIA L1130 BK	Black
910505103241	SM530C 12S/940 PSD LE2 L570 ALU	Aluminum
910505103251	SM531C 30S/940 PSD L2250 BK	Black
910505103265	SM530C 62S/940 PSD L2810 BK	Black
910505103268	SM530C 86S/940 SIA U4LF1 L2850 ALU	Aluminum


Order Code	Full Product Name	Housing Color
910505103243	SM530C 17S/940 PSD LE2 L570 BK	Black
910505103237	SM530C 40S/940 SIA U4 L1170 ALU	Aluminum
910505103238	SM530C 34S/930 SIA U4 L1170 ALU	Aluminum
910505103239	SM530C 43S/940 SIA U4 L1450 ALU	Aluminum
910505103240	SM530C 31S/940 SIA U4 L1450 ALU	Aluminum
910505103278	SM530C 43S/TW9 SIA U4 L1450 ALU	Aluminum
910505103266	SM531C 62S/940 PSD L2810 WH	White

Product Data


Order Code	Full Product Name	Product family code
910505103218	SM530C 40S/940 PSD L1130 ALU	SM530C
910505103219	SM530C 34S/940 PSD L1130 ALU	SM530C
910505103220	SM530C 19S/940 PSD L1410 ALU	SM530C
910505103223	SM531C 19S/940 PSD L1410 ALU	SM531C
910505103224	SM531C 19S/930 PSD L1410 ALU	SM531C
910505103227	SM530C 43S/940 PSD L1410 ALU	SM530C
910505103228	SM530C 34S/930 PSD L1130 ALU	SM530C
910505103229	SM531C 31S/940 PSD L1410 ALU	SM531C
910505103233	SM530C 50S/940 PSD L1410 ALU	SM530C
910505103275	SM530C 40S/TW9 DIA L1130 ALU	SM530C
910505103221	SM534C 40S/940 PSD L1130 ALU	SM534C
910505103222	SM534C 50S/940 PSD L1410 ALU	SM534C
910505103217	SM530C 19S/940 PSD L1410 WH	SM530C
910505103225	SM530C 43S/940 PSD L1410 WH	SM530C
910505103226	SM530C 50S/940 PSD L1410 WH	SM530C
910505103230	SM530C 31S/940 PSD L1410 WH	SM530C
910505103231	SM531C 19S/930 PSD L1410 WH	SM531C
910505103232	SM531C 19S/940 PSD L1410 WH	SM531C
910505103277	SM531C 31S/TW9 DIA L1410 WH	SM531C
910505103242	SM531C 12S/940 PSD LE2 L570 WH	SM531C

Order Code	Full Product Name	Product family code
910505103250	SM530C 30S/940 PSD L2250 ALU	SM530C
910505103253	SM530C 50S/930 PSD L2250 ALU	SM530C
910505103254	SM530C 30S/940 PSD LF1 L2250 ALU	SM530C
910505103255	SM530C 68S/940 PSD L2250 ALU	SM530C
910505103264	SM530C 62S/930 PSD L2810 ALU	SM530C
910505103267	SM530C 38S/940 PSD LF1 L2810 ALU	SM530C
910505103252	SM530C 50S/940 SIA U4 L2290 BK	SM530C
910505103236	SM530C 31S/940 PSD L1410 BK	SM530C
910505103276	SM530C 34S/TW9 DIA L1130 BK	SM530C
910505103241	SM530C 12S/940 PSD LE2 L570 ALU	SM530C
910505103251	SM531C 30S/940 PSD L2250 BK	SM531C
910505103265	SM530C 62S/940 PSD L2810 BK	SM530C
910505103268	SM530C 86S/940 SIA U4LF1 L2850 ALU	SM530C
910505103243	SM530C 17S/940 PSD LE2 L570 BK	SM530C
910505103237	SM530C 40S/940 SIA U4 L1170 ALU	SM530C
910505103238	SM530C 34S/930 SIA U4 L1170 ALU	SM530C
910505103239	SM530C 43S/940 SIA U4 L1450 ALU	SM530C
910505103240	SM530C 31S/940 SIA U4 L1450 ALU	SM530C
910505103278	SM530C 43S/TW9 SIA U4 L1450 ALU	SM530C
910505103266	SM531C 62S/940 PSD L2810 WH	SM531C


Polar Wide Diagrams



Polar Normal (separate) - SM530CI -
910505103239






Polar Normal (separate) - SM530CI -
910505103223



Polar Normal (separate) - SM530CI -
910505103224




Polar Wide Diagrams



Polar Normal (separate) - SM530CI - 910505103228

Polar Normal (separate) - SM530CI - 910505103228




Polar Normal (separate) - SM530CI - 910505103278



Polar Normal (separate) - SM530CI - 910505103251

Polar Normal (separate) - SM530CI - 910505103229

Polar Normal (separate) - SM530CI - 910505103267




Polar Normal (separate) - SM530CI - 910505103264


Polar Normal (separate) - SM530CI - 910505103255

Polar Normal (separate) - SM530CI - 910505103226


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103217




Polar Normal (separate) - SM530CI - 910505103230




Polar Normal (separate) - SM530CI - 910505103232




Polar Normal (separate) - SM530CI - 910505103222




Polar Normal (separate) - SM530CI - 910505103238




Polar Normal (separate) - SM530CI - 910505103221



Polar Normal (separate) - SM530CI - 910505103250






Polar Normal (separate) - SM530CI - 910505103227



Polar Normal (separate) - SM530CI - 910505103218




Polar Wide Diagrams



Polar Normal (separate) - SM530CI - 910505103225

Polar Normal (separate) - SM530CI - 910505103275




Polar Normal (separate) - SM530CI - 910505103254



Polar Normal (separate) - SM530CI - 910505103243

Polar Normal (separate) - SM530CI - 910505103252

Polar Normal (separate) - SM530CI - 910505103277




Polar Normal (separate) - SM530CI - 910505103276


Polar Normal (separate) - SM530CI - 910505103240

Polar Normal (separate) - SM530CI - 910505103266


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103268




Polar Normal (separate) - SM530CI - 910505103242




Polar Normal (separate) - SM530CI - 910505103231




Polar Normal (separate) - SM530CI - 910505103253




Polar Normal (separate) - SM530CI - 910505103233




Polar Normal (separate) - SM530CI - 910505103265



Polar Normal (separate) - SM530CI - 910505103219




Polar Normal (separate) - SM530CI - 910505103241



Polar Normal (separate) - SM530CI - 910505103220

TrueLine, surface mounted

Polar Wide Diagrams



Polar Normal (separate) - SM530CI -
910505103236

