



Flexible and Elegant

SlimBalance G3

SlimBalance G3 SP570P is a flexible linear office offer which fits a variety of spaces like office, education. It offers flexible width of 35/60/90/120mm and length of 600/1200/1500mm to fit multiple applications. Geometric shapes help further create differentiated space. By means of its special designed structure, it offers quick and easy installation and maintenance. UGR19 is available for certain types through customized solution to provide a better visual comfort office environment.

Benefits

- High lm/w provides better energy saving
- Flexible width offers the feasibility to fit multiple ceiling spaces
- Dali and Interact interfaces available for easy system control
- Low UGR offer for visual comfort
- Multiple mounting installations and geometric shapes to cater for various applications
- Easy installation mechanism and modular design help save installation and maintenance time

Features

- System efficiency: max 130lm/W
- Product width with 35/60/90/120mm options
- CRI 80 and 90 available
- Lifetime: 50k hours (L70@ta=25deg)
- UGR19 available for certain types through customized solution
- Easy 'Slide and Click' mechanism for quick continuous installation

Application

- Open plan office
- Public indoor area
- Meeting/Training room
- Library


Specifications

SlimBalance G3


Ceiling type	Open ceiling office for suspension installation
	Plaster board ceiling for recessed installation and surface mounted installation
Mains Voltage	220-240V / 50 - 60Hz
Dimming	PSU: non-dimmable
	PSD: Dimmable via Dali-broadcasting
	WIA: Wireless control, compatible with Interact
	SIA: Wireless control, compatible with SNS210 sensor
Control system input	Dali
Integrated sensors	SNS210 available for SIA version
Material	Extrusion aluminium
Luminaire efficacy	130lm/w

Correlated color	840
temperature - CCT	940
Color Rendering index - 840, 940	
CRI	
Optic	UGR19 is available through lens design
Ingress protection	IP20
Driver replaceable	Yes
UGR	19 is available through lens design
Installation	Suspension
	Recessed
	Surface mounted


Versions




Dimensional drawing




SP570 W6L120 SD shop drawing





SP570 L60W6 Y shop drawing





SP570 L60W6 X shop drawing





SP570 W6L60 SD shop drawing







SP570 W9L120 SD shop drawing




Dimensional drawing



Product Type	Length (mm)	Width (mm)	Height (mm)
L60W6 T.C	1235	63	88
L60W6 T.C	1252	63	88
L60W6 T.C	1265	63	88




SP570 L60W6 T shop drawing




SP570 W6L120 CD shop drawing

SlimBalance G3


Dimensional drawing



SP570 W6L60 SD shop drawing



SP570 L60W6 HEX shop drawing



Product details

SlimBalance G3




SlimBalance G3




SlimBalance G3



SlimBalance G3



Product details



General Information	
Gear	-
Service tag	Yes
Operating and Electrical	
Protection class IEC	Safety class I
Line Frequency	50 or 60 Hz
Mechanical and Housing	
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
CE mark	Yes
ENEC mark	-
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Initial chromaticity	SDCM<=4

General Information			
Order Code	Full Product Name	Driver included	Number of gear units
911401534842	SP570P LED50/840 L150W6 SD PSU	Yes	1 unit
911401534942	SP570P LED31/840 L150W6 SD PSU	Yes	1 unit
911401536242	SP570P LED50/940 L150W6 SD PSD	Yes	1 unit
911401536742	SM570C LED50/840 L150W6 SD PSU	Yes	1 unit
911401537342	SP570P LED50/840 L150W6 CD PSU	Yes	1 unit
911401537442	SP570P LED31/840 L150W6 CD PSU	Yes	1 unit
911401538642	SP570P LED50/940 L150W6 CD PSD	Yes	1 unit
911401539142	SM570C LED50/840 L150W6 CD PSU	Yes	1 unit
911401539542	SP571P LED50/840 L150W6 SD PSU	Yes	1 unit
911401540342	SP571P LED50/840 L150W6 CD PSU	Yes	1 unit
911401534642	SP570P LED40/840 L120W6 SD PSU	Yes	1 unit
911401534742	SP570P LED25/840 L120W6 SD PSU	Yes	1 unit
911401536142	SP570P LED40/940 L120W6 SD PSD	Yes	1 unit
911401536542	SM570C LED40/840 L120W6 SD PSU	Yes	1 unit
911401537142	SP570P LED40/840 L120W6 CD PSU	Yes	1 unit
911401537242	SP570P LED25/840 L120W6 CD PSU	Yes	1 unit
911401538542	SP570P LED40/940 L120W6 CD PSD	Yes	1 unit
911401538942	SM570C LED40/840 L120W6 CD PSU	Yes	1 unit
911401539442	SP571P LED40/840 L120W6 SD PSU	Yes	1 unit
911401540142	SP571P LED40/840 L120W6 CD PSU	Yes	1 unit
911401534442	SP570P LED20/840 L60W6 SD PSU	Yes	1 unit
911401534542	SP570P LED12/840 L60W6 SD PSU	Yes	1 unit
911401536042	SP570P LED20/940 L60W6 SD PSD	Yes	1 unit

Order Code	Full Product Name	Driver included	Number of gear units
911401536342	SM570C LED20/840 L60W6 SD PSU	Yes	1 unit
911401536942	SP570P LED20/840 L60W6 CD PSU	Yes	1 unit
911401537042	SP570P LED12/840 L60W6 CD PSU	Yes	1 unit
911401538442	SP570P LED20/940 L60W6 CD PSD	Yes	1 unit
911401538742	SM570C LED20/840 L60W6 CD PSU	Yes	1 unit
911401539342	SP571P LED20/840 L60W6 SD PSU	Yes	1 unit
911401539942	SP571P LED20/840 L60W6 CD PSU	Yes	1 unit
911401540042	SP571P LED12/840 L60W6 CD PSU	Yes	1 unit
911401568942	RC570B LED40/840 L120W12 SD PSU	-	-
911401569842	RC570B LED40/940 L120W12 SD PSD	-	-
911401570242	RC570B LED40/840 L120W12 CD PSU	-	-
911401570342	RC570B LED25/840 L120W12 CD PSU	-	-
911401571342	RC570X LED40/940 L120W12 SD WIA	-	-
911401571442	RC570X LED40/940 L120W12 CD WIA	-	-
911401571642	RC570B LED40/940 L120W12 CD PSD	-	-
911401540942	SP570P LED40/840 L120W9 SD PSU	Yes	1 unit
911401541042	SP570P LED25/840 L120W9 SD PSU	Yes	1 unit
911401542342	SP570P LED40/940 L120W9 SD PSD	Yes	1 unit
911401542742	SM570C LED40/840 L120W9 SD PSU	Yes	1 unit
911401543342	SP570P LED40/840 L120W9 CD PSU	Yes	1 unit
911401543442	SP570P LED25/840 L120W9 CD PSU	Yes	1 unit
911401544742	SP570P LED40/940 L120W9 CD PSD	Yes	1 unit
911401545142	SM570C LED40/840 L120W9 CD PSU	Yes	1 unit
911401545742	SP571P LED40/840 L120W9 SD PSU	Yes	1 unit
911401546642	SP571P LED40/840 L120W9 CD PSU	Yes	1 unit
911401547542	SP570P LED50/840 L150W12 SD PSU	Yes	1 unit
911401548442	SP570P LED50/940 L150W12 SD PSD	Yes	1 unit
911401548942	SM570C LED50/840 L150W12 SD PSU	Yes	1 unit
911401549542	SP570P LED50/840 L150W12 CD PSU	Yes	1 unit
911401549642	SP570P LED31/840 L150W12 CD PSU	Yes	1 unit
911401550842	SP570P LED50/940 L150W12 CD PSD	Yes	1 unit
911401551342	SM570C LED50/840 L150W12 CD PSU	Yes	1 unit
911401551742	SP571P LED50/840 L150W12 SD PSU	Yes	1 unit
911401552342	SP571P LED50/840 L150W12 CD PSU	Yes	1 unit
911401572042	RC570B LED40/940 L60W6 PSD LC	-	-
911401574042	RC570B LED40/840 L60W6 PSU LC	-	-
911401566042	RC570B LED50/840 L150W6 SD PSU	-	-
911401566942	RC570B LED50/940 L150W6 SD PSD	-	-
911401567442	RC570B LED50/840 L150W6 CD PSU	-	-
911401567542	RC570B LED31/840 L150W6 CD PSU	-	-
911401568742	RC570B LED50/940 L150W6 CD PSD	-	-
911401569342	RC570B LED50/9TW L150W6 SD PSD	-	-
911401569642	RC570B LED50/9TW L150W6 CD PSD	-	-
911401570942	RC570X LED50/940 L150W6 SD WIA	-	-
911401571242	RC570X LED50/940 L150W6 CD WIA	-	-
911401553943	SP570P LED40/840 L60W6 PSU X	Yes	-
911401554043	SP570P LED40/840 L60W6 PSD X	Yes	-
911401554443	SP570P LED40/940 L60W6 PSD X	Yes	-
911401547442	SP570P LED40/840 L120W12 SD PSU	Yes	1 unit
911401548342	SP570P LED40/940 L120W12 SD PSD	Yes	1 unit
911401548742	SM570C LED40/840 L120W12 SD PSU	Yes	1 unit
911401549342	SP570P LED40/840 L120W12 CD PSU	Yes	1 unit

Order Code	Full Product Name	Driver included	Number of gear units
911401549442	SP570P LED25/840 L120W12 CD PSU	Yes	1 unit
911401550742	SP570P LED40/940 L120W12 CD PSD	Yes	1 unit
911401551142	SM570C LED40/840 L120W12 CD PSU	Yes	1 unit
911401551642	SP571P LED40/840 L120W12 SD PSU	Yes	1 unit
911401552242	SP571P LED40/840 L120W12 CD PSU	Yes	1 unit
911401569042	RC570B LED50/840 L150W12 SD PSU	-	-
911401569942	RC570B LED50/940 L150W12 SD PSD	-	-
911401570442	RC570B LED50/840 L150W12 CD PSU	-	-
911401570542	RC570B LED31/840 L150W12 CD PSU	-	-
911401571742	RC570B LED50/940 L150W12 CD PSD	-	-
911401541142	SP570P LED50/840 L150W9 SD PSU	Yes	1 unit
911401541242	SP570P LED31/840 L150W9 SD PSU	Yes	1 unit
911401542442	SP570P LED50/940 L150W9 SD PSD	Yes	1 unit
911401542942	SM570C LED50/840 L150W9 SD PSU	Yes	1 unit
911401543542	SP570P LED50/840 L150W9 CD PSU	Yes	1 unit
911401543642	SP570P LED31/840 L150W9 CD PSU	Yes	1 unit
911401544842	SP570P LED50/940 L150W9 CD PSD	Yes	1 unit
911401545342	SM570C LED50/840 L150W9 CD PSU	Yes	1 unit
911401545942	SP571P LED50/840 L150W9 SD PSU	Yes	1 unit
911401546842	SP571P LED50/840 L150W9 CD PSU	Yes	1 unit
911401565942	RC570B LED40/840 L120W6 SD PSU	-	-
911401566842	RC570B LED40/940 L120W6 SD PSD	-	-
911401567242	RC570B LED40/840 L120W6 CD PSU	-	-
911401567342	RC570B LED25/840 L120W6 CD PSU	-	-
911401568642	RC570B LED40/940 L120W6 CD PSD	-	-
911401569242	RC570B LED40/9TW L120W6 SD PSD	-	-
911401569542	RC570B LED40/9TW L120W6 CD PSD	-	-
911401570842	RC570X LED40/940 L120W6 SD WIA	-	-
911401571142	RC570X LED40/940 L120W6 CD WIA	-	-
911401540742	SP570P LED20/840 L60W9 SD PSU	Yes	1 unit
911401540842	SP570P LED12/840 L60W9 SD PSU	Yes	1 unit
911401542242	SP570P LED20/940 L60W9 SD PSD	Yes	1 unit
911401542542	SM570C LED20/840 L60W9 SD PSU	Yes	1 unit
911401543142	SP570P LED20/840 L60W9 CD PSU	Yes	1 unit
911401543242	SP570P LED12/840 L60W9 CD PSU	Yes	1 unit
911401544642	SP570P LED20/940 L60W9 CD PSD	Yes	1 unit
911401544942	SM570C LED20/840 L60W9 CD PSU	Yes	1 unit
911401545542	SP571P LED20/840 L60W9 SD PSU	Yes	1 unit
911401545642	SP571P LED12/840 L60W9 SD PSU	Yes	1 unit
911401546442	SP571P LED20/840 L60W9 CD PSU	Yes	1 unit
911401546542	SP571P LED12/840 L60W9 CD PSU	Yes	1 unit
911401554743	SP570P LED60/840 L60W6 PSU Y	Yes	-
911401555243	SP570P LED60/940 L60W6 PSD Y	Yes	-
911401565842	RC570B LED20/840 L60W6 SD PSU	-	-
911401566742	RC570B LED20/940 L60W6 SD PSD	-	-
911401567042	RC570B LED20/840 L60W6 CD PSU	-	-
911401567142	RC570B LED12/840 L60W6 CD PSU	-	-
911401568542	RC570B LED20/940 L60W6 CD PSD	-	-
911401569142	RC570B LED20/9TW L60W6 SD PSD	-	-
911401569442	RC570B LED20/9TW L60W6 CD PSD	-	-
911401570742	RC570X LED20/940 L60W6 SD WIA	-	-
911401571042	RC570X LED20/940 L60W6 CD WIA	-	-

Order Code	Full Product Name	Driver included	Number of gear units
911401555643	SP570P LED45/840 L60W6 PSU HEX	Yes	-
911401556043	SP570P LED45/840 L60W6 PSD HEX	Yes	-
911401556443	SP570P LED45/940 L60W6 PSU HEX	Yes	-
911401556843	SP570P LED45/940 L60W6 PSD HEX	Yes	-
911401553143	SP570P LED40/840 L60W6 PSU T	Yes	-
911401553243	SP570P LED40/840 L60W6 PSD T	Yes	-
911401553643	SP570P LED40/940 L60W6 PSD T	Yes	-
911401547342	SP570P LED20/840 L60W12 SD PSU	Yes	1 unit
911401548242	SP570P LED20/940 L60W12 SD PSD	Yes	1 unit
911401548542	SM570C LED20/840 L60W12 SD PSU	Yes	1 unit
911401549142	SP570P LED20/840 L60W12 CD PSU	Yes	1 unit
911401549242	SP570P LED12/840 L60W12 CD PSU	Yes	1 unit
911401550642	SP570P LED20/940 L60W12 CD PSD	Yes	1 unit
911401550942	SM570C LED20/840 L60W12 CD PSU	Yes	1 unit
911401551542	SP571P LED20/840 L60W12 SD PSU	Yes	1 unit
911401552142	SP571P LED20/840 L60W12 CD PSU	Yes	1 unit

Light Technical (1/2)

Order Code	Full Product Name	Beam angle of light	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Order Code	Full Product Name	Beam angle of light	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
		source	(Nom)	(CRI)	(rated) (Nom)			source	(Nom)	(CRI)	(rated) (Nom)
911401534842	SP570P LED50/840 L150W6 SD PSU	120 degree(s)	4000 K	80	131.9506172839506 lm/W	911401539142	SM570C LED50/840 L150W6 CD PSU	120 degree(s)	4000 K	80	131.85185185185185 lm/W
911401534942	SP570P LED31/840 L150W6 SD PSU	120 degree(s)	4000 K	80	138.29787234042553 lm/W	911401539542	SP571P LED50/840 L150W6 SD PSU	120 degree(s)	4000 K	80	133.86666666666667 lm/W
911401536242	SP570P LED50/940 L150W6 SD PSD	120 degree(s)	4000 K	90	111.70731707317073 lm/W	911401540342	SP571P LED50/840 L150W6 CD PSU	120 degree(s)	4000 K	80	133.86666666666667 lm/W
911401536742	SM570C LED50/840 L150W6 SD PSU	120 degree(s)	4000 K	80	131.9506172839506 lm/W	911401534642	SP570P LED40/840 L120W6 SD PSU	120 degree(s)	4000 K	80	131.25 lm/W
911401537342	SP570P LED50/840 L150W6 CD PSU	120 degree(s)	4000 K	80	131.85185185185185 lm/W	911401534742	SP570P LED25/840 L120W6 SD PSU	120 degree(s)	4000 K	80	140.54054054054055 lm/W
911401537442	SP570P LED31/840 L150W6 CD PSU	120 degree(s)	4000 K	80	136.59574468085106 lm/W	911401536142	SP570P LED40/940 L120W6 SD PSD	120 degree(s)	4000 K	90	119.70149253731343 lm/W
911401538642	SP570P LED50/940 L150W6 CD PSD	120 degree(s)	4000 K	90	122.4390243902439 lm/W	911401536542	SM570C LED40/840 L120W6 SD PSU	120 degree(s)	4000 K	80	131.25 lm/W

SlimBalance G3

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401537142	SP570P LED40/840 L120W6 CD PSU	120 degree(s)	4000 K	80	133.4375 lm/W
911401537242	SP570P LED25/840 L120W6 CD PSU	120 degree(s)	4000 K	80	138.9189189189189 lm/W
911401538542	SP570P LED40/940 L120W6 CD PSD	120 degree(s)	4000 K	90	119.70149253731343 lm/W
911401538942	SM570C LED40/840 L120W6 CD PSU	120 degree(s)	4000 K	80	133.4375 lm/W
911401539442	SP571P LED40/840 L120W6 SD PSU	120 degree(s)	4000 K	80	136.27118644067798 lm/W
911401540142	SP571P LED40/840 L120W6 CD PSU	120 degree(s)	4000 K	80	136.27118644067798 lm/W
911401534442	SP570P LED20/840 L60W6 SD PSU	120 degree(s)	4000 K	80	118.85714285714286 lm/W
911401534542	SP570P LED12/840 L60W6 SD PSU	120 degree(s)	4000 K	80	125 lm/W
911401536042	SP570P LED20/940 L60W6 SD PSD	120 degree(s)	4000 K	90	111.42857142857143 lm/W
911401536342	SM570C LED20/840 L60W6 SD PSU	120 degree(s)	4000 K	80	118.85714285714286 lm/W
911401536942	SP570P LED20/840 L60W6 CD PSU	120 degree(s)	4000 K	80	118.85714285714286 lm/W
911401537042	SP570P LED12/840 L60W6 CD PSU	120 degree(s)	4000 K	80	125 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401538442	SP570P LED20/940 L60W6 CD PSD	120 degree(s)	4000 K	90	111.42857142857143 lm/W
911401538742	SM570C LED20/840 L60W6 CD PSU	120 degree(s)	4000 K	80	118.85714285714286 lm/W
911401539342	SP571P LED20/840 L60W6 SD PSU	120 degree(s)	4000 K	80	147.85714285714286 lm/W
911401539942	SP571P LED20/840 L60W6 CD PSU	120 degree(s)	4000 K	80	147.85714285714286 lm/W
911401540042	SP571P LED12/840 L60W6 CD PSU	120 degree(s)	4000 K	80	155.55555555555554 lm/W
911401568942	RC570B LED40/840 L120W12 SD PSU	116 degree(s)	4000 K	>80	147 lm/W
911401569842	RC570B LED40/940 L120W12 SD PSD	116 degree(s)	4000 K	>90	131 lm/W
911401570242	RC570B LED40/840 L120W12 CD PSU	116 degree(s)	4000 K	>80	147 lm/W
911401570342	RC570B LED25/840 L120W12 CD PSU	116 degree(s)	4000 K	>80	143 lm/W
911401571342	RC570X LED40/940 L120W12 SD WIA	116 degree(s)	4000 K	>90	135 lm/W
911401571442	RC570X LED40/940 L120W12 CD WIA	116 degree(s)	4000 K	>90	135 lm/W
911401571642	RC570B LED40/940 L120W12 CD PSD	116 degree(s)	4000 K	>90	131 lm/W

Order Code	Full Product Name	Beam angle of light	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
		source			
911401540942	SP570P	120	4000 K	80	131.25 lm/W
	LED40/840	degree(s)			
	L120W9 SD				
	PSU				
911401541042	SP570P	120	4000 K	80	143.24324324324326
	LED25/840	degree(s)			lm/W
	L120W9 SD				
	PSU				
911401542342	SP570P	120	4000 K	90	119.70149253731343
	LED40/940	degree(s)			lm/W
	L120W9 SD				
	PSD				
911401542742	SM570C	120	4000 K	80	131.25 lm/W
	LED40/840	degree(s)			
	L120W9 SD				
	PSU				
911401543342	SP570P	120	4000 K	80	131.25 lm/W
	LED40/840	degree(s)			
	L120W9 CD				
	PSU				
911401543442	SP570P	120	4000 K	80	136.21621621621622
	LED25/840	degree(s)			lm/W
	L120W9 CD				
	PSU				
911401544742	SP570P	120	4000 K	90	117.61194029850746
	LED40/940	degree(s)			lm/W
	L120W9 CD				
	PSD				
911401545142	SM570C	120	4000 K	80	131.25 lm/W
	LED40/840	degree(s)			
	L120W9 CD				
	PSU				
911401545742	SP571P	120	4000 K	80	136.61016949152543
	LED40/840	degree(s)			lm/W
	L120W9 SD				
	PSU				
911401546642	SP571P	120	4000 K	80	136.61016949152543
	LED40/840	degree(s)			lm/W
	L120W9 CD				
	PSU				
911401547542	SP570P	120	4000 K	80	146.1764705882353
	LED50/840	degree(s)			lm/W
	L150W12 SD				
	PSU				
911401548442	SP570P	120	4000 K	90	137.64705882352942
	LED50/940	degree(s)			lm/W
	L150W12 SD				
	PSD				

Order Code	Full Product Name	Beam angle of light	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
		source			
911401548942	SM570C	120	4000 K	80	146.1764705882353
	LED50/840	degree(s)			lm/W
	L150W12 SD				
	PSU				
911401549542	SP570P	120	4000 K	80	146.1764705882353
	LED50/840	degree(s)			lm/W
	L150W12 CD				
	PSU				
911401549642	SP570P	120	4000 K	80	148.8095238095238
	LED31/840	degree(s)			lm/W
	L150W12 CD				
	PSU				
911401550842	SP570P	120	4000 K	90	137.64705882352942
	LED50/940	degree(s)			lm/W
	L150W12 CD				
	PSD				
911401551342	SM570C	120	4000 K	80	146.1764705882353
	LED50/840	degree(s)			lm/W
	L150W12 CD				
	PSU				
911401551742	SP571P	120	4000 K	80	143.33333333333334
	LED50/840	degree(s)			lm/W
	L150W12 SD				
	PSU				
911401552342	SP571P	120	4000 K	80	143.33333333333334
	LED50/840	degree(s)			lm/W
	L150W12 CD				
	PSU				
911401572042	RC570B	116	4000 K	>90	119 lm/W
	LED40/940	degree(s)			
	L60W6 PSD				
	LC				
911401574042	RC570B	116	4000 K	>80	133 lm/W
	LED40/840	degree(s)			
	L60W6 PSU				
	LC				
911401566042	RC570B	116	4000 K	>80	132 lm/W
	LED50/840	degree(s)			
	L150W6 SD				
	PSU				
911401566942	RC570B	116	4000 K	>90	110 lm/W
	LED50/940	degree(s)			
	L150W6 SD				
	PSD				
911401567442	RC570B	116	4000 K	>80	132 lm/W
	LED50/840	degree(s)			
	L150W6 CD				
	PSU				

Order Code	Full Product Name	Beam angle of light	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
		source			
911401567542	RC570B	116	4000 K	>80	138 lm/W
	LED31/840	degree(s)			
	L150W6 CD				
	PSU				
911401568742	RC570B	116	4000 K	>90	110 lm/W
	LED50/940	degree(s)			
	L150W6 CD				
	PSD				
911401569342	RC570B	116	Tunable	>90	122 lm/W
	LED50/9TW	degree(s)	White		
	L150W6 SD				
	PSD				
911401569642	RC570B	116	Tunable	>90	122 lm/W
	LED50/9TW	degree(s)	White		
	L150W6 CD				
	PSD				
911401570942	RC570X	116	4000 K	>90	125 lm/W
	LED50/940	degree(s)			
	L150W6 SD				
	WIA				
911401571242	RC570X	116	4000 K	>90	125 lm/W
	LED50/940	degree(s)			
	L150W6 CD				
	WIA				
911401553943	SP570P	116	4000 K	>80	133 lm/W
	LED40/840	degree(s)			
	L60W6 PSU				
	X				
911401554043	SP570P	116	4000 K	>80	128 lm/W
	LED40/840	degree(s)			
	L60W6 PSD				
	X				
911401554443	SP570P	116	4000 K	>90	128 lm/W
	LED40/940	degree(s)			
	L60W6 PSD				
	X				
911401547442	SP570P	120	4000 K	80	147.40740740740742 lm/W
	LED40/840	degree(s)			
	L120W12 SD				
	PSU				
911401548342	SP570P	120	4000 K	90	131.2280701754386 lm/W
	LED40/940	degree(s)			
	L120W12 SD				
	PSD				
911401548742	SM570C	120	4000 K	80	147.40740740740742 lm/W
	LED40/840	degree(s)			
	L120W12 SD				
	PSU				

Order Code	Full Product Name	Beam angle of light	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
		source			
911401549342	SP570P	120	4000 K	80	147.40740740740742 lm/W
	LED40/840	degree(s)			
	L120W12 CD				
	PSU				
911401549442	SP570P	120	4000 K	80	142.85714285714286 lm/W
	LED25/840	degree(s)			
	L120W12 CD				
	PSU				
911401550742	SP570P	120	4000 K	90	131.2280701754386 lm/W
	LED40/940	degree(s)			
	L120W12 CD				
	PSD				
911401551142	SM570C	120	4000 K	80	147.40740740740742 lm/W
	LED40/840	degree(s)			
	L120W12 CD				
	PSU				
911401551642	SP571P	120	4000 K	80	140.37735849056602 lm/W
	LED40/840	degree(s)			
	L120W12 SD				
	PSU				
911401552242	SP571P	120	4000 K	80	140.37735849056602 lm/W
	LED40/840	degree(s)			
	L120W12 CD				
	PSU				
911401569042	RC570B	116	4000 K	>80	146 lm/W
	LED50/840	degree(s)			
	L150W12 SD				
	PSU				
911401569942	RC570B	116	4000 K	>90	138 lm/W
	LED50/940	degree(s)			
	L150W12 SD				
	PSD				
911401570442	RC570B	116	4000 K	>80	146 lm/W
	LED50/840	degree(s)			
	L150W12 CD				
	PSU				
911401570542	RC570B	116	4000 K	>80	149 lm/W
	LED31/840	degree(s)			
	L150W12 CD				
	PSU				
911401571742	RC570B	116	4000 K	>90	138 lm/W
	LED50/940	degree(s)			
	L150W12 CD				
	PSD				
911401541142	SP570P	120	4000 K	80	122.46913580246914 lm/W
	LED50/840	degree(s)			
	L150W9 SD				
	PSU				

SlimBalance G3

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401541242	SP570P LED31/840 L150W9 SD PSU	120 degree(s)	4000 K	80	140.85106382978722 lm/W
911401542442	SP570P LED50/940 L150W9 SD PSD	120 degree(s)	4000 K	90	113.65853658536585 lm/W
911401542942	SM570C LED50/840 L150W9 SD PSU	120 degree(s)	4000 K	80	124 lm/W
911401543542	SP570P LED50/840 L150W9 CD PSU	120 degree(s)	4000 K	80	129.3827160493827 lm/W
911401543642	SP570P LED31/840 L150W9 CD PSU	120 degree(s)	4000 K	80	134.04255319148936 lm/W
911401544842	SP570P LED50/940 L150W9 CD PSD	120 degree(s)	4000 K	90	120.29268292682927 lm/W
911401545342	SM570C LED50/840 L150W9 CD PSU	120 degree(s)	4000 K	80	129.3827160493827 lm/W
911401545942	SP571P LED50/840 L150W9 SD PSU	120 degree(s)	4000 K	80	136.8 lm/W
911401546842	SP571P LED50/840 L150W9 CD PSU	120 degree(s)	4000 K	80	136.8 lm/W
911401565942	RC570B LED40/840 L120W6 SD PSU	116 degree(s)	4000 K	>80	135 lm/W
911401566842	RC570B LED40/940 L120W6 SD PSD	116 degree(s)	4000 K	>90	122 lm/W
911401567242	RC570B LED40/840 L120W6 CD PSU	116 degree(s)	4000 K	>80	135 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401567342	RC570B LED25/840 L120W6 CD PSU	116 degree(s)	4000 K	>80	141 lm/W
911401568642	RC570B LED40/940 L120W6 CD PSD	116 degree(s)	4000 K	>90	122 lm/W
911401569242	RC570B LED40/9T W L120W6 SD PSD	116 degree(s)	Tunable White	>90	119 lm/W
911401569542	RC570B LED40/9T W L120W6 CD PSD	116 degree(s)	Tunable White	>90	119 lm/W
911401570842	RC570X LED40/940 L120W6 SD WIA	116 degree(s)	4000 K	>90	125 lm/W
911401571142	RC570X LED40/940 L120W6 CD WIA	116 degree(s)	4000 K	>90	125 lm/W
911401540742	SP570P LED20/840 L60W9 SD PSU	120 degree(s)	4000 K	80	121.14285714285714 lm/W
911401540842	SP570P LED12/840 L60W9 SD PSU	120 degree(s)	4000 K	80	128 lm/W
911401542242	SP570P LED20/940 L60W9 SD PSD	120 degree(s)	4000 K	90	114.28571428571429 lm/W
911401542542	SM570C LED20/840 L60W9 SD PSU	120 degree(s)	4000 K	80	121.14285714285714 lm/W
911401543142	SP570P LED20/840 L60W9 CD PSU	120 degree(s)	4000 K	80	121.14285714285714 lm/W
911401543242	SP570P LED12/840 L60W9 CD PSU	120 degree(s)	4000 K	80	128 lm/W

SlimBalance G3

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401544642	SP570P LED20/940 L60W9 CD PSD	120 degree(s)	4000 K	90	114.28571428571429 lm/W
911401544942	SM570C LED20/840 L60W9 CD PSU	120 degree(s)	4000 K	80	121.14285714285714 lm/W
911401545542	SP571P LED20/840 L60W9 SD PSU	120 degree(s)	4000 K	80	148.57142857142858 lm/W
911401545642	SP571P LED12/840 L60W9 SD PSU	120 degree(s)	4000 K	80	156.55555555555554 lm/W
911401546442	SP571P LED20/840 L60W9 CD PSU	120 degree(s)	4000 K	80	148.57142857142858 lm/W
911401546542	SP571P LED12/840 L60W9 CD PSU	120 degree(s)	4000 K	80	156.55555555555554 lm/W
911401554743	SP570P LED60/840 L60W6 PSU Y	116 degree(s)	4000 K	>80	145 lm/W
911401555243	SP570P LED60/940 L60W6 PSD Y	116 degree(s)	4000 K	>90	144 lm/W
911401565842	RC570B LED20/840 L60W6 SD PSU	116 degree(s)	4000 K	>80	119 lm/W
911401566742	RC570B LED20/940 L60W6 SD PSD	116 degree(s)	4000 K	>90	111 lm/W
911401567042	RC570B LED20/840 L60W6 CD PSU	116 degree(s)	4000 K	>80	119 lm/W
911401567142	RC570B LED12/840 L60W6 CD PSU	116 degree(s)	4000 K	>80	125 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401568542	RC570B LED20/940 L60W6 CD PSD	116 degree(s)	4000 K	>90	111 lm/W
911401569142	RC570B LED20/9TW L60W6 SD PSD	116 degree(s)	Tunable White	>90	108 lm/W
911401569442	RC570B LED20/9TW L60W6 CD PSD	116 degree(s)	Tunable White	>90	108 lm/W
911401570742	RC570X LED20/940 L60W6 SD WIA	116 degree(s)	4000 K	>90	111 lm/W
911401571042	RC570X LED20/940 L60W6 CD WIA	116 degree(s)	4000 K	>90	111 lm/W
911401555643	SP570P LED45/840 L60W6 PSU HEX	116 degree(s)	4000 K	>80	141 lm/W
911401556043	SP570P LED45/840 L60W6 PSD HEX	116 degree(s)	4000 K	>80	136 lm/W
911401556443	SP570P LED45/940 L60W6 PSU HEX	116 degree(s)	4000 K	>90	141 lm/W
911401556843	SP570P LED45/940 L60W6 PSD HEX	116 degree(s)	4000 K	>90	136 lm/W
911401553143	SP570P LED40/840 L60W6 PSU T	116 degree(s)	4000 K	>80	133 lm/W
911401553243	SP570P LED40/840 L60W6 PSD T	116 degree(s)	4000 K	>80	128 lm/W
911401553643	SP570P LED40/940 L60W6 PSD T	116 degree(s)	4000 K	>90	128 lm/W

SlimBalance G3

Order Code	Full Product Name	Beam angle of light	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
		source			
911401547342	SP570P	120	4000 K	80	125.88235294117646
	LED20/840	degree(s)			lm/W
	L60W12 SD				
	PSU				
911401548242	SP570P	120	4000 K	90	114.85714285714286
	LED20/940	degree(s)			lm/W
	L60W12 SD				
	PSD				
911401548542	SM570C	120	4000 K	80	125.88235294117646
	LED20/840	degree(s)			lm/W
	L60W12 SD				
	PSU				
911401549142	SP570P	120	4000 K	80	125.88235294117646
	LED20/840	degree(s)			lm/W
	L60W12 CD				
	PSU				
911401549242	SP570P	120	4000 K	80	122.25490196078432
	LED12/840	degree(s)			lm/W

Order Code	Full Product Name	Beam angle of light	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
		source			
	L60W12 CD				
	PSU				
911401550642	SP570P	120	4000 K	90	114.85714285714286
	LED20/940	degree(s)			lm/W
	L60W12 CD				
	PSD				
911401550942	SM570C	120	4000 K	80	125.88235294117646
	LED20/840	degree(s)			lm/W
	L60W12 CD				
	PSU				
911401551542	SP571P	120	4000 K	80	151.42857142857142
	LED20/840	degree(s)			lm/W
	L60W12 SD				
	PSU				
911401552142	SP571P	120	4000 K	80	151.42857142857142
	LED20/840	degree(s)			lm/W
	L60W12 CD				
	PSU				

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Number of light		Optic type
			sources		
911401534842	SP570P LED50/840	5,344 lm	2		Beam angle
	L150W6 SD PSU				100°
911401534942	SP570P LED31/840 L150W6	3,250 lm	2		Beam angle
	SD PSU				100°
911401536242	SP570P LED50/940	4,580 lm	2		Beam angle
	L150W6 SD PSD				100°
911401536742	SM570C LED50/840	5,344 lm	2		Beam angle
	L150W6 SD PSU				100°
911401537342	SP570P LED50/840	5,340 lm	2		Beam angle
	L150W6 CD PSU				100°
911401537442	SP570P LED31/840 L150W6	3,210 lm	2		Beam angle
	CD PSU				100°
911401538642	SP570P LED50/940	5,020 lm	2		Beam angle
	L150W6 CD PSD				100°
911401539142	SM570C LED50/840	5,340 lm	2		Beam angle
	L150W6 CD PSU				100°
911401539542	SP571P LED50/840 L150W6	5,020 lm	2		Beam angle
	SD PSU				100°
911401540342	SP571P LED50/840 L150W6	5,020 lm	2		Beam angle
	CD PSU				100°
911401534642	SP570P LED40/840	4,200 lm	1		Beam angle
	L120W6 SD PSU				100°
911401534742	SP570P LED25/840 L120W6	2,600 lm	1		Beam angle
	SD PSU				100°

Order Code	Full Product Name	Luminous Flux	Number of light		Optic type
			sources		
911401536142	SP570P LED40/940	4,010 lm	1		Beam angle
	L120W6 SD PSD				100°
911401536542	SM570C LED40/840	4,200 lm	1		Beam angle
	L120W6 SD PSU				100°
911401537142	SP570P LED40/840	4,270 lm	1		Beam angle
	L120W6 CD PSU				100°
911401537242	SP570P LED25/840 L120W6	2,570 lm	1		Beam angle
	CD PSU				100°
911401538542	SP570P LED40/940	4,010 lm	1		Beam angle
	L120W6 CD PSD				100°
911401538942	SM570C LED40/840	4,270 lm	1		Beam angle
	L120W6 CD PSU				100°
911401539442	SP571P LED40/840 L120W6	4,020 lm	1		Beam angle
	SD PSU				100°
911401540142	SP571P LED40/840 L120W6	4,020 lm	1		Beam angle
	CD PSU				100°
911401534442	SP570P LED20/840 L60W6	2,080 lm	1		Beam angle
	SD PSU				100°
911401534542	SP570P LED12/840 L60W6	1,250 lm	1		Beam angle
	SD PSU				100°
911401536042	SP570P LED20/940 L60W6	1,950 lm	1		Beam angle
	SD PSD				100°
911401536342	SM570C LED20/840	2,080 lm	1		Beam angle
	L60W6 SD PSU				100°

SlimBalance G3

Order Code	Full Product Name	Luminous Flux	Number of light		Optic type
			sources		
911401536942	SP570P LED20/840 L60W6 CD PSU	2,080 lm	1		Beam angle 100°
911401537042	SP570P LED12/840 L60W6 CD PSU	1,250 lm	1		Beam angle 100°
911401538442	SP570P LED20/940 L60W6 CD PSD	1,950 lm	1		Beam angle 100°
911401538742	SM570C LED20/840 L60W6 CD PSU	2,080 lm	1		Beam angle 100°
911401539342	SP571P LED20/840 L60W6 SD PSU	2,070 lm	1		Beam angle 100°
911401539942	SP571P LED20/840 L60W6 CD PSU	2,070 lm	1		Beam angle 100°
911401540042	SP571P LED12/840 L60W6 CD PSU	1,400 lm	1		Beam angle 100°
911401568942	RC570B LED40/840 L120W12 SD PSU	3,980 lm	-	-	
911401569842	RC570B LED40/940 L120W12 SD PSD	3,740 lm	-	-	
911401570242	RC570B LED40/840 L120W12 CD PSU	3,980 lm	-	-	
911401570342	RC570B LED25/840 L120W12 CD PSU	2,500 lm	-	-	
911401571342	RC570X LED40/940 L120W12 SD WIA	3,650 lm	-	-	
911401571442	RC570X LED40/940 L120W12 CD WIA	3,650 lm	-	-	
911401571642	RC570B LED40/940 L120W12 CD PSD	3,740 lm	-	-	
911401540942	SP570P LED40/840 L120W9 SD PSU	4,200 lm	1		Beam angle 100°
911401541042	SP570P LED25/840 L120W9 SD PSU	2,650 lm	1		Beam angle 100°
911401542342	SP570P LED40/940 L120W9 SD PSD	4,010 lm	1		Beam angle 100°
911401542742	SM570C LED40/840 L120W9 SD PSU	4,200 lm	1		Beam angle 100°
911401543342	SP570P LED40/840 L120W9 CD PSU	4,200 lm	1		Beam angle 100°
911401543442	SP570P LED25/840 L120W9 CD PSU	2,520 lm	1		Beam angle 100°
911401544742	SP570P LED40/940 L120W9 CD PSD	3,940 lm	1		Beam angle 100°
911401545142	SM570C LED40/840 L120W9 CD PSU	4,200 lm	1		Beam angle 100°
911401545742	SP571P LED40/840 L120W9 SD PSU	4,030 lm	1		Beam angle 100°
911401546642	SP571P LED40/840 L120W9 CD PSU	4,030 lm	1		Beam angle 100°
911401547542	SP570P LED50/840 L150W12 SD PSU	4,970 lm	4		Beam angle 100°

Order Code	Full Product Name	Luminous Flux	Number of light		Optic type
			sources		
911401548442	SP570P LED50/940 L150W12 SD PSD	4,680 lm	4		Beam angle 100°
911401548942	SM570C LED50/840 L150W12 SD PSU	4,970 lm	4		Beam angle 100°
911401549542	SP570P LED50/840 L150W12 CD PSU	4,970 lm	4		Beam angle 100°
911401549642	SP570P LED31/840 L150W12 CD PSU	3,125 lm	4		Beam angle 100°
911401550842	SP570P LED50/940 L150W12 CD PSD	4,680 lm	4		Beam angle 100°
911401551342	SM570C LED50/840 L150W12 CD PSU	4,970 lm	4		Beam angle 100°
911401551742	SP571P LED50/840 L150W12 SD PSU	4,730 lm	4		Beam angle 100°
911401552342	SP571P LED50/840 L150W12 CD PSU	4,730 lm	4		Beam angle 100°
911401572042	RC570B LED40/940 L60W6 PSD LC	3,880 lm	-	-	
911401574042	RC570B LED40/840 L60W6 PSU LC	4,130 lm	-	-	
911401566042	RC570B LED50/840 L150W6 SD PSU	5,344 lm	-	-	
911401566942	RC570B LED50/940 L150W6 SD PSD	4,580 lm	-	-	
911401567442	RC570B LED50/840 L150W6 CD PSU	5,344 lm	-	-	
911401567542	RC570B LED31/840 L150W6 CD PSU	3,250 lm	-	-	
911401568742	RC570B LED50/940 L150W6 CD PSD	4,580 lm	-	-	
911401569342	RC570B LED50/9TW L150W6 SD PSD	5,020 lm	-	-	
911401569642	RC570B LED50/9TW L150W6 CD PSD	5,020 lm	-	-	
911401570942	RC570X LED50/940 L150W6 SD WIA	5,020 lm	-	-	
911401571242	RC570X LED50/940 L150W6 CD WIA	5,020 lm	-	-	
911401553943	SP570P LED40/840 L60W6 PSU X	4,133 lm	-	-	
911401554043	SP570P LED40/840 L60W6 PSD X	4,133 lm	-	-	
911401554443	SP570P LED40/940 L60W6 PSD X	4,133 lm	-	-	
911401547442	SP570P LED40/840 L120W12 SD PSU	3,980 lm	2		Beam angle 100°
911401548342	SP570P LED40/940 L120W12 SD PSD	3,740 lm	2		Beam angle 100°
911401548742	SM570C LED40/840 L120W12 SD PSU	3,980 lm	2		Beam angle 100°

SlimBalance G3

Order Code	Full Product Name	Luminous Flux	Number of light		Optic type
			sources		
911401549342	SP570P LED40/840 L120W12 CD PSU	3,980 lm	2		Beam angle 100°
911401549442	SP570P LED25/840 L120W12 CD PSU	2,500 lm	2		Beam angle 100°
911401550742	SP570P LED40/940 L120W12 CD PSD	3,740 lm	2		Beam angle 100°
911401551142	SM570C LED40/840 L120W12 CD PSU	3,980 lm	2		Beam angle 100°
911401551642	SP571P LED40/840 L120W12 SD PSU	3,720 lm	2		Beam angle 100°
911401552242	SP571P LED40/840 L120W12 CD PSU	3,720 lm	2		Beam angle 100°
911401569042	RC570B LED50/840 L150W12 SD PSU	4,970 lm	-	-	
911401569942	RC570B LED50/940 L150W12 SD PSD	4,680 lm	-	-	
911401570442	RC570B LED50/840 L150W12 CD PSU	4,970 lm	-	-	
911401570542	RC570B LED31/840 L150W12 CD PSU	3,125 lm	-	-	
911401571742	RC570B LED50/940 L150W12 CD PSD	4,680 lm	-	-	
911401541142	SP570P LED50/840 L150W9 SD PSU	4,960 lm	2		Beam angle 100°
911401541242	SP570P LED31/840 L150W9 SD PSU	3,310 lm	2		Beam angle 100°
911401542442	SP570P LED50/940 L150W9 SD PSD	4,660 lm	2		Beam angle 100°
911401542942	SM570C LED50/840 L150W9 SD PSU	4,960 lm	2		Beam angle 100°
911401543542	SP570P LED50/840 L150W9 CD PSU	5,240 lm	2		Beam angle 100°
911401543642	SP570P LED31/840 L150W9 CD PSU	3,150 lm	2		Beam angle 100°
911401544842	SP570P LED50/940 L150W9 CD PSD	4,932 lm	2		Beam angle 100°
911401545342	SM570C LED50/840 L150W9 CD PSU	5,240 lm	2		Beam angle 100°
911401545942	SP571P LED50/840 L150W9 SD PSU	5,130 lm	2		Beam angle 100°
911401546842	SP571P LED50/840 L150W9 CD PSU	5,130 lm	2		Beam angle 100°
911401565942	RC570B LED40/840 L120W6 SD PSU	4,400 lm	-	-	
911401566842	RC570B LED40/940 L120W6 SD PSD	4,136 lm	-	-	
911401567242	RC570B LED40/840 L120W6 CD PSU	4,400 lm	-	-	
911401567342	RC570B LED25/840 L120W6 CD PSU	2,600 lm	-	-	

Order Code	Full Product Name	Luminous Flux	Number of light		Optic type
			sources		
911401568642	RC570B LED40/940 L120W6 CD PSD	4,136 lm	-	-	
911401569242	RC570B LED40/9TW L120W6 SD PSD	4,010 lm	-	-	
911401569542	RC570B LED40/9TW L120W6 CD PSD	4,010 lm	-	-	
911401570842	RC570X LED40/940 L120W6 SD WIA	4,010 lm	-	-	
911401571142	RC570X LED40/940 L120W6 CD WIA	4,010 lm	-	-	
911401540742	SP570P LED20/840 L60W9 SD PSU	2,120 lm	1		Beam angle 100°
911401540842	SP570P LED12/840 L60W9 SD PSU	1,280 lm	1		Beam angle 100°
911401542242	SP570P LED20/940 L60W9 SD PSD	2,000 lm	1		Beam angle 100°
911401542542	SM570C LED20/840 L60W9 SD PSU	2,120 lm	1		Beam angle 100°
911401543142	SP570P LED20/840 L60W9 CD PSU	2,120 lm	1		Beam angle 100°
911401543242	SP570P LED12/840 L60W9 CD PSU	1,280 lm	1		Beam angle 100°
911401544642	SP570P LED20/940 L60W9 CD PSD	2,000 lm	1		Beam angle 100°
911401544942	SM570C LED20/840 L60W9 CD PSU	2,120 lm	1		Beam angle 100°
911401545542	SP571P LED20/840 L60W9 SD PSU	2,080 lm	1		Beam angle 100°
911401545642	SP571P LED12/840 L60W9 SD PSU	1,409 lm	1		Beam angle 100°
911401546442	SP571P LED20/840 L60W9 CD PSU	2,080 lm	1		Beam angle 100°
911401546542	SP571P LED12/840 L60W9 CD PSU	1,409 lm	1		Beam angle 100°
911401554743	SP570P LED60/840 L60W6 PSU Y	6,000 lm	-	-	
911401555243	SP570P LED60/940 L60W6 PSD Y	6,000 lm	-	-	
911401565842	RC570B LED20/840 L60W6 SD PSU	2,080 lm	-	-	
911401566742	RC570B LED20/940 L60W6 SD PSD	1,950 lm	-	-	
911401567042	RC570B LED20/840 L60W6 CD PSU	2,080 lm	-	-	
911401567142	RC570B LED12/840 L60W6 CD PSU	1,250 lm	-	-	
911401568542	RC570B LED20/940 L60W6 CD PSD	1,950 lm	-	-	
911401569142	RC570B LED20/9TW L60W6 SD PSD	1,950 lm	-	-	

SlimBalance G3

Order Code	Full Product Name	Luminous Flux	Number of light	
			sources	Optic type
911401569442	RC570B LED20/9TW L60W6 CD PSD	1,950 lm	-	-
911401570742	RC570X LED20/940 L60W6 SD WIA	1,950 lm	-	-
911401571042	RC570X LED20/940 L60W6 CD WIA	1,950 lm	-	-
911401555643	SP570P LED45/840 L60W6 PSU HEX	4,500 lm	-	-
911401556043	SP570P LED45/840 L60W6 PSD HEX	4,500 lm	-	-
911401556443	SP570P LED45/940 L60W6 PSU HEX	4,500 lm	-	-
911401556843	SP570P LED45/940 L60W6 PSD HEX	4,500 lm	-	-
911401553143	SP570P LED40/840 L60W6 PSU T	4,133 lm	-	-
911401553243	SP570P LED40/840 L60W6 PSD T	4,133 lm	-	-
911401553643	SP570P LED40/940 L60W6 PSD T	4,133 lm	-	-

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Power		Suitable for random switching
			Consumption		
911401534842	SP570P LED50/840 L150W6 SD PSU	220 to 240 V	40.5 W		No
911401534942	SP570P LED31/840 L150W6 SD PSU	220 to 240 V	23.5 W		No
911401536242	SP570P LED50/940 L150W6 SD PSD	220 to 240 V	41 W		No
911401536742	SM570C LED50/840 L150W6 SD PSU	220 to 240 V	40.5 W		No
911401537342	SP570P LED50/840 L150W6 CD PSU	220 to 240 V	40.5 W		No
911401537442	SP570P LED31/840 L150W6 CD PSU	220 to 240 V	23.5 W		No
911401538642	SP570P LED50/940 L150W6 CD PSD	220 to 240 V	41 W		No
911401539142	SM570C LED50/840 L150W6 CD PSU	220 to 240 V	40.5 W		No
911401539542	SP571P LED50/840 L150W6 SD PSU	220 to 240 V	37.5 W		No
911401540342	SP571P LED50/840 L150W6 CD PSU	220 to 240 V	37.5 W		No
911401534642	SP570P LED40/840 L120W6 SD PSU	220 to 240 V	32 W		No
911401534742	SP570P LED25/840 L120W6 SD PSU	220 to 240 V	18.5 W		No

Order Code	Full Product Name	Luminous Flux	Number of light	
			sources	Optic type
911401547342	SP570P LED20/840 L60W12 SD PSU	2,140 lm	2	Beam angle 100°
911401548242	SP570P LED20/940 L60W12 SD PSD	2,010 lm	2	Beam angle 100°
911401548542	SM570C LED20/840 L60W12 SD PSU	2,140 lm	2	Beam angle 100°
911401549142	SP570P LED20/840 L60W12 CD PSU	2,140 lm	2	Beam angle 100°
911401549242	SP570P LED12/840 L60W12 CD PSU	1,247 lm	2	Beam angle 100°
911401550642	SP570P LED20/940 L60W12 CD PSD	2,010 lm	2	Beam angle 100°
911401550942	SM570C LED20/840 L60W12 CD PSU	2,140 lm	2	Beam angle 100°
911401551542	SP571P LED20/840 L60W12 SD PSU	2,120 lm	2	Beam angle 100°
911401552142	SP571P LED20/840 L60W12 CD PSU	2,120 lm	2	Beam angle 100°

Order Code	Full Product Name	Input Voltage	Power		Suitable for random switching
			Consumption		
911401536142	SP570P LED40/940 L120W6 SD PSD	220 to 240 V	33.5 W		No
911401536542	SM570C LED40/840 L120W6 SD PSU	220 to 240 V	32 W		No
911401537142	SP570P LED40/840 L120W6 CD PSU	220 to 240 V	32 W		No
911401537242	SP570P LED25/840 L120W6 CD PSU	220 to 240 V	18.5 W		No
911401538542	SP570P LED40/940 L120W6 CD PSD	220 to 240 V	33.5 W		No
911401538942	SM570C LED40/840 L120W6 CD PSU	220 to 240 V	32 W		No
911401539442	SP571P LED40/840 L120W6 SD PSU	220 to 240 V	29.5 W		No
911401540142	SP571P LED40/840 L120W6 CD PSU	220 to 240 V	29.5 W		No
911401534442	SP570P LED20/840 L60W6 SD PSU	220 to 240 V	17.5 W		No
911401534542	SP570P LED12/840 L60W6 SD PSU	220 to 240 V	10 W		No
911401536042	SP570P LED20/940 L60W6 SD PSD	220 to 240 V	17.5 W		No
911401536342	SM570C LED20/840 L60W6 SD PSU	220 to 240 V	17.5 W		No

Order Code	Full Product Name	Input Voltage	Power	Suitable for random switching
			Consumption	
911401536942	SP570P LED20/840 L60W6 CD PSU	220 to 240 V	17.5 W	No
911401537042	SP570P LED12/840 L60W6 CD PSU	220 to 240 V	10 W	No
911401538442	SP570P LED20/940 L60W6 CD PSD	220 to 240 V	17.5 W	No
911401538742	SM570C LED20/840 L60W6 CD PSU	220 to 240 V	17.5 W	No
911401539342	SP571P LED20/840 L60W6 SD PSU	220 to 240 V	14 W	No
911401539942	SP571P LED20/840 L60W6 CD PSU	220 to 240 V	14 W	No
911401540042	SP571P LED12/840 L60W6 CD PSU	220 to 240 V	9 W	No
911401568942	RC570B LED40/840 L120W12 SD PSU	220-240 V	27 W	-
911401569842	RC570B LED40/940 L120W12 SD PSD	220-240 V	28.5 W	-
911401570242	RC570B LED40/840 L120W12 CD PSU	220-240 V	27 W	-
911401570342	RC570B LED25/840 L120W12 CD PSU	220-240 V	17.5 W	-
911401571342	RC570X LED40/940 L120W12 SD WIA	220-240 V	27 W	-
911401571442	RC570X LED40/940 L120W12 CD WIA	220-240 V	27 W	-
911401571642	RC570B LED40/940 L120W12 CD PSD	220-240 V	28.5 W	-
911401540942	SP570P LED40/840 L120W9 SD PSU	220 to 240 V	32 W	No
911401541042	SP570P LED25/840 L120W9 SD PSU	220 to 240 V	18.5 W	No
911401542342	SP570P LED40/940 L120W9 SD PSD	220 to 240 V	33.5 W	No
911401542742	SM570C LED40/840 L120W9 SD PSU	220 to 240 V	32 W	No
911401543342	SP570P LED40/840 L120W9 CD PSU	220 to 240 V	32 W	No
911401543442	SP570P LED25/840 L120W9 CD PSU	220 to 240 V	18.5 W	No
911401544742	SP570P LED40/940 L120W9 CD PSD	220 to 240 V	33.5 W	No
911401545142	SM570C LED40/840 L120W9 CD PSU	220 to 240 V	32 W	No
911401545742	SP571P LED40/840 L120W9 SD PSU	220 to 240 V	29.5 W	No
911401546642	SP571P LED40/840 L120W9 CD PSU	220 to 240 V	29.5 W	No
911401547542	SP570P LED50/840 L150W12 SD PSU	220 to 240 V	34 W	No

Order Code	Full Product Name	Input Voltage	Power	Suitable for random switching
			Consumption	
911401548442	SP570P LED50/940 L150W12 SD PSD	220 to 240 V	34 W	No
911401548942	SM570C LED50/840 L150W12 SD PSU	220 to 240 V	34 W	No
911401549542	SP570P LED50/840 L150W12 CD PSU	220 to 240 V	34 W	No
911401549642	SP570P LED31/840 L150W12 CD PSU	220 to 240 V	21 W	No
911401550842	SP570P LED50/940 L150W12 CD PSD	220 to 240 V	34 W	No
911401551342	SM570C LED50/840 L150W12 CD PSU	220 to 240 V	34 W	No
911401551742	SP571P LED50/840 L150W12 SD PSU	220 to 240 V	33 W	No
911401552342	SP571P LED50/840 L150W12 CD PSU	220 to 240 V	33 W	No
911401572042	RC570B LED40/940 L60W6 PSD LC	220-240 V	32.5 W	-
911401574042	RC570B LED40/840 L60W6 PSU LC	220-240 V	31 W	-
911401566042	RC570B LED50/840 L150W6 SD PSU	220-240 V	40.5 W	-
911401566942	RC570B LED50/940 L150W6 SD PSD	220-240 V	41.5 W	-
911401567442	RC570B LED50/840 L150W6 CD PSU	220-240 V	40.5 W	-
911401567542	RC570B LED31/840 L150W6 CD PSU	220-240 V	23.5 W	-
911401568742	RC570B LED50/940 L150W6 CD PSD	220-240 V	41.5 W	-
911401569342	RC570B LED50/9TW L150W6 SD PSD	220-240 V	41 W	-
911401569642	RC570B LED50/9TW L150W6 CD PSD	220-240 V	41 W	-
911401570942	RC570X LED50/940 L150W6 SD WIA	220-240 V	40 W	-
911401571242	RC570X LED50/940 L150W6 CD WIA	220-240 V	40 W	-
911401553943	SP570P LED40/840 L60W6 PSU X	220-240 V	31 W	-
911401554043	SP570P LED40/840 L60W6 PSD X	220-240 V	32.4 W	-
911401554443	SP570P LED40/940 L60W6 PSD X	220-240 V	32.4 W	-
911401547442	SP570P LED40/840 L120W12 SD PSU	220 to 240 V	27 W	No
911401548342	SP570P LED40/940 L120W12 SD PSD	220 to 240 V	28.5 W	No
911401548742	SM570C LED40/840 L120W12 SD PSU	220 to 240 V	27 W	No

SlimBalance G3

Order Code	Full Product Name	Power		Suitable for random switching
		Input Voltage	Consumption	
911401549342	SP570P LED40/840 L120W12 CD PSU	220 to 240 V	27 W	No
911401549442	SP570P LED25/840 L120W12 CD PSU	220 to 240 V	17.5 W	No
911401550742	SP570P LED40/940 L120W12 CD PSD	220 to 240 V	28.5 W	No
911401551142	SM570C LED40/840 L120W12 CD PSU	220 to 240 V	27 W	No
911401551642	SP571P LED40/840 L120W12 SD PSU	220 to 240 V	26.5 W	No
911401552242	SP571P LED40/840 L120W12 CD PSU	220 to 240 V	26.5 W	No
911401569042	RC570B LED50/840 L150W12 SD PSU	220-240 V	34 W	-
911401569942	RC570B LED50/940 L150W12 SD PSD	220-240 V	34 W	-
911401570442	RC570B LED50/840 L150W12 CD PSU	220-240 V	34 W	-
911401570542	RC570B LED31/840 L150W12 CD PSU	220-240 V	21 W	-
911401571742	RC570B LED50/940 L150W12 CD PSD	220-240 V	34 W	-
911401541142	SP570P LED50/840 L150W9 SD PSU	220 to 240 V	40.5 W	No
911401541242	SP570P LED31/840 L150W9 SD PSU	220 to 240 V	23.5 W	No
911401542442	SP570P LED50/940 L150W9 SD PSD	220 to 240 V	41 W	No
911401542942	SM570C LED50/840 L150W9 SD PSU	220 to 240 V	40 W	No
911401543542	SP570P LED50/840 L150W9 CD PSU	220 to 240 V	40.5 W	No
911401543642	SP570P LED31/840 L150W9 CD PSU	220 to 240 V	23.5 W	No
911401544842	SP570P LED50/940 L150W9 CD PSD	220 to 240 V	41 W	No
911401545342	SM570C LED50/840 L150W9 CD PSU	220 to 240 V	40.5 W	No
911401545942	SP571P LED50/840 L150W9 SD PSU	220 to 240 V	37.5 W	No
911401546842	SP571P LED50/840 L150W9 CD PSU	220 to 240 V	37.5 W	No
911401565942	RC570B LED40/840 L120W6 SD PSU	220-240 V	32.5 W	-
911401566842	RC570B LED40/940 L120W6 SD PSD	220-240 V	34 W	-
911401567242	RC570B LED40/840 L120W6 CD PSU	220-240 V	32.5 W	-
911401567342	RC570B LED25/840 L120W6 CD PSU	220-240 V	18.5 W	-

Order Code	Full Product Name	Power		Suitable for random switching
		Input Voltage	Consumption	
911401568642	RC570B LED40/940 L120W6 CD PSD	220-240 V	34 W	-
911401569242	RC570B LED40/9TW L120W6 SD PSD	220-240 V	33.5 W	-
911401569542	RC570B LED40/9TW L120W6 CD PSD	220-240 V	33.5 W	-
911401570842	RC570X LED40/940 L120W6 SD WIA	220-240 V	32 W	-
911401571142	RC570X LED40/940 L120W6 CD WIA	220-240 V	32 W	-
911401540742	SP570P LED20/840 L60W9 SD PSU	220 to 240 V	17.5 W	No
911401540842	SP570P LED12/840 L60W9 SD PSU	220 to 240 V	10 W	No
911401542242	SP570P LED20/940 L60W9 SD PSD	220 to 240 V	17.5 W	No
911401542542	SM570C LED20/840 L60W9 SD PSU	220 to 240 V	17.5 W	No
911401543142	SP570P LED20/840 L60W9 CD PSU	220 to 240 V	17.5 W	No
911401543242	SP570P LED12/840 L60W9 CD PSU	220 to 240 V	10 W	No
911401544642	SP570P LED20/940 L60W9 CD PSD	220 to 240 V	17.5 W	No
911401544942	SM570C LED20/840 L60W9 CD PSU	220 to 240 V	17.5 W	No
911401545542	SP571P LED20/840 L60W9 SD PSU	220 to 240 V	14 W	No
911401545642	SP571P LED12/840 L60W9 SD PSU	220 to 240 V	9 W	No
911401546442	SP571P LED20/840 L60W9 CD PSU	220 to 240 V	14 W	No
911401546542	SP571P LED12/840 L60W9 CD PSU	220 to 240 V	9 W	No
911401554743	SP570P LED60/840 L60W6 PSU Y	220-240 V	42 W	-
911401555243	SP570P LED60/940 L60W6 PSD Y	220-240 V	44.5 W	-
911401565842	RC570B LED20/840 L60W6 SD PSU	220-240 V	17.5 W	-
911401566742	RC570B LED20/940 L60W6 SD PSD	220-240 V	17.5 W	-
911401567042	RC570B LED20/840 L60W6 CD PSU	220-240 V	17.5 W	-
911401567142	RC570B LED12/840 L60W6 CD PSU	220-240 V	10 W	-
911401568542	RC570B LED20/940 L60W6 CD PSD	220-240 V	17.5 W	-
911401569142	RC570B LED20/9TW L60W6 SD PSD	220-240 V	18 W	-

SlimBalance G3

Order Code	Full Product Name	Power		Suitable for random switching
		Input Voltage	Consumption	
911401569442	RC570B LED20/9TW L60W6 CD PSD	220-240 V	18 W	-
911401570742	RC570X LED20/940 L60W6 SD WIA	220-240 V	17.5 W	-
911401571042	RC570X LED20/940 L60W6 CD WIA	220-240 V	17.5 W	-
911401555643	SP570P LED45/840 L60W6 PSU HEX	220-240 V	32 W	-
911401556043	SP570P LED45/840 L60W6 PSD HEX	220-240 V	32 W	-
911401556443	SP570P LED45/940 L60W6 PSU HEX	220-240 V	32 W	-
911401556843	SP570P LED45/940 L60W6 PSD HEX	220-240 V	32 W	-
911401553143	SP570P LED40/840 L60W6 PSU T	220-240 V	31 W	-
911401553243	SP570P LED40/840 L60W6 PSD T	220-240 V	32.4 W	-
911401553643	SP570P LED40/940 L60W6 PSD T	220-240 V	32.4 W	-

Order Code	Full Product Name	Power		Suitable for random switching
		Input Voltage	Consumption	
911401547342	SP570P LED20/840 L60W12 SD PSU	220 to 240 V	17 W	No
911401548242	SP570P LED20/940 L60W12 SD PSD	220 to 240 V	17.5 W	No
911401548542	SM570C LED20/840 L60W12 SD PSU	220 to 240 V	17 W	No
911401549142	SP570P LED20/840 L60W12 CD PSU	220 to 240 V	17 W	No
911401549242	SP570P LED12/840 L60W12 CD PSU	220 to 240 V	10.2 W	No
911401550642	SP570P LED20/940 L60W12 CD PSD	220 to 240 V	17.5 W	No
911401550942	SM570C LED20/840 L60W12 CD PSU	220 to 240 V	17 W	No
911401551542	SP571P LED20/840 L60W12 SD PSU	220 to 240 V	14 W	No
911401552142	SP571P LED20/840 L60W12 CD PSU	220 to 240 V	14 W	No

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
911401534842	SP570P LED50/840 L150W6 SD PSU	No	Not applicable
911401534942	SP570P LED31/840 L150W6 SD PSU	No	Not applicable
911401536242	SP570P LED50/940 L150W6 SD PSD	DALI	1%
911401536742	SM570C LED50/840 L150W6 SD PSU	No	Not applicable
911401537342	SP570P LED50/840 L150W6 CD PSU	No	Not applicable
911401537442	SP570P LED31/840 L150W6 CD PSU	No	Not applicable
911401538642	SP570P LED50/940 L150W6 CD PSD	DALI	1%
911401539142	SM570C LED50/840 L150W6 CD PSU	No	Not applicable
911401539542	SP571P LED50/840 L150W6 SD PSU	No	Not applicable
911401540342	SP571P LED50/840 L150W6 CD PSU	No	Not applicable
911401534642	SP570P LED40/840 L120W6 SD PSU	No	Not applicable
911401534742	SP570P LED25/840 L120W6 SD PSU	No	Not applicable
911401536142	SP570P LED40/940 L120W6 SD PSD	DALI	1%
911401536542	SM570C LED40/840 L120W6 SD PSU	No	Not applicable
911401537142	SP570P LED40/840 L120W6 CD PSU	No	Not applicable
911401537242	SP570P LED25/840 L120W6 CD PSU	No	Not applicable
911401538542	SP570P LED40/940 L120W6 CD PSD	DALI	1%
911401538942	SM570C LED40/840 L120W6 CD PSU	No	Not applicable
911401539442	SP571P LED40/840 L120W6 SD PSU	No	Not applicable
911401540142	SP571P LED40/840 L120W6 CD PSU	No	Not applicable
911401534442	SP570P LED20/840 L60W6 SD PSU	No	Not applicable
911401534542	SP570P LED12/840 L60W6 SD PSU	No	Not applicable
911401536042	SP570P LED20/940 L60W6 SD PSD	DALI	3%
911401536342	SM570C LED20/840 L60W6 SD PSU	No	Not applicable
911401536942	SP570P LED20/840 L60W6 CD PSU	No	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
911401537042	SP570P LED12/840 L60W6 CD PSU	No	Not applicable
911401538442	SP570P LED20/940 L60W6 CD PSD	DALI	3%
911401538742	SM570C LED20/840 L60W6 CD PSU	No	Not applicable
911401539342	SP571P LED20/840 L60W6 SD PSU	No	Not applicable
911401539942	SP571P LED20/840 L60W6 CD PSU	No	Not applicable
911401540042	SP571P LED12/840 L60W6 CD PSU	No	Not applicable
911401568942	RC570B LED40/840 L120W12 SD PSU	-	-
911401569842	RC570B LED40/940 L120W12 SD PSD	DALI	-
911401570242	RC570B LED40/840 L120W12 CD PSU	-	-
911401570342	RC570B LED25/840 L120W12 CD PSU	-	-
911401571342	RC570X LED40/940 L120W12 SD WIA	Wireless Dim	-
911401571442	RC570X LED40/940 L120W12 CD WIA	Wireless Dim	-
911401571642	RC570B LED40/940 L120W12 CD PSD	DALI	-
911401540942	SP570P LED40/840 L120W9 SD PSU	No	Not applicable
911401541042	SP570P LED25/840 L120W9 SD PSU	No	Not applicable
911401542342	SP570P LED40/940 L120W9 SD PSD	DMX	1%
911401542742	SM570C LED40/840 L120W9 SD PSU	No	Not applicable
911401543342	SP570P LED40/840 L120W9 CD PSU	No	Not applicable
911401543442	SP570P LED25/840 L120W9 CD PSU	No	Not applicable
911401544742	SP570P LED40/940 L120W9 CD PSD	DALI	1%
911401545142	SM570C LED40/840 L120W9 CD PSU	No	Not applicable
911401545742	SP571P LED40/840 L120W9 SD PSU	No	Not applicable
911401546642	SP571P LED40/840 L120W9 CD PSU	No	Not applicable
911401547542	SP570P LED50/840 L150W12 SD PSU	No	Not applicable
911401548442	SP570P LED50/940 L150W12 SD PSD	DALI	1%

Order Code	Full Product Name	Dimmable	Maximum dim level
911401548942	SM570C LED50/840 L150W12 SD PSU	No	Not applicable
911401549542	SP570P LED50/840 L150W12 CD PSU	No	Not applicable
911401549642	SP570P LED31/840 L150W12 CD PSU	No	Not applicable
911401550842	SP570P LED50/940 L150W12 CD PSD	DALI	1%
911401551342	SM570C LED50/840 L150W12 CD PSU	No	Not applicable
911401551742	SP571P LED50/840 L150W12 SD PSU	No	Not applicable
911401552342	SP571P LED50/840 L150W12 CD PSU	No	Not applicable
911401572042	RC570B LED40/940 L60W6 PSD LC	DALI	-
911401574042	RC570B LED40/840 L60W6 PSU LC	-	-
911401566042	RC570B LED50/840 L150W6 SD PSU	-	-
911401566942	RC570B LED50/940 L150W6 SD PSD	DALI	-
911401567442	RC570B LED50/840 L150W6 CD PSU	-	-
911401567542	RC570B LED31/840 L150W6 CD PSU	-	-
911401568742	RC570B LED50/940 L150W6 CD PSD	DALI	-
911401569342	RC570B LED50/9TW L150W6 SD PSD	DALI	-
911401569642	RC570B LED50/9TW L150W6 CD PSD	DALI	-
911401570942	RC570X LED50/940 L150W6 SD WIA	Wireless Dim	-
911401571242	RC570X LED50/940 L150W6 CD WIA	Wireless Dim	-
911401553943	SP570P LED40/840 L60W6 PSU X	-	-
911401554043	SP570P LED40/840 L60W6 PSD X	DALI	-
911401554443	SP570P LED40/940 L60W6 PSD X	DALI	-
911401547442	SP570P LED40/840 L120W12 SD PSU	No	Not applicable
911401548342	SP570P LED40/940 L120W12 SD PSD	DALI	1%
911401548742	SM570C LED40/840 L120W12 SD PSU	No	Not applicable
911401549342	SP570P LED40/840 L120W12 CD PSU	No	Not applicable
911401549442	SP570P LED25/840 L120W12 CD PSU	No	Not applicable
911401550742	SP570P LED40/940 L120W12 CD PSD	DALI	1%
911401551142	SM570C LED40/840 L120W12 CD PSU	No	Not applicable
911401551642	SP571P LED40/840 L120W12 SD PSU	No	Not applicable
911401552242	SP571P LED40/840 L120W12 CD PSU	No	Not applicable
911401569042	RC570B LED50/840 L150W12 SD PSU	-	-
911401569942	RC570B LED50/940 L150W12 SD PSD	DALI	-
911401570442	RC570B LED50/840 L150W12 CD PSU	-	-
911401570542	RC570B LED31/840 L150W12 CD PSU	-	-
911401571742	RC570B LED50/940 L150W12 CD PSD	DALI	-
911401541142	SP570P LED50/840 L150W9 SD PSU	No	Not applicable
911401541242	SP570P LED31/840 L150W9 SD PSU	No	Not applicable
911401542442	SP570P LED50/940 L150W9 SD PSD	DMX	1%
911401542942	SM570C LED50/840 L150W9 SD PSU	No	Not applicable
911401543542	SP570P LED50/840 L150W9 CD PSU	No	Not applicable
911401543642	SP570P LED31/840 L150W9 CD PSU	No	Not applicable
911401544842	SP570P LED50/940 L150W9 CD PSD	DALI	1%
911401545342	SM570C LED50/840 L150W9 CD PSU	No	Not applicable
911401545942	SP571P LED50/840 L150W9 SD PSU	No	Not applicable
911401546842	SP571P LED50/840 L150W9 CD PSU	No	Not applicable
911401565942	RC570B LED40/840 L120W6 SD PSU	-	-
911401566842	RC570B LED40/940 L120W6 SD PSD	DALI	-

Order Code	Full Product Name	Dimmable	Maximum dim level
911401567242	RC570B LED40/840 L120W6 CD PSU	-	-
911401567342	RC570B LED25/840 L120W6 CD PSU	-	-
911401568642	RC570B LED40/940 L120W6 CD PSD	DALI	-
911401569242	RC570B LED40/9TW L120W6 SD PSD	DALI	-
911401569542	RC570B LED40/9TW L120W6 CD PSD	DALI	-
911401570842	RC570X LED40/940 L120W6 SD WIA	Wireless Dim	-
911401571142	RC570X LED40/940 L120W6 CD WIA	Wireless Dim	-
911401540742	SP570P LED20/840 L60W9 SD PSU	No	Not applicable
911401540842	SP570P LED12/840 L60W9 SD PSU	No	Not applicable
911401542242	SP570P LED20/940 L60W9 SD PSD	DMX	3%
911401542542	SM570C LED20/840 L60W9 SD PSU	No	Not applicable
911401543142	SP570P LED20/840 L60W9 CD PSU	No	Not applicable
911401543242	SP570P LED12/840 L60W9 CD PSU	No	Not applicable
911401544642	SP570P LED20/940 L60W9 CD PSD	DALI	3%
911401544942	SM570C LED20/840 L60W9 CD PSU	No	Not applicable
911401545542	SP571P LED20/840 L60W9 SD PSU	No	Not applicable
911401545642	SP571P LED12/840 L60W9 SD PSU	No	Not applicable
911401546442	SP571P LED20/840 L60W9 CD PSU	No	Not applicable
911401546542	SP571P LED12/840 L60W9 CD PSU	No	Not applicable
911401554743	SP570P LED60/840 L60W6 PSU Y	-	-
911401555243	SP570P LED60/940 L60W6 PSD Y	DALI	-
911401565842	RC570B LED20/840 L60W6 SD PSU	-	-
911401566742	RC570B LED20/940 L60W6 SD PSD	DALI	-
911401567042	RC570B LED20/840 L60W6 CD PSU	-	-
911401567142	RC570B LED12/840 L60W6 CD PSU	-	-
911401568542	RC570B LED20/940 L60W6 CD PSD	DALI	-
911401569142	RC570B LED20/9TW L60W6 SD PSD	DALI	-
911401569442	RC570B LED20/9TW L60W6 CD PSD	DALI	-
911401570742	RC570X LED20/940 L60W6 SD WIA	Wireless Dim	-
911401571042	RC570X LED20/940 L60W6 CD WIA	Wireless Dim	-
911401555643	SP570P LED45/840 L60W6 PSU HEX	-	-
911401556043	SP570P LED45/840 L60W6 PSD HEX	DALI	-
911401556443	SP570P LED45/940 L60W6 PSU HEX	-	-
911401556843	SP570P LED45/940 L60W6 PSD HEX	DALI	-
911401553143	SP570P LED40/840 L60W6 PSU T	-	-
911401553243	SP570P LED40/840 L60W6 PSD T	DALI	-
911401553643	SP570P LED40/940 L60W6 PSD T	DALI	-
911401547342	SP570P LED20/840 L60W12 SD PSU	No	Not applicable
911401548242	SP570P LED20/940 L60W12 SD PSD	DALI	3%
911401548542	SM570C LED20/840 L60W12 SD PSU	No	Not applicable
911401549142	SP570P LED20/840 L60W12 CD PSU	No	Not applicable
911401549242	SP570P LED12/840 L60W12 CD PSU	No	Not applicable
911401550642	SP570P LED20/940 L60W12 CD PSD	DALI	3%
911401550942	SM570C LED20/840 L60W12 CD PSU	No	Not applicable
911401551542	SP571P LED20/840 L60W12 SD PSU	No	Not applicable
911401552142	SP571P LED20/840 L60W12 CD PSU	No	Not applicable

Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Housing Color
911401534842	SP570P LED50/840 L150W6 SD PSU	Opal	White
911401534942	SP570P LED31/840 L150W6 SD PSU	Opal	White
911401536242	SP570P LED50/940 L150W6 SD PSD	Opal	White
911401536742	SM570C LED50/840 L150W6 SD PSU	Opal	White
911401537342	SP570P LED50/840 L150W6 CD PSU	Opal	White
911401537442	SP570P LED31/840 L150W6 CD PSU	Opal	White
911401538642	SP570P LED50/940 L150W6 CD PSD	Opal	White
911401539142	SM570C LED50/840 L150W6 CD PSU	Opal	White
911401539542	SP571P LED50/840 L150W6 SD PSU	Opal	White
911401540342	SP571P LED50/840 L150W6 CD PSU	Opal	White
911401534642	SP570P LED40/840 L120W6 SD PSU	Opal	White
911401534742	SP570P LED25/840 L120W6 SD PSU	Opal	White
911401536142	SP570P LED40/940 L120W6 SD PSD	Opal	White
911401536542	SM570C LED40/840 L120W6 SD PSU	Opal	White
911401537142	SP570P LED40/840 L120W6 CD PSU	Opal	White
911401537242	SP570P LED25/840 L120W6 CD PSU	Opal	White
911401538542	SP570P LED40/940 L120W6 CD PSD	Opal	White
911401538942	SM570C LED40/840 L120W6 CD PSU	Opal	White
911401539442	SP571P LED40/840 L120W6 SD PSU	Opal	White
911401540142	SP571P LED40/840 L120W6 CD PSU	Opal	White
911401534442	SP570P LED20/840 L60W6 SD PSU	Opal	White
911401534542	SP570P LED12/840 L60W6 SD PSU	Opal	White
911401536042	SP570P LED20/940 L60W6 SD PSD	Opal	White
911401536342	SM570C LED20/840 L60W6 SD PSU	Opal	White
911401536942	SP570P LED20/840 L60W6 CD PSU	Opal	White
911401537042	SP570P LED12/840 L60W6 CD PSU	Opal	White

Order Code	Full Product Name	Optical cover type	Housing Color
911401538442	SP570P LED20/940 L60W6 CD PSD	Opal	White
911401538742	SM570C LED20/840 L60W6 CD PSU	Opal	White
911401539342	SP571P LED20/840 L60W6 SD PSU	Opal	White
911401539942	SP571P LED20/840 L60W6 CD PSU	Opal	White
911401540042	SP571P LED12/840 L60W6 CD PSU	Opal	White
911401568942	RC570B LED40/840 L120W12 SD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401569842	RC570B LED40/940 L120W12 SD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401570242	RC570B LED40/840 L120W12 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401570342	RC570B LED25/840 L120W12 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401571342	RC570X LED40/940 L120W12 SD WIA	Polycarbonate bowl/cover frosted	White RAL 9003
911401571442	RC570X LED40/940 L120W12 CD WIA	Polycarbonate bowl/cover frosted	White RAL 9003
911401571642	RC570B LED40/940 L120W12 CD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401540942	SP570P LED40/840 L120W9 SD PSU	Opal	White
911401541042	SP570P LED25/840 L120W9 SD PSU	Opal	White
911401542342	SP570P LED40/940 L120W9 SD PSD	Opal	White
911401542742	SM570C LED40/840 L120W9 SD PSU	Opal	White
911401543342	SP570P LED40/840 L120W9 CD PSU	Opal	White
911401543442	SP570P LED25/840 L120W9 CD PSU	Opal	White
911401544742	SP570P LED40/940 L120W9 CD PSD	Opal	White
911401545142	SM570C LED40/840 L120W9 CD PSU	Opal	White
911401545742	SP571P LED40/840 L120W9 SD PSU	Opal	White
911401546642	SP571P LED40/840 L120W9 CD PSU	Opal	White
911401547542	SP570P LED50/840 L150W12 SD PSU	Opal	White
911401548442	SP570P LED50/940 L150W12 SD PSD	Opal	White
911401548942	SM570C LED50/840 L150W12 SD PSU	Opal	White
911401549542	SP570P LED50/840 L150W12 CD PSU	Opal	White

Order Code	Full Product Name	Optical cover type	Housing Color
911401549642	SP570P LED31/840 L150W12 CD PSU	Opal	White
911401550842	SP570P LED50/940 L150W12 CD PSD	Opal	White
911401551342	SM570C LED50/840 L150W12 CD PSU	Opal	White
911401551742	SP571P LED50/840 L150W12 SD PSU	Opal	White
911401552342	SP571P LED50/840 L150W12 CD PSU	Opal	White
911401572042	RC570B LED40/940 L60W6 PSD LC	Polycarbonate bowl/cover frosted	White RAL 9003
911401574042	RC570B LED40/840 L60W6 PSU LC	Polycarbonate bowl/cover frosted	White RAL 9003
911401566042	RC570B LED50/840 L150W6 SD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401566942	RC570B LED50/940 L150W6 SD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401567442	RC570B LED50/840 L150W6 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401567542	RC570B LED31/840 L150W6 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401568742	RC570B LED50/940 L150W6 CD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401569342	RC570B LED50/9TW L150W6 SD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401569642	RC570B LED50/9TW L150W6 CD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401570942	RC570X LED50/940 L150W6 SD WIA	Polycarbonate bowl/cover frosted	White RAL 9003
911401571242	RC570X LED50/940 L150W6 CD WIA	Polycarbonate bowl/cover frosted	White RAL 9003
911401553943	SP570P LED40/840 L60W6 PSU X	Polycarbonate bowl/cover frosted	White RAL 9003
911401554043	SP570P LED40/840 L60W6 PSD X	Polycarbonate bowl/cover frosted	White RAL 9003
911401554443	SP570P LED40/940 L60W6 PSD X	Polycarbonate bowl/cover frosted	White RAL 9003
911401547442	SP570P LED40/840 L120W12 SD PSU	Opal	White
911401548342	SP570P LED40/940 L120W12 SD PSD	Opal	White
911401548742	SM570C LED40/840 L120W12 SD PSU	Opal	White
911401549342	SP570P LED40/840 L120W12 CD PSU	Opal	White
911401549442	SP570P LED25/840 L120W12 CD PSU	Opal	White
911401550742	SP570P LED40/940 L120W12 CD PSD	Opal	White
911401551142	SM570C LED40/840 L120W12 CD PSU	Opal	White

Order Code	Full Product Name	Optical cover type	Housing Color
911401551642	SP571P LED40/840 L120W12 SD PSU	Opal	White
911401552242	SP571P LED40/840 L120W12 CD PSU	Opal	White
911401569042	RC570B LED50/840 L150W12 SD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401569942	RC570B LED50/940 L150W12 SD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401570442	RC570B LED50/840 L150W12 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401570542	RC570B LED31/840 L150W12 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401571742	RC570B LED50/940 L150W12 CD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401541142	SP570P LED50/840 L150W9 SD PSU	Opal	White
911401541242	SP570P LED31/840 L150W9 SD PSU	Opal	White
911401542442	SP570P LED50/940 L150W9 SD PSD	Opal	White
911401542942	SM570C LED50/840 L150W9 SD PSU	Opal	White
911401543542	SP570P LED50/840 L150W9 CD PSU	Opal	White
911401543642	SP570P LED31/840 L150W9 CD PSU	Opal	White
911401544842	SP570P LED50/940 L150W9 CD PSD	Opal	White
911401545342	SM570C LED50/840 L150W9 CD PSU	Opal	White
911401545942	SP571P LED50/840 L150W9 SD PSU	Opal	White
911401546842	SP571P LED50/840 L150W9 CD PSU	Opal	White
911401565942	RC570B LED40/840 L120W6 SD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401566842	RC570B LED40/940 L120W6 SD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401567242	RC570B LED40/840 L120W6 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401567342	RC570B LED25/840 L120W6 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401568642	RC570B LED40/940 L120W6 CD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401569242	RC570B LED40/9TW L120W6 SD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401569542	RC570B LED40/9TW L120W6 CD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401570842	RC570X LED40/940 L120W6 SD WIA	Polycarbonate bowl/cover frosted	White RAL 9003
911401571142	RC570X LED40/940 L120W6 CD WIA	Polycarbonate bowl/cover frosted	White RAL 9003

Order Code	Full Product Name	Optical cover type	Housing Color
911401540742	SP570P LED20/840 L60W9 SD PSU	Opal	White
911401540842	SP570P LED12/840 L60W9 SD PSU	Opal	White
911401542242	SP570P LED20/940 L60W9 SD PSD	Opal	White
911401542542	SM570C LED20/840 L60W9 SD PSU	Opal	White
911401543142	SP570P LED20/840 L60W9 CD PSU	Opal	White
911401543242	SP570P LED12/840 L60W9 CD PSU	Opal	White
911401544642	SP570P LED20/940 L60W9 CD PSD	Opal	White
911401544942	SM570C LED20/840 L60W9 CD PSU	Opal	White
911401545542	SP571P LED20/840 L60W9 SD PSU	Opal	White
911401545642	SP571P LED12/840 L60W9 SD PSU	Opal	White
911401546442	SP571P LED20/840 L60W9 CD PSU	Opal	White
911401546542	SP571P LED12/840 L60W9 CD PSU	Opal	White
911401554743	SP570P LED60/840 L60W6 PSU Y	Polycarbonate bowl/cover frosted	White RAL 9003
911401555243	SP570P LED60/940 L60W6 PSD Y	Polycarbonate bowl/cover frosted	White RAL 9003
911401565842	RC570B LED20/840 L60W6 SD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401566742	RC570B LED20/940 L60W6 SD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401567042	RC570B LED20/840 L60W6 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401567142	RC570B LED12/840 L60W6 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401568542	RC570B LED20/940 L60W6 CD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401569142	RC570B LED20/9TW L60W6 SD PSD	Polycarbonate bowl/cover frosted	White RAL 9003

Order Code	Full Product Name	Optical cover type	Housing Color
911401569442	RC570B LED20/9TW L60W6 CD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401570742	RC570X LED20/940 L60W6 SD WIA	Polycarbonate bowl/cover frosted	White RAL 9003
911401571042	RC570X LED20/940 L60W6 CD WIA	Polycarbonate bowl/cover frosted	White RAL 9003
911401555643	SP570P LED45/840 L60W6 PSU HEX	Polycarbonate bowl/cover frosted	White RAL 9003
911401556043	SP570P LED45/840 L60W6 PSD HEX	Polycarbonate bowl/cover frosted	White RAL 9003
911401556443	SP570P LED45/940 L60W6 PSU HEX	Polycarbonate bowl/cover frosted	White RAL 9003
911401556843	SP570P LED45/940 L60W6 PSD HEX	Polycarbonate bowl/cover frosted	White RAL 9003
911401553143	SP570P LED40/840 L60W6 PSU T	Polycarbonate bowl/cover frosted	White RAL 9003
911401553243	SP570P LED40/840 L60W6 PSD T	Polycarbonate bowl/cover frosted	White RAL 9003
911401553643	SP570P LED40/940 L60W6 PSD T	Polycarbonate bowl/cover frosted	White RAL 9003
911401547342	SP570P LED20/840 L60W12 SD PSU	Opal	White
911401548242	SP570P LED20/940 L60W12 SD PSD	Opal	White
911401548542	SM570C LED20/840 L60W12 SD PSU	Opal	White
911401549142	SP570P LED20/840 L60W12 CD PSU	Opal	White
911401549242	SP570P LED12/840 L60W12 CD PSU	Opal	White
911401550642	SP570P LED20/940 L60W12 CD PSD	Opal	White
911401550942	SM570C LED20/840 L60W12 CD CD PSU	Opal	White
911401551542	SP571P LED20/840 L60W12 SD PSU	Opal	White
911401552142	SP571P LED20/840 L60W12 CD PSU	Opal	White

Approval and Application

Order Code	Full Product Name	Ambient temperature range
911401534842	SP570P LED50/840 L150W6 SD PSU	-20 °C to 40 °C
911401534942	SP570P LED31/840 L150W6 SD PSU	-20 °C to 40 °C
911401536242	SP570P LED50/940 L150W6 SD PSD	-20 °C to 40 °C
911401536742	SM570C LED50/840 L150W6 SD PSU	-20 °C to 40 °C
911401537342	SP570P LED50/840 L150W6 CD PSU	-20 °C to 40 °C
911401537442	SP570P LED31/840 L150W6 CD PSU	-20 °C to 40 °C
911401538642	SP570P LED50/940 L150W6 CD PSD	-20 °C to 40 °C
911401539142	SM570C LED50/840 L150W6 CD PSU	-20 °C to 40 °C

Order Code	Full Product Name	Ambient temperature range
911401539542	SP571P LED50/840 L150W6 SD PSU	-20 °C to 40 °C
911401540342	SP571P LED50/840 L150W6 CD PSU	-20 °C to 40 °C
911401534642	SP570P LED40/840 L120W6 SD PSU	-20 °C to 40 °C
911401534742	SP570P LED25/840 L120W6 SD PSU	-20 °C to 40 °C
911401536142	SP570P LED40/940 L120W6 SD PSD	-20 °C to 40 °C
911401536542	SM570C LED40/840 L120W6 SD PSU	-20 °C to 40 °C
911401537142	SP570P LED40/840 L120W6 CD PSU	-20 °C to 40 °C
911401537242	SP570P LED25/840 L120W6 CD PSU	-20 °C to 40 °C

Order Code	Full Product Name	Ambient temperature range
911401538542	SP570P LED40/940 L120W6 CD PSD	-20 °C to 40 °C
911401538942	SM570C LED40/840 L120W6 CD PSU	-20 °C to 40 °C
911401539442	SP571P LED40/840 L120W6 SD PSU	-20 °C to 40 °C
911401540142	SP571P LED40/840 L120W6 CD PSU	-20 °C to 40 °C
911401534442	SP570P LED20/840 L60W6 SD PSU	-20 °C to 40 °C
911401534542	SP570P LED12/840 L60W6 SD PSU	-20 °C to 40 °C
911401536042	SP570P LED20/940 L60W6 SD PSD	-20 °C to 40 °C
911401536342	SM570C LED20/840 L60W6 SD PSU	-20 °C to 40 °C
911401536942	SP570P LED20/840 L60W6 CD PSU	-20 °C to 40 °C
911401537042	SP570P LED12/840 L60W6 CD PSU	-20 °C to 40 °C
911401538442	SP570P LED20/940 L60W6 CD PSD	-20 °C to 40 °C
911401538742	SM570C LED20/840 L60W6 CD PSU	-20 °C to 40 °C
911401539342	SP571P LED20/840 L60W6 SD PSU	-20 °C to 40 °C
911401539942	SP571P LED20/840 L60W6 CD PSU	-20 °C to 40 °C
911401540042	SP571P LED12/840 L60W6 CD PSU	-20 °C to 40 °C
911401568942	RC570B LED40/840 L120W12 SD PSU	-20 to +40 °C
911401569842	RC570B LED40/940 L120W12 SD PSD	-20 to +40 °C
911401570242	RC570B LED40/840 L120W12 CD PSU	-20 to +40 °C
911401570342	RC570B LED25/840 L120W12 CD PSU	-20 to +40 °C
911401571342	RC570X LED40/940 L120W12 SD WIA	-20 to +40 °C
911401571442	RC570X LED40/940 L120W12 CD WIA	-20 to +40 °C
911401571642	RC570B LED40/940 L120W12 CD PSD	-20 to +40 °C
911401540942	SP570P LED40/840 L120W9 SD PSU	-20 °C to 40 °C
911401541042	SP570P LED25/840 L120W9 SD PSU	-20 °C to 40 °C
911401542342	SP570P LED40/940 L120W9 SD PSD	-20 °C to 40 °C
911401542742	SM570C LED40/840 L120W9 SD PSU	-20 °C to 40 °C
911401543342	SP570P LED40/840 L120W9 CD PSU	-20 °C to 40 °C
911401543442	SP570P LED25/840 L120W9 CD PSU	-20 °C to 40 °C
911401544742	SP570P LED40/940 L120W9 CD PSD	-20 °C to 40 °C
911401545142	SM570C LED40/840 L120W9 CD PSU	-20 °C to 40 °C
911401545742	SP571P LED40/840 L120W9 SD PSU	-20 °C to 40 °C
911401546642	SP571P LED40/840 L120W9 CD PSU	-20 °C to 40 °C
911401547542	SP570P LED50/840 L150W12 SD PSU	-20 °C to 40 °C
911401548442	SP570P LED50/940 L150W12 SD PSD	-20 °C to 40 °C
911401548942	SM570C LED50/840 L150W12 SD PSU	-20 °C to 40 °C
911401549542	SP570P LED50/840 L150W12 CD PSU	-20 °C to 40 °C
911401549642	SP570P LED31/840 L150W12 CD PSU	-20 °C to 40 °C
911401550842	SP570P LED50/940 L150W12 CD PSD	-20 °C to 40 °C
911401551342	SM570C LED50/840 L150W12 CD PSU	-20 °C to 40 °C
911401551742	SP571P LED50/840 L150W12 SD PSU	-20 °C to 40 °C
911401552342	SP571P LED50/840 L150W12 CD PSU	-20 °C to 40 °C
911401572042	RC570B LED40/940 L60W6 PSD LC	-20 to +40 °C
911401574042	RC570B LED40/840 L60W6 PSU LC	-20 to +40 °C
911401566042	RC570B LED50/840 L150W6 SD PSU	-20 to +40 °C
911401566942	RC570B LED50/940 L150W6 SD PSD	-20 to +40 °C
911401567442	RC570B LED50/840 L150W6 CD PSU	-20 to +40 °C
911401567542	RC570B LED31/840 L150W6 CD PSU	-20 to +40 °C
911401568742	RC570B LED50/940 L150W6 CD PSD	-20 to +40 °C
911401569342	RC570B LED50/9TW L150W6 SD PSD	-20 to +40 °C
911401569642	RC570B LED50/9TW L150W6 CD PSD	-20 to +40 °C
911401570942	RC570X LED50/940 L150W6 SD WIA	-20 to +40 °C
911401571242	RC570X LED50/940 L150W6 CD WIA	-20 to +40 °C

Order Code	Full Product Name	Ambient temperature range
911401553943	SP570P LED40/840 L60W6 PSU X	-20 to +40 °C
911401554043	SP570P LED40/840 L60W6 PSD X	-20 to +40 °C
911401554443	SP570P LED40/940 L60W6 PSD X	-20 to +40 °C
911401547442	SP570P LED40/840 L120W12 SD PSU	-20 °C to 40 °C
911401548342	SP570P LED40/940 L120W12 SD PSD	-20 °C to 40 °C
911401548742	SM570C LED40/840 L120W12 SD PSU	-20 °C to 40 °C
911401549342	SP570P LED40/840 L120W12 CD PSU	-20 °C to 40 °C
911401549442	SP570P LED25/840 L120W12 CD PSU	-20 °C to 40 °C
911401550742	SP570P LED40/940 L120W12 CD PSD	-20 °C to 40 °C
911401551142	SM570C LED40/840 L120W12 CD PSU	-20 °C to 40 °C
911401551642	SP571P LED40/840 L120W12 SD PSU	-20 °C to 40 °C
911401552242	SP571P LED40/840 L120W12 CD PSU	-20 °C to 40 °C
911401569042	RC570B LED50/840 L150W12 SD PSU	-20 to +40 °C
911401569942	RC570B LED50/940 L150W12 SD PSD	-20 to +40 °C
911401570442	RC570B LED50/840 L150W12 CD PSU	-20 to +40 °C
911401570542	RC570B LED31/840 L150W12 CD PSU	-20 to +40 °C
911401571742	RC570B LED50/940 L150W12 CD PSD	-20 to +40 °C
911401541142	SP570P LED50/840 L150W9 SD PSU	-20 °C to 40 °C
911401541242	SP570P LED31/840 L150W9 SD PSU	-20 °C to 40 °C
911401542442	SP570P LED50/940 L150W9 SD PSD	-20 °C to 40 °C
911401542942	SM570C LED50/840 L150W9 SD PSU	-20 °C to 40 °C
911401543542	SP570P LED50/840 L150W9 CD PSU	-20 °C to 40 °C
911401543642	SP570P LED31/840 L150W9 CD PSU	-20 °C to 40 °C
911401544842	SP570P LED50/940 L150W9 CD PSD	-20 °C to 40 °C
911401545342	SM570C LED50/840 L150W9 CD PSU	-20 °C to 40 °C
911401545942	SP571P LED50/840 L150W9 SD PSU	-20 °C to 40 °C
911401546842	SP571P LED50/840 L150W9 CD PSU	-20 °C to 40 °C
911401565942	RC570B LED40/840 L120W6 SD PSU	-20 to +40 °C
911401566842	RC570B LED40/940 L120W6 SD PSD	-20 to +40 °C
911401567242	RC570B LED40/840 L120W6 CD PSU	-20 to +40 °C
911401567342	RC570B LED25/840 L120W6 CD PSU	-20 to +40 °C
911401568642	RC570B LED40/940 L120W6 CD PSD	-20 to +40 °C
911401569242	RC570B LED40/9TW L120W6 SD PSD	-20 to +40 °C
911401569542	RC570B LED40/9TW L120W6 CD PSD	-20 to +40 °C
911401570842	RC570X LED40/940 L120W6 SD WIA	-20 to +40 °C
911401571142	RC570X LED40/940 L120W6 CD WIA	-20 to +40 °C
911401540742	SP570P LED20/840 L60W9 SD PSU	-20 °C to 40 °C
911401540842	SP570P LED12/840 L60W9 SD PSU	-20 °C to 40 °C
911401542242	SP570P LED20/940 L60W9 SD PSD	-20 °C to 40 °C
911401542542	SM570C LED20/840 L60W9 SD PSU	-20 °C to 40 °C
911401543142	SP570P LED20/840 L60W9 CD PSU	-20 °C to 40 °C
911401543242	SP570P LED12/840 L60W9 CD PSU	-20 °C to 40 °C
911401544642	SP570P LED20/940 L60W9 CD PSD	-20 °C to 40 °C
911401544942	SM570C LED20/840 L60W9 CD PSU	-20 °C to 40 °C
911401545542	SP571P LED20/840 L60W9 SD PSU	-20 °C to 40 °C
911401545642	SP571P LED12/840 L60W9 SD PSU	-20 °C to 40 °C
911401546442	SP571P LED20/840 L60W9 CD PSU	-20 °C to 40 °C
911401546542	SP571P LED12/840 L60W9 CD PSU	-20 °C to 40 °C
911401554743	SP570P LED60/840 L60W6 PSU Y	-20 to +40 °C
911401555243	SP570P LED60/940 L60W6 PSD Y	-20 to +40 °C
911401565842	RC570B LED20/840 L60W6 SD PSU	-20 to +40 °C
911401566742	RC570B LED20/940 L60W6 SD PSD	-20 to +40 °C

Order Code	Full Product Name	Ambient temperature range
911401567042	RC570B LED20/840 L60W6 CD PSU	-20 to +40 °C
911401567142	RC570B LED12/840 L60W6 CD PSU	-20 to +40 °C
911401568542	RC570B LED20/940 L60W6 CD PSD	-20 to +40 °C
911401569142	RC570B LED20/9TW L60W6 SD PSD	-20 to +40 °C
911401569442	RC570B LED20/9TW L60W6 CD PSD	-20 to +40 °C
911401570742	RC570X LED20/940 L60W6 SD WIA	-20 to +40 °C
911401571042	RC570X LED20/940 L60W6 CD WIA	-20 to +40 °C
911401555643	SP570P LED45/840 L60W6 PSU HEX	-20 to +40 °C
911401556043	SP570P LED45/840 L60W6 PSD HEX	-20 to +40 °C
911401556443	SP570P LED45/940 L60W6 PSU HEX	-20 to +40 °C
911401556843	SP570P LED45/940 L60W6 PSD HEX	-20 to +40 °C
911401553143	SP570P LED40/840 L60W6 PSU T	-20 to +40 °C

Order Code	Full Product Name	Ambient temperature range
911401553243	SP570P LED40/840 L60W6 PSD T	-20 to +40 °C
911401553643	SP570P LED40/940 L60W6 PSD T	-20 to +40 °C
911401547342	SP570P LED20/840 L60W12 SD PSU	-20 °C to 40 °C
911401548242	SP570P LED20/940 L60W12 SD PSD	-20 °C to 40 °C
911401548542	SM570C LED20/840 L60W12 SD PSU	-20 °C to 40 °C
911401549142	SP570P LED20/840 L60W12 CD PSU	-20 °C to 40 °C
911401549242	SP570P LED12/840 L60W12 CD PSU	-20 °C to 40 °C
911401550642	SP570P LED20/940 L60W12 CD PSD	-20 °C to 40 °C
911401550942	SM570C LED20/840 L60W12 CD PSU	-20 °C to 40 °C
911401551542	SP571P LED20/840 L60W12 SD PSU	-20 °C to 40 °C
911401552142	SP571P LED20/840 L60W12 CD PSU	-20 °C to 40 °C

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Luminous flux tolerance
911401534842	SP570P LED50/840 L150W6 SD PSU	-10% / +10%
911401534942	SP570P LED31/840 L150W6 SD PSU	-10% / +10%
911401536242	SP570P LED50/940 L150W6 SD PSD	-10% / +10%
911401536742	SM570C LED50/840 L150W6 SD PSU	-10% / +10%
911401537342	SP570P LED50/840 L150W6 CD PSU	-10% / +10%
911401537442	SP570P LED31/840 L150W6 CD PSU	-10% / +10%
911401538642	SP570P LED50/940 L150W6 CD PSD	-10% / +10%
911401539142	SM570C LED50/840 L150W6 CD PSU	-10% / +10%
911401539542	SP571P LED50/840 L150W6 SD PSU	-10% / +10%
911401540342	SP571P LED50/840 L150W6 CD PSU	-10% / +10%
911401534642	SP570P LED40/840 L120W6 SD PSU	-10% / +10%
911401534742	SP570P LED25/840 L120W6 SD PSU	-10% / +10%
911401536142	SP570P LED40/940 L120W6 SD PSD	-10% / +10%
911401536542	SM570C LED40/840 L120W6 SD PSU	-10% / +10%
911401537142	SP570P LED40/840 L120W6 CD PSU	-10% / +10%
911401537242	SP570P LED25/840 L120W6 CD PSU	-10% / +10%
911401538542	SP570P LED40/940 L120W6 CD PSD	-10% / +10%
911401538942	SM570C LED40/840 L120W6 CD PSU	-10% / +10%
911401539442	SP571P LED40/840 L120W6 SD PSU	-10% / +10%
911401540142	SP571P LED40/840 L120W6 CD PSU	-10% / +10%
911401534442	SP570P LED20/840 L60W6 SD PSU	-10% / +10%
911401534542	SP570P LED12/840 L60W6 SD PSU	-10% / +10%
911401536042	SP570P LED20/940 L60W6 SD PSD	-10% / +10%
911401536342	SM570C LED20/840 L60W6 SD PSU	-10% / +10%
911401536942	SP570P LED20/840 L60W6 CD PSU	-10% / +10%
911401537042	SP570P LED12/840 L60W6 CD PSU	-10% / +10%
911401538442	SP570P LED20/940 L60W6 CD PSD	-10% / +10%
911401538742	SM570C LED20/840 L60W6 CD PSU	-10% / +10%
911401539342	SP571P LED20/840 L60W6 SD PSU	-10% / +10%
911401539942	SP571P LED20/840 L60W6 CD PSU	-10% / +10%
911401540042	SP571P LED12/840 L60W6 CD PSU	-10% / +10%
911401568942	RC570B LED40/840 L120W12 SD PSU	+/-10%
911401569842	RC570B LED40/940 L120W12 SD PSD	+/-10%
911401570242	RC570B LED40/840 L120W12 CD PSU	+/-10%
911401570342	RC570B LED25/840 L120W12 CD PSU	+/-10%
911401571342	RC570X LED40/940 L120W12 SD WIA	+/-10%

Order Code	Full Product Name	Luminous flux tolerance
911401571442	RC570X LED40/940 L120W12 CD WIA	+/-10%
911401571642	RC570B LED40/940 L120W12 CD PSD	+/-10%
911401540942	SP570P LED40/840 L120W9 SD PSU	-10% / +10%
911401541042	SP570P LED25/840 L120W9 SD PSU	-10% / +10%
911401542342	SP570P LED40/940 L120W9 SD PSD	-10% / +10%
911401542742	SM570C LED40/840 L120W9 SD PSU	-10% / +10%
911401543342	SP570P LED40/840 L120W9 CD PSU	-10% / +10%
911401543442	SP570P LED25/840 L120W9 CD PSU	-10% / +10%
911401544742	SP570P LED40/940 L120W9 CD PSD	-10% / +10%
911401545142	SM570C LED40/840 L120W9 CD PSU	-10% / +10%
911401545742	SP571P LED40/840 L120W9 SD PSU	-10% / +10%
911401546642	SP571P LED40/840 L120W9 CD PSU	-10% / +10%
911401547542	SP570P LED50/840 L150W12 SD PSU	-10% / +10%
911401548442	SP570P LED50/940 L150W12 SD PSD	-10% / +10%
911401548942	SM570C LED50/840 L150W12 SD PSU	-10% / +10%
911401549542	SP570P LED50/840 L150W12 CD PSU	-10% / +10%
911401549642	SP570P LED31/840 L150W12 CD PSU	-10% / +10%
911401550842	SP570P LED50/940 L150W12 CD PSD	-10% / +10%
911401551342	SM570C LED50/840 L150W12 CD PSU	-10% / +10%
911401551742	SP571P LED50/840 L150W12 SD PSU	-10% / +10%
911401552342	SP571P LED50/840 L150W12 CD PSU	-10% / +10%
911401572042	RC570B LED40/940 L60W6 PSD LC	+/-10%
911401574042	RC570B LED40/840 L60W6 PSU LC	+/-10%
911401566042	RC570B LED50/840 L150W6 SD PSU	+/-10%
911401566942	RC570B LED50/940 L150W6 SD PSD	+/-10%
911401567442	RC570B LED50/840 L150W6 CD PSU	+/-10%
911401567542	RC570B LED31/840 L150W6 CD PSU	+/-10%
911401568742	RC570B LED50/940 L150W6 CD PSD	+/-10%
911401569342	RC570B LED50/9TW L150W6 SD PSD	+/-10%
911401569642	RC570B LED50/9TW L150W6 CD PSD	+/-10%
911401570942	RC570X LED50/940 L150W6 SD WIA	+/-10%
911401571242	RC570X LED50/940 L150W6 CD WIA	+/-10%
911401553943	SP570P LED40/840 L60W6 PSU X	+/-10%
911401554043	SP570P LED40/840 L60W6 PSD X	+/-10%
911401554443	SP570P LED40/940 L60W6 PSD X	+/-10%
911401547442	SP570P LED40/840 L120W12 SD PSU	-10% / +10%

Order Code	Full Product Name	Luminous flux tolerance
911401548342	SP570P LED40/940 L120W12 SD PSD	-10% / +10%
911401548742	SM570C LED40/840 L120W12 SD PSU	-10% / +10%
911401549342	SP570P LED40/840 L120W12 CD PSU	-10% / +10%
911401549442	SP570P LED25/840 L120W12 CD PSU	-10% / +10%
911401550742	SP570P LED40/940 L120W12 CD PSD	-10% / +10%
911401551142	SM570C LED40/840 L120W12 CD PSU	-10% / +10%
911401551642	SP571P LED40/840 L120W12 SD PSU	-10% / +10%
911401552242	SP571P LED40/840 L120W12 CD PSU	-10% / +10%
911401569042	RC570B LED50/840 L150W12 SD PSU	+/-10%
911401569942	RC570B LED50/940 L150W12 SD PSD	+/-10%
911401570442	RC570B LED50/840 L150W12 CD PSU	+/-10%
911401570542	RC570B LED31/840 L150W12 CD PSU	+/-10%
911401571742	RC570B LED50/940 L150W12 CD PSD	+/-10%
911401541142	SP570P LED50/840 L150W9 SD PSU	-10% / +10%
911401541242	SP570P LED31/840 L150W9 SD PSU	-10% / +10%
911401542442	SP570P LED50/940 L150W9 SD PSD	-10% / +10%
911401542942	SM570C LED50/840 L150W9 SD PSU	-10% / +10%
911401543542	SP570P LED50/840 L150W9 CD PSU	-10% / +10%
911401543642	SP570P LED31/840 L150W9 CD PSU	-10% / +10%
911401544842	SP570P LED50/940 L150W9 CD PSD	-10% / +10%
911401545342	SM570C LED50/840 L150W9 CD PSU	-10% / +10%
911401545942	SP571P LED50/840 L150W9 SD PSU	-10% / +10%
911401546842	SP571P LED50/840 L150W9 CD PSU	-10% / +10%
911401565942	RC570B LED40/840 L120W6 SD PSU	+/-10%
911401566842	RC570B LED40/940 L120W6 SD PSD	+/-10%
911401567242	RC570B LED40/840 L120W6 CD PSU	+/-10%
911401567342	RC570B LED25/840 L120W6 CD PSU	+/-10%
911401568642	RC570B LED40/940 L120W6 CD PSD	+/-10%
911401569242	RC570B LED40/9TW L120W6 SD PSD	+/-10%
911401569542	RC570B LED40/9TW L120W6 CD PSD	+/-10%
911401570842	RC570X LED40/940 L120W6 SD WIA	+/-10%
911401571142	RC570X LED40/940 L120W6 CD WIA	+/-10%
911401540742	SP570P LED20/840 L60W9 SD PSU	-10% / +10%
911401540842	SP570P LED12/840 L60W9 SD PSU	-10% / +10%
911401542242	SP570P LED20/940 L60W9 SD PSD	-10% / +10%
911401542542	SM570C LED20/840 L60W9 SD PSU	-10% / +10%

Order Code	Full Product Name	Luminous flux tolerance
911401543142	SP570P LED20/840 L60W9 CD PSU	-10% / +10%
911401543242	SP570P LED12/840 L60W9 CD PSU	-10% / +10%
911401544642	SP570P LED20/940 L60W9 CD PSD	-10% / +10%
911401544942	SM570C LED20/840 L60W9 CD PSU	-10% / +10%
911401545542	SP571P LED20/840 L60W9 SD PSU	-10% / +10%
911401545642	SP571P LED12/840 L60W9 SD PSU	-10% / +10%
911401546442	SP571P LED20/840 L60W9 CD PSU	-10% / +10%
911401546542	SP571P LED12/840 L60W9 CD PSU	-10% / +10%
911401554743	SP570P LED60/840 L60W6 PSU Y	+/-10%
911401555243	SP570P LED60/940 L60W6 PSD Y	+/-10%
911401565842	RC570B LED20/840 L60W6 SD PSU	+/-10%
911401566742	RC570B LED20/940 L60W6 SD PSD	+/-10%
911401567042	RC570B LED20/840 L60W6 CD PSU	+/-10%
911401567142	RC570B LED12/840 L60W6 CD PSU	+/-10%
911401568542	RC570B LED20/940 L60W6 CD PSD	+/-10%
911401569142	RC570B LED20/9TW L60W6 SD PSD	+/-10%
911401569442	RC570B LED20/9TW L60W6 CD PSD	+/-10%
911401570742	RC570X LED20/940 L60W6 SD WIA	+/-10%
911401571042	RC570X LED20/940 L60W6 CD WIA	+/-10%
911401555643	SP570P LED45/840 L60W6 PSU HEX	+/-10%
911401556043	SP570P LED45/840 L60W6 PSD HEX	+/-10%
911401556443	SP570P LED45/940 L60W6 PSU HEX	+/-10%
911401556843	SP570P LED45/940 L60W6 PSD HEX	+/-10%
911401553143	SP570P LED40/840 L60W6 PSU T	+/-10%
911401553243	SP570P LED40/840 L60W6 PSD T	+/-10%
911401553643	SP570P LED40/940 L60W6 PSD T	+/-10%
911401547342	SP570P LED20/840 L60W12 SD PSU	-10% / +10%
911401548242	SP570P LED20/940 L60W12 SD PSD	-10% / +10%
911401548542	SM570C LED20/840 L60W12 SD PSU	-10% / +10%
911401549142	SP570P LED20/840 L60W12 CD PSU	-10% / +10%
911401549242	SP570P LED12/840 L60W12 CD PSU	-10% / +10%
911401550642	SP570P LED20/940 L60W12 CD PSD	-10% / +10%
911401550942	SM570C LED20/840 L60W12 CD PSU	-10% / +10%
911401551542	SP571P LED20/840 L60W12 SD PSU	-10% / +10%
911401552142	SP571P LED20/840 L60W12 CD PSU	-10% / +10%

