



Flexible and Elegant

SlimBalance G3

SlimBalance G3 SP570P is a flexible linear office offer which fits a variety of spaces like office, education. It offers flexible width of 35/60/90/120mm and length of 600/1200/1500mm to fit multiple applications. Geometric shapes help further create differentiated space. By means of its special designed structure, it offers quick and easy installation and maintenance. UGR19 is available for certain types through customized solution to provide a better visual comfort office environment.

Benefits

- High lm/w provides better energy saving
- Flexible width offers the feasibility to fit multiple ceiling spaces
- Dali and Interact interfaces available for easy system control
- Low UGR offer for visual comfort
- Multiple mounting installations and geometric shapes to cater for various applications
- Easy installation mechanism and modular design help save installation and maintenance time

Features

- System efficiency: max 130lm/W
- Product width with 35/60/90/120mm options
- CRI 80 and 90 available
- Lifetime: 50k hours (L70@ta=25deg)
- UGR19 available for certain types through customized solution
- Easy 'Slide and Click' mechanism for quick continuous installation

Application

- Open plan office
- Public indoor area
- Meeting/Training room
- Library

Specifications

SlimBalance G3


Ceiling type	Open ceiling office for suspension installation
	Plaster board ceiling for recessed installation and surface mounted installation
Mains Voltage	220-240V / 50 - 60Hz
Dimming	PSU: non-dimmable
	PSD: Dimmable via Dali-broadcasting
	WIA: Wireless control, compatible with Interact
	SIA: Wireless control, compatible with SNS210 sensor
Control system input	Dali
Integrated sensors	SNS210 available for SIA version
Material	Extrusion aluminium
Luminaire efficacy	130lm/w

Correlated color	840
temperature - CCT	940
Color Rendering index - 840, 940	
CRI	
Optic	UGR19 is available through lens design
Ingress protection	IP20
Driver replaceable	Yes
UGR	19 is available through lens design
	Suspension
	Recessed
Installation	Surface mounted


Versions





Dimensional drawing







Dimensional drawing







SP570 W6L60 SD shop drawing



Product Type	Length (mm)	Width (mm)	Height (mm)
SP570	1235	60	7.52
SP570 L.C.	60	60	8.22
SP570 L.C.	60	60	8.52



Dimensional drawing



Product details

SlimBalance G3



SlimBalance G3



Product details

SlimBalance G3



General Information	
Gear	-
Service tag	Yes
Operating and Electrical	
Protection class IEC	Safety class I
Line Frequency	50 or 60 Hz
Mechanical and Housing	
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
CE mark	Yes
ENEC mark	-
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Initial chromaticity	SDCM<=4

General Information

Order Code	Full Product Name	Driver included	Number of gear units
911401534642	SP570P LED40/840 L120W6 SD PSU	Yes	1 unit
911401538542	SP570P LED40/940 L120W6 CD PSD	Yes	1 unit
911401540142	SP571P LED40/840 L120W6 CD PSU	Yes	1 unit
911401534442	SP570P LED20/840 L60W6 SD PSU	Yes	1 unit
911401538442	SP570P LED20/940 L60W6 CD PSD	Yes	1 unit
911401539342	SP571P LED20/840 L60W6 SD PSU	Yes	1 unit
911401539942	SP571P LED20/840 L60W6 CD PSU	Yes	1 unit
911401568942	RC570B LED40/840 L120W12 SD PSU	-	-
911401569842	RC570B LED40/940 L120W12 SD PSD	-	-
911401570242	RC570B LED40/840 L120W12 CD PSU	-	-
911401570342	RC570B LED25/840 L120W12 CD PSU	-	-
911401571342	RC570X LED40/940 L120W12 SD WIA	-	-
911401571442	RC570X LED40/940 L120W12 CD WIA	-	-
911401571642	RC570B LED40/940 L120W12 CD PSD	-	-
911401542342	SP570P LED40/940 L120W9 SD PSD	Yes	1 unit
911401572042	RC570B LED40/940 L60W6 PSD LC	-	-
911401574042	RC570B LED40/840 L60W6 PSU LC	-	-
911401566042	RC570B LED50/840 L150W6 SD PSU	-	-
911401566942	RC570B LED50/940 L150W6 SD PSD	-	-
911401567442	RC570B LED50/840 L150W6 CD PSU	-	-
911401567542	RC570B LED31/840 L150W6 CD PSU	-	-
911401568742	RC570B LED50/940 L150W6 CD PSD	-	-
911401569342	RC570B LED50/9TW L150W6 SD PSD	-	-
911401569642	RC570B LED50/9TW L150W6 CD PSD	-	-
911401570942	RC570X LED50/940 L150W6 SD WIA	-	-
911401571242	RC570X LED50/940 L150W6 CD WIA	-	-
911401569042	RC570B LED50/840 L150W12 SD PSU	-	-
911401569942	RC570B LED50/940 L150W12 SD PSD	-	-
911401570442	RC570B LED50/840 L150W12 CD PSU	-	-
911401570542	RC570B LED31/840 L150W12 CD PSU	-	-
911401571742	RC570B LED50/940 L150W12 CD PSD	-	-
911401565942	RC570B LED40/840 L120W6 SD PSU	-	-
911401566842	RC570B LED40/940 L120W6 SD PSD	-	-
911401567242	RC570B LED40/840 L120W6 CD PSU	-	-
911401567342	RC570B LED25/840 L120W6 CD PSU	-	-
911401568642	RC570B LED40/940 L120W6 CD PSD	-	-
911401569242	RC570B LED40/9TW L120W6 SD PSD	-	-
911401569542	RC570B LED40/9TW L120W6 CD PSD	-	-
911401570842	RC570X LED40/940 L120W6 SD WIA	-	-
911401571142	RC570X LED40/940 L120W6 CD WIA	-	-

Order Code	Full Product Name	Driver included	Number of gear units
911401565842	RC570B LED20/840 L60W6 SD PSU	-	-
911401566742	RC570B LED20/940 L60W6 SD PSD	-	-
911401567042	RC570B LED20/840 L60W6 CD PSU	-	-
911401567142	RC570B LED12/840 L60W6 CD PSU	-	-
911401568542	RC570B LED20/940 L60W6 CD PSD	-	-
911401569142	RC570B LED20/9TW L60W6 SD PSD	-	-
911401569442	RC570B LED20/9TW L60W6 CD PSD	-	-
911401570742	RC570X LED20/940 L60W6 SD WIA	-	-
911401571042	RC570X LED20/940 L60W6 CD WIA	-	-
911401556443	SP570P LED45/940 L60W6 PSU HEX	Yes	-

Light Technical (1/2)

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401534642	SP570P LED40/840 L120W6 SD PSU	120 degree(s)	4000 K	80	131.25 lm/W
911401538542	SP570P LED40/940 L120W6 CD PSD	120 degree(s)	4000 K	90	119.70149253731343 lm/W
911401540142	SP571P LED40/840 L120W6 CD PSU	120 degree(s)	4000 K	80	136.27118644067798 lm/W
911401534442	SP570P LED20/840 L60W6 SD PSU	120 degree(s)	4000 K	80	118.85714285714286 lm/W
911401538442	SP570P LED20/940 L60W6 CD PSD	120 degree(s)	4000 K	90	111.42857142857143 lm/W
911401539342	SP571P LED20/840 L60W6 SD PSU	120 degree(s)	4000 K	80	147.85714285714286 lm/W
911401539942	SP571P LED20/840 L60W6 CD PSU	120 degree(s)	4000 K	80	147.85714285714286 lm/W
911401568942	RC570B LED40/840 L120W12 SD PSU	116 degree(s)	4000 K	>80	147 lm/W
911401569842	RC570B LED40/940	116 degree(s)	4000 K	>90	131 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
	L120W12 SD PSD				
911401570242	RC570B LED40/840 L120W12 CD PSU	116 degree(s)	4000 K	>80	147 lm/W
911401570342	RC570B LED25/840 L120W12 CD PSU	116 degree(s)	4000 K	>80	143 lm/W
911401571342	RC570X LED40/940 L120W12 SD WIA	116 degree(s)	4000 K	>90	135 lm/W
911401571442	RC570X LED40/940 L120W12 CD WIA	116 degree(s)	4000 K	>90	135 lm/W
911401571642	RC570B LED40/940 L120W12 CD PSD	116 degree(s)	4000 K	>90	131 lm/W
911401542342	SP570P LED40/940 L120W9 SD PSD	120 degree(s)	4000 K	90	119.70149253731343 lm/W
911401572042	RC570B LED40/940 L60W6 PSD LC	116 degree(s)	4000 K	>90	119 lm/W
911401574042	RC570B LED40/840 L60W6 PSU LC	116 degree(s)	4000 K	>80	133 lm/W

SlimBalance G3

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401566042	RC570B LED50/840 L150W6 SD PSU	116 degree(s)	4000 K	>80	132 lm/W
911401566942	RC570B LED50/940 L150W6 SD PSD	116 degree(s)	4000 K	>90	110 lm/W
911401567442	RC570B LED50/840 L150W6 CD PSU	116 degree(s)	4000 K	>80	132 lm/W
911401567542	RC570B LED31/840 L150W6 CD PSU	116 degree(s)	4000 K	>80	138 lm/W
911401568742	RC570B LED50/940 L150W6 CD PSD	116 degree(s)	4000 K	>90	110 lm/W
911401569342	RC570B LED50/9TW L150W6 SD PSD	116 degree(s)	Tunable White	>90	122 lm/W
911401569642	RC570B LED50/9TW L150W6 CD PSD	116 degree(s)	Tunable White	>90	122 lm/W
911401570942	RC570X LED50/940 L150W6 SD WIA	116 degree(s)	4000 K	>90	125 lm/W
911401571242	RC570X LED50/940 L150W6 CD WIA	116 degree(s)	4000 K	>90	125 lm/W
911401569042	RC570B LED50/840 L150W12 SD PSU	116 degree(s)	4000 K	>80	146 lm/W
911401569942	RC570B LED50/940 L150W12 SD PSD	116 degree(s)	4000 K	>90	138 lm/W
911401570442	RC570B LED50/840 L150W12 CD PSU	116 degree(s)	4000 K	>80	146 lm/W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401570542	RC570B LED31/840 L150W12 CD PSU	116 degree(s)	4000 K	>80	149 lm/W
911401571742	RC570B LED50/940 L150W12 CD PSD	116 degree(s)	4000 K	>90	138 lm/W
911401565942	RC570B LED40/840 L120W6 SD PSU	116 degree(s)	4000 K	>80	135 lm/W
911401566842	RC570B LED40/940 L120W6 SD PSD	116 degree(s)	4000 K	>90	122 lm/W
911401567242	RC570B LED40/840 L120W6 CD PSU	116 degree(s)	4000 K	>80	135 lm/W
911401567342	RC570B LED25/840 L120W6 CD PSU	116 degree(s)	4000 K	>80	141 lm/W
911401568642	RC570B LED40/940 L120W6 CD PSD	116 degree(s)	4000 K	>90	122 lm/W
911401569242	RC570B LED40/9TW L120W6 SD PSD	116 degree(s)	Tunable White	>90	119 lm/W
911401569542	RC570B LED40/9TW L120W6 CD PSD	116 degree(s)	Tunable White	>90	119 lm/W
911401570842	RC570X LED40/940 L120W6 SD WIA	116 degree(s)	4000 K	>90	125 lm/W
911401571142	RC570X LED40/940 L120W6 CD WIA	116 degree(s)	4000 K	>90	125 lm/W
911401565842	RC570B LED20/840 L60W6 SD PSU	116 degree(s)	4000 K	>80	119 lm/W

SlimBalance G3

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401566742	RC570B LED20/940 L60W6 SD PSD	116 degree(s)	4000 K	>90	111 lm/W
911401567042	RC570B LED20/840 L60W6 CD PSU	116 degree(s)	4000 K	>80	119 lm/W
911401567142	RC570B LED12/840 L60W6 CD PSU	116 degree(s)	4000 K	>80	125 lm/W
911401568542	RC570B LED20/940 L60W6 CD PSD	116 degree(s)	4000 K	>90	111 lm/W
911401569142	RC570B LED20/9TW White	116 degree(s)	Tunable	>90	108 lm/W

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type
911401534642	SP570P LED40/840 L120W6 SD PSU	4,200 lm	1	Beam angle 100°
911401538542	SP570P LED40/940 L120W6 CD PSD	4,010 lm	1	Beam angle 100°
911401540142	SP571P LED40/840 L120W6 CD PSU	4,020 lm	1	Beam angle 100°
911401534442	SP570P LED20/840 L60W6 SD PSU	2,080 lm	1	Beam angle 100°
911401538442	SP570P LED20/940 L60W6 CD PSD	1,950 lm	1	Beam angle 100°
911401539342	SP571P LED20/840 L60W6 SD PSU	2,070 lm	1	Beam angle 100°
911401539942	SP571P LED20/840 L60W6 CD PSU	2,070 lm	1	Beam angle 100°
911401568942	RC570B LED40/840 L120W12 SD PSU	3,980 lm	-	-
911401569842	RC570B LED40/940 L120W12 SD PSD	3,740 lm	-	-
911401570242	RC570B LED40/840 L120W12 CD PSU	3,980 lm	-	-
911401570342	RC570B LED25/840 L120W12 CD PSU	2,500 lm	-	-
911401571342	RC570X LED40/940 L120W12 SD WIA	3,650 lm	-	-

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401569442	RC570B LED20/9TW L60W6 CD PSD	116 degree(s)	Tunable White	>90	108 lm/W
911401570742	RC570X LED20/940 L60W6 SD WIA	116 degree(s)	4000 K	>90	111 lm/W
911401571042	RC570X LED20/940 L60W6 CD WIA	116 degree(s)	4000 K	>90	111 lm/W
911401556443	SP570P LED45/940 L60W6 PSU HEX	116 degree(s)	4000 K	>90	141 lm/W

Order Code	Full Product Name	Luminous Flux	Number of light sources	Optic type
911401571442	RC570X LED40/940 L120W12 CD WIA	3,650 lm	-	-
911401571642	RC570B LED40/940 L120W12 CD PSD	3,740 lm	-	-
911401542342	SP570P LED40/940 L120W9 SD PSD	4,010 lm	1	Beam angle 100°
911401572042	RC570B LED40/940 L60W6 PSD LC	3,880 lm	-	-
911401574042	RC570B LED40/840 L60W6 PSU LC	4,130 lm	-	-
911401566042	RC570B LED50/840 L150W6 SD PSU	5,344 lm	-	-
911401566942	RC570B LED50/940 L150W6 SD PSD	4,580 lm	-	-
911401567442	RC570B LED50/840 L150W6 CD PSU	5,344 lm	-	-
911401567542	RC570B LED31/840 L150W6 CD PSU	3,250 lm	-	-
911401568742	RC570B LED50/940 L150W6 CD PSD	4,580 lm	-	-
911401569342	RC570B LED50/9TW L150W6 SD PSD	5,020 lm	-	-
911401569642	RC570B LED50/9TW L150W6 CD PSD	5,020 lm	-	-

SlimBalance G3

Order Code	Full Product Name	Luminous Flux	Number of light sources		Optic type
911401570942	RC570X LED50/940 L150W6 SD WIA	5,020 lm	-	-	-
911401571242	RC570X LED50/940 L150W6 CD WIA	5,020 lm	-	-	-
911401569042	RC570B LED50/840 L150W12 SD PSU	4,970 lm	-	-	-
911401569942	RC570B LED50/940 L150W12 SD PSD	4,680 lm	-	-	-
911401570442	RC570B LED50/840 L150W12 CD PSU	4,970 lm	-	-	-
911401570542	RC570B LED31/840 L150W12 CD PSU	3,125 lm	-	-	-
911401571742	RC570B LED50/940 L150W12 CD PSD	4,680 lm	-	-	-
911401565942	RC570B LED40/840 L120W6 SD PSU	4,400 lm	-	-	-
911401566842	RC570B LED40/940 L120W6 SD PSD	4,136 lm	-	-	-
911401567242	RC570B LED40/840 L120W6 CD PSU	4,400 lm	-	-	-
911401567342	RC570B LED25/840 L120W6 CD PSU	2,600 lm	-	-	-
911401568642	RC570B LED40/940 L120W6 CD PSD	4,136 lm	-	-	-
911401569242	RC570B LED40/9TW L120W6 SD PSD	4,010 lm	-	-	-

Order Code	Full Product Name	Luminous Flux	Number of light sources		Optic type
911401569542	RC570B LED40/9TW L120W6 CD PSD	4,010 lm	-	-	-
911401570842	RC570X LED40/940 L120W6 SD WIA	4,010 lm	-	-	-
911401571142	RC570X LED40/940 L120W6 CD WIA	4,010 lm	-	-	-
911401565842	RC570B LED20/840 L60W6 SD PSU	2,080 lm	-	-	-
911401566742	RC570B LED20/940 L60W6 SD PSD	1,950 lm	-	-	-
911401567042	RC570B LED20/840 L60W6 CD PSU	2,080 lm	-	-	-
911401567142	RC570B LED12/840 L60W6 CD PSU	1,250 lm	-	-	-
911401568542	RC570B LED20/940 L60W6 CD PSD	1,950 lm	-	-	-
911401569142	RC570B LED20/9TW L60W6 SD PSD	1,950 lm	-	-	-
911401569442	RC570B LED20/9TW L60W6 CD PSD	1,950 lm	-	-	-
911401570742	RC570X LED20/940 L60W6 SD WIA	1,950 lm	-	-	-
911401571042	RC570X LED20/940 L60W6 CD WIA	1,950 lm	-	-	-
911401556443	SP570P LED45/940 L60W6 PSU HEX	4,500 lm	-	-	-

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Power Consumption		Suitable for random switching
911401534642	SP570P LED40/840 L120W6 SD PSU	220 to 240 V	32 W		No
911401538542	SP570P LED40/940 L120W6 CD PSD	220 to 240 V	33.5 W		No
911401540142	SP571P LED40/840 L120W6 CD PSU	220 to 240 V	29.5 W		No
911401534442	SP570P LED20/840 L60W6 SD PSU	220 to 240 V	17.5 W		No
911401538442	SP570P LED20/940 L60W6 CD PSD	220 to 240 V	17.5 W		No
911401539342	SP571P LED20/840 L60W6 SD PSU	220 to 240 V	14 W		No
911401539942	SP571P LED20/840 L60W6 CD PSU	220 to 240 V	14 W		No
911401568942	RC570B LED40/840 L120W12 SD PSU	220-240 V	27 W		-
911401569842	RC570B LED40/940 L120W12 SD PSD	220-240 V	28.5 W		-

Order Code	Full Product Name	Input Voltage	Power Consumption		Suitable for random switching
911401570242	RC570B LED40/840 L120W12 CD PSU	220-240 V	27 W		-
911401570342	RC570B LED25/840 L120W12 CD PSU	220-240 V	17.5 W		-
911401571342	RC570X LED40/940 L120W12 SD WIA	220-240 V	27 W		-
911401571442	RC570X LED40/940 L120W12 CD WIA	220-240 V	27 W		-
911401571642	RC570B LED40/940 L120W12 CD PSD	220-240 V	28.5 W		-
911401542342	SP570P LED40/940 L120W9 SD PSD	220 to 240 V	33.5 W		No
911401572042	RC570B LED40/940 L60W6 PSD LC	220-240 V	32.5 W		-
911401574042	RC570B LED40/840 L60W6 PSU LC	220-240 V	31 W		-
911401566042	RC570B LED50/840 L150W6 SD PSU	220-240 V	40.5 W		-

SlimBalance G3

Order Code	Full Product Name	Input Voltage	Power	Suitable for random switching
			Consumption	
911401566942	RC570B LED50/940 L150W6 SD PSD	220-240 V	41.5 W	-
911401567442	RC570B LED50/840 L150W6 CD PSU	220-240 V	40.5 W	-
911401567542	RC570B LED31/840 L150W6 CD PSU	220-240 V	23.5 W	-
911401568742	RC570B LED50/940 L150W6 CD PSD	220-240 V	41.5 W	-
911401569342	RC570B LED50/9TW L150W6 SD PSD	220-240 V	41 W	-
911401569642	RC570B LED50/9TW L150W6 CD PSD	220-240 V	41 W	-
911401570942	RC570X LED50/940 L150W6 SD WIA	220-240 V	40 W	-
911401571242	RC570X LED50/940 L150W6 CD WIA	220-240 V	40 W	-
911401569042	RC570B LED50/840 L150W12 SD PSU	220-240 V	34 W	-
911401569942	RC570B LED50/940 L150W12 SD PSD	220-240 V	34 W	-
911401570442	RC570B LED50/840 L150W12 CD PSU	220-240 V	34 W	-
911401570542	RC570B LED31/840 L150W12 CD PSU	220-240 V	21 W	-
911401571742	RC570B LED50/940 L150W12 CD PSD	220-240 V	34 W	-
911401565942	RC570B LED40/840 L120W6 SD PSU	220-240 V	32.5 W	-
911401566842	RC570B LED40/940 L120W6 SD PSD	220-240 V	34 W	-
911401567242	RC570B LED40/840 L120W6 CD PSU	220-240 V	32.5 W	-

Order Code	Full Product Name	Input Voltage	Power	Suitable for random switching
			Consumption	
911401567342	RC570B LED25/840 L120W6 CD PSU	220-240 V	18.5 W	-
911401568642	RC570B LED40/940 L120W6 CD PSD	220-240 V	34 W	-
911401569242	RC570B LED40/9TW L120W6 SD PSD	220-240 V	33.5 W	-
911401569542	RC570B LED40/9TW L120W6 CD PSD	220-240 V	33.5 W	-
911401570842	RC570X LED40/940 L120W6 SD WIA	220-240 V	32 W	-
911401571142	RC570X LED40/940 L120W6 CD WIA	220-240 V	32 W	-
911401565842	RC570B LED20/840 L60W6 SD PSU	220-240 V	17.5 W	-
911401566742	RC570B LED20/940 L60W6 SD PSD	220-240 V	17.5 W	-
911401567042	RC570B LED20/840 L60W6 CD PSU	220-240 V	17.5 W	-
911401567142	RC570B LED12/840 L60W6 CD PSU	220-240 V	10 W	-
911401568542	RC570B LED20/940 L60W6 CD PSD	220-240 V	17.5 W	-
911401569142	RC570B LED20/9TW L60W6 SD PSD	220-240 V	18 W	-
911401569442	RC570B LED20/9TW L60W6 CD PSD	220-240 V	18 W	-
911401570742	RC570X LED20/940 L60W6 SD WIA	220-240 V	17.5 W	-
911401571042	RC570X LED20/940 L60W6 CD WIA	220-240 V	17.5 W	-
911401556443	SP570P LED45/940 L60W6 PSU HEX	220-240 V	32 W	-

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
911401534642	SP570P LED40/840 L120W6 SD PSU	No	Not applicable
911401538542	SP570P LED40/940 L120W6 CD PSD	DALI	1%
911401540142	SP571P LED40/840 L120W6 CD PSU	No	Not applicable
911401534442	SP570P LED20/840 L60W6 SD PSU	No	Not applicable
911401538442	SP570P LED20/940 L60W6 CD PSD	DALI	3%
911401539342	SP571P LED20/840 L60W6 SD PSU	No	Not applicable
911401539942	SP571P LED20/840 L60W6 CD PSU	No	Not applicable
911401568942	RC570B LED40/840 L120W12 SD PSU	-	-
911401569842	RC570B LED40/940 L120W12 SD PSD	DALI	-
911401570242	RC570B LED40/840 L120W12 CD PSU	-	-
911401570342	RC570B LED25/840 L120W12 CD PSU	-	-
911401571342	RC570X LED40/940 L120W12 SD WIA	Wireless Dim	-
911401571442	RC570X LED40/940 L120W12 CD WIA	Wireless Dim	-

Order Code	Full Product Name	Dimmable	Maximum dim level
911401571642	RC570B LED40/940 L120W12 CD PSD	DALI	-
911401542342	SP570P LED40/940 L120W9 SD PSD	DMX	1%
911401572042	RC570B LED40/940 L60W6 PSD LC	DALI	-
911401574042	RC570B LED40/840 L60W6 PSU LC	-	-
911401566042	RC570B LED50/840 L150W6 SD PSU	-	-
911401566942	RC570B LED50/940 L150W6 SD PSD	DALI	-
911401567442	RC570B LED50/840 L150W6 CD PSU	-	-
911401567542	RC570B LED31/840 L150W6 CD PSU	-	-
911401568742	RC570B LED50/940 L150W6 CD PSD	DALI	-
911401569342	RC570B LED50/9TW L150W6 SD PSD	DALI	-
911401569642	RC570B LED50/9TW L150W6 CD PSD	DALI	-
911401570942	RC570X LED50/940 L150W6 SD WIA	Wireless Dim	-
911401571242	RC570X LED50/940 L150W6 CD WIA	Wireless Dim	-

SlimBalance G3

Order Code	Full Product Name	Dimmable	Maximum dim level
911401569042	RC570B LED50/840 L150W12 SD PSU	-	-
911401569942	RC570B LED50/940 L150W12 SD PSD DALI	-	-
911401570442	RC570B LED50/840 L150W12 CD PSU	-	-
911401570542	RC570B LED31/840 L150W12 CD PSU	-	-
911401571742	RC570B LED50/940 L150W12 CD PSD DALI	-	-
911401565942	RC570B LED40/840 L120W6 SD PSU	-	-
911401566842	RC570B LED40/940 L120W6 SD PSD DALI	-	-
911401567242	RC570B LED40/840 L120W6 CD PSU	-	-
911401567342	RC570B LED25/840 L120W6 CD PSU	-	-
911401568642	RC570B LED40/940 L120W6 CD PSD DALI	-	-
911401569242	RC570B LED40/9TW L120W6 SD PSD DALI	-	-
911401569542	RC570B LED40/9TW L120W6 CD PSD DALI	-	-

Order Code	Full Product Name	Dimmable	Maximum dim level
911401570842	RC570X LED40/940 L120W6 SD WIA	Wireless Dim	-
911401571142	RC570X LED40/940 L120W6 CD WIA	Wireless Dim	-
911401565842	RC570B LED20/840 L60W6 SD PSU	-	-
911401566742	RC570B LED20/940 L60W6 SD PSD DALI	-	-
911401567042	RC570B LED20/840 L60W6 CD PSU	-	-
911401567142	RC570B LED12/840 L60W6 CD PSU	-	-
911401568542	RC570B LED20/940 L60W6 CD PSD DALI	-	-
911401569142	RC570B LED20/9TW L60W6 SD PSD DALI	-	-
911401569442	RC570B LED20/9TW L60W6 CD PSD DALI	-	-
911401570742	RC570X LED20/940 L60W6 SD WIA	Wireless Dim	-
911401571042	RC570X LED20/940 L60W6 CD WIA	Wireless Dim	-
911401556443	SP570P LED45/940 L60W6 PSU HEX	-	-

Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Housing Color
911401534642	SP570P LED40/840 L120W6 SD PSU	Opal	White
911401538542	SP570P LED40/940 L120W6 CD PSD	Opal	White
911401540142	SP571P LED40/840 L120W6 CD PSU	Opal	White
911401534442	SP570P LED20/840 L60W6 SD PSU	Opal	White
911401538442	SP570P LED20/940 L60W6 CD PSD	Opal	White
911401539342	SP571P LED20/840 L60W6 SD PSU	Opal	White
911401539942	SP571P LED20/840 L60W6 CD PSU	Opal	White
911401568942	RC570B LED40/840 L120W12 SD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401569842	RC570B LED40/940 L120W12 SD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401570242	RC570B LED40/840 L120W12 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401570342	RC570B LED25/840 L120W12 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401571342	RC570X LED40/940 L120W12 SD WIA	Polycarbonate bowl/cover frosted	White RAL 9003
911401571442	RC570X LED40/940 L120W12 CD WIA	Polycarbonate bowl/cover frosted	White RAL 9003
911401571642	RC570B LED40/940 L120W12 CD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401542342	SP570P LED40/940 L120W9 SD PSD	Opal	White
911401572042	RC570B LED40/940 L60W6 PSD LC	Polycarbonate bowl/cover frosted	White RAL 9003
911401574042	RC570B LED40/840 L60W6 PSU LC	Polycarbonate bowl/cover frosted	White RAL 9003

Order Code	Full Product Name	Optical cover type	Housing Color
911401566042	RC570B LED50/840 L150W6 SD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401566942	RC570B LED50/940 L150W6 SD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401567442	RC570B LED50/840 L150W6 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401567542	RC570B LED31/840 L150W6 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401568742	RC570B LED50/940 L150W6 CD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401569342	RC570B LED50/9TW L150W6 SD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401569642	RC570B LED50/9TW L150W6 CD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401570942	RC570X LED50/940 L150W6 SD WIA	Polycarbonate bowl/cover frosted	White RAL 9003
911401571242	RC570X LED50/940 L150W6 CD WIA	Polycarbonate bowl/cover frosted	White RAL 9003
911401569042	RC570B LED50/840 L150W12 SD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401569942	RC570B LED50/940 L150W12 SD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401570442	RC570B LED50/840 L150W12 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401570542	RC570B LED31/840 L150W12 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401571742	RC570B LED50/940 L150W12 CD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401565942	RC570B LED40/840 L120W6 SD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401566842	RC570B LED40/940 L120W6 SD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401567242	RC570B LED40/840 L120W6 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003

Order Code	Full Product Name	Optical cover type	Housing Color
911401567342	RC570B LED25/840 L120W6 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401568642	RC570B LED40/940 L120W6 CD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401569242	RC570B LED40/9TW L120W6 SD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401569542	RC570B LED40/9TW L120W6 CD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401570842	RC570X LED40/940 L120W6 SD WIA	Polycarbonate bowl/cover frosted	White RAL 9003
911401571142	RC570X LED40/940 L120W6 CD WIA	Polycarbonate bowl/cover frosted	White RAL 9003
911401565842	RC570B LED20/840 L60W6 SD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401566742	RC570B LED20/940 L60W6 SD PSD	Polycarbonate bowl/cover frosted	White RAL 9003

Order Code	Full Product Name	Optical cover type	Housing Color
911401567042	RC570B LED20/840 L60W6 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401567142	RC570B LED12/840 L60W6 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401568542	RC570B LED20/940 L60W6 CD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401569142	RC570B LED20/9TW L60W6 SD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401569442	RC570B LED20/9TW L60W6 CD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401570742	RC570X LED20/940 L60W6 SD WIA	Polycarbonate bowl/cover frosted	White RAL 9003
911401571042	RC570X LED20/940 L60W6 CD WIA	Polycarbonate bowl/cover frosted	White RAL 9003
911401556443	SP570P LED45/940 L60W6 PSU HEX	Polycarbonate bowl/cover frosted	White RAL 9003

Approval and Application

Order Code	Full Product Name	Ambient temperature range
911401534642	SP570P LED40/840 L120W6 SD PSU	-20 °C to 40 °C
911401538542	SP570P LED40/940 L120W6 CD PSD	-20 °C to 40 °C
911401540142	SP571P LED40/840 L120W6 CD PSU	-20 °C to 40 °C
911401534442	SP570P LED20/840 L60W6 SD PSU	-20 °C to 40 °C
911401538442	SP570P LED20/940 L60W6 CD PSD	-20 °C to 40 °C
911401539342	SP571P LED20/840 L60W6 SD PSU	-20 °C to 40 °C
911401539942	SP571P LED20/840 L60W6 CD PSU	-20 °C to 40 °C
911401568942	RC570B LED40/840 L120W12 SD PSU	-20 to +40 °C
911401569842	RC570B LED40/940 L120W12 SD PSD	-20 to +40 °C
911401570242	RC570B LED40/840 L120W12 CD PSU	-20 to +40 °C
911401570342	RC570B LED25/840 L120W12 CD PSU	-20 to +40 °C
911401571342	RC570X LED40/940 L120W12 SD WIA	-20 to +40 °C
911401571442	RC570X LED40/940 L120W12 CD WIA	-20 to +40 °C
911401571642	RC570B LED40/940 L120W12 CD PSD	-20 to +40 °C
911401542342	SP570P LED40/940 L120W9 SD PSD	-20 °C to 40 °C
911401572042	RC570B LED40/940 L60W6 PSD LC	-20 to +40 °C
911401574042	RC570B LED40/840 L60W6 PSU LC	-20 to +40 °C
911401566042	RC570B LED50/840 L150W6 SD PSU	-20 to +40 °C
911401566942	RC570B LED50/940 L150W6 SD PSD	-20 to +40 °C
911401567442	RC570B LED50/840 L150W6 CD PSU	-20 to +40 °C
911401567542	RC570B LED31/840 L150W6 CD PSU	-20 to +40 °C
911401568742	RC570B LED50/940 L150W6 CD PSD	-20 to +40 °C
911401569342	RC570B LED50/9TW L150W6 SD PSD	-20 to +40 °C
911401569642	RC570B LED50/9TW L150W6 CD PSD	-20 to +40 °C
911401570942	RC570X LED50/940 L150W6 SD WIA	-20 to +40 °C

Order Code	Full Product Name	Ambient temperature range
911401571242	RC570X LED50/940 L150W6 CD WIA	-20 to +40 °C
911401569042	RC570B LED50/840 L150W12 SD PSU	-20 to +40 °C
911401569942	RC570B LED50/940 L150W12 SD PSD	-20 to +40 °C
911401570442	RC570B LED50/840 L150W12 CD PSU	-20 to +40 °C
911401570542	RC570B LED31/840 L150W12 CD PSU	-20 to +40 °C
911401571742	RC570B LED50/940 L150W12 CD PSD	-20 to +40 °C
911401565942	RC570B LED40/840 L120W6 SD PSU	-20 to +40 °C
911401566842	RC570B LED40/940 L120W6 SD PSD	-20 to +40 °C
911401567242	RC570B LED40/840 L120W6 CD PSU	-20 to +40 °C
911401567342	RC570B LED25/840 L120W6 CD PSU	-20 to +40 °C
911401568642	RC570B LED40/940 L120W6 CD PSD	-20 to +40 °C
911401569242	RC570B LED40/9TW L120W6 SD PSD	-20 to +40 °C
911401569542	RC570B LED40/9TW L120W6 CD PSD	-20 to +40 °C
911401570842	RC570X LED40/940 L120W6 SD WIA	-20 to +40 °C
911401571142	RC570X LED40/940 L120W6 CD WIA	-20 to +40 °C
911401565842	RC570B LED20/840 L60W6 SD PSU	-20 to +40 °C
911401566742	RC570B LED20/940 L60W6 SD PSD	-20 to +40 °C
911401567042	RC570B LED20/840 L60W6 CD PSU	-20 to +40 °C
911401567142	RC570B LED12/840 L60W6 CD PSU	-20 to +40 °C
911401568542	RC570B LED20/940 L60W6 CD PSD	-20 to +40 °C
911401569142	RC570B LED20/9TW L60W6 SD PSD	-20 to +40 °C
911401569442	RC570B LED20/9TW L60W6 CD PSD	-20 to +40 °C
911401570742	RC570X LED20/940 L60W6 SD WIA	-20 to +40 °C
911401571042	RC570X LED20/940 L60W6 CD WIA	-20 to +40 °C
911401556443	SP570P LED45/940 L60W6 PSU HEX	-20 to +40 °C

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Luminous flux tolerance
911401534642	SP570P LED40/840 L120W6 SD PSU	-10% / +10%
911401538542	SP570P LED40/940 L120W6 CD PSD	-10% / +10%

Order Code	Full Product Name	Luminous flux tolerance
911401540142	SP571P LED40/840 L120W6 CD PSU	-10% / +10%
911401534442	SP570P LED20/840 L60W6 SD PSU	-10% / +10%

SlimBalance G3

Order Code	Full Product Name	Luminous flux tolerance
911401538442	SP570P LED20/940 L60W6 CD PSD	-10% / +10%
911401539342	SP571P LED20/840 L60W6 SD PSU	-10% / +10%
911401539942	SP571P LED20/840 L60W6 CD PSU	-10% / +10%
911401568942	RC570B LED40/840 L120W12 SD PSU	+/-10%
911401569842	RC570B LED40/940 L120W12 SD PSD	+/-10%
911401570242	RC570B LED40/840 L120W12 CD PSU	+/-10%
911401570342	RC570B LED25/840 L120W12 CD PSU	+/-10%
911401571342	RC570X LED40/940 L120W12 SD WIA	+/-10%
911401571442	RC570X LED40/940 L120W12 CD WIA	+/-10%
911401571642	RC570B LED40/940 L120W12 CD PSD	+/-10%
911401542342	SP570P LED40/940 L120W9 SD PSD	-10% / +10%
911401572042	RC570B LED40/940 L60W6 PSD LC	+/-10%
911401574042	RC570B LED40/840 L60W6 PSU LC	+/-10%
911401566042	RC570B LED50/840 L150W6 SD PSU	+/-10%
911401566942	RC570B LED50/940 L150W6 SD PSD	+/-10%
911401567442	RC570B LED50/840 L150W6 CD PSU	+/-10%
911401567542	RC570B LED31/840 L150W6 CD PSU	+/-10%
911401568742	RC570B LED50/940 L150W6 CD PSD	+/-10%
911401569342	RC570B LED50/9TW L150W6 SD PSD	+/-10%
911401569642	RC570B LED50/9TW L150W6 CD PSD	+/-10%
911401570942	RC570X LED50/940 L150W6 SD WIA	+/-10%
911401571242	RC570X LED50/940 L150W6 CD WIA	+/-10%
911401569042	RC570B LED50/840 L150W12 SD PSU	+/-10%

Order Code	Full Product Name	Luminous flux tolerance
911401569942	RC570B LED50/940 L150W12 SD PSD	+/-10%
911401570442	RC570B LED50/840 L150W12 CD PSU	+/-10%
911401570542	RC570B LED31/840 L150W12 CD PSU	+/-10%
911401571742	RC570B LED50/940 L150W12 CD PSD	+/-10%
911401565942	RC570B LED40/840 L120W6 SD PSU	+/-10%
911401566842	RC570B LED40/940 L120W6 SD PSD	+/-10%
911401567242	RC570B LED40/840 L120W6 CD PSU	+/-10%
911401567342	RC570B LED25/840 L120W6 CD PSU	+/-10%
911401568642	RC570B LED40/940 L120W6 CD PSD	+/-10%
911401569242	RC570B LED40/9TW L120W6 SD PSD	+/-10%
911401569542	RC570B LED40/9TW L120W6 CD PSD	+/-10%
911401570842	RC570X LED40/940 L120W6 SD WIA	+/-10%
911401571142	RC570X LED40/940 L120W6 CD WIA	+/-10%
911401565842	RC570B LED20/840 L60W6 SD PSU	+/-10%
911401566742	RC570B LED20/940 L60W6 SD PSD	+/-10%
911401567042	RC570B LED20/840 L60W6 CD PSU	+/-10%
911401567142	RC570B LED12/840 L60W6 CD PSU	+/-10%
911401568542	RC570B LED20/940 L60W6 CD PSD	+/-10%
911401569142	RC570B LED20/9TW L60W6 SD PSD	+/-10%
911401569442	RC570B LED20/9TW L60W6 CD PSD	+/-10%
911401570742	RC570X LED20/940 L60W6 SD WIA	+/-10%
911401571042	RC570X LED20/940 L60W6 CD WIA	+/-10%
911401556443	SP570P LED45/940 L60W6 PSU HEX	+/-10%

