



Flexible and Elegant

SlimBalance G3

SlimBalance G3 SP570P is a flexible linear office offer which fits a variety of spaces like office, education. It offers flexible width of 35/60/90/120mm and length of 600/1200/1500mm to fit multiple applications. Geometric shapes help further create differentiated space. By means of its special designed structure, it offers quick and easy installation and maintenance. UGR19 is available for certain types through customized solution to provide a better visual comfort office environment.

Benefits

- High lm/w provides better energy saving
- Flexible width offers the feasibility to fit multiple ceiling spaces
- Dali and Interact interfaces available for easy system control
- Low UGR offer for visual comfort
- Multiple mounting installations and geometric shapes to cater for various applications
- Easy installation mechanism and modular design help save installation and maintenance time

Features

- System efficiency: max 130lm/W
- Product width with 35/60/90/120mm options
- CRI 80 and 90 available
- Lifetime: 50k hours (L70@ta=25deg)
- UGR19 available for certain types through customized solution
- Easy 'Slide and Click' mechanism for quick continuous installation

Application

- Open plan office
- Public indoor area
- Meeting/Training room
- Library

Specifications

SlimBalance G3

Ceiling type	Open ceiling office for suspension installation
	Plaster board ceiling for recessed installation and surface mounted installation
Mains Voltage	220-240V / 50 - 60Hz
Dimming	PSU: non-dimmable
	PSD: Dimmable via Dali-broadcasting
	WIA: Wireless control, compatible with Interact
	SIA: Wireless control, compatible with SNS210 sensor
Control system input	Dali
Integrated sensors	SNS210 available for SIA version
Material	Extrusion aluminium
Luminaire efficacy	130lm/w

Correlated color	840
temperature - CCT	940
Color Rendering index - 840, 940	
CRI	
Optic	UGR19 is available through lens design
Ingress protection	IP20
Driver replaceable	Yes
UGR	19 is available through lens design
	Suspension
	Recessed
Surface mounted	

Versions





SlimBalance G3


SlimBalance G3

SlimBalance G3



Dimensional drawing




Dimensional drawing




SP570 W6L60 SD shop drawing





SP570 W6L150 SD shop drawing




Product Type	Length (mm)	Width (mm)	Height (mm)
SP570	1235	60	7.52
SP570 L.C.	1235	60	8.22
SP570 L.C.	1235	60	8.52






SP570 W6L60 SD shop drawing



Dimensional drawing



SP570 W6L120 CD shop drawing



SP570 W6L60 SD shop drawing



SP570 W6L60 SD shop drawing

SlimBalance G3

Product details

SlimBalance G3



SlimBalance G3

SlimBalance G3



General Information	
Gear	-
Service tag	Yes
Operating and Electrical	
Protection class IEC	Safety class I
Line Frequency	50 or 60 Hz
Mechanical and Housing	
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
CE mark	Yes
ENEC mark	-
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Initial chromaticity	SDCM<=4

General Information

Order Code	Full Product Name	Driver included	Number of gear units
911401534842	SP570P LED50/840 L150W6 SD PSU	Yes	1 unit
911401537342	SP570P LED50/840 L150W6 CD PSU	Yes	1 unit
911401534642	SP570P LED40/840 L120W6 SD PSU	Yes	1 unit
911401534742	SP570P LED25/840 L120W6 SD PSU	Yes	1 unit
911401537142	SP570P LED40/840 L120W6 CD PSU	Yes	1 unit
911401537242	SP570P LED25/840 L120W6 CD PSU	Yes	1 unit
911401538542	SP570P LED40/940 L120W6 CD PSD	Yes	1 unit
911401540142	SP571P LED40/840 L120W6 CD PSU	Yes	1 unit
911401534442	SP570P LED20/840 L60W6 SD PSU	Yes	1 unit
911401534542	SP570P LED12/840 L60W6 SD PSU	Yes	1 unit
911401536942	SP570P LED20/840 L60W6 CD PSU	Yes	1 unit
911401537042	SP570P LED12/840 L60W6 CD PSU	Yes	1 unit
911401539342	SP571P LED20/840 L60W6 SD PSU	Yes	1 unit
911401539942	SP571P LED20/840 L60W6 CD PSU	Yes	1 unit
911401568942	RC570B LED40/840 L120W12 SD PSU	-	-
911401570242	RC570B LED40/840 L120W12 CD PSU	-	-
911401570342	RC570B LED25/840 L120W12 CD PSU	-	-
911401574042	RC570B LED40/840 L60W6 PSU LC	-	-
911401566042	RC570B LED50/840 L150W6 SD PSU	-	-
911401567442	RC570B LED50/840 L150W6 CD PSU	-	-
911401567542	RC570B LED31/840 L150W6 CD PSU	-	-
911401569342	RC570B LED50/9TW L150W6 SD PSD	-	-
911401569642	RC570B LED50/9TW L150W6 CD PSD	-	-
911401569042	RC570B LED50/840 L150W12 SD PSU	-	-
911401570442	RC570B LED50/840 L150W12 CD PSU	-	-
911401570542	RC570B LED31/840 L150W12 CD PSU	-	-
911401565942	RC570B LED40/840 L120W6 SD PSU	-	-
911401566842	RC570B LED40/940 L120W6 SD PSD	-	-

Order Code	Full Product Name	Driver included	Number of gear units
911401567242	RC570B LED40/840 L120W6 CD PSU	-	-
911401567342	RC570B LED25/840 L120W6 CD PSU	-	-
911401569242	RC570B LED40/9TW L120W6 SD PSD	-	-
911401569542	RC570B LED40/9TW L120W6 CD PSD	-	-
911401565842	RC570B LED20/840 L60W6 SD PSU	-	-
911401567042	RC570B LED20/840 L60W6 CD PSU	-	-
911401567142	RC570B LED12/840 L60W6 CD PSU	-	-
911401569142	RC570B LED20/9TW L60W6 SD PSD	-	-
911401569442	RC570B LED20/9TW L60W6 CD PSD	-	-

Light Technical (1/2)

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
911401534842	SP570P LED50/840 L150W6 SD PSU	120 degree(s)	4000 K	80	131.9506172839506 lm/W
911401537342	SP570P LED50/840 L150W6 CD PSU	120 degree(s)	4000 K	80	131.85185185185185 lm/W
911401534642	SP570P LED40/840 L120W6 SD PSU	120 degree(s)	4000 K	80	131.25 lm/W
911401534742	SP570P LED25/840 L120W6 SD PSU	120 degree(s)	4000 K	80	140.54054054054055 lm/W
911401537142	SP570P LED40/840 L120W6 CD PSU	120 degree(s)	4000 K	80	133.4375 lm/W
911401537242	SP570P LED25/840 L120W6 CD PSU	120 degree(s)	4000 K	80	138.9189189189189 lm/W
911401538542	SP570P LED40/940 L120W6 CD PSD	120 degree(s)	4000 K	90	119.70149253731343 lm/W
911401540142	SP571P LED40/840 L120W6 CD PSU	120 degree(s)	4000 K	80	136.27118644067798 lm/W
911401534442	SP570P LED20/840 L60W6 SD PSU	120 degree(s)	4000 K	80	118.85714285714286 lm/W
911401534542	SP570P LED12/840 L60W6 SD PSU	120 degree(s)	4000 K	80	125 lm/W
911401536942	SP570P LED20/840 L60W6 CD PSU	120 degree(s)	4000 K	80	118.85714285714286 lm/W
911401537042	SP570P LED12/840 L60W6 CD PSU	120 degree(s)	4000 K	80	125 lm/W
911401539342	SP571P LED20/840 L60W6 SD PSU	120 degree(s)	4000 K	80	147.85714285714286 lm/W
911401539942	SP571P LED20/840 L60W6 CD PSU	120 degree(s)	4000 K	80	147.85714285714286 lm/W
911401568942	RC570B LED40/840 L120W12 SD PSU	116 degree(s)	4000 K	>80	147 lm/W
911401570242	RC570B LED40/840 L120W12 CD PSU	116 degree(s)	4000 K	>80	147 lm/W
911401570342	RC570B LED25/840 L120W12 CD PSU	116 degree(s)	4000 K	>80	143 lm/W
911401574042	RC570B LED40/840 L60W6 PSU LC	116 degree(s)	4000 K	>80	133 lm/W

SlimBalance G3

Order Code	Full Product Name	Beam angle of light	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
		source			
911401566042	RC570B	116	4000 K	>80	132 lm/W
	LED50/840	degree(s)			
	L150W6 SD				
	PSU				
911401567442	RC570B	116	4000 K	>80	132 lm/W
	LED50/840	degree(s)			
	L150W6 CD				
	PSU				
911401567542	RC570B	116	4000 K	>80	138 lm/W
	LED31/840	degree(s)			
	L150W6 CD				
	PSU				
911401569342	RC570B	116	Tunable	>90	122 lm/W
	LED50/9TW	degree(s)	White		
	L150W6 SD				
	PSD				
911401569642	RC570B	116	Tunable	>90	122 lm/W
	LED50/9TW	degree(s)	White		
	L150W6 CD				
	PSD				
911401569042	RC570B	116	4000 K	>80	146 lm/W
	LED50/840	degree(s)			
	L150W12 SD				
	PSU				
911401570442	RC570B	116	4000 K	>80	146 lm/W
	LED50/840	degree(s)			
	L150W12 CD				
	PSU				
911401570542	RC570B	116	4000 K	>80	149 lm/W
	LED31/840	degree(s)			
	L150W12 CD				
	PSU				
911401565942	RC570B	116	4000 K	>80	135 lm/W
	LED40/840	degree(s)			
	L120W6 SD				
	PSU				
911401566842	RC570B	116	4000 K	>90	122 lm/W
	LED40/940	degree(s)			

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Number of light		Optic type
			sources		
911401534842	SP570P LED50/840 L150W6 SD PSU	5,344 lm	2		Beam angle 100°
911401537342	SP570P LED50/840 L150W6 CD PSU	5,340 lm	2		Beam angle 100°

Order Code	Full Product Name	Beam angle of light	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
		source			
911401567242	L120W6 SD				
	PSD				
911401567242	RC570B	116	4000 K	>80	135 lm/W
	LED40/840	degree(s)			
	L120W6 CD				
	PSU				
911401567342	RC570B	116	4000 K	>80	141 lm/W
	LED25/840	degree(s)			
	L120W6 CD				
	PSU				
911401569242	RC570B	116	Tunable	>90	119 lm/W
	LED40/9TW	degree(s)	White		
	L120W6 SD				
	PSD				
911401569542	RC570B	116	Tunable	>90	119 lm/W
	LED40/9TW	degree(s)	White		
	L120W6 CD				
	PSD				
911401565842	RC570B	116	4000 K	>80	119 lm/W
	LED20/840	degree(s)			
	L60W6 SD				
	PSU				
911401567042	RC570B	116	4000 K	>80	119 lm/W
	LED20/840	degree(s)			
	L60W6 CD				
	PSU				
911401567142	RC570B	116	4000 K	>80	125 lm/W
	LED12/840	degree(s)			
	L60W6 CD				
	PSU				
911401569142	RC570B	116	Tunable	>90	108 lm/W
	LED20/9TW	degree(s)	White		
	L60W6 SD				
	PSD				
911401569442	RC570B	116	Tunable	>90	108 lm/W
	LED20/9TW	degree(s)	White		
	L60W6 CD				
	PSD				

Order Code	Full Product Name	Luminous Flux	Number of light		Optic type
			sources		
911401534642	SP570P LED40/840 L120W6 SD PSU	4,200 lm	1		Beam angle 100°
911401534742	SP570P LED25/840 L120W6 SD PSU	2,600 lm	1		Beam angle 100°

SlimBalance G3

Order Code	Full Product Name	Luminous Flux	Number of light	
			sources	Optic type
911401537142	SP570P LED40/840 L120W6 CD PSU	4,270 lm	1	Beam angle 100°
911401537242	SP570P LED25/840 L120W6 CD PSU	2,570 lm	1	Beam angle 100°
911401538542	SP570P LED40/940 L120W6 CD PSD	4,010 lm	1	Beam angle 100°
911401540142	SP571P LED40/840 L120W6 CD PSU	4,020 lm	1	Beam angle 100°
911401534442	SP570P LED20/840 L60W6 SD PSU	2,080 lm	1	Beam angle 100°
911401534542	SP570P LED12/840 L60W6 SD PSU	1,250 lm	1	Beam angle 100°
911401536942	SP570P LED20/840 L60W6 CD PSU	2,080 lm	1	Beam angle 100°
911401537042	SP570P LED12/840 L60W6 CD PSU	1,250 lm	1	Beam angle 100°
911401539342	SP571P LED20/840 L60W6 SD PSU	2,070 lm	1	Beam angle 100°
911401539942	SP571P LED20/840 L60W6 CD PSU	2,070 lm	1	Beam angle 100°
911401568942	RC570B LED40/840 L120W12 SD PSU	3,980 lm	-	-
911401570242	RC570B LED40/840 L120W12 CD PSU	3,980 lm	-	-
911401570342	RC570B LED25/840 L120W12 CD PSU	2,500 lm	-	-
911401574042	RC570B LED40/840 L60W6 PSU LC	4,130 lm	-	-
911401566042	RC570B LED50/840 L150W6 SD PSU	5,344 lm	-	-
911401567442	RC570B LED50/840 L150W6 CD PSU	5,344 lm	-	-
911401567542	RC570B LED31/840 L150W6 CD PSU	3,250 lm	-	-

Operating and Electrical

Order Code	Full Product Name	Power		Suitable for random switching
		Input Voltage	Consumption	
911401534842	SP570P LED50/840 L150W6 SD PSU	220 to 240 V	40.5 W	No
911401537342	SP570P LED50/840 L150W6 CD PSU	220 to 240 V	40.5 W	No
911401534642	SP570P LED40/840 L120W6 SD PSU	220 to 240 V	32 W	No
911401534742	SP570P LED25/840 L120W6 SD PSU	220 to 240 V	18.5 W	No
911401537142	SP570P LED40/840 L120W6 CD PSU	220 to 240 V	32 W	No

Order Code	Full Product Name	Luminous Flux	Number of light	
			sources	Optic type
911401569342	RC570B LED50/9TW L150W6 SD PSD	5,020 lm	-	-
911401569642	RC570B LED50/9TW L150W6 CD PSD	5,020 lm	-	-
911401569042	RC570B LED50/840 L150W12 SD PSU	4,970 lm	-	-
911401570442	RC570B LED50/840 L150W12 CD PSU	4,970 lm	-	-
911401570542	RC570B LED31/840 L150W12 CD PSU	3,125 lm	-	-
911401565942	RC570B LED40/840 L120W6 SD PSU	4,400 lm	-	-
911401566842	RC570B LED40/940 L120W6 SD PSD	4,136 lm	-	-
911401567242	RC570B LED40/840 L120W6 CD PSU	4,400 lm	-	-
911401567342	RC570B LED25/840 L120W6 CD PSU	2,600 lm	-	-
911401569242	RC570B LED40/9TW L120W6 SD PSD	4,010 lm	-	-
911401569542	RC570B LED40/9TW L120W6 CD PSD	4,010 lm	-	-
911401565842	RC570B LED20/840 L60W6 SD PSU	2,080 lm	-	-
911401567042	RC570B LED20/840 L60W6 CD PSU	2,080 lm	-	-
911401567142	RC570B LED12/840 L60W6 CD PSU	1,250 lm	-	-
911401569142	RC570B LED20/9TW L60W6 SD PSD	1,950 lm	-	-
911401569442	RC570B LED20/9TW L60W6 CD PSD	1,950 lm	-	-

Order Code	Full Product Name	Input Voltage	Power	Suitable for random switching
			Consumption	
911401536942	SP570P LED20/840 L60W6 CD PSU	220 to 240 V	17.5 W	No
911401537042	SP570P LED12/840 L60W6 CD PSU	220 to 240 V	10 W	No
911401539342	SP571P LED20/840 L60W6 SD PSU	220 to 240 V	14 W	No
911401539942	SP571P LED20/840 L60W6 CD PSU	220 to 240 V	14 W	No
911401568942	RC570B LED40/840 L120W12 SD PSU	220-240 V	27 W	-
911401570242	RC570B LED40/840 L120W12 CD PSU	220-240 V	27 W	-
911401570342	RC570B LED25/840 L120W12 CD PSU	220-240 V	17.5 W	-
911401574042	RC570B LED40/840 L60W6 PSU LC	220-240 V	31 W	-
911401566042	RC570B LED50/840 L150W6 SD PSU	220-240 V	40.5 W	-
911401567442	RC570B LED50/840 L150W6 CD PSU	220-240 V	40.5 W	-
911401567542	RC570B LED31/840 L150W6 CD PSU	220-240 V	23.5 W	-
911401569342	RC570B LED50/9TW L150W6 SD PSD	220-240 V	41 W	-
911401569642	RC570B LED50/9TW L150W6 CD PSD	220-240 V	41 W	-
911401569042	RC570B LED50/840 L150W12 SD PSU	220-240 V	34 W	-

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
911401534842	SP570P LED50/840 L150W6 SD PSU	No	Not applicable
911401537342	SP570P LED50/840 L150W6 CD PSU	No	Not applicable
911401534642	SP570P LED40/840 L120W6 SD PSU	No	Not applicable
911401534742	SP570P LED25/840 L120W6 SD PSU	No	Not applicable
911401537142	SP570P LED40/840 L120W6 CD PSU	No	Not applicable
911401537242	SP570P LED25/840 L120W6 CD PSU	No	Not applicable
911401538542	SP570P LED40/940 L120W6 CD PSD	DALI	1%
911401540142	SP571P LED40/840 L120W6 CD PSU	No	Not applicable
911401534442	SP570P LED20/840 L60W6 SD PSU	No	Not applicable
911401534542	SP570P LED12/840 L60W6 SD PSU	No	Not applicable
911401536942	SP570P LED20/840 L60W6 CD PSU	No	Not applicable
911401537042	SP570P LED12/840 L60W6 CD PSU	No	Not applicable
911401539342	SP571P LED20/840 L60W6 SD PSU	No	Not applicable
911401539942	SP571P LED20/840 L60W6 CD PSU	No	Not applicable
911401568942	RC570B LED40/840 L120W12 SD PSU	-	-
911401570242	RC570B LED40/840 L120W12 CD PSU	-	-
911401570342	RC570B LED25/840 L120W12 CD PSU	-	-
911401574042	RC570B LED40/840 L60W6 PSU LC	-	-

Order Code	Full Product Name	Input Voltage	Power	Suitable for random switching
			Consumption	
911401570442	RC570B LED50/840 L150W12 CD PSU	220-240 V	34 W	-
911401570542	RC570B LED31/840 L150W12 CD PSU	220-240 V	21 W	-
911401565942	RC570B LED40/840 L120W6 SD PSU	220-240 V	32.5 W	-
911401566842	RC570B LED40/940 L120W6 SD PSD	220-240 V	34 W	-
911401567242	RC570B LED40/840 L120W6 CD PSU	220-240 V	32.5 W	-
911401567342	RC570B LED25/840 L120W6 CD PSU	220-240 V	18.5 W	-
911401569242	RC570B LED40/9TW L120W6 SD PSD	220-240 V	33.5 W	-
911401569542	RC570B LED40/9TW L120W6 CD PSD	220-240 V	33.5 W	-
911401565842	RC570B LED20/840 L60W6 SD PSU	220-240 V	17.5 W	-
911401567042	RC570B LED20/840 L60W6 CD PSU	220-240 V	17.5 W	-
911401567142	RC570B LED12/840 L60W6 CD PSU	220-240 V	10 W	-
911401569142	RC570B LED20/9TW L60W6 SD PSD	220-240 V	18 W	-
911401569442	RC570B LED20/9TW L60W6 CD PSD	220-240 V	18 W	-

Order Code	Full Product Name	Dimmable	Maximum dim level
911401566042	RC570B LED50/840 L150W6 SD PSU	-	-
911401567442	RC570B LED50/840 L150W6 CD PSU	-	-
911401567542	RC570B LED31/840 L150W6 CD PSU	-	-
911401569342	RC570B LED50/9TW L150W6 SD PSD	DALI	-
911401569642	RC570B LED50/9TW L150W6 CD PSD	DALI	-
911401569042	RC570B LED50/840 L150W12 SD PSU	-	-
911401570442	RC570B LED50/840 L150W12 CD PSU	-	-
911401570542	RC570B LED31/840 L150W12 CD PSU	-	-
911401565942	RC570B LED40/840 L120W6 SD PSU	-	-
911401566842	RC570B LED40/940 L120W6 SD PSD	DALI	-
911401567242	RC570B LED40/840 L120W6 CD PSU	-	-
911401567342	RC570B LED25/840 L120W6 CD PSU	-	-
911401569242	RC570B LED40/9TW L120W6 SD PSD	DALI	-
911401569542	RC570B LED40/9TW L120W6 CD PSD	DALI	-
911401565842	RC570B LED20/840 L60W6 SD PSU	-	-
911401567042	RC570B LED20/840 L60W6 CD PSU	-	-
911401567142	RC570B LED12/840 L60W6 CD PSU	-	-
911401569142	RC570B LED20/9TW L60W6 SD PSD	DALI	-

Order Code	Full Product Name	Dimmable	Maximum dim level
911401569442	RC570B LED20/9TW L60W6 CD PSD	DALI	-

Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Housing Color
911401534842	SP570P LED50/840 L150W6 SD PSU	Opal	White
911401537342	SP570P LED50/840 L150W6 CD PSU	Opal	White
911401534642	SP570P LED40/840 L120W6 SD PSU	Opal	White
911401534742	SP570P LED25/840 L120W6 SD PSU	Opal	White
911401537142	SP570P LED40/840 L120W6 CD PSU	Opal	White
911401537242	SP570P LED25/840 L120W6 CD PSU	Opal	White
911401538542	SP570P LED40/940 L120W6 CD PSD	Opal	White
911401540142	SP571P LED40/840 L120W6 CD PSU	Opal	White
911401534442	SP570P LED20/840 L60W6 SD PSU	Opal	White
911401534542	SP570P LED12/840 L60W6 SD PSU	Opal	White
911401536942	SP570P LED20/840 L60W6 CD PSU	Opal	White
911401537042	SP570P LED12/840 L60W6 CD PSU	Opal	White
911401539342	SP571P LED20/840 L60W6 SD PSU	Opal	White
911401539942	SP571P LED20/840 L60W6 CD PSU	Opal	White
911401568942	RC570B LED40/840 L120W12 SD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401570242	RC570B LED40/840 L120W12 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401570342	RC570B LED25/840 L120W12 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401574042	RC570B LED40/840 L60W6 PSU LC	Polycarbonate bowl/cover frosted	White RAL 9003
911401566042	RC570B LED50/840 L150W6 SD PSU	Polycarbonate bowl/cover frosted	White RAL 9003

Order Code	Full Product Name	Optical cover type	Housing Color
911401567442	RC570B LED50/840 L150W6 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401567542	RC570B LED31/840 L150W6 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401569342	RC570B LED50/9TW L150W6 SD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401569642	RC570B LED50/9TW L150W6 CD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401569042	RC570B LED50/840 L150W12 SD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401570442	RC570B LED50/840 L150W12 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401570542	RC570B LED31/840 L150W12 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401565942	RC570B LED40/840 L120W6 SD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401566842	RC570B LED40/940 L120W6 SD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401567242	RC570B LED40/840 L120W6 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401567342	RC570B LED25/840 L120W6 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401569242	RC570B LED40/9TW L120W6 SD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401569542	RC570B LED40/9TW L120W6 CD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401565842	RC570B LED20/840 L60W6 SD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401567042	RC570B LED20/840 L60W6 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401567142	RC570B LED12/840 L60W6 CD PSU	Polycarbonate bowl/cover frosted	White RAL 9003
911401569142	RC570B LED20/9TW L60W6 SD PSD	Polycarbonate bowl/cover frosted	White RAL 9003
911401569442	RC570B LED20/9TW L60W6 CD PSD	Polycarbonate bowl/cover frosted	White RAL 9003

Approval and Application

Order Code	Full Product Name	Ambient temperature range
911401534842	SP570P LED50/840 L150W6 SD PSU	-20 °C to 40 °C
911401537342	SP570P LED50/840 L150W6 CD PSU	-20 °C to 40 °C
911401534642	SP570P LED40/840 L120W6 SD PSU	-20 °C to 40 °C
911401534742	SP570P LED25/840 L120W6 SD PSU	-20 °C to 40 °C

Order Code	Full Product Name	Ambient temperature range
911401537142	SP570P LED40/840 L120W6 CD PSU	-20 °C to 40 °C
911401537242	SP570P LED25/840 L120W6 CD PSU	-20 °C to 40 °C
911401538542	SP570P LED40/940 L120W6 CD PSD	-20 °C to 40 °C
911401540142	SP571P LED40/840 L120W6 CD PSU	-20 °C to 40 °C

Order Code	Full Product Name	Ambient temperature range
911401534442	SP570P LED20/840 L60W6 SD PSU	-20 °C to 40 °C
911401534542	SP570P LED12/840 L60W6 SD PSU	-20 °C to 40 °C
911401536942	SP570P LED20/840 L60W6 CD PSU	-20 °C to 40 °C
911401537042	SP570P LED12/840 L60W6 CD PSU	-20 °C to 40 °C
911401539342	SP571P LED20/840 L60W6 SD PSU	-20 °C to 40 °C
911401539942	SP571P LED20/840 L60W6 CD PSU	-20 °C to 40 °C
911401568942	RC570B LED40/840 L120W12 SD PSU	-20 to +40 °C
911401570242	RC570B LED40/840 L120W12 CD PSU	-20 to +40 °C
911401570342	RC570B LED25/840 L120W12 CD PSU	-20 to +40 °C
911401574042	RC570B LED40/840 L60W6 PSU LC	-20 to +40 °C
911401566042	RC570B LED50/840 L150W6 SD PSU	-20 to +40 °C
911401567442	RC570B LED50/840 L150W6 CD PSU	-20 to +40 °C
911401567542	RC570B LED31/840 L150W6 CD PSU	-20 to +40 °C
911401569342	RC570B LED50/9TW L150W6 SD PSD	-20 to +40 °C
911401569642	RC570B LED50/9TW L150W6 CD PSD	-20 to +40 °C

Order Code	Full Product Name	Ambient temperature range
911401569042	RC570B LED50/840 L150W12 SD PSU	-20 to +40 °C
911401570442	RC570B LED50/840 L150W12 CD PSU	-20 to +40 °C
911401570542	RC570B LED31/840 L150W12 CD PSU	-20 to +40 °C
911401565942	RC570B LED40/840 L120W6 SD PSU	-20 to +40 °C
911401566842	RC570B LED40/940 L120W6 SD PSD	-20 to +40 °C
911401567242	RC570B LED40/840 L120W6 CD PSU	-20 to +40 °C
911401567342	RC570B LED25/840 L120W6 CD PSU	-20 to +40 °C
911401569242	RC570B LED40/9TW L120W6 SD PSD	-20 to +40 °C
911401569542	RC570B LED40/9TW L120W6 CD PSD	-20 to +40 °C
911401565842	RC570B LED20/840 L60W6 SD PSU	-20 to +40 °C
911401567042	RC570B LED20/840 L60W6 CD PSU	-20 to +40 °C
911401567142	RC570B LED12/840 L60W6 CD PSU	-20 to +40 °C
911401569142	RC570B LED20/9TW L60W6 SD PSD	-20 to +40 °C
911401569442	RC570B LED20/9TW L60W6 CD PSD	-20 to +40 °C

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Luminous flux tolerance
911401534842	SP570P LED50/840 L150W6 SD PSU	-10% / +10%
911401537342	SP570P LED50/840 L150W6 CD PSU	-10% / +10%
911401534642	SP570P LED40/840 L120W6 SD PSU	-10% / +10%
911401534742	SP570P LED25/840 L120W6 SD PSU	-10% / +10%
911401537142	SP570P LED40/840 L120W6 CD PSU	-10% / +10%
911401537242	SP570P LED25/840 L120W6 CD PSU	-10% / +10%
911401538542	SP570P LED40/940 L120W6 CD PSD	-10% / +10%
911401540142	SP571P LED40/840 L120W6 CD PSU	-10% / +10%
911401534442	SP570P LED20/840 L60W6 SD PSU	-10% / +10%
911401534542	SP570P LED12/840 L60W6 SD PSU	-10% / +10%
911401536942	SP570P LED20/840 L60W6 CD PSU	-10% / +10%
911401537042	SP570P LED12/840 L60W6 CD PSU	-10% / +10%
911401539342	SP571P LED20/840 L60W6 SD PSU	-10% / +10%
911401539942	SP571P LED20/840 L60W6 CD PSU	-10% / +10%
911401568942	RC570B LED40/840 L120W12 SD PSU	+/-10%
911401570242	RC570B LED40/840 L120W12 CD PSU	+/-10%
911401570342	RC570B LED25/840 L120W12 CD PSU	+/-10%
911401574042	RC570B LED40/840 L60W6 PSU LC	+/-10%
911401566042	RC570B LED50/840 L150W6 SD PSU	+/-10%

Order Code	Full Product Name	Luminous flux tolerance
911401567442	RC570B LED50/840 L150W6 CD PSU	+/-10%
911401567542	RC570B LED31/840 L150W6 CD PSU	+/-10%
911401569342	RC570B LED50/9TW L150W6 SD PSD	+/-10%
911401569642	RC570B LED50/9TW L150W6 CD PSD	+/-10%
911401569042	RC570B LED50/840 L150W12 SD PSU	+/-10%
911401570442	RC570B LED50/840 L150W12 CD PSU	+/-10%
911401570542	RC570B LED31/840 L150W12 CD PSU	+/-10%
911401565942	RC570B LED40/840 L120W6 SD PSU	+/-10%
911401566842	RC570B LED40/940 L120W6 SD PSD	+/-10%
911401567242	RC570B LED40/840 L120W6 CD PSU	+/-10%
911401567342	RC570B LED25/840 L120W6 CD PSU	+/-10%
911401569242	RC570B LED40/9TW L120W6 SD PSD	+/-10%
911401569542	RC570B LED40/9TW L120W6 CD PSD	+/-10%
911401565842	RC570B LED20/840 L60W6 SD PSU	+/-10%
911401567042	RC570B LED20/840 L60W6 CD PSU	+/-10%
911401567142	RC570B LED12/840 L60W6 CD PSU	+/-10%
911401569142	RC570B LED20/9TW L60W6 SD PSD	+/-10%
911401569442	RC570B LED20/9TW L60W6 CD PSD	+/-10%

