



Compact LED spot that's the right fit for energy savings

StoreFit

Retailers are always looking for ways to reduce their environmental footprint and energy cost. With this StoreFit projector, conventional CDM luminaires can be replaced effortlessly with LED, leading to significantly less power consumption. The subtle and compact design reduces the visibility of the StoreFit projector in the store, and keeps shoppers' attention on the merchandise available on the shelves. As an affordable LED projector, this spot will enable you to start saving on energy costs straight away.

Benefits

- The small spot head results in a very discreet design
- Perfect LED replacement for CDM conventional luminaires
- Low initial investment

Features

- Up to 3900 lm
- Choose from a white or black finish (ST201T and ST210Y)
- Available in 3000K, 4000K and PremiumWhite 3000K
- Medium beam or wide beam reflector options



Application

- Convenience stores
- Supermarkets & hypermarkets
- Fashion stores

Warnings and Safety

- Cleaning the optic should only be done with pressurized air. Touching the LED or reflector is forbidden.
- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove

Dimensional drawing



Product details

StoreFit ST210T, black



General Information	
Driver included	Yes
Light source replaceable	No
Light Technical	
Beam angle of light source	120 degree(s)
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Mechanical and Housing	
Mech. impact protection code	IK02
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	+10 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.5
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Number of gear units	Service tag
910505102057	ST210Y 19S/FMT PSU MB WH	2 units	Yes
910505102058	ST210Y 19S/FMT DIA MB WH	2 units	Yes
910505102059	ST210Y 27S/830 PSU MB WH	2 units	Yes
910505102060	ST210Y 27S/830 DIA MB WH	2 units	Yes
910505102061	ST210Y 27S/840 PSU MB WH	2 units	Yes
910505102062	ST210Y 27S/840 DIA MB WH	2 units	Yes
910505102063	ST210Y 27S/PW930 PSU MB WH	2 units	Yes
910505102064	ST210Y 27S/PW930 DIA MB WH	2 units	Yes
910505102065	ST210Y 39S/830 PSU MB WH	2 units	Yes
910505102066	ST210Y 39S/830 DIA MB WH	2 units	Yes
910505102067	ST210Y 39S/840 PSU MB WH	2 units	Yes
910505102068	ST210Y 39S/840 DIA MB WH	2 units	Yes
910505102069	ST210Y 39S/PW930 PSU MB WH	2 units	Yes
910505102070	ST210Y 39S/PW930 DIA MB WH	2 units	Yes
910505102043	ST210T 27S/830 PSU MB BK	1 unit	Yes
910505102044	ST210T 27S/830 PSU WB BK	1 unit	Yes
910505102047	ST210T 39S/830 PSU MB BK	1 unit	Yes
910505102048	ST210T 39S/830 PSU WB BK	1 unit	Yes
910505102051	ST210T 27S/840 PSU MB BK	1 unit	Yes
910505102052	ST210T 27S/840 PSU WB BK	1 unit	Yes
910505102055	ST210T 39S/840 PSU MB BK	1 unit	Yes
910505102056	ST210T 39S/840 PSU WB BK	1 unit	Yes
910505102550	ST210T 27S/830 WIA MB BK	1 unit	Yes
910505102551	ST210T 27S/830 WIA WB BK	1 unit	Yes
910505102554	ST210T 39S/830 WIA MB BK	1 unit	Yes
910505102555	ST210T 39S/830 WIA WB BK	1 unit	Yes
910505102558	ST210T 27S/840 WIA MB BK	1 unit	Yes
910505102559	ST210T 27S/840 WIA WB BK	1 unit	Yes
910505102562	ST210T 39S/840 WIA MB BK	1 unit	Yes
910505102563	ST210T 39S/840 WIA WB BK	1 unit	Yes
910505102041	ST210T 27S/830 PSU MB WH	1 unit	-
910505102042	ST210T 27S/830 PSU WB WH	1 unit	Yes
910505102045	ST210T 39S/830 PSU MB WH	1 unit	Yes
910505102046	ST210T 39S/830 PSU WB WH	1 unit	Yes
910505102049	ST210T 27S/840 PSU MB WH	1 unit	Yes
910505102050	ST210T 27S/840 PSU WB WH	1 unit	Yes
910505102053	ST210T 39S/840 PSU MB WH	1 unit	Yes
910505102054	ST210T 39S/840 PSU WB WH	1 unit	Yes
910505102548	ST210T 27S/830 WIA MB WH	1 unit	Yes
910505102549	ST210T 27S/830 WIA WB WH	1 unit	Yes
910505102552	ST210T 39S/830 WIA MB WH	1 unit	Yes
910505102553	ST210T 39S/830 WIA WB WH	1 unit	Yes
910505102556	ST210T 27S/840 WIA MB WH	1 unit	Yes
910505102557	ST210T 27S/840 WIA WB WH	1 unit	Yes
910505102560	ST210T 39S/840 WIA MB WH	1 unit	Yes
910505102561	ST210T 39S/840 WIA WB WH	1 unit	Yes

Light Technical (1/2)

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505102057	ST210Y 19S/FMT PSU MB WH	3000 K	>90	79 lm/W	3,900 lm
910505102058	ST210Y 19S/FMT DIA MB WH	3000 K	>90	79 lm/W	3,900 lm
910505102059	ST210Y 27S/830 PSU MB WH	3000 K	>80	136 lm/W	5,400 lm
910505102060	ST210Y 27S/830 DIA MB WH	3000 K	>80	136 lm/W	5,400 lm
910505102061	ST210Y 27S/840 PSU MB WH	4000 K	>80	142 lm/W	5,600 lm
910505102062	ST210Y 27S/840 DIA MB WH	4000 K	>80	143 lm/W	5,600 lm
910505102063	ST210Y 27S/ PW930 PSU MB WH	3000 K	>90	134 lm/W	5,400 lm
910505102064	ST210Y 27S/ PW930 DIA MB WH	3000 K	>90	139 lm/W	5,400 lm
910505102065	ST210Y 39S/830 PSU MB WH	3000 K	>80	142 lm/W	4,100 lm
910505102066	ST210Y 39S/830 DIA MB WH	3000 K	>80	142 lm/W	8,200 lm
910505102067	ST210Y 39S/840 PSU MB WH	4000 K	>80	147 lm/W	8,400 lm
910505102068	ST210Y 39S/840 DIA MB WH	4000 K	>80	147 lm/W	8,400 lm
910505102069	ST210Y 39S/ PW930 PSU MB WH	3000 K	>90	130 lm/W	8,000 lm
910505102070	ST210Y 39S/ PW930 DIA MB WH	3000 K	>90	130 lm/W	8,000 lm
910505102043	ST210T 27S/830 PSU MB BK	3000 K	>80	134 lm/W	2,700 lm
910505102044	ST210T 27S/830 PSU WB BK	3000 K	>80	134 lm/W	2,700 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505102047	ST210T 39S/830 PSU MB BK	3000 K	>80	139 lm/W	4,100 lm
910505102048	ST210T 39S/830 PSU WB BK	3000 K	>80	139 lm/W	4,100 lm
910505102051	ST210T 27S/840 PSU MB BK	4000 K	>80	140 lm/W	2,800 lm
910505102052	ST210T 27S/840 PSU WB BK	4000 K	>80	140 lm/W	2,800 lm
910505102055	ST210T 39S/840 PSU MB BK	4000 K	>80	144 lm/W	4,200 lm
910505102056	ST210T 39S/840 PSU WB BK	4000 K	>80	144 lm/W	4,200 lm
910505102550	ST210T 27S/830 WIA MB BK	3000 K	>80	128 lm/W	2,700 lm
910505102551	ST210T 27S/830 WIA WB BK	3000 K	>80	128 lm/W	2,700 lm
910505102554	ST210T 39S/830 WIA MB BK	3000 K	>80	134 lm/W	4,100 lm
910505102555	ST210T 39S/830 WIA WB BK	3000 K	>80	134 lm/W	4,100 lm
910505102558	ST210T 27S/840 WIA MB BK	4000 K	>80	133 lm/W	2,800 lm
910505102559	ST210T 27S/840 WIA WB BK	4000 K	>80	133 lm/W	2,800 lm
910505102562	ST210T 39S/840 WIA MB BK	4000 K	>80	138 lm/W	4,200 lm
910505102563	ST210T 39S/840 WIA WB BK	4000 K	>80	138 lm/W	4,200 lm
910505102041	ST210T 27S/830 PSU MB WH	3000 K	80	134 lm/W	2,700 lm
910505102042	ST210T 27S/830 PSU WB WH	3000 K	>80	134 lm/W	2,700 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505102045	ST210T 39S/830 PSU MB WH	3000 K	>80	139 lm/W	4,100 lm
910505102046	ST210T 39S/830 PSU WB WH	3000 K	>80	139 lm/W	4,100 lm
910505102049	ST210T 27S/840 PSU MB WH	4000 K	>80	140 lm/W	2,800 lm
910505102050	ST210T 27S/840 PSU WB WH	4000 K	>80	140 lm/W	2,800 lm
910505102053	ST210T 39S/840 PSU MB WH	4000 K	>80	144 lm/W	4,200 lm
910505102054	ST210T 39S/840 PSU WB WH	4000 K	>80	144 lm/W	4,200 lm
910505102548	ST210T 27S/830 WIA MB WH	3000 K	>80	128 lm/W	2,700 lm

Light Technical (2/2)

Order Code	Full Product Name	Optic type
910505102057	ST210Y 19S/FMT PSU MB WH	Medium beam
910505102058	ST210Y 19S/FMT DIA MB WH	Medium beam
910505102059	ST210Y 27S/830 PSU MB WH	Medium beam
910505102060	ST210Y 27S/830 DIA MB WH	Medium beam
910505102061	ST210Y 27S/840 PSU MB WH	Medium beam
910505102062	ST210Y 27S/840 DIA MB WH	Medium beam
910505102063	ST210Y 27S/PW930 PSU MB WH	Medium beam
910505102064	ST210Y 27S/PW930 DIA MB WH	Medium beam
910505102065	ST210Y 39S/830 PSU MB WH	Medium beam
910505102066	ST210Y 39S/830 DIA MB WH	Medium beam
910505102067	ST210Y 39S/840 PSU MB WH	Medium beam
910505102068	ST210Y 39S/840 DIA MB WH	Medium beam
910505102069	ST210Y 39S/PW930 PSU MB WH	Medium beam
910505102070	ST210Y 39S/PW930 DIA MB WH	Medium beam
910505102043	ST210T 27S/830 PSU MB BK	Medium beam
910505102044	ST210T 27S/830 PSU WB BK	Wide beam
910505102047	ST210T 39S/830 PSU MB BK	Medium beam
910505102048	ST210T 39S/830 PSU WB BK	Wide beam
910505102051	ST210T 27S/840 PSU MB BK	Medium beam
910505102052	ST210T 27S/840 PSU WB BK	Wide beam
910505102055	ST210T 39S/840 PSU MB BK	Medium beam
910505102056	ST210T 39S/840 PSU WB BK	Wide beam
910505102550	ST210T 27S/830 WIA MB BK	Medium beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505102549	ST210T 27S/830 WIA WB WH	3000 K	>80	128 lm/W	2,700 lm
910505102552	ST210T 39S/830 WIA MB WH	3000 K	>80	134 lm/W	4,100 lm
910505102553	ST210T 39S/830 WIA WB WH	3000 K	>80	134 lm/W	4,100 lm
910505102556	ST210T 27S/840 WIA MB WH	4000 K	>80	133 lm/W	2,800 lm
910505102557	ST210T 27S/840 WIA WB WH	4000 K	>80	133 lm/W	2,800 lm
910505102560	ST210T 39S/840 WIA MB WH	4000 K	>80	138 lm/W	4,200 lm
910505102561	ST210T 39S/840 WIA WB WH	4000 K	>80	138 lm/W	4,200 lm

Order Code	Full Product Name	Optic type
910505102551	ST210T 27S/830 WIA WB BK	Wide beam
910505102554	ST210T 39S/830 WIA MB BK	Medium beam
910505102555	ST210T 39S/830 WIA WB BK	Wide beam
910505102558	ST210T 27S/840 WIA MB BK	Medium beam
910505102559	ST210T 27S/840 WIA WB BK	Wide beam
910505102562	ST210T 39S/840 WIA MB BK	Medium beam
910505102563	ST210T 39S/840 WIA WB BK	Wide beam
910505102041	ST210T 27S/830 PSU MB WH	Medium beam
910505102042	ST210T 27S/830 PSU WB WH	Wide beam
910505102045	ST210T 39S/830 PSU MB WH	Medium beam
910505102046	ST210T 39S/830 PSU WB WH	Wide beam
910505102049	ST210T 27S/840 PSU MB WH	Medium beam
910505102050	ST210T 27S/840 PSU WB WH	Wide beam
910505102053	ST210T 39S/840 PSU MB WH	Medium beam
910505102054	ST210T 39S/840 PSU WB WH	Wide beam
910505102548	ST210T 27S/830 WIA MB WH	Medium beam
910505102549	ST210T 27S/830 WIA WB WH	Wide beam
910505102552	ST210T 39S/830 WIA MB WH	Medium beam
910505102553	ST210T 39S/830 WIA WB WH	Wide beam
910505102556	ST210T 27S/840 WIA MB WH	Medium beam
910505102557	ST210T 27S/840 WIA WB WH	Wide beam
910505102560	ST210T 39S/840 WIA MB WH	Medium beam
910505102561	ST210T 39S/840 WIA WB WH	Wide beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910505102057	ST210Y 19S/FMT PSU MB WH	50 W
910505102058	ST210Y 19S/FMT DIA MB WH	49 W
910505102059	ST210Y 27S/830 PSU MB WH	39 W
910505102060	ST210Y 27S/830 DIA MB WH	39 W
910505102061	ST210Y 27S/840 PSU MB WH	39 W
910505102062	ST210Y 27S/840 DIA MB WH	39 W
910505102063	ST210Y 27S/PW930 PSU MB WH	40 W
910505102064	ST210Y 27S/PW930 DIA MB WH	40 W
910505102065	ST210Y 39S/830 PSU MB WH	29 W
910505102066	ST210Y 39S/830 DIA MB WH	58 W
910505102067	ST210Y 39S/840 PSU MB WH	58 W
910505102068	ST210Y 39S/840 DIA MB WH	58 W
910505102069	ST210Y 39S/PW930 PSU MB WH	62 W
910505102070	ST210Y 39S/PW930 DIA MB WH	62 W
910505102043	ST210T 27S/830 PSU MB BK	20 W
910505102044	ST210T 27S/830 PSU WB BK	20 W
910505102047	ST210T 39S/830 PSU MB BK	29.5 W
910505102048	ST210T 39S/830 PSU WB BK	29.5 W
910505102051	ST210T 27S/840 PSU MB BK	20 W
910505102052	ST210T 27S/840 PSU WB BK	20 W
910505102055	ST210T 39S/840 PSU MB BK	29.5 W
910505102056	ST210T 39S/840 PSU WB BK	29.5 W
910505102550	ST210T 27S/830 WIA MB BK	21 W

Order Code	Full Product Name	Power Consumption
910505102551	ST210T 27S/830 WIA WB BK	21 W
910505102554	ST210T 39S/830 WIA MB BK	30.5 W
910505102555	ST210T 39S/830 WIA WB BK	30.5 W
910505102558	ST210T 27S/840 WIA MB BK	21 W
910505102559	ST210T 27S/840 WIA WB BK	21 W
910505102562	ST210T 39S/840 WIA MB BK	30.5 W
910505102563	ST210T 39S/840 WIA WB BK	30.5 W
910505102041	ST210T 27S/830 PSU MB WH	20 W
910505102042	ST210T 27S/830 PSU WB WH	20 W
910505102045	ST210T 39S/830 PSU MB WH	29.5 W
910505102046	ST210T 39S/830 PSU WB WH	29.5 W
910505102049	ST210T 27S/840 PSU MB WH	20 W
910505102050	ST210T 27S/840 PSU WB WH	20 W
910505102053	ST210T 39S/840 PSU MB WH	29.5 W
910505102054	ST210T 39S/840 PSU WB WH	29.5 W
910505102548	ST210T 27S/830 WIA MB WH	21 W
910505102549	ST210T 27S/830 WIA WB WH	21 W
910505102552	ST210T 39S/830 WIA MB WH	30.5 W
910505102553	ST210T 39S/830 WIA WB WH	30.5 W
910505102556	ST210T 27S/840 WIA MB WH	21 W
910505102557	ST210T 27S/840 WIA WB WH	21 W
910505102560	ST210T 39S/840 WIA MB WH	30.5 W
910505102561	ST210T 39S/840 WIA WB WH	30.5 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
910505102057	ST210Y 19S/FMT PSU MB WH	No	Not applicable
910505102058	ST210Y 19S/FMT DIA MB WH	Yes	1%
910505102059	ST210Y 27S/830 PSU MB WH	No	Not applicable
910505102060	ST210Y 27S/830 DIA MB WH	Yes	1%
910505102061	ST210Y 27S/840 PSU MB WH	No	Not applicable
910505102062	ST210Y 27S/840 DIA MB WH	Yes	1%
910505102063	ST210Y 27S/PW930 PSU MB WH	No	Not applicable
910505102064	ST210Y 27S/PW930 DIA MB WH	Yes	1%
910505102065	ST210Y 39S/830 PSU MB WH	No	Not applicable
910505102066	ST210Y 39S/830 DIA MB WH	Yes	1%
910505102067	ST210Y 39S/840 PSU MB WH	No	Not applicable
910505102068	ST210Y 39S/840 DIA MB WH	Yes	1%
910505102069	ST210Y 39S/PW930 PSU MB WH	No	Not applicable
910505102070	ST210Y 39S/PW930 DIA MB WH	Yes	1%
910505102043	ST210T 27S/830 PSU MB BK	No	Not applicable
910505102044	ST210T 27S/830 PSU WB BK	No	Not applicable
910505102047	ST210T 39S/830 PSU MB BK	No	Not applicable
910505102048	ST210T 39S/830 PSU WB BK	No	Not applicable
910505102051	ST210T 27S/840 PSU MB BK	No	Not applicable
910505102052	ST210T 27S/840 PSU WB BK	No	Not applicable
910505102055	ST210T 39S/840 PSU MB BK	No	Not applicable
910505102056	ST210T 39S/840 PSU WB BK	No	Not applicable
910505102550	ST210T 27S/830 WIA MB BK	Yes	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim level
910505102551	ST210T 27S/830 WIA WB BK	Yes	Not applicable
910505102554	ST210T 39S/830 WIA MB BK	Yes	Not applicable
910505102555	ST210T 39S/830 WIA WB BK	Yes	Not applicable
910505102558	ST210T 27S/840 WIA MB BK	Yes	Not applicable
910505102559	ST210T 27S/840 WIA WB BK	Yes	Not applicable
910505102562	ST210T 39S/840 WIA MB BK	Yes	Not applicable
910505102563	ST210T 39S/840 WIA WB BK	Yes	Not applicable
910505102041	ST210T 27S/830 PSU MB WH	No	Not applicable
910505102042	ST210T 27S/830 PSU WB WH	No	Not applicable
910505102045	ST210T 39S/830 PSU MB WH	No	Not applicable
910505102046	ST210T 39S/830 PSU WB WH	No	Not applicable
910505102049	ST210T 27S/840 PSU MB WH	No	Not applicable
910505102050	ST210T 27S/840 PSU WB WH	No	Not applicable
910505102053	ST210T 39S/840 PSU MB WH	No	Not applicable
910505102054	ST210T 39S/840 PSU WB WH	No	Not applicable
910505102548	ST210T 27S/830 WIA MB WH	Yes	Not applicable
910505102549	ST210T 27S/830 WIA WB WH	Yes	Not applicable
910505102552	ST210T 39S/830 WIA MB WH	Yes	Not applicable
910505102553	ST210T 39S/830 WIA WB WH	Yes	Not applicable
910505102556	ST210T 27S/840 WIA MB WH	Yes	Not applicable
910505102557	ST210T 27S/840 WIA WB WH	Yes	Not applicable
910505102560	ST210T 39S/840 WIA MB WH	Yes	Not applicable
910505102561	ST210T 39S/840 WIA WB WH	Yes	Not applicable

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910505102057	ST210Y 19S/FMT PSU MB WH	White
910505102058	ST210Y 19S/FMT DIA MB WH	White
910505102059	ST210Y 27S/830 PSU MB WH	White
910505102060	ST210Y 27S/830 DIA MB WH	White
910505102061	ST210Y 27S/840 PSU MB WH	White
910505102062	ST210Y 27S/840 DIA MB WH	White
910505102063	ST210Y 27S/PW930 PSU MB WH	White
910505102064	ST210Y 27S/PW930 DIA MB WH	White
910505102065	ST210Y 39S/830 PSU MB WH	White
910505102066	ST210Y 39S/830 DIA MB WH	White
910505102067	ST210Y 39S/840 PSU MB WH	White
910505102068	ST210Y 39S/840 DIA MB WH	White
910505102069	ST210Y 39S/PW930 PSU MB WH	White
910505102070	ST210Y 39S/PW930 DIA MB WH	White
910505102043	ST210T 27S/830 PSU MB BK	Black
910505102044	ST210T 27S/830 PSU WB BK	Black
910505102047	ST210T 39S/830 PSU MB BK	Black
910505102048	ST210T 39S/830 PSU WB BK	Black
910505102051	ST210T 27S/840 PSU MB BK	Black
910505102052	ST210T 27S/840 PSU WB BK	Black
910505102055	ST210T 39S/840 PSU MB BK	Black
910505102056	ST210T 39S/840 PSU WB BK	Black
910505102550	ST210T 27S/830 WIA MB BK	Black

Order Code	Full Product Name	Housing Color
910505102551	ST210T 27S/830 WIA WB BK	Black
910505102554	ST210T 39S/830 WIA MB BK	Black
910505102555	ST210T 39S/830 WIA WB BK	Black
910505102558	ST210T 27S/840 WIA MB BK	Black
910505102559	ST210T 27S/840 WIA WB BK	Black
910505102562	ST210T 39S/840 WIA MB BK	Black
910505102563	ST210T 39S/840 WIA WB BK	Black
910505102041	ST210T 27S/830 PSU MB WH	White
910505102042	ST210T 27S/830 PSU WB WH	White
910505102045	ST210T 39S/830 PSU MB WH	White
910505102046	ST210T 39S/830 PSU WB WH	White
910505102049	ST210T 27S/840 PSU MB WH	White
910505102050	ST210T 27S/840 PSU WB WH	White
910505102053	ST210T 39S/840 PSU MB WH	White
910505102054	ST210T 39S/840 PSU WB WH	White
910505102548	ST210T 27S/830 WIA MB WH	White
910505102549	ST210T 27S/830 WIA WB WH	White
910505102552	ST210T 39S/830 WIA MB WH	White
910505102553	ST210T 39S/830 WIA WB WH	White
910505102556	ST210T 27S/840 WIA MB WH	White
910505102557	ST210T 27S/840 WIA WB WH	White
910505102560	ST210T 39S/840 WIA MB WH	White
910505102561	ST210T 39S/840 WIA WB WH	White

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505102057	ST210Y 19S/FMT PSU MB WH	(0.457,0.385)<3
910505102058	ST210Y 19S/FMT DIA MB WH	(0.457,0.385)<3
910505102059	ST210Y 27S/830 PSU MB WH	(0.434,0.403)<3
910505102060	ST210Y 27S/830 DIA MB WH	(0.434,0.403)<3
910505102061	ST210Y 27S/840 PSU MB WH	(0.382,0.380)<3
910505102062	ST210Y 27S/840 DIA MB WH	(0.382,0.380)<3
910505102063	ST210Y 27S/PW930 PSU MB WH	(0.422,0.386)<2
910505102064	ST210Y 27S/PW930 DIA MB WH	(0.422,0.386)<2
910505102065	ST210Y 39S/830 PSU MB WH	(0.434,0.403)<3
910505102066	ST210Y 39S/830 DIA MB WH	(0.434,0.403)<3
910505102067	ST210Y 39S/840 PSU MB WH	(0.382,0.380)<3
910505102068	ST210Y 39S/840 DIA MB WH	(0.382,0.380)<3
910505102069	ST210Y 39S/PW930 PSU MB WH	(0.422,0.386)<2
910505102070	ST210Y 39S/PW930 DIA MB WH	(0.422,0.386)<2
910505102043	ST210T 27S/830 PSU MB BK	(0.434,0.403)<3
910505102044	ST210T 27S/830 PSU WB BK	(0.434,0.403)<3
910505102047	ST210T 39S/830 PSU MB BK	(0.434,0.403)<3
910505102048	ST210T 39S/830 PSU WB BK	(0.434,0.403)<3
910505102051	ST210T 27S/840 PSU MB BK	(0.382,0.380)<3
910505102052	ST210T 27S/840 PSU WB BK	(0.382,0.380)<3
910505102055	ST210T 39S/840 PSU MB BK	(0.382,0.380)<3
910505102056	ST210T 39S/840 PSU WB BK	(0.382,0.380)<3
910505102550	ST210T 27S/830 WIA MB BK	(0.434,0.403)<3

Order Code	Full Product Name	Initial chromaticity
910505102551	ST210T 27S/830 WIA WB BK	(0.434,0.403)<3
910505102554	ST210T 39S/830 WIA MB BK	(0.434,0.403)<3
910505102555	ST210T 39S/830 WIA WB BK	(0.434,0.403)<3
910505102558	ST210T 27S/840 WIA MB BK	(0.382,0.380)<3
910505102559	ST210T 27S/840 WIA WB BK	(0.382,0.380)<3
910505102562	ST210T 39S/840 WIA MB BK	(0.382,0.380)<3
910505102563	ST210T 39S/840 WIA WB BK	(0.382,0.380)<3
910505102041	ST210T 27S/830 PSU MB WH	(0.434,0.403)<3
910505102042	ST210T 27S/830 PSU WB WH	(0.434,0.403)<3
910505102045	ST210T 39S/830 PSU MB WH	(0.434,0.403)<3
910505102046	ST210T 39S/830 PSU WB WH	(0.434,0.403)<3
910505102049	ST210T 27S/840 PSU MB WH	(0.382,0.380)<3
910505102050	ST210T 27S/840 PSU WB WH	(0.382,0.380)<3
910505102053	ST210T 39S/840 PSU MB WH	(0.382,0.380)<3
910505102054	ST210T 39S/840 PSU WB WH	(0.382,0.380)<3
910505102548	ST210T 27S/830 WIA MB WH	(0.434,0.403)<3
910505102549	ST210T 27S/830 WIA WB WH	(0.434,0.403)<3
910505102552	ST210T 39S/830 WIA MB WH	(0.434,0.403)<3
910505102553	ST210T 39S/830 WIA WB WH	(0.434,0.403)<3
910505102556	ST210T 27S/840 WIA MB WH	(0.382,0.380)<3
910505102557	ST210T 27S/840 WIA WB WH	(0.382,0.380)<3
910505102560	ST210T 39S/840 WIA MB WH	(0.382,0.380)<3
910505102561	ST210T 39S/840 WIA WB WH	(0.382,0.380)<3

Product Data

Order Code	Full Product Name	Product family code	Order Code	Full Product Name	Product family code
910505102057	ST210Y 19S/FMT PSU MB WH	ST210Y	910505102551	ST210T 27S/830 WIA WB BK	ST210T
910505102058	ST210Y 19S/FMT DIA MB WH	ST210Y	910505102554	ST210T 39S/830 WIA MB BK	ST210T
910505102059	ST210Y 27S/830 PSU MB WH	ST210Y	910505102555	ST210T 39S/830 WIA WB BK	ST210T
910505102060	ST210Y 27S/830 DIA MB WH	ST210Y	910505102558	ST210T 27S/840 WIA MB BK	ST210T
910505102061	ST210Y 27S/840 PSU MB WH	ST210Y	910505102559	ST210T 27S/840 WIA WB BK	ST210T
910505102062	ST210Y 27S/840 DIA MB WH	ST210Y	910505102562	ST210T 39S/840 WIA MB BK	ST210T
910505102063	ST210Y 27S/PW930 PSU MB WH	ST210Y	910505102563	ST210T 39S/840 WIA WB BK	ST210T
910505102064	ST210Y 27S/PW930 DIA MB WH	ST210Y	910505102041	ST210T 27S/830 PSU MB WH	ST210T
910505102065	ST210Y 39S/830 PSU MB WH	ST210Y	910505102042	ST210T 27S/830 PSU WB WH	ST210T
910505102066	ST210Y 39S/830 DIA MB WH	ST210Y	910505102045	ST210T 39S/830 PSU MB WH	ST210T
910505102067	ST210Y 39S/840 PSU MB WH	ST210Y	910505102046	ST210T 39S/830 PSU WB WH	ST210T
910505102068	ST210Y 39S/840 DIA MB WH	ST210Y	910505102049	ST210T 27S/840 PSU MB WH	ST210T
910505102069	ST210Y 39S/PW930 PSU MB WH	ST210Y	910505102050	ST210T 27S/840 PSU WB WH	ST210T
910505102070	ST210Y 39S/PW930 DIA MB WH	ST210Y	910505102053	ST210T 39S/840 PSU MB WH	ST210T
910505102043	ST210T 27S/830 PSU MB BK	ST210T	910505102054	ST210T 39S/840 PSU WB WH	ST210T
910505102044	ST210T 27S/830 PSU WB BK	ST210T	910505102548	ST210T 27S/830 WIA MB WH	ST210T
910505102047	ST210T 39S/830 PSU MB BK	ST210T	910505102549	ST210T 27S/830 WIA WB WH	ST210T
910505102048	ST210T 39S/830 PSU WB BK	ST210T	910505102552	ST210T 39S/830 WIA MB WH	ST210T
910505102051	ST210T 27S/840 PSU MB BK	ST210T	910505102553	ST210T 39S/830 WIA WB WH	ST210T
910505102052	ST210T 27S/840 PSU WB BK	ST210T	910505102556	ST210T 27S/840 WIA MB WH	ST210T
910505102055	ST210T 39S/840 PSU MB BK	ST210T	910505102557	ST210T 27S/840 WIA WB WH	ST210T
910505102056	ST210T 39S/840 PSU WB BK	ST210T	910505102560	ST210T 39S/840 WIA MB WH	ST210T
910505102550	ST210T 27S/830 WIA MB BK	ST210T	910505102561	ST210T 39S/840 WIA WB WH	ST210T

