



Aesthetic, Comprehensive and Reliable

GreenUp Track

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Track product family offers a complete track light solutions with aesthetic and compact product design, comprehensive control availability and specification options. It offers an outstanding color rendering performance and glare control effect, tailored for retail and hospitality applications.

Benefits

- Aesthetic product design with compact and integrated concept.
- Comprehensive offerings to meet various application requirements.
- Outstanding color rendering performance and visual comfort design

Features

- Multiple options of lumen output, wattage and optics.
- Full control availability including on/off, 1-10v, triac and DALI.
- CRI 90, R9 \geq 50
- UGR 19, cut off angle 50°

Application




- Retail
- Hospitality
- Fashion

Versions



GreenUp Track

Dimensional drawing



Light Technical	
Color rendering index (CRI)	>90
Operating and Electrical	
Input Voltage	220~240 V
Line Frequency	50 or 60 Hz
Mechanical and Housing	
Optical cover type	Lens
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	No
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
52585699	ST306T P20 940 PSU WB WH BR	4000 K	90 lm/W	1,800 lm
52618199	ST306T P10 940 PSD WB WH SR	4000 K	90 lm/W	900 lm
52368599	ST306T P20 930 PSD WB WH SR	3000 K	85 lm/W	1,700 lm
51790599	ST306T P10 940 PSD NB BK BR	4000 K	90 lm/W	900 lm
52297899	ST306T P20 930 PSU WB BK BR	3000 K	85 lm/W	1,700 lm
52967099	ST306T P20 940 PSU WB BK BR	4000 K	90 lm/W	1,800 lm
52486699	ST306T P40 930 PSU WB BK BR	3000 K	93 lm/W	3,720 lm
52730099	ST306T P10 930 PSU WB BK SR	3000 K	85 lm/W	850 lm
52516099	ST306T P40 930 PSU WB BK SR	3000 K	93 lm/W	3,720 lm
52860499	ST306T P40 940 PSU WB BK SR	4000 K	95 lm/W	3,800 lm

Operating and Electrical

Order Code	Full Product Name	Protection class IEC	Power
			Consumption
52585699	ST306T P20 940 PSU WB WH BR	Safety class II	20 W
52618199	ST306T P10 940 PSD WB WH SR	Safety class I	10 W
52368599	ST306T P20 930 PSD WB WH SR	Safety class I	20 W
51790599	ST306T P10 940 PSD NB BK BR	Safety class I	10 W
52297899	ST306T P20 930 PSU WB BK BR	Safety class II	20 W

Order Code	Full Product Name	Protection class IEC	Power
			Consumption
52967099	ST306T P20 940 PSU WB BK BR	Safety class II	20 W
52486699	ST306T P40 930 PSU WB BK BR	Safety class II	40 W
52730099	ST306T P10 930 PSU WB BK SR	Safety class II	10 W
52516099	ST306T P40 930 PSU WB BK SR	Safety class II	40 W
52860499	ST306T P40 940 PSU WB BK SR	Safety class II	40 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
52585699	ST306T P20 940 PSU WB WH BR	No
52618199	ST306T P10 940 PSD WB WH SR	Yes
52368599	ST306T P20 930 PSD WB WH SR	Yes
51790599	ST306T P10 940 PSD NB BK BR	Yes
52297899	ST306T P20 930 PSU WB BK BR	No

Order Code	Full Product Name	Dimmable
52967099	ST306T P20 940 PSU WB BK BR	No
52486699	ST306T P40 930 PSU WB BK BR	No
52730099	ST306T P10 930 PSU WB BK SR	No
52516099	ST306T P40 930 PSU WB BK SR	No
52860499	ST306T P40 940 PSU WB BK SR	No

Mechanical and Housing

Order Code	Full Product Name	Housing Color
52585699	ST306T P20 940 PSU WB WH BR	White
52618199	ST306T P10 940 PSD WB WH SR	White
52368599	ST306T P20 930 PSD WB WH SR	White
51790599	ST306T P10 940 PSD NB BK BR	Black
52297899	ST306T P20 930 PSU WB BK BR	Black

Order Code	Full Product Name	Housing Color
52967099	ST306T P20 940 PSU WB BK BR	Black
52486699	ST306T P40 930 PSU WB BK BR	Black
52730099	ST306T P10 930 PSU WB BK SR	Black
52516099	ST306T P40 930 PSU WB BK SR	Black
52860499	ST306T P40 940 PSU WB BK SR	Black

