



A powerful and sustainable all-rounder for retail applications

GreenSpace Evo

GreenSpace Evo Projector is a powerful and flexible projector for retail with a subtle and neutral design. The 3D printed housing is crafted from at least 65% recycled or bio-circular materials, while the heatsink is made from 85% recycled aluminium. Because of its circular design, the luminaire is upgradable, reusable, fully serviceable and recyclable. Combined with the high energy efficiency, this makes the GreenSpace Evo a sustainable projector choice. The PerfectAccent reflectors ensure a light effect with increased sparkle and improved shopper eye comfort. GreenSpace Evo also comes in state-of-the-art ultra-efficient variants and integrates seamlessly onto 3C- and DALI-tracks, CoreLine Trunking and Maxos fusion. Further customization of colors and textures is possible via Philips MyCreation

Benefits

- Blends into stores with a clean and neutral design
- More sparkle and enhanced shopper eye comfort with PerfectAccent reflectors
- Extend the useful life of the product with easy serviceability and upgradeability
- The recycled materials and high energy efficiency help further reduce the carbon footprint of the product

Features

- Toolless access to the optics, LED and front glass
- Serviceable and upgradeable with standard tools
- Reduced carbon footprint due to high efficacy (ultra-efficient versions available)
- Equipped with state-of-the-art PerfectAccent reflectors
- Very broad aiming flexibility, including upward lighting
- Connectivity options: Interact compatible DALI (DIA), Indoor positioning (DIA-VLC) and Wireless (WIA)
- Optional front glass (recommended for dusty environments)

Application

- Food and Large Retailers
- Fashion
- Petrol and Convenience

Warnings and Safety

- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For food preparation areas and areas with high levels of dust, the use of the optional front glass is strongly advised, as it can be cleaned with a (dry) microfiber cloth
- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove


Versions




ST333X2 GreenSpace Evo
Projector double spotlight for
Maxos fusion, black

Dimensional drawing


Flux	CCT	B (mm)
205	827/830/840/PW930/PW940/PC930	126
195	FMT/Rose	
275	827/CH/830/840/PW930/PW940/PC930	
395	827/CH/830/840/PW930/PW940	
275	FMT/Rose/FR	149
395	FR/PC930	
495	827/830/840/PW930/PW940	



Flux	CCT	B (mm)
205	827/830/840/PW930/PW940/PC930	126
195	FMT/Rose	
275	827/CH/830/840/PW930/PW940/PC930	
395	827/CH/830/840/PW930/PW940	
275	FMT/Rose/FR	149
395	FR/PC930	
495	827/830/840/PW930/PW940	



Dimensional drawing



Product details



ST333T GreenSpace Evo Projector
grey



ST333T GreenSpace Evo Projector
white



ST333T GreenSpace Evo Projector
black

General Information	
Driver included	Yes
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	210 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable
Mechanical and Housing	
Mech. impact protection code	IK02
Ingress protection code	IP20
Emergency Operation	
Central Emergency	No
Approval and Application	
Ambient temperature range	+10 to +25 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Number of gear units
59082300	ST333T 20S/PC930 PSU NB WH481	1 unit
59084700	ST333T 27S/827 PSU WB WH481	1 unit
59085400	ST333T 27S/830 PSU WB WH481	1 unit
59086100	ST333T 27S/840 PSU WB WH481	1 unit
59088500	ST333T 27S/PW930 UE PSU HWB WH481	1 unit
59089200	ST333T 27S/PW930 UE DIA-VLC HWB WH481	1 unit
59092200	ST333T 27S/CH DIA MB FG WH481	1 unit
59093900	ST333T 27S/FMT DIA MB FG WH481	1 unit
59094600	ST333T 27S/ROSE WIA MB FG WH481	1 unit
59095300	ST333T 27S/FR WIA MB FG WH481	1 unit
59096000	ST333T 39S/830 PSU WB WH481	1 unit
59097700	ST333T 39S/830 DIA-VLC WB WH481	1 unit
83501600	ST333T 39S/PW930 UE PSU HWB WH481	1 unit
83502300	ST333T 39S/PW930 UE DIA-VLC HWB WH481	1 unit
83503000	ST333T 49S/830 PSU WB WH481	1 unit
83509200	ST333Y2 27S/830 PSU WB WH481	2 units
83510800	ST333Y2 27S/PW930 DIA HRCT WH481	2 units
83511500	ST333Y2 39S/830 PSU WB WH481	2 units
83512200	ST333Y2 39S/PW930 DIA HRCT WH481	2 units
59090800	ST333T 27S/PW940 PSU HMB GR482	1 unit
59099100	ST333T 39S/PW940 PSU WB GR482	1 unit
59080900	ST333T 19S/FMT WIA HMB BK482	1 unit
59081600	ST333T 19S/ROSE WIA HMB BK482	1 unit
59083000	ST333T 20S/PW930 PSU HNB BK482	1 unit
59087800	ST333T 27S/PW930 PSU HRCT BK482	1 unit
59091500	ST333T 27S/PC930 PSU HMB FG BK482	1 unit
59098400	ST333T 39S/PW930 PSU HRCT BK482	1 unit
83500900	ST333T 39S/PC930 PSU WB BK482	1 unit
83504700	ST333T 49S/PW930 PSU WB BK482	1 unit
83505400	ST333X2 27S/830 PSU WB WH481	2 units
83507800	ST333X2 39S/830 PSU WB WH481	2 units
83506100	ST333X2 27S/PW930 DIA HMB BK482	2 units
83508500	ST333X2 39S/PW930 DIA HMB BK482	2 units

Light Technical (1/2)

		Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux			Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
Order Code	Full Product Name					Order Code	Full Product Name				
59082300	ST333T 20S/PC930 PSU NB WH481	3000 K	90	105 lm/W	2,100 lm	59088500	ST333T 27S/PW930 UE PSU HWB WH481	3000 K	90	155 lm/W	2,700 lm
59084700	ST333T 27S/827 PSU WB WH481	2700 K	80	133 lm/W	2,800 lm	59089200	ST333T 27S/PW930 UE DIA-VLC HWB WH481	3000 K	90	144 lm/W	2,800 lm
59085400	ST333T 27S/830 PSU WB WH481	3000 K	80	144 lm/W	2,700 lm	59092200	ST333T 27S/CH DIA MB FG WH481	2700 K	80	127 lm/W	2,800 lm
59086100	ST333T 27S/840 PSU WB WH481	4000 K	80	149 lm/W	2,800 lm						

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
59093900	ST333T 27S/FMT DIA MB FG WH481	3000 K	90	78 lm/W	2,600 lm
59094600	ST333T 27S/ ROSE WIA MB FG WH481	2200 K	80	85 lm/W	2,600 lm
59095300	ST333T 27S/FR WIA MB FG WH481	5000 K	90	85 lm/W	2,800 lm
59096000	ST333T 39S/830 PSU WB WH481	3000 K	80	143 lm/W	4,000 lm
59097700	ST333T 39S/830 DIA- VLC WB WH481	3000 K	80	133 lm/W	4,000 lm
83501600	ST333T 39S/ PW930 UE PSU HWB WH481	3000 K	90	159 lm/W	3,900 lm
83502300	ST333T 39S/ PW930 UE DIA- VLC HWB WH481	3000 K	90	147 lm/W	3,900 lm
83503000	ST333T 49S/830 PSU WB WH481	3000 K	80	132 lm/W	4,900 lm
83509200	ST333Y2 27S/830 PSU WB WH481	3000 K	80	137 lm/W	5,400 lm
83510800	ST333Y2 27S/ PW930 DIA HRCT WH481	3000 K	90	131 lm/W	5,800 lm
83511500	ST333Y2 39S/830 PSU WB WH481	3000 K	80	134 lm/W	8,000 lm
83512200	ST333Y2 39S/ PW930 DIA HRCT WH481	3000 K	90	134 lm/W	7,800 lm
59090800	ST333T 27S/ PW940 PSU HMB GR482	4000 K	90	149 lm/W	2,800 lm

Light Technical (2/2)

Order Code	Full Product Name	Optic type
59082300	ST333T 20S/PC930 PSU NB WH481	Narrow beam
59084700	ST333T 27S/827 PSU WB WH481	Wide beam
59085400	ST333T 27S/830 PSU WB WH481	Wide beam
59086100	ST333T 27S/840 PSU WB WH481	Wide beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
59099100	ST333T 39S/ PW940 PSU WB GR482	4000 K	90	143 lm/W	4,000 lm
59080900	ST333T 19S/FMT WIA HMB BK482	3000 K	90	75 lm/W	1,900 lm
59081600	ST333T 19S/ ROSE WIA HMB BK482	2200 K	80	95 lm/W	1,900 lm
59083000	ST333T 20S/ PW930 PSU HNB BK482	3000 K	90	118 lm/W	2,200 lm
59087800	ST333T 27S/ PW930 PSU HRCT BK482	3000 K	90	138 lm/W	2,900 lm
59091500	ST333T 27S/ PC930 PSU HMB FG BK482	3000 K	90	122 lm/W	2,800 lm
59098400	ST333T 39S/ PW930 PSU HRCT BK482	3000 K	90	139 lm/W	3,900 lm
83500900	ST333T 39S/ PC930 PSU WB BK482	3000 K	90	115 lm/W	3,900 lm
83504700	ST333T 49S/ PW930 PSU WB BK482	3000 K	90	122 lm/W	5,000 lm
83505400	ST333X2 27S/830 PSU WB WH481	3000 K	80	137 lm/W	5,400 lm
83507800	ST333X2 39S/830 PSU WB WH481	3000 K	80	134 lm/W	8,000 lm
83506100	ST333X2 27S/ PW930 DIA HMB BK482	3000 K	90	131 lm/W	5,800 lm
83508500	ST333X2 39S/ PW930 DIA HMB BK482	3000 K	90	134 lm/W	7,800 lm

Order Code	Full Product Name	Optic type
59088500	ST333T 27S/PW930 UE PSU HWB WH481	High-reflective metal reflector Wide beam 40 to 80 degrees
59089200	ST333T 27S/PW930 UE DIA- VLC HWB WH481	High-reflective metal reflector Wide beam 40 to 80 degrees
59092200	ST333T 27S/CH DIA MB FG WH481	Medium beam

Order Code	Full Product Name	Optic type
59093900	ST333T 27S/FMT DIA MB FG WH481	Medium beam
59094600	ST333T 27S/ROSE WIA MB FG WH481	Medium beam
59095300	ST333T 27S/FR WIA MB FG WH481	Medium beam
59096000	ST333T 39S/830 PSU WB WH481	Wide beam
59097700	ST333T 39S/830 DIA-VLC WB WH481	Wide beam
83501600	ST333T 39S/PW930 UE PSU HWB WH481	High-reflective metal reflector Wide beam 40 to 80 degrees
83502300	ST333T 39S/PW930 UE DIA-VLC HWB WH481	High-reflective metal reflector Wide beam 40 to 80 degrees
83503000	ST333T 49S/830 PSU WB WH481	Wide beam
83509200	ST333Y2 27S/830 PSU WB WH481	Wide beam
83510800	ST333Y2 27S/PW930 DIA HRCT WH481	High-reflective metal reflector Rectangular beam
83511500	ST333Y2 39S/830 PSU WB WH481	Wide beam
83512200	ST333Y2 39S/PW930 DIA HRCT WH481	High-reflective metal reflector Rectangular beam
59090800	ST333T 27S/PW940 PSU HMB GR482	High-reflective metal reflector Medium beam 20 to 40 degrees
59099100	ST333T 39S/PW940 PSU WB GR482	Wide beam
59080900	ST333T 19S/FMT WIA HMB BK482	High-reflective metal reflector Medium beam 20 to 40 degrees

Operating and Electrical

Order Code	Full Product Name	Power Consumption
59082300	ST333T 20S/PC930 PSU NB WH481	22 W
59084700	ST333T 27S/827 PSU WB WH481	22.5 W
59085400	ST333T 27S/830 PSU WB WH481	20.5 W
59086100	ST333T 27S/840 PSU WB WH481	20.5 W
59088500	ST333T 27S/PW930 UE PSU HWB WH481	19 W
59089200	ST333T 27S/PW930 UE DIA-VLC HWB WH481	18.8 W
59092200	ST333T 27S/CH DIA MB FG WH481	22 W
59093900	ST333T 27S/FMT DIA MB FG WH481	33.5 W
59094600	ST333T 27S/ROSE WIA MB FG WH481	30.5 W
59095300	ST333T 27S/FR WIA MB FG WH481	33 W
59096000	ST333T 39S/830 PSU WB WH481	31.5 W
59097700	ST333T 39S/830 DIA-VLC WB WH481	30 W
83501600	ST333T 39S/PW930 UE PSU HWB WH481	26.5 W
83502300	ST333T 39S/PW930 UE DIA-VLC HWB WH481	26.5 W
83503000	ST333T 49S/830 PSU WB WH481	39.5 W
83509200	ST333Y2 27S/830 PSU WB WH481	39.8 W
83510800	ST333Y2 27S/PW930 DIA HRCT WH481	43.5 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
59082300	ST333T 20S/PC930 PSU NB WH481	No
59084700	ST333T 27S/827 PSU WB WH481	No
59085400	ST333T 27S/830 PSU WB WH481	No
59086100	ST333T 27S/840 PSU WB WH481	No
59088500	ST333T 27S/PW930 UE PSU HWB WH481	No

Order Code	Full Product Name	Optic type
59081600	ST333T 19S/ROSE WIA HMB BK482	High-reflective metal reflector Medium beam 20 to 40 degrees
59083000	ST333T 20S/PW930 PSU HNB BK482	High-reflective metal reflector Narrow beam 10 to 20 degrees
59087800	ST333T 27S/PW930 PSU HRCT BK482	High-reflective metal reflector Rectangular beam
59091500	ST333T 27S/PC930 PSU HMB FG BK482	High-reflective metal reflector Medium beam 20 to 40 degrees
59098400	ST333T 39S/PW930 PSU HRCT BK482	High-reflective metal reflector Rectangular beam
83500900	ST333T 39S/PC930 PSU WB BK482	Wide beam
83504700	ST333T 49S/PW930 PSU WB BK482	Wide beam
83505400	ST333X2 27S/830 PSU WB WH481	Wide beam
83507800	ST333X2 39S/830 PSU WB WH481	Wide beam
83506100	ST333X2 27S/PW930 DIA HMB BK482	High-reflective metal reflector Medium beam 20 to 40 degrees
83508500	ST333X2 39S/PW930 DIA HMB BK482	High-reflective metal reflector Medium beam 20 to 40 degrees

Order Code	Full Product Name	Power Consumption
83511500	ST333Y2 39S/830 PSU WB WH481	59 W
83512200	ST333Y2 39S/PW930 DIA HRCT WH481	57.5 W
59090800	ST333T 27S/PW940 PSU HMB GR482	20.5 W
59099100	ST333T 39S/PW940 PSU WB GR482	29.5 W
59080900	ST333T 19S/FMT WIA HMB BK482	25.5 W
59081600	ST333T 19S/ROSE WIA HMB BK482	20 W
59083000	ST333T 20S/PW930 PSU HNB BK482	19.6 W
59087800	ST333T 27S/PW930 PSU HRCT BK482	22.5 W
59091500	ST333T 27S/PC930 PSU HMB FG BK482	25 W
59098400	ST333T 39S/PW930 PSU HRCT BK482	29.5 W
83500900	ST333T 39S/PC930 PSU WB BK482	35 W
83504700	ST333T 49S/PW930 PSU WB BK482	41 W
83505400	ST333X2 27S/830 PSU WB WH481	39.8 W
83507800	ST333X2 39S/830 PSU WB WH481	59 W
83506100	ST333X2 27S/PW930 DIA HMB BK482	43.5 W
83508500	ST333X2 39S/PW930 DIA HMB BK482	57.5 W

Order Code	Full Product Name	Dimmable
59089200	ST333T 27S/PW930 UE DIA-VLC HWB WH481	Yes
59092200	ST333T 27S/CH DIA MB FG WH481	Yes
59093900	ST333T 27S/FMT DIA MB FG WH481	Yes
59094600	ST333T 27S/ROSE WIA MB FG WH481	Yes
59095300	ST333T 27S/FR WIA MB FG WH481	Yes

Order Code	Full Product Name	Dimmable
59096000	ST333T 39S/830 PSU WB WH481	No
59097700	ST333T 39S/830 DIA-VLC WB WH481	Yes
83501600	ST333T 39S/PW930 UE PSU HWB WH481	No
83502300	ST333T 39S/PW930 UE DIA-VLC HWB WH481	Yes
83503000	ST333T 49S/830 PSU WB WH481	No
83509200	ST333Y2 27S/830 PSU WB WH481	No
83510800	ST333Y2 27S/PW930 DIA HRCT WH481	Yes
83511500	ST333Y2 39S/830 PSU WB WH481	No
83512200	ST333Y2 39S/PW930 DIA HRCT WH481	Yes
59090800	ST333T 27S/PW940 PSU HMB GR482	No
59099100	ST333T 39S/PW940 PSU WB GR482	No
59080900	ST333T 19S/FMT WIA HMB BK482	Yes

Order Code	Full Product Name	Dimmable
59081600	ST333T 19S/ROSE WIA HMB BK482	Yes
59083000	ST333T 20S/PW930 PSU HNB BK482	No
59087800	ST333T 27S/PW930 PSU HRCT BK482	No
59091500	ST333T 27S/PC930 PSU HMB FG BK482	No
59098400	ST333T 39S/PW930 PSU HRCT BK482	No
83500900	ST333T 39S/PC930 PSU WB BK482	No
83504700	ST333T 49S/PW930 PSU WB BK482	No
83505400	ST333X2 27S/830 PSU WB WH481	No
83507800	ST333X2 39S/830 PSU WB WH481	No
83506100	ST333X2 27S/PW930 DIA HMB BK482	Yes
83508500	ST333X2 39S/PW930 DIA HMB BK482	Yes

Mechanical and Housing

Order Code	Full Product Name	Housing Color
59082300	ST333T 20S/PC930 PSU NB WH481	White
59084700	ST333T 27S/827 PSU WB WH481	White
59085400	ST333T 27S/830 PSU WB WH481	White
59086100	ST333T 27S/840 PSU WB WH481	White
59088500	ST333T 27S/PW930 UE PSU HWB WH481	White
59089200	ST333T 27S/PW930 UE DIA-VLC HWB WH481	White
59092200	ST333T 27S/CH DIA MB FG WH481	White
59093900	ST333T 27S/FMT DIA MB FG WH481	White
59094600	ST333T 27S/ROSE WIA MB FG WH481	White
59095300	ST333T 27S/FR WIA MB FG WH481	White
59096000	ST333T 39S/830 PSU WB WH481	White
59097700	ST333T 39S/830 DIA-VLC WB WH481	White
83501600	ST333T 39S/PW930 UE PSU HWB WH481	White
83502300	ST333T 39S/PW930 UE DIA-VLC HWB WH481	White
83503000	ST333T 49S/830 PSU WB WH481	White
83509200	ST333Y2 27S/830 PSU WB WH481	White
83510800	ST333Y2 27S/PW930 DIA HRCT WH481	White

Order Code	Full Product Name	Housing Color
83511500	ST333Y2 39S/830 PSU WB WH481	White
83512200	ST333Y2 39S/PW930 DIA HRCT WH481	White
59090800	ST333T 27S/PW940 PSU HMB GR482	Gray
59099100	ST333T 39S/PW940 PSU WB GR482	Gray
59080900	ST333T 19S/FMT WIA HMB BK482	Black
59081600	ST333T 19S/ROSE WIA HMB BK482	Black
59083000	ST333T 20S/PW930 PSU HNB BK482	Black
59087800	ST333T 27S/PW930 PSU HRCT BK482	Black
59091500	ST333T 27S/PC930 PSU HMB FG BK482	Black
59098400	ST333T 39S/PW930 PSU HRCT BK482	Black
83500900	ST333T 39S/PC930 PSU WB BK482	Black
83504700	ST333T 49S/PW930 PSU WB BK482	Black
83505400	ST333X2 27S/830 PSU WB WH481	White
83507800	ST333X2 39S/830 PSU WB WH481	White
83506100	ST333X2 27S/PW930 DIA HMB BK482	Black
83508500	ST333X2 39S/PW930 DIA HMB BK482	Black

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
59082300	ST333T 20S/PC930 PSU NB WH481	(0.422, 0.386)
59084700	ST333T 27S/827 PSU WB WH481	(0.458, 0.410)
59085400	ST333T 27S/830 PSU WB WH481	(0.434, 0.403)
59086100	ST333T 27S/840 PSU WB WH481	(0.382,0.380)
59088500	ST333T 27S/PW930 UE PSU HWB WH481	(0.422, 0.386)
59089200	ST333T 27S/PW930 UE DIA-VLC HWB WH481	(0.422, 0.386)
59092200	ST333T 27S/CH DIA MB FG WH481	(0.458, 0.410)
59093900	ST333T 27S/FMT DIA MB FG WH481	(0.457,0.385)
59094600	ST333T 27S/ROSE WIA MB FG WH481	(0.457,0.385)
59095300	ST333T 27S/FR WIA MB FG WH481	(0.343,0.331)
59096000	ST333T 39S/830 PSU WB WH481	(0.434, 0.403)
59097700	ST333T 39S/830 DIA-VLC WB WH481	(0.434, 0.403)
83501600	ST333T 39S/PW930 UE PSU HWB WH481	(0.422, 0.386)
83502300	ST333T 39S/PW930 UE DIA-VLC HWB WH481	(0.422, 0.386)

Order Code	Full Product Name	Initial chromaticity
83503000	ST333T 49S/830 PSU WB WH481	(0.434, 0.403)
83509200	ST333Y2 27S/830 PSU WB WH481	(0.434, 0.403)
83510800	ST333Y2 27S/PW930 DIA HRCT WH481	(0.422, 0.386)
83511500	ST333Y2 39S/830 PSU WB WH481	(0.434, 0.403)
83512200	ST333Y2 39S/PW930 DIA HRCT WH481	(0.422, 0.386)
59090800	ST333T 27S/PW940 PSU HMB GR482	(0.374,0.364)
59099100	ST333T 39S/PW940 PSU WB GR482	(0.374,0.364)
59080900	ST333T 19S/FMT WIA HMB BK482	(0.457,0.385)
59081600	ST333T 19S/ROSE WIA HMB BK482	(0.457,0.385)
59083000	ST333T 20S/PW930 PSU HNB BK482	(0.422, 0.386)
59087800	ST333T 27S/PW930 PSU HRCT BK482	(0.422, 0.386)
59091500	ST333T 27S/PC930 PSU HMB FG BK482	(0.422, 0.386)
59098400	ST333T 39S/PW930 PSU HRCT BK482	(0.422, 0.386)
83500900	ST333T 39S/PC930 PSU WB BK482	(0.422, 0.386)

Order Code	Full Product Name	Initial chromaticity
83504700	ST333T 49S/PW930 PSU WB BK482	(0.422, 0.386)
83505400	ST333X2 27S/830 PSU WB WH481	(0.434, 0.403)
83507800	ST333X2 39S/830 PSU WB WH481	(0.434, 0.403)




Order Code	Full Product Name	Initial chromaticity
83506100	ST333X2 27S/PW930 DIA HMB BK482	(0.422, 0.386)
83508500	ST333X2 39S/PW930 DIA HMB BK482	(0.422, 0.386)

Product Data

Order Code	Full Product Name	Product family code
59082300	ST333T 20S/PC930 PSU NB WH481	ST333T
59084700	ST333T 27S/827 PSU WB WH481	ST333T
59085400	ST333T 27S/830 PSU WB WH481	ST333T
59086100	ST333T 27S/840 PSU WB WH481	ST333T
59088500	ST333T 27S/PW930 UE PSU HWB WH481	ST333T
59089200	ST333T 27S/PW930 UE DIA-VLC HWB WH481	ST333T
59092200	ST333T 27S/CH DIA MB FG WH481	ST333T
59093900	ST333T 27S/FMT DIA MB FG WH481	ST333T
59094600	ST333T 27S/ROSE WIA MB FG WH481	ST333T
59095300	ST333T 27S/FR WIA MB FG WH481	ST333T
59096000	ST333T 39S/830 PSU WB WH481	ST333T
59097700	ST333T 39S/830 DIA-VLC WB WH481	ST333T
83501600	ST333T 39S/PW930 UE PSU HWB WH481	ST333T
83502300	ST333T 39S/PW930 UE DIA-VLC HWB WH481	ST333T
83503000	ST333T 49S/830 PSU WB WH481	ST333T
83509200	ST333Y2 27S/830 PSU WB WH481	ST333Y2
83510800	ST333Y2 27S/PW930 DIA HRCT WH481	ST333Y2

Order Code	Full Product Name	Product family code
83511500	ST333Y2 39S/830 PSU WB WH481	ST333Y2
83512200	ST333Y2 39S/PW930 DIA HRCT WH481	ST333Y2
59090800	ST333T 27S/PW940 PSU HMB GR482	ST333T
59099100	ST333T 39S/PW940 PSU WB GR482	ST333T
59080900	ST333T 19S/FMT WIA HMB BK482	ST333T
59081600	ST333T 19S/ROSE WIA HMB BK482	ST333T
59083000	ST333T 20S/PW930 PSU HNB BK482	ST333T
59087800	ST333T 27S/PW930 PSU HRCT BK482	ST333T
59091500	ST333T 27S/PC930 PSU HMB FG BK482	ST333T
59098400	ST333T 39S/PW930 PSU HRCT BK482	ST333T
83500900	ST333T 39S/PC930 PSU WB BK482	ST333T
83504700	ST333T 49S/PW930 PSU WB BK482	ST333T
83505400	ST333X2 27S/830 PSU WB WH481	ST333X2
83507800	ST333X2 39S/830 PSU WB WH481	ST333X2
83506100	ST333X2 27S/PW930 DIA HMB BK482	ST333X2
83508500	ST333X2 39S/PW930 DIA HMB BK482	ST333X2

Polar Wide Diagrams




Polar Normal (separate) - ST333TI - 910505104625


Polar Normal (separate) - ST333TI - 910505104610

Polar Normal (separate) - ST333TI - 910505104594


Polar Wide Diagrams




Polar Normal (separate) - ST333TI - 910505104616




Polar Normal (separate) - ST333TI - 910505104607




Polar Normal (separate) - ST333TI - 910505104615




Polar Normal (separate) - ST333TI - 910505104602




Polar Normal (separate) - ST333TI - 910505104592




Polar Normal (separate) - ST333TI - 910505104606



Polar Normal (separate) - ST333TI - 910505104599




Polar Normal (separate) - ST333TI - 910505104609




Polar Normal (separate) - ST333TI - 910505104593


Polar Wide Diagrams




Polar Normal (separate) - ST333TI - 910505104597




Polar Normal (separate) - ST333TI - 910505104624




Polar Normal (separate) - ST333TI - 910505104608




Polar Normal (separate) - ST333TI - 910505104604




Polar Normal (separate) - ST333TI - 910505104614




Polar Normal (separate) - ST333TI - 910505104620



Polar Normal (separate) - ST333TI - 910505104605




Polar Normal (separate) - ST333TI - 910505104601




Polar Normal (separate) - ST333TI - 910505104618


Polar Wide Diagrams




Polar Normal (separate) - ST333TI - 910505104611




Polar Normal (separate) - ST333TI - 910505104623




Polar Normal (separate) - ST333TI - 910505104612




Polar Normal (separate) - ST333TI - 910505104595




Polar Normal (separate) - ST333TI - 910505104622




Polar Normal (separate) - ST333TI - 910505104598



Polar Normal (separate) - ST333TI - 910505104603




Polar Normal (separate) - ST333TI - 910505104596




Polar Normal (separate) - ST333TI - 910505104617


Polar Wide Diagrams



Polar Normal (separate) - ST333TI -
910505104613



Polar Normal (separate) - ST333TI -
910505104619



Polar Normal (separate) - ST333TI -
910505104621

