



Energy saving elegance with improved lumens and design versatility

Candle LED

Philips Candle Dimmable LED Lamps offer decorative energy saving ambience with the elegant effect of incandescent candles. Available in bent, blunt and flame tip candles, their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

Benefits

- Long life properties-- lowers maintenance costs by reducing re-lamp frequency
- Installs into existing candelabra and medium-base fixtures
- Will not fade colors, avoids inventory spoilage
- Contains no mercury
- Emits virtually no UV/IR light in beam
- 3-year or 5-year limited warranty depending upon operating hours

Features

- Dimmable* and non-dimmable versions available
- Clear design available in bent, blunt and flame tip
- 25,000-hour rated average life⁺ for 3.5W Philips LED candle
- ^{*}Dimmable when using leading edge dimmers (see Philips Website: www.philips.com/ledtechguide for compatible leading edge dimmers.)
- ⁺Rated average life based on engineering testing and probability analysis.

Candle LED

Application


- Ideal for wall sconces, chandeliers and decorative lighting in retail, office, and hospitality spaces.

Versions



LEDcandle 25W E14 T25 Frosted
827 16D ND

Dimensional drawing



| Product | D | C |
|--------------------------------|-------|-------|
| LED 25W T25 E14 WW FR ND 1SRT4 | 25 mm | 71 mm |



Candle LED

