



Ο πιο φωτεινός φωτισμός φθορισμού στον κόσμο

MASTER TL5 Υψηλής Φωτεινής Ροής

Αυτός ο λαμπτήρας TL5 (διάμετρος σωλήνα 16 mm) προσφέρει υψηλή φωτεινή ροή. Ο λαμπτήρας TL5 HO έχει βελτιστοποιηθεί για εγκαταστάσεις που απαιτούν υψηλή φωτεινή ροή, ενώ προσφέρει εξαιρετική διατήρηση φωτεινής ροής και απόδοση χρωμάτων. Οι εφαρμογές του περιλαμβάνουν από γραφεία και βιομηχανία, έως σχολεία και χώρους λιανικής πώλησης.

Οφέλη

- Allows system miniaturization and maximum luminaire design freedom
- Lamp lengths enable easy fitting into ceiling module systems
- Optimized for installations which need high luminous flux
- Virtually constant lumen level with excellent lumen maintenance
- Good color rendering

Χαρακτηριστικά

- 40% thinner than TL-D lamps
- Designed for high light output and system miniaturization
- Highly efficient 3-band fluorescent coating in combination with precoating
- Specifically designed for operation with electronic gear and well-suited for dimming
- Maximum light output reached at approximately 35 °C in free-burning position if an electronic driver with cut-off feature is used
- Can be ignited from -15 to +50 °C

MASTER TL5 Υψηλής Φωτεινής Ροής

Εφαρμογή

- The combination of a compact lamp and high lumen package of the MASTER TL5 HO offers exciting opportunities for architectural lighting and customized solutions
- Offers economic solutions with high-ceiling lighting in shops, industry and department stores
- The high luminous flux gives optimal results in aesthetic pendants and furniture-mounted luminaires in offices, workshops, restaurants and reception areas

Προειδοποίηση & ασφάλεια


- Ένας λαμπτήρας που σπάει είναι εξαιρετικά απίθανο να έχει επίδραση στην υγεία σας. Εάν σπάσει ένας λαμπτήρας, αερίστε τον χώρο για 30 λεπτά και αφαιρέστε τα σπασμένα κομμάτια, κατά προτίμηση με γάντια. Τοποθετήστε τα σε μια πλαστική σακούλα, κλείστε τη καλά και αποθέστε τη στα προς ανακύκλωση απορρίμματα της περιοχής σας. Μην χρησιμοποιείτε ηλεκτρική σκούπα.

Versions



LPPR TL5-HO8

Σχεδιάγραμμα διαστάσεων



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 24W/840 SLV/40	17 mm	549,0 mm	556,1 mm	553,7 mm	563,2 mm

MASTER TL5 Υψηλής Φωτεινής Ροής

