



# Efficient fluorescent lighting with improved color rendering

## TL-D LIFEMAX Super 80

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

### Benefits

- Good color rendering
- Relatively high efficacy, both initially and during lamp lifetime, with high lumen maintenance
- Create atmospheres from warm white to cool daylight

### Features

- Highly efficient 3-band fluorescent coating
- High initial light output compared with standard colors
- Low mercury dose
- Can be used with conventional or electronic gear
- Higher efficacy is achieved with electronic gear

### Application

- Suitable for use in a wide range of luminaires for TL-D fluorescent lamps for 'human' applications such as schools, offices, shops, factory halls etc.


### Versions



18 W G13 Linear fluorescent tube - RFT

# TL-D LIFEMAX Super 80

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
30 W G13 Cool white Linear fluorescent tube	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8 mm

