



Efficient fluorescent lighting with improved color rendering

TL-D LIFEMAX Super 80

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

优点

- Good color rendering
- Relatively high efficacy, both initially and during lamp lifetime, with high lumen maintenance
- Create atmospheres from warm white to cool daylight

特点

- Highly efficient 3-band fluorescent coating
- High initial light output compared with standard colors
- Low mercury dose
- Can be used with conventional or electronic gear
- Higher efficacy is achieved with electronic gear

应用

- Suitable for use in a wide range of luminaires for TL-D fluorescent lamps for 'human' applications such as schools, offices, shops, factory halls etc.

TL-D LIFEMAX Super 80

二维绘图



Product	D (max)	A (max)	B (max)	B (min)	C (max)
18 W G13 Warm white Linear fluorescent tube	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
30 W G13 Cool daylight Linear fluorescent tube	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8 mm
30 W G13 Cool white Linear fluorescent tube	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8 mm
58 W G13 Cool daylight Linear fluorescent tube	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm
58 W G13 Cool white Linear fluorescent tube	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

一般資訊	
燈座基底	G13
標稱使用壽命	15,000 h
控制與調光	
可調光	是
機械與外罩	
燈泡形狀	T8
認證與應用	
汞 (Hg) 含量 (標稱)	2.0 mg

照明技術

Order Code	Full Product Name	色彩名稱	相關色溫 (標稱)	演色性指數 (CRI)	光效 (額定) (標準)
927980283036	18 W G13 Warm white Linear fluorescent tube	暖白光 (WW)	3000 K	83	75 lm/W
927981284036	30 W G13 Cool white Linear fluorescent tube	冷白光 (CW)	4000 K	82	80 lm/W
927981286536	30 W G13 Cool daylight Linear fluorescent tube	冷日光色	6500 K	80	77 lm/W

Order Code	Full Product Name	色彩名稱	相關色溫 (標稱)	演色性指數 (CRI)	光效 (額定) (標準)
927983284036	58 W G13 Cool white Linear fluorescent tube	冷白光 (CW)	4000 K	82	88 lm/W
927983286536	58 W G13 Cool daylight Linear fluorescent tube	冷日光色	6500 K	80	82 lm/W

運轉與電力

Order Code	Full Product Name	燈具電流 (標稱)	電壓 (標稱)	耗電量
927980283036	18 W G13 Warm white Linear fluorescent tube	0.360 A	59 V	18 W
927981284036	30 W G13 Cool white Linear fluorescent tube	0.360 A	98 V	30 W
927981286536	30 W G13 Cool daylight Linear fluorescent tube	0.360 A	98 V	30 W

Order Code	Full Product Name	燈具電流 (標稱)	電壓 (標稱)	耗電量
927983284036	58 W G13 Cool white Linear fluorescent tube	0.670 A	111 V	58.5 W
927983286536	58 W G13 Cool daylight Linear fluorescent tube	0.670 A	111 V	58 W

TL-D LIFEMAX Super 80

