



Product Description

TL-D Standard Colours

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Benefits

- Create atmospheres from warm white to cool daylight

Features

- Standard colours with moderate colour rendering
- Available in various colour designations

Application

- Suitable for use in a wide range of luminaires for TL-D fluorescent lamps, used in applications where colour rendering is not an important factor

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Versions



LPPR TL-DSTD G13

TL-D Standard Colours

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 10W/33-640 1SL/25	28 mm	331.5 mm	338.6 mm	336.2 mm	345.7 mm
TL-D 15W/33-640 1SL/9	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

General Information	
Cap-Base	G13
Light Technical	
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg

Light Technical

Order Code	Full Product Name	Color rendering index (CRI)	Luminous Flux
928024003331	TL-D 10W/33-640 1SL/25	60	440 lm

Order Code	Full Product Name	Color rendering index (CRI)	Luminous Flux
928024803347	TL-D 15W/33-640 1SL/9	63	830 lm

Operating and Electrical

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
928024003331	TL-D 10W/33-640 1SL/25	0.230 A	46 V	10 W

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
928024803347	TL-D 15W/33-640 1SL/9	0.310 A	51 V	15.0 W

