



T12 lamp with reliable ignition

TL Rapid Start Standard Colours

The TL RS (Rapid Start) lamp (tube diameter 38 mm) has an external silicon coating. It is suitable for situations where high humidity requires fast and stable ignition but color rendering is not important. Rapid Start lamps can be ignited without a starter.

Benefits

- Creating atmospheres from warm white to cool daylight
- Fast, well-defined ignition at low temperatures

Features

- RS (Rapid Start) lamps with an external silicon coating
- Standard colors with moderate color rendering
- Available in varying color designations

Application

- Mostly used in applications where color rendering is not an important factor


TL Rapid Start Standard Colours

Versions



LPPR TL-RS G13

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 40W/54-765 RSYL 1SL/25	28.0 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

