



Product Description

TL-X XL

Single-pin low-pressure mercury discharge lamps with a tubular 38 mm envelope

Benefits

- In combination with a special lampholder all possible sparking effects during ignition are eliminated
- In combination with a special lampholder all possible sparking effects during ignition are eliminated
- Extended lifetime compared with standard TL lamps
- Extended lifetime compared with standard TL lamps

Features

- Provided with internal ignition strip for EM starterless operation or HF Non-preheat operation
- 40W and 65W lamps with internal ignition strip for instant start, non-preheat, starterless operation
- Special Fa6 lamp cap has a long and thick pin, requiring a special lampholder

Application

- Used in flameproof and increased-safety luminaires for both indoor and outdoor applications
- Used in flameproof and increased-safety luminaires for both indoor and outdoor applications
- Used in applications like (petro-)chemical industry, offshore, mines and any locations where traces of explosive gases may be found
- Used in applications like petro-chemical industry, offshore, mines and any locations where traces of explosive gases may be found

TL-X XL

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



LPPR TL-X

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-X XL 20W/33-640 SLV/25	40.5 mm	574 mm	592.5 mm	589 mm	611 mm
TL-X XL 40W/33-640 SLV/25	40.5 mm	1,183.5 mm	1,202 mm	1,198.5 mm	1,220.5 mm

TL-X XL

General Information	
Cap-Base	FA6
Light Technical	
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	60
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T12
Approval and Application	
Mercury (Hg) Content (Max)	12 mg
Mercury (Hg) Content (Nom)	12.0 mg

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
928037703332	TL-X XL 20W/33-640 SLV/25	47 lm/W	940 lm
928037903332	TL-X XL 40W/33-640 SLV/25	58 lm/W	2,300 lm

Operating and Electrical

Order Code	Full Product Name	Lamp	Voltage (Nom)	Power Consumption
		Current (Nom)		
928037703332	TL-X XL 20W/33-640 SLV/25	0.380 A	58 V	20.0 W

Order Code	Full Product Name	Lamp	Voltage (Nom)	Power Consumption
		Current (Nom)		
928037903332	TL-X XL 40W/33-640 SLV/25	0.430 A	103 V	40.0 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
928037703332	TL-X XL 20W/33-640 SLV/25	20 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
928037903332	TL-X XL 40W/33-640 SLV/25	40 kWh

