



Philips Ledinaire wall-mounted – For your everyday lighting jobs, effortless installation and reliable performance.

Ledinaire Wall-mounted gen2

Upgrade your lighting with Philips Ledinaire wall-mounted All-in. These wall-mounted luminaires offer exceptional flexibility of application and installation. All-in feature provides up to three lumen packages and three color temperature options in one luminaire. Installers can easily fit the luminaire according to the application need on site. And the easy installation process makes them the perfect choice for any space, whether you're an installer looking for a hassle-free solution or a business owner seeking to reduce energy costs. Integrated sensor options allow further energy saving with dipswitch dimming choices during no presence as well as sufficient daylight in the application. Experience the benefits of effortless installation, high efficiency, and versatile lighting with Ledinaire wall-mounted.

Benefits

- Philips quality and reliability
- Covers indoor and outdoor applications
- All-in as standard (multi-lumen & multi-CCT)
- Scene setting possibility on site depending on application
- High energy efficiency and savings with embedded controls
- Installation flexibility with cable entry options
- Unobtrusive design

Ledinaire Wall-mounted gen2


Features

- WL070V: high protection IP65/IK08, one size (ø300mm)
- WL070V: multi-lumen (1100lm-1700lm) and multi-CCT (3000K-4000K-6000K)
- WL060V: frameless decorative design, IP44, two sizes (ø300mm and ø350mm)
- WL060V: multi-lumen (1100lm-1700lm-2200lm) and multi-CCT (3000K-4000K)
- Efficacy up to 105lm/W
- Through wiring possible as standard
- Optional integrated presence and daylight sensor (MDU)
- Included frame to hide the screws (WL070V)
- Black frame option

Application

- Offices
- Parking Garages
- Corridors
- Staircases

Dimensional drawing



WL070 D300

Product details



Ledinaire wall-mounted gen2
WL070V side view



Ledinaire wall-mounted gen2
WL070V top view

Ledinaire Wall-mounted gen2

Product details



Ledinaire wall-mounted gen2
WL070V back view

General Information	
Driver included	Yes
Number of gear units	1 unit
Light Technical	
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	80
Luminous Efficacy (rated) (Nom)	105 lm/W
Luminous Flux	1,150 lm
Optic type	Opal
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	17 W
Mechanical and Housing	
Housing Color	White RAL 9003
Mech. impact protection code	IK08
Ingress protection code	IP65
Approval and Application	
Ambient temperature range	-20 °C to 40 °C
CE mark	Yes
ENEC mark	-
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 850 °C, duration 30 s
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.40,0.40) SDCM<5
Luminous flux tolerance	+/-10%

Operating and Electrical

Order Code	Full Product Name	Suitable for random switching
76746199	WL070V gen2 11_17S/830_840_860 PSU	No
76747899	WL070V gen2 11_17S/830_840_860 PSU MDU	Yes (relates to presence/ movement detection and daylight harvesting)

Ledinaire Wall-mounted gen2

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
76746199	WL070V gen2 11_17S/830_840_860 PSU	No	76747899	WL070V gen2 11_17S/830_840_860 PSU MDU	Yes

